

LFD18829MMP2E093



Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Consumer equipment, Industrial Equipment, Medical equipment [GHTF A/B], Mobile Electronics Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.
Recommended Applications	Consumer equipment, Industrial Equipment, Medical equipment [GHTF A/B], Mobile Electronics

Packaging Information


Packaging	Specifications	Standard Packing Quantity
-	180mm Paper Tape	4000

Features

Adiplexer branching low and high band.

1. Low insertion loss.
2. Small size, low-profiled and light weight.
3. Absolutely no adjustment required.
4. Reflow solderable.

Appearance & Shape



Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

LFD18829MMP2E093



Specifications

Applications	LTE
Center Frequency(f1)	829.50MHz
Frequency Range(f1)	699.00MHz to 960.00MHz
Center Frequency(f2)	2200.00MHz
Frequency Range(f2)	1710.00MHz to 2690.00MHz
Insertion Loss I)(in f1)	0.67dB max. (at 25°C)
Insertion Loss II)(in f1)	0.77dB max. (-40 to +85°C)
Insertion Loss I)(in f2)	0.80dB max. (at 25°C)
Insertion Loss II)(in f2)	0.90dB max. (-40 to +85°C)
Attenuation(in f2)	20.0dB min.
Attenuation(in f1)	20.5dB min.
VSWR{P1}(in f1)	1.64 max.
VSWR{P2}(in f2)	1.74 max.
VSWR{P3}(in f1,f2)	(f1)1.64 max., (f2)1.74 max.
Power Capacity	2W
Operating Temperature Range	-40°C to 85°C
L x W (size)	1.60x0.80mm
Thickness(max.)	0.7mm

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.