Part Numbering

Ceramic Filters (CERAFIL®) for IF

Product ID

②Oscillating/Element

Product ID			Oscillating/Element	
CF	Ceramic Filters	U	4 Elements Area Expansion mode	
CF		W	6 Elements Area Expansion mode	
SF		Р	4 Elements Area Expansion mode	
		Е	2 Elements Thickness Expansion mode	
		s	2 Elements Thickness Shear mode	

3Structure/Size

Code	Structure/Size
C□/K□	Chip Type
L	Lead Type

☐ is "A" or subsequent code, which indicates the size. It varies depending on vibration mode and number of elements. Chip type is only applied for SF series.

4 Nominal Center Frequency

Expressed by four-digit alphanumerics. The unit is hertz (Hz). If the unit is "kHz", it is expressed by three figures plus " \mathbf{K} ." If the unit is "MHz", a decimal point is expressed by the capital letter " \mathbf{M} ."

6Product Specification

Code	Product Specification	
D4A	Three-digit alphanumerics express pass bandwidth, center frequency tolerance and design type.	

SFE/S/J series are expressed by four-digit alphanumerics.

6Individual Specification

Code	Individual Specification Code
001	Expressed by three-digit alphanumerics.

SFE/S/J series are expressed by two-digit alphanumerics. With standard type, (a) is omitted.

Packaging					
Code	Packaging				
-B0	Bulk				
-R0	Embossed Taping ø=180mm				
-R1	Embossed Taping ø=330mm				

Embossed taping is applied to chip type.