
Taping Dimensions (NTPA9/A7/A6/A5_B1A0 Series)



Item	Code	Dimensions (mm)
Pitch of Component	Р	12.7
Pitch of Sprocket Hole	Po	12.7±0.3
Lead Spacing	F	5.0 ^{+0.8}
Length from Hole Center to Component Center	P2	6.35±1.3
Length from Hole Center to Lead	P1	3.85±0.8
Body Diameter	D	(refer to the table below)
Body Thickness	Т	5.0 max.
Deviation Along Tape, Left or Right	ΔS	±1.5
Carrier Tape Width	W	18.0±0.5
Position of Sprocket Hole	W1	9.0 ^{+0.5} -0.75
Lead Distance between Reference and Bottom Planes	Ho	16.0±1.0
Height of Component	H2	6.0 max.
Protrusion Length	Ι	+0.5 to -4.0
Diameter of Sprocket Hole	Do	4.0±0.3
Lead Diameter	d	0.6±0.05
Total Tape Thickness	t1	0.6±0.3
Total Thickness, Tape and Lead Wire	t2	2.0 max.
Deviation Across Tape	Δ h1, Δ h2	1.5 max.
Portion to Cut in Case of Defect	L	11.0 ⁺⁰ _{-2.0}
Hold down Tape Width	Wo	11.0 min.
Hold down Tape Position	W2	4.0 max.
Coating Extension on Lead	е	to line A

Туре	D (mm)	
NTPA9	11.0 max.	
NTPA7	9.0 max.	
NTPA6	7.5 max.	
NTPA5	6.0 max.	

muRata