



FEATURES

- RoHS compliant
- Maxim MAX250/MAX251/MAX253 compatible
- EN62368-1 TUV certificate of compliance
- Isolation to 6kVDC
- Toroidal construction
- Industry-standard pinout
- UL 94 V-0 package materials
- Fully encapsulated
- Compatible with RoHS soldering systems
- Backward compatible with Sn/Pb soldering systems

DESCRIPTION

The 76250ENC converter transformer is specifically designed for use with Maxim chipsets to provide isolated RS232 interfaces. A carefully controlled turns ratio ensures consistent performance whilst a toroidal construction minimises EMI.

The 76253/XXENC converter transformers are specifically designed for use with the MAX253 chip set to provide isolated power supplies. The 5V version can supply 1W and the 3.3V version can supply 500mW. A centre tapped secondary winding allows for full bridge, half bridge or voltage doubling.



www.murata.com

76250ENC, 76253/XXENC

EN Approved MAX250/251/253 Compatible Converter Transformers

SELECTION GUIDE						
Order Code	Input Voltage	Output Voltage	Max. Output Current	Isolation Voltage	Turns	
	V	V	mA	VDC	Ratio	
76250ENC	-	-	-	6000	1CT:1	
76253/35ENC	3.3	5.0	100	6000	1:√5	
76253/55ENC	5.0	5.0	200	6000	1:1.33	

76250ENC CHARACTERISTICS					
Parameter	Conditions	Min.	Тур.	Max.	Units
Primary Inductance, L_{P} (1&5)	10kHz, 100mV	1.0	2.0	2.5	mH
Leakage Inductance, L_{L} (1&5) ²	100kHz, 100mV		35	40	μH
Interwinding Capacitance, C _{ww} (1&2)	100kHz, 100mV		1.5	3.0	pF
D.C. Resistance, R _{DC} (1&5)	<0.1VDC		1.0	2.0	Ω
Volt-time Product, E_{T} (1&5)		50			Vµs

76253/35ENC CHARACTERISTICS					
Parameter	Conditions	Min.	Тур.	Max.	Units
Primary Inductance, L _P (1&5)	100kHz, 250mV	140	200		μH
Secondary Inductance, L_s (2&6)	100kHz, 250mV	700	1000		μH
Leakage Inductance, L_{L} (1&5) ²	100kHz, 250mV		5.0	7.0	μH
Interwinding Capacitance, C _{ww} (1&2)	100kHz, 250mV		2.7	3.5	pF
D.C. Resistance, R _{DC} (1&5)	<0.1VDC		0.4	0.8	Ω
Volt-time Product, E_{T} (1&5)		25	35		Vµs

76253/55ENC CHARACTE	RISTICS
----------------------	---------

Parameter	Conditions	Min.	Тур.	Max.	Units
Primary Inductance, L_{P} (1&5)	100kHz, 250mV	80		150	μH
Secondary Inductance, L _s (2&6)	100kHz, 250mV	142		267	μH
Leakage Inductance, L_{L} (1&5) ²	100kHz, 250mV		7.0	10.0	μH
Interwinding Capacitance, C _{ww} (1&2)	100kHz, 250mV		2.7	3.5	pF
D.C. Resistance, R _{DC} (1&5)	<0.1Vdc		0.5	0.9	Ω
Volt-time Product, E _T (1&5)		30	40		Vµs

0°C to 70°C
-40°C to 85°C
-50°C to 125°C
300°C
300mA
400mA
6000Vdc

SOLDERING INFORMATION ³			
Peak wave solder temperature	300°C for 10 seconds		
Pin finish	Matte tin		

All specifications typical at T₄=25°C

1 Refer to mechanical dimensions for pin locations shown in brackets.

2 With pins 2 & 6 short circuited.

3 For further information, please visit www.murata-ps.com/rohs

76250ENC, 76253/XXENC

EN Approved MAX250/251/253 Compatible Converter Transformers

TECHNICAL NOTES

ISOLATION VOLTAGE

'Hi Pot Test', 'Flash Tested', 'Withstand Voltage', 'Proof Voltage', 'Dielectric Withstand Voltage' & 'Isolation Test Voltage' are all terms that relate to the same thing, a test voltage, applied for a specified time, across a component designed to provide electrical isolation, to verify the integrity of that isolation.

All products in this series are 100% production tested at their stated isolation voltage.

This series is certified by TUV to EN62368-1 with a working voltage of 300Vrms for Reinforced Insulation systems.

REPEATED HIGH-VOLTAGE ISOLATION TESTING

It is well known that repeated high-voltage isolation testing of a barrier component can actually degrade isolation capability, to a lesser or greater degree depending on materials, construction and environment. We therefore strongly advise against repeated high voltage isolation testing, but if it is absolutely required, that the voltage be reduced by 20% from the specified test voltage.

SAFETY APPROVAL


EN62368-1

The7625xEN series has been certified by TUV to EN62368-1 for reinforced insulation to a working voltage of 300Vrms, 2500Vpk and a working frequency of 30kHz. Operation above 30kHz would need evaluation during system level evaluation.

Working altitude OVC II 5000m. Creepage and clearance is 9.3mm.

76250ENC, 76253/XXENC

EN Approved MAX250/251/253 Compatible Converter Transformers




All curves are derived from testing with the Maxim MAX235 IC using the circuit shown in application note MPAN-03 (download at http://www.murata-ps.com/data/apnotes/mpan-03.pdf).

www.murata.com

76250ENC, 76253/XXENC

EN Approved MAX250/251/253 Compatible Converter Transformers



76250ENC, 76253/XXENC

EN Approved MAX250/251/253 Compatible Converter Transformers

DISCLAIMER

Unless otherwise stated in the datasheet, all products are designed for standard commercial and industrial applications and NOT for safety-critical and/or life-critical applications.

Particularly for safety-critical and/or life-critical applications, i.e. applications that may directly endanger or cause the loss of life, inflict bodily harm and/or loss or severe damage to equipment/property, and severely harm the environment, a prior explicit written approval from Murata is strictly required. Any use of Murata standard products for any safety-critical, life-critical or any related applications without any prior explicit written approval from Murata shall be deemed unauthorised use.

These applications include but are not limited to:

- Aircraft equipment
- Aerospace equipment
- Undersea equipment
- Power plant control equipment
- Medical equipment
- Transportation equipment (automobiles, trains, ships, etc.)
- Traffic signal equipment
- Disaster prevention / crime prevention equipment
- Data Processing equipment

Murata makes no express or implied warranty, representation, or guarantee of suitability, fitness for any particular use/purpose and/or compatibility with any application or device of the buyer, nor does Murata assume any liability whatsoever arising out of unauthorised use of any Murata product for the application of the buyer. The suitability, fitness for any particular use/purpose and/or compatibility of Murata product with any application or device of the buyer remain to be the responsibility and liability of the buyer.

Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm, and take appropriate remedial actions. Buyer will fully indemnify and hold Murata, its affiliated companies, and its representatives harmless against any damages arising out of unauthorised use of any Murata products in any safety-critical and/ or life-critical applications.

Remark: Murata in this section refers to Murata Manufacturing Company and its affiliated companies worldwide including, but not limited to, Murata Power Solutions.



This product is subject to the following <u>operating requirements</u> and the <u>Life and Safety Critical Application Sales Policy</u>: Refer to: https://www.murata.com/en-eu/products/power/requirements

Murata Power Solutions (Milton Keynes) Ltd. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not imply the granning of licenses to make, use, or sell equipment constructed in accordance therevith. Specifications are subject to change without notice. © 2021 Murata Power Solutions (Milton Keynes) Ltd