


# PVG3A504C01R00

已经停产

RoHS

REACH

## 外观&形状



## 特点

1. Sealed construction protects the interior from dust and liquid, which achieves stable performance.
2. Driver plate with cross-slot is suitable for automatic adjustment.
3. Rotor with large diameter and deep groove improves driver insertion.
4. 3mm and 4mm land pattern can be used without change. (Gull-wing is suitable for 4mm size land pattern.)

## 包装信息

| 包装  | 规格       | 标准包装数量 |
|-----|----------|--------|
| R00 | 180mm压纹带 | 1000   |

注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。
2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，谨请核准其规格或者办理产品规格表。

# PVG3A504C01R00

规格

|              |                                                                       |
|--------------|-----------------------------------------------------------------------|
| 额定功率         | 0.25W                                                                 |
| 形状           | SMD                                                                   |
| 最大工作电压       | 200Vdc                                                                |
| 调整方向         | 上方                                                                    |
| 尺寸           | 3mm                                                                   |
| 自动调整         | Yes                                                                   |
| 调节转数(有效旋转角度) | 1(210°±10°)                                                           |
| 机械旋转角度       | 250+/-10 deg.                                                         |
| 总电阻值         | 500kΩ                                                                 |
| 总电阻值公差       | ±20%                                                                  |
| 电阻温度系数       | ±150ppm/°C                                                            |
| 电阻变化特性       | B(Linear)                                                             |
| 接触电阻变化       | 2% of total resistance value<br>or 3ohm max., whichever is<br>greater |
| 剩余电阻         | 1% of total resistance value<br>or 3ohm max., whichever is<br>greater |
| 力矩           | 4.9mN · m max.                                                        |
| 额定功率测量条件     | 70°C                                                                  |
| 工作温度范围       | -55°C to 125°C                                                        |
| 质量           | 0.06g                                                                 |

注意

1.

本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。

2.

本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，谨请核准其规格或者办理产品规格表。

# PVG3A504C01R00



## 产品数据



### 结构

在3 / 3页

#### 注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。
2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，谨请核准其规格或者办理产品规格表。