

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GJ821BB31H105KA12	1uF	50	B	2012M/0805	1.35	+/-10%	Acoustic noise reduction
GRM022B11A101KA01	100pF	10	B	0402M/01005	0.22	+/-10%	Ultra-small
GRM022B11A101MA01	100pF	10	B	0402M/01005	0.22	+/-20%	Ultra-small
GRM022B11A151KA01	150pF	10	B	0402M/01005	0.22	+/-10%	Ultra-small
GRM022B11A151MA01	150pF	10	B	0402M/01005	0.22	+/-20%	Ultra-small
GRM022B11A221KA01	220pF	10	B	0402M/01005	0.22	+/-10%	Ultra-small
GRM022B11A221MA01	220pF	10	B	0402M/01005	0.22	+/-20%	Ultra-small
GRM022B11A331KA01	330pF	10	B	0402M/01005	0.22	+/-10%	Ultra-small
GRM022B11A331MA01	330pF	10	B	0402M/01005	0.22	+/-20%	Ultra-small
GRM022B11A471KA01	470pF	10	B	0402M/01005	0.22	+/-10%	Ultra-small
GRM022B11A471MA01	470pF	10	B	0402M/01005	0.22	+/-20%	Ultra-small
GRM022B11A680KA01	68pF	10	B	0402M/01005	0.22	+/-10%	Ultra-small
GRM022B11A680MA01	68pF	10	B	0402M/01005	0.22	+/-20%	Ultra-small
GRM022B30J102KE19	1000pF	6.3	B	0402M/01005	0.22	+/-10%	Ultra-small
GRM022B30J102ME19	1000pF	6.3	B	0402M/01005	0.22	+/-20%	Ultra-small
GRM022B30J103KE19	1000pF	6.3	B	0402M/01005	0.22	+/-10%	Ultra-small
GRM022B30J103ME19	1000pF	6.3	B	0402M/01005	0.22	+/-20%	Ultra-small
GRM022B30J152KE19	1500pF	6.3	B	0402M/01005	0.22	+/-10%	Ultra-small
GRM022B30J152ME19	1500pF	6.3	B	0402M/01005	0.22	+/-20%	Ultra-small
GRM022B30J222KE19	2200pF	6.3	B	0402M/01005	0.22	+/-10%	Ultra-small
GRM022B30J222ME19	2200pF	6.3	B	0402M/01005	0.22	+/-20%	Ultra-small
GRM022B30J332KE19	3300pF	6.3	B	0402M/01005	0.22	+/-10%	Ultra-small
GRM022B30J332ME19	3300pF	6.3	B	0402M/01005	0.22	+/-20%	Ultra-small
GRM022B30J472KE19	4700pF	6.3	B	0402M/01005	0.22	+/-10%	Ultra-small
GRM022B30J472ME19	4700pF	6.3	B	0402M/01005	0.22	+/-20%	Ultra-small
GRM022B30J681KE19	680pF	6.3	B	0402M/01005	0.22	+/-10%	Ultra-small
GRM022B30J681ME19	680pF	6.3	B	0402M/01005	0.22	+/-20%	Ultra-small
GRM022B30J682KE19	680pF	6.3	B	0402M/01005	0.22	+/-10%	Ultra-small
GRM022B30J682ME19	680pF	6.3	B	0402M/01005	0.22	+/-20%	Ultra-small
GRM022B31A102KE19	1000pF	10	B	0402M/01005	0.22	+/-10%	Ultra-small
GRM022B31A102ME19	1000pF	10	B	0402M/01005	0.22	+/-20%	Ultra-small
GRM022B31A103KE19	1000pF	10	B	0402M/01005	0.22	+/-10%	Ultra-small
GRM022B31A103ME19	1000pF	10	B	0402M/01005	0.22	+/-20%	Ultra-small
GRM022B31A152KE19	1500pF	10	B	0402M/01005	0.22	+/-10%	Ultra-small
GRM022B31A152ME19	1500pF	10	B	0402M/01005	0.22	+/-20%	Ultra-small
GRM022B31A222KE19	2200pF	10	B	0402M/01005	0.22	+/-10%	Ultra-small
GRM022B31A222ME19	2200pF	10	B	0402M/01005	0.22	+/-20%	Ultra-small
GRM022B31A332KE19	3300pF	10	B	0402M/01005	0.22	+/-10%	Ultra-small
GRM022B31A332ME19	3300pF	10	B	0402M/01005	0.22	+/-20%	Ultra-small
GRM022B31A472KE19	4700pF	10	B	0402M/01005	0.22	+/-10%	Ultra-small
GRM022B31A472ME19	4700pF	10	B	0402M/01005	0.22	+/-20%	Ultra-small
GRM022B31A681KE19	680pF	10	B	0402M/01005	0.22	+/-10%	Ultra-small
GRM022B31A681ME19	680pF	10	B	0402M/01005	0.22	+/-20%	Ultra-small
GRM022B31A682KE19	680pF	10	B	0402M/01005	0.22	+/-10%	Ultra-small
GRM022B31A682ME19	680pF	10	B	0402M/01005	0.22	+/-20%	Ultra-small
GRM033B10J103KA01	1000pF	6.3	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B10J152KA01	1500pF	6.3	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B10J153KE01	1500pF	6.3	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B10J153ME01	1500pF	6.3	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B10J222KA01	2200pF	6.3	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B10J223KE01	2200pF	6.3	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B10J223ME01	2200pF	6.3	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B10J332KA01	3300pF	6.3	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B10J333KE01	3300pF	6.3	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B10J333ME01	3300pF	6.3	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B10J472KA01	4700pF	6.3	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B10J682KA01	680pF	6.3	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B11A103KA01	1000pF	10	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B11A103MA01	1000pF	10	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B11A152KA01	1500pF	10	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B11A222KA01	2200pF	10	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B11A332KA01	3300pF	10	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B11A472KA01	4700pF	10	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B11A472MA01	4700pF	10	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B11A682KA01	680pF	10	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B11A682MA01	680pF	10	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B11C101KA01	100pF	16	B	0603M/0201	0.33	+/-10%	Ultra-small

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM033B11C102KA01	100pF	16	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B11C151KA01	150pF	16	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B11C152KA01	1500pF	16	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B11C221KA01	220pF	16	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B11C331KA01	330pF	16	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B11C471KA01	470pF	16	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B11C681KA01	680pF	16	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B11E101KA01	100pF	25	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B11E102KA01	1000pF	25	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B11E102MA01	1000pF	25	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B11E151KA01	150pF	25	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B11E152KA01	1500pF	25	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B11E152MA01	1500pF	25	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B11E221KA01	220pF	25	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B11E331KA01	330pF	25	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B11E471KA01	470pF	25	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B11E681KA01	680pF	25	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B30G224ME15	0.22uF	4	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B30J224ME15	0.22uF	6.3	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B30J473KE18	47000pF	6.3	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31A104KE84	0.1uF	10	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31A104ME84	0.1uF	10	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31A123KE84	12000pF	10	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31A123ME84	12000pF	10	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31A153KE84	15000pF	10	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31A153ME84	15000pF	10	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31A183KE84	18000pF	10	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31A183ME84	18000pF	10	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31A223KE84	22000pF	10	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31A223ME84	22000pF	10	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31A273KE84	27000pF	10	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31A273ME84	27000pF	10	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31A333KE84	33000pF	10	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31A333ME84	33000pF	10	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31A393KE84	39000pF	10	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31A393ME84	39000pF	10	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31A473KE84	47000pF	10	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31A473ME84	47000pF	10	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31A683KE84	68000pF	10	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31A683ME84	68000pF	10	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31C103KA12	10000pF	16	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31C103MA12	10000pF	16	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31C104KE84	0.1uF	16	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31C104ME84	0.1uF	16	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31C153KE84	15000pF	16	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31C153ME84	15000pF	16	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31C222KA87	2200pF	16	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31C222MA87	2200pF	16	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31C223KE84	2200pF	16	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31C223ME84	2200pF	16	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31C332KA87	3300pF	16	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31C332MA87	3300pF	16	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31C333KE84	3300pF	16	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31C333ME84	3300pF	16	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31C473KE84	47000pF	16	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31C473ME84	47000pF	16	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31C683KE84	68000pF	16	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31C683ME84	68000pF	16	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31E103KA12	10000pF	25	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31E103MA12	10000pF	25	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31E222KA12	2200pF	25	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31E222MA12	2200pF	25	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31E332KA12	3300pF	25	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31E332MA12	3300pF	25	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31H101KA12	100pF	50	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31H101MA12	100pF	50	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31H102KA12	100pF	50	B	0603M/0201	0.33	+/-10%	Ultra-small

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM033B31H102MA12	1000pF	50	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31H151KA12	150pF	50	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31H151MA12	150pF	50	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31H152KA12	1500pF	50	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31H152MA12	1500pF	50	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31H221KA12	220pF	50	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31H221MA12	220pF	50	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31H331KA12	330pF	50	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31H331MA12	330pF	50	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31H471KA12	470pF	50	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31H471MA12	470pF	50	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033B31H681KA12	680pF	50	B	0603M/0201	0.33	+/-10%	Ultra-small
GRM033B31H681MA12	680pF	50	B	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R10J103KA01	10000pF	6.3	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R10J152KA01	1500pF	6.3	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R10J222KA01	2200pF	6.3	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R10J332KA01	3300pF	6.3	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R10J472KA01	4700pF	6.3	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R10J682KA01	6800pF	6.3	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11A103KA01	10000pF	10	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11A103MA01	10000pF	10	R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R11A152KA01	1500pF	10	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11A222KA01	2200pF	10	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11A332KA01	3300pF	10	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11A472KA01	4700pF	10	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11A472MA01	4700pF	10	R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R11A682KA01	6800pF	10	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11A682MA01	6800pF	10	R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R11C101KA01	100pF	16	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11C102KA01	1000pF	16	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11C151KA01	150pF	16	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11C152KA01	1500pF	16	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11C221KA01	220pF	16	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11C222KA88	2200pF	16	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11C331KA01	330pF	16	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11C332KA88	3300pF	16	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11C471KA01	470pF	16	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11C681KA01	680pF	16	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11E101KA01	100pF	25	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11E102KA01	1000pF	25	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11E151KA01	150pF	25	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11E152KA01	1500pF	25	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11E221KA01	220pF	25	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11E331KA01	330pF	25	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11E471KA01	470pF	25	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R11E681KA01	680pF	25	R	0603M/0201	0.33	+/-10%	Ultra-small
GRM152B30J104KE19	0.1uF	6.3	B	1005M/0402	0.22	+/-10%	General Purpose
GRM152B30J104ME19	0.1uF	6.3	B	1005M/0402	0.22	+/-20%	General Purpose
GRM152B30J224KE19	0.22uF	6.3	B	1005M/0402	0.22	+/-10%	General Purpose
GRM152B30J224ME19	0.22uF	6.3	B	1005M/0402	0.22	+/-20%	General Purpose
GRM152B30J474ME15	0.47uF	6.3	B	1005M/0402	0.22	+/-20%	General Purpose
GRM152B31A104KE19	0.1uF	10	B	1005M/0402	0.22	+/-10%	General Purpose
GRM152B31A104ME19	0.1uF	10	B	1005M/0402	0.22	+/-20%	General Purpose
GRM152B31A224KE19	0.22uF	10	B	1005M/0402	0.22	+/-10%	General Purpose
GRM152B31A224ME19	0.22uF	10	B	1005M/0402	0.22	+/-20%	General Purpose
GRM153B30G225ME95	2.2uF	4	B	1005M/0402	0.33	+/-20%	General Purpose
GRM153B30J105ME95	1uF	6.3	B	1005M/0402	0.33	+/-20%	General Purpose
GRM153B30J225ME95	2.2uF	6.3	B	1005M/0402	0.33	+/-20%	General Purpose
GRM153B31A105ME95	1uF	10	B	1005M/0402	0.33	+/-20%	General Purpose
GRM155B10J104KA01	0.1uF	6.3	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B10J154KE01	0.15uF	6.3	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B10J154ME01	0.15uF	6.3	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B10J224KE01	0.22uF	6.3	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B10J224ME01	0.22uF	6.3	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B10J334KE01	0.33uF	6.3	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B10J334ME01	0.33uF	6.3	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B11A104KA01	0.1uF	10	B	1005M/0402	0.55	+/-10%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM155B11C103KA01	10000pF	16	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B11C103MA01	10000pF	16	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B11C223KA01	22000pF	16	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B11C333KA01	33000pF	16	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B11C473KA01	47000pF	16	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B11E102KA01	1000pF	25	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B11E103KA01	10000pF	25	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B11E103MA01	10000pF	25	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B11E153KA61	15000pF	25	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B11E153MA61	15000pF	25	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B11E222KA01	2200pF	25	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B11E223KA61	22000pF	25	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B11E223MA61	22000pF	25	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B11E472KA01	4700pF	25	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B11E682KA01	6800pF	25	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B11H102KA01	1000pF	50	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B11H102MA01	1000pF	50	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B11H152KA01	1500pF	50	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B11H152MA01	1500pF	50	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B11H221KA01	220pF	50	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B11H221MA01	220pF	50	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B11H222KA01	2200pF	50	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B11H222MA01	2200pF	50	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B11H331KA01	330pF	50	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B11H331MA01	330pF	50	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B11H332KA01	3300pF	50	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B11H332MA01	3300pF	50	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B11H471KA01	470pF	50	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B11H471MA01	470pF	50	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B11H472KA01	4700pF	50	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B11H472MA01	4700pF	50	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B11H681KA01	680pF	50	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B11H681MA01	680pF	50	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B30G475ME47	4.7uF	4	B	1005M/0402	0.6	+/-20%	General Purpose
GRM155B30J105KE18	1uF	6.3	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B30J105ME18	1uF	6.3	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B30J225KE95	2.2uF	6.3	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B30J225ME95	2.2uF	6.3	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B30J474KE18	0.47uF	6.3	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B30J474ME18	0.47uF	6.3	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B30J475ME47	4.7uF	6.3	B	1005M/0402	0.6	+/-20%	General Purpose
GRM155B30J475ME87	4.7uF	6.3	B	1005M/0402	0.65	+/-20%	General Purpose
GRM155B30J684KE18	0.68uF	6.3	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B30J684ME18	0.68uF	6.3	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B31A105ME01	1uF	10	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B31A154KE18	0.15uF	10	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B31A154ME18	0.15uF	10	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B31A224KE18	0.22uF	10	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B31A224ME18	0.22uF	10	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B31A225KE95	2.2uF	10	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B31A225ME95	2.2uF	10	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B31A334KE14	0.33uF	10	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B31A334ME14	0.33uF	10	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B31A474KE14	0.47uF	10	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B31A474ME14	0.47uF	10	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B31A684KE15	0.68uF	10	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B31A684ME15	0.68uF	10	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B31C104KA87	0.1uF	16	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B31C105KA12	1uF	16	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B31C105MA12	1uF	16	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B31C683KA87	68000pF	16	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B31E104KA87	0.1uF	25	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B31E104MA87	0.1uF	25	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B31E105KA12	1uF	25	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B31E105MA12	1uF	25	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B31E333KA87	33000pF	25	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B31E333MA87	33000pF	25	B	1005M/0402	0.55	+/-20%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM155B31E473KA87	47000pF	25	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B31E473MA87	47000pF	25	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B31E683KA87	68000pF	25	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B31E683MA87	68000pF	25	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B31H103KA88	10000pF	50	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B31H103MA88	10000pF	50	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B31H104KE14	0.1uF	50	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B31H104ME14	0.1uF	50	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B31H153KA12	15000pF	50	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B31H153MA12	15000pF	50	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B31H223KA12	22000pF	50	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B31H223MA12	22000pF	50	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155B31H682KA88	6800pF	50	B	1005M/0402	0.55	+/-10%	General Purpose
GRM155B31H682MA88	6800pF	50	B	1005M/0402	0.55	+/-20%	General Purpose
GRM155R11A104KA01	0.1uF	10	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11A683KA01	68000pF	10	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11A683MA01	68000pF	10	R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R11C104KA88	0.1uF	16	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11C223KA01	22000pF	16	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11C333KA01	33000pF	16	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11C473KA01	47000pF	16	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11C683KA88	68000pF	16	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11E103KA01	10000pF	25	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11E153KA61	15000pF	25	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11E223KA61	22000pF	25	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11E333KA88	33000pF	25	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11E472KA01	4700pF	25	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11E473KA88	47000pF	25	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11E682KA01	6800pF	25	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11H102KA01	1000pF	50	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11H103KA88	10000pF	50	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11H152KA01	1500pF	50	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11H221KA01	220pF	50	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11H222KA01	2200pF	50	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11H331KA01	330pF	50	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11H332KA01	3300pF	50	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11H471KA01	470pF	50	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11H472KA01	4700pF	50	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11H681KA01	680pF	50	R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R11H682KA88	6800pF	50	R	1005M/0402	0.55	+/-10%	General Purpose
GRM15XB11C103KA86	10000pF	16	B	1005M/0402	0.3	+/-10%	General Purpose
GRM15XB11C103MA86	10000pF	16	B	1005M/0402	0.3	+/-20%	General Purpose
GRM15XB11C332KA86	3300pF	16	B	1005M/0402	0.3	+/-10%	General Purpose
GRM15XB11C332MA86	3300pF	16	B	1005M/0402	0.3	+/-20%	General Purpose
GRM15XB11C472KA86	4700pF	16	B	1005M/0402	0.3	+/-10%	General Purpose
GRM15XB11C472MA86	4700pF	16	B	1005M/0402	0.3	+/-20%	General Purpose
GRM15XB11C682KA86	6800pF	16	B	1005M/0402	0.3	+/-10%	General Purpose
GRM15XB11C682MA86	6800pF	16	B	1005M/0402	0.3	+/-20%	General Purpose
GRM15XB11E222KA86	2200pF	25	B	1005M/0402	0.3	+/-10%	General Purpose
GRM15XB11E222MA86	2200pF	25	B	1005M/0402	0.3	+/-20%	General Purpose
GRM15XB11H102KA86	1000pF	50	B	1005M/0402	0.3	+/-10%	General Purpose
GRM15XB11H102MA86	1000pF	50	B	1005M/0402	0.3	+/-20%	General Purpose
GRM15XB11H152KA86	1500pF	50	B	1005M/0402	0.3	+/-10%	General Purpose
GRM15XB11H152MA86	1500pF	50	B	1005M/0402	0.3	+/-20%	General Purpose
GRM15XB11H221KA86	220pF	50	B	1005M/0402	0.3	+/-10%	General Purpose
GRM15XB11H221MA86	220pF	50	B	1005M/0402	0.3	+/-20%	General Purpose
GRM15XB11H331KA86	330pF	50	B	1005M/0402	0.3	+/-10%	General Purpose
GRM15XB11H331MA86	330pF	50	B	1005M/0402	0.3	+/-20%	General Purpose
GRM15XB11H471KA86	470pF	50	B	1005M/0402	0.3	+/-10%	General Purpose
GRM15XB11H471MA86	470pF	50	B	1005M/0402	0.3	+/-20%	General Purpose
GRM15XB11H681KA86	680pF	50	B	1005M/0402	0.3	+/-10%	General Purpose
GRM15XB11H681MA86	680pF	50	B	1005M/0402	0.3	+/-20%	General Purpose
GRM15XR11C103KA86	10000pF	16	R	1005M/0402	0.3	+/-10%	General Purpose
GRM15XR11C472KA86	4700pF	16	R	1005M/0402	0.3	+/-10%	General Purpose
GRM15XR11E222KA86	2200pF	25	R	1005M/0402	0.3	+/-10%	General Purpose
GRM15XR11H102KA86	1000pF	50	R	1005M/0402	0.3	+/-10%	General Purpose
GRM15XR11H152KA86	1500pF	50	R	1005M/0402	0.3	+/-10%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM15XR11H221KA86	220pF	50	R	1005M/0402	0.3	+/-10%	General Purpose
GRM15XR11H331KA86	330pF	50	R	1005M/0402	0.3	+/-10%	General Purpose
GRM15XR11H471KA86	470pF	50	R	1005M/0402	0.3	+/-10%	General Purpose
GRM15XR11H681KA86	680pF	50	R	1005M/0402	0.3	+/-10%	General Purpose
GRM185B30J105KE25	1uF	6.3	B	1608M/0603	0.5	+/-10%	General Purpose
GRM185B31A105KE35	1uF	10	B	1608M/0603	0.5	+/-10%	General Purpose
GRM185B31C105KE43	1uF	16	B	1608M/0603	0.5	+/-10%	General Purpose
GRM185B31C105ME43	1uF	16	B	1608M/0603	0.5	+/-20%	General Purpose
GRM185B31E105KA12	1uF	25	B	1608M/0603	0.5	+/-10%	General Purpose
GRM185B31E105MA12	1uF	25	B	1608M/0603	0.5	+/-20%	General Purpose
GRM188B10J105KA01	1uF	6.3	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B10J474KA01	0.47uF	6.3	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11A105KA61	1uF	10	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11A224KA01	0.22uF	10	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11A334KA61	0.33uF	10	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11A334MA61	0.33uF	10	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11A474KA61	0.47uF	10	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11A684KA61	0.68uF	10	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11A684MA61	0.68uF	10	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11C104KA01	0.1uF	16	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11C104MA01	0.1uF	16	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11C154KA01	0.15uF	16	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11C224KA01	0.22uF	16	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11C224MA01	0.22uF	16	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11C334KA01	0.33uF	16	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11C334MA01	0.33uF	16	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11E102KA01	1000pF	25	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11E103KA01	10000pF	25	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11E103MA01	10000pF	25	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11E104KA01	0.1uF	25	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11E104MA01	0.1uF	25	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11E152KA01	1500pF	25	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11E153KA01	15000pF	25	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11E153MA01	15000pF	25	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11E154KA01	0.15uF	25	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11E222KA01	2200pF	25	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11E222MA01	2200pF	25	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11E223KA01	22000pF	25	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11E223MA01	22000pF	25	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11E332KA01	3300pF	25	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11E333KA01	33000pF	25	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11E333MA01	33000pF	25	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11E472KA01	4700pF	25	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11E472MA01	4700pF	25	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11E473KA01	47000pF	25	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11E473MA01	47000pF	25	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11E682KA01	6800pF	25	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11E683KA01	68000pF	25	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11E683MA01	68000pF	25	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11H102KA01	1000pF	50	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11H102MA01	1000pF	50	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11H103KA01	10000pF	50	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11H103MA01	10000pF	50	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11H152KA01	1500pF	50	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11H152MA01	1500pF	50	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11H153KA01	15000pF	50	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11H153MA01	15000pF	50	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11H221KA01	220pF	50	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11H221MA01	220pF	50	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11H222KA01	2200pF	50	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11H222MA01	2200pF	50	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11H223KA01	22000pF	50	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11H223MA01	22000pF	50	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11H331KA01	330pF	50	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11H331MA01	330pF	50	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11H332KA01	3300pF	50	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11H332MA01	3300pF	50	B	1608M/0603	0.9	+/-20%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM188B11H333KA61	33000pF	50	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11H333MA61	33000pF	50	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11H471KA01	470pF	50	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11H471MA01	470pF	50	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11H472KA01	4700pF	50	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11H472MA01	4700pF	50	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11H473KA61	47000pF	50	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11H473MA61	47000pF	50	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11H681KA01	680pF	50	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11H681MA01	680pF	50	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B11H682KA01	6800pF	50	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B11H682MA01	6800pF	50	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B30G106ME46	10uF	4	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B30G226MEA0	22uF	4	B	1608M/0603	1.0	+/-20%	General Purpose
GRM188B30J106ME47	10uF	6.3	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B30J106ME84	10uF	6.3	B	1608M/0603	0.95	+/-20%	General Purpose
GRM188B30J225KE18	2.2uF	6.3	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B30J226MEA0	22uF	6.3	B	1608M/0603	1.0	+/-20%	General Purpose
GRM188B30J475KE18	4.7uF	6.3	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B30J475ME18	4.7uF	6.3	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B30J475ME84	4.7uF	6.3	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B31A106KE69	10uF	10	B	1608M/0603	0.95	+/-10%	General Purpose
GRM188B31A106ME69	10uF	10	B	1608M/0603	0.95	+/-20%	General Purpose
GRM188B31A225KE33	2.2uF	10	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B31A225ME33	2.2uF	10	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B31A475KE15	4.7uF	10	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B31A475ME15	4.7uF	10	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B31C105KA92	1uF	16	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B31C105MA92	1uF	16	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B31C225KE14	2.2uF	16	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B31C474KA75	0.47uF	16	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B31C474KA87	0.47uF	16	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B31C474MA75	0.47uF	16	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B31C474MA87	0.47uF	16	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B31C475KAAJ	4.7uF	16	B	1608M/0603	0.95	+/-10%	General Purpose
GRM188B31C475MAAJ	4.7uF	16	B	1608M/0603	0.95	+/-20%	General Purpose
GRM188B31C684KA75	0.68uF	16	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B31C684MA75	0.68uF	16	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B31E105KA75	1uF	25	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B31E105MA75	1uF	25	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B31E224KA87	0.22uF	25	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B31E224MA87	0.22uF	25	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B31E225KA12	2.2uF	25	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B31E225MA12	2.2uF	25	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B31E474KA75	0.47uF	25	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B31E474MA75	0.47uF	25	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B31E684KA75	0.68uF	25	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B31E684MA75	0.68uF	25	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B31H104KA92	0.1uF	50	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B31H104MA92	0.1uF	50	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B31H105KAAL	1uF	50	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B31H105MAAL	1uF	50	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B31H154KAC4	0.15uF	50	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B31H154MAC4	0.15uF	50	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B31H224KAC4	0.22uF	50	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B31H224MAC4	0.22uF	50	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188B31H683KA92	68000pF	50	B	1608M/0603	0.9	+/-10%	General Purpose
GRM188B31H683MA92	68000pF	50	B	1608M/0603	0.9	+/-20%	General Purpose
GRM188R11A224KA01	0.22uF	10	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11C104KA01	0.1uF	16	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11C154KA01	0.15uF	16	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11C224KA01	0.22uF	16	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11C224MA01	0.22uF	16	R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R11C334KA01	0.33uF	16	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11C474KA88	0.47uF	16	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11C474MA88	0.47uF	16	R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R11E102KA01	1000pF	25	R	1608M/0603	0.9	+/-10%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM188R11E103KA01	10000pF	25	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11E103MA01	10000pF	25	R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R11E104KA01	0.1uF	25	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11E104MA01	0.1uF	25	R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R11E152KA01	1500pF	25	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11E153KA01	15000pF	25	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11E154KA01	0.15uF	25	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11E222KA01	2200pF	25	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11E222MA01	2200pF	25	R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R11E223KA01	22000pF	25	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11E223MA01	22000pF	25	R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R11E224KA88	0.22uF	25	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11E224MA88	0.22uF	25	R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R11E332KA01	3300pF	25	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11E333KA01	33000pF	25	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11E472KA01	4700pF	25	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11E472MA01	4700pF	25	R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R11E473KA01	47000pF	25	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11E473MA01	47000pF	25	R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R11E682KA01	6800pF	25	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11E683KA01	68000pF	25	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11H102KA01	1000pF	50	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11H102MA01	1000pF	50	R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R11H103KA01	10000pF	50	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11H103MA01	10000pF	50	R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R11H104KA93	0.1uF	50	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11H104MA93	0.1uF	50	R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R11H152KA01	1500pF	50	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11H153KA01	15000pF	50	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11H221KA01	220pF	50	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11H221MA01	220pF	50	R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R11H222KA01	2200pF	50	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11H222MA01	2200pF	50	R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R11H223KA01	22000pF	50	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11H223MA01	22000pF	50	R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R11H331KA01	330pF	50	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11H332KA01	3300pF	50	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11H333KA61	33000pF	50	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11H471KA01	470pF	50	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11H471MA01	470pF	50	R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R11H472KA01	4700pF	50	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11H472MA01	4700pF	50	R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R11H473KA61	47000pF	50	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11H473MA61	47000pF	50	R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R11H681KA01	680pF	50	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11H682KA01	6800pF	50	R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R11H683KA93	68000pF	50	R	1608M/0603	0.9	+/-10%	General Purpose
GRM216B31C105KA87	1uF	16	B	2012M/0805	0.7	+/-10%	General Purpose
GRM216B31E105KA75	1uF	25	B	2012M/0805	0.7	+/-10%	General Purpose
GRM219B11A105KA01	1uF	10	B	2012M/0805	0.95	+/-10%	General Purpose
GRM219B11A225KA01	2.2uF	10	B	2012M/0805	0.95	+/-10%	General Purpose
GRM219B11C684KA01	0.68uF	16	B	2012M/0805	0.95	+/-10%	General Purpose
GRM219B11H333KA01	33000pF	50	B	2012M/0805	0.95	+/-10%	General Purpose
GRM219B30G226ME66	22uF	4	B	2012M/0805	0.95	+/-20%	General Purpose
GRM219B30J106KE18	10uF	6.3	B	2012M/0805	0.95	+/-10%	General Purpose
GRM219B30J106ME18	10uF	6.3	B	2012M/0805	0.95	+/-20%	General Purpose
GRM219B30J226ME47	22uF	6.3	B	2012M/0805	0.95	+/-20%	General Purpose
GRM219B30J226MEA0	22uF	6.3	B	2012M/0805	0.95	+/-20%	General Purpose
GRM219B30J475KE18	4.7uF	6.3	B	2012M/0805	0.95	+/-10%	General Purpose
GRM219B31A106KE44	10uF	10	B	2012M/0805	0.95	+/-10%	General Purpose
GRM219B31A106ME44	10uF	10	B	2012M/0805	0.95	+/-20%	General Purpose
GRM219B31A226MEA0	22uF	10	B	2012M/0805	0.95	+/-20%	General Purpose
GRM219B31A475KE33	4.7uF	10	B	2012M/0805	0.95	+/-10%	General Purpose
GRM219B31A475ME33	4.7uF	10	B	2012M/0805	0.95	+/-20%	General Purpose
GRM219B31C106KA73	10uF	16	B	2012M/0805	0.95	+/-10%	General Purpose
GRM219B31C106MA73	10uF	16	B	2012M/0805	0.95	+/-20%	General Purpose
GRM219B31C225KA87	2.2uF	16	B	2012M/0805	0.95	+/-10%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM219B31C475KE15	4.7uF	16	B	2012M/0805	0.95	+/-10%	General Purpose
GRM219B31E105KA88	1uF	25	B	2012M/0805	0.95	+/-10%	General Purpose
GRM219B31E106KA12	10uF	25	B	2012M/0805	0.95	+/-10%	General Purpose
GRM219B31E106MA12	10uF	25	B	2012M/0805	0.95	+/-20%	General Purpose
GRM219B31E225KA75	2.2uF	25	B	2012M/0805	0.95	+/-10%	General Purpose
GRM219B31E225MA75	2.2uF	25	B	2012M/0805	0.95	+/-20%	General Purpose
GRM219B31E474KA88	0.47uF	25	B	2012M/0805	0.95	+/-10%	General Purpose
GRM219B31E474MA88	0.47uF	25	B	2012M/0805	0.95	+/-20%	General Purpose
GRM219B31E684KA88	0.68uF	25	B	2012M/0805	0.95	+/-10%	General Purpose
GRM219B31H105KA73	1uF	50	B	2012M/0805	0.95	+/-10%	General Purpose
GRM219B31H105MA73	1uF	50	B	2012M/0805	0.95	+/-20%	General Purpose
GRM219B31H225KE15	2.2uF	50	B	2012M/0805	0.95	+/-10%	General Purpose
GRM219B31H225ME15	2.2uF	50	B	2012M/0805	0.95	+/-20%	General Purpose
GRM219B31H334KA87	0.33uF	50	B	2012M/0805	0.95	+/-10%	General Purpose
GRM219B31H334MA87	0.33uF	50	B	2012M/0805	0.95	+/-20%	General Purpose
GRM219R11C684KA01	0.68uF	16	R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R11E474KA88	0.47uF	25	R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R11E474MA88	0.47uF	25	R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R11E683KA01	68000pF	25	R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R11H333KA01	33000pF	50	R	2012M/0805	0.95	+/-10%	General Purpose
GRM21BB10J105KC01	1uF	6.3	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB10J225KA01	2.2uF	6.3	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB10J475KA11	4.7uF	6.3	B	2012M/0805	1.4	+/-10%	General Purpose
GRM21BB10J475MA11	4.7uF	6.3	B	2012M/0805	1.4	+/-20%	General Purpose
GRM21BB11A105KA01	1uF	10	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB11A225KA01	2.2uF	10	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB11A225MA01	2.2uF	10	B	2012M/0805	1.35	+/-20%	General Purpose
GRM21BB11C105KA01	1uF	16	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB11C224KA01	0.22uF	16	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB11C224MA01	0.22uF	16	B	2012M/0805	1.35	+/-20%	General Purpose
GRM21BB11E154KA01	0.15uF	25	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB11E224KA01	0.22uF	25	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB11E224MA01	0.22uF	25	B	2012M/0805	1.35	+/-20%	General Purpose
GRM21BB11E334KA01	0.33uF	25	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB11H104KA01	0.1uF	50	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB11H104MA01	0.1uF	50	B	2012M/0805	1.35	+/-20%	General Purpose
GRM21BB11H473KA01	47000pF	50	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB11H473MA01	47000pF	50	B	2012M/0805	1.35	+/-20%	General Purpose
GRM21BB11H683KA01	68000pF	50	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB30G476ME15	47uF	4	B	2012M/0805	1.45	+/-20%	General Purpose
GRM21BB30J106KE18	10uF	6.3	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB30J106ME18	10uF	6.3	B	2012M/0805	1.35	+/-20%	General Purpose
GRM21BB30J226ME38	22uF	6.3	B	2012M/0805	1.4	+/-20%	General Purpose
GRM21BB30J476ME15	47uF	6.3	B	2012M/0805	1.45	+/-20%	General Purpose
GRM21BB31A106KE18	10uF	10	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB31A106ME18	10uF	10	B	2012M/0805	1.35	+/-20%	General Purpose
GRM21BB31A226ME51	22uF	10	B	2012M/0805	1.4	+/-20%	General Purpose
GRM21BB31A475KA74	4.7uF	10	B	2012M/0805	1.4	+/-10%	General Purpose
GRM21BB31A475MA74	4.7uF	10	B	2012M/0805	1.4	+/-20%	General Purpose
GRM21BB31C106KE15	10uF	16	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB31C106ME15	10uF	16	B	2012M/0805	1.35	+/-20%	General Purpose
GRM21BB31C225KA87	2.2uF	16	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB31C475KA87	4.7uF	16	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB31D106KE15	10uF	20	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB31D106ME15	10uF	20	B	2012M/0805	1.35	+/-20%	General Purpose
GRM21BB31E105KA98	1uF	25	B	2012M/0805	1.4	+/-10%	General Purpose
GRM21BB31E106KA73	10uF	25	B	2012M/0805	1.4	+/-10%	General Purpose
GRM21BB31E106MA73	10uF	25	B	2012M/0805	1.4	+/-20%	General Purpose
GRM21BB31E225KA75	2.2uF	25	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB31E225MA75	2.2uF	25	B	2012M/0805	1.35	+/-20%	General Purpose
GRM21BB31E475KA75	4.7uF	25	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB31E475MA75	4.7uF	25	B	2012M/0805	1.35	+/-20%	General Purpose
GRM21BB31H105KA12	1uF	50	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB31H105MA12	1uF	50	B	2012M/0805	1.35	+/-20%	General Purpose
GRM21BB31H154KA88	0.15uF	50	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB31H154MA88	0.15uF	50	B	2012M/0805	1.35	+/-20%	General Purpose
GRM21BB31H224KA88	0.22uF	50	B	2012M/0805	1.35	+/-10%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM21BB31H224MA88	0.22uF	50	B	2012M/0805	1.35	+/-20%	General Purpose
GRM21BB31H225KA73	2.2uF	50	B	2012M/0805	1.4	+/-10%	General Purpose
GRM21BB31H225MA73	2.2uF	50	B	2012M/0805	1.4	+/-20%	General Purpose
GRM21BB31H474KA87	0.47uF	50	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB31H474MA87	0.47uF	50	B	2012M/0805	1.35	+/-20%	General Purpose
GRM21BB31H475KE51	4.7uF	50	B	2012M/0805	1.4	+/-10%	General Purpose
GRM21BB31H475ME51	4.7uF	50	B	2012M/0805	1.4	+/-20%	General Purpose
GRM21BB31H684KAC4	0.68uF	50	B	2012M/0805	1.35	+/-10%	General Purpose
GRM21BB31H684MAC4	0.68uF	50	B	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR10J105KC01	1uF	6.3	R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR11A105KA01	1uF	10	R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR11C105KA01	1uF	16	R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR11C224KA01	0.22uF	16	R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR11C224MA01	0.22uF	16	R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR11E104KA01	0.1uF	25	R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR11E104MA01	0.1uF	25	R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR11E105KA99	1uF	25	R	2012M/0805	1.4	+/-10%	General Purpose
GRM21BR11E154KA01	0.15uF	25	R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR11E154MA01	0.15uF	25	R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR11E224KA01	0.22uF	25	R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR11E224MA01	0.22uF	25	R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR11E684KA88	0.68uF	25	R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR11H104KA01	0.1uF	50	R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR11H104MA01	0.1uF	50	R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR11H473KA01	47000pF	50	R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR11H473MA01	47000pF	50	R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR11H683KA01	68000pF	50	R	2012M/0805	1.35	+/-10%	General Purpose
GRM316B31A475KE18	4.7uF	10	B	3216M/1206	0.7	+/-10%	General Purpose
GRM316B31C225KA87	2.2uF	16	B	3216M/1206	0.7	+/-10%	General Purpose
GRM316B31E225KA75	2.2uF	25	B	3216M/1206	0.7	+/-10%	General Purpose
GRM319B11A105KA01	1uF	10	B	3216M/1206	0.95	+/-10%	General Purpose
GRM319B11A225KA01	2.2uF	10	B	3216M/1206	0.95	+/-10%	General Purpose
GRM319B11A475KA01	4.7uF	10	B	3216M/1206	0.95	+/-10%	General Purpose
GRM319B11C105KAA3	1uF	16	B	3216M/1206	0.95	+/-10%	General Purpose
GRM319B11C474KA01	0.47uF	16	B	3216M/1206	0.95	+/-10%	General Purpose
GRM319B11C474MA01	0.47uF	16	B	3216M/1206	0.95	+/-20%	General Purpose
GRM319B11E334KA01	0.33uF	25	B	3216M/1206	0.95	+/-10%	General Purpose
GRM319B11E474KA01	0.47uF	25	B	3216M/1206	0.95	+/-10%	General Purpose
GRM319B11E474MA01	0.47uF	25	B	3216M/1206	0.95	+/-20%	General Purpose
GRM319B11E684KA01	0.68uF	25	B	3216M/1206	0.95	+/-10%	General Purpose
GRM319B30J106KE18	10uF	6.3	B	3216M/1206	0.95	+/-10%	General Purpose
GRM319B30J226ME15	22uF	6.3	B	3216M/1206	0.95	+/-20%	General Purpose
GRM319B31A106KE18	10uF	10	B	3216M/1206	0.95	+/-10%	General Purpose
GRM319B31A106ME18	10uF	10	B	3216M/1206	0.95	+/-20%	General Purpose
GRM319B31A226ME15	22uF	10	B	3216M/1206	0.95	+/-20%	General Purpose
GRM319B31C106KE15	10uF	16	B	3216M/1206	0.95	+/-10%	General Purpose
GRM319B31C106ME15	10uF	16	B	3216M/1206	0.95	+/-20%	General Purpose
GRM319B31C226ME15	22uF	16	B	3216M/1206	0.95	+/-20%	General Purpose
GRM319B31C335KA75	3.3uF	16	B	3216M/1206	0.95	+/-10%	General Purpose
GRM319B31C475KA87	4.7uF	16	B	3216M/1206	0.95	+/-10%	General Purpose
GRM319B31E105KC45	1uF	25	B	3216M/1206	0.95	+/-10%	General Purpose
GRM319B31E475KA75	4.7uF	25	B	3216M/1206	0.95	+/-10%	General Purpose
GRM319B31H225KA12	2.2uF	50	B	3216M/1206	0.95	+/-10%	General Purpose
GRM319B31H225MA12	2.2uF	50	B	3216M/1206	0.95	+/-20%	General Purpose
GRM319B31H475KA12	4.7uF	50	B	3216M/1206	0.95	+/-10%	General Purpose
GRM319B31H475MA12	4.7uF	50	B	3216M/1206	0.95	+/-20%	General Purpose
GRM319R11A105KA01	1uF	10	R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R11C105KAA3	1uF	16	R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R11E334KA01	0.33uF	25	R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R11E474KA01	0.47uF	25	R	3216M/1206	0.95	+/-10%	General Purpose
GRM31CB10J475KA01	4.7uF	6.3	B	3216M/1206	1.8	+/-10%	General Purpose
GRM31CB11A475KA01	4.7uF	10	B	3216M/1206	1.8	+/-10%	General Purpose
GRM31CB11C475KA01	4.7uF	16	B	3216M/1206	1.8	+/-10%	General Purpose
GRM31CB30J226KE18	22uF	6.3	B	3216M/1206	1.8	+/-10%	General Purpose
GRM31CB30J226ME18	22uF	6.3	B	3216M/1206	1.8	+/-20%	General Purpose
GRM31CB30J476KE18	47uF	6.3	B	3216M/1206	1.8	+/-10%	General Purpose
GRM31CB30J476ME18	47uF	6.3	B	3216M/1206	1.8	+/-20%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM31CB31A226KE19	22uF	10	B	3216M/1206	1.8	+/-10%	General Purpose
GRM31CB31A226ME19	22uF	10	B	3216M/1206	1.8	+/-20%	General Purpose
GRM31CB31A476KE15	47uF	10	B	3216M/1206	1.8	+/-10%	General Purpose
GRM31CB31A476ME15	47uF	10	B	3216M/1206	1.8	+/-20%	General Purpose
GRM31CB31C106KA88	10uF	16	B	3216M/1206	1.8	+/-10%	General Purpose
GRM31CB31C226KE15	22uF	16	B	3216M/1206	1.8	+/-10%	General Purpose
GRM31CB31C226ME15	22uF	16	B	3216M/1206	1.8	+/-20%	General Purpose
GRM31CB31E106KA75	10uF	25	B	3216M/1206	1.8	+/-10%	General Purpose
GRM31CB31E106MA75	10uF	25	B	3216M/1206	1.8	+/-20%	General Purpose
GRM31CB31E226KE15	22uF	25	B	3216M/1206	1.8	+/-10%	General Purpose
GRM31CB31E226ME15	22uF	25	B	3216M/1206	1.8	+/-20%	General Purpose
GRM31CB31E475KA87	4.7uF	25	B	3216M/1206	1.8	+/-10%	General Purpose
GRM31CB31H106KA12	10uF	50	B	3216M/1206	1.8	+/-10%	General Purpose
GRM31CB31H106MA12	10uF	50	B	3216M/1206	1.8	+/-20%	General Purpose
GRM31CB31H225KA87	2.2uF	50	B	3216M/1206	1.8	+/-10%	General Purpose
GRM31CB31H225MA87	2.2uF	50	B	3216M/1206	1.8	+/-20%	General Purpose
GRM31CB31H475KA12	4.7uF	50	B	3216M/1206	1.8	+/-10%	General Purpose
GRM31CB31H475MA12	4.7uF	50	B	3216M/1206	1.8	+/-20%	General Purpose
GRM31CB3YA106KA12	10uF	35	B	3216M/1206	1.8	+/-10%	General Purpose
GRM31CB3YA106MA12	10uF	35	B	3216M/1206	1.8	+/-20%	General Purpose
GRM31CR11A106KA01	10uF	10	R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR11A106MA01	10uF	10	R	3216M/1206	1.8	+/-20%	General Purpose
GRM31CR11C475KA01	4.7uF	16	R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR11C475MA01	4.7uF	16	R	3216M/1206	1.8	+/-20%	General Purpose
GRM31MB11A225KA01	2.2uF	10	B	3216M/1206	1.25	+/-10%	General Purpose
GRM31MB11C105KA01	1uF	16	B	3216M/1206	1.25	+/-10%	General Purpose
GRM31MB11C225KA35	2.2uF	16	B	3216M/1206	1.3	+/-10%	General Purpose
GRM31MB11C225MA35	2.2uF	16	B	3216M/1206	1.3	+/-20%	General Purpose
GRM31MB11C684KA01	0.68uF	16	B	3216M/1206	1.25	+/-10%	General Purpose
GRM31MB11E105KA01	1uF	25	B	3216M/1206	1.25	+/-10%	General Purpose
GRM31MB11E224KA01	0.22uF	25	B	3216M/1206	1.25	+/-10%	General Purpose
GRM31MB11E224MA01	0.22uF	25	B	3216M/1206	1.25	+/-20%	General Purpose
GRM31MB11H154KA01	0.15uF	50	B	3216M/1206	1.25	+/-10%	General Purpose
GRM31MB11H224KA01	0.22uF	50	B	3216M/1206	1.25	+/-10%	General Purpose
GRM31MB11H224MA01	0.22uF	50	B	3216M/1206	1.25	+/-20%	General Purpose
GRM31MB30J106KE18	10uF	6.3	B	3216M/1206	1.25	+/-10%	General Purpose
GRM31MB31A106KE18	10uF	10	B	3216M/1206	1.25	+/-10%	General Purpose
GRM31MB31A106ME18	10uF	10	B	3216M/1206	1.25	+/-20%	General Purpose
GRM31MB31E225KA92	2.2uF	25	B	3216M/1206	1.3	+/-10%	General Purpose
GRM31MB31H105KA87	1uF	50	B	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR11A225KA01	2.2uF	10	R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR11C105KA01	1uF	16	R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR11C225KA35	2.2uF	16	R	3216M/1206	1.3	+/-10%	General Purpose
GRM31MR11C225MA35	2.2uF	16	R	3216M/1206	1.3	+/-20%	General Purpose
GRM31MR11E105KA01	1uF	25	R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR11E225KA93	2.2uF	25	R	3216M/1206	1.3	+/-10%	General Purpose
GRM31MR11H154KA01	0.15uF	50	R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR11H224KA01	0.22uF	50	R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR11H224MA01	0.22uF	50	R	3216M/1206	1.25	+/-20%	General Purpose
GRM32AB31C106KAB6	10uF	16	B	3225M/1210	1.0	+/-10%	General Purpose
GRM32DB11C106KA01	10uF	16	B	3225M/1210	2.2	+/-10%	General Purpose
GRM32DB11E475KA61	4.7uF	25	B	3225M/1210	2.2	+/-10%	General Purpose
GRM32DB31E106KA75	10uF	25	B	3225M/1210	2.2	+/-10%	General Purpose
GRM32DR11C106KA01	10uF	16	R	3225M/1210	2.2	+/-10%	General Purpose
GRM32DR11E475KA61	4.7uF	25	R	3225M/1210	2.2	+/-10%	General Purpose
GRM32EB11A106KA01	10uF	10	B	3225M/1210	2.7	+/-10%	General Purpose
GRM32EB30J107ME16	100uF	6.3	B	3225M/1210	2.7	+/-20%	General Purpose
GRM32EB30J476ME16	47uF	6.3	B	3225M/1210	2.7	+/-20%	General Purpose
GRM32EB31A476KE20	47uF	10	B	3225M/1210	2.7	+/-10%	General Purpose
GRM32EB31A476ME20	47uF	10	B	3225M/1210	2.7	+/-20%	General Purpose
GRM32EB31C226ME16	22uF	16	B	3225M/1210	2.7	+/-20%	General Purpose
GRM32EB31C476KE15	47uF	16	B	3225M/1210	2.7	+/-10%	General Purpose
GRM32EB31C476ME15	47uF	16	B	3225M/1210	2.7	+/-20%	General Purpose
GRM32EB31E226KE15	22uF	25	B	3225M/1210	2.7	+/-10%	General Purpose
GRM32EB31E226ME15	22uF	25	B	3225M/1210	2.7	+/-20%	General Purpose
GRM32EB31H106KA12	10uF	50	B	3225M/1210	2.7	+/-10%	General Purpose
GRM32EB31H106MA12	10uF	50	B	3225M/1210	2.7	+/-20%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM32EB31H475KA87	4.7uF	50	B	3225M/1210	2.7	+/-10%	General Purpose
GRM32EB3YA106KA12	10uF	35	B	3225M/1210	2.7	+/-10%	General Purpose
GRM32EB3YA106MA12	10uF	35	B	3225M/1210	2.7	+/-20%	General Purpose
GRM32ER11A226ME20	22uF	10	R	3225M/1210	2.7	+/-20%	General Purpose
GRM32MB11C225KA01	2.2uF	16	B	3225M/1210	1.25	+/-10%	General Purpose
GRM32MB11H474KA01	0.47uF	50	B	3225M/1210	1.25	+/-10%	General Purpose
GRM32MB11H474MA01	0.47uF	50	B	3225M/1210	1.25	+/-20%	General Purpose
GRM32MR11C225KA01	2.2uF	16	R	3225M/1210	1.25	+/-10%	General Purpose
GRM32NB11H684KA01	0.68uF	50	B	3225M/1210	1.5	+/-10%	General Purpose
GRM32NB31A226KE19	22uF	10	B	3225M/1210	1.5	+/-10%	General Purpose
GRM32NB31A226ME19	22uF	10	B	3225M/1210	1.5	+/-20%	General Purpose
GRM32RB11C475KA01	4.7uF	16	B	3225M/1210	2.0	+/-10%	General Purpose
GRM32RB11E225KA01	2.2uF	25	B	3225M/1210	2.0	+/-10%	General Purpose
GRM32RB11H105KA01	1uF	50	B	3225M/1210	2.0	+/-10%	General Purpose
GRM32RR11C475KA01	4.7uF	16	R	3225M/1210	2.0	+/-10%	General Purpose
GRM32RR11H105KA01	1uF	50	R	3225M/1210	2.0	+/-10%	General Purpose
GRM43EB11C226ME01	22uF	16	B	4532M/1812	2.7	+/-20%	General Purpose
GRM43EB31H475KA88	4.7uF	50	B	4532M/1812	2.7	+/-10%	General Purpose
GRM43ER11E475KA01	4.7uF	25	R	4532M/1812	2.7	+/-10%	General Purpose
GRM43ER11H225KA01	2.2uF	50	R	4532M/1812	2.7	+/-10%	General Purpose
GRM55DB11E106KA01	10uF	25	B	5750M/2220	2.1	+/-10%	General Purpose
GRM55DB31H106KA87	10uF	50	B	5750M/2220	2.2	+/-10%	General Purpose
GRM55DR11E106KA01	10uF	25	R	5750M/2220	2.1	+/-10%	General Purpose
GRM55EB11H475KA01	4.7uF	50	B	5750M/2220	2.7	+/-10%	General Purpose
GRM55ER11H475KA01	4.7uF	50	R	5750M/2220	2.7	+/-10%	General Purpose
GRM55RB11H105KA01	1uF	50	B	5750M/2220	2.0	+/-10%	General Purpose
GRM55RR11H105KA01	1uF	50	R	5750M/2220	2.0	+/-10%	General Purpose
GXM155B30G475ME47	4.7uF	4	B	1005M/0402	0.6	+/-20%	Water repellent/ General Purpose
GXM155B30J225KE95	2.2uF	6.3	B	1005M/0402	0.55	+/-10%	Water repellent/ General Purpose
GXM155B30J475ME47	4.7uF	6.3	B	1005M/0402	0.6	+/-20%	Water repellent/ General Purpose
GXM155B31A225KE95	2.2uF	10	B	1005M/0402	0.55	+/-10%	Water repellent/ General Purpose
GXM188B30G226MEA0	22uF	4	B	1608M/0603	1.0	+/-20%	Water repellent/ General Purpose
GXM188B30J226MEA0	22uF	6.3	B	1608M/0603	1.0	+/-20%	Water repellent/ General Purpose
GXM188B31C475KAAJ	4.7uF	16	B	1608M/0603	0.95	+/-10%	Water repellent/ General Purpose
GXM219B31A226MEA0	22uF	10	B	2012M/0805	0.95	+/-20%	Water repellent/ General Purpose
GXM21BB31A226ME50	22uF	10	B	2012M/0805	1.4	+/-20%	Water repellent/ General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GCM033R11A103KA01	10000pF	10	R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive
GCM033R11A152KA01	1500pF	10	R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive
GCM033R11A222KA01	2200pF	10	R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive
GCM033R11A332KA01	3300pF	10	R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive
GCM033R11A472KA01	4700pF	10	R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive
GCM033R11A682KA01	6800pF	10	R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive
GCM033R11C222KA40	2200pF	16	R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive
GCM033R11C332KA40	3300pF	16	R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive
GCM033R11E101KA01	100pF	25	R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive
GCM033R11E102KA01	1000pF	25	R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive
GCM033R11E151KA01	150pF	25	R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive
GCM033R11E152KA01	1500pF	25	R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive
GCM033R11E221KA01	220pF	25	R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive
GCM033R11E331KA01	330pF	25	R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive
GCM033R11E471KA01	470pF	25	R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive
GCM033R11E681KA01	680pF	25	R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive
GCM155R11A104KA01	0.1uF	10	R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R11C104KA40	0.1uF	16	R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R11C333KA01	33000pF	16	R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R11C473KA01	47000pF	16	R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R11C683KA40	68000pF	16	R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R11E103KA01	10000pF	25	R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R11E153KA40	15000pF	25	R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R11E223KA40	22000pF	25	R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R11E333KA40	33000pF	25	R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R11E473KA40	47000pF	25	R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R11E682KA01	6800pF	25	R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R11H102KA01	1000pF	50	R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R11H103KA40	10000pF	50	R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R11H152KA01	1500pF	50	R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R11H221KA01	220pF	50	R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R11H222KA01	2200pF	50	R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R11H331KA01	330pF	50	R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R11H332KA01	3300pF	50	R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R11H471KA01	470pF	50	R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R11H472KA01	4700pF	50	R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R11H681KA01	680pF	50	R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R11H682KA40	6800pF	50	R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM188R11A224KA01	0.22uF	10	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11C104KA01	0.1uF	16	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11C224KA01	0.22uF	16	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11C334KA01	0.33uF	16	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11C474KA40	0.47uF	16	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11E102KA01	1000pF	25	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11E103KA01	10000pF	25	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11E104KA42	0.1uF	25	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11E152KA01	1500pF	25	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11E153KA01	15000pF	25	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11E154KA01	0.15uF	25	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11E222KA01	2200pF	25	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11E223KA01	22000pF	25	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11E224KA40	0.22uF	25	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11E332KA01	3300pF	25	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11E333KA01	33000pF	25	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11E472KA01	4700pF	25	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11E473KA01	47000pF	25	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11E682KA01	6800pF	25	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11E683KA42	68000pF	25	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11H102KA01	1000pF	50	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11H103KA01	10000pF	50	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11H104KA42	0.1uF	50	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11H152KA01	1500pF	50	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11H153KA01	15000pF	50	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11H222KA01	2200pF	50	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11H223KA01	22000pF	50	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11H332KA01	3300pF	50	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11H333KA40	33000pF	50	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11H472KA01	4700pF	50	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GCM188R11H473KA40	47000pF	50	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11H682KA01	6800pF	50	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R11H683KA42	68000pF	50	R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM219R11A474KA01	0.47uF	10	R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive
GCM219R11C105KA01	1uF	16	R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive
GCM219R11C224KA01	0.22uF	16	R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive
GCM219R11C684KA01	0.68uF	16	R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive
GCM219R11E334KA01	0.33uF	25	R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive
GCM219R11E474KA40	0.47uF	25	R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive
GCM21BR11A105KA01	1uF	10	R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR11C474KA01	0.47uF	16	R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR11E104KA01	0.1uF	25	R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR11E105KA42	1uF	25	R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR11E154KA01	0.15uF	25	R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR11E224KA01	0.22uF	25	R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR11E684KA40	0.68uF	25	R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR11H104KA01	0.1uF	50	R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR11H154KA01	0.15uF	50	R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR11H224KA01	0.22uF	50	R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR11H333KA01	33000pF	50	R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR11H473KA01	47000pF	50	R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR11H683KA01	68000pF	50	R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM31CR11A106KA49	10uF	10	R	3216M/1206	1.8	+/-10%	Powertrain/Safety for Automotive
GCM31CR11C475KA01	4.7uF	16	R	3216M/1206	1.8	+/-10%	Powertrain/Safety for Automotive
GCM31CR11H684KA01	0.68uF	50	R	3216M/1206	1.8	+/-10%	Powertrain/Safety for Automotive
GCM31MR11A225KA36	2.2uF	10	R	3216M/1206	1.3	+/-10%	Powertrain/Safety for Automotive
GCM31MR11C105KA01	1uF	16	R	3216M/1206	1.25	+/-10%	Powertrain/Safety for Automotive
GCM31MR11C225KA36	2.2uF	16	R	3216M/1206	1.3	+/-10%	Powertrain/Safety for Automotive
GCM31MR11E105KA01	1uF	25	R	3216M/1206	1.25	+/-10%	Powertrain/Safety for Automotive
GCM31MR11E225KA42	2.2uF	25	R	3216M/1206	1.3	+/-10%	Powertrain/Safety for Automotive
GCM31MR11H334KA01	0.33uF	50	R	3216M/1206	1.25	+/-10%	Powertrain/Safety for Automotive
GCM31MR11H474KA01	0.47uF	50	R	3216M/1206	1.25	+/-10%	Powertrain/Safety for Automotive
GCM32DR11C106KA01	10uF	16	R	3225M/1210	2.2	+/-10%	Powertrain/Safety for Automotive
GCM32DR11E475KA40	4.7uF	25	R	3225M/1210	2.2	+/-10%	Powertrain/Safety for Automotive
GCM32ER11A226KE11	22uF	10	R	3225M/1210	2.7	+/-10%	Powertrain/Safety for Automotive
GCM32ER11A226ME11	22uF	10	R	3225M/1210	2.7	+/-20%	Powertrain/Safety for Automotive
GCM32ER11H105KA01	1uF	50	R	3225M/1210	2.7	+/-10%	Powertrain/Safety for Automotive
GCM32RR11E105KA01	1uF	25	R	3225M/1210	2.0	+/-10%	Powertrain/Safety for Automotive

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GJ431CC81E105KA01	1uF	25	X6S	3216M/1206	1.8	+/-10%	Audio signal low distortion
GJ821BR71H105KA12	1uF	50	X7R	2012M/0805	1.35	+/-10%	Acoustic noise reduction
GJ8319R61H225KA12	2.2uF	50	X5R	3216M/1206	0.95	+/-10%	Acoustic noise reduction
GJ831CC81E105KA01	1uF	25	X6S	3216M/1206	1.8	+/-10%	Acoustic noise reduction
GJ831CR61E106KE83	10uF	25	X5R	3216M/1206	1.9	+/-10%	Acoustic noise reduction
GJ831CR71H475KA12	4.7uF	50	X7R	3216M/1206	1.8	+/-10%	Acoustic noise reduction
GJ832ER7YA106KA12	10uF	35	X7R	3225M/1210	2.7	+/-10%	Acoustic noise reduction
GRJ155R60J106ME11	10uF	6.3	X5R	1005M/0402	0.7	+/-20%	Resin external electrode
GRJ188C70J475KE11	4.7uF	6.3	X7S	1608M/0603	1.0	+/-10%	Resin external electrode
GRJ188C70J475ME11	4.7uF	6.3	X7S	1608M/0603	1.0	+/-20%	Resin external electrode
GRJ188R60J106ME11	10uF	6.3	X5R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R60J475KE11	4.7uF	6.3	X5R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R60J475ME11	4.7uF	6.3	X5R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R61A106ME11	10uF	10	X5R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R61A475KE11	4.7uF	10	X5R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R61A475ME11	4.7uF	10	X5R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R61C105KE11	1uF	16	X5R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R61C105ME11	1uF	16	X5R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R6YA105KE11	1uF	35	X5R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R70J225KE11	2.2uF	6.3	X7R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R70J225ME11	2.2uF	6.3	X7R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R71C474KE11	0.47uF	16	X7R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R71C474ME11	0.47uF	16	X7R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R71E105KE11	1uF	25	X7R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R71E105ME11	1uF	25	X7R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R71E224KE11	0.22uF	25	X7R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R71E224ME11	0.22uF	25	X7R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R71E473KE11	4700pF	25	X7R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R71E473ME11	4700pF	25	X7R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R71H102KE11	1000pF	50	X7R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R71H102ME11	1000pF	50	X7R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R71H103KE11	10000pF	50	X7R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R71H103ME11	10000pF	50	X7R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R71H104KE11	0.1uF	50	X7R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R71H104ME11	0.1uF	50	X7R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R71H222KE11	2200pF	50	X7R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R71H222ME11	2200pF	50	X7R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R71H223KE11	22000pF	50	X7R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R71H223ME11	22000pF	50	X7R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R71H224KE11	0.22uF	50	X7R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R71H224ME11	0.22uF	50	X7R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R71H472KE11	4700pF	50	X7R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R71H472ME11	4700pF	50	X7R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R71H473KE11	47000pF	50	X7R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R71H473ME11	47000pF	50	X7R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R72A102KE11	1000pF	100	X7R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R72A102ME11	1000pF	100	X7R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R72A103KE11	10000pF	100	X7R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R72A103ME11	10000pF	100	X7R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R72A104KE11	0.1uF	100	X7R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R72A104ME11	0.1uF	100	X7R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R72A222KE11	2200pF	100	X7R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R72A222ME11	2200pF	100	X7R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R72A223KE11	22000pF	100	X7R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R72A223ME11	22000pF	100	X7R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ188R72A472KE11	4700pF	100	X7R	1608M/0603	0.9	+/-10%	Resin external electrode
GRJ188R72A472ME11	4700pF	100	X7R	1608M/0603	0.9	+/-20%	Resin external electrode
GRJ216R71H102KE01	1000pF	50	X7R	2012M/0805	0.7	+/-10%	Resin external electrode
GRJ216R71H102ME01	1000pF	50	X7R	2012M/0805	0.7	+/-20%	Resin external electrode
GRJ216R71H103KE01	10000pF	50	X7R	2012M/0805	0.7	+/-10%	Resin external electrode
GRJ216R71H103ME01	10000pF	50	X7R	2012M/0805	0.7	+/-20%	Resin external electrode
GRJ216R71H222KE01	2200pF	50	X7R	2012M/0805	0.7	+/-10%	Resin external electrode
GRJ216R71H222ME01	2200pF	50	X7R	2012M/0805	0.7	+/-20%	Resin external electrode
GRJ216R71H223KE01	22000pF	50	X7R	2012M/0805	0.7	+/-10%	Resin external electrode
GRJ216R71H223ME01	22000pF	50	X7R	2012M/0805	0.7	+/-20%	Resin external electrode
GRJ216R71H471KE01	470pF	50	X7R	2012M/0805	0.7	+/-10%	Resin external electrode
GRJ216R71H471ME01	470pF	50	X7R	2012M/0805	0.7	+/-20%	Resin external electrode
GRJ216R71H472KE01	4700pF	50	X7R	2012M/0805	0.7	+/-10%	Resin external electrode

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRJ216R71H472ME01	4700pF	50	X7R	2012M/0805	0.7	+/-20%	Resin external electrode
GRJ216R72A102KE01	1000pF	100	X7R	2012M/0805	0.7	+/-10%	Resin external electrode
GRJ216R72A102ME01	1000pF	100	X7R	2012M/0805	0.7	+/-20%	Resin external electrode
GRJ216R72A103KE01	10000pF	100	X7R	2012M/0805	0.7	+/-10%	Resin external electrode
GRJ216R72A103ME01	10000pF	100	X7R	2012M/0805	0.7	+/-20%	Resin external electrode
GRJ216R72A222KE01	2200pF	100	X7R	2012M/0805	0.7	+/-10%	Resin external electrode
GRJ216R72A222ME01	2200pF	100	X7R	2012M/0805	0.7	+/-20%	Resin external electrode
GRJ216R72A223KE01	22000pF	100	X7R	2012M/0805	0.7	+/-10%	Resin external electrode
GRJ216R72A223ME01	22000pF	100	X7R	2012M/0805	0.7	+/-20%	Resin external electrode
GRJ216R72A472KE01	4700pF	100	X7R	2012M/0805	0.7	+/-10%	Resin external electrode
GRJ216R72A472ME01	4700pF	100	X7R	2012M/0805	0.7	+/-20%	Resin external electrode
GRJ219R72A221KE01	220pF	100	X7R	2012M/0805	0.95	+/-10%	Resin external electrode
GRJ219R72A221ME01	220pF	100	X7R	2012M/0805	0.95	+/-20%	Resin external electrode
GRJ219R72A471KE01	470pF	100	X7R	2012M/0805	0.95	+/-10%	Resin external electrode
GRJ219R72A471ME01	470pF	100	X7R	2012M/0805	0.95	+/-20%	Resin external electrode
GRJ21BC72A105KE11	1uF	100	X7S	2012M/0805	1.5	+/-10%	Resin external electrode
GRJ21BC72A105ME11	1uF	100	X7S	2012M/0805	1.5	+/-20%	Resin external electrode
GRJ21BR61E106KE01	10uF	25	X5R	2012M/0805	1.45	+/-10%	Resin external electrode
GRJ21BR71A106KE01	10uF	10	X7R	2012M/0805	1.45	+/-10%	Resin external electrode
GRJ21BR71A106ME01	10uF	10	X7R	2012M/0805	1.45	+/-20%	Resin external electrode
GRJ21BR71C475KE01	4.7uF	16	X7R	2012M/0805	1.45	+/-10%	Resin external electrode
GRJ21BR71C475ME01	4.7uF	16	X7R	2012M/0805	1.45	+/-20%	Resin external electrode
GRJ21BR71E105KE11	1uF	25	X7R	2012M/0805	1.45	+/-10%	Resin external electrode
GRJ21BR71E105ME11	1uF	25	X7R	2012M/0805	1.45	+/-20%	Resin external electrode
GRJ21BR71E225KE01	2.2uF	25	X7R	2012M/0805	1.45	+/-10%	Resin external electrode
GRJ21BR71E225ME01	2.2uF	25	X7R	2012M/0805	1.45	+/-20%	Resin external electrode
GRJ21BR71H104KE01	0.1uF	50	X7R	2012M/0805	1.45	+/-10%	Resin external electrode
GRJ21BR71H104ME01	0.1uF	50	X7R	2012M/0805	1.45	+/-20%	Resin external electrode
GRJ21BR71H105KE01	1uF	50	X7R	2012M/0805	1.45	+/-10%	Resin external electrode
GRJ21BR71H105ME01	1uF	50	X7R	2012M/0805	1.45	+/-20%	Resin external electrode
GRJ21BR71H224KE01	0.22uF	50	X7R	2012M/0805	1.45	+/-10%	Resin external electrode
GRJ21BR71H224ME01	0.22uF	50	X7R	2012M/0805	1.45	+/-20%	Resin external electrode
GRJ21BR71H473KE01	47000pF	50	X7R	2012M/0805	1.45	+/-10%	Resin external electrode
GRJ21BR71H473ME01	47000pF	50	X7R	2012M/0805	1.45	+/-20%	Resin external electrode
GRJ21BR71H474KE01	0.47uF	50	X7R	2012M/0805	1.45	+/-10%	Resin external electrode
GRJ21BR71H474ME01	0.47uF	50	X7R	2012M/0805	1.45	+/-20%	Resin external electrode
GRJ21BR72A104KE01	0.1uF	100	X7R	2012M/0805	1.45	+/-10%	Resin external electrode
GRJ21BR72A104ME01	0.1uF	100	X7R	2012M/0805	1.45	+/-20%	Resin external electrode
GRJ21BR72A473KE01	47000pF	100	X7R	2012M/0805	1.45	+/-10%	Resin external electrode
GRJ21BR72A473ME01	47000pF	100	X7R	2012M/0805	1.45	+/-20%	Resin external electrode
GRJ319R71H104KE11	0.1uF	50	X7R	3216M/1206	0.95	+/-10%	Resin external electrode
GRJ319R71H104ME11	0.1uF	50	X7R	3216M/1206	0.95	+/-20%	Resin external electrode
GRJ319R72A104KE11	0.1uF	100	X7R	3216M/1206	0.95	+/-10%	Resin external electrode
GRJ319R72A104ME11	0.1uF	100	X7R	3216M/1206	0.95	+/-20%	Resin external electrode
GRJ31CC71E106KE11	10uF	25	X7S	3216M/1206	2.0	+/-10%	Resin external electrode
GRJ31CC71E106ME11	10uF	25	X7S	3216M/1206	2.0	+/-20%	Resin external electrode
GRJ31CC72A475KE01	4.7uF	100	X7S	3216M/1206	1.9	+/-10%	Resin external electrode
GRJ31CC72A475ME01	4.7uF	100	X7S	3216M/1206	1.9	+/-20%	Resin external electrode
GRJ31CC8YA106KE01	10uF	35	X6S	3216M/1206	1.9	+/-10%	Resin external electrode
GRJ31CC8YA106ME01	10uF	35	X6S	3216M/1206	1.9	+/-20%	Resin external electrode
GRJ31CR61E106KE11	10uF	25	X5R	3216M/1206	1.9	+/-10%	Resin external electrode
GRJ31CR70J226KE12	22uF	6.3	X7R	3216M/1206	1.9	+/-10%	Resin external electrode
GRJ31CR70J226ME12	22uF	6.3	X7R	3216M/1206	1.9	+/-20%	Resin external electrode
GRJ31CR71A106KE11	10uF	10	X7R	3216M/1206	1.9	+/-10%	Resin external electrode
GRJ31CR71A106ME11	10uF	10	X7R	3216M/1206	1.9	+/-20%	Resin external electrode
GRJ31CR71A226KE12	22uF	10	X7R	3216M/1206	1.9	+/-10%	Resin external electrode
GRJ31CR71A226ME12	22uF	10	X7R	3216M/1206	1.9	+/-20%	Resin external electrode
GRJ31CR71C106KE11	10uF	16	X7R	3216M/1206	1.9	+/-10%	Resin external electrode
GRJ31CR71C106ME11	10uF	16	X7R	3216M/1206	1.9	+/-20%	Resin external electrode
GRJ31CR71C475KE11	4.7uF	16	X7R	3216M/1206	1.9	+/-10%	Resin external electrode
GRJ31CR71C475ME11	4.7uF	16	X7R	3216M/1206	1.9	+/-20%	Resin external electrode
GRJ31CR71E106KE11	10uF	25	X7R	3216M/1206	1.9	+/-10%	Resin external electrode
GRJ31CR71E106ME11	10uF	25	X7R	3216M/1206	1.9	+/-20%	Resin external electrode
GRJ31CR71H105KE11	1uF	50	X7R	3216M/1206	1.9	+/-10%	Resin external electrode
GRJ31CR71H105ME11	1uF	50	X7R	3216M/1206	1.9	+/-20%	Resin external electrode
GRJ31CR71H225KE11	2.2uF	50	X7R	3216M/1206	1.9	+/-10%	Resin external electrode
GRJ31CR71H225ME11	2.2uF	50	X7R	3216M/1206	1.9	+/-20%	Resin external electrode
GRJ31CR71H475KE11	4.7uF	50	X7R	3216M/1206	1.9	+/-10%	Resin external electrode

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRJ31CR71H475ME11	4.7uF	50	X7R	3216M/1206	1.9	+/-20%	Resin external electrode
GRJ31CR72A105KE11	1uF	100	X7R	3216M/1206	1.9	+/-10%	Resin external electrode
GRJ31CR72A105ME11	1uF	100	X7R	3216M/1206	1.9	+/-20%	Resin external electrode
GRJ31CZ72A475KE01	4.7uF	100	X7R(Murata)	3216M/1206	1.9	+/-10%	Resin external electrode
GRJ31CZ72A475ME01	4.7uF	100	X7R(Murata)	3216M/1206	1.9	+/-20%	Resin external electrode
GRJ31MR71C225KE11	2.2uF	16	X7R	3216M/1206	1.35	+/-10%	Resin external electrode
GRJ31MR71C225ME11	2.2uF	16	X7R	3216M/1206	1.35	+/-20%	Resin external electrode
GRJ31MR71E225KE11	2.2uF	25	X7R	3216M/1206	1.35	+/-10%	Resin external electrode
GRJ31MR71E225ME11	2.2uF	25	X7R	3216M/1206	1.35	+/-20%	Resin external electrode
GRJ31MR71H104KE01	0.1uF	50	X7R	3216M/1206	1.35	+/-10%	Resin external electrode
GRJ31MR71H104ME01	0.1uF	50	X7R	3216M/1206	1.35	+/-20%	Resin external electrode
GRJ31MR71H105KE01	1uF	50	X7R	3216M/1206	1.35	+/-10%	Resin external electrode
GRJ31MR71H105ME01	1uF	50	X7R	3216M/1206	1.35	+/-20%	Resin external electrode
GRJ31MR71H224KE01	0.22uF	50	X7R	3216M/1206	1.35	+/-10%	Resin external electrode
GRJ31MR71H224ME01	0.22uF	50	X7R	3216M/1206	1.35	+/-20%	Resin external electrode
GRJ31MR71H474KE01	0.47uF	50	X7R	3216M/1206	1.35	+/-10%	Resin external electrode
GRJ31MR71H474ME01	0.47uF	50	X7R	3216M/1206	1.35	+/-20%	Resin external electrode
GRJ31MR72A224KE01	0.22uF	100	X7R	3216M/1206	1.35	+/-10%	Resin external electrode
GRJ31MR72A224ME01	0.22uF	100	X7R	3216M/1206	1.35	+/-20%	Resin external electrode
GRJ32DC72A475KE11	4.7uF	100	X7S	3225M/1210	2.3	+/-10%	Resin external electrode
GRJ32DC72A475ME11	4.7uF	100	X7S	3225M/1210	2.3	+/-20%	Resin external electrode
GRJ32DR72A225KE11	2.2uF	100	X7R	3225M/1210	2.3	+/-10%	Resin external electrode
GRJ32DR72A225ME11	2.2uF	100	X7R	3225M/1210	2.3	+/-20%	Resin external electrode
GRJ32EC71E226KE11	22uF	25	X7S	3225M/1210	2.85	+/-10%	Resin external electrode
GRJ32EC71H106KE11	10uF	50	X7S	3225M/1210	2.8	+/-10%	Resin external electrode
GRJ32EC71H106ME11	10uF	50	X7S	3225M/1210	2.8	+/-20%	Resin external electrode
GRJ32ER70J476KE11	47uF	6.3	X7R	3225M/1210	2.8	+/-10%	Resin external electrode
GRJ32ER70J476ME11	47uF	6.3	X7R	3225M/1210	2.8	+/-20%	Resin external electrode
GRJ32ER71A226KE11	22uF	10	X7R	3225M/1210	2.8	+/-10%	Resin external electrode
GRJ32ER71A226ME11	22uF	10	X7R	3225M/1210	2.8	+/-20%	Resin external electrode
GRJ32ER71A476KE11	47uF	10	X7R	3225M/1210	2.8	+/-10%	Resin external electrode
GRJ32ER71A476ME11	47uF	10	X7R	3225M/1210	2.8	+/-20%	Resin external electrode
GRJ32ER71C226KE11	22uF	16	X7R	3225M/1210	2.8	+/-10%	Resin external electrode
GRJ32ER71C226ME11	22uF	16	X7R	3225M/1210	2.8	+/-20%	Resin external electrode
GRJ32ER71E106KE11	10uF	25	X7R	3225M/1210	2.8	+/-10%	Resin external electrode
GRJ32ER71E106ME11	10uF	25	X7R	3225M/1210	2.8	+/-20%	Resin external electrode
GRJ32ER71H106KE11	10uF	50	X7R	3225M/1210	2.8	+/-10%	Resin external electrode
GRJ32ER71H106ME11	10uF	50	X7R	3225M/1210	2.8	+/-20%	Resin external electrode
GRJ32ER71H475KE11	4.7uF	50	X7R	3225M/1210	2.8	+/-10%	Resin external electrode
GRJ32ER71H475ME11	4.7uF	50	X7R	3225M/1210	2.8	+/-20%	Resin external electrode
GRJ32ER71K475KE11	4.7uF	80	X7R	3225M/1210	2.8	+/-10%	Resin external electrode
GRJ32ER71K475ME11	4.7uF	80	X7R	3225M/1210	2.8	+/-20%	Resin external electrode
GRM011R60G103KE01	10000pF	4	X5R	0201M/008004	0.14	+/-10%	Ultra-small
GRM011R60G332KE01	3300pF	4	X5R	0201M/008004	0.14	+/-10%	Ultra-small
GRM011R60G472KE01	4700pF	4	X5R	0201M/008004	0.14	+/-10%	Ultra-small
GRM011R60G682KE01	6800pF	4	X5R	0201M/008004	0.14	+/-10%	Ultra-small
GRM011R60J102KE01	1000pF	6.3	X5R	0201M/008004	0.14	+/-10%	Ultra-small
GRM011R60J102ME01	1000pF	6.3	X5R	0201M/008004	0.14	+/-20%	Ultra-small
GRM011R60J103KE01	10000pF	6.3	X5R	0201M/008004	0.14	+/-10%	Ultra-small
GRM011R60J103ME01	10000pF	6.3	X5R	0201M/008004	0.14	+/-20%	Ultra-small
GRM011R60J152KE01	1500pF	6.3	X5R	0201M/008004	0.14	+/-10%	Ultra-small
GRM011R60J152ME01	1500pF	6.3	X5R	0201M/008004	0.14	+/-20%	Ultra-small
GRM011R60J222KE01	2200pF	6.3	X5R	0201M/008004	0.14	+/-10%	Ultra-small
GRM011R60J222ME01	2200pF	6.3	X5R	0201M/008004	0.14	+/-20%	Ultra-small
GRM011R60J332KE01	3300pF	6.3	X5R	0201M/008004	0.14	+/-10%	Ultra-small
GRM011R60J332ME01	3300pF	6.3	X5R	0201M/008004	0.14	+/-20%	Ultra-small
GRM011R60J472KE01	4700pF	6.3	X5R	0201M/008004	0.14	+/-10%	Ultra-small
GRM011R60J472ME01	4700pF	6.3	X5R	0201M/008004	0.14	+/-20%	Ultra-small
GRM011R60J682KE01	6800pF	6.3	X5R	0201M/008004	0.14	+/-10%	Ultra-small
GRM011R60J682ME01	6800pF	6.3	X5R	0201M/008004	0.14	+/-20%	Ultra-small
GRM011R61A101KE01	100pF	10	X5R	0201M/008004	0.14	+/-10%	Ultra-small
GRM011R61A101ME01	100pF	10	X5R	0201M/008004	0.14	+/-20%	Ultra-small
GRM011R61A151KE01	150pF	10	X5R	0201M/008004	0.14	+/-10%	Ultra-small
GRM011R61A151ME01	150pF	10	X5R	0201M/008004	0.14	+/-20%	Ultra-small
GRM011R61A221KE01	220pF	10	X5R	0201M/008004	0.14	+/-10%	Ultra-small
GRM011R61A221ME01	220pF	10	X5R	0201M/008004	0.14	+/-20%	Ultra-small
GRM011R61A331KE01	330pF	10	X5R	0201M/008004	0.14	+/-10%	Ultra-small
GRM011R61A331ME01	330pF	10	X5R	0201M/008004	0.14	+/-20%	Ultra-small

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM011R61A471KE01	470pF	10	X5R	0201M/008004	0.14	+/-10%	Ultra-small
GRM011R61A471ME01	470pF	10	X5R	0201M/008004	0.14	+/-20%	Ultra-small
GRM011R61A681KE01	680pF	10	X5R	0201M/008004	0.14	+/-10%	Ultra-small
GRM011R61A681ME01	680pF	10	X5R	0201M/008004	0.14	+/-20%	Ultra-small
GRM022D80E104ME15	0.1uF	2.5	X6T	0402M/01005	0.22	+/-20%	Ultra-small
GRM022D80E224ME14	0.22uF	2.5	X6T	0402M/01005	0.22	+/-20%	Ultra-small
GRM022D80G104ME15	0.1uF	4	X6T	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R60G104ME15	0.1uF	4	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R60G153KE15	15000pF	4	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R60G153ME15	15000pF	4	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R60G223KE15	22000pF	4	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R60G223ME15	22000pF	4	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R60G224ME14	0.22uF	4	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R60G333KE15	33000pF	4	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R60G333ME15	33000pF	4	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R60G473KE15	47000pF	4	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R60G473ME15	47000pF	4	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R60G474ME15	0.47uF	4	X5R	0402M/01005	0.25	+/-20%	Ultra-small
GRM022R60G683ME15	68000pF	4	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R60J102KE19	1000pF	6.3	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R60J102ME19	1000pF	6.3	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R60J103KE19	10000pF	6.3	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R60J103ME19	10000pF	6.3	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R60J104KE15	0.1uF	6.3	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R60J104ME15	0.1uF	6.3	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R60J152KE19	1500pF	6.3	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R60J152ME19	1500pF	6.3	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R60J153ME15	15000pF	6.3	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R60J182KE19	1800pF	6.3	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R60J222KE19	2200pF	6.3	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R60J222ME19	2200pF	6.3	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R60J223KE15	22000pF	6.3	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R60J223ME15	22000pF	6.3	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R60J224KE14	0.22uF	6.3	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R60J224ME14	0.22uF	6.3	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R60J332KE19	3300pF	6.3	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R60J332ME19	3300pF	6.3	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R60J333ME15	33000pF	6.3	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R60J392KE19	3900pF	6.3	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R60J472KE19	4700pF	6.3	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R60J472ME19	4700pF	6.3	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R60J473ME15	47000pF	6.3	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R60J474ME15	0.47uF	6.3	X5R	0402M/01005	0.25	+/-20%	Ultra-small
GRM022R60J681KE19	680pF	6.3	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R60J681ME19	680pF	6.3	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R60J682KE19	6800pF	6.3	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R60J682ME19	6800pF	6.3	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R60J683ME15	68000pF	6.3	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R61A101KA01	100pF	10	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R61A101MA01	100pF	10	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R61A102KE19	1000pF	10	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R61A102ME19	1000pF	10	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R61A103KE19	10000pF	10	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R61A103ME19	10000pF	10	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R61A104ME01	0.1uF	10	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R61A151KA01	150pF	10	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R61A151MA01	150pF	10	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R61A152KE19	1500pF	10	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R61A152ME19	1500pF	10	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R61A221KA01	220pF	10	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R61A221MA01	220pF	10	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R61A222KE19	2200pF	10	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R61A222ME19	2200pF	10	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R61A331KA01	330pF	10	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R61A331MA01	330pF	10	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R61A332KE19	3300pF	10	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R61A332ME19	3300pF	10	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R61A471KA01	470pF	10	X5R	0402M/01005	0.22	+/-10%	Ultra-small

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM022R61A471MA01	470pF	10	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R61A472KE19	4700pF	10	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R61A472ME19	4700pF	10	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R61A562KE19	5600pF	10	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R61A680KA01	68pF	10	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R61A680MA01	68pF	10	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R61A681KE19	680pF	10	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R61A681ME19	680pF	10	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R61A682KE19	6800pF	10	X5R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R61A682ME19	6800pF	10	X5R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R61A821KE19	820pF	10	X5R	0402M/01005	0.22	+/-10%	General Purpose
GRM022R71A101KA01	100pF	10	X7R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R71A101MA01	100pF	10	X7R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R71A102KA12	1000pF	10	X7R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R71A102MA12	1000pF	10	X7R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R71A121KA01	120pF	10	X7R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R71A151KA01	150pF	10	X7R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R71A151MA01	150pF	10	X7R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R71A181KA01	180pF	10	X7R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R71A221KA01	220pF	10	X7R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R71A221MA01	220pF	10	X7R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R71A331KA01	330pF	10	X7R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R71A331MA01	330pF	10	X7R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R71A471KA01	470pF	10	X7R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R71A471MA01	470pF	10	X7R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R71A680KA01	68pF	10	X7R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R71A680MA01	68pF	10	X7R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R71A681KA12	680pF	10	X7R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R71A681MA12	680pF	10	X7R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R71A821KA12	820pF	10	X7R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R71A821MA12	820pF	10	X7R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R71C101KE14	100pF	16	X7R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R71C101ME14	100pF	16	X7R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R71C102KE14	1000pF	16	X7R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R71C102ME14	1000pF	16	X7R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R71C151KE14	150pF	16	X7R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R71C151ME14	150pF	16	X7R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R71C221KE14	220pF	16	X7R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R71C221ME14	220pF	16	X7R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R71C271KE14	270pF	16	X7R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R71C331KE14	330pF	16	X7R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R71C331ME14	330pF	16	X7R	0402M/01005	0.22	+/-20%	Ultra-small
GRM022R71C471KE14	470pF	16	X7R	0402M/01005	0.22	+/-10%	Ultra-small
GRM022R71C471ME14	470pF	16	X7R	0402M/01005	0.22	+/-20%	Ultra-small
GRM032R60G105ME05	1uF	4	X5R	0603M/0201	0.22	+/-20%	Ultra-small
GRM032R60J104KE15	0.1uF	6.3	X5R	0603M/0201	0.22	+/-10%	Ultra-small
GRM032R60J105ME05	1uF	6.3	X5R	0603M/0201	0.22	+/-20%	Ultra-small
GRM033C71A104KE14	0.1uF	10	X7S	0603M/0201	0.33	+/-10%	Ultra-small
GRM033C71A104ME14	0.1uF	10	X7S	0603M/0201	0.33	+/-20%	Ultra-small
GRM033C71C104KE14	0.1uF	16	X7S	0603M/0201	0.33	+/-10%	Ultra-small
GRM033C71C104ME14	0.1uF	16	X7S	0603M/0201	0.33	+/-20%	Ultra-small
GRM033C80E224ME15	0.22uF	2.5	X6S	0603M/0201	0.33	+/-20%	Ultra-small
GRM033C80G104KE19	0.1uF	4	X6S	0603M/0201	0.33	+/-10%	Ultra-small
GRM033C80G153KE01	15000pF	4	X6S	0603M/0201	0.33	+/-10%	Ultra-small
GRM033C80G223KE01	22000pF	4	X6S	0603M/0201	0.33	+/-10%	Ultra-small
GRM033C80G224ME15	0.22uF	4	X6S	0603M/0201	0.33	+/-20%	Ultra-small
GRM033C80G224ME90	0.22uF	4	X6S	0603M/0201	0.33	+/-20%	Ultra-small
GRM033C80G333KE01	33000pF	4	X6S	0603M/0201	0.33	+/-10%	Ultra-small
GRM033C80G473KE01	47000pF	4	X6S	0603M/0201	0.33	+/-10%	Ultra-small
GRM033C80J104KE15	0.1uF	6.3	X6S	0603M/0201	0.33	+/-10%	Ultra-small
GRM033C80J104KE84	0.1uF	6.3	X6S	0603M/0201	0.33	+/-10%	Ultra-small
GRM033C80J104ME84	0.1uF	6.3	X6S	0603M/0201	0.33	+/-20%	Ultra-small
GRM033C80J105ME05	1uF	6.3	X6S	0603M/0201	0.39	+/-20%	Ultra-small
GRM033C80J153KE01	15000pF	6.3	X6S	0603M/0201	0.33	+/-10%	Ultra-small
GRM033C80J153ME01	15000pF	6.3	X6S	0603M/0201	0.33	+/-20%	Ultra-small
GRM033C80J223KE01	22000pF	6.3	X6S	0603M/0201	0.33	+/-10%	Ultra-small
GRM033C80J223ME01	22000pF	6.3	X6S	0603M/0201	0.33	+/-20%	Ultra-small
GRM033C80J224KE90	0.22uF	6.3	X6S	0603M/0201	0.33	+/-10%	Ultra-small

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM033C80J224ME90	0.22uF	6.3	X6S	0603M/0201	0.33	+/-20%	Ultra-small
GRM033C80J333KE01	33000pF	6.3	X6S	0603M/0201	0.33	+/-10%	Ultra-small
GRM033C80J333ME01	33000pF	6.3	X6S	0603M/0201	0.33	+/-20%	Ultra-small
GRM033C80J473KE19	47000pF	6.3	X6S	0603M/0201	0.33	+/-10%	Ultra-small
GRM033C80J473ME19	47000pF	6.3	X6S	0603M/0201	0.33	+/-20%	Ultra-small
GRM033C80J683KE84	68000pF	6.3	X6S	0603M/0201	0.33	+/-10%	Ultra-small
GRM033C80J683ME84	68000pF	6.3	X6S	0603M/0201	0.33	+/-20%	Ultra-small
GRM033C81A104KE14	0.1uF	10	X6S	0603M/0201	0.33	+/-10%	Ultra-small
GRM033C81A105ME05	1uF	10	X6S	0603M/0201	0.39	+/-20%	Ultra-small
GRM033C81A473KE05	47000pF	10	X6S	0603M/0201	0.33	+/-10%	Ultra-small
GRM033C81C104KE14	0.1uF	16	X6S	0603M/0201	0.33	+/-10%	Ultra-small
GRM033C81C104ME14	0.1uF	16	X6S	0603M/0201	0.33	+/-20%	Ultra-small
GRM033C81E103KE14	10000pF	25	X6S	0603M/0201	0.33	+/-10%	Ultra-small
GRM033C81E103ME14	10000pF	25	X6S	0603M/0201	0.33	+/-20%	Ultra-small
GRM033C81E104KE14	0.1uF	25	X6S	0603M/0201	0.33	+/-10%	Ultra-small
GRM033C81E104ME14	0.1uF	25	X6S	0603M/0201	0.33	+/-20%	Ultra-small
GRM033D70E105ME15	1uF	2.5	X7T	0603M/0201	0.39	+/-20%	Ultra-small
GRM033R60G105MEA2	1uF	4	X5R	0603M/0201	0.35	+/-20%	Ultra-small
GRM033R60G155ME14	1.5uF	4	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R60G224ME15	0.22uF	4	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R60G225ME44	2.2uF	4	X5R	0603M/0201	0.35	+/-20%	Ultra-small
GRM033R60G225ME47	2.2uF	4	X5R	0603M/0201	0.39	+/-20%	Ultra-small
GRM033R60G474ME90	0.47uF	4	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R60J103KA01	10000pF	6.3	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R60J104KE19	0.1uF	6.3	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R60J104KE84	0.1uF	6.3	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R60J105MEA2	1uF	6.3	X5R	0603M/0201	0.35	+/-20%	Ultra-small
GRM033R60J153KE01	15000pF	6.3	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R60J155ME14	1.5uF	6.3	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R60J223KE01	22000pF	6.3	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R60J224KE15	0.22uF	6.3	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R60J224ME15	0.22uF	6.3	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R60J224ME90	0.22uF	6.3	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R60J225ME15	2.2uF	6.3	X5R	0603M/0201	0.35	+/-20%	Ultra-small
GRM033R60J225ME47	2.2uF	6.3	X5R	0603M/0201	0.39	+/-20%	Ultra-small
GRM033R60J273KE01	27000pF	6.3	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R60J333KE01	33000pF	6.3	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R60J473KE19	47000pF	6.3	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R60J474KE90	0.47uF	6.3	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61A103KA01	10000pF	10	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61A103MA01	10000pF	10	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61A104KE15	0.1uF	10	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61A104KE84	0.1uF	10	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61A104ME84	0.1uF	10	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61A105ME15	1uF	10	X5R	0603M/0201	0.39	+/-20%	Ultra-small
GRM033R61A123KE84	12000pF	10	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61A123ME84	12000pF	10	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61A152KA01	1500pF	10	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61A153KE84	15000pF	10	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61A153ME84	15000pF	10	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61A182KA01	1800pF	10	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61A183KE84	18000pF	10	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61A183ME84	18000pF	10	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61A222KA01	2200pF	10	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61A223KE84	22000pF	10	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61A223ME84	22000pF	10	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61A224KE90	0.22uF	10	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61A224ME90	0.22uF	10	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61A225KE47	2.2uF	10	X5R	0603M/0201	0.39	+/-10%	Ultra-small
GRM033R61A225ME47	2.2uF	10	X5R	0603M/0201	0.39	+/-20%	Ultra-small
GRM033R61A273KE84	27000pF	10	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61A273ME84	27000pF	10	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61A332KA01	3300pF	10	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61A333KE84	33000pF	10	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61A333ME84	33000pF	10	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61A393KE84	39000pF	10	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61A393ME84	39000pF	10	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61A472KA01	4700pF	10	X5R	0603M/0201	0.33	+/-10%	Ultra-small

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM033R61A472MA01	4700pF	10	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61A473KE84	4700pF	10	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61A473ME84	4700pF	10	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61A682KA01	6800pF	10	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61A682MA01	6800pF	10	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61A683KE84	6800pF	10	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61A683ME84	6800pF	10	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61C103KA12	10000pF	16	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61C103MA12	10000pF	16	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61C104KE14	0.1uF	16	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61C104KE18	0.1uF	16	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61C104KE84	0.1uF	16	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61C104ME14	0.1uF	16	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61C104ME18	0.1uF	16	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61C104ME84	0.1uF	16	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61C153KE84	15000pF	16	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61C153ME84	15000pF	16	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61C223KE84	22000pF	16	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61C223ME84	22000pF	16	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61C224KE14	0.22uF	16	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61C224ME14	0.22uF	16	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61C333KE84	33000pF	16	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61C333ME84	33000pF	16	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61C473KE84	47000pF	16	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61C473ME84	47000pF	16	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61C683KE84	68000pF	16	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61C683ME84	68000pF	16	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61E101KA01	100pF	25	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61E102KA01	1000pF	25	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61E103KA12	10000pF	25	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61E103MA12	10000pF	25	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61E104KE14	0.1uF	25	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61E104ME14	0.1uF	25	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61E151KA01	150pF	25	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61E221KA01	220pF	25	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61E331KA01	330pF	25	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61E471KA01	470pF	25	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61E472KA12	4700pF	25	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61E472MA12	4700pF	25	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61E681KA01	680pF	25	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61E682KA12	6800pF	25	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R61E682MA12	6800pF	25	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R61H471KA12	470pF	50	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R6YA104KE14	0.1uF	35	X5R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R6YA104ME14	0.1uF	35	X5R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R70J103KA01	10000pF	6.3	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R70J152KA01	1500pF	6.3	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R70J222KA01	2200pF	6.3	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R70J332KA01	3300pF	6.3	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R70J472KA01	4700pF	6.3	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R70J682KA01	6800pF	6.3	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71A103KA01	10000pF	10	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71A103MA01	10000pF	10	X7R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R71A122KA01	1200pF	10	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71A152KA01	1500pF	10	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71A222KA01	2200pF	10	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71A272KA01	2700pF	10	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71A332KA01	3300pF	10	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71A472KA01	4700pF	10	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71A472MA01	4700pF	10	X7R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R71A562KA01	5600pF	10	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71A682KA01	6800pF	10	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71A682MA01	6800pF	10	X7R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R71A822KA01	8200pF	10	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71C101KA01	100pF	16	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71C102KA01	1000pF	16	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71C103KE14	10000pF	16	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71C103ME14	10000pF	16	X7R	0603M/0201	0.33	+/-20%	Ultra-small

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM033R71C151KA01	150pF	16	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71C152KA01	1500pF	16	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71C182KA88	1800pF	16	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71C221KA01	220pF	16	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71C222KA88	2200pF	16	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71C271JA01	270pF	16	X7R	0603M/0201	0.33	+/-5%	Ultra-small
GRM033R71C271KA01	270pF	16	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71C331KA01	330pF	16	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71C332KA88	3300pF	16	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71C471KA01	470pF	16	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71C472KE14	4700pF	16	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71C472ME14	4700pF	16	X7R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R71C681KA01	680pF	16	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71C682KE14	6800pF	16	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71C682ME14	6800pF	16	X7R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R71E101KA01	100pF	25	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71E102KA01	1000pF	25	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71E103KE14	10000pF	25	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71E103ME14	10000pF	25	X7R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R71E121KA01	120pF	25	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71E151KA01	150pF	25	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71E152KA01	1500pF	25	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71E182KA12	1800pF	25	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71E221KA01	220pF	25	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71E222KA12	2200pF	25	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71E222MA12	2200pF	25	X7R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R71E331KA01	330pF	25	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71E332KA12	3300pF	25	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71E332MA12	3300pF	25	X7R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R71E471KA01	470pF	25	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71E472KE14	4700pF	25	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71E472ME14	4700pF	25	X7R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R71E681KA01	680pF	25	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71E682KE14	6800pF	25	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71E682ME14	6800pF	25	X7R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R71E821KA01	820pF	25	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71H101KA12	100pF	50	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71H101MA12	100pF	50	X7R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R71H102KA12	1000pF	50	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71H102MA12	1000pF	50	X7R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R71H151KA12	150pF	50	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71H151MA12	150pF	50	X7R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R71H152KA12	1500pF	50	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71H152MA12	1500pF	50	X7R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R71H221KA12	220pF	50	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71H221MA12	220pF	50	X7R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R71H331KA12	330pF	50	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71H331MA12	330pF	50	X7R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R71H471KA12	470pF	50	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71H471MA12	470pF	50	X7R	0603M/0201	0.33	+/-20%	Ultra-small
GRM033R71H561KA12	560pF	50	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71H681KA12	680pF	50	X7R	0603M/0201	0.33	+/-10%	Ultra-small
GRM033R71H681MA12	680pF	50	X7R	0603M/0201	0.33	+/-20%	Ultra-small
GRM035R60G475ME15	4.7uF	4	X5R	0603M/0201	0.55	+/-20%	Ultra-small
GRM035R60J475ME15	4.7uF	6.3	X5R	0603M/0201	0.55	+/-20%	Ultra-small
GRM152C80G104KE19	0.1uF	4	X6S	1005M/0402	0.22	+/-10%	General Purpose
GRM152C80G104ME19	0.1uF	4	X6S	1005M/0402	0.22	+/-20%	General Purpose
GRM152C80G224KE19	0.22uF	4	X6S	1005M/0402	0.22	+/-10%	General Purpose
GRM152C80G224ME19	0.22uF	4	X6S	1005M/0402	0.22	+/-20%	General Purpose
GRM152C80J104KE19	0.1uF	6.3	X6S	1005M/0402	0.22	+/-10%	General Purpose
GRM152C80J104ME19	0.1uF	6.3	X6S	1005M/0402	0.22	+/-20%	General Purpose
GRM152C80J224KE19	0.22uF	6.3	X6S	1005M/0402	0.22	+/-10%	General Purpose
GRM152C80J224ME19	0.22uF	6.3	X6S	1005M/0402	0.22	+/-20%	General Purpose
GRM152D70E104KE19	0.1uF	2.5	X7T	1005M/0402	0.22	+/-10%	General Purpose
GRM152D70E104ME19	0.1uF	2.5	X7T	1005M/0402	0.22	+/-20%	General Purpose
GRM152D70E224KE19	0.22uF	2.5	X7T	1005M/0402	0.22	+/-10%	General Purpose
GRM152D70E224ME19	0.22uF	2.5	X7T	1005M/0402	0.22	+/-20%	General Purpose
GRM152D70G104KE15	0.1uF	4	X7T	1005M/0402	0.22	+/-10%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM152D70G104ME15	0.1uF	4	X7T	1005M/0402	0.22	+/-20%	General Purpose
GRM152D70G224KE15	0.22uF	4	X7T	1005M/0402	0.22	+/-10%	General Purpose
GRM152D70G224ME15	0.22uF	4	X7T	1005M/0402	0.22	+/-20%	General Purpose
GRM152D80G105ME15	1uF	4	X6T	1005M/0402	0.22	+/-20%	General Purpose
GRM152D80G474ME15	0.47uF	4	X6T	1005M/0402	0.22	+/-20%	General Purpose
GRM152R60G105ME15	1uF	4	X5R	1005M/0402	0.22	+/-20%	General Purpose
GRM152R60J104KE19	0.1uF	6.3	X5R	1005M/0402	0.22	+/-10%	General Purpose
GRM152R60J104ME19	0.1uF	6.3	X5R	1005M/0402	0.22	+/-20%	General Purpose
GRM152R60J105ME15	1uF	6.3	X5R	1005M/0402	0.22	+/-20%	General Purpose
GRM152R60J224KE19	0.22uF	6.3	X5R	1005M/0402	0.22	+/-10%	General Purpose
GRM152R60J224ME19	0.22uF	6.3	X5R	1005M/0402	0.22	+/-20%	General Purpose
GRM152R60J225ME05	2.2uF	6.3	X5R	1005M/0402	0.22	+/-20%	General Purpose
GRM152R60J474ME15	0.47uF	6.3	X5R	1005M/0402	0.22	+/-20%	General Purpose
GRM152R61A104KE19	0.1uF	10	X5R	1005M/0402	0.22	+/-10%	General Purpose
GRM152R61A104ME19	0.1uF	10	X5R	1005M/0402	0.22	+/-20%	General Purpose
GRM152R61A224KE19	0.22uF	10	X5R	1005M/0402	0.22	+/-10%	General Purpose
GRM152R61A224ME19	0.22uF	10	X5R	1005M/0402	0.22	+/-20%	General Purpose
GRM153D80G105ME95	1uF	4	X6T	1005M/0402	0.33	+/-20%	General Purpose
GRM153D80J105ME95	1uF	6.3	X6T	1005M/0402	0.33	+/-20%	General Purpose
GRM153R60G105ME95	1uF	4	X5R	1005M/0402	0.33	+/-20%	General Purpose
GRM153R60G225ME95	2.2uF	4	X5R	1005M/0402	0.33	+/-20%	General Purpose
GRM153R60G475ME15	4.7uF	4	X5R	1005M/0402	0.33	+/-20%	General Purpose
GRM153R60J105ME95	1uF	6.3	X5R	1005M/0402	0.33	+/-20%	General Purpose
GRM153R60J225ME95	2.2uF	6.3	X5R	1005M/0402	0.33	+/-20%	General Purpose
GRM153R60J475ME15	4.7uF	6.3	X5R	1005M/0402	0.33	+/-20%	General Purpose
GRM153R61A105ME95	1uF	10	X5R	1005M/0402	0.33	+/-20%	General Purpose
GRM155C70J225KE11	2.2uF	6.3	X7S	1005M/0402	0.7	+/-10%	General Purpose
GRM155C70J225ME11	2.2uF	6.3	X7S	1005M/0402	0.7	+/-20%	General Purpose
GRM155C71A105KE11	1uF	10	X7S	1005M/0402	0.6	+/-10%	General Purpose
GRM155C71A225KE11	2.2uF	10	X7S	1005M/0402	0.7	+/-10%	General Purpose
GRM155C71A225ME11	2.2uF	10	X7S	1005M/0402	0.7	+/-20%	General Purpose
GRM155C71H104KE19	0.1uF	50	X7S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C71H333KE19	33000pF	50	X7S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C71H333ME19	33000pF	50	X7S	1005M/0402	0.55	+/-20%	General Purpose
GRM155C71H473KE19	47000pF	50	X7S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C71H473ME19	47000pF	50	X7S	1005M/0402	0.55	+/-20%	General Purpose
GRM155C71H683KE19	68000pF	50	X7S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C71H683ME19	68000pF	50	X7S	1005M/0402	0.55	+/-20%	General Purpose
GRM155C80G105KE19	1uF	4	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C80G154KE01	0.15uF	4	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C80G154ME01	0.15uF	4	X6S	1005M/0402	0.55	+/-20%	General Purpose
GRM155C80G224KE01	0.22uF	4	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C80G224ME01	0.22uF	4	X6S	1005M/0402	0.55	+/-20%	General Purpose
GRM155C80G334KE01	0.33uF	4	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C80G334ME01	0.33uF	4	X6S	1005M/0402	0.55	+/-20%	General Purpose
GRM155C80G474KE01	0.47uF	4	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C80G474ME01	0.47uF	4	X6S	1005M/0402	0.55	+/-20%	General Purpose
GRM155C80J105KE15	1uF	6.3	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C80J106ME11	10uF	6.3	X6S	1005M/0402	0.7	+/-20%	General Purpose
GRM155C80J154KE01	0.15uF	6.3	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C80J154ME01	0.15uF	6.3	X6S	1005M/0402	0.55	+/-20%	General Purpose
GRM155C80J224KE01	0.22uF	6.3	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C80J224ME01	0.22uF	6.3	X6S	1005M/0402	0.55	+/-20%	General Purpose
GRM155C80J225KE95	2.2uF	6.3	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C80J225ME95	2.2uF	6.3	X6S	1005M/0402	0.55	+/-20%	General Purpose
GRM155C80J334KE01	0.33uF	6.3	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C80J334ME01	0.33uF	6.3	X6S	1005M/0402	0.55	+/-20%	General Purpose
GRM155C80J474KE19	0.47uF	6.3	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C80J474ME19	0.47uF	6.3	X6S	1005M/0402	0.55	+/-20%	General Purpose
GRM155C80J475MEAA	4.7uF	6.3	X6S	1005M/0402	0.65	+/-20%	General Purpose
GRM155C81A105KA12	1uF	10	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C81A105MA12	1uF	10	X6S	1005M/0402	0.55	+/-20%	General Purpose
GRM155C81A225KE11	2.2uF	10	X6S	1005M/0402	0.7	+/-10%	General Purpose
GRM155C81A225ME11	2.2uF	10	X6S	1005M/0402	0.7	+/-20%	General Purpose
GRM155C81A225ME44	2.2uF	10	X6S	1005M/0402	0.6	+/-20%	General Purpose
GRM155C81C105KE11	1uF	16	X6S	1005M/0402	0.6	+/-10%	General Purpose
GRM155C81C105KE15	1uF	16	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C81C105ME11	1uF	16	X6S	1005M/0402	0.6	+/-20%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM155C81C225KE11	2.2uF	16	X6S	1005M/0402	0.7	+/-10%	General Purpose
GRM155C81C225ME11	2.2uF	16	X6S	1005M/0402	0.7	+/-20%	General Purpose
GRM155C81C474KE01	0.47uF	16	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C81C474ME01	0.47uF	16	X6S	1005M/0402	0.55	+/-20%	General Purpose
GRM155C81E104KA12	0.1uF	25	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C81E104MA12	0.1uF	25	X6S	1005M/0402	0.55	+/-20%	General Purpose
GRM155C81E105KE11	1uF	25	X6S	1005M/0402	0.6	+/-10%	General Purpose
GRM155C81E105ME11	1uF	25	X6S	1005M/0402	0.6	+/-20%	General Purpose
GRM155C81E224KE01	0.22uF	25	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C81E224ME01	0.22uF	25	X6S	1005M/0402	0.55	+/-20%	General Purpose
GRM155C81E225KE11	2.2uF	25	X6S	1005M/0402	0.7	+/-10%	General Purpose
GRM155C81E225ME11	2.2uF	25	X6S	1005M/0402	0.7	+/-20%	General Purpose
GRM155C81E683KA12	68000pF	25	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C81H104KE14	0.1uF	50	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C81H104KE19	0.1uF	50	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C81H104ME14	0.1uF	50	X6S	1005M/0402	0.55	+/-20%	General Purpose
GRM155C81H333KE14	33000pF	50	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C81H333ME14	33000pF	50	X6S	1005M/0402	0.55	+/-20%	General Purpose
GRM155C81H473KE14	47000pF	50	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C81H473KE19	47000pF	50	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C81H473ME14	47000pF	50	X6S	1005M/0402	0.55	+/-20%	General Purpose
GRM155C81H683KE14	68000pF	50	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C81H683ME14	68000pF	50	X6S	1005M/0402	0.55	+/-20%	General Purpose
GRM155C8YA224KE01	0.22uF	35	X6S	1005M/0402	0.55	+/-10%	General Purpose
GRM155C8YA224ME01	0.22uF	35	X6S	1005M/0402	0.55	+/-20%	General Purpose
GRM155D80E475ME47	4.7uF	2.5	X6T	1005M/0402	0.6	+/-20%	General Purpose
GRM155D80G225KE95	2.2uF	4	X6T	1005M/0402	0.55	+/-10%	General Purpose
GRM155D80G225ME95	2.2uF	4	X6T	1005M/0402	0.55	+/-20%	General Purpose
GRM155D80J225KE95	2.2uF	6.3	X6T	1005M/0402	0.55	+/-10%	General Purpose
GRM155D80J225ME95	2.2uF	6.3	X6T	1005M/0402	0.55	+/-20%	General Purpose
GRM155R60E106ME16	10uF	2.5	X5R	1005M/0402	0.7	+/-20%	General Purpose
GRM155R60G105ME01	1uF	4	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R60G106ME15	10uF	4	X5R	1005M/0402	0.65	+/-20%	General Purpose
GRM155R60G106ME44	10uF	4	X5R	1005M/0402	0.7	+/-20%	General Purpose
GRM155R60G106ME47	10uF	4	X5R	1005M/0402	0.5	+/-20%	General Purpose
GRM155R60G475ME47	4.7uF	4	X5R	1005M/0402	0.6	+/-20%	General Purpose
GRM155R60J104KA01	0.1uF	6.3	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R60J104MA01	0.1uF	6.3	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R60J105KE19	1uF	6.3	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R60J105ME19	1uF	6.3	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R60J106ME15	10uF	6.3	X5R	1005M/0402	0.65	+/-20%	General Purpose
GRM155R60J106ME47	10uF	6.3	X5R	1005M/0402	0.5	+/-20%	General Purpose
GRM155R60J154KE01	0.15uF	6.3	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R60J154ME01	0.15uF	6.3	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R60J224KE01	0.22uF	6.3	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R60J224ME01	0.22uF	6.3	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R60J334KE01	0.33uF	6.3	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R60J334ME01	0.33uF	6.3	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R60J474KE19	0.47uF	6.3	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R60J474ME19	0.47uF	6.3	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R60J475ME47	4.7uF	6.3	X5R	1005M/0402	0.6	+/-20%	General Purpose
GRM155R60J684KE19	0.68uF	6.3	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R60J684ME19	0.68uF	6.3	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R60J824KE19	0.82uF	6.3	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61A104KA01	0.1uF	10	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61A104MA01	0.1uF	10	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R61A105KE01	1uF	10	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61A105KE15	1uF	10	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61A105ME01	1uF	10	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R61A124KE19	0.12uF	10	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61A154KE19	0.15uF	10	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61A154ME19	0.15uF	10	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R61A184KE19	0.18uF	10	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61A224KE19	0.22uF	10	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61A224ME19	0.22uF	10	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R61A333KA01	33000pF	10	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61A334KE15	0.33uF	10	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61A334ME15	0.33uF	10	X5R	1005M/0402	0.55	+/-20%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM155R61A393KA01	39000pF	10	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61A473KA01	47000pF	10	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61A474KE15	0.47uF	10	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61A474ME15	0.47uF	10	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R61A475MEAA	4.7uF	10	X5R	1005M/0402	0.65	+/-20%	General Purpose
GRM155R61A683KA01	68000pF	10	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61A684KE15	0.68uF	10	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61A684ME15	0.68uF	10	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R61C103KA01	10000pF	16	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61C104KA88	0.1uF	16	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61C105KA12	1uF	16	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61C105MA12	1uF	16	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R61C223KA01	22000pF	16	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61C224KA12	0.22uF	16	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61C224MA12	0.22uF	16	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R61C225KE11	2.2uF	16	X5R	1005M/0402	0.7	+/-10%	General Purpose
GRM155R61C225KE44	2.2uF	16	X5R	1005M/0402	0.6	+/-10%	General Purpose
GRM155R61C225ME11	2.2uF	16	X5R	1005M/0402	0.7	+/-20%	General Purpose
GRM155R61C333KA01	33000pF	16	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61C473KA01	47000pF	16	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61C474KE01	0.47uF	16	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61C474ME01	0.47uF	16	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R61C683KA88	68000pF	16	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61E102KA01	1000pF	25	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61E104KA87	0.1uF	25	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61E104MA87	0.1uF	25	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R61E105KA12	1uF	25	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61E105MA12	1uF	25	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R61E222KA01	2200pF	25	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61E224KE01	0.22uF	25	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61E224ME01	0.22uF	25	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R61E225KE11	2.2uF	25	X5R	1005M/0402	0.7	+/-10%	General Purpose
GRM155R61E225ME11	2.2uF	25	X5R	1005M/0402	0.7	+/-20%	General Purpose
GRM155R61E225ME15	2.2uF	25	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R61E472KA01	4700pF	25	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61E474KE01	0.47uF	25	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61E474ME01	0.47uF	25	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R61E683KA87	68000pF	25	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61E683MA87	68000pF	25	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R61H102KA01	1000pF	50	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61H104KE14	0.1uF	50	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61H104KE19	0.1uF	50	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61H104ME14	0.1uF	50	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R61H222KA01	2200pF	50	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61H333KE14	33000pF	50	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61H333KE19	33000pF	50	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61H333ME14	33000pF	50	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R61H333ME19	33000pF	50	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R61H472KA01	4700pF	50	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61H473KE14	47000pF	50	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61H473KE19	47000pF	50	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61H473ME14	47000pF	50	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R61H473ME19	47000pF	50	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R61H474KE11	0.47uF	50	X5R	1005M/0402	0.6	+/-10%	General Purpose
GRM155R61H474ME11	0.47uF	50	X5R	1005M/0402	0.6	+/-20%	General Purpose
GRM155R61H683KE14	68000pF	50	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61H683KE19	68000pF	50	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R61H683ME14	68000pF	50	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R61H683ME19	68000pF	50	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R62A104KE14	0.1uF	100	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R6YA105KE11	1uF	35	X5R	1005M/0402	0.6	+/-10%	General Purpose
GRM155R6YA105ME11	1uF	35	X5R	1005M/0402	0.6	+/-20%	General Purpose
GRM155R6YA224KE01	0.22uF	35	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R6YA224ME01	0.22uF	35	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R6YA225ME11	2.2uF	35	X5R	1005M/0402	0.7	+/-20%	General Purpose
GRM155R6YA474KE01	0.47uF	35	X5R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R6YA474ME01	0.47uF	35	X5R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R70G105KA12	1uF	4	X7R	1005M/0402	0.55	+/-10%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM155R70G105MA12	1uF	4	X7R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R70J104KA01	0.1uF	6.3	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R70J105KA12	1uF	6.3	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R70J105MA12	1uF	6.3	X7R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R70J223KA01	2200pF	6.3	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71A104KA01	0.1uF	10	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71A104MA01	0.1uF	10	X7R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R71A224KE01	0.22uF	10	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71A224ME01	0.22uF	10	X7R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R71A333MA01	3300pF	10	X7R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R71A474KE01	0.47uF	10	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71A474ME01	0.47uF	10	X7R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R71A683KA01	6800pF	10	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71A683MA01	6800pF	10	X7R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R71C102KA01	1000pF	16	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71C103KA01	1000pF	16	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71C103MA01	1000pF	16	X7R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R71C104KA88	0.1uF	16	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71C153KA01	1500pF	16	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71C154KA12	0.15uF	16	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71C183KA01	1800pF	16	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71C223KA01	2200pF	16	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71C223MA01	2200pF	16	X7R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R71C224KA12	0.22uF	16	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71C333KA01	3300pF	16	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71C472KA01	4700pF	16	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71C473KA01	4700pF	16	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71C563KA88	5600pF	16	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71C683KA88	6800pF	16	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71C823KA88	8200pF	16	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71E103KA01	1000pF	25	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71E104KE14	0.1uF	25	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71E104ME14	0.1uF	25	X7R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R71E123KA61	1200pF	25	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71E153KA61	1500pF	25	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71E222KA01	220pF	25	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71E223KA61	2200pF	25	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71E273KA88	2700pF	25	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71E333KA88	3300pF	25	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71E472KA01	4700pF	25	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71E473KA88	4700pF	25	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71E562KA01	5600pF	25	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71E682KA01	6800pF	25	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71E683KE14	6800pF	25	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71E683ME14	6800pF	25	X7R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R71E822KA01	8200pF	25	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H102KA01	1000pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H102MA01	1000pF	50	X7R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R71H103KA88	1000pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H104KE14	0.1uF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H104ME14	0.1uF	50	X7R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R71H122KA01	1200pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H152KA01	1500pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H153KA12	1500pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H182KA01	1800pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H221KA01	220pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H222KA01	220pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H223KA12	2200pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H271KA01	270pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H272KA01	2700pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H331KA01	330pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H332KA01	3300pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H333KE14	3300pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H333ME14	3300pF	50	X7R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R71H391KA01	390pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H392KA01	3900pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H393KE14	3900pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H471KA01	470pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM155R71H472KA01	4700pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H473KE14	47000pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H473ME14	47000pF	50	X7R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R71H561KA01	560pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H562KA88	5600pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H681KA01	680pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H682KA88	6800pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H683KE14	68000pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H683ME14	68000pF	50	X7R	1005M/0402	0.55	+/-20%	General Purpose
GRM155R71H821KA01	820pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R71H823KE14	82000pF	50	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R72A102KA01	1000pF	100	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R72A152KA01	1500pF	100	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R72A221KA01	220pF	100	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R72A222KA01	2200pF	100	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R72A331KA01	330pF	100	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R72A332KA01	3300pF	100	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R72A471KA01	470pF	100	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R72A472KA01	4700pF	100	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM155R72A681KA01	680pF	100	X7R	1005M/0402	0.55	+/-10%	General Purpose
GRM15XR61A153KA86	15000pF	10	X5R	1005M/0402	0.3	+/-10%	General Purpose
GRM15XR61A153MA86	15000pF	10	X5R	1005M/0402	0.3	+/-20%	General Purpose
GRM15XR61A223KA86	22000pF	10	X5R	1005M/0402	0.3	+/-10%	General Purpose
GRM15XR61A223MA86	22000pF	10	X5R	1005M/0402	0.3	+/-20%	General Purpose
GRM15XR61A333KA86	33000pF	10	X5R	1005M/0402	0.3	+/-10%	General Purpose
GRM15XR61A333MA86	33000pF	10	X5R	1005M/0402	0.3	+/-20%	General Purpose
GRM15XR71C103KA86	10000pF	16	X7R	1005M/0402	0.3	+/-10%	General Purpose
GRM15XR71C103MA86	10000pF	16	X7R	1005M/0402	0.3	+/-20%	General Purpose
GRM15XR71C332KA86	3300pF	16	X7R	1005M/0402	0.3	+/-10%	General Purpose
GRM15XR71C332MA86	3300pF	16	X7R	1005M/0402	0.3	+/-20%	General Purpose
GRM15XR71C472KA86	4700pF	16	X7R	1005M/0402	0.3	+/-10%	General Purpose
GRM15XR71C472MA86	4700pF	16	X7R	1005M/0402	0.3	+/-20%	General Purpose
GRM15XR71C682KA86	6800pF	16	X7R	1005M/0402	0.3	+/-10%	General Purpose
GRM15XR71C682MA86	6800pF	16	X7R	1005M/0402	0.3	+/-20%	General Purpose
GRM15XR71E222KA86	2200pF	25	X7R	1005M/0402	0.3	+/-10%	General Purpose
GRM15XR71E222MA86	2200pF	25	X7R	1005M/0402	0.3	+/-20%	General Purpose
GRM15XR71H102KA86	1000pF	50	X7R	1005M/0402	0.3	+/-10%	General Purpose
GRM15XR71H152KA86	1500pF	50	X7R	1005M/0402	0.3	+/-10%	General Purpose
GRM15XR71H221KA86	220pF	50	X7R	1005M/0402	0.3	+/-10%	General Purpose
GRM15XR71H331KA86	330pF	50	X7R	1005M/0402	0.3	+/-10%	General Purpose
GRM15XR71H471KA86	470pF	50	X7R	1005M/0402	0.3	+/-10%	General Purpose
GRM15XR71H681KA86	680pF	50	X7R	1005M/0402	0.3	+/-10%	General Purpose
GRM185C80J105KE26	1uF	6.3	X6S	1608M/0603	0.5	+/-10%	General Purpose
GRM185C80J475ME11	4.7uF	6.3	X6S	1608M/0603	0.55	+/-20%	General Purpose
GRM185C81A105KE36	1uF	10	X6S	1608M/0603	0.5	+/-10%	General Purpose
GRM185C81A475KE11	4.7uF	10	X6S	1608M/0603	0.55	+/-10%	General Purpose
GRM185C81A475ME11	4.7uF	10	X6S	1608M/0603	0.55	+/-20%	General Purpose
GRM185D70J475ME11	4.7uF	6.3	X7T	1608M/0603	0.55	+/-20%	General Purpose
GRM185D71A105KE36	1uF	10	X7T	1608M/0603	0.5	+/-10%	General Purpose
GRM185R60G106ME15	10uF	4	X5R	1608M/0603	0.5	+/-20%	General Purpose
GRM185R60J105KE26	1uF	6.3	X5R	1608M/0603	0.5	+/-10%	General Purpose
GRM185R60J106ME15	10uF	6.3	X5R	1608M/0603	0.5	+/-20%	General Purpose
GRM185R60J225KE26	2.2uF	6.3	X5R	1608M/0603	0.5	+/-10%	General Purpose
GRM185R61A475KE11	4.7uF	10	X5R	1608M/0603	0.55	+/-10%	General Purpose
GRM185R61A475ME11	4.7uF	10	X5R	1608M/0603	0.55	+/-20%	General Purpose
GRM185R61C105KE44	1uF	16	X5R	1608M/0603	0.5	+/-10%	General Purpose
GRM185R61C105ME44	1uF	16	X5R	1608M/0603	0.5	+/-20%	General Purpose
GRM185R61C475KE11	4.7uF	16	X5R	1608M/0603	0.55	+/-10%	General Purpose
GRM185R61C475ME11	4.7uF	16	X5R	1608M/0603	0.55	+/-20%	General Purpose
GRM185R61E105KA12	1uF	25	X5R	1608M/0603	0.5	+/-10%	General Purpose
GRM185R61E105MA12	1uF	25	X5R	1608M/0603	0.5	+/-20%	General Purpose
GRM186R60G226ME15	22uF	4	X5R	1608M/0603	0.6	+/-20%	General Purpose
GRM186R60J226ME15	22uF	6.3	X5R	1608M/0603	0.6	+/-20%	General Purpose
GRM187R60J226ME15	22uF	6.3	X5R	1608M/0603	0.8	+/-20%	General Purpose
GRM187R61A226ME15	22uF	10	X5R	1608M/0603	0.8	+/-20%	General Purpose
GRM188C60J226MEA0	22uF	6.3	X5S	1608M/0603	1.0	+/-20%	General Purpose
GRM188C70G225KE20	2.2uF	4	X7S	1608M/0603	0.9	+/-10%	General Purpose
GRM188C70G225ME20	2.2uF	4	X7S	1608M/0603	0.9	+/-20%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM188C70J225KE20	2.2uF	6.3	X7S	1608M/0603	0.9	+/-10%	General Purpose
GRM188C70J225ME20	2.2uF	6.3	X7S	1608M/0603	0.9	+/-20%	General Purpose
GRM188C71A475KE11	4.7uF	10	X7S	1608M/0603	0.95	+/-10%	General Purpose
GRM188C71A475ME11	4.7uF	10	X7S	1608M/0603	0.95	+/-20%	General Purpose
GRM188C71C225KE11	2.2uF	16	X7S	1608M/0603	1.0	+/-10%	General Purpose
GRM188C71C225ME11	2.2uF	16	X7S	1608M/0603	1.0	+/-20%	General Purpose
GRM188C71C475KE21	4.7uF	16	X7S	1608M/0603	1.0	+/-10%	General Purpose
GRM188C71C475ME21	4.7uF	16	X7S	1608M/0603	1.0	+/-20%	General Purpose
GRM188C71C684MA12	0.68uF	16	X7S	1608M/0603	0.9	+/-20%	General Purpose
GRM188C71E225KE11	2.2uF	25	X7S	1608M/0603	1.0	+/-10%	General Purpose
GRM188C71E225ME11	2.2uF	25	X7S	1608M/0603	1.0	+/-20%	General Purpose
GRM188C80E106ME47	10uF	2.5	X6S	1608M/0603	0.9	+/-20%	General Purpose
GRM188C80E476ME05	47uF	2.5	X6S	1608M/0603	1.0	+/-20%	General Purpose
GRM188C80G105MA01	1uF	4	X6S	1608M/0603	0.9	+/-20%	General Purpose
GRM188C80G106KE47	10uF	4	X6S	1608M/0603	0.9	+/-10%	General Purpose
GRM188C80G106ME47	10uF	4	X6S	1608M/0603	0.9	+/-20%	General Purpose
GRM188C80G226ME15	22uF	4	X6S	1608M/0603	1.0	+/-20%	General Purpose
GRM188C80G226MEA0	22uF	4	X6S	1608M/0603	1.0	+/-20%	General Purpose
GRM188C80G475KE19	4.7uF	4	X6S	1608M/0603	0.9	+/-10%	General Purpose
GRM188C80G475ME19	4.7uF	4	X6S	1608M/0603	0.9	+/-20%	General Purpose
GRM188C80J225KE19	2.2uF	6.3	X6S	1608M/0603	0.9	+/-10%	General Purpose
GRM188C80J225ME19	2.2uF	6.3	X6S	1608M/0603	0.9	+/-20%	General Purpose
GRM188C80J475KE15	4.7uF	6.3	X6S	1608M/0603	0.9	+/-10%	General Purpose
GRM188C80J475ME15	4.7uF	6.3	X6S	1608M/0603	0.9	+/-20%	General Purpose
GRM188C81A105KA12	1uF	10	X6S	1608M/0603	0.9	+/-10%	General Purpose
GRM188C81A106MA73	10uF	10	X6S	1608M/0603	1.0	+/-20%	General Purpose
GRM188C81A225KAAD	2.2uF	10	X6S	1608M/0603	0.9	+/-10%	General Purpose
GRM188C81A225KE34	2.2uF	10	X6S	1608M/0603	0.9	+/-10%	General Purpose
GRM188C81A225ME34	2.2uF	10	X6S	1608M/0603	0.9	+/-20%	General Purpose
GRM188C81C105KA12	1uF	16	X6S	1608M/0603	0.9	+/-10%	General Purpose
GRM188C81C105MA12	1uF	16	X6S	1608M/0603	0.9	+/-20%	General Purpose
GRM188C81C106MA73	10uF	16	X6S	1608M/0603	1.0	+/-20%	General Purpose
GRM188C81C225KA12	2.2uF	16	X6S	1608M/0603	0.9	+/-10%	General Purpose
GRM188C81C225MA12	2.2uF	16	X6S	1608M/0603	0.9	+/-20%	General Purpose
GRM188C81C475KE11	4.7uF	16	X6S	1608M/0603	0.95	+/-10%	General Purpose
GRM188C81C475ME11	4.7uF	16	X6S	1608M/0603	0.95	+/-20%	General Purpose
GRM188C81E105KA12	1uF	25	X6S	1608M/0603	0.9	+/-10%	General Purpose
GRM188C81E105KAAD	1uF	25	X6S	1608M/0603	0.9	+/-10%	General Purpose
GRM188C81E105MAAD	1uF	25	X6S	1608M/0603	0.9	+/-20%	General Purpose
GRM188C81E225KE11	2.2uF	25	X6S	1608M/0603	1.0	+/-10%	General Purpose
GRM188C81E225ME11	2.2uF	25	X6S	1608M/0603	1.0	+/-20%	General Purpose
GRM188C81E475KE11	4.7uF	25	X6S	1608M/0603	1.0	+/-10%	General Purpose
GRM188C81E475ME11	4.7uF	25	X6S	1608M/0603	1.0	+/-20%	General Purpose
GRM188C8YA105KAAL	1uF	35	X6S	1608M/0603	0.9	+/-10%	General Purpose
GRM188C8YA225KE11	2.2uF	35	X6S	1608M/0603	1.0	+/-10%	General Purpose
GRM188C8YA225ME11	2.2uF	35	X6S	1608M/0603	1.0	+/-20%	General Purpose
GRM188D70J106MA73	10uF	6.3	X7T	1608M/0603	1.0	+/-20%	General Purpose
GRM188D71A106MA73	10uF	10	X7T	1608M/0603	1.0	+/-20%	General Purpose
GRM188R60E476ME15	47uF	2.5	X5R	1608M/0603	1.0	+/-20%	General Purpose
GRM188R60G106ME47	10uF	4	X5R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R60G226MEA0	22uF	4	X5R	1608M/0603	1.0	+/-20%	General Purpose
GRM188R60G476ME15	47uF	4	X5R	1608M/0603	1.0	+/-20%	General Purpose
GRM188R60J105KA01	1uF	6.3	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R60J105MA01	1uF	6.3	X5R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R60J106ME47	10uF	6.3	X5R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R60J106ME84	10uF	6.3	X5R	1608M/0603	0.95	+/-20%	General Purpose
GRM188R60J225KE19	2.2uF	6.3	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R60J226MEA0	22uF	6.3	X5R	1608M/0603	1.0	+/-20%	General Purpose
GRM188R60J474KA01	0.47uF	6.3	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R60J475KE19	4.7uF	6.3	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R60J475ME19	4.7uF	6.3	X5R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R60J475ME84	4.7uF	6.3	X5R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R60J476ME15	47uF	6.3	X5R	1608M/0603	1.0	+/-20%	General Purpose
GRM188R61A105KA61	1uF	10	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61A105MA61	1uF	10	X5R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R61A106KAAL	10uF	10	X5R	1608M/0603	0.95	+/-10%	General Purpose
GRM188R61A106KE69	10uF	10	X5R	1608M/0603	0.95	+/-10%	General Purpose
GRM188R61A106MAAL	10uF	10	X5R	1608M/0603	0.95	+/-20%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM188R61A106ME69	10uF	10	X5R	1608M/0603	0.95	+/-20%	General Purpose
GRM188R61A224KA01	0.22uF	10	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61A225KE34	2.2uF	10	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61A225ME34	2.2uF	10	X5R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R61A226ME15	22uF	10	X5R	1608M/0603	1.0	+/-20%	General Purpose
GRM188R61A334KA61	0.33uF	10	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61A334MA61	0.33uF	10	X5R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R61A335KE15	3.3uF	10	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61A474KA61	0.47uF	10	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61A475KAAJ	4.7uF	10	X5R	1608M/0603	0.95	+/-10%	General Purpose
GRM188R61A475KE15	4.7uF	10	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61A475MAAJ	4.7uF	10	X5R	1608M/0603	0.95	+/-20%	General Purpose
GRM188R61A475ME15	4.7uF	10	X5R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R61A684KA61	0.68uF	10	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61A684MA61	0.68uF	10	X5R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R61C104KA01	0.1uF	16	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61C105KA12	1uF	16	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61C105KA93	1uF	16	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61C105MA12	1uF	16	X5R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R61C105MA93	1uF	16	X5R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R61C106KAAL	10uF	16	X5R	1608M/0603	0.95	+/-10%	General Purpose
GRM188R61C106MA73	10uF	16	X5R	1608M/0603	1.0	+/-20%	General Purpose
GRM188R61C106MAAL	10uF	16	X5R	1608M/0603	0.95	+/-20%	General Purpose
GRM188R61C224KA88	0.22uF	16	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61C225KAAD	2.2uF	16	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61C225KE15	2.2uF	16	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61C474KA12	0.47uF	16	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61C474KA93	0.47uF	16	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61C474MA12	0.47uF	16	X5R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R61C474MA93	0.47uF	16	X5R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R61C475KAAJ	4.7uF	16	X5R	1608M/0603	0.95	+/-10%	General Purpose
GRM188R61C475KE11	4.7uF	16	X5R	1608M/0603	0.95	+/-10%	General Purpose
GRM188R61C475MAAJ	4.7uF	16	X5R	1608M/0603	0.95	+/-20%	General Purpose
GRM188R61C475ME11	4.7uF	16	X5R	1608M/0603	0.95	+/-20%	General Purpose
GRM188R61C684KA75	0.68uF	16	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61C684MA75	0.68uF	16	X5R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R61E104KA01	0.1uF	25	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61E105KA12	1uF	25	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61E105KAAD	1uF	25	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61E105MA12	1uF	25	X5R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R61E106MA73	10uF	25	X5R	1608M/0603	1.0	+/-20%	General Purpose
GRM188R61E224KA88	0.22uF	25	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61E225KA12	2.2uF	25	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61E225MA12	2.2uF	25	X5R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R61E474KA12	0.47uF	25	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61E474MA12	0.47uF	25	X5R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R61E475KE11	4.7uF	25	X5R	1608M/0603	0.95	+/-10%	General Purpose
GRM188R61E475KE15	4.7uF	25	X5R	1608M/0603	1.0	+/-10%	General Purpose
GRM188R61E475ME11	4.7uF	25	X5R	1608M/0603	0.95	+/-20%	General Purpose
GRM188R61E475ME15	4.7uF	25	X5R	1608M/0603	1.0	+/-20%	General Purpose
GRM188R61E684KA75	0.68uF	25	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61E684MA75	0.68uF	25	X5R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R61H102KA01	1000pF	50	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61H103KA01	10000pF	50	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61H105KAAL	1uF	50	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61H105MAAL	1uF	50	X5R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R61H222KA01	2200pF	50	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61H223KA01	22000pF	50	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61H224KAC4	0.22uF	50	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61H225KE11	2.2uF	50	X5R	1608M/0603	1.0	+/-10%	General Purpose
GRM188R61H225ME11	2.2uF	50	X5R	1608M/0603	1.0	+/-20%	General Purpose
GRM188R61H472KA01	4700pF	50	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61H474KA12	0.47uF	50	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R61H474MA12	0.47uF	50	X5R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R61H684KA75	0.68uF	50	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R6YA105KA12	1uF	35	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R6YA105KAAL	1uF	35	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R6YA106MA73	10uF	35	X5R	1608M/0603	1.0	+/-20%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM188R6YA225KA12	2.2uF	35	X5R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R6YA475KE15	4.7uF	35	X5R	1608M/0603	1.0	+/-10%	General Purpose
GRM188R6YA475ME15	4.7uF	35	X5R	1608M/0603	1.0	+/-20%	General Purpose
GRM188R70J104KA01	0.1uF	6.3	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R70J105KA01	1uF	6.3	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R70J105MA01	1uF	6.3	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R70J224KA88	0.22uF	6.3	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R70J225KE15	2.2uF	6.3	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R70J474KA01	0.47uF	6.3	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71A105KA61	1uF	10	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71A154KA01	0.15uF	10	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71A224JA01	0.22uF	10	X7R	1608M/0603	0.9	+/-5%	General Purpose
GRM188R71A224KA01	0.22uF	10	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71A225KE15	2.2uF	10	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71A225ME15	2.2uF	10	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71A334KA61	0.33uF	10	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71A334MA61	0.33uF	10	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71A474KA61	0.47uF	10	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71A474MA61	0.47uF	10	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71A684KA61	0.68uF	10	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71A684MA61	0.68uF	10	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71C104KA01	0.1uF	16	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71C104MA01	0.1uF	16	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71C105KA12	1uF	16	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71C105KE15	1uF	16	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71C105MA12	1uF	16	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71C105ME15	1uF	16	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71C154KA01	0.15uF	16	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71C224KA01	0.22uF	16	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71C224MA01	0.22uF	16	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71C334KA01	0.33uF	16	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71C473JA01	47000pF	16	X7R	1608M/0603	0.9	+/-5%	General Purpose
GRM188R71C474KA88	0.47uF	16	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71C474MA88	0.47uF	16	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71E102KA01	1000pF	25	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71E103KA01	10000pF	25	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71E103MA01	10000pF	25	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71E104KA01	0.1uF	25	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71E104MA01	0.1uF	25	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71E105KA12	1uF	25	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71E105MA12	1uF	25	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71E152KA01	1500pF	25	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71E153KA01	15000pF	25	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71E154KA01	0.15uF	25	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71E222KA01	2200pF	25	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71E222MA01	2200pF	25	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71E223KA01	22000pF	25	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71E223MA01	22000pF	25	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71E224KA88	0.22uF	25	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71E224MA88	0.22uF	25	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71E272KA01	2700pF	25	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71E332KA01	3300pF	25	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71E333KA01	33000pF	25	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71E472KA01	4700pF	25	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71E472MA01	4700pF	25	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71E473KA01	47000pF	25	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71E473MA01	47000pF	25	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71E474KA12	0.47uF	25	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71E474MA12	0.47uF	25	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71E682KA01	6800pF	25	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71E683KA01	68000pF	25	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71E823KA01	82000pF	25	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H102KA01	1000pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H102MA01	1000pF	50	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71H103JA01	10000pF	50	X7R	1608M/0603	0.9	+/-5%	General Purpose
GRM188R71H103KA01	10000pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H103MA01	10000pF	50	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71H104KA93	0.1uF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM188R71H104MA93	0.1uF	50	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71H123JA01	12000pF	50	X7R	1608M/0603	0.9	+/-5%	General Purpose
GRM188R71H123KA01	12000pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H152KA01	1500pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H153JA01	15000pF	50	X7R	1608M/0603	0.9	+/-5%	General Purpose
GRM188R71H153KA01	15000pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H154KAC4	0.15uF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H154MAC4	0.15uF	50	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71H182KA01	1800pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H183KA01	18000pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H221KA01	220pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H221MA01	220pF	50	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71H222JA01	2200pF	50	X7R	1608M/0603	0.9	+/-5%	General Purpose
GRM188R71H222KA01	2200pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H222MA01	2200pF	50	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71H223KA01	22000pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H223MA01	22000pF	50	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71H224KAC4	0.22uF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H224MAC4	0.22uF	50	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71H273KA61	27000pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H331KA01	330pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H332KA01	3300pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H333KA61	33000pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H392KA01	3900pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H393KA61	39000pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H471JA01	470pF	50	X7R	1608M/0603	0.9	+/-5%	General Purpose
GRM188R71H471KA01	470pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H471MA01	470pF	50	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71H472JA01	4700pF	50	X7R	1608M/0603	0.9	+/-5%	General Purpose
GRM188R71H472KA01	4700pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H472MA01	4700pF	50	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71H473KA61	47000pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H473MA61	47000pF	50	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R71H562KA01	5600pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H681KA01	680pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H682KA01	6800pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H683KA93	68000pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R71H822KA01	8200pF	50	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R72A102KA01	1000pF	100	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R72A102MA01	1000pF	100	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R72A104KA35	0.1uF	100	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R72A104MA35	0.1uF	100	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R72A152KA01	1500pF	100	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R72A153KAC4	15000pF	100	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R72A153MAC4	15000pF	100	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R72A221KA01	220pF	100	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R72A221MA01	220pF	100	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R72A222KA01	2200pF	100	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R72A222MA01	2200pF	100	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R72A223KAC4	22000pF	100	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R72A223MAC4	22000pF	100	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R72A331KA01	330pF	100	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R72A332KA01	3300pF	100	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R72A471KA01	470pF	100	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R72A471MA01	470pF	100	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R72A681KA01	680pF	100	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R7YA105KA12	1uF	35	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R7YA105MA12	1uF	35	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188R7YA474KE05	0.47uF	35	X7R	1608M/0603	0.9	+/-10%	General Purpose
GRM188R7YA474ME05	0.47uF	35	X7R	1608M/0603	0.9	+/-20%	General Purpose
GRM188Z71A106KA73	10uF	10	X7R(Murata)	1608M/0603	1.0	+/-10%	General Purpose
GRM188Z71C475KE21	4.7uF	16	X7R(Murata)	1608M/0603	1.0	+/-10%	General Purpose
GRM188Z71C475ME21	4.7uF	16	X7R(Murata)	1608M/0603	1.0	+/-20%	General Purpose
GRM216C81C105KA12	1uF	16	X6S	2012M/0805	0.7	+/-10%	General Purpose
GRM216D71C105KA12	1uF	16	X7T	2012M/0805	0.7	+/-10%	General Purpose
GRM216D71C105MA12	1uF	16	X7T	2012M/0805	0.7	+/-20%	General Purpose
GRM216R61C105KA88	1uF	16	X5R	2012M/0805	0.7	+/-10%	General Purpose
GRM216R61E105KA12	1uF	25	X5R	2012M/0805	0.7	+/-10%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM216R71H103KA01	10000pF	50	X7R	2012M/0805	0.7	+/-10%	General Purpose
GRM216R71H123KA01	12000pF	50	X7R	2012M/0805	0.7	+/-10%	General Purpose
GRM216R71H223KA01	22000pF	50	X7R	2012M/0805	0.7	+/-10%	General Purpose
GRM216R71H223MA01	22000pF	50	X7R	2012M/0805	0.7	+/-20%	General Purpose
GRM216R71H472KA01	4700pF	50	X7R	2012M/0805	0.7	+/-10%	General Purpose
GRM216R71H682KA01	6800pF	50	X7R	2012M/0805	0.7	+/-10%	General Purpose
GRM219C71C475KE21	4.7uF	16	X7S	2012M/0805	1.0	+/-10%	General Purpose
GRM219C71C475ME21	4.7uF	16	X7S	2012M/0805	1.0	+/-20%	General Purpose
GRM219C71E475KE21	4.7uF	25	X7S	2012M/0805	1.0	+/-10%	General Purpose
GRM219C71E475ME21	4.7uF	25	X7S	2012M/0805	1.0	+/-20%	General Purpose
GRM219C80G106KE19	10uF	4	X6S	2012M/0805	0.95	+/-10%	General Purpose
GRM219C80G106ME19	10uF	4	X6S	2012M/0805	0.95	+/-20%	General Purpose
GRM219C80J106KE39	10uF	6.3	X6S	2012M/0805	0.95	+/-10%	General Purpose
GRM219C80J106ME39	10uF	6.3	X6S	2012M/0805	0.95	+/-20%	General Purpose
GRM219C80J475KE19	4.7uF	6.3	X6S	2012M/0805	0.95	+/-10%	General Purpose
GRM219C81A475KE34	4.7uF	10	X6S	2012M/0805	0.95	+/-10%	General Purpose
GRM219C81A475ME34	4.7uF	10	X6S	2012M/0805	0.95	+/-20%	General Purpose
GRM219C81C225KA12	2.2uF	16	X6S	2012M/0805	0.95	+/-10%	General Purpose
GRM219C81C475KA73	4.7uF	16	X6S	2012M/0805	0.95	+/-10%	General Purpose
GRM219C81C475MA73	4.7uF	16	X6S	2012M/0805	0.95	+/-20%	General Purpose
GRM219C81E225KE15	2.2uF	25	X6S	2012M/0805	0.95	+/-10%	General Purpose
GRM219C81E225ME15	2.2uF	25	X6S	2012M/0805	0.95	+/-20%	General Purpose
GRM219C81E475KE21	4.7uF	25	X6S	2012M/0805	1.0	+/-10%	General Purpose
GRM219C81E475ME21	4.7uF	25	X6S	2012M/0805	1.0	+/-20%	General Purpose
GRM219C8YA225KE15	2.2uF	35	X6S	2012M/0805	0.95	+/-10%	General Purpose
GRM219C8YA225ME15	2.2uF	35	X6S	2012M/0805	0.95	+/-20%	General Purpose
GRM219C8YA475KE21	4.7uF	35	X6S	2012M/0805	1.0	+/-10%	General Purpose
GRM219C8YA475ME21	4.7uF	35	X6S	2012M/0805	1.0	+/-20%	General Purpose
GRM219D71A475KE15	4.7uF	10	X7T	2012M/0805	0.95	+/-10%	General Purpose
GRM219D71A475ME15	4.7uF	10	X7T	2012M/0805	0.95	+/-20%	General Purpose
GRM219D71C225KA12	2.2uF	16	X7T	2012M/0805	0.95	+/-10%	General Purpose
GRM219D71C225MA12	2.2uF	16	X7T	2012M/0805	0.95	+/-20%	General Purpose
GRM219D80E476ME44	47uF	2.5	X6T	2012M/0805	0.95	+/-20%	General Purpose
GRM219R60G226ME66	22uF	4	X5R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R60G476ME44	47uF	4	X5R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R60J106KE19	10uF	6.3	X5R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R60J106ME19	10uF	6.3	X5R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R60J226ME47	22uF	6.3	X5R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R60J226MEA0	22uF	6.3	X5R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R60J475KE19	4.7uF	6.3	X5R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R60J476ME44	47uF	6.3	X5R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R61A105KA01	1uF	10	X5R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R61A106KE44	10uF	10	X5R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R61A106ME44	10uF	10	X5R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R61A106ME47	10uF	10	X5R	2012M/0805	1.0	+/-20%	General Purpose
GRM219R61A225KA01	2.2uF	10	X5R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R61A226MEA0	22uF	10	X5R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R61A335KE19	3.3uF	10	X5R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R61A475KE34	4.7uF	10	X5R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R61A475ME34	4.7uF	10	X5R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R61C106KA73	10uF	16	X5R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R61C106MA73	10uF	16	X5R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R61C225KA88	2.2uF	16	X5R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R61C226ME15	22uF	16	X5R	2012M/0805	1.0	+/-20%	General Purpose
GRM219R61C475KE15	4.7uF	16	X5R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R61E106KA12	10uF	25	X5R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R61E106MA12	10uF	25	X5R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R61E225KA12	2.2uF	25	X5R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R61E225MA12	2.2uF	25	X5R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R61E475KA73	4.7uF	25	X5R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R61E475MA73	4.7uF	25	X5R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R61H105KA73	1uF	50	X5R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R61H105MA73	1uF	50	X5R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R61H225KE15	2.2uF	50	X5R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R61H225ME15	2.2uF	50	X5R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R6YA475KA73	4.7uF	35	X5R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R6YA475MA73	4.7uF	35	X5R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R71A225KE15	2.2uF	10	X7R	2012M/0805	0.95	+/-10%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM219R71A225ME15	2.2uF	10	X7R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R71C225KE15	2.2uF	16	X7R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R71C225ME15	2.2uF	16	X7R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R71C334KA88	0.33uF	16	X7R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R71C474KA01	0.47uF	16	X7R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R71C684KA01	0.68uF	16	X7R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R71E104KA01	0.1uF	25	X7R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R71E104MA01	0.1uF	25	X7R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R71E105KA88	1uF	25	X7R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R71E224MA01	0.22uF	25	X7R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R71E474KA88	0.47uF	25	X7R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R71E474MA88	0.47uF	25	X7R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R71E683KA01	6800pF	25	X7R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R71E684KA88	0.68uF	25	X7R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R71H103KA01	10000pF	50	X7R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R71H103MA01	10000pF	50	X7R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R71H153KA01	15000pF	50	X7R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R71H153MA01	15000pF	50	X7R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R71H223KA17	22000pF	50	X7R	2012M/0805	1.0	+/-10%	General Purpose
GRM219R71H223MA17	22000pF	50	X7R	2012M/0805	1.0	+/-20%	General Purpose
GRM219R71H333KA01	33000pF	50	X7R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R71H334KA88	0.33uF	50	X7R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R72A103KA01	10000pF	100	X7R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R72A103MA01	10000pF	100	X7R	2012M/0805	0.95	+/-20%	General Purpose
GRM219R72A682KA01	6800pF	100	X7R	2012M/0805	0.95	+/-10%	General Purpose
GRM219R7YA105KA12	1uF	35	X7R	2012M/0805	0.95	+/-10%	General Purpose
GRM21AR72A224KAC5	0.22uF	100	X7R	2012M/0805	1.0	+/-10%	General Purpose
GRM21AR72A224MAC5	0.22uF	100	X7R	2012M/0805	1.0	+/-20%	General Purpose
GRM21AR72A334KAC5	0.33uF	100	X7R	2012M/0805	1.0	+/-10%	General Purpose
GRM21BC70G106KE45	10uF	4	X7S	2012M/0805	1.4	+/-10%	General Purpose
GRM21BC71C106KE11	10uF	16	X7S	2012M/0805	1.45	+/-10%	General Purpose
GRM21BC71C106ME11	10uF	16	X7S	2012M/0805	1.45	+/-20%	General Purpose
GRM21BC71E106KE11	10uF	25	X7S	2012M/0805	1.45	+/-10%	General Purpose
GRM21BC71E106ME11	10uF	25	X7S	2012M/0805	1.45	+/-20%	General Purpose
GRM21BC71E475KE11	4.7uF	25	X7S	2012M/0805	1.45	+/-10%	General Purpose
GRM21BC71E475ME11	4.7uF	25	X7S	2012M/0805	1.45	+/-20%	General Purpose
GRM21BC71H475KE11	4.7uF	50	X7S	2012M/0805	1.45	+/-10%	General Purpose
GRM21BC71H475ME11	4.7uF	50	X7S	2012M/0805	1.45	+/-20%	General Purpose
GRM21BC72A105KE01	1uF	100	X7S	2012M/0805	1.45	+/-10%	General Purpose
GRM21BC7YA475KE11	4.7uF	35	X7S	2012M/0805	1.45	+/-10%	General Purpose
GRM21BC7YA475ME11	4.7uF	35	X7S	2012M/0805	1.45	+/-20%	General Purpose
GRM21BC80E107ME15	100uF	2.5	X6S	2012M/0805	1.45	+/-20%	General Purpose
GRM21BC80G106KE01	10uF	4	X6S	2012M/0805	1.35	+/-10%	General Purpose
GRM21BC80G106ME19	10uF	4	X6S	2012M/0805	1.35	+/-20%	General Purpose
GRM21BC80G107ME15	100uF	4	X6S	2012M/0805	1.45	+/-20%	General Purpose
GRM21BC80G226ME39	22uF	4	X6S	2012M/0805	1.4	+/-20%	General Purpose
GRM21BC80G476ME15	47uF	4	X6S	2012M/0805	1.45	+/-20%	General Purpose
GRM21BC80J106KE19	10uF	6.3	X6S	2012M/0805	1.35	+/-10%	General Purpose
GRM21BC80J106ME19	10uF	6.3	X6S	2012M/0805	1.35	+/-20%	General Purpose
GRM21BC80J226ME51	22uF	6.3	X6S	2012M/0805	1.4	+/-20%	General Purpose
GRM21BC81A106KE18	10uF	10	X6S	2012M/0805	1.35	+/-10%	General Purpose
GRM21BC81A106ME18	10uF	10	X6S	2012M/0805	1.35	+/-20%	General Purpose
GRM21BC81A226ME44	22uF	10	X6S	2012M/0805	1.45	+/-20%	General Purpose
GRM21BC81C106KA73	10uF	16	X6S	2012M/0805	1.4	+/-10%	General Purpose
GRM21BC81C106KE15	10uF	16	X6S	2012M/0805	1.35	+/-10%	General Purpose
GRM21BC81C106MA73	10uF	16	X6S	2012M/0805	1.4	+/-20%	General Purpose
GRM21BC81C106ME15	10uF	16	X6S	2012M/0805	1.35	+/-20%	General Purpose
GRM21BC81C226ME44	22uF	16	X6S	2012M/0805	1.45	+/-20%	General Purpose
GRM21BC81C475KA88	4.7uF	16	X6S	2012M/0805	1.35	+/-10%	General Purpose
GRM21BC81E106KE11	10uF	25	X6S	2012M/0805	1.45	+/-10%	General Purpose
GRM21BC81E106ME11	10uF	25	X6S	2012M/0805	1.45	+/-20%	General Purpose
GRM21BC81E225KA12	2.2uF	25	X6S	2012M/0805	1.35	+/-10%	General Purpose
GRM21BC81E475KA12	4.7uF	25	X6S	2012M/0805	1.35	+/-10%	General Purpose
GRM21BC81E475MA12	4.7uF	25	X6S	2012M/0805	1.35	+/-20%	General Purpose
GRM21BC81H475KE11	4.7uF	50	X6S	2012M/0805	1.45	+/-10%	General Purpose
GRM21BC81H475ME11	4.7uF	50	X6S	2012M/0805	1.45	+/-20%	General Purpose
GRM21BC8YA106KE11	10uF	35	X6S	2012M/0805	1.45	+/-10%	General Purpose
GRM21BC8YA106ME11	10uF	35	X6S	2012M/0805	1.45	+/-20%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM21BC8YA225KA73	2.2uF	35	X6S	2012M/0805	1.4	+/-10%	General Purpose
GRM21BC8YA225MA73	2.2uF	35	X6S	2012M/0805	1.4	+/-20%	General Purpose
GRM21BC8YA475KE51	4.7uF	35	X6S	2012M/0805	1.4	+/-10%	General Purpose
GRM21BD70J226ME44	22uF	6.3	X7T	2012M/0805	1.45	+/-20%	General Purpose
GRM21BD71A226ME44	22uF	10	X7T	2012M/0805	1.45	+/-20%	General Purpose
GRM21BD71C475KA12	4.7uF	16	X7T	2012M/0805	1.35	+/-10%	General Purpose
GRM21BD71C475MA12	4.7uF	16	X7T	2012M/0805	1.35	+/-20%	General Purpose
GRM21BE70G226ME51	22uF	4	X7U	2012M/0805	1.4	+/-20%	General Purpose
GRM21BE71C475KA12	4.7uF	16	X7U	2012M/0805	1.35	+/-10%	General Purpose
GRM21BE71C475MA12	4.7uF	16	X7U	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR60G107ME11	100uF	4	X5R	2012M/0805	1.45	+/-20%	General Purpose
GRM21BR60J106KE19	10uF	6.3	X5R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR60J106ME19	10uF	6.3	X5R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR60J107ME15	100uF	6.3	X5R	2012M/0805	1.45	+/-20%	General Purpose
GRM21BR60J225KA01	2.2uF	6.3	X5R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR60J226ME39	22uF	6.3	X5R	2012M/0805	1.4	+/-20%	General Purpose
GRM21BR60J475KA11	4.7uF	6.3	X5R	2012M/0805	1.4	+/-10%	General Purpose
GRM21BR60J475MA11	4.7uF	6.3	X5R	2012M/0805	1.4	+/-20%	General Purpose
GRM21BR61A105KA01	1uF	10	X5R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR61A106KE19	10uF	10	X5R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR61A106ME19	10uF	10	X5R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR61A225KA01	2.2uF	10	X5R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR61A225MA01	2.2uF	10	X5R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR61A226ME44	22uF	10	X5R	2012M/0805	1.45	+/-20%	General Purpose
GRM21BR61A226ME51	22uF	10	X5R	2012M/0805	1.4	+/-20%	General Purpose
GRM21BR61A475KA73	4.7uF	10	X5R	2012M/0805	1.4	+/-10%	General Purpose
GRM21BR61A475MA73	4.7uF	10	X5R	2012M/0805	1.4	+/-20%	General Purpose
GRM21BR61A476ME15	47uF	10	X5R	2012M/0805	1.45	+/-20%	General Purpose
GRM21BR61C105KA01	1uF	16	X5R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR61C106KE15	10uF	16	X5R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR61C106ME15	10uF	16	X5R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR61C225KA88	2.2uF	16	X5R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR61C226ME44	22uF	16	X5R	2012M/0805	1.45	+/-20%	General Purpose
GRM21BR61C475KA88	4.7uF	16	X5R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR61D106KE15	10uF	20	X5R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR61D106ME15	10uF	20	X5R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR61E106KA73	10uF	25	X5R	2012M/0805	1.4	+/-10%	General Purpose
GRM21BR61E106MA73	10uF	25	X5R	2012M/0805	1.4	+/-20%	General Purpose
GRM21BR61E225KA12	2.2uF	25	X5R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR61E226ME44	22uF	25	X5R	2012M/0805	1.45	+/-20%	General Purpose
GRM21BR61E475KA12	4.7uF	25	X5R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR61E475MA12	4.7uF	25	X5R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR61H105KA12	1uF	50	X5R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR61H225KA73	2.2uF	50	X5R	2012M/0805	1.4	+/-10%	General Purpose
GRM21BR61H225MA73	2.2uF	50	X5R	2012M/0805	1.4	+/-20%	General Purpose
GRM21BR61H475KE51	4.7uF	50	X5R	2012M/0805	1.4	+/-10%	General Purpose
GRM21BR61H475ME51	4.7uF	50	X5R	2012M/0805	1.4	+/-20%	General Purpose
GRM21BR6YA106KE43	10uF	35	X5R	2012M/0805	1.45	+/-10%	General Purpose
GRM21BR6YA106ME43	10uF	35	X5R	2012M/0805	1.45	+/-20%	General Purpose
GRM21BR70J106KA73	10uF	6.3	X7R	2012M/0805	1.4	+/-10%	General Purpose
GRM21BR70J106KE76	10uF	6.3	X7R	2012M/0805	1.4	+/-10%	General Purpose
GRM21BR70J106ME76	10uF	6.3	X7R	2012M/0805	1.4	+/-20%	General Purpose
GRM21BR70J225KA01	2.2uF	6.3	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR71A105KA01	1uF	10	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR71A106KA73	10uF	10	X7R	2012M/0805	1.4	+/-10%	General Purpose
GRM21BR71A106KE51	10uF	10	X7R	2012M/0805	1.4	+/-10%	General Purpose
GRM21BR71A106MA73	10uF	10	X7R	2012M/0805	1.4	+/-20%	General Purpose
GRM21BR71A106ME51	10uF	10	X7R	2012M/0805	1.4	+/-20%	General Purpose
GRM21BR71A225KA01	2.2uF	10	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR71A225MA01	2.2uF	10	X7R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR71A475KA73	4.7uF	10	X7R	2012M/0805	1.4	+/-10%	General Purpose
GRM21BR71A475MA73	4.7uF	10	X7R	2012M/0805	1.4	+/-20%	General Purpose
GRM21BR71C105KA01	1uF	16	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR71C224KA01	0.22uF	16	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR71C224MA01	0.22uF	16	X7R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR71C225KA12	2.2uF	16	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR71C225MA12	2.2uF	16	X7R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR71C474MA01	0.47uF	16	X7R	2012M/0805	1.35	+/-20%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM21BR71C475KA73	4.7uF	16	X7R	2012M/0805	1.4	+/-10%	General Purpose
GRM21BR71C475KE51	4.7uF	16	X7R	2012M/0805	1.4	+/-10%	General Purpose
GRM21BR71C475MA73	4.7uF	16	X7R	2012M/0805	1.4	+/-20%	General Purpose
GRM21BR71E104JA01	0.1uF	25	X7R	2012M/0805	1.35	+/-5%	General Purpose
GRM21BR71E104KA01	0.1uF	25	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR71E104MA01	0.1uF	25	X7R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR71E105KA99	1uF	25	X7R	2012M/0805	1.4	+/-10%	General Purpose
GRM21BR71E154KA01	0.15uF	25	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR71E224KA01	0.22uF	25	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR71E224MA01	0.22uF	25	X7R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR71E225KA73	2.2uF	25	X7R	2012M/0805	1.4	+/-10%	General Purpose
GRM21BR71E225KE11	2.2uF	25	X7R	2012M/0805	1.4	+/-10%	General Purpose
GRM21BR71E225ME11	2.2uF	25	X7R	2012M/0805	1.4	+/-20%	General Purpose
GRM21BR71E334KA01	0.33uF	25	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR71E475KA73	4.7uF	25	X7R	2012M/0805	1.4	+/-10%	General Purpose
GRM21BR71E475MA73	4.7uF	25	X7R	2012M/0805	1.4	+/-20%	General Purpose
GRM21BR71H104KA01	0.1uF	50	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR71H104MA01	0.1uF	50	X7R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR71H105KA12	1uF	50	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR71H154KA01	0.15uF	50	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR71H224KA01	0.22uF	50	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR71H224MA01	0.22uF	50	X7R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR71H473KA01	47000pF	50	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR71H473MA01	47000pF	50	X7R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR71H474KA88	0.47uF	50	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR71H474MA88	0.47uF	50	X7R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR71H683KA01	68000pF	50	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR72A103KA01	10000pF	100	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR72A103MA01	10000pF	100	X7R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR72A104KAC4	0.1uF	100	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR72A104MAC4	0.1uF	100	X7R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR72A153KA01	15000pF	100	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR72A223KA01	22000pF	100	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR72A223MA01	22000pF	100	X7R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR72A333KA01	33000pF	100	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR72A473KA01	47000pF	100	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR72A473MA01	47000pF	100	X7R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BR72A474KA73	0.47uF	100	X7R	2012M/0805	1.4	+/-10%	General Purpose
GRM21BR72A474MA73	0.47uF	100	X7R	2012M/0805	1.4	+/-20%	General Purpose
GRM21BR72A683KAC4	68000pF	100	X7R	2012M/0805	1.35	+/-10%	General Purpose
GRM21BR72A683MAC4	68000pF	100	X7R	2012M/0805	1.35	+/-20%	General Purpose
GRM21BZ71E106KE15	10uF	25	X7R(Murata)	2012M/0805	1.45	+/-10%	General Purpose
GRM316C81C225KA12	2.2uF	16	X6S	3216M/1206	0.7	+/-10%	General Purpose
GRM316D71C225KA12	2.2uF	16	X7T	3216M/1206	0.7	+/-10%	General Purpose
GRM316D71C225MA12	2.2uF	16	X7T	3216M/1206	0.7	+/-20%	General Purpose
GRM316R61A475KE19	4.7uF	10	X5R	3216M/1206	0.7	+/-10%	General Purpose
GRM316R61C225KA88	2.2uF	16	X5R	3216M/1206	0.7	+/-10%	General Purpose
GRM316R61E225KA12	2.2uF	25	X5R	3216M/1206	0.7	+/-10%	General Purpose
GRM319C80J106KE19	10uF	6.3	X6S	3216M/1206	0.95	+/-10%	General Purpose
GRM319C80J106ME19	10uF	6.3	X6S	3216M/1206	0.95	+/-20%	General Purpose
GRM319C80J226ME15	22uF	6.3	X6S	3216M/1206	0.95	+/-20%	General Purpose
GRM319C81A106KA12	10uF	10	X6S	3216M/1206	0.95	+/-10%	General Purpose
GRM319C81A106MA12	10uF	10	X6S	3216M/1206	0.95	+/-20%	General Purpose
GRM319C81C106KA12	10uF	16	X6S	3216M/1206	0.95	+/-10%	General Purpose
GRM319C81C106MA12	10uF	16	X6S	3216M/1206	0.95	+/-20%	General Purpose
GRM319C81C475KA12	4.7uF	16	X6S	3216M/1206	0.95	+/-10%	General Purpose
GRM319C8YA225KA12	2.2uF	35	X6S	3216M/1206	0.95	+/-10%	General Purpose
GRM319C8YA225MA12	2.2uF	35	X6S	3216M/1206	0.95	+/-20%	General Purpose
GRM319D71C475KA12	4.7uF	16	X7T	3216M/1206	0.95	+/-10%	General Purpose
GRM319D71C475MA12	4.7uF	16	X7T	3216M/1206	0.95	+/-20%	General Purpose
GRM319R60J106KE19	10uF	6.3	X5R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R60J226ME15	22uF	6.3	X5R	3216M/1206	0.95	+/-20%	General Purpose
GRM319R61A105KA01	1uF	10	X5R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R61A106KE19	10uF	10	X5R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R61A106ME19	10uF	10	X5R	3216M/1206	0.95	+/-20%	General Purpose
GRM319R61A225KA01	2.2uF	10	X5R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R61A226ME15	22uF	10	X5R	3216M/1206	0.95	+/-20%	General Purpose
GRM319R61A475KA01	4.7uF	10	X5R	3216M/1206	0.95	+/-10%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM319R61C105KAA3	1uF	16	X5R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R61C106KE15	10uF	16	X5R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R61C106ME15	10uF	16	X5R	3216M/1206	0.95	+/-20%	General Purpose
GRM319R61C226ME15	22uF	16	X5R	3216M/1206	0.95	+/-20%	General Purpose
GRM319R61C335KA12	3.3uF	16	X5R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R61C475KA88	4.7uF	16	X5R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R61E105KC36	1uF	25	X5R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R61E106KA12	10uF	25	X5R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R61E106MA12	10uF	25	X5R	3216M/1206	0.95	+/-20%	General Purpose
GRM319R61E475KA12	4.7uF	25	X5R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R61H225KA12	2.2uF	50	X5R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R61H225MA12	2.2uF	50	X5R	3216M/1206	0.95	+/-20%	General Purpose
GRM319R61H475KA12	4.7uF	50	X5R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R61H475MA12	4.7uF	50	X5R	3216M/1206	0.95	+/-20%	General Purpose
GRM319R6YA106KA12	10uF	35	X5R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R6YA106MA12	10uF	35	X5R	3216M/1206	0.95	+/-20%	General Purpose
GRM319R71A105KA01	1uF	10	X7R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R71C105KAA3	1uF	16	X7R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R71E334KA01	0.33uF	25	X7R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R71E474KA01	0.47uF	25	X7R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R71H104JA01	0.1uF	50	X7R	3216M/1206	0.95	+/-5%	General Purpose
GRM319R71H153KA01	15000pF	50	X7R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R71H223KA01	22000pF	50	X7R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R71H334KA01	0.33uF	50	X7R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R71H683KA01	68000pF	50	X7R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R72A104KA01	0.1uF	100	X7R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R72A153KA01	15000pF	100	X7R	3216M/1206	0.95	+/-10%	General Purpose
GRM319R72A222KA01	2200pF	100	X7R	3216M/1206	0.95	+/-10%	General Purpose
GRM31CC70G226ME01	22uF	4	X7S	3216M/1206	1.8	+/-20%	General Purpose
GRM31CC70J226KE15	22uF	6.3	X7S	3216M/1206	1.8	+/-10%	General Purpose
GRM31CC71C226ME11	22uF	16	X7S	3216M/1206	1.9	+/-20%	General Purpose
GRM31CC72A475KE11	4.7uF	100	X7S	3216M/1206	1.9	+/-10%	General Purpose
GRM31CC72A475ME11	4.7uF	100	X7S	3216M/1206	1.9	+/-20%	General Purpose
GRM31CC80E157ME11	150uF	2.5	X6S	3216M/1206	1.9	+/-20%	General Purpose
GRM31CC80E227ME11	220uF	2.5	X6S	3216M/1206	1.9	+/-20%	General Purpose
GRM31CC80G157ME11	150uF	4	X6S	3216M/1206	1.9	+/-20%	General Purpose
GRM31CC80G226KE19	22uF	4	X6S	3216M/1206	1.8	+/-10%	General Purpose
GRM31CC80G226ME19	22uF	4	X6S	3216M/1206	1.8	+/-20%	General Purpose
GRM31CC80G227ME11	220uF	4	X6S	3216M/1206	1.9	+/-20%	General Purpose
GRM31CC80G476ME19	47uF	4	X6S	3216M/1206	1.8	+/-20%	General Purpose
GRM31CC80J226KE19	22uF	6.3	X6S	3216M/1206	1.8	+/-10%	General Purpose
GRM31CC80J226ME19	22uF	6.3	X6S	3216M/1206	1.8	+/-20%	General Purpose
GRM31CC80J476KE18	47uF	6.3	X6S	3216M/1206	1.8	+/-10%	General Purpose
GRM31CC80J476ME18	47uF	6.3	X6S	3216M/1206	1.8	+/-20%	General Purpose
GRM31CC81A226KE19	22uF	10	X6S	3216M/1206	1.8	+/-10%	General Purpose
GRM31CC81A226ME19	22uF	10	X6S	3216M/1206	1.8	+/-20%	General Purpose
GRM31CC81A476ME44	47uF	10	X6S	3216M/1206	1.9	+/-20%	General Purpose
GRM31CC81C106KA12	10uF	16	X6S	3216M/1206	1.8	+/-10%	General Purpose
GRM31CC81C106KE19	10uF	16	X6S	3216M/1206	1.8	+/-10%	General Purpose
GRM31CC81C106MA12	10uF	16	X6S	3216M/1206	1.8	+/-20%	General Purpose
GRM31CC81C226KE15	22uF	16	X6S	3216M/1206	1.8	+/-10%	General Purpose
GRM31CC81C226ME15	22uF	16	X6S	3216M/1206	1.8	+/-20%	General Purpose
GRM31CC81E106KE15	10uF	25	X6S	3216M/1206	1.8	+/-10%	General Purpose
GRM31CC81E106MA12	10uF	25	X6S	3216M/1206	1.8	+/-20%	General Purpose
GRM31CC81E226ME11	22uF	25	X6S	3216M/1206	1.9	+/-20%	General Purpose
GRM31CC8YA106KA12	10uF	35	X6S	3216M/1206	1.8	+/-10%	General Purpose
GRM31CC8YA106MA12	10uF	35	X6S	3216M/1206	1.8	+/-20%	General Purpose
GRM31CD70J226KE19	22uF	6.3	X7T	3216M/1206	1.8	+/-10%	General Purpose
GRM31CD70J226ME19	22uF	6.3	X7T	3216M/1206	1.8	+/-20%	General Purpose
GRM31CD71A226KE15	22uF	10	X7T	3216M/1206	1.8	+/-10%	General Purpose
GRM31CD71A226ME15	22uF	10	X7T	3216M/1206	1.8	+/-20%	General Purpose
GRM31CD80G107ME39	100uF	4	X6T	3216M/1206	1.9	+/-20%	General Purpose
GRM31CD80G476ME19	47uF	4	X6T	3216M/1206	1.8	+/-20%	General Purpose
GRM31CD80J107ME39	100uF	6.3	X6T	3216M/1206	1.9	+/-20%	General Purpose
GRM31CE70G107ME39	100uF	4	X7U	3216M/1206	1.9	+/-20%	General Purpose
GRM31CE70G476ME15	47uF	4	X7U	3216M/1206	1.8	+/-20%	General Purpose
GRM31CE70J476ME15	47uF	6.3	X7U	3216M/1206	1.8	+/-20%	General Purpose
GRM31CR60E227ME11	220uF	2.5	X5R	3216M/1206	1.9	+/-20%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM31CR60G107ME39	100uF	4	X5R	3216M/1206	1.9	+/-20%	General Purpose
GRM31CR60G157ME11	150uF	4	X5R	3216M/1206	1.9	+/-20%	General Purpose
GRM31CR60G227ME11	220uF	4	X5R	3216M/1206	1.9	+/-20%	General Purpose
GRM31CR60J106KA01	10uF	6.3	X5R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR60J106MC01	10uF	6.3	X5R	3216M/1206	1.8	+/-20%	General Purpose
GRM31CR60J107ME39	100uF	6.3	X5R	3216M/1206	1.9	+/-20%	General Purpose
GRM31CR60J157ME11	150uF	6.3	X5R	3216M/1206	1.9	+/-20%	General Purpose
GRM31CR60J226KE19	22uF	6.3	X5R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR60J226ME19	22uF	6.3	X5R	3216M/1206	1.8	+/-20%	General Purpose
GRM31CR60J227ME11	220uF	6.3	X5R	3216M/1206	1.9	+/-20%	General Purpose
GRM31CR60J475KA01	4.7uF	6.3	X5R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR60J476KE19	47uF	6.3	X5R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR60J476ME19	47uF	6.3	X5R	3216M/1206	1.8	+/-20%	General Purpose
GRM31CR61A106KA01	10uF	10	X5R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR61A107ME05	100uF	10	X5R	3216M/1206	1.9	+/-20%	General Purpose
GRM31CR61A226KE19	22uF	10	X5R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR61A226ME19	22uF	10	X5R	3216M/1206	1.8	+/-20%	General Purpose
GRM31CR61A475KA01	4.7uF	10	X5R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR61A476KE15	47uF	10	X5R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR61A476ME15	47uF	10	X5R	3216M/1206	1.8	+/-20%	General Purpose
GRM31CR61C106KA88	10uF	16	X5R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR61C106KC31	10uF	16	X5R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR61C226KE15	22uF	16	X5R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR61C226ME15	22uF	16	X5R	3216M/1206	1.8	+/-20%	General Purpose
GRM31CR61C475KA01	4.7uF	16	X5R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR61C475MA01	4.7uF	16	X5R	3216M/1206	1.8	+/-20%	General Purpose
GRM31CR61C476ME44	47uF	16	X5R	3216M/1206	1.9	+/-20%	General Purpose
GRM31CR61E106KA12	10uF	25	X5R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR61E106MA12	10uF	25	X5R	3216M/1206	1.8	+/-20%	General Purpose
GRM31CR61E226KE15	22uF	25	X5R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR61E226ME15	22uF	25	X5R	3216M/1206	1.8	+/-20%	General Purpose
GRM31CR61E335KA88	3.3uF	25	X5R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR61E475KA88	4.7uF	25	X5R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR61H106KA12	10uF	50	X5R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR61H106MA12	10uF	50	X5R	3216M/1206	1.8	+/-20%	General Purpose
GRM31CR61H225KA88	2.2uF	50	X5R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR6YA106KA12	10uF	35	X5R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR6YA106MA12	10uF	35	X5R	3216M/1206	1.8	+/-20%	General Purpose
GRM31CR70J106KA01	10uF	6.3	X7R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR70J226KE19	22uF	6.3	X7R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR70J226ME19	22uF	6.3	X7R	3216M/1206	1.8	+/-20%	General Purpose
GRM31CR71A106KA01	10uF	10	X7R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR71A106MA01	10uF	10	X7R	3216M/1206	1.8	+/-20%	General Purpose
GRM31CR71A226KE15	22uF	10	X7R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR71A226ME15	22uF	10	X7R	3216M/1206	1.8	+/-20%	General Purpose
GRM31CR71A475KA01	4.7uF	10	X7R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR71C106KA12	10uF	16	X7R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR71C106KAC7	10uF	16	X7R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR71C106MA12	10uF	16	X7R	3216M/1206	1.8	+/-20%	General Purpose
GRM31CR71C106MAC7	10uF	16	X7R	3216M/1206	1.8	+/-20%	General Purpose
GRM31CR71C475KA01	4.7uF	16	X7R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR71C475MA01	4.7uF	16	X7R	3216M/1206	1.8	+/-20%	General Purpose
GRM31CR71E106KA12	10uF	25	X7R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR71E106MA12	10uF	25	X7R	3216M/1206	1.8	+/-20%	General Purpose
GRM31CR71E475KA88	4.7uF	25	X7R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR71H225KA88	2.2uF	50	X7R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR71H475KA12	4.7uF	50	X7R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR71H475MA12	4.7uF	50	X7R	3216M/1206	1.8	+/-20%	General Purpose
GRM31CR72A105KA01	1uF	100	X7R	3216M/1206	1.8	+/-10%	General Purpose
GRM31CR72A225KA73	2.2uF	100	X7R	3216M/1206	1.9	+/-10%	General Purpose
GRM31CR72A225MA73	2.2uF	100	X7R	3216M/1206	1.9	+/-20%	General Purpose
GRM31CZ72A475KE11	4.7uF	100	X7R(Murata)	3216M/1206	1.9	+/-10%	General Purpose
GRM31CZ72A475ME11	4.7uF	100	X7R(Murata)	3216M/1206	1.9	+/-20%	General Purpose
GRM31MC81A106KE19	10uF	10	X6S	3216M/1206	1.25	+/-10%	General Purpose
GRM31MC81A106ME19	10uF	10	X6S	3216M/1206	1.25	+/-20%	General Purpose
GRM31MC81C106KA12	10uF	16	X6S	3216M/1206	1.25	+/-10%	General Purpose
GRM31MC81C685KA12	6.8uF	16	X6S	3216M/1206	1.25	+/-10%	General Purpose
GRM31MC81C685MA12	6.8uF	16	X6S	3216M/1206	1.25	+/-20%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM31MC81E106KA12	10uF	25	X6S	3216M/1206	1.25	+/-10%	General Purpose
GRM31MC81E106MA12	10uF	25	X6S	3216M/1206	1.25	+/-20%	General Purpose
GRM31MR61A106KE19	10uF	10	X5R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR61A225KA01	2.2uF	10	X5R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR61C105KA01	1uF	16	X5R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR61C106KA12	10uF	16	X5R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR61C225KA35	2.2uF	16	X5R	3216M/1206	1.3	+/-10%	General Purpose
GRM31MR61E106KA12	10uF	25	X5R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR61E106MA12	10uF	25	X5R	3216M/1206	1.25	+/-20%	General Purpose
GRM31MR71A225KA01	2.2uF	10	X7R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR71C105KA01	1uF	16	X7R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR71C105MA01	1uF	16	X7R	3216M/1206	1.25	+/-20%	General Purpose
GRM31MR71C225KA35	2.2uF	16	X7R	3216M/1206	1.3	+/-10%	General Purpose
GRM31MR71C225MA35	2.2uF	16	X7R	3216M/1206	1.3	+/-20%	General Purpose
GRM31MR71E105KA01	1uF	25	X7R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR71E105MC01	1uF	25	X7R	3216M/1206	1.25	+/-20%	General Purpose
GRM31MR71E225KA93	2.2uF	25	X7R	3216M/1206	1.3	+/-10%	General Purpose
GRM31MR71E474KA01	0.47uF	25	X7R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR71H105KA88	1uF	50	X7R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR71H154KA01	0.15uF	50	X7R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR71H224KA01	0.22uF	50	X7R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR71H224MA01	0.22uF	50	X7R	3216M/1206	1.25	+/-20%	General Purpose
GRM31MR71H474JA01	0.47uF	50	X7R	3216M/1206	1.25	+/-5%	General Purpose
GRM31MR71H474KA01	0.47uF	50	X7R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR71H474MA01	0.47uF	50	X7R	3216M/1206	1.25	+/-20%	General Purpose
GRM31MR71H684KA88	0.68uF	50	X7R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR72A154KA01	0.15uF	100	X7R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR72A223KA01	22000pF	100	X7R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR72A223MA01	22000pF	100	X7R	3216M/1206	1.25	+/-20%	General Purpose
GRM31MR72A224KA01	0.22uF	100	X7R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR72A333KA01	33000pF	100	X7R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR72A473KA01	47000pF	100	X7R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR72A473MA01	47000pF	100	X7R	3216M/1206	1.25	+/-20%	General Purpose
GRM31MR72A474KA35	0.47uF	100	X7R	3216M/1206	1.3	+/-10%	General Purpose
GRM31MR72A474MA35	0.47uF	100	X7R	3216M/1206	1.3	+/-20%	General Purpose
GRM31MR72A683KA01	68000pF	100	X7R	3216M/1206	1.25	+/-10%	General Purpose
GRM31MR72A684KA35	0.68uF	100	X7R	3216M/1206	1.3	+/-10%	General Purpose
GRM32AR61C106KAB7	10uF	16	X5R	3225M/1210	1.0	+/-10%	General Purpose
GRM32CR72A105KA35	1uF	100	X7R	3225M/1210	1.8	+/-10%	General Purpose
GRM32CR72A105MA35	1uF	100	X7R	3225M/1210	1.8	+/-20%	General Purpose
GRM32CR72A684KA01	0.68uF	100	X7R	3225M/1210	1.8	+/-10%	General Purpose
GRM32DC72A475KE01	4.7uF	100	X7S	3225M/1210	2.2	+/-10%	General Purpose
GRM32DC72A475ME01	4.7uF	100	X7S	3225M/1210	2.2	+/-20%	General Purpose
GRM32DC81E106KA12	10uF	25	X6S	3225M/1210	2.2	+/-10%	General Purpose
GRM32DR60J226MA01	22uF	6.3	X5R	3225M/1210	2.2	+/-20%	General Purpose
GRM32DR60J336ME19	33uF	6.3	X5R	3225M/1210	2.2	+/-20%	General Purpose
GRM32DR61C106KA01	10uF	16	X5R	3225M/1210	2.2	+/-10%	General Purpose
GRM32DR61E106KA12	10uF	25	X5R	3225M/1210	2.2	+/-10%	General Purpose
GRM32DR61E106MA12	10uF	25	X5R	3225M/1210	2.2	+/-20%	General Purpose
GRM32DR71A106KA01	10uF	10	X7R	3225M/1210	2.2	+/-10%	General Purpose
GRM32DR71C106KA01	10uF	16	X7R	3225M/1210	2.2	+/-10%	General Purpose
GRM32DR71E106KA12	10uF	25	X7R	3225M/1210	2.2	+/-10%	General Purpose
GRM32DR71E475KA61	4.7uF	25	X7R	3225M/1210	2.2	+/-10%	General Purpose
GRM32EC70G107ME15	100uF	4	X7S	3225M/1210	2.7	+/-20%	General Purpose
GRM32EC70J107ME15	100uF	6.3	X7S	3225M/1210	2.7	+/-20%	General Purpose
GRM32EC72A106KE05	10uF	100	X7S	3225M/1210	2.7	+/-10%	General Purpose
GRM32EC72A106ME05	10uF	100	X7S	3225M/1210	2.7	+/-20%	General Purpose
GRM32EC80E227ME05	220uF	2.5	X6S	3225M/1210	2.8	+/-20%	General Purpose
GRM32EC80E337ME05	330uF	2.5	X6S	3225M/1210	2.8	+/-20%	General Purpose
GRM32EC80G107KE20	100uF	4	X6S	3225M/1210	2.7	+/-10%	General Purpose
GRM32EC80G107ME20	100uF	4	X6S	3225M/1210	2.7	+/-20%	General Purpose
GRM32EC80G227ME05	220uF	4	X6S	3225M/1210	2.8	+/-20%	General Purpose
GRM32EC80J107ME20	100uF	6.3	X6S	3225M/1210	2.7	+/-20%	General Purpose
GRM32EC80J476KE64	47uF	6.3	X6S	3225M/1210	2.7	+/-10%	General Purpose
GRM32EC80J476ME64	47uF	6.3	X6S	3225M/1210	2.7	+/-20%	General Purpose
GRM32EC81A476KE19	47uF	10	X6S	3225M/1210	2.7	+/-10%	General Purpose
GRM32EC81A476ME19	47uF	10	X6S	3225M/1210	2.7	+/-20%	General Purpose
GRM32EC81C476KE15	47uF	16	X6S	3225M/1210	2.7	+/-10%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM32EC81C476ME15	47uF	16	X6S	3225M/1210	2.7	+/-20%	General Purpose
GRM32EC81E226KE15	22uF	25	X6S	3225M/1210	2.7	+/-10%	General Purpose
GRM32EC81E226ME15	22uF	25	X6S	3225M/1210	2.7	+/-20%	General Purpose
GRM32ED70J476KE20	47uF	6.3	X7T	3225M/1210	2.7	+/-10%	General Purpose
GRM32ED70J476ME20	47uF	6.3	X7T	3225M/1210	2.7	+/-20%	General Purpose
GRM32ED71A476KE15	47uF	10	X7T	3225M/1210	2.7	+/-10%	General Purpose
GRM32ED71A476ME15	47uF	10	X7T	3225M/1210	2.7	+/-20%	General Purpose
GRM32EE70G107ME19	100uF	4	X7U	3225M/1210	2.7	+/-20%	General Purpose
GRM32EE70J107ME15	100uF	6.3	X7U	3225M/1210	2.7	+/-20%	General Purpose
GRM32EE70J476KE20	47uF	6.3	X7U	3225M/1210	2.7	+/-10%	General Purpose
GRM32EE70J476ME20	47uF	6.3	X7U	3225M/1210	2.7	+/-20%	General Purpose
GRM32ER60E337ME05	330uF	2.5	X5R	3225M/1210	2.8	+/-20%	General Purpose
GRM32ER60G227ME05	220uF	4	X5R	3225M/1210	2.8	+/-20%	General Purpose
GRM32ER60G337ME05	330uF	4	X5R	3225M/1210	2.8	+/-20%	General Purpose
GRM32ER60J107ME20	100uF	6.3	X5R	3225M/1210	2.7	+/-20%	General Purpose
GRM32ER60J227ME05	220uF	6.3	X5R	3225M/1210	2.8	+/-20%	General Purpose
GRM32ER60J476KE64	47uF	6.3	X5R	3225M/1210	2.7	+/-10%	General Purpose
GRM32ER60J476ME20	47uF	6.3	X5R	3225M/1210	2.7	+/-20%	General Purpose
GRM32ER60J476ME64	47uF	6.3	X5R	3225M/1210	2.7	+/-20%	General Purpose
GRM32ER61A106KA01	10uF	10	X5R	3225M/1210	2.7	+/-10%	General Purpose
GRM32ER61A107ME20	100uF	10	X5R	3225M/1210	2.7	+/-20%	General Purpose
GRM32ER61A476KE20	47uF	10	X5R	3225M/1210	2.7	+/-10%	General Purpose
GRM32ER61A476ME20	47uF	10	X5R	3225M/1210	2.7	+/-20%	General Purpose
GRM32ER61C226ME20	22uF	16	X5R	3225M/1210	2.7	+/-20%	General Purpose
GRM32ER61C476KE15	47uF	16	X5R	3225M/1210	2.7	+/-10%	General Purpose
GRM32ER61C476ME15	47uF	16	X5R	3225M/1210	2.7	+/-20%	General Purpose
GRM32ER61E226KE15	22uF	25	X5R	3225M/1210	2.7	+/-10%	General Purpose
GRM32ER61E226ME15	22uF	25	X5R	3225M/1210	2.7	+/-20%	General Purpose
GRM32ER61H106KA12	10uF	50	X5R	3225M/1210	2.7	+/-10%	General Purpose
GRM32ER61H106MA12	10uF	50	X5R	3225M/1210	2.7	+/-20%	General Purpose
GRM32ER6YA106KA12	10uF	35	X5R	3225M/1210	2.7	+/-10%	General Purpose
GRM32ER6YA106MA12	10uF	35	X5R	3225M/1210	2.7	+/-20%	General Purpose
GRM32ER70J476KE20	47uF	6.3	X7R	3225M/1210	2.7	+/-10%	General Purpose
GRM32ER70J476ME20	47uF	6.3	X7R	3225M/1210	2.7	+/-20%	General Purpose
GRM32ER71A226ME20	22uF	10	X7R	3225M/1210	2.7	+/-20%	General Purpose
GRM32ER71A476KE15	47uF	10	X7R	3225M/1210	2.7	+/-10%	General Purpose
GRM32ER71A476ME15	47uF	10	X7R	3225M/1210	2.7	+/-20%	General Purpose
GRM32ER71C226KEA8	22uF	16	X7R	3225M/1210	2.7	+/-10%	General Purpose
GRM32ER71C226MEA8	22uF	16	X7R	3225M/1210	2.7	+/-20%	General Purpose
GRM32ER71E226ME15	22uF	25	X7R	3225M/1210	2.7	+/-20%	General Purpose
GRM32ER71H106KA12	10uF	50	X7R	3225M/1210	2.7	+/-10%	General Purpose
GRM32ER71H106MA12	10uF	50	X7R	3225M/1210	2.7	+/-20%	General Purpose
GRM32ER71H475KA88	4.7uF	50	X7R	3225M/1210	2.7	+/-10%	General Purpose
GRM32ER71J106KA12	10uF	63	X7R	3225M/1210	2.7	+/-10%	General Purpose
GRM32ER71J106MA12	10uF	63	X7R	3225M/1210	2.7	+/-20%	General Purpose
GRM32ER71K475KE14	4.7uF	80	X7R	3225M/1210	2.7	+/-10%	General Purpose
GRM32ER71K475ME14	4.7uF	80	X7R	3225M/1210	2.7	+/-20%	General Purpose
GRM32ER72A225KA35	2.2uF	100	X7R	3225M/1210	2.7	+/-10%	General Purpose
GRM32ER72A225MA35	2.2uF	100	X7R	3225M/1210	2.7	+/-20%	General Purpose
GRM32ER7YA106KA12	10uF	35	X7R	3225M/1210	2.7	+/-10%	General Purpose
GRM32ER7YA106MA12	10uF	35	X7R	3225M/1210	2.7	+/-20%	General Purpose
GRM32MR71C225KA01	2.2uF	16	X7R	3225M/1210	1.25	+/-10%	General Purpose
GRM32MR71H104KA01	0.1uF	50	X7R	3225M/1210	1.25	+/-10%	General Purpose
GRM32NC81A226ME19	22uF	10	X6S	3225M/1210	1.5	+/-20%	General Purpose
GRM32NC81C226KE15	22uF	16	X6S	3225M/1210	1.5	+/-10%	General Purpose
GRM32NC81C226ME15	22uF	16	X6S	3225M/1210	1.5	+/-20%	General Purpose
GRM32ND70J226ME19	22uF	6.3	X7T	3225M/1210	1.5	+/-20%	General Purpose
GRM32ND71A226KE15	22uF	10	X7T	3225M/1210	1.5	+/-10%	General Purpose
GRM32ND71A226ME15	22uF	10	X7T	3225M/1210	1.5	+/-20%	General Purpose
GRM32NR61A226KE19	22uF	10	X5R	3225M/1210	1.5	+/-10%	General Purpose
GRM32NR61A226ME19	22uF	10	X5R	3225M/1210	1.5	+/-20%	General Purpose
GRM32NR71H154KA01	0.15uF	50	X7R	3225M/1210	1.5	+/-10%	General Purpose
GRM32NR71H684KA01	0.68uF	50	X7R	3225M/1210	1.5	+/-10%	General Purpose
GRM32NR72A104KA01	0.1uF	100	X7R	3225M/1210	1.5	+/-10%	General Purpose
GRM32RR61C475KA01	4.7uF	16	X5R	3225M/1210	2.0	+/-10%	General Purpose
GRM32RR61E475KA12	4.7uF	25	X5R	3225M/1210	2.0	+/-10%	General Purpose
GRM32RR71C475KA01	4.7uF	16	X7R	3225M/1210	2.0	+/-10%	General Purpose
GRM32RR71E225KA01	2.2uF	25	X7R	3225M/1210	2.0	+/-10%	General Purpose

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRM32RR71H105KA01	1uF	50	X7R	3225M/1210	2.0	+/-10%	General Purpose
GRM43DR61E106KA12	10uF	25	X5R	4532M/1812	2.2	+/-10%	General Purpose
GRM43ER61C226ME01	22uF	16	X5R	4532M/1812	2.7	+/-20%	General Purpose
GRM43ER61H475KA88	4.7uF	50	X5R	4532M/1812	2.7	+/-10%	General Purpose
GRM43ER71E475KA01	4.7uF	25	X7R	4532M/1812	2.7	+/-10%	General Purpose
GRM43ER71H225KA01	2.2uF	50	X7R	4532M/1812	2.7	+/-10%	General Purpose
GRM43ER72A225KA01	2.2uF	100	X7R	4532M/1812	2.7	+/-10%	General Purpose
GRM55DR61H106KA88	10uF	50	X5R	5750M/2220	2.2	+/-10%	General Purpose
GRM55DR71E106KA01	10uF	25	X7R	5750M/2220	2.1	+/-10%	General Purpose
GRM55DR72A105KA01	1uF	100	X7R	5750M/2220	2.2	+/-10%	General Purpose
GRM55ER61H475KA01	4.7uF	50	X5R	5750M/2220	2.7	+/-10%	General Purpose
GRM55ER71H475KA01	4.7uF	50	X7R	5750M/2220	2.7	+/-10%	General Purpose
GRM55ER72A475KA01	4.7uF	100	X7R	5750M/2220	2.7	+/-10%	General Purpose
GRM55RR71H105KA01	1uF	50	X7R	5750M/2220	2.0	+/-10%	General Purpose
GRMMDXR60J105ME05	1uF	6.3	X5R	05025M/015008	0.28	+/-20%	Ultra-small
GXM155C80J225KE95	2.2uF	6.3	X6S	1005M/0402	0.55	+/-10%	Water repellent/ General Purpose
GXM155C80J475MEAA	4.7uF	6.3	X6S	1005M/0402	0.65	+/-20%	Water repellent/ General Purpose
GXM155D80E475ME47	4.7uF	2.5	X6T	1005M/0402	0.6	+/-20%	Water repellent/ General Purpose
GXM155R60E106ME16	10uF	2.5	X5R	1005M/0402	0.7	+/-20%	Water repellent/ General Purpose
GXM155R60G106ME44	10uF	4	X5R	1005M/0402	0.7	+/-20%	Water repellent/ General Purpose
GXM155R60G475ME47	4.7uF	4	X5R	1005M/0402	0.6	+/-20%	Water repellent/ General Purpose
GXM155R60J475ME47	4.7uF	6.3	X5R	1005M/0402	0.6	+/-20%	Water repellent/ General Purpose
GXM155R61A475MEAA	4.7uF	10	X5R	1005M/0402	0.65	+/-20%	Water repellent/ General Purpose
GXM188R60G226MEA0	22uF	4	X5R	1608M/0603	1.0	+/-20%	Water repellent/ General Purpose
GXM188R60J226MEA0	22uF	6.3	X5R	1608M/0603	1.0	+/-20%	Water repellent/ General Purpose
GXM219C80J106KE39	10uF	6.3	X6S	2012M/0805	0.95	+/-10%	Water repellent/ General Purpose
GXM219D80E476ME44	47uF	2.5	X6T	2012M/0805	0.95	+/-20%	Water repellent/ General Purpose
GXM219R60G476ME44	47uF	4	X5R	2012M/0805	0.95	+/-20%	Water repellent/ General Purpose
GXM219R60J226MEA0	22uF	6.3	X5R	2012M/0805	0.95	+/-20%	Water repellent/ General Purpose
GXM219R61A226MEA0	22uF	10	X5R	2012M/0805	0.95	+/-20%	Water repellent/ General Purpose
GXM21BC80E107ME10	100uF	2.5	X6S	2012M/0805	1.45	+/-20%	Water repellent/ General Purpose
GXM21BC80G107ME10	100uF	4	X6S	2012M/0805	1.45	+/-20%	Water repellent/ General Purpose
GXM21BC80G226ME39	22uF	4	X6S	2012M/0805	1.4	+/-20%	Water repellent/ General Purpose
GXM21BC80J226ME50	22uF	6.3	X6S	2012M/0805	1.4	+/-20%	Water repellent/ General Purpose
GXM21BE70G226ME50	22uF	4	X7U	2012M/0805	1.4	+/-20%	Water repellent/ General Purpose
GXM21BR60J107ME10	100uF	6.3	X5R	2012M/0805	1.45	+/-20%	Water repellent/ General Purpose
GXM21BR61A476ME10	47uF	10	X5R	2012M/0805	1.45	+/-20%	Water repellent/ General Purpose
GXM31CC80E157ME11	150uF	2.5	X6S	3216M/1206	1.9	+/-20%	Water repellent/ General Purpose
GXM31CC80G157ME11	150uF	4	X6S	3216M/1206	1.9	+/-20%	Water repellent/ General Purpose
GXM31CD80G107ME39	100uF	4	X6T	3216M/1206	1.9	+/-20%	Water repellent/ General Purpose
GXM31CD80J107ME39	100uF	6.3	X6T	3216M/1206	1.9	+/-20%	Water repellent/ General Purpose
GXM31CE70G107ME39	100uF	4	X7U	3216M/1206	1.9	+/-20%	Water repellent/ General Purpose
GXM31CR60E227ME11	220uF	2.5	X5R	3216M/1206	1.9	+/-20%	Water repellent/ General Purpose
GXM31CR60G107ME39	100uF	4	X5R	3216M/1206	1.9	+/-20%	Water repellent/ General Purpose
GXM31CR60G157ME11	150uF	4	X5R	3216M/1206	1.9	+/-20%	Water repellent/ General Purpose
GXM31CR60G227ME11	220uF	4	X5R	3216M/1206	1.9	+/-20%	Water repellent/ General Purpose
GXM31CR60J157ME11	150uF	6.3	X5R	3216M/1206	1.9	+/-20%	Water repellent/ General Purpose
LLL153C70E105ME21	1uF	2.5	X7S	0510M/0204	0.35	+/-20%	Low ESL
LLL153C70G474ME17	0.47uF	4	X7S	0510M/0204	0.35	+/-20%	Low ESL
LLL153C80G105ME21	1uF	4	X6S	0510M/0204	0.35	+/-20%	Low ESL
LLL153C80J104ME01	0.1uF	6.3	X6S	0510M/0204	0.35	+/-20%	Low ESL
LLL153C80J224ME14	0.22uF	6.3	X6S	0510M/0204	0.35	+/-20%	Low ESL
LLL153R61A104ME01	0.1uF	10	X5R	0510M/0204	0.35	+/-20%	Low ESL
LLL185C70G105ME01	1uF	4	X7S	0816M/0306	0.55	+/-20%	Low ESL
LLL185C70G224MA11	0.22uF	4	X7S	0816M/0306	0.5	+/-20%	Low ESL
LLL185C70G225ME01	2.2uF	4	X7S	0816M/0306	0.55	+/-20%	Low ESL
LLL185C70G474MA01	0.47uF	4	X7S	0816M/0306	0.6	+/-20%	Low ESL
LLL185C70J105ME14	1uF	6.3	X7S	0816M/0306	0.55	+/-20%	Low ESL
LLL185R71A104MA01	0.1uF	10	X7R	0816M/0306	0.6	+/-20%	Low ESL
LLL185R71A104MA11	0.1uF	10	X7R	0816M/0306	0.5	+/-20%	Low ESL
LLL185R71A224MA01	0.22uF	10	X7R	0816M/0306	0.6	+/-20%	Low ESL
LLL185R71C103MA01	10000pF	16	X7R	0816M/0306	0.6	+/-20%	Low ESL
LLL185R71C223MA01	22000pF	16	X7R	0816M/0306	0.6	+/-20%	Low ESL
LLL185R71C223MA11	22000pF	16	X7R	0816M/0306	0.5	+/-20%	Low ESL
LLL185R71C473MA01	47000pF	16	X7R	0816M/0306	0.6	+/-20%	Low ESL
LLL185R71C473MA11	47000pF	16	X7R	0816M/0306	0.5	+/-20%	Low ESL
LLL185R71E103MA01	10000pF	25	X7R	0816M/0306	0.6	+/-20%	Low ESL
LLL185R71E103MA11	10000pF	25	X7R	0816M/0306	0.5	+/-20%	Low ESL

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
LLL185R71E223MA01	22000pF	25	X7R	0816M/0306	0.6	+/-20%	Low ESL
LLL185R71H222MA01	2200pF	50	X7R	0816M/0306	0.6	+/-20%	Low ESL
LLL185R71H472MA01	4700pF	50	X7R	0816M/0306	0.6	+/-20%	Low ESL
LLL1U4R60G435ME22	4.3uF	4	X5R	0610M/02404	0.45	+/-20%	Low ESL
LLL215C70G105MA11	1uF	4	X7S	1220M/0508	0.5	+/-20%	Low ESL
LLL215R70J474MA11	0.47uF	6.3	X7R	1220M/0508	0.5	+/-20%	Low ESL
LLL215R71A224MA11	0.22uF	10	X7R	1220M/0508	0.5	+/-20%	Low ESL
LLL215R71C104MA11	0.1uF	16	X7R	1220M/0508	0.5	+/-20%	Low ESL
LLL215R71C223MA11	22000pF	16	X7R	1220M/0508	0.5	+/-20%	Low ESL
LLL215R71C473MA11	47000pF	16	X7R	1220M/0508	0.5	+/-20%	Low ESL
LLL215R71E103MA11	10000pF	25	X7R	1220M/0508	0.5	+/-20%	Low ESL
LLL215R71E223MA11	22000pF	25	X7R	1220M/0508	0.5	+/-20%	Low ESL
LLL215R71H103MA11	10000pF	50	X7R	1220M/0508	0.5	+/-20%	Low ESL
LLL216R71A224MA01	0.22uF	10	X7R	1220M/0508	0.7	+/-20%	Low ESL
LLL216R71C104MA01	0.1uF	16	X7R	1220M/0508	0.7	+/-20%	Low ESL
LLL216R71C473MA01	47000pF	16	X7R	1220M/0508	0.7	+/-20%	Low ESL
LLL216R71E104MA01	0.1uF	25	X7R	1220M/0508	0.7	+/-20%	Low ESL
LLL216R71E223MA01	22000pF	25	X7R	1220M/0508	0.7	+/-20%	Low ESL
LLL216R71E473MA01	47000pF	25	X7R	1220M/0508	0.7	+/-20%	Low ESL
LLL216R71H103MA01	10000pF	50	X7R	1220M/0508	0.7	+/-20%	Low ESL
LLL216R71H223MA01	22000pF	50	X7R	1220M/0508	0.7	+/-20%	Low ESL
LLL219C70G225MA01	2.2uF	4	X7S	1220M/0508	0.95	+/-20%	Low ESL
LLL219R70J105MA01	1uF	6.3	X7R	1220M/0508	0.95	+/-20%	Low ESL
LLL219R71A105MA01	1uF	10	X7R	1220M/0508	0.95	+/-20%	Low ESL
LLL219R71A474MA01	0.47uF	10	X7R	1220M/0508	0.95	+/-20%	Low ESL
LLL219R71C224MA01	0.22uF	16	X7R	1220M/0508	0.95	+/-20%	Low ESL
LLL315R71A474MA11	0.47uF	10	X7R	1632M/0612	0.5	+/-20%	Low ESL
LLL315R71C104MA11	0.1uF	16	X7R	1632M/0612	0.5	+/-20%	Low ESL
LLL315R71C223MA11	22000pF	16	X7R	1632M/0612	0.5	+/-20%	Low ESL
LLL315R71C224MA11	0.22uF	16	X7R	1632M/0612	0.5	+/-20%	Low ESL
LLL315R71C473MA11	47000pF	16	X7R	1632M/0612	0.5	+/-20%	Low ESL
LLL315R71E104MA11	0.1uF	25	X7R	1632M/0612	0.5	+/-20%	Low ESL
LLL315R71E223MA11	22000pF	25	X7R	1632M/0612	0.5	+/-20%	Low ESL
LLL315R71E473MA11	47000pF	25	X7R	1632M/0612	0.5	+/-20%	Low ESL
LLL315R71H103MA11	10000pF	50	X7R	1632M/0612	0.5	+/-20%	Low ESL
LLL315R71H223MA11	22000pF	50	X7R	1632M/0612	0.5	+/-20%	Low ESL
LLL317R70J225MA01	2.2uF	6.3	X7R	1632M/0612	0.8	+/-20%	Low ESL
LLL317R71A105MA01	1uF	10	X7R	1632M/0612	0.8	+/-20%	Low ESL
LLL317R71A474MA01	0.47uF	10	X7R	1632M/0612	0.8	+/-20%	Low ESL
LLL317R71C104MA01	0.1uF	16	X7R	1632M/0612	0.8	+/-20%	Low ESL
LLL317R71C224MA01	0.22uF	16	X7R	1632M/0612	0.8	+/-20%	Low ESL
LLL317R71C474MA01	0.47uF	16	X7R	1632M/0612	0.8	+/-20%	Low ESL
LLL317R71E104MA01	0.1uF	25	X7R	1632M/0612	0.8	+/-20%	Low ESL
LLL317R71E223MA01	22000pF	25	X7R	1632M/0612	0.8	+/-20%	Low ESL
LLL317R71E473MA01	47000pF	25	X7R	1632M/0612	0.8	+/-20%	Low ESL
LLL317R71H103MA01	10000pF	50	X7R	1632M/0612	0.8	+/-20%	Low ESL
LLL317R71H223MA01	22000pF	50	X7R	1632M/0612	0.8	+/-20%	Low ESL
LLL317R71H473MA01	47000pF	50	X7R	1632M/0612	0.8	+/-20%	Low ESL
LLL31MR60J106ME01	10uF	6.3	X5R	1632M/0612	1.25	+/-20%	Low ESL
LLL31MR70J475MA01	4.7uF	6.3	X7R	1632M/0612	1.25	+/-20%	Low ESL
LLL31MR71A225MA01	2.2uF	10	X7R	1632M/0612	1.25	+/-20%	Low ESL
LLL31MR71C105MA01	1uF	16	X7R	1632M/0612	1.25	+/-20%	Low ESL
LLL31MR71E224MA01	0.22uF	25	X7R	1632M/0612	1.25	+/-20%	Low ESL
LLL31MR71E474MA01	0.47uF	25	X7R	1632M/0612	1.25	+/-20%	Low ESL
LLL31MR71H104MA01	0.1uF	50	X7R	1632M/0612	1.25	+/-20%	Low ESL
LLR185C70G105ME01	1uF	4	X7S	0816M/0306	0.55	+/-20%	Low ESL
LLR185C70G105ME03	1uF	4	X7S	0816M/0306	0.55	+/-20%	Low ESL
LLR185C70G105ME05	1uF	4	X7S	0816M/0306	0.55	+/-20%	Low ESL
LLR185C70G105ME07	1uF	4	X7S	0816M/0306	0.55	+/-20%	Low ESL
ZRB15XC80J106ME05	10uF	6.3	X6S	1005M/0402	0.85	+/-20%	Acoustic noise reduction (interposer)
ZRB15XR60J106ME12	10uF	6.3	X5R	1005M/0402	0.8	+/-20%	Acoustic noise reduction (interposer)
ZRB186R60G226ME11	22uF	4	X5R	1608M/0603	0.8	+/-20%	Acoustic noise reduction (interposer)
ZRB186R60J226ME11	22uF	6.3	X5R	1608M/0603	0.8	+/-20%	Acoustic noise reduction (interposer)
ZRB188R61A226ME05	22uF	10	X5R	1608M/0603	0.95	+/-20%	Acoustic noise reduction (interposer)
ZRB18AR60J476ME01	47uF	6.3	X5R	1608M/0603	1.2	+/-20%	Acoustic noise reduction (interposer)
ZRB18AR61E106ME01	10uF	25	X5R	1608M/0603	1.2	+/-20%	Acoustic noise reduction (interposer)
ZRB18AR6YA475KE05	4.7uF	35	X5R	1608M/0603	1.2	+/-10%	Acoustic noise reduction (interposer)
ZRB18AR6YA475ME05	4.7uF	35	X5R	1608M/0603	1.2	+/-20%	Acoustic noise reduction (interposer)

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GCE219R72A821MA01	820pF	100	X7R	2012M/0805	0.95	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR71H104KA01	0.1uF	50	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR71H104MA01	0.1uF	50	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR71H153KA01	15000pF	50	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR71H153MA01	15000pF	50	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR71H183KA01	18000pF	50	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR71H183MA01	18000pF	50	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR71H223KA01	22000pF	50	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR71H223MA01	22000pF	50	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR71H273KA01	27000pF	50	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR71H273MA01	27000pF	50	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR71H333KA01	33000pF	50	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR71H333MA01	33000pF	50	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR71H393KA01	39000pF	50	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR71H393MA01	39000pF	50	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR71H473KA01	47000pF	50	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR71H473MA01	47000pF	50	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR71H563KA01	56000pF	50	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR71H563MA01	56000pF	50	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR71H683KA01	68000pF	50	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR71H683MA01	68000pF	50	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR71H823KA01	82000pF	50	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR71H823MA01	82000pF	50	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A103KA01	10000pF	100	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A103MA01	10000pF	100	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A104KA01	0.1uF	100	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A104MA01	0.1uF	100	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A123KA01	12000pF	100	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A123MA01	12000pF	100	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A153KA01	15000pF	100	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A153MA01	15000pF	100	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A183KA01	18000pF	100	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A183MA01	18000pF	100	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A223KA01	22000pF	100	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A223MA01	22000pF	100	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A273KA01	27000pF	100	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A273MA01	27000pF	100	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A333KA01	33000pF	100	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A333MA01	33000pF	100	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A393KA01	39000pF	100	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A393MA01	39000pF	100	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A473KA01	47000pF	100	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A473MA01	47000pF	100	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A563KA01	56000pF	100	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A563MA01	56000pF	100	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A683KA01	68000pF	100	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A683MA01	68000pF	100	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A822KA01	8200pF	100	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A822MA01	8200pF	100	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A823KA01	82000pF	100	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCE21BR72A823MA01	82000pF	100	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCH155C71A105KE11	1uF	10	X7S	1005M/0402	0.7	+/-10%	Implantable medical device
GCH155R71A104KE01	0.1uF	10	X7R	1005M/0402	0.55	+/-10%	Implantable medical device
GCH155R71C104KE01	0.1uF	16	X7R	1005M/0402	0.55	+/-10%	Implantable medical device
GCH155R71C224KE01	0.22uF	16	X7R	1005M/0402	0.55	+/-10%	Implantable medical device
GCH155R71C473KE01	47000pF	16	X7R	1005M/0402	0.55	+/-10%	Implantable medical device
GCH155R71E103KE01	10000pF	25	X7R	1005M/0402	0.55	+/-10%	Implantable medical device
GCH155R71E223KE01	22000pF	25	X7R	1005M/0402	0.55	+/-10%	Implantable medical device
GCH155R71E473KE01	47000pF	25	X7R	1005M/0402	0.55	+/-10%	Implantable medical device
GCH155R71H102KE01	1000pF	50	X7R	1005M/0402	0.55	+/-10%	Implantable medical device
GCH155R71H103KE01	1000pF	50	X7R	1005M/0402	0.55	+/-10%	Implantable medical device
GCH155R71H104KE01	0.1uF	50	X7R	1005M/0402	0.55	+/-10%	Implantable medical device
GCH155R71H221KE01	220pF	50	X7R	1005M/0402	0.55	+/-10%	Implantable medical device
GCH155R71H222KE01	2200pF	50	X7R	1005M/0402	0.55	+/-10%	Implantable medical device
GCH155R71H223KE01	22000pF	50	X7R	1005M/0402	0.55	+/-10%	Implantable medical device
GCH155R71H471KE01	470pF	50	X7R	1005M/0402	0.55	+/-10%	Implantable medical device
GCH155R71H472KE01	4700pF	50	X7R	1005M/0402	0.55	+/-10%	Implantable medical device
GCH155R71H473KE01	47000pF	50	X7R	1005M/0402	0.55	+/-10%	Implantable medical device

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GCH155R72A102KE01	1000pF	100	X7R	1005M/0402	0.55	+/-10%	Implantable medical device
GCH155R72A221KE01	220pF	100	X7R	1005M/0402	0.55	+/-10%	Implantable medical device
GCH155R72A222KE01	2200pF	100	X7R	1005M/0402	0.55	+/-10%	Implantable medical device
GCH155R72A331KE01	330pF	100	X7R	1005M/0402	0.55	+/-10%	Implantable medical device
GCH155R72A471KE01	470pF	100	X7R	1005M/0402	0.55	+/-10%	Implantable medical device
GCH155R72A472KE01	4700pF	100	X7R	1005M/0402	0.55	+/-10%	Implantable medical device
GCH188C71A225KE01	2.2uF	10	X7S	1608M/0603	0.9	+/-10%	Implantable medical device
GCH188R70J225KE01	2.2uF	6.3	X7R	1608M/0603	0.9	+/-10%	Implantable medical device
GCH188R71C104KE01	0.1uF	16	X7R	1608M/0603	0.9	+/-10%	Implantable medical device
GCH188R71C105KE01	1uF	16	X7R	1608M/0603	0.9	+/-10%	Implantable medical device
GCH188R71C474KE01	0.47uF	16	X7R	1608M/0603	0.9	+/-10%	Implantable medical device
GCH188R71E104KE01	0.1uF	25	X7R	1608M/0603	0.9	+/-10%	Implantable medical device
GCH188R71E105KE01	1uF	25	X7R	1608M/0603	0.9	+/-10%	Implantable medical device
GCH188R71E224KE01	0.22uF	25	X7R	1608M/0603	0.9	+/-10%	Implantable medical device
GCH188R71E473KE01	47000pF	25	X7R	1608M/0603	0.9	+/-10%	Implantable medical device
GCH188R71H102KE01	1000pF	50	X7R	1608M/0603	0.9	+/-10%	Implantable medical device
GCH188R71H103KE01	10000pF	50	X7R	1608M/0603	0.9	+/-10%	Implantable medical device
GCH188R71H104KE01	0.1uF	50	X7R	1608M/0603	0.9	+/-10%	Implantable medical device
GCH188R71H222KE01	2200pF	50	X7R	1608M/0603	0.9	+/-10%	Implantable medical device
GCH188R71H223KE01	22000pF	50	X7R	1608M/0603	0.9	+/-10%	Implantable medical device
GCH188R71H224KE01	0.22uF	50	X7R	1608M/0603	0.9	+/-10%	Implantable medical device
GCH188R71H472KE01	4700pF	50	X7R	1608M/0603	0.9	+/-10%	Implantable medical device
GCH188R71H473KE01	47000pF	50	X7R	1608M/0603	0.9	+/-10%	Implantable medical device
GCH188R72A102KE01	1000pF	100	X7R	1608M/0603	0.9	+/-10%	Implantable medical device
GCH188R72A103KE01	10000pF	100	X7R	1608M/0603	0.9	+/-10%	Implantable medical device
GCH188R72A104KE01	0.1uF	100	X7R	1608M/0603	0.9	+/-10%	Implantable medical device
GCH188R72A222KE01	2200pF	100	X7R	1608M/0603	0.9	+/-10%	Implantable medical device
GCH188R72A223KE01	22000pF	100	X7R	1608M/0603	0.9	+/-10%	Implantable medical device
GCH188R72A472KE01	4700pF	100	X7R	1608M/0603	0.9	+/-10%	Implantable medical device
GCH219R71C105KE01	1uF	16	X7R	2012M/0805	0.95	+/-10%	Implantable medical device
GCH219R71E474KE01	0.47uF	25	X7R	2012M/0805	0.95	+/-10%	Implantable medical device
GCH21BC71E475KE11	4.7uF	25	X7S	2012M/0805	1.45	+/-10%	Implantable medical device
GCH21BC72A105KE11	1uF	100	X7S	2012M/0805	1.45	+/-10%	Implantable medical device
GCH21BC7YA475KE11	4.7uF	35	X7S	2012M/0805	1.45	+/-10%	Implantable medical device
GCH21BR71A106KE01	10uF	10	X7R	2012M/0805	1.4	+/-10%	Implantable medical device
GCH21BR71A225KE01	2.2uF	10	X7R	2012M/0805	1.4	+/-10%	Implantable medical device
GCH21BR71C225KE01	2.2uF	16	X7R	2012M/0805	1.4	+/-10%	Implantable medical device
GCH21BR71E105KE01	1uF	25	X7R	2012M/0805	1.4	+/-10%	Implantable medical device
GCH21BR71E224KE01	0.22uF	25	X7R	2012M/0805	1.4	+/-10%	Implantable medical device
GCH21BR71H104KE01	0.1uF	50	X7R	2012M/0805	1.4	+/-10%	Implantable medical device
GCH21BR71H105KE01	1uF	50	X7R	2012M/0805	1.4	+/-10%	Implantable medical device
GCH21BR71H224KE01	0.22uF	50	X7R	2012M/0805	1.4	+/-10%	Implantable medical device
GCH21BR71H473KE01	47000pF	50	X7R	2012M/0805	1.4	+/-10%	Implantable medical device
GCH21BR71H474KE01	0.47uF	50	X7R	2012M/0805	1.4	+/-10%	Implantable medical device
GCH21BR72A103KE01	10000pF	100	X7R	2012M/0805	1.4	+/-10%	Implantable medical device
GCH21BR72A104KE01	0.1uF	100	X7R	2012M/0805	1.4	+/-10%	Implantable medical device
GCH21BR72A223KE01	22000pF	100	X7R	2012M/0805	1.4	+/-10%	Implantable medical device
GCH21BR72A473KE01	47000pF	100	X7R	2012M/0805	1.4	+/-10%	Implantable medical device
GCH21BR7YA105KE01	1uF	35	X7R	2012M/0805	1.4	+/-10%	Implantable medical device
GCH319R72A104KE01	0.1uF	100	X7R	3216M/1206	0.95	+/-10%	Implantable medical device
GCH31CR71A106KE01	10uF	10	X7R	3216M/1206	1.8	+/-10%	Implantable medical device
GCH31CR71C475KE01	4.7uF	16	X7R	3216M/1206	1.8	+/-10%	Implantable medical device
GCH31CR71E475KE01	4.7uF	25	X7R	3216M/1206	1.8	+/-10%	Implantable medical device
GCH31CR71H225KE01	2.2uF	50	X7R	3216M/1206	1.8	+/-10%	Implantable medical device
GCH31CR72A105KE01	1uF	100	X7R	3216M/1206	1.8	+/-10%	Implantable medical device
GCH31MR71E225KE01	2.2uF	25	X7R	3216M/1206	1.3	+/-10%	Implantable medical device
GCH31MR71H105KE01	1uF	50	X7R	3216M/1206	1.25	+/-10%	Implantable medical device
GCH31MR71H474KE01	0.47uF	50	X7R	3216M/1206	1.25	+/-10%	Implantable medical device
GCH31MR72A224KE01	0.22uF	100	X7R	3216M/1206	1.25	+/-10%	Implantable medical device
GCH32DR71C106KE01	10uF	16	X7R	3225M/1210	2.2	+/-10%	Implantable medical device
GCH32DR71E475KE01	4.7uF	25	X7R	3225M/1210	2.2	+/-10%	Implantable medical device
GCH32DR72A225KE01	2.2uF	100	X7R	3225M/1210	2.2	+/-10%	Implantable medical device
GCH32ER71A226KE01	22uF	10	X7R	3225M/1210	2.7	+/-10%	Implantable medical device
GCH32ER71H105KE01	1uF	50	X7R	3225M/1210	2.7	+/-10%	Implantable medical device
GCH32ER71H475KE01	4.7uF	50	X7R	3225M/1210	2.7	+/-10%	Implantable medical device
GCH188C70J335KE02	3.3uF	6.3	X7S	1608M/0603	1.0	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188C70J335ME02	3.3uF	6.3	X7S	1608M/0603	1.0	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188C70J475KE02	4.7uF	6.3	X7S	1608M/0603	1.0	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GCJ188C70J475ME02	4.7uF	6.3	X7S	1608M/0603	1.0	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81C104KA01	0.1uF	16	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81C104MA01	0.1uF	16	X8L	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81C124KA01	0.12uF	16	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81C154KA01	0.15uF	16	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81C154MA01	0.15uF	16	X8L	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81C224KA01	0.22uF	16	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81C224MA01	0.22uF	16	X8L	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81C393KA01	39000pF	16	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81C473KA01	47000pF	16	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81C473MA01	47000pF	16	X8L	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81C683KA01	68000pF	16	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81C683MA01	68000pF	16	X8L	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81E154KA01	0.15uF	25	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81E154MA01	0.15uF	25	X8L	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81E224KA01	0.22uF	25	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81E224MA01	0.22uF	25	X8L	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81E393KA01	39000pF	25	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81E683KA01	68000pF	25	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81E683MA01	68000pF	25	X8L	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81H102KA01	1000pF	50	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81H102MA01	1000pF	50	X8L	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81H103KA01	1000pF	50	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81H103MA01	1000pF	50	X8L	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81H123KA01	1200pF	50	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81H152KA01	1500pF	50	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81H152MA01	1500pF	50	X8L	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81H153KA01	1500pF	50	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81H153MA01	1500pF	50	X8L	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81H182KA01	1800pF	50	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81H222KA01	2200pF	50	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81H222MA01	2200pF	50	X8L	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81H223KA01	2200pF	50	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81H223MA01	2200pF	50	X8L	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81H272KA01	2700pF	50	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81H332KA01	3300pF	50	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81H392KA01	3900pF	50	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81H472KA01	4700pF	50	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81H472MA01	4700pF	50	X8L	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81H562KA01	5600pF	50	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81H682KA01	6800pF	50	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L81H822KA01	8200pF	50	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L8EC335KE08	3.3uF	6.3	X8L	1608M/0603	1.0	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L8EH154KA07	0.15uF	50	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L8EH224KA07	0.22uF	50	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L8EL104KA07	0.1uF	100	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L8YA393KA01	39000pF	35	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L8YA683KA01	68000pF	35	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188L8YA683MA01	68000pF	35	X8L	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188M8EC475KE08	4.7uF	6.3	X8M	1608M/0603	1.0	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R70J225KE01	2.2uF	6.3	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R70J225ME01	2.2uF	6.3	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71A124KA01	0.12uF	10	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71A154KA01	0.15uF	10	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71A154MA01	0.15uF	10	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71A224KA01	0.22uF	10	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71A224MA01	0.22uF	10	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71C103KA01	10000pF	16	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71C103MA01	10000pF	16	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71C124KA01	0.12uF	16	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71C154KA01	0.15uF	16	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71C154MA01	0.15uF	16	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71C224KA01	0.22uF	16	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71C224MA01	0.22uF	16	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71C273KA01	27000pF	16	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71C273MA01	27000pF	16	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71C274KA01	0.27uF	16	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71C333KA01	33000pF	16	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GCJ188R71C333MA01	33000pF	16	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71C334KA01	0.33uF	16	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71C334MA01	0.33uF	16	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71C393KA01	39000pF	16	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71C393MA01	39000pF	16	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71C473KA01	47000pF	16	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71C473MA01	47000pF	16	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71C474KA12	0.47uF	16	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71C474MA12	0.47uF	16	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71C563KA01	56000pF	16	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71C823KA01	82000pF	16	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E102KA01	1000pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E102MA01	1000pF	25	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E103KA01	10000pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E103MA01	10000pF	25	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E104KA12	0.1uF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E104MA12	0.1uF	25	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E123KA01	12000pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E124KA01	0.12uF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E152KA01	1500pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E152MA01	1500pF	25	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E153KA01	15000pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E153MA01	15000pF	25	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E154KA01	0.15uF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E154MA01	0.15uF	25	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E182KA01	1800pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E222KA01	2200pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E222MA01	2200pF	25	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E223KA01	22000pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E223MA01	22000pF	25	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E224KA12	0.22uF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E224MA12	0.22uF	25	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E272KA01	2700pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E273KA01	27000pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E273MA01	27000pF	25	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E332KA01	3300pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E333KA01	33000pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E333MA01	33000pF	25	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E392KA01	3900pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E393KA01	39000pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E393MA01	39000pF	25	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E472KA01	4700pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E472MA01	4700pF	25	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E473KA01	47000pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E473MA01	47000pF	25	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E562KA01	5600pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E682KA01	6800pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E683KA12	68000pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E683MA12	68000pF	25	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71E822KA01	8200pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71H102KA01	1000pF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71H102MA01	1000pF	50	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71H103KA01	10000pF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71H103MA01	10000pF	50	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71H104KA12	0.1uF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71H104MA12	0.1uF	50	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71H123KA01	12000pF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71H152KA01	1500pF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71H152MA01	1500pF	50	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71H153KA01	15000pF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71H153MA01	15000pF	50	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71H154KA01	0.15uF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71H182KA01	1800pF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71H222KA01	2200pF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71H222MA01	2200pF	50	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71H223KA01	22000pF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71H223MA01	22000pF	50	X7R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R71H224KA01	0.22uF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GCJ188R92A333MA01	33000pF	100	X8R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R92A392KA01	3900pF	100	X8R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R92A393KA01	39000pF	100	X8R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R92A472KA01	4700pF	100	X8R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R92A472MA01	4700pF	100	X8R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R92A473KA01	47000pF	100	X8R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R92A473MA01	47000pF	100	X8R	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R92A562KA01	5600pF	100	X8R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R92A682KA01	6800pF	100	X8R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ188R92A683KA01	68000pF	100	X8R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71E102KA01	1000pF	25	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71E102MA01	1000pF	25	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71E103KA01	10000pF	25	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71E103MA01	10000pF	25	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71E222KA01	2200pF	25	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71E222MA01	2200pF	25	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71E332KA01	3300pF	25	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71E332MA01	3300pF	25	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71E471KA01	470pF	25	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71E471MA01	470pF	25	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71E472KA01	4700pF	25	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71E472MA01	4700pF	25	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71E561KA01	560pF	25	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71E561MA01	560pF	25	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71E682KA01	6800pF	25	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71E682MA01	6800pF	25	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71E821KA01	820pF	25	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H102KA01	1000pF	50	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H102MA01	1000pF	50	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H103KA01	10000pF	50	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H103MA01	10000pF	50	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H153KA01	15000pF	50	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H153MA01	15000pF	50	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H222KA01	2200pF	50	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H222MA01	2200pF	50	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H223KA01	22000pF	50	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H223MA01	22000pF	50	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H331KA01	330pF	50	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H331MA01	330pF	50	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H332KA01	3300pF	50	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H332MA01	3300pF	50	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H471KA01	470pF	50	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H471MA01	470pF	50	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H472KA01	4700pF	50	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H472MA01	4700pF	50	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H561KA01	560pF	50	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H561MA01	560pF	50	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H682KA01	6800pF	50	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H682MA01	6800pF	50	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R71H821KA01	820pF	50	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A102KA01	1000pF	100	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A102MA01	1000pF	100	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A103KA01	10000pF	100	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A103MA01	10000pF	100	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A122KA01	1200pF	100	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A123KA01	12000pF	100	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A152KA01	1500pF	100	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive
GCJ216R72A153KA01	15000pF	100	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A153MA01	15000pF	100	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A182KA01	1800pF	100	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A183KA01	18000pF	100	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A222KA01	2200pF	100	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A222MA01	2200pF	100	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A223KA01	22000pF	100	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A223MA01	22000pF	100	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A272KA01	2700pF	100	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A332KA01	3300pF	100	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A332MA01	3300pF	100	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GCJ216R72A392KA01	3900pF	100	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A472KA01	4700pF	100	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A472MA01	4700pF	100	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A562KA01	5600pF	100	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A682KA01	6800pF	100	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A682MA01	6800pF	100	X7R	2012M/0805	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ216R72A822KA01	8200pF	100	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R71C105KA01	1uF	16	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R71C105MA01	1uF	16	X7R	2012M/0805	0.95	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R71E223KA01	22000pF	25	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R71E223MA01	22000pF	25	X7R	2012M/0805	0.95	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R71E474KA12	0.47uF	25	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R71E474MA12	0.47uF	25	X7R	2012M/0805	0.95	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R71H273KA01	27000pF	50	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R71H273MA01	27000pF	50	X7R	2012M/0805	0.95	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R71H333KA01	33000pF	50	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R71H333MA01	33000pF	50	X7R	2012M/0805	0.95	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R71H334KA12	0.33uF	50	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R71H334MA12	0.33uF	50	X7R	2012M/0805	0.95	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R71H393KA01	39000pF	50	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R72A221KA01	220pF	100	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R72A221MA01	220pF	100	X7R	2012M/0805	0.95	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R72A271KA01	270pF	100	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R72A273KA01	27000pF	100	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R72A273MA01	27000pF	100	X7R	2012M/0805	0.95	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R72A331KA01	330pF	100	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R72A333KA01	33000pF	100	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R72A333MA01	33000pF	100	X7R	2012M/0805	0.95	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R72A391KA01	390pF	100	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R72A393KA01	39000pF	100	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R72A471KA01	470pF	100	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R72A471MA01	470pF	100	X7R	2012M/0805	0.95	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R72A561KA01	560pF	100	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R72A681KA01	680pF	100	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R72A681MA01	680pF	100	X7R	2012M/0805	0.95	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ219R72A821KA01	820pF	100	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BC72A105KE02	1uF	100	X7S	2012M/0805	1.5	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BC72A105ME02	1uF	100	X7S	2012M/0805	1.5	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81C105KA01	1uF	16	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81C105MA01	1uF	16	X8L	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81C564KA01	0.56uF	16	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81C684KA01	0.68uF	16	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81C684MA01	0.68uF	16	X8L	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81C824KA01	0.82uF	16	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive
GCJ21BL81E105KA01	1uF	25	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81E105MA01	1uF	25	X8L	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81E124KA01	0.12uF	25	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81E154KA01	0.15uF	25	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81E154MA01	0.15uF	25	X8L	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81E184KA01	0.18uF	25	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81E184MA01	0.18uF	25	X8L	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81E224KA01	0.22uF	25	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81E224MA01	0.22uF	25	X8L	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81E274KA01	0.27uF	25	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81E334KA01	0.33uF	25	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81E334MA01	0.33uF	25	X8L	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81E394KA01	0.39uF	25	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81E684KA01	0.68uF	25	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81E684MA01	0.68uF	25	X8L	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81E824KA01	0.82uF	25	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive
GCJ21BL81H104KA01	0.1uF	50	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81H104MA01	0.1uF	50	X8L	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81H273KA01	27000pF	50	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81H393KA01	39000pF	50	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81H473KA01	47000pF	50	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81H473MA01	47000pF	50	X8L	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81H563KA01	56000pF	50	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81H683KA01	68000pF	50	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GCJ21BL81H683MA01	68000pF	50	X8L	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL81H823KA01	82000pF	50	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL8YA124KA01	0.12uF	35	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL8YA154KA01	0.15uF	35	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL8YA154MA01	0.15uF	35	X8L	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL8YA184KA01	0.18uF	35	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL8YA184MA01	0.18uF	35	X8L	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL8YA224KA01	0.22uF	35	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL8YA224MA01	0.22uF	35	X8L	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL8YA334KA01	0.33uF	35	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BL8YA334MA01	0.33uF	35	X8L	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71A106KE01	10uF	10	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71A106ME01	10uF	10	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71A225KA01	2.2uF	10	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71A225MA01	2.2uF	10	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71C105KA01	1uF	16	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71C105MA01	1uF	16	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71C225KA13	2.2uF	16	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71C225MA13	2.2uF	16	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71C274KA01	0.27uF	16	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71C334KA01	0.33uF	16	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71C334MA01	0.33uF	16	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71C394KA01	0.39uF	16	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71C475KA01	4.7uF	16	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71C475MA01	4.7uF	16	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71C564KA01	0.56uF	16	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71C684KA01	0.68uF	16	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71C684MA01	0.68uF	16	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71E104KA01	0.1uF	25	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71E104MA01	0.1uF	25	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71E105KA12	1uF	25	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71E105MA12	1uF	25	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71E155KA01	1.5uF	25	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71E225KA01	2.2uF	25	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71E225MA01	2.2uF	25	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71E273KA01	27000pF	25	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71E274KA01	0.27uF	25	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71E334KA01	0.33uF	25	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71E334MA01	0.33uF	25	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71E394KA01	0.39uF	25	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71E473KA01	47000pF	25	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71E473MA01	47000pF	25	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71E563KA01	56000pF	25	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71E564KA12	0.56uF	25	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71E683KA01	68000pF	25	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71E683MA01	68000pF	25	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71E684KA12	0.68uF	25	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71E684MA12	0.68uF	25	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71E823KA01	82000pF	25	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71E824KA12	0.82uF	25	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive
GCJ21BR71H104KA01	0.1uF	50	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71H104MA01	0.1uF	50	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71H124KA01	0.12uF	50	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71H154KA01	0.15uF	50	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71H154MA01	0.15uF	50	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71H184KA01	0.18uF	50	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71H184MA01	0.18uF	50	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71H224KA01	0.22uF	50	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71H224MA01	0.22uF	50	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71H334KA12	0.33uF	50	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71H334MA12	0.33uF	50	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71H473KA01	47000pF	50	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71H473MA01	47000pF	50	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71H563KA01	56000pF	50	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71H683KA01	68000pF	50	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71H683MA01	68000pF	50	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR71H823KA01	82000pF	50	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR72A104KA01	0.1uF	100	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GCJ21BR72A104MA01	0.1uF	100	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR72A473KA01	47000pF	100	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR72A473MA01	47000pF	100	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR72A563KA01	56000pF	100	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR72A683KA01	68000pF	100	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR72A683MA01	68000pF	100	X7R	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ21BR72A823KA01	82000pF	100	X7R	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ319R71H104KA01	0.1uF	50	X7R	3216M/1206	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ319R71H104MA01	0.1uF	50	X7R	3216M/1206	0.95	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ319R72A104KA01	0.1uF	100	X7R	3216M/1206	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ319R72A104MA01	0.1uF	100	X7R	3216M/1206	0.95	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CC71E106KA15	10uF	25	X7S	3216M/1206	2.0	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CC71E106MA15	10uF	25	X7S	3216M/1206	2.0	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CC71H475KA01	4.7uF	50	X7S	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CC71H475MA01	4.7uF	50	X7S	3216M/1206	1.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CC72A225KE01	2.2uF	100	X7S	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CL81C475KA01	4.7uF	16	X8L	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CL81C475MA01	4.7uF	16	X8L	3216M/1206	1.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CL81E105KA01	1uF	25	X8L	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CL81E105MA01	1uF	25	X8L	3216M/1206	1.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CL81E564KA01	0.56uF	25	X8L	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CL81E684KA01	0.68uF	25	X8L	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CL81E684MA01	0.68uF	25	X8L	3216M/1206	1.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CL81E824KA01	0.82uF	25	X8L	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CL8ED226KE07	22uF	10	X8L	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CL8EL105KA07	1uF	100	X8L	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CL8YA105KA01	1uF	35	X8L	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CL8YA105MA01	1uF	35	X8L	3216M/1206	1.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CL8YA564KA01	0.56uF	35	X8L	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CL8YA684KA01	0.68uF	35	X8L	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CL8YA684MA01	0.68uF	35	X8L	3216M/1206	1.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CL8YA824KA01	0.82uF	35	X8L	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CR70J226KE01	22uF	6.3	X7R	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CR70J226ME01	22uF	6.3	X7R	3216M/1206	1.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CR71A106KA13	10uF	10	X7R	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CR71A106MA13	10uF	10	X7R	3216M/1206	1.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CR71A226KE01	22uF	10	X7R	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CR71A226ME01	22uF	10	X7R	3216M/1206	1.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CR71C106KA15	10uF	16	X7R	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CR71C106MA15	10uF	16	X7R	3216M/1206	1.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CR71C475KA01	4.7uF	16	X7R	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CR71C475MA01	4.7uF	16	X7R	3216M/1206	1.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CR71E475KA12	4.7uF	25	X7R	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CR71E475MA12	4.7uF	25	X7R	3216M/1206	1.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CR71H105KA12	1uF	50	X7R	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CR71H105MA12	1uF	50	X7R	3216M/1206	1.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CR71H155KA12	1.5uF	50	X7R	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CR71H155MA12	1.5uF	50	X7R	3216M/1206	1.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CR71H225KA12	2.2uF	50	X7R	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CR71H225MA12	2.2uF	50	X7R	3216M/1206	1.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CR71H684KA01	0.68uF	50	X7R	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CR71H684MA01	0.68uF	50	X7R	3216M/1206	1.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CR72A105KA01	1uF	100	X7R	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31CR72A105MA01	1uF	100	X7R	3216M/1206	1.9	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31ML81C105KA01	1uF	16	X8L	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31ML81C105MA01	1uF	16	X8L	3216M/1206	1.35	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31ML81C225KA01	2.2uF	16	X8L	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31ML81C225MA01	2.2uF	16	X8L	3216M/1206	1.35	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31ML81E394KA01	0.39uF	25	X8L	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31ML81E394MA01	0.39uF	25	X8L	3216M/1206	1.35	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31ML81E474KA01	0.47uF	25	X8L	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31ML81E474MA01	0.47uF	25	X8L	3216M/1206	1.35	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31ML8YA394KA01	0.39uF	35	X8L	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31ML8YA394MA01	0.39uF	35	X8L	3216M/1206	1.35	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31ML8YA474KA01	0.47uF	35	X8L	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31ML8YA474MA01	0.47uF	35	X8L	3216M/1206	1.35	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71C105KA01	1uF	16	X7R	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71C105MA01	1uF	16	X7R	3216M/1206	1.35	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GCJ31MR71C225KA01	2.2uF	16	X7R	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71C225MA01	2.2uF	16	X7R	3216M/1206	1.35	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71E104KA01	0.1uF	25	X7R	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71E104MA01	0.1uF	25	X7R	3216M/1206	1.35	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71E105KA01	1uF	25	X7R	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71E105MA01	1uF	25	X7R	3216M/1206	1.35	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71E124KA01	0.12uF	25	X7R	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71E154KA01	0.15uF	25	X7R	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71E184KA01	0.18uF	25	X7R	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71E224KA01	0.22uF	25	X7R	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71E224MA01	0.22uF	25	X7R	3216M/1206	1.35	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71E225KA12	2.2uF	25	X7R	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71E225MA12	2.2uF	25	X7R	3216M/1206	1.35	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71E335KA12	3.3uF	25	X7R	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71E335MA12	3.3uF	25	X7R	3216M/1206	1.35	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71H104KA01	0.1uF	50	X7R	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71H104MA01	0.1uF	50	X7R	3216M/1206	1.35	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71H105KA12	1uF	50	X7R	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71H105MA12	1uF	50	X7R	3216M/1206	1.35	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71H224KA01	0.22uF	50	X7R	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71H224MA01	0.22uF	50	X7R	3216M/1206	1.35	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71H274KA01	0.27uF	50	X7R	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71H394KA01	0.39uF	50	X7R	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71H394MA01	0.39uF	50	X7R	3216M/1206	1.35	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71H474KA01	0.47uF	50	X7R	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71H474MA01	0.47uF	50	X7R	3216M/1206	1.35	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71H564KA12	0.56uF	50	X7R	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR71H564MA12	0.56uF	50	X7R	3216M/1206	1.35	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR72A154KA01	0.15uF	100	X7R	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR72A184KA01	0.18uF	100	X7R	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR72A224KA01	0.22uF	100	X7R	3216M/1206	1.35	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ31MR72A224MA01	0.22uF	100	X7R	3216M/1206	1.35	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ32DC72A475KE01	4.7uF	100	X7S	3225M/1210	2.3	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ32DL8EL225KA07	2.2uF	100	X8L	3225M/1210	2.3	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ32DR72A225KA01	2.2uF	100	X7R	3225M/1210	2.3	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ32DR72A225MA01	2.2uF	100	X7R	3225M/1210	2.3	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ32EC71E226KE02	22uF	25	X7S	3225M/1210	2.85	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ32EC71H106KA01	10uF	50	X7S	3225M/1210	2.8	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ32EC71H106MA01	10uF	50	X7S	3225M/1210	2.8	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ32EL81E475KA01	4.7uF	25	X8L	3225M/1210	2.8	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ32EL81E475MA01	4.7uF	25	X8L	3225M/1210	2.8	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ32EL8EF226KE08	22uF	25	X8L	3225M/1210	2.85	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ32ER70J476KE01	47uF	6.3	X7R	3225M/1210	2.8	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ32ER70J476ME01	47uF	6.3	X7R	3225M/1210	2.8	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ32ER71C226KE01	22uF	16	X7R	3225M/1210	2.8	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ32ER71C226ME01	22uF	16	X7R	3225M/1210	2.8	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ32ER71H475KA12	4.7uF	50	X7R	3225M/1210	2.8	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ32ER71H475MA12	4.7uF	50	X7R	3225M/1210	2.8	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ32ER91C106KE01	10uF	16	X8R	3225M/1210	2.8	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ32ER91C106ME01	10uF	16	X8R	3225M/1210	2.8	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCJ32ER91C685KE01	6.8uF	16	X8R	3225M/1210	2.8	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM033R71A103KA03	10000pF	10	X7R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM033R71A152KA03	1500pF	10	X7R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM033R71A222KA03	2200pF	10	X7R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM033R71A332KA03	3300pF	10	X7R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM033R71A472KA03	4700pF	10	X7R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM033R71A682KA03	6800pF	10	X7R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM033R71C222KA55	2200pF	16	X7R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM033R71C331KA03	3300pF	16	X7R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM033R71C332KA55	3300pF	16	X7R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM033R71C681KA03	680pF	16	X7R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM033R71E101KA03	100pF	25	X7R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM033R71E102KA03	1000pF	25	X7R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM033R71E151KA03	150pF	25	X7R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM033R71E152KA03	1500pF	25	X7R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM033R71E221KA03	220pF	25	X7R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM033R71E222KE01	2200pF	25	X7R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive
GCM033R71E222KE02	2200pF	25	X7R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GCM033R71E331KA03	330pF	25	X7R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM033R71E332KE01	3300pF	25	X7R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive
GCM033R71E332KE02	3300pF	25	X7R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM033R71E471KA03	470pF	25	X7R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM033R71E681KA03	680pF	25	X7R	0603M/0201	0.33	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155C71A105KE38	1uF	10	X7S	1005M/0402	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155C71A105KE39	1uF	10	X7S	1005M/0402	0.7	+/-10%	Powertrain/Safety for Automotive
GCM155C71A474KE35	0.47uF	10	X7S	1005M/0402	0.6	+/-10%	Powertrain/Safety for Automotive
GCM155C71A474KE36	0.47uF	10	X7S	1005M/0402	0.6	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155C71A474ME35	0.47uF	10	X7S	1005M/0402	0.6	+/-20%	Powertrain/Safety for Automotive
GCM155C71A474ME36	0.47uF	10	X7S	1005M/0402	0.6	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155C71A684KE38	0.68uF	10	X7S	1005M/0402	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155C71A684KE39	0.68uF	10	X7S	1005M/0402	0.7	+/-10%	Powertrain/Safety for Automotive
GCM155C71A684ME38	0.68uF	10	X7S	1005M/0402	0.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155C71A684ME39	0.68uF	10	X7S	1005M/0402	0.7	+/-20%	Powertrain/Safety for Automotive
GCM155L81C223KA01	22000pF	16	X8L	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155L81C223KA37	22000pF	16	X8L	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155L81C473KA01	47000pF	16	X8L	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155L81C473KA37	47000pF	16	X8L	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155L81E103KA01	10000pF	25	X8L	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155L81E103KA37	10000pF	25	X8L	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155L81E104KE01	0.1uF	25	X8L	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155L81E104KE02	0.1uF	25	X8L	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155L81H102KA01	1000pF	50	X8L	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155L81H102KA37	1000pF	50	X8L	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155L81H221KA01	220pF	50	X8L	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155L81H221KA37	220pF	50	X8L	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155L81H222KA01	2200pF	50	X8L	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155L81H222KA37	2200pF	50	X8L	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155L81H471KA01	470pF	50	X8L	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155L81H471KA37	470pF	50	X8L	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155L81H472KA01	4700pF	50	X8L	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155L81H472KA37	4700pF	50	X8L	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155L81H473KA01	4700pF	50	X8L	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155L81H473KA37	4700pF	50	X8L	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155L8EH333KE07	33000pF	50	X8L	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155L8EH473KE07	47000pF	50	X8L	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71A104KA01	0.1uF	10	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R71C104KA55	0.1uF	16	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71C154KE02	0.15uF	16	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71C224KE01	0.22uF	16	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R71C224KE02	0.22uF	16	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71C333KA37	33000pF	16	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71C473KA37	47000pF	16	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71C683KA55	68000pF	16	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71E103KA37	10000pF	25	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71E153KA55	15000pF	25	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71E223KA55	22000pF	25	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71E333KA55	33000pF	25	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71E473KA55	47000pF	25	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71E682KA37	6800pF	25	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71H102KA37	1000pF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71H103KA55	10000pF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71H104KE02	0.1uF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71H104KE37	0.1uF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R71H152KA37	1500pF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71H153KA40	15000pF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R71H153KA55	15000pF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71H221KA37	220pF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71H222KA37	2200pF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71H223KA40	22000pF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R71H223KA55	22000pF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71H331KA37	330pF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71H332KA37	3300pF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71H333KE01	33000pF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R71H333KE02	33000pF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71H471KA37	470pF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71H472KA37	4700pF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71H473KE01	47000pF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R71H473KE02	47000pF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GCM155R71H681KA37	680pF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71H682KA55	6800pF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R71H683KE01	68000pF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R71H683KE02	68000pF	50	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R72A102KA01	1000pF	100	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R72A102KA37	1000pF	100	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R72A152KA01	1500pF	100	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R72A152KA37	1500pF	100	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R72A221KA01	220pF	100	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R72A221KA37	220pF	100	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R72A222KA01	2200pF	100	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R72A222KA37	2200pF	100	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R72A331KA01	330pF	100	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R72A331KA37	330pF	100	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R72A332KA01	3300pF	100	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R72A332KA37	3300pF	100	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R72A471KA01	470pF	100	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R72A471KA37	470pF	100	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R72A472KA01	4700pF	100	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R72A472KA37	4700pF	100	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM155R72A681KA01	680pF	100	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive
GCM155R72A681KA37	680pF	100	X7R	1005M/0402	0.55	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188C71A225KE01	2.2uF	10	X7S	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188C71A225ME01	2.2uF	10	X7S	1608M/0603	0.9	+/-20%	Powertrain/Safety for Automotive
GCM188D70G106ME35	10uF	4	X7T	1608M/0603	1.0	+/-20%	Powertrain/Safety for Automotive
GCM188D70G106ME36	10uF	4	X7T	1608M/0603	1.0	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188L81C224KA01	0.22uF	16	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188L81C224KA37	0.22uF	16	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188L81H104KA57	0.1uF	50	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188L81H223KA37	22000pF	50	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188L81H473KA40	47000pF	50	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188L81H473KA55	47000pF	50	X8L	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R70J225KE21	2.2uF	6.3	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R70J225KE22	2.2uF	6.3	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71C104KA37	0.1uF	16	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71C105KA49	1uF	16	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R71C105KA64	1uF	16	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71C334KA37	0.33uF	16	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71C474KA55	0.47uF	16	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71E102KA37	1000pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71E103KA37	10000pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71E104KA57	0.1uF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71E105KA49	1uF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R71E105KA64	1uF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71E152KA37	1500pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71E153KA37	15000pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71E154KA37	0.15uF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71E222KA37	2200pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71E223KA37	22000pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71E224KA55	0.22uF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71E332KA37	3300pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71E333KA37	33000pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71E472KA37	4700pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71E473KA37	47000pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71E474KA49	0.47uF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R71E474KA64	0.47uF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71E682KA37	6800pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71E683KA57	68000pF	25	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71H102KA37	1000pF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71H103KA37	10000pF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71H104KA57	0.1uF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71H152KA37	1500pF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71H153KA37	15000pF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71H154KA49	0.15uF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R71H154KA64	0.15uF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71H222KA37	2200pF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71H223KA37	22000pF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71H224KA49	0.22uF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GCM188R71H224KA64	0.22uF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71H332KA37	3300pF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71H333KA55	33000pF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71H472KA37	4700pF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71H473KA55	47000pF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71H682KA37	6800pF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R71H683KA57	68000pF	50	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R72A102KA01	1000pF	100	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R72A102KA37	1000pF	100	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R72A103KA01	10000pF	100	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R72A103KA37	10000pF	100	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R72A152KA01	1500pF	100	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R72A152KA37	1500pF	100	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R72A153KA01	15000pF	100	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R72A153KA37	15000pF	100	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R72A222KA01	2200pF	100	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R72A222KA37	2200pF	100	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R72A223KA01	22000pF	100	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R72A223KA37	22000pF	100	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R72A332KA01	3300pF	100	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R72A332KA37	3300pF	100	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R72A472KA01	4700pF	100	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R72A472KA37	4700pF	100	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM188R72A682KA01	6800pF	100	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive
GCM188R72A682KA37	6800pF	100	X7R	1608M/0603	0.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM216R72A103KA37	10000pF	100	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM216R72A153KA37	15000pF	100	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM216R72A223KA37	22000pF	100	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM216R72A682KA37	6800pF	100	X7R	2012M/0805	0.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM219R71C105KA37	1uF	16	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM219R71C224KA37	0.22uF	16	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM219R71C684KA37	0.68uF	16	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM219R71E474KA55	0.47uF	25	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM219R71H333KA37	33000pF	50	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM219R71H334KA40	0.33uF	50	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive
GCM219R71H334KA55	0.33uF	50	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM219R72A333KA37	33000pF	100	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM219R72A682KA01	6800pF	100	X7R	2012M/0805	0.95	+/-10%	Powertrain/Safety for Automotive
GCM21BC71A475KA67	4.7uF	10	X7S	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BC71A475KA73	4.7uF	10	X7S	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BC71C106KE35	10uF	16	X7S	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive
GCM21BC71C106KE36	10uF	16	X7S	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BC71E475KE35	4.7uF	25	X7S	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive
GCM21BC71E475KE36	4.7uF	25	X7S	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BC72A105KE35	1uF	100	X7S	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive
GCM21BC72A105KE36	1uF	100	X7S	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BC72A105ME35	1uF	100	X7S	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive
GCM21BC72A105ME36	1uF	100	X7S	2012M/0805	1.45	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BC7YA225KE01	2.2uF	35	X7S	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BC7YA225KE02	2.2uF	35	X7S	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BC7YA475KE35	4.7uF	35	X7S	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive
GCM21BC7YA475KE36	4.7uF	35	X7S	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BL8EF155KA07	1.5uF	25	X8L	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BL8EF475KE08	4.7uF	25	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BL8EG225KE07	2.2uF	35	X8L	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BL8EG475KE08	4.7uF	35	X8L	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BM8EE106KE08	10uF	16	X8M	2012M/0805	1.45	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR70J106KE21	10uF	6.3	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR70J106KE22	10uF	6.3	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR71A106KE21	10uF	10	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR71A106KE22	10uF	10	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR71A225KA01	2.2uF	10	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR71A225KA37	2.2uF	10	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR71C225KA49	2.2uF	16	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR71C225KA64	2.2uF	16	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR71C474KA37	0.47uF	16	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR71C475KA67	4.7uF	16	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR71C475KA73	4.7uF	16	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GCM21BR71E104KA37	0.1uF	25	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR71E105KA56	1uF	25	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR71E154KA37	0.15uF	25	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR71E155KA36	1.5uF	25	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR71E155KA54	1.5uF	25	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR71E155MA36	1.5uF	25	X7R	2012M/0805	1.4	+/-20%	Powertrain/Safety for Automotive
GCM21BR71E155MA54	1.5uF	25	X7R	2012M/0805	1.4	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR71E224KA37	0.22uF	25	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR71E225KA67	2.2uF	25	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR71E225KA73	2.2uF	25	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR71E334KA37	0.33uF	25	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR71E684KA55	0.68uF	25	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR71H104KA37	0.1uF	50	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR71H105KA01	1uF	50	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR71H105KA03	1uF	50	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR71H154KA37	0.15uF	50	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR71H224KA37	0.22uF	50	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR71H473KA37	47000pF	50	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR71H474KA40	0.47uF	50	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR71H474KA55	0.47uF	50	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR71H683KA37	68000pF	50	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR72A103KA01	10000pF	100	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR72A104KA01	0.1uF	100	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR72A104KA37	0.1uF	100	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR72A153KA01	15000pF	100	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR72A223KA01	22000pF	100	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR72A333KA01	33000pF	100	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR72A473KA01	47000pF	100	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR72A473KA37	47000pF	100	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR72A683KA01	68000pF	100	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR72A683KA37	68000pF	100	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR7YA105KA40	1uF	35	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR7YA105KA55	1uF	35	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR7YA155KA36	1.5uF	35	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR7YA155KA54	1.5uF	35	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM21BR7YA684KA40	0.68uF	35	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive
GCM21BR7YA684KA55	0.68uF	35	X7R	2012M/0805	1.4	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM319R72A104KA01	0.1uF	100	X7R	3216M/1206	0.95	+/-10%	Powertrain/Safety for Automotive
GCM319R72A104KA37	0.1uF	100	X7R	3216M/1206	0.95	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM31CC71E106KA01	10uF	25	X7S	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive
GCM31CC71E106KA03	10uF	25	X7S	3216M/1206	1.9	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM31CC71H475KA03	4.7uF	50	X7S	3216M/1206	1.8	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM31CC71H475KA49	4.7uF	50	X7S	3216M/1206	1.8	+/-10%	Powertrain/Safety for Automotive
GCM31CC72A225KE01	2.2uF	100	X7S	3216M/1206	1.8	+/-10%	Powertrain/Safety for Automotive
GCM31CC72A225KE02	2.2uF	100	X7S	3216M/1206	1.8	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM31CC72A225ME01	2.2uF	100	X7S	3216M/1206	1.8	+/-20%	Powertrain/Safety for Automotive
GCM31CC72A225ME02	2.2uF	100	X7S	3216M/1206	1.8	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCM31CL8EL225KE07	2.2uF	100	X8L	3216M/1206	1.8	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM31CR70J226ME23	22uF	6.3	X7R	3216M/1206	1.8	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCM31CR70J226ME26	22uF	6.3	X7R	3216M/1206	1.8	+/-20%	Powertrain/Safety for Automotive
GCM31CR71A106KA64	10uF	10	X7R	3216M/1206	1.8	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM31CR71A226KE01	22uF	10	X7R	3216M/1206	1.8	+/-10%	Powertrain/Safety for Automotive
GCM31CR71A226KE02	22uF	10	X7R	3216M/1206	1.8	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM31CR71C106KA49	10uF	16	X7R	3216M/1206	1.8	+/-10%	Powertrain/Safety for Automotive
GCM31CR71C106KA64	10uF	16	X7R	3216M/1206	1.8	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM31CR71C475KA37	4.7uF	16	X7R	3216M/1206	1.8	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM31CR71E475KA40	4.7uF	25	X7R	3216M/1206	1.8	+/-10%	Powertrain/Safety for Automotive
GCM31CR71E475KA55	4.7uF	25	X7R	3216M/1206	1.8	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM31CR71H225KA40	2.2uF	50	X7R	3216M/1206	1.8	+/-10%	Powertrain/Safety for Automotive
GCM31CR71H225KA55	2.2uF	50	X7R	3216M/1206	1.8	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM31CR72A105KA01	1uF	100	X7R	3216M/1206	1.8	+/-10%	Powertrain/Safety for Automotive
GCM31CR72A105KA03	1uF	100	X7R	3216M/1206	1.8	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM31MR71E105KA37	1uF	25	X7R	3216M/1206	1.25	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM31MR71E225KA57	2.2uF	25	X7R	3216M/1206	1.3	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM31MR71H105KA40	1uF	50	X7R	3216M/1206	1.25	+/-10%	Powertrain/Safety for Automotive
GCM31MR71H105KA55	1uF	50	X7R	3216M/1206	1.25	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM31MR71H334KA37	0.33uF	50	X7R	3216M/1206	1.25	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM31MR71H474KA37	0.47uF	50	X7R	3216M/1206	1.25	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GCM31MR71H684KA55	0.68uF	50	X7R	3216M/1206	1.25	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM31MR72A154KA01	0.15uF	100	X7R	3216M/1206	1.25	+/-10%	Powertrain/Safety for Automotive
GCM31MR72A154KA37	0.15uF	100	X7R	3216M/1206	1.25	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM31MR72A224KA01	0.22uF	100	X7R	3216M/1206	1.25	+/-10%	Powertrain/Safety for Automotive
GCM31MR72A224KA37	0.22uF	100	X7R	3216M/1206	1.25	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM32DC72A475KE01	4.7uF	100	X7S	3225M/1210	2.2	+/-10%	Powertrain/Safety for Automotive
GCM32DC72A475KE02	4.7uF	100	X7S	3225M/1210	2.2	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM32DC72A475ME01	4.7uF	100	X7S	3225M/1210	2.2	+/-20%	Powertrain/Safety for Automotive
GCM32DC72A475ME02	4.7uF	100	X7S	3225M/1210	2.2	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCM32DL8EL475KE07	4.7uF	100	X8L	3225M/1210	2.2	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM32DR71C106KA37	10uF	16	X7R	3225M/1210	2.2	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM32DR71E475KA55	4.7uF	25	X7R	3225M/1210	2.2	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM32EC71E226KE35	22uF	25	X7S	3225M/1210	2.85	+/-10%	Powertrain/Safety for Automotive
GCM32EC71E226KE36	22uF	25	X7S	3225M/1210	2.85	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM32EC71H106KA01	10uF	50	X7S	3225M/1210	2.7	+/-10%	Powertrain/Safety for Automotive
GCM32EC71H106KA03	10uF	50	X7S	3225M/1210	2.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM32EC7YA106KA01	10uF	35	X7S	3225M/1210	2.7	+/-10%	Powertrain/Safety for Automotive
GCM32EC7YA106KA03	10uF	35	X7S	3225M/1210	2.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM32EL8EF226KE08	22uF	25	X8L	3225M/1210	2.85	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM32EL8EH106KA07	10uF	50	X8L	3225M/1210	2.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM32ER70J476KE16	47uF	6.3	X7R	3225M/1210	2.7	+/-10%	Powertrain/Safety for Automotive
GCM32ER70J476ME16	47uF	6.3	X7R	3225M/1210	2.7	+/-20%	Powertrain/Safety for Automotive
GCM32ER70J476ME19	47uF	6.3	X7R	3225M/1210	2.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCM32ER71A226KE12	22uF	10	X7R	3225M/1210	2.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM32ER71A226ME12	22uF	10	X7R	3225M/1210	2.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCM32ER71C226ME15	22uF	16	X7R	3225M/1210	2.7	+/-20%	Powertrain/Safety for Automotive
GCM32ER71C226ME19	22uF	16	X7R	3225M/1210	2.7	+/-20%	Powertrain/Safety for Automotive [AEC-Q200]
GCM32ER71E106KA42	10uF	25	X7R	3225M/1210	2.7	+/-10%	Powertrain/Safety for Automotive
GCM32ER71E106KA57	10uF	25	X7R	3225M/1210	2.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM32ER71H105KA37	1uF	50	X7R	3225M/1210	2.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GCM32ER71H475KA40	4.7uF	50	X7R	3225M/1210	2.7	+/-10%	Powertrain/Safety for Automotive
GCM32ER71H475KA55	4.7uF	50	X7R	3225M/1210	2.7	+/-10%	Powertrain/Safety for Automotive [AEC-Q200]
GGD188R71E273KA02	27000pF	25	X7R	1608M/0603	0.9	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD188R71E333KA02	33000pF	25	X7R	1608M/0603	0.9	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD188R71E393KA02	39000pF	25	X7R	1608M/0603	0.9	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD188R71E473KA02	47000pF	25	X7R	1608M/0603	0.9	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD188R71H103KA02	10000pF	50	X7R	1608M/0603	0.9	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD188R71H123KA02	12000pF	50	X7R	1608M/0603	0.9	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD188R71H153KA02	15000pF	50	X7R	1608M/0603	0.9	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD188R71H183KA02	18000pF	50	X7R	1608M/0603	0.9	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD188R71H223KA02	22000pF	50	X7R	1608M/0603	0.9	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD188R71H562KA02	5600pF	50	X7R	1608M/0603	0.9	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD188R71H682KA02	6800pF	50	X7R	1608M/0603	0.9	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD188R71H822KA02	8200pF	50	X7R	1608M/0603	0.9	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD188R72A103KA02	10000pF	100	X7R	1608M/0603	0.9	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD188R72A123KA02	12000pF	100	X7R	1608M/0603	0.9	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD188R72A153KA02	15000pF	100	X7R	1608M/0603	0.9	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD188R72A183KA02	18000pF	100	X7R	1608M/0603	0.9	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD188R72A223KA02	22000pF	100	X7R	1608M/0603	0.9	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD188R72A562KA02	5600pF	100	X7R	1608M/0603	0.9	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD188R72A682KA02	6800pF	100	X7R	1608M/0603	0.9	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD188R72A822KA02	8200pF	100	X7R	1608M/0603	0.9	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD21BR71H104KA02	0.1uF	50	X7R	2012M/0805	1.4	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD21BR71H153KA02	15000pF	50	X7R	2012M/0805	1.4	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD21BR71H183KA02	18000pF	50	X7R	2012M/0805	1.4	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD21BR71H223KA02	22000pF	50	X7R	2012M/0805	1.4	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD21BR71H273KA02	27000pF	50	X7R	2012M/0805	1.4	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD21BR71H333KA02	33000pF	50	X7R	2012M/0805	1.4	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD21BR71H393KA02	39000pF	50	X7R	2012M/0805	1.4	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD21BR71H473KA02	47000pF	50	X7R	2012M/0805	1.4	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD21BR71H563KA02	56000pF	50	X7R	2012M/0805	1.4	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD21BR71H683KA02	68000pF	50	X7R	2012M/0805	1.4	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD21BR71H823KA02	82000pF	50	X7R	2012M/0805	1.4	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD21BR72A104KA02	0.1uF	100	X7R	2012M/0805	1.4	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD21BR72A153KA02	15000pF	100	X7R	2012M/0805	1.4	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD21BR72A183KA02	18000pF	100	X7R	2012M/0805	1.4	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD21BR72A223KA02	22000pF	100	X7R	2012M/0805	1.4	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD21BR72A273KA02	27000pF	100	X7R	2012M/0805	1.4	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GGD21BR72A333KA02	33000pF	100	X7R	2012M/0805	1.4	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD21BR72A393KA02	39000pF	100	X7R	2012M/0805	1.4	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD21BR72A473KA02	47000pF	100	X7R	2012M/0805	1.4	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD21BR72A563KA02	56000pF	100	X7R	2012M/0805	1.4	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD21BR72A683KA02	68000pF	100	X7R	2012M/0805	1.4	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GGD21BR72A823KA02	82000pF	100	X7R	2012M/0805	1.4	+/-10%	Water repellent MLSC design/ Automotive [AEC-Q200]
GRT033C80G104KE01	0.1uF	4	X6S	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033C80G224ME01	0.22uF	4	X6S	0603M/0201	0.33	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT033C80J103KE01	10000pF	6.3	X6S	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033C80J104KE01	0.1uF	6.3	X6S	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033C80J153KE01	15000pF	6.3	X6S	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033C80J153ME01	15000pF	6.3	X6S	0603M/0201	0.33	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT033C80J222KE01	2200pF	6.3	X6S	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033C80J223KE01	22000pF	6.3	X6S	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033C80J223ME01	22000pF	6.3	X6S	0603M/0201	0.33	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT033C80J224KE01	0.22uF	6.3	X6S	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033C80J224ME01	0.22uF	6.3	X6S	0603M/0201	0.33	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT033C80J333KE01	33000pF	6.3	X6S	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033C80J333ME01	33000pF	6.3	X6S	0603M/0201	0.33	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT033C80J472KE01	4700pF	6.3	X6S	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033C80J473KE01	47000pF	6.3	X6S	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033C80J473ME01	47000pF	6.3	X6S	0603M/0201	0.33	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT033C81A104KE01	0.1uF	10	X6S	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033C81C104KE01	0.1uF	16	X6S	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033C81C104ME01	0.1uF	16	X6S	0603M/0201	0.33	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT033C81E102KE01	1000pF	25	X6S	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033C81E104KE01	0.1uF	25	X6S	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033C81E104ME01	0.1uF	25	X6S	0603M/0201	0.33	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT033C81E471KE01	470pF	25	X6S	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R60G105ME13	1uF	4	X5R	0603M/0201	0.35	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT033R60J103KE01	10000pF	6.3	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R60J104KE01	0.1uF	6.3	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R60J105ME13	1uF	6.3	X5R	0603M/0201	0.35	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT033R60J153KE01	15000pF	6.3	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R60J223KE01	22000pF	6.3	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R60J224KE01	0.22uF	6.3	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R60J333KE01	33000pF	6.3	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R60J473KE01	47000pF	6.3	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R60J474KE01	0.47uF	6.3	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R61A103KE01	10000pF	10	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R61A104KE01	0.1uF	10	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R61A222KE01	2200pF	10	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R61A223KE01	22000pF	10	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R61A224KE01	0.22uF	10	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R61A224ME01	0.22uF	10	X5R	0603M/0201	0.33	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT033R61A472KE01	4700pF	10	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R61A473KE01	47000pF	10	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R61C103KE01	10000pF	16	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R61C104KE01	0.1uF	16	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R61C223KE01	22000pF	16	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R61C473KE01	47000pF	16	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R61E101KE01	100pF	25	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R61E102KE01	1000pF	25	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R61E103KE01	10000pF	25	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R61E104KE01	0.1uF	25	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R61E221KE01	220pF	25	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R61E471KE01	470pF	25	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R61E472KE01	4700pF	25	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R61E473KE01	47000pF	25	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R61E104KE01	0.1uF	35	X5R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R70J103KE01	10000pF	6.3	X7R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R70J222KE01	2200pF	6.3	X7R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R70J472KE01	4700pF	6.3	X7R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R71A103KE01	10000pF	10	X7R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R71E102KE01	1000pF	25	X7R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT033R71E471KE01	470pF	25	X7R	0603M/0201	0.33	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155C71A105KE13	1uF	10	X7S	1005M/0402	0.6	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155C71A225KE13	2.2uF	10	X7S	1005M/0402	0.7	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155C80E106ME13	10uF	2.5	X6S	1005M/0402	0.7	+/-20%	Infotainment for Automotive [AEC-Q200]

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRT155C80J105KE01	1uF	6.3	X6S	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155C80J224KE01	0.22uF	6.3	X6S	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155C80J224ME01	0.22uF	6.3	X6S	1005M/0402	0.55	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155C80J225KE01	2.2uF	6.3	X6S	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155C80J225ME01	2.2uF	6.3	X6S	1005M/0402	0.55	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155C80J334KE01	0.33uF	6.3	X6S	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155C80J334ME01	0.33uF	6.3	X6S	1005M/0402	0.55	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155C80J474KE01	0.47uF	6.3	X6S	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155C80J474ME01	0.47uF	6.3	X6S	1005M/0402	0.55	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155C80J475ME13	4.7uF	6.3	X6S	1005M/0402	0.65	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155C81A105KE01	1uF	10	X6S	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155C81A225KE13	2.2uF	10	X6S	1005M/0402	0.7	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155C81A225ME13	2.2uF	10	X6S	1005M/0402	0.7	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155C81C105KE13	1uF	16	X6S	1005M/0402	0.6	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155C81C105ME13	1uF	16	X6S	1005M/0402	0.6	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155C81C225KE13	2.2uF	16	X6S	1005M/0402	0.7	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155C81C225ME13	2.2uF	16	X6S	1005M/0402	0.7	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155C81C474KE01	0.47uF	16	X6S	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155C81C474ME01	0.47uF	16	X6S	1005M/0402	0.55	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155C81E105KE13	1uF	25	X6S	1005M/0402	0.6	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155C81E105ME13	1uF	25	X6S	1005M/0402	0.6	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155C81E224KE01	0.22uF	25	X6S	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155C81E224ME01	0.22uF	25	X6S	1005M/0402	0.55	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155C8YA224KE01	0.22uF	35	X6S	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155C8YA224ME01	0.22uF	35	X6S	1005M/0402	0.55	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155R60G475ME13	4.7uF	4	X5R	1005M/0402	0.6	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155R60J105KE01	1uF	6.3	X5R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R60J224KE01	0.22uF	6.3	X5R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R60J224ME01	0.22uF	6.3	X5R	1005M/0402	0.55	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155R60J225KE01	2.2uF	6.3	X5R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R60J225ME01	2.2uF	6.3	X5R	1005M/0402	0.55	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155R60J334KE01	0.33uF	6.3	X5R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R60J334ME01	0.33uF	6.3	X5R	1005M/0402	0.55	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155R60J474KE01	0.47uF	6.3	X5R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R60J474ME01	0.47uF	6.3	X5R	1005M/0402	0.55	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155R60J475ME13	4.7uF	6.3	X5R	1005M/0402	0.6	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155R60J684KE01	0.68uF	6.3	X5R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R60J684ME01	0.68uF	6.3	X5R	1005M/0402	0.55	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155R61A105KE01	1uF	10	X5R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R61A224KE01	0.22uF	10	X5R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R61A224ME01	0.22uF	10	X5R	1005M/0402	0.55	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155R61A225KE01	2.2uF	10	X5R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R61A225ME01	2.2uF	10	X5R	1005M/0402	0.55	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155R61A334KE01	0.33uF	10	X5R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R61A334ME01	0.33uF	10	X5R	1005M/0402	0.55	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155R61A474KE01	0.47uF	10	X5R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R61A474ME01	0.47uF	10	X5R	1005M/0402	0.55	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155R61A475ME13	4.7uF	10	X5R	1005M/0402	0.65	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155R61A684KE01	0.68uF	10	X5R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R61A684ME01	0.68uF	10	X5R	1005M/0402	0.55	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155R61C105KE01	1uF	16	X5R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R61C224KE01	0.22uF	16	X5R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R61C225KE13	2.2uF	16	X5R	1005M/0402	0.7	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R61C474KE01	0.47uF	16	X5R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R61C474ME01	0.47uF	16	X5R	1005M/0402	0.55	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155R61E105KE01	1uF	25	X5R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R61E224KE01	0.22uF	25	X5R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R61E224ME01	0.22uF	25	X5R	1005M/0402	0.55	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155R61E225KE13	2.2uF	25	X5R	1005M/0402	0.7	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R61E474KE01	0.47uF	25	X5R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R61E474ME01	0.47uF	25	X5R	1005M/0402	0.55	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155R6YA105KE13	1uF	35	X5R	1005M/0402	0.6	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R6YA105ME13	1uF	35	X5R	1005M/0402	0.6	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155R6YA224KE01	0.22uF	35	X5R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R6YA224ME01	0.22uF	35	X5R	1005M/0402	0.55	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155R6YA474KE01	0.47uF	35	X5R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R6YA474ME01	0.47uF	35	X5R	1005M/0402	0.55	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT155R70G105KE01	1uF	4	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRT155R70J105KE01	1uF	6.3	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R70J223KE01	22000pF	6.3	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R71A224KE01	0.22uF	10	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R71A474KE01	0.47uF	10	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R71C103KE01	10000pF	16	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R71C104KE01	0.1uF	16	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R71C223KE01	22000pF	16	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R71C224KE01	0.22uF	16	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R71C473KE01	47000pF	16	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R71E103KE01	10000pF	25	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R71E104KE01	0.1uF	25	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R71E223KE01	22000pF	25	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R71E473KE01	47000pF	25	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R71H102KE01	1000pF	50	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R71H103KE01	10000pF	50	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R71H104KE01	0.1uF	50	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R71H221KE01	220pF	50	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R71H222KE01	2200pF	50	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R71H223KE01	22000pF	50	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R71H471KE01	470pF	50	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R71H472KE01	4700pF	50	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT155R71H473KE01	47000pF	50	X7R	1005M/0402	0.55	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188C80G105ME01	1uF	4	X6S	1608M/0603	0.9	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188C80G106ME13	10uF	4	X6S	1608M/0603	0.9	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188C80G226ME13	22uF	4	X6S	1608M/0603	1.0	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188C80G475KE01	4.7uF	4	X6S	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188C80G475ME01	4.7uF	4	X6S	1608M/0603	0.9	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188C80J226ME13	22uF	6.3	X6S	1608M/0603	1.0	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188C80J475KE01	4.7uF	6.3	X6S	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188C80J475ME01	4.7uF	6.3	X6S	1608M/0603	0.9	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188C81A105KE13	1uF	10	X6S	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188C81A106ME13	10uF	10	X6S	1608M/0603	1.0	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188C81C105KE13	1uF	16	X6S	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188C81C106ME13	10uF	16	X6S	1608M/0603	1.0	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188C81C225KE13	2.2uF	16	X6S	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188C81C475KE13	4.7uF	16	X6S	1608M/0603	0.95	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188C81C475ME13	4.7uF	16	X6S	1608M/0603	0.95	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188C81E105KE13	1uF	25	X6S	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188C81E225KE13	2.2uF	25	X6S	1608M/0603	1.0	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188C81E225ME13	2.2uF	25	X6S	1608M/0603	1.0	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188C81E475KE13	4.7uF	25	X6S	1608M/0603	1.0	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188C81E475ME13	4.7uF	25	X6S	1608M/0603	1.0	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188C8YA105KE13	1uF	35	X6S	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188C8YA225KE13	2.2uF	35	X6S	1608M/0603	1.0	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188R60G106ME13	10uF	4	X5R	1608M/0603	0.9	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188R60J105KE01	1uF	6.3	X5R	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188R60J105ME01	1uF	6.3	X5R	1608M/0603	0.9	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188R60J106ME13	10uF	6.3	X5R	1608M/0603	0.9	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188R60J225KE13	2.2uF	6.3	X5R	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188R60J226ME13	22uF	6.3	X5R	1608M/0603	1.0	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188R60J475KE01	4.7uF	6.3	X5R	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188R61A105KE01	1uF	10	X5R	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188R61A105ME01	1uF	10	X5R	1608M/0603	0.9	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188R61A106KE13	10uF	10	X5R	1608M/0603	0.95	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188R61A106ME13	10uF	10	X5R	1608M/0603	0.95	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188R61A225KE13	2.2uF	10	X5R	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188R61A226ME13	22uF	10	X5R	1608M/0603	1.0	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188R61C105KE13	1uF	16	X5R	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188R61C106KE13	10uF	16	X5R	1608M/0603	0.95	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188R61C106ME13	10uF	16	X5R	1608M/0603	0.95	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188R61C475KE13	4.7uF	16	X5R	1608M/0603	0.95	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188R61C475ME13	4.7uF	16	X5R	1608M/0603	0.95	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188R61E105KE13	1uF	25	X5R	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188R61E106ME13	10uF	25	X5R	1608M/0603	1.0	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188R61E225KE13	2.2uF	25	X5R	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188R61E475KE13	4.7uF	25	X5R	1608M/0603	0.95	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188R61E475ME13	4.7uF	25	X5R	1608M/0603	0.95	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188R61H105KE13	1uF	50	X5R	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRT188R61H225KE13	2.2uF	50	X5R	1608M/0603	1.0	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188R61H225ME13	2.2uF	50	X5R	1608M/0603	1.0	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188R6YA105KE13	1uF	35	X5R	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188R6YA225KE13	2.2uF	35	X5R	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188R6YA475KE13	4.7uF	35	X5R	1608M/0603	1.0	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188R6YA475ME13	4.7uF	35	X5R	1608M/0603	1.0	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT188R70J225KE13	2.2uF	6.3	X7R	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188R71C105KE13	1uF	16	X7R	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188R71E105KE13	1uF	25	X7R	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188R71E224KE01	0.22uF	25	X7R	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188R71H104KE13	0.1uF	50	X7R	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT188R71H473KE01	47000pF	50	X7R	1608M/0603	0.9	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BC71E106KE13	10uF	25	X7S	2012M/0805	1.45	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BC80G476ME13	47uF	4	X6S	2012M/0805	1.45	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT21BC81A106KE01	10uF	10	X6S	2012M/0805	1.35	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BC81A226ME13	22uF	10	X6S	2012M/0805	1.45	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT21BC81C106KE01	10uF	16	X6S	2012M/0805	1.35	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BC81C225KA02	2.2uF	16	X6S	2012M/0805	1.35	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BC81C475KA02	4.7uF	16	X6S	2012M/0805	1.35	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BC81E105KE13	1uF	25	X6S	2012M/0805	1.4	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BC81E225KA02	2.2uF	25	X6S	2012M/0805	1.35	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BC81E475KA02	4.7uF	25	X6S	2012M/0805	1.35	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BC8YA225KE13	2.2uF	35	X6S	2012M/0805	1.4	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BC8YA475KE13	4.7uF	35	X6S	2012M/0805	1.4	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BR60J106KE01	10uF	6.3	X5R	2012M/0805	1.35	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BR60J226ME13	22uF	6.3	X5R	2012M/0805	1.4	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT21BR60J475KE13	4.7uF	6.3	X5R	2012M/0805	1.4	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BR61A106KE01	10uF	10	X5R	2012M/0805	1.35	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BR61A226ME13	22uF	10	X5R	2012M/0805	1.4	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT21BR61A475KE13	4.7uF	10	X5R	2012M/0805	1.4	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BR61C106KE01	10uF	16	X5R	2012M/0805	1.35	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BR61C225KA02	2.2uF	16	X5R	2012M/0805	1.35	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BR61C226ME13	22uF	16	X5R	2012M/0805	1.45	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT21BR61C475KA02	4.7uF	16	X5R	2012M/0805	1.35	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BR61E106KE13	10uF	25	X5R	2012M/0805	1.4	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BR61E225KA02	2.2uF	25	X5R	2012M/0805	1.35	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BR61E226ME13	22uF	25	X5R	2012M/0805	1.45	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT21BR61E475KA02	4.7uF	25	X5R	2012M/0805	1.35	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BR61H225KE13	2.2uF	50	X5R	2012M/0805	1.4	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BR61H475KE13	4.7uF	50	X5R	2012M/0805	1.4	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BR70J106KE13	10uF	6.3	X7R	2012M/0805	1.4	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BR71A106KE13	10uF	10	X7R	2012M/0805	1.4	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BR71A475KE13	4.7uF	10	X7R	2012M/0805	1.4	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BR71C225KE01	2.2uF	16	X7R	2012M/0805	1.35	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BR71C475KE13	4.7uF	16	X7R	2012M/0805	1.4	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BR71E105KE13	1uF	25	X7R	2012M/0805	1.4	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BR71E225KE13	2.2uF	25	X7R	2012M/0805	1.4	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BR71H105KE01	1uF	50	X7R	2012M/0805	1.35	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT21BR71H474KE01	0.47uF	50	X7R	2012M/0805	1.35	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CC80G226KE01	22uF	4	X6S	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CC80G476ME01	47uF	4	X6S	3216M/1206	1.8	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT31CC80J226KE01	22uF	6.3	X6S	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CC80J476KE13	47uF	6.3	X6S	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CC81A106KE01	10uF	10	X6S	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CC81A106ME01	10uF	10	X6S	3216M/1206	1.8	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT31CC81A226KE01	22uF	10	X6S	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CC81C106KE01	10uF	16	X6S	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CC81C106ME01	10uF	16	X6S	3216M/1206	1.8	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT31CC81C226KE01	22uF	16	X6S	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CC81C475KE01	4.7uF	16	X6S	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CC81C475ME01	4.7uF	16	X6S	3216M/1206	1.8	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT31CC81E106KE01	10uF	25	X6S	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CC81E475KE01	4.7uF	25	X6S	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CC81H225KE01	2.2uF	50	X6S	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CC8YA106KE01	10uF	35	X6S	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CC8YA106ME01	10uF	35	X6S	3216M/1206	1.8	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT31CR60J226KE01	22uF	6.3	X5R	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CR60J476KE13	47uF	6.3	X5R	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GRT31CR61A106KE01	10uF	10	X5R	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CR61A226KE01	22uF	10	X5R	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CR61A476KE13	47uF	10	X5R	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CR61C106KE01	10uF	16	X5R	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CR61C226KE01	22uF	16	X5R	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CR61C475KE01	4.7uF	16	X5R	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CR61C475ME01	4.7uF	16	X5R	3216M/1206	1.8	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT31CR61E106KE01	10uF	25	X5R	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CR61E106ME01	10uF	25	X5R	3216M/1206	1.8	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT31CR61E226KE01	22uF	25	X5R	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CR61E335KE01	3.3uF	25	X5R	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CR61E475KE01	4.7uF	25	X5R	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CR61H106KE01	10uF	50	X5R	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CR61H225KE01	2.2uF	50	X5R	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CR6YA106KE01	10uF	35	X5R	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CR6YA106ME01	10uF	35	X5R	3216M/1206	1.8	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT31CR70J226KE13	22uF	6.3	X7R	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CR71E106KE13	10uF	25	X7R	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT31CR71H225KE13	2.2uF	50	X7R	3216M/1206	1.8	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT32DC81A106KE01	10uF	10	X6S	3225M/1210	2.2	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT32DC81C106KE01	10uF	16	X6S	3225M/1210	2.2	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT32DC81E106KE01	10uF	25	X6S	3225M/1210	2.2	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT32DR60J336ME01	33uF	6.3	X5R	3225M/1210	2.2	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT32DR61C106KE01	10uF	16	X5R	3225M/1210	2.2	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT32DR61E106KE01	10uF	25	X5R	3225M/1210	2.2	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT32DR61E106ME01	10uF	25	X5R	3225M/1210	2.2	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT32EC80J476KE13	47uF	6.3	X6S	3225M/1210	2.7	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT32EC81A226ME13	22uF	10	X6S	3225M/1210	2.7	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT32EC81A476KE13	47uF	10	X6S	3225M/1210	2.7	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT32EC81C476KE13	47uF	16	X6S	3225M/1210	2.7	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT32EC81H475KE01	4.7uF	50	X6S	3225M/1210	2.7	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT32ER60J107ME13	100uF	6.3	X5R	3225M/1210	2.7	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT32ER61C226ME13	22uF	16	X5R	3225M/1210	2.7	+/-20%	Infotainment for Automotive [AEC-Q200]
GRT32ER61E226KE13	22uF	25	X5R	3225M/1210	2.7	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT32ER61H475KE01	4.7uF	50	X5R	3225M/1210	2.7	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT32ER70J476KE13	47uF	6.3	X7R	3225M/1210	2.7	+/-10%	Infotainment for Automotive [AEC-Q200]
GRT32ER71H475KE01	4.7uF	50	X7R	3225M/1210	2.7	+/-10%	Infotainment for Automotive [AEC-Q200]
GXT155C80J224KE01	0.22uF	6.3	X6S	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155C80J224ME01	0.22uF	6.3	X6S	1005M/0402	0.55	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155C80J334KE01	0.33uF	6.3	X6S	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155C80J334ME01	0.33uF	6.3	X6S	1005M/0402	0.55	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155C80J474KE01	0.47uF	6.3	X6S	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155C80J474ME01	0.47uF	6.3	X6S	1005M/0402	0.55	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155C81A105KE01	1uF	10	X6S	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155C81A225KE13	2.2uF	10	X6S	1005M/0402	0.7	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155C81A225ME13	2.2uF	10	X6S	1005M/0402	0.7	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155C81C105ME13	1uF	16	X6S	1005M/0402	0.6	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155C81C225KE13	2.2uF	16	X6S	1005M/0402	0.7	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155C81C225ME13	2.2uF	16	X6S	1005M/0402	0.7	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155C81C474KE01	0.47uF	16	X6S	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155C81C474ME01	0.47uF	16	X6S	1005M/0402	0.55	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155C81E105ME13	1uF	25	X6S	1005M/0402	0.6	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155C81E224KE01	0.22uF	25	X6S	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155C81E224ME01	0.22uF	25	X6S	1005M/0402	0.55	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155C8YA224KE01	0.22uF	35	X6S	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155C8YA224ME01	0.22uF	35	X6S	1005M/0402	0.55	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R60J105KE01	1uF	6.3	X5R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R60J224KE01	0.22uF	6.3	X5R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R60J224ME01	0.22uF	6.3	X5R	1005M/0402	0.55	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R60J334KE01	0.33uF	6.3	X5R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R60J334ME01	0.33uF	6.3	X5R	1005M/0402	0.55	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R60J474KE01	0.47uF	6.3	X5R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R60J474ME01	0.47uF	6.3	X5R	1005M/0402	0.55	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R60J684KE01	0.68uF	6.3	X5R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R60J684ME01	0.68uF	6.3	X5R	1005M/0402	0.55	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R61A105KE01	1uF	10	X5R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R61A224KE01	0.22uF	10	X5R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R61A224ME01	0.22uF	10	X5R	1005M/0402	0.55	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GXT155R61A334KE01	0.33uF	10	X5R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R61A334ME01	0.33uF	10	X5R	1005M/0402	0.55	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R61A474KE01	0.47uF	10	X5R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R61A474ME01	0.47uF	10	X5R	1005M/0402	0.55	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R61A684KE01	0.68uF	10	X5R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R61A684ME01	0.68uF	10	X5R	1005M/0402	0.55	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R61C105KE01	1uF	16	X5R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R61C224KE01	0.22uF	16	X5R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R61C225KE13	2.2uF	16	X5R	1005M/0402	0.7	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R61C474KE01	0.47uF	16	X5R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R61C474ME01	0.47uF	16	X5R	1005M/0402	0.55	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R61E105KE01	1uF	25	X5R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R61E224KE01	0.22uF	25	X5R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R61E224ME01	0.22uF	25	X5R	1005M/0402	0.55	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R61E225KE13	2.2uF	25	X5R	1005M/0402	0.7	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R61E474KE01	0.47uF	25	X5R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R61E474ME01	0.47uF	25	X5R	1005M/0402	0.55	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R6YA105KE13	1uF	35	X5R	1005M/0402	0.6	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R6YA105ME13	1uF	35	X5R	1005M/0402	0.6	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R6YA224KE01	0.22uF	35	X5R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R6YA224ME01	0.22uF	35	X5R	1005M/0402	0.55	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R6YA474KE01	0.47uF	35	X5R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R6YA474ME01	0.47uF	35	X5R	1005M/0402	0.55	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R71A224KE01	0.22uF	10	X7R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R71A474KE01	0.47uF	10	X7R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R71C224KE01	0.22uF	16	X7R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R71C473KE01	47000pF	16	X7R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R71E104KE01	0.1uF	25	X7R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R71E473KE01	47000pF	25	X7R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R71H103KE01	10000pF	50	X7R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R71H104KE01	0.1uF	50	X7R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R71H223KE01	22000pF	50	X7R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT155R71H473KE01	47000pF	50	X7R	1005M/0402	0.55	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188C80G105ME01	1uF	4	X6S	1608M/0603	0.9	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188C80G106ME13	10uF	4	X6S	1608M/0603	0.9	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188C81A106ME13	10uF	10	X6S	1608M/0603	1.0	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188C81C106ME13	10uF	16	X6S	1608M/0603	1.0	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188C81C225KE13	2.2uF	16	X6S	1608M/0603	0.9	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188C81C475KE13	4.7uF	16	X6S	1608M/0603	0.95	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188C81C475ME13	4.7uF	16	X6S	1608M/0603	0.95	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188C81E225KE13	2.2uF	25	X6S	1608M/0603	1.0	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188C81E225ME13	2.2uF	25	X6S	1608M/0603	1.0	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188C81E475KE13	4.7uF	25	X6S	1608M/0603	1.0	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188C81E475ME13	4.7uF	25	X6S	1608M/0603	1.0	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188C8YA225KE13	2.2uF	35	X6S	1608M/0603	1.0	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R60G106ME13	10uF	4	X5R	1608M/0603	0.9	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R60J105KE01	1uF	6.3	X5R	1608M/0603	0.9	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R60J105ME01	1uF	6.3	X5R	1608M/0603	0.9	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R60J106ME13	10uF	6.3	X5R	1608M/0603	0.9	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R60J225KE13	2.2uF	6.3	X5R	1608M/0603	0.9	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R60J475KE01	4.7uF	6.3	X5R	1608M/0603	0.9	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R61A105KE01	1uF	10	X5R	1608M/0603	0.9	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R61A105ME01	1uF	10	X5R	1608M/0603	0.9	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R61A225KE13	2.2uF	10	X5R	1608M/0603	0.9	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R61C106ME13	10uF	16	X5R	1608M/0603	0.95	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R61C475KE13	4.7uF	16	X5R	1608M/0603	0.95	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R61C475ME13	4.7uF	16	X5R	1608M/0603	0.95	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R61E106ME13	10uF	25	X5R	1608M/0603	1.0	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R61E225KE13	2.2uF	25	X5R	1608M/0603	0.9	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R61E475KE13	4.7uF	25	X5R	1608M/0603	0.95	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R61E475ME13	4.7uF	25	X5R	1608M/0603	0.95	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R61H225KE13	2.2uF	50	X5R	1608M/0603	1.0	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R61H225ME13	2.2uF	50	X5R	1608M/0603	1.0	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R6YA225KE13	2.2uF	35	X5R	1608M/0603	0.9	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R6YA475KE13	4.7uF	35	X5R	1608M/0603	1.0	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R6YA475ME13	4.7uF	35	X5R	1608M/0603	1.0	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R70J225KE13	2.2uF	6.3	X7R	1608M/0603	0.9	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT188R71C105KE13	1uF	16	X7R	1608M/0603	0.9	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]

品番	静電容量 (公称値)	定格電圧 (V)	温度特性	Size Code (mm)/(inch)	T寸法 (mm Max.)	静電容量許容差	Type
GXT188R71E105KE13	1uF	25	X7R	1608M/0603	0.9	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT21BC81A226ME13	22uF	10	X6S	2012M/0805	1.45	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT21BR60J106KE01	10uF	6.3	X5R	2012M/0805	1.35	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT21BR61A106KE01	10uF	10	X5R	2012M/0805	1.35	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT21BR61C106KE01	10uF	16	X5R	2012M/0805	1.35	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT21BR61C226ME13	22uF	16	X5R	2012M/0805	1.45	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT21BR61E226ME13	22uF	25	X5R	2012M/0805	1.45	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT21BR71A106KE13	10uF	10	X7R	2012M/0805	1.4	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT21BR71A475KE13	4.7uF	10	X7R	2012M/0805	1.4	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT21BR71E225KE13	2.2uF	25	X7R	2012M/0805	1.4	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT21BR71H105KE01	1uF	50	X7R	2012M/0805	1.35	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT31CC81E106KE01	10uF	25	X6S	3216M/1206	1.8	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT31CC8YA106KE01	10uF	35	X6S	3216M/1206	1.8	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT31CC8YA106ME01	10uF	35	X6S	3216M/1206	1.8	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT31CR61E106KE01	10uF	25	X5R	3216M/1206	1.8	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT31CR61E106ME01	10uF	25	X5R	3216M/1206	1.8	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT31CR6YA106KE01	10uF	35	X5R	3216M/1206	1.8	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT31CR6YA106ME01	10uF	35	X5R	3216M/1206	1.8	+/-20%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT31CR70J226KE13	22uF	6.3	X7R	3216M/1206	1.8	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT31CR71E106KE13	10uF	25	X7R	3216M/1206	1.8	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT32DC81E106KE01	10uF	25	X6S	3225M/1210	2.2	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT32EC80J476KE13	47uF	6.3	X6S	3225M/1210	2.7	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT32EC81A476KE13	47uF	10	X6S	3225M/1210	2.7	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT32EC81C476KE13	47uF	16	X6S	3225M/1210	2.7	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]
GXT32ER70J476KE13	47uF	6.3	X7R	3225M/1210	2.7	+/-10%	Compliant water repellent/ Infotainment [AEC-Q200]

品番	インダクタンス (uH)	Sizecode (inch/mm)	T寸法 (mmMax.)	定格電流 (mA温度基準)	定格電流 (mAL変化基準)	直流抵抗 (ohmTyp.)	直流抵抗 (ohmMax.)
LQM18PN1R0MFH	1	0603/1608	0.95	1300	550	0.13	0.163
LQM18PN1R0MFR	1	0603/1608	0.95	950		0.2	0.25
LQM18PN1R0NC0	1	0603/1608	0.55	750		0.2	0.25
LQM18PN1R0NF0	1	0603/1608	0.95	600		0.28	0.35
LQM18PN1R5MFR	1.5	0603/1608	0.95	800		0.23	0.288
LQM18PN1R5NB0	1.5	0603/1608	0.4	600		0.35	0.438
LQM18PN1R5NC0	1.5	0603/1608	0.55	720		0.22	0.275
LQM18PN1R8NC0	1.8	0603/1608	0.55	700		0.24	0.3
LQM18PN2R2MDH	2.2	0603/1608	0.75	650	250	0.38	0.475
LQM18PN2R2MFH	2.2	0603/1608	0.95	700	300	0.38	0.475
LQM18PN2R2MFR	2.2	0603/1608	0.95	750		0.3	0.375
LQM18PN2R2NC0	2.2	0603/1608	0.55	700		0.24	0.3
LQM18PN2R5ND0	2.5	0603/1608	0.75	700		0.24	0.3
LQM18PN3R3MFR	3.3	0603/1608	0.95	700		0.35	0.438
LQM18PN4R7MFR	4.7	0603/1608	0.95	620		0.44	0.55
LQM18PNR22NFR	0.22	0603/1608	0.95	1250		0.11	0.138
LQM18PNR47NC0	0.47	0603/1608	0.55	850		0.15	0.1875
LQM18PNR47NFR	0.47	0603/1608	0.95	1100		0.15	0.188
LQM21PN1R0MC0	1	0805/2012	0.55	800		0.19	0.238
LQM21PN1R0MGH	1	0805/2012	1	1700	1100	0.08	0.1
LQM21PN1R0NGC	1	0805/2012	1	900		0.1	0.125
LQM21PN1R0NGR	1	0805/2012	1	1300		0.066	0.0825
LQM21PN1R5MC0	1.5	0805/2012	0.55	700		0.26	0.325
LQM21PN2R2MC0	2.2	0805/2012	0.55	600		0.34	0.425
LQM21PN2R2MGH	2.2	0805/2012	1	1300	450	0.125	0.156
LQM21PN2R2MGS	2.2	0805/2012	1	950		0.18	0.225
LQM21PN2R2NGC	2.2	0805/2012	1	800		0.23	0.288
LQM21PN3R3NG0	3.3	0805/2012	1	800		0.165	0.207
LQM21PN3R3NGR	3.3	0805/2012	1	1000		0.15	0.188
LQM21PN4R7MGS	4.7	0805/2012	1	750		0.29	0.363
LQM21PN4R7NGR	4.7	0805/2012	1	800		0.23	0.288
LQM21PNR47MC0	0.47	0805/2012	0.55	1100		0.12	0.15
LQM21PNR47MG0	0.47	0805/2012	1	1300		0.075	0.094
LQM21PNR54MG0	0.54	0805/2012	1	1300		0.075	0.094
LQM2HPN1R0MG0	1	1008/2520	1	1600		0.055	0.069
LQM2HPN1R0MGC	1	1008/2520	1	1500		0.08	0.1
LQM2HPN1R0MGH	1	1008/2520	1	2300	2000	0.05	0.063
LQM2HPN1R0MJ0	1	1008/2520	1.2	1500		0.09	0.113
LQM2HPN1R0MJC	1	1008/2520	1.2	1500		0.086	0.108
LQM2HPN1R0MJH	1	1008/2520	1.2	2300	2100	0.05	0.063
LQM2HPN1R5MG0	1.5	1008/2520	1	1500		0.07	0.088
LQM2HPN2R2MG0	2.2	1008/2520	1	1300		0.08	0.1
LQM2HPN2R2MGH	2.2	1008/2520	1	1500	1500	0.11	0.138
LQM2HPN2R2MGS	2.2	1008/2520	1	1100		0.18	0.225
LQM2HPN2R2MJ0	2.2	1008/2520	1.2	1000		0.12	0.15
LQM2HPN2R2MJH	2.2	1008/2520	1.2	1500	1400	0.11	0.138
LQM2HPN2R2NJC	2.2	1008/2520	1.2	1000		0.175	0.219
LQM2HPN3R3MG0	3.3	1008/2520	1	1200		0.1	0.125
LQM2HPN3R3MGC	3.3	1008/2520	1	1000		0.16	0.2
LQM2HPN3R3MGS	3.3	1008/2520	1	1050		0.21	0.263
LQM2HPN3R3MJ0	3.3	1008/2520	1.2	1000		0.12	0.15
LQM2HPN4R7MG0	4.7	1008/2520	1	1100		0.11	0.138
LQM2HPN4R7MGC	4.7	1008/2520	1	800		0.18	0.225
LQM2HPN4R7MGS	4.7	1008/2520	1	1000		0.25	0.313
LQM2HPNR47MG0	0.47	1008/2520	1	1800		0.04	0.05
LQM2HPNR47MGH	0.47	1008/2520	1	2600	4500	0.04	0.05
LQM2HPNR47MJH	0.47	1008/2520	1.2	2700	3200	0.037	0.046
LQM2HPNR56ME0	0.56	1008/2520	0.8	1500		0.06	0.075
LQM2HPNR68MGH	0.68	1008/2520	1	2300	3800	0.05	0.063
LQM2MPN1R0MGH	1	0806/2016	1	1900	2000	0.064	0.08
LQM2MPN1R0NG0	1	0806/2016	1	1400		0.085	0.107
LQM2MPN1R5MG0	1.5	0806/2016	1	1200		0.11	0.138
LQM2MPN1R5MGH	1.5	0806/2016	1	1500	1800	0.104	0.13
LQM2MPN2R2MG0	2.2	0806/2016	1	1200		0.11	0.138
LQM2MPN2R2MGH	2.2	0806/2016	1	1000	1300	0.21	0.263
LQM2MPN3R3NG0	3.3	0806/2016	1	1200		0.12	0.15
LQM2MPN4R7MG0	4.7	0806/2016	1	1100		0.14	0.175
LQM2MPNR16MGH	0.16	0806/2016	1	4000	5000	0.014	0.018

品番	インダクタンス (uH)	Sizecode (inch/mm)	T寸法 (mmMax.)	定格電流 (mA温度基準)	定格電流 (mAL変化基準)	直流抵抗 (ohmTyp.)	直流抵抗 (ohmMax.)
LQM2MPNR24MGH	0.24	0806/2016	1	3400	4800	0.02	0.025
LQM2MPNR33MGH	0.33	0806/2016	1	3100	3700	0.024	0.03
LQM2MPNR47MG0	0.47	0806/2016	1	1600		0.06	0.075
LQM2MPNR47MGH	0.47	0806/2016	1	2500	3400	0.037	0.046
LQM2MPNR68MGH	0.68	0806/2016	1	1900	3100	0.055	0.069
LQM31PN1R0M00	1	1206/3216	0.95	1200		0.12	0.15
LQM31PN1R0MC0	1	1206/3216	0.55	1100		0.14	0.175
LQM31PN1R5M00	1.5	1206/3216	0.95	1000		0.14	0.175
LQM31PN1R5MC0	1.5	1206/3216	0.55	1000		0.17	0.213
LQM31PN2R2M00	2.2	1206/3216	0.95	900		0.19	0.238
LQM31PN2R2MC0	2.2	1206/3216	0.55	900		0.25	0.313
LQM31PN3R3M00	3.3	1206/3216	0.95	800		0.24	0.3
LQM31PN4R7M00	4.7	1206/3216	0.95	700		0.3	0.375
LQM31PNR47M00	0.47	1206/3216	0.95	1400		0.07	0.0875
LQM31PNR47MC0	0.47	1206/3216	0.55	1300		0.085	0.107