Part Numbering

CERALOCK® (MHz)



Product ID

Product ID	
cs	Ceramic Resonators

2Frequency/Capacitance

Code	Frequency/Capacitance
Α	MHz without Built-in Capacitance
Т	MHz with Built-in Capacitance

3Structure/Size

Code	Structure/Size
LS	Round Lead Type
СС	Cap Chip Type
CR/CE/CG/NR/NE	Small-cap Chip Type
cv	Monolithic Chip Type
cw	Small Monolithic Chip Type

4 Nominal Center Frequency

Expressed by four-digit alphanumerics. The unit is in hertz (Hz). Decimal point is expressed by capital letter ${}^{\rm H}$."

5 Design

Code	Design
G	Thickness Shear mode
T/V	Thickness Expander mode
X	Thickness Expander mode (3rd overtone)

6 Initial Frequency Tolerance

Code	Initial Frequency Tolerance
5	±0.5%
3	±0.3%
2	±0.2%
1	±0.1%
Н	±0.07%

Load Capacity

Code	Load Capacity
1	5pF
2	10pF
3	15pF
4	22pF
5	33/39pF
6	47pF

8 Individual Specification

Code	Individual Specification
***	Four-digit alphanumerics express "Individual Specification."

"0000" or "-": Standard specification type.

Packaging

Code	Packaging
во	Bulk
A0	Radial Taping H₀=18mm
RO	Plastic Taping ø=180mm Reel
R1	Plastic Taping ø=330mm Reel

Radial taping is applied to lead type and plastic taping to chip type.