## Part Numbering

## NTC Thermistors for Inrush Current Suppression Lead Type

(Part Number)	NT PA7 160 L BM B0 <b>0 2 3 5 6</b>	
Product ID		
Product ID		
NT	NTC Thermistors	

## 2 Series

Code	Series	Nominal Body Diameter	
PA5	Inrush Current Suppression Lead Type	ø5mm	
PA6		ø6mm	
PA7		ø7mm	
PA9		ø9mm	
PAA		ø10mm	
PAD		ø13mm	
PAJ		ø18mm	
PAN		ø22mm	

#### 3Resistance

Expressed by three-digit alphanumerics. The unit is ohm ( $\Omega$ ). The first and second figures are significant digits, and the third figure expresses the number of zeros that follow the two figures. If there is a decimal point, it is expressed by the capital letter "**R**." In this case, all figures are significant digits.

Ex.	Code	Resistance
	3R0	3Ω
	100	10Ω

## **4**Resistance Tolerance

Code	Resistance Tolerance	
L	±15%	

#### Individual Specifications

The lead structure and other specifications are expressed by two-digit alphanumerics.

Code	Individual Specifications	Body Diameter
B1	Standard Type (Ammo Pack)	ø7mm, ø9mm
ВМ	Standard Type (Bulk)	ø7mm, ø9mm
D6	Standard Type (Ammo Pack)	ø10mm, ø13mm
DK	Standard (Bulk)	ø18mm, ø22mm
DN	Standard (Bulk)	ø10mm, ø13mm

#### 6 Packaging

Code	Packaging	
A0	Ammo Pack Taping	
B0	Bulk	

# muRata