Block Type EMIFIL BNX00 -11 Reference Specification

1. Scope

This reference specification applies to Block Type EMIFIL.

2. Rating

Customer Part Number	Murata Part Number	Rated Voltage V(DC)	Withstanding Voltage V(DC)	Rated Current A(DC)	Insulation Resistance MΩmin.	Voltage Drop mV max.	Insertion Loss dB min.
	BNX002-11	50	125	10	100	30	1 MHz to 1 GHz: 40
	BNX003-11	150	375	10	100	30	5 MHz to 1 GHz: 40
	BNX005-11	50	125	15	100	30	1 MHz to 1 GHz: 40

Operating Temperature
Storage Temperature

-40°C to +85°C -40°C to +85°C

3. Standard Testing Condition

<Unless otherwise specified> Temperature : Ordinary Temp. 15 °C to 35 °C Humidity : Ordinary Humidity 25 %(RH) to 85 %(RH)

å

5.0±0.5

0.8±0.1

2.5±0.2

∢

4. Style and Dimensions

3.5±1.0

2.5±0.2

2.5±0.2

12.0±0.5

7.5±0.2

<In case of doubt>

Temperature : 20 °C ± 2 °C Humidity : 60 %(RH) to 70 %(RH) Atmospheric pressure : 86 kPa to 106 kPa


Part Number	А	В	С
BNX002-11	18.0 max.	12.5 max.	(ø0.8)
BNX003-11	18.0 max.	12.5 max.	(ø0.8)
BNX005-11	18.0 max.	13.0 max.	(ø1.0)

(in mm)

*The upper one between the top of the case and the surface of the capacitor is adopted in the measurement of the height of the product.


Note) Although some part of the product surface seems to be white in some cases, do not care because it is the result of waxing process for humidity resistance improvement. This wax does not make bad affection to mechanical or electrical performance, reliability of the product.

• TERMINAL LAYOUT (BOTTOM FIGURE)




DIMENSIONS OF INSTALLATION HOLES

(front view)



• EQUIVALENT CIRCUIT



5. Marking

Filter shall be marked as follows.

muRata <	— Murata mark
BNX002-11-	- Part Number
	── Manufacturing Date (Ex.) 59 5 ··· 1995 (Last digit of the year)
	9 ··· September (Jan. to Sept. 1 ~ 9 (Oct. : O , Nov. : N , Dec, : D)

6. Electrical Performance

No.	Item	Specification	Test Method
6.1	Insulation Resistance	Meet item 2.	Measured at DC rated voltage between terminal $(1)(2)$ and $(3)(4)$. Time: 1 minute Suitable resistor: 1M Ω .
6.2	Withstanding Voltage	Filter shall be no failure.	Voltage shall be applied between terminal (1)(2) and terminal (3)(4). Time : 1 to 5 seconds. Charging current : 50 mA max.
6.3	Voltage Drop	Meet item 2.	Rated Current: 10 A (BNX002-11,BNX003-11) 15 A (BNX005-11) A (BNX005-11) (1) (2) Specimen (3) (4)
6.4	Insertion Loss	Meet item 2.	$\begin{array}{c c} & \overbrace{10\text{dB}}^{50\Omega} & \overbrace{10\text{dB}}^{1} & (1) & (2) & \overbrace{10\text{dB}}^{1} & 1\\ & \overbrace{10\text{dB}}^{\text{Attenuator}} & \overbrace{10\text{dB}}^{\text{Specimen}} & \overbrace{10\text{dB}}^$

7. Mechanical Performance

Ν	۱o.	Item	Specification	Test Method
7	7.1	Appearance and	Meet item 4.	Visual Inspection and measured with Slide
		Dimensions		Calipers.
7	7.2	Marking	Marking is able to be read easily.	It is inspected Visually.


No.	Item	Specification	Test Method
7.3	Vibration	Meet Table 1.	It shall be soldered on the substrate.
		Table 1_ Appearance No damaged	Range of Vibration Frequency : 10 to 2000 to 10Hz for 20 minutes
		Appearance No damaged Insulation 30 MΩ min.	Testing Time: A period of 2 hours in each of 3 Mutually perpendicular directions
		Dielectric No failure	(Total 6 hours) Double Amplitude: 1.5mm or acceleration 196m / s ²
		Insertion Loss Meet item 2.	Then measured after exposure in the room condition for 4 to 24 hours.
7.4	Solderability	Then the lead is covered with a continuous new solder coating at least 75% along the circumference of the immersed part.	Flux: Ethanol solution of rosin, 25(wt)% Pre-heat: 150 \pm 10 °C, 60 ~ 90 s Solder: Sn-3.0Ag-0.5Cu Solder Temperature: 245 \pm 5 °C Immersion Time: 2 \pm 0.5 seconds Immersion Time: 2 \pm 0.5 seconds Molten Solder
7.5	Resistance to soldering heat	Meet Table 1.	Flux : Ethanol solution of rosin, 25(wt)% Pre-heat: 150 ± 10 °C, 60 ~ 90 s Solder: Sn-3.0Ag-0.5Cu Solder Temperature: 270 ± 10 °C Immersion Time: 10s (+ 2s, - 0s) Then measure values after exposure in the room condition for 24 to 48 hours.
7.6	Resistance to soldering iron		Solder: Sn-3.0Ag-0.5Cu Tip Temperature: 350 ± 10 °C Time: 4 ± 1 s Then measure values after exposure in the room condition for 24 to 48 hours.

8. Environmental Performance

No.	Item	Specification	Test Method
8.1	Temperature Cycle	Meet Table 1.	 1 Cycle step: - 40 °C (+ 0°C , - 3°C) / 30 minutes step: Room Temperature / within 5 minutes. step: + 85 °C (+ 3°C , - 0°C) / 30 minutes step: Room Temperature / within 5 minutes. Total of 10 cycle Then measured after exposure in the room condition for 24 to 48 hours.
8.2	Humidity Life		Temperature: 40 ± 2 °C Humidity: 95 %(RH) Applying Voltage: Rated Voltage Time: 500 h (+ 24h , - 0h) Then measured after exposure in the room condition for 4 to 24 hours.
8.3	Heat Life		Temperature: 85 ± 2 °C Applying Voltage: Rated Voltage × 2 Time: 1000 h (+ 48h , - 0h) Then measured after exposure in the room condition for 24 to 48 hours.


9. Specification of Packaging

9.1.Packing Quantity



9.2. Packing Method

Styrene foam which have 50 pcs of the stuck products on are placed in an Individual packaging as 2 steps. A quantity in an Outer packaging is depending on a quantity of an order.



In some cases , omit the Buffer material and/or Corrugated cardboard.

9.3. Marking of packaging

(1) Individual packaing

The following items shall be marked on a label and the label is stuck on the Individual packaing.

Customer part number, MURATA part number, Inspection number(*1), RoHS discrimination(*2), Quantity, etc

*1) « Expression of Inspe	ction No. »		<u>0000</u>	$\times \times \times$	
		(1)	(2)	(3)	
(1) Factory Code					
(2) Date	First digit	: Ye	ear /Las	t digit of	f year
	Second digit	: M	onth / Jan	. to Sep	\rightarrow 1 to 9, Oct. to Dec. \rightarrow O,N,D
	Third, Fourth c	ligit : Da	ау		
(3) Serial No.		-	-		

*2) « Expression of RoHS discrimination » ROHS – \underline{Y} ($\underline{\Delta}$)


(1) (2)

- (1) RoHS regulation conformity parts.
- (2) MURATA classification number

(2) Marking for Outside package

The following items shall be marked on a label and the label is stuck on the outside package. Customer name, Purchasing Order Number, Customer Part Number, MURATA part number, RoHS discrimination(*2), Quantity, etc

9.4 Specification of Outer Case



	Outer Case Dimensions (mm)			Standard Individual package Quantity
_abel	W	D	Н	in Outer Case
	265	89	118	5

*Above Outer Case size is typical. It depends on a quantity of an order.

10. 🕂 Caution

10.1 Limitation of Applications

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life,body or property.

(1)Aircraft equipment (2)Aerospace equipment (3)Undersea equipment (4)Power plant control equipment
 (5)Medical equipment (6)Transportation equipment(automobiles,trains,ships,etc.) (7)Traffic signal equipment
 (8)Disaster prevention / crime prevention equipment (9)Data-processing equipment

(10)Applications of similar complexity or with reliability requirements comparable to the applications listed in the above

10.2 Corrosive gas

Please refrain from use since contact with environments with corrosive gases (sulfur gas [hydrogen sulfide, sulfur dioxide, etc.], chlorine, ammonia, etc.) or oils (cutting oil, silicone oil, etc.) that have come into contact with the previously stated corrosive gas environment will result in deterioration of product quality or an open from deterioration due to corrosion of product electrode, etc. We will not bear any responsibility for use under these environments.

11. Notice

11.1. Using the block type EMIFIL® (BNX) effectively

This product effectively prevents undesired radiation and external noise from going out / entering the circuit by grounding the high frequency components which cause noise problem. Therefore, grouding condition may affect on the performance of the filter and following attentions should be paid for effective use.

(1) Design maximized grounding area in the P.C. board, and grounding pattern for all the grounding terminals of the product to be connected.(Recommended to use our recommendation in this spec.)

(2) Minimize the distance between ground of the P.C. board and the ground plate of the product.

(Recommended to use through-hole connection

between grounding area both of component side and bottom side.

(3) Insert the terminals into the holes on P.C. board completely.

(4) Don't connect PSG terminal with CG terminal directly. (See the item 4. TERMINAL LAYOUT)

11.2. Self-heating

Though this product has a large rated current, the localized self-heating may be caused depending on soldering conditions. To avoid this, following attention should be paid.


(1) Use P.C. board with our recommendation on hole diameter / land pattern dimensions, mentioned in the right hand drawing, especially for 4 terminals which pass current. (2)Solder the terminals to the P.C.board with solder-cover area at least 90%. Otherwise, excess self-heating at connection between terminals and P.C. board may lead to smoke and / or fire of the product even when operating at rated current.


(3)After installing this product in your product, please make sure of the self-heating with the rated current.

[P.C. BOARD PATTERNS]

Use a bilateral P.C.board. Insert the BNX into the P.C.board until the root of the terminal is secured. then solder.

(1) COMPONENT SIDE VIEW (2) BOTTOM VIEW






11.3. Soldering

- (1) Flux, Solder
 - Rosin-based flux should be used.

Do not use strong acidic flux with halide content exceeding 0.2(wt)% (chlorine conversion value.) • Use Sn-3.0Ag-0.5Cu solder.

(2) Standard flow soldering profile.



- (3) Resistance to soldering iron goes in the following condition that tip temperature is 350 °C max. and soldering time is 5 s max.
- (4) Products and the leads should not be subjected to any mechanical stress during soldering process. (and also while subjected to the equivalent high temperature.)

11.4. Cleaning Conditions

Products shall be cleaned on the following conditions.

- (1) Cleaning temperature shall be limited to 60 °C max. (40 °C max. for IPA.)
- (2) Ultrasonic cleaning shall comply with the following conditions, with avoiding the resonance phenomenon at the mounted products and P.C.B.

Power : 20W / I max. Frequency : 28kHz to 40kHz Time : 5 minutes max.

- (3) Cleaner
 - 1.Cleaner • Isopropyl alcohol (IPA)
 - 2.Aqueous agent
 - PINE ALPHA ST-100S
- (4) There shall be no residual flux and residual cleaner after cleaning.
- In the case of using aqueous agent, products shall be dried completely after rinse with de-ionized water in order to remove the cleaner.
- (5) The surface of products may become dirty whitely after cleaning.
- But there is no deterioration on mechanical, electrical characteristics and reliability.
- (6) Other cleaning
 - Please contact us.

11.5. Operating Environment

- (1) Do not use products in the corrodible atmosphere such as acidic gases, alkaline gases, chlorine, sulfur gases, organic gases and etc.(the sea breeze, Cl2, H2S, NH3, SO2, NO2,etc)
- (2) Do not use products in the environment where water, oil or organic solvents may adhere to product.
- (3) Do not use products in the atmosphere where the temperature / humidity changes rapidly and it is easy to dew.

11.6. Storage condition

(1) Storage period

Use the products within 12 months after delivered.

Solderability should be checked if this period is exceeded.

- (2) Storage environment condition
 - · Products should be stored in the warehouse on the following conditions.
 - Temperature : -10 °C to +40 °C
 - Humidity : 15 % to 85% relative humidity No rapid change on temperature and humidity
 - Don't keep products in corrosive gases such as sulfur, chlorine gas or acid, or it may cause oxidization of electrode, resulting in poor solderability.
 - Products should be stored on the palette for the prevention of the influence from humidity, dust and so on.
 - Products should be stored in the warehouse without heat shock, vibration, direct sunlight and so on.
- (3) Delivery

Care should be taken when transporting or handling product to avoid excessive vibration or mechanical shock.



12. / Notes

- (1) Please make sure that your product has been evaluated in view of your specifications with our product being mounted to your product.
- (2) You are requested not to use our product deviating from the reference specifications.
- (3) The contents of this reference specification are subject to change without advance notice. Please approve our product specifications or transact the approval sheet for product specifications before ordering.