



FEATURES
Efficiency up to 80%
<ul> <li>Wide temperature performance at full</li> <li>1 Watt load, -40°C to 85°C</li> </ul>
Dual output from a single input rail
Industry standard pinout
Power sharing on output
1kVDC isolation 'Hi Pot Test'
■ 5V & 12V inputs
■ 5V, 9V, 12V & 15V outputs
Internal SMD construction
Fully encapsulated with toroidal magnetics
No external components required
MTTF up to 3.1 million hours

Pin compatible with NKA & MEA1 series

NMA1515DC

NMA1515SC

No electrolytic or tantalum capacitors

### DESCRIPTION

The NMA series of industrial temperature range DC-DC converters are the standard building blocks for on-board distributed power systems. They are ideally suited for providing dual rail supplies on primarily digital boards with the added benefit of galvanic isolation to reduce switching noise. All of the rated power may be drawn from a single pin provided the total load does not exceed 1 watt.

## NMA 5V, 12V & 15V Series

### Isolated 1W Dual Output DC-DC Converters

SELECTION G	UIDE								
Order Code	Nominal Input Voltage	Output Voltage	Output Current	Input Current at Rated Load	Efficiency	Isolation Capacitance	MTTF <sup>1</sup>	Package Style	Recommended Alternative
	V	V	mA	mA	%	pF	kHrs		-
			Recom	nendec	In Pr	oductic	n		
NMA0505DC	5	±5	±100	289	69	28	3103		
NMA0512DC	5	±12	±42	260	77	34	1579	DIP	
NMA0515DC	5	±15	±33	256	78	36	1065		
NMA0505SC	5	±5	±100	289	69	28	3103		
NMA0509SC	5	±9	±55	267	75	32	2257	CID	
NMA0512SC	5	±12	±42	260	77	34	1579	SIP	
NMA0515SC	5	±15	±33	256	78	36	1065		
NMA1205DC	12	±5	±100	120	69	33	2193		
NMA1212DC	12	±12	±42	111	75	55	1303	DIP	
NMA1215DC	12	±15	±33	110	76	54	932		
NMA1205SC	12	±5	±100	120	69	33	2193		
NMA1209SC	12	±9	±55	113	74	46	1734	SIP	
NMA1212SC	12	±12	±42	111	75	55	1303	SIF	
NMA1215SC	12	±15	±33	110	76	54	932		
				Discor	ntinuec				
NMA0509DC	5	±9	±55	267	75	32	2257		MEA1D0509S
NMA1209DC	12	±9	±55	113	74	46	1734	DIP	NKA1209SC
NMA1505DC	15	±5	±100	91	71	39	1941		Contact Murat
NMA1505SC	15	±5	±100	91	71	39	1941	SIP	Contact Murat
NMA1512DC	15	±12	±42	87	78	68	790	DIP	Contact Murat
NMA1512SC	15	±12	±42	87	78	68	790	SIP	MEA1D1512S

INPUT CHARACTE				
Parameter	Conditions	Min.	Тур.	Max.
	Continuous operation, 5V input types	4.5	5	5.5
Voltage range	Continuous operation, 12V input types	10.8	12	13.2
	Continuous operation, 15V input types	13.5	15	16.5
Reflected ripple curre	nt		20	40

84

84

80

84

84

DIP

NMV1515SC

MEA1D1515SC

Units

۷

mA p-p

GENERAL CHARACTE	RISTICS				
Parameter	Conditions	Min.	Тур.	Max.	Units
	5V input types		110		
Switching frequency	12V input types		140		kHz
	15V input types		90		





1. Calculated using MIL-HDBK-217FN2 calculation model with nominal input voltage at full load. All specifications typical at  $T_A=25^{\circ}$ C, nominal input voltage and rated output current unless otherwise specified.

www.murata.com

## NMA 5V, 12V & 15V Series

Isolated 1W Dual Output DC-DC Converters

Parameter	Conditions	Conditions			Max.	Units
Rated Power	T <sub>A</sub> =-40°C to 120°C, see derating			1	W	
Voltage Set Point Accuracy	See tolerance envelope					
Line regulation	High VIN to low VIN		1.0	1.2	%/%	
Load Regulation		5V output types		10	12.5	
	5V & 12V input 15V input	9V output types		9	10	.5 .0 %
		12V output types		6.5	7.5	
10% load to rated load		15V output types		6	7.0	
		5V output types		5.5	10	
		12V output types		2.6	3.0	3.0 3.0
		15V output types		2.3	3.0	
	BW=DC to 20MHz, 5V output type	S		10	20	
Disals and Nation	BW=DC to 20MHz, 9V output type		7	15		
Ripple and Noise <sup>1</sup>	BW=DC to 20MHz, 12V output typ	es		7.5	15	mV p-p
	BW=DC to 20MHz, 15V output typ	es		8	15	

ISOLATION CHARACTERISTICS	S				
Parameter	Conditions	Min.	Тур.	Max.	Units
Isolation test voltage	Flash tested for 1 second	1000			VDC
Resistance	Viso= 1000VDC		10		GΩ

TEMPERATURE CHARACTERIS	TICS				
Parameter	Conditions	Min.	Тур.	Max.	Units
Specification	All output types	-40		85	
Storage		-50		130	
	0505, 1205		33		°C
Case Temperature above ambient	0509, 0512, 0515, 1209, 1212, 1215		28		0
Case temperature above ambient	1505		26		
	1512, 1515		17		
Cooling	Free air convection				

ABSOLUTE MAXIMUM RATINGS	
Lead temperature 1.5mm from case for 10 seconds	260°C
Wave Solder	Wave Solder profile not to exceed the profile recommended in IEC 61760-1 Section 6.1.3. Please refer to <u>application notes</u> for further information.
Input voltage V <sub>IN</sub> , NMA05 types	7V
Input voltage VIN, NMA12 types	15V
Input voltage VIN, NMA15 types	18V

1. See Ripple & Noise characterisation method.

## NMA 5V, 12V & 15V Series

Isolated 1W Dual Output DC-DC Converters

### **TECHNICAL NOTES**

### **ISOLATION VOLTAGE**

'Hi Pot Test', 'Flash Tested', 'Withstand Voltage', 'Proof Voltage', 'Dielectric Withstand Voltage' & 'Isolation Test Voltage' are all terms that relate to the same thing, a test voltage, applied for a specified time, across a component designed to provide electrical isolation, to verify the integrity of that isolation.

Murata Power Solutions NMA series of DC-DC converters are all 100% production tested at their stated isolation voltage. This is 1kVDC for 1 second.

A question commonly asked is, "What is the continuous voltage that can be applied across the part in normal operation?"

For a part holding no specific agency approvals, such as the NMA series, both input and output should normally be maintained within SELV limits i.e. less than 42.4V peak, or 60VDC. The isolation test voltage represents a measure of immunity to transient voltages and the part should never be used as an element of a safety isolation system. The part could be expected to function correctly with several hundred volts offset applied continuously across the isolation barrier; but then the circuitry on both sides of the barrier must be regarded as operating at an unsafe voltage and further isolation/insulation systems must form a barrier between these circuits and any user-accessible circuitry according to safety standard requirements.

#### **REPEATED HIGH-VOLTAGE ISOLATION TESTING**


It is well known that repeated high-voltage isolation testing of a barrier component can actually degrade isolation capability, to a lesser or greater degree depending on materials, construction and environment. The NMA series has toroidal isolation transformers, with no additional insulation between primary and secondary windings of enamelled wire. While parts can be expected to withstand several times the stated test voltage, the isolation capability does depend on the wire insulation. Any material, including this enamel (typically polyurethane) is susceptible to eventual chemical degradation when subject to very high applied voltages thus implying that the number of tests should be strictly limited. We therefore strongly advise against repeated high voltage isolation testing, but if it is absolutely required, that the voltage be reduced by 20% from specified test voltage.

This consideration equally applies to agency recognised parts rated for better than functional isolation where the wire enamel insulation is always supplemented by a further insulation system of physical spacing or barriers.

### **RoHS COMPLIANT INFORMATION**



This series is compatible with RoHS soldering systems with a peak wave solder temperature of260°C for 10 seconds. Please refer to <u>application notes</u> for further information. The pin termination finish on the SIP package type is Tin Plate, Hot Dipped over Matte Tin with Nickel Preplate. The DIP types are Matte Tin over Nickel Preplate. Both types in this series are backward compatible with Sn/Pb soldering systems. For further information, please visit www.murata.com/en-global/products/power/rohs



## NMA 5V, 12V & 15V Series

Isolated 1W Dual Output DC-DC Converters


### CHARACTERISATION TEST METHODS

#### **Ripple & Noise Characterisation Method**

Ripple and noise measurements are performed with the following test configuration.

	1µF X7R multilayer ceramic capacitor, voltage rating to be a minimum of 3 times the output voltage of the DC-DC converter
C2	$10\mu$ F tantalum capacitor, voltage rating to be a minimum of 1.5 times the output voltage of the DC-DC converter with an ESR of less than $100m\Omega$ at $100$ kHz
C3	100nF multilayer ceramic capacitor, general purpose
R1	450Ω resistor, carbon film, $\pm$ 1% tolerance
R2	50Ω BNC termination
Г1	3T of the coax cable through a ferrite toroid
RLOAD	Resistive load to the maximum power rating of the DC-DC converter. Connections should be made via twisted wires
Measured value	es are multiplied by 10 to obtain the specified values.

Differential Mode Noise Test Schematic



### **APPLICATION NOTES**

#### Minimum load

The minimum load to meet datasheet specification is 10% of the full rated load across the specified input voltage range. Lower than 10% minimum loading will result in an increase in output voltage, which may rise to typically double the specified output voltage if the output load falls to less than 5%.

#### Capacitive loading and start up

Typical start up times for this series, with a typical input voltage rise time of 2.2 $\mu$ s and output capacitance of 10 $\mu$ F, are shown in the table below. The product series will start into a capacitance of 47 $\mu$ F with an increased start time, however, the maximum recommended output capacitance is 10 $\mu$ F.

	Start-up time		Start-up time	
	μs		μs	
0505xC	2018	NMA1212xC	9765	
509xC	6610	NMA1215xC	15980	
A0512xC	14520	NMA1505xC	1060	
0515xC	20200	NMA1512xC	1627	
A1205xC	1061	NMA1515xC	6275	
1209xC	3935			
				24
				Gini 5 V Ch2 5 V M 2.5ms Ch2 1 2

# NMA 5V, 12V & 15V Series

Isolated 1W Dual Output DC-DC Converters

### **APPLICATION NOTES (Continued)**


#### **Output Ripple Reduction**

By using the values of inductance and capacitance stated, the output ripple at the rated load is lowered to 5mV p-p max.

#### **Component selection**

Capacitor: It is required that the ESR (Equivalent Series Resistance) should be as low as possible, ceramic types are recommended. The voltage rating should be at least twice (except for 15V output), the rated output voltage of the DC-DC converter.

Inductor: The rated current of the inductor should not be less than that of the output of the DC-DC converter. At the rated current, the DC resistance of the inductor should be such that the voltage drop across the inductor is <2% of the rated voltage of the DC-DC converter. The SRF (Self Resonant Frequency) should be >20MHz.




		Inductor		Capacitor
	L, μΗ	SMD	Through Hole	C, µF
NMA0505xC	22	82223C	11R223C	2.2uF
NMA0509xC	100	82104C	11R104C	0.47uF
NMA0512xC	150	82154C	11R154C	0.33uF
NMA0515xC	220	82224C	11R224C	1uF
NMA1205xC	22	82223C	11R223C	2.2uF
NMA1209xC	47	82473C	11R473C	1uF
NMA1212xC	150	82154C	11R154C	0.33uF
NMA1215xC	220	82224C	11R224C	1uF
NMA1505xC	22	82223C	11R223C	2.2uF
NMA1512xC	150	82154C	11R154C	0.33uF
NMA1515xC	220	82224C	11R224C	2.2uF

# NMA 5V, 12V & 15V Series


Isolated 1W Dual Output DC-DC Converters

### **TOLERANCE ENVELOPES**

The voltage tolerance envelope shows typical load regulation characteristics for this product series. The tolerance envelope is the maximum output voltage variation due to changes in output loading.




### **TEMPERATURE DERATING GRAPH**




## NMA 5V, 12V & 15V Series

Isolated 1W Dual Output DC-DC Converters



## NMA 5V, 12V & 15V Series

Isolated 1W Dual Output DC-DC Converters



# NMA 5V, 12V & 15V Series

Isolated 1W Dual Output DC-DC Converters

#### DISCLAIMER

Unless otherwise stated in the datasheet, all products are designed for standard commercial and industrial applications and NOT for safety-critical and/or life-critical applications.

Particularly for safety-critical and/or life-critical applications, i.e. applications that may directly endanger or cause the loss of life, inflict bodily harm and/or loss or severe damage to equipment/property, and severely harm the environment, a prior explicit written approval from Murata is strictly required. Any use of Murata standard products for any safety-critical, life-critical or any related applications without any prior explicit written approval from Murata shall be deemed unauthorised use.

These applications include but are not limited to:

- Aircraft equipment
- Aerospace equipment
- Undersea equipment
- Power plant control equipment
- Medical equipment
- Transportation equipment (automobiles, trains, ships, etc.)
- Traffic signal equipment
- Disaster prevention / crime prevention equipment
- Data Processing equipment

Murata makes no express or implied warranty, representation, or guarantee of suitability, fitness for any particular use/purpose and/or compatibility with any application or device of the buyer, nor does Murata assume any liability whatsoever arising out of unauthorised use of any Murata product for the application of the buyer. The suitability, fitness for any particular use/purpose and/or compatibility of Murata product with any application or device of the buyer remain to be the responsibility and liability of the buyer.

Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm, and take appropriate remedial actions. Buyer will fully indemnify and hold Murata, its affiliated companies, and its representatives harmless against any damages arising out of unauthorised use of any Murata products in any safety-critical and/ or life-critical applications.

Remark: Murata in this section refers to Murata Manufacturing Company and its affiliated companies worldwide including, but not limited to, Murata Power Solutions.



This product is subject to the following <u>operating requirements</u> and the <u>Life and Safety Critical Application Sales Policy</u>: Refer to: https://www.murata.com/en-eu/products/power/requirements

Murata Power Solutions (Milton Keynes) Ltd. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not imply the granting of licenses to make, use, or sell equipment constructed in accordance therewith. Specifications are subject to change without notice. © 2023 Murata Power Solutions (Milton Keynes) Ltd.