


TZB4P300AB10R01

已经停产

RoHS

REACH

外观&形状



特点

1. Miniature rectangular shape: 4.0(W)x4.5(L)x3.0(H)mm.
2. Color coded case facilitates identification of capacitance range.
3. Designed for automatic placement in surface mount applications.
4. Designed to withstand flux baths and solder baths (with cover film type).
5. Can be temporarily attached to PCB with adhesives (Terminal style A and B).
6. Can be reflow and flow (with cover film type) soldering method.
7. Stable characteristics over a wide frequency range. (Resonant frequency: 1000MHz min. / 6pF)

包装信息

包装	规格	标准包装数量
R01	330mm压纹带	2500

注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。
2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，谨请核准其规格或者办理产品规格表。

TZB4P300AB10R01

规格

形状	SMD
工作温度范围	-25°C to 85°C
厚度	3mm
厚度公差	±0.2
额定电压	100Vdc
静电容量最小值(max.)	6.5pF
静电容量最大值	30pF
静电容量最大值公差	+50/-0%
调整方向	上方
温度特性	N1200±500ppm/°C
Q	300min. at 1MHz, Cmax
耐电压	220Vdc
绝缘电阻(min.)	10000MΩ
力矩	1.5 to 9.8mNm
定子/外壳颜色	Green
质量	0.15g


注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。


2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，谨请核准其规格或者办理产品规格表。

TZB4P300AB10R01

产品数据



结构



温度特性

注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。
2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，请确认其规格或者办理产品规格表。