

78602/8JC

目前生产

RoHS

用途

不能使用的用途	请务必确认并遵守“操作要求”。
可以使用的用途	民用设备,工业设备 针对上述用途所要求的性能、功能、质量、管理、安全性，请参照本网站及规格说明书等，并在确认实机性能与信赖性之后使用。

外观&形状



注意
1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。
2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，谨请核准其规格或者办理产品规格表。

78602/8JC

规格

Height (inch)	0.25inch
Height (mm)	6.35mm
Width (mm)	12.7mm
Depth (mm)	9mm
Mounting Option	Surface Mount
Turns Ratio (Pri)	1
Turns Ratio (Sec)	1
Turns Ratio (Sec2)	1
Turns Ratio	1 to 1 to 1
Primary Inductance Min. (μH)	970μH
Primary Constant, ET Min (Vμs)	15Vμs
Leakage Inductance Typ. (μH)	0.37μH
Primary DC Resistance Max. (Ω)	0.46Ω
Interwinding Capacitance Typ. (pF)	47pF
Isolation Voltage (V)	1000Vrms
Packaging style	Tube
Package weight (g)	1.1g
Package Qty.	50
Short Description	The 786J series surface mount general purpose pulse transformer
Description	The 786J series surface mount general purpose pulse transformer

Series	786J
Series Headline	Surface Mount General Purpose Pulse Transformers
Series Description	The 786J series is a comprehensive range of general purpose pulse transformers. Common applications include line coupling, matching or isolating. The devices can also be used in small isolated power supplies and also as commonmode chokes in filtering applications. For through hole variants please see 786 Series datasheet.

注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。

2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前， 谨请核准其规格或者办理产品规格表。