

# CSTNE16M0V51Z000R0


目前生产

推荐

RoHS

REACH

## 外观&形状



## 特点

MURATA's package technology expertise has enabled the development of the Chip CERALOCK(R) with built-in load capacitors.

High-density mounting is made possible by the small package and the elimination of the need for an external load capacitor.

### Features

1. Oscillation circuits do not require external load capacitors.
2. Available for a wide frequency range.
3. Extremely small and have a low profile.
4. No adjustment is necessary for oscillation circuits.
5. Available for a wide temperature range.
6. Stable supply is ensured due to not using precious metal(Palladium).

## 用途

其他用途	消费级/工业级
------	---------

## 包装信息

包装	规格	标准包装数量
R0	180mm压纹带	3000

### 注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。
2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，请核准其规格或者办理产品规格表。

# CSTNE16M0V51Z000R0

## 规格

产品型	陶瓷谐振器
系列名	CSTNE_V
频率	16.000MHz
频率公差	±0.50% max.
工作温度范围	-40°C~125°C
频率温度特性	±0.30% max.
频率老化	±0.20% max.
谐振电阻 (R1)	40Ω max.
内置负载电容(CL1/CL2)	5pF
形状	SMD
清洗	不支持
长x宽	3.2x1.3mm
质量	12.56mg

### 注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。
2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，请核准其规格或者办理产品规格表。