


SVM4A103A0L17B00

已经停产

RoHS

REACH

外观&形状



特点

- 1.It' s smallest in the world, therefore can be mounted everywhere!
- 2.To get precise control for even small size robot, portable gaming devise and so on.....
High reliability! High accuracy! Enhanced rotational life!
- 3.It' s very easy to use without electrical circuit.
- 4.Available for measuring an angle and amount of movement for narrow space!!

■Applications

- 1.Game controller
- 2.Headset
- 3.Robot
- 4.DSC switch

包装信息

包装	规格	标准包装数量
B00	散装袋	100

注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。

2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，谨请核准其规格或者办理产品规格表。

SVM4A103A0L17B00

规格

工作温度范围	-40°C to 85°C
形状	SMD
总电阻值	10kΩ
总电阻值公差	±30%
线性	±2%
有效旋转角度(标准值)	260°
电阻温度系数	±500ppm/°C
旋转寿命(max.)	1M cycles
力矩(max.)	6mN·m
额定电压	5Vdc
耐电压	250Vac, 1 min., Leakage current 50 micro A max.
绝缘电阻(min.)	100MΩ
绝缘电阻测量条件	250Vdc
质量	0.08g


注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。

2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，请核准其规格或者办理产品规格表。

SVM4A103A0L17B00

产品数据



结构

注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。
2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，谨请核准其规格或者办理产品规格表。