


PVG3G204C01B00

已经停产

RoHS

REACH

外观&形状



特点

1. Sealed construction protects the interior from dust and liquid, which achieves stable performance.
2. Driver plate with cross-slot is suitable for automatic adjustment.
3. Rotor with large diameter and deep groove improves driver insertion.
4. 3mm and 4mm land pattern can be used without change. (Gull-wing is suitable for 4mm size land pattern.)

包装信息

包装	规格	标准包装数量
B00	散装袋	500

注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。
2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，谨请核准其规格或者办理产品规格表。

PVG3G204C01B00

规格

额定功率	0.25W
形状	SMD
最大工作电压	200Vdc
调整方向	上方
尺寸	3mm
自动调整	Yes
调节转数(有效旋转角度)	1(210°±10°)
机械旋转角度	250+/-10 deg.
总电阻值	200kΩ
总电阻值公差	±20%
电阻温度系数	±150ppm/°C
电阻变化特性	B(Linear)
接触电阻变化	2% of total resistance value or 3ohm max., whichever is greater
剩余电阻	1% of total resistance value or 3ohm max., whichever is greater
力矩	4.9mN · m max.
额定功率测量条件	70°C
工作温度范围	-55°C to 125°C
质量	0.06g

注意

1.


本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。

2.

本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，谨请核准其规格或者办理产品规格表。

PVG3G204C01B00

产品数据



结构

注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。
2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，谨请核准其规格或者办理产品规格表。