

BLM18HG471SN1#

末尾的“#” 为包装规格代号。

目前生产

RoHS

REACH

< 品名（附包装代号）一览 >

BLM18HG471SN1B

BLM18HG471SN1D

BLM18HG471SN1J


用途

不能使用的用途	请务必确认并遵守“操作要求”。
可以使用的用途	民用设备、植入式、手术、自动输药应用 以外的医疗器械设备[GHTF A/B/C]、运 输、重工、商用能源相关应用除外的工业 设备 针对上述用途所要求的性能、功能、质 量、管理、安全性，请参照本网站及规格 说明书等，并在确认实机性能与信赖性之 后使用。
推荐使用的用途	民用设备

包装信息

包装	规格	标准包装数量
B	散装袋	1000
D	180mm纸带	4000
J	330mm纸带	10000

外观&形状



注意
1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。
2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，谨请核准其规格或者办理产品规格表。

BLM18HG471SN1#

末尾的“#”为包装规格代号。

特点

BLM18H/BLM18E series has a modified internal electrode structure, that minimizes stray capacitance and increases the effective frequency range.

Features (BLM18H series)

1. BLM18H series realizes high impedance at 1GHz and is suitable for noise suppression from 500MHz to GHz range. The impedance value of HG/HD-type is about three times as large as that of A/B-type at 1GHz, though the impedance characteristic of HG/HD-type is similar to A/B-type at 100MHz or less.
2. HG-type is effective in noise suppression in wide frequency range (several MHz to several GHz). HB/HD-type for high-speed signal line provides a sharper roll-off after the cut-off frequency. HK-type for digital interface and HE-type for optical pickup modules are effective in suppressing the ringing because resistance especially grows in the lower frequency.
3. The magnetic shielded structure minimizes crosstalk.

Features (BLM18E series)

1. Low DC Resistance and a large Rated Current are suitable for noise suppression of the driver circuit.
2. Excellent direct current characteristics
3. Thin type (t=0.5mm) is suitable for small and low profile equipment such as DSC, cellular phones.

注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。
2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，请核准其规格或者办理产品规格表。

BLM18HG471SN1#

末尾的 “#” 为包装规格代号。

规格

形状	SMD
长度	1.6mm
长度公差	±0.15mm
宽度	0.8mm
宽度公差	±0.15mm
厚度	0.8mm
厚度公差	±0.15mm
工作温度范围	-55°C to 125°C
质量(标准值)	0.005g
电路数目	1
额定电流(at 85°C)	200mA
额定电流(at 125°C)	200mA
直流电阻(max)	0.85Ω
阻抗(at 100MHz)	470Ω
阻抗(at 100MHz)公差	±25%
阻抗(at 1GHz)	600Ω
阻抗(at 1GHz)公差	(Typ.)
尺寸代码(单位为mm)	1608

注意


1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。

2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前， 谨请核准其规格或者办理产品规格表。


BLM18HG471SN1#

末尾的“#”为包装规格代号。

产品数据



阻抗-频率特性



等效电路

注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。
2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，请核准其规格或者办理产品规格表。