



## Reliability Test Results

P/N : ECASD60D477M006K00 (2V/470uF/6mohm)




All measurement data are reference values.

# Reliability Test Results

P/N : ECASD60J157M010K00 (6.3V/150uF/10mohm)

— Avg    — Max    — Min    — Criteria  
 (init : initial , RF : Reflow , Vr : Rated Voltage applied , RH : Relative Humidity)




All measurement data are reference values.

## Reliability Test Results

P/N : ECASD61C226M030K00 (16V/22uF/30mohm)

— Avg    — Max    — Min    — Criteria  
 (init : initial , RF : Reflow , Vr : Rated Voltage applied , RH : Relative Humidity)



All measurement data are reference values.