

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1555C1HR10WA01	General	0402	0.1	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GRM1555C2AR10WA01	General	0402	0.1	+/-0.05[pF]	100	C0G	100[MHz]-20[GHz]
GRM1555C1HR20BA01	General	0402	0.2	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GRM1555C1HR20WA01	General	0402	0.2	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GRM1555C2AR20BA01	General	0402	0.2	+/-0.1[pF]	100	C0G	100[MHz]-20[GHz]
GRM1555C2AR20WA01	General	0402	0.2	+/-0.05[pF]	100	C0G	100[MHz]-20[GHz]
GRM1555C1HR30BA01	General	0402	0.3	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GRM1555C1HR30WA01	General	0402	0.3	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GRM1555C2AR30BA01	General	0402	0.3	+/-0.1[pF]	100	C0G	100[MHz]-20[GHz]
GRM1555C2AR30WA01	General	0402	0.3	+/-0.05[pF]	100	C0G	100[MHz]-20[GHz]
GRM1555C1HR40BA01	General	0402	0.4	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GRM1555C1HR40WA01	General	0402	0.4	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GRM1555C2AR40BA01	General	0402	0.4	+/-0.1[pF]	100	C0G	100[MHz]-20[GHz]
GRM1555C2AR40WA01	General	0402	0.4	+/-0.05[pF]	100	C0G	100[MHz]-20[GHz]
GRM1555C1HR50BA01	General	0402	0.5	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GRM1555C1HR50WA01	General	0402	0.5	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GRM1555C2AR50BA01	General	0402	0.5	+/-0.1[pF]	100	C0G	100[MHz]-20[GHz]
GRM1555C2AR50WA01	General	0402	0.5	+/-0.05[pF]	100	C0G	100[MHz]-20[GHz]
GRM1555C1HR60BA01	General	0402	0.6	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GRM1555C1HR60WA01	General	0402	0.6	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GRM1555C2AR60BA01	General	0402	0.6	+/-0.1[pF]	100	C0G	100[MHz]-20[GHz]
GRM1555C2AR60WA01	General	0402	0.6	+/-0.05[pF]	100	C0G	100[MHz]-20[GHz]
GRM1555C1HR70BA01	General	0402	0.7	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GRM1555C1HR70WA01	General	0402	0.7	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GRM1555C2AR70BA01	General	0402	0.7	+/-0.1[pF]	100	C0G	100[MHz]-20[GHz]
GRM1555C2AR70WA01	General	0402	0.7	+/-0.05[pF]	100	C0G	100[MHz]-20[GHz]
GRM1555C1HR80BA01	General	0402	0.8	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GRM1555C1HR80WA01	General	0402	0.8	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GRM1555C2AR80BA01	General	0402	0.8	+/-0.1[pF]	100	C0G	100[MHz]-20[GHz]
GRM1555C2AR80WA01	General	0402	0.8	+/-0.05[pF]	100	C0G	100[MHz]-20[GHz]
GRM1555C1HR90BA01	General	0402	0.9	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GRM1555C1HR90WA01	General	0402	0.9	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GRM1555C2AR90BA01	General	0402	0.9	+/-0.1[pF]	100	C0G	100[MHz]-20[GHz]
GRM1555C2AR90WA01	General	0402	0.9	+/-0.05[pF]	100	C0G	100[MHz]-20[GHz]
GRM1555C1H1R0BA01	General	0402	1	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GRM1555C1H1R0CA01	General	0402	1	+/-0.25[pF]	50	C0G	100[MHz]-20[GHz]
GRM1555C1H1R0WA01	General	0402	1	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GRM1555C2A1R0BA01	General	0402	1	+/-0.1[pF]	100	C0G	100[MHz]-20[GHz]
GRM1555C2A1R0CA01	General	0402	1	+/-0.25[pF]	100	C0G	100[MHz]-20[GHz]
GRM1555C2A1R0WA01	General	0402	1	+/-0.05[pF]	100	C0G	100[MHz]-20[GHz]
GRM1555C1E1R1CA01	General	0402	1.1	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R1BA01	General	0402	1.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R1CA01	General	0402	1.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R1WA01	General	0402	1.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R1BA01	General	0402	1.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R1CA01	General	0402	1.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R1WA01	General	0402	1.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E1R2CA01	General	0402	1.2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R2BA01	General	0402	1.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R2CA01	General	0402	1.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R2WA01	General	0402	1.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R2BA01	General	0402	1.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R2CA01	General	0402	1.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R2WA01	General	0402	1.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E1R3CA01	General	0402	1.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R3BA01	General	0402	1.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1555C1H1R3CA01	General	0402	1.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R3WA01	General	0402	1.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R3BA01	General	0402	1.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R3CA01	General	0402	1.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R3WA01	General	0402	1.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R4BA01	General	0402	1.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R4CA01	General	0402	1.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R4WA01	General	0402	1.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R4BA01	General	0402	1.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R4CA01	General	0402	1.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R4WA01	General	0402	1.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E1R5CA01	General	0402	1.5	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R5BA01	General	0402	1.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R5CA01	General	0402	1.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R5WA01	General	0402	1.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R5BA01	General	0402	1.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R5CA01	General	0402	1.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R5WA01	General	0402	1.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E1R6CA01	General	0402	1.6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R6BA01	General	0402	1.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R6CA01	General	0402	1.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R6WA01	General	0402	1.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R6BA01	General	0402	1.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R6CA01	General	0402	1.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R6WA01	General	0402	1.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R7BA01	General	0402	1.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R7CA01	General	0402	1.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R7WA01	General	0402	1.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R7BA01	General	0402	1.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R7CA01	General	0402	1.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R7WA01	General	0402	1.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E1R8CA01	General	0402	1.8	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R8BA01	General	0402	1.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R8CA01	General	0402	1.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R8WA01	General	0402	1.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R8BA01	General	0402	1.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R8CA01	General	0402	1.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R8WA01	General	0402	1.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R9BA01	General	0402	1.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R9CA01	General	0402	1.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H1R9WA01	General	0402	1.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R9BA01	General	0402	1.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R9CA01	General	0402	1.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A1R9WA01	General	0402	1.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E2R0CA01	General	0402	2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R0BA01	General	0402	2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R0CA01	General	0402	2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R0WA01	General	0402	2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R0BA01	General	0402	2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R0CA01	General	0402	2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R0WA01	General	0402	2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R1BA01	General	0402	2.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R1CA01	General	0402	2.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R1WA01	General	0402	2.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R1BA01	General	0402	2.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R1CA01	General	0402	2.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1555C2A2R1WA01	General	0402	2.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E2R2CA01	General	0402	2.2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R2BA01	General	0402	2.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R2CA01	General	0402	2.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R2WA01	General	0402	2.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R2BA01	General	0402	2.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R2CA01	General	0402	2.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R2WA01	General	0402	2.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R3BA01	General	0402	2.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R3CA01	General	0402	2.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R3WA01	General	0402	2.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R3BA01	General	0402	2.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R3CA01	General	0402	2.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R3WA01	General	0402	2.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E2R4CA01	General	0402	2.4	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R4BA01	General	0402	2.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R4CA01	General	0402	2.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R4WA01	General	0402	2.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R4BA01	General	0402	2.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R4CA01	General	0402	2.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R4WA01	General	0402	2.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R5BA01	General	0402	2.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R5CA01	General	0402	2.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R5WA01	General	0402	2.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R5BA01	General	0402	2.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R5CA01	General	0402	2.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R5WA01	General	0402	2.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R6BA01	General	0402	2.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R6CA01	General	0402	2.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R6WA01	General	0402	2.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R6BA01	General	0402	2.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R6CA01	General	0402	2.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R6WA01	General	0402	2.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E2R7CA01	General	0402	2.7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R7BA01	General	0402	2.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R7CA01	General	0402	2.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R7WA01	General	0402	2.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R7BA01	General	0402	2.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R7CA01	General	0402	2.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R7WA01	General	0402	2.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R8BA01	General	0402	2.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R8CA01	General	0402	2.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R8WA01	General	0402	2.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R8BA01	General	0402	2.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R8CA01	General	0402	2.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R8WA01	General	0402	2.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R9BA01	General	0402	2.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R9CA01	General	0402	2.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H2R9WA01	General	0402	2.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R9BA01	General	0402	2.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R9CA01	General	0402	2.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A2R9WA01	General	0402	2.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E3R0CA01	General	0402	3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R0BA01	General	0402	3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R0CA01	General	0402	3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R0WA01	General	0402	3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1555C2A3R0BA01	General	0402	3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R0CA01	General	0402	3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R0WA01	General	0402	3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R1BA01	General	0402	3.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R1CA01	General	0402	3.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R1WA01	General	0402	3.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R1BA01	General	0402	3.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R1CA01	General	0402	3.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R1WA01	General	0402	3.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R2BA01	General	0402	3.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R2CA01	General	0402	3.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R2WA01	General	0402	3.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R2BA01	General	0402	3.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R2CA01	General	0402	3.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R2WA01	General	0402	3.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E3R3CA01	General	0402	3.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R3BA01	General	0402	3.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R3CA01	General	0402	3.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R3WA01	General	0402	3.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R3BA01	General	0402	3.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R3CA01	General	0402	3.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R3WA01	General	0402	3.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R4BA01	General	0402	3.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R4CA01	General	0402	3.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R4WA01	General	0402	3.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R4BA01	General	0402	3.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R4CA01	General	0402	3.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R4WA01	General	0402	3.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R5BA01	General	0402	3.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R5CA01	General	0402	3.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R5WA01	General	0402	3.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R5BA01	General	0402	3.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R5CA01	General	0402	3.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R5WA01	General	0402	3.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E3R6CA01	General	0402	3.6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R6BA01	General	0402	3.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R6CA01	General	0402	3.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R6WA01	General	0402	3.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R6BA01	General	0402	3.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R6CA01	General	0402	3.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R6WA01	General	0402	3.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R7BA01	General	0402	3.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R7CA01	General	0402	3.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R7WA01	General	0402	3.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R7BA01	General	0402	3.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R7CA01	General	0402	3.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R7WA01	General	0402	3.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R8BA01	General	0402	3.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R8CA01	General	0402	3.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R8WA01	General	0402	3.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R8BA01	General	0402	3.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R8CA01	General	0402	3.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R8WA01	General	0402	3.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E3R9CA01	General	0402	3.9	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R9BA01	General	0402	3.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H3R9CA01	General	0402	3.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1555C1H3R9WA01	General	0402	3.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R9BA01	General	0402	3.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R9CA01	General	0402	3.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A3R9WA01	General	0402	3.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R0BA01	General	0402	4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R0CA01	General	0402	4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R0WA01	General	0402	4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R0BA01	General	0402	4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R0CA01	General	0402	4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R0WA01	General	0402	4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R1BA01	General	0402	4.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R1CA01	General	0402	4.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R1WA01	General	0402	4.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R1BA01	General	0402	4.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R1CA01	General	0402	4.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R1WA01	General	0402	4.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R2BA01	General	0402	4.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R2CA01	General	0402	4.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R2WA01	General	0402	4.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R2BA01	General	0402	4.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R2CA01	General	0402	4.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R2WA01	General	0402	4.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E4R3CA01	General	0402	4.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R3BA01	General	0402	4.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R3CA01	General	0402	4.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R3WA01	General	0402	4.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R3BA01	General	0402	4.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R3CA01	General	0402	4.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R3WA01	General	0402	4.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R4BA01	General	0402	4.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R4CA01	General	0402	4.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R4WA01	General	0402	4.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R4BA01	General	0402	4.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R4CA01	General	0402	4.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R4WA01	General	0402	4.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R5BA01	General	0402	4.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R5CA01	General	0402	4.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R5WA01	General	0402	4.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R5BA01	General	0402	4.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R5CA01	General	0402	4.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R5WA01	General	0402	4.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R6BA01	General	0402	4.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R6CA01	General	0402	4.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R6WA01	General	0402	4.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R6BA01	General	0402	4.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R6CA01	General	0402	4.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R6WA01	General	0402	4.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E4R7CA01	General	0402	4.7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R7BA01	General	0402	4.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R7CA01	General	0402	4.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R7WA01	General	0402	4.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R7BA01	General	0402	4.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R7CA01	General	0402	4.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R7WA01	General	0402	4.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R8BA01	General	0402	4.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R8CA01	General	0402	4.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1555C1H4R8WA01	General	0402	4.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R8BA01	General	0402	4.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R8CA01	General	0402	4.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R8WA01	General	0402	4.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R9BA01	General	0402	4.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R9CA01	General	0402	4.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H4R9WA01	General	0402	4.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R9BA01	General	0402	4.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R9CA01	General	0402	4.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A4R9WA01	General	0402	4.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R0BA01	General	0402	5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R0CA01	General	0402	5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R0WA01	General	0402	5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R0BA01	General	0402	5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R0CA01	General	0402	5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R0WA01	General	0402	5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E5R1DA01	General	0402	5.1	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R1BA01	General	0402	5.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R1CA01	General	0402	5.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R1DA01	General	0402	5.1	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R1WA01	General	0402	5.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R1BA01	General	0402	5.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R1CA01	General	0402	5.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R1DA01	General	0402	5.1	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R1WA01	General	0402	5.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R2BA01	General	0402	5.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R2CA01	General	0402	5.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R2DA01	General	0402	5.2	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R2WA01	General	0402	5.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R2BA01	General	0402	5.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R2CA01	General	0402	5.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R2DA01	General	0402	5.2	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R2WA01	General	0402	5.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R3BA01	General	0402	5.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R3CA01	General	0402	5.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R3DA01	General	0402	5.3	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R3WA01	General	0402	5.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R3BA01	General	0402	5.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R3CA01	General	0402	5.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R3DA01	General	0402	5.3	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R3WA01	General	0402	5.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R4BA01	General	0402	5.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R4CA01	General	0402	5.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R4DA01	General	0402	5.4	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R4WA01	General	0402	5.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R4BA01	General	0402	5.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R4CA01	General	0402	5.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R4DA01	General	0402	5.4	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R4WA01	General	0402	5.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R5BA01	General	0402	5.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R5CA01	General	0402	5.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R5DA01	General	0402	5.5	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R5WA01	General	0402	5.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R5BA01	General	0402	5.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R5CA01	General	0402	5.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R5DA01	General	0402	5.5	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1555C2A5R5WA01	General	0402	5.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E5R6DA01	General	0402	5.6	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R6BA01	General	0402	5.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R6CA01	General	0402	5.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R6DA01	General	0402	5.6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R6WA01	General	0402	5.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R6BA01	General	0402	5.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R6CA01	General	0402	5.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R6DA01	General	0402	5.6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R6WA01	General	0402	5.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R7BA01	General	0402	5.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R7CA01	General	0402	5.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R7DA01	General	0402	5.7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R7WA01	General	0402	5.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R7BA01	General	0402	5.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R7CA01	General	0402	5.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R7DA01	General	0402	5.7	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R7WA01	General	0402	5.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R8BA01	General	0402	5.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R8CA01	General	0402	5.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R8DA01	General	0402	5.8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R8WA01	General	0402	5.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R8BA01	General	0402	5.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R8CA01	General	0402	5.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R8DA01	General	0402	5.8	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R8WA01	General	0402	5.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R9BA01	General	0402	5.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R9CA01	General	0402	5.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R9DA01	General	0402	5.9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H5R9WA01	General	0402	5.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R9BA01	General	0402	5.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R9CA01	General	0402	5.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R9DA01	General	0402	5.9	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A5R9WA01	General	0402	5.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R0BA01	General	0402	6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R0CA01	General	0402	6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R0DA01	General	0402	6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R0WA01	General	0402	6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R0BA01	General	0402	6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R0CA01	General	0402	6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R0DA01	General	0402	6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R0WA01	General	0402	6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R1BA01	General	0402	6.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R1CA01	General	0402	6.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R1DA01	General	0402	6.1	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R1WA01	General	0402	6.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R1BA01	General	0402	6.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R1CA01	General	0402	6.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R1DA01	General	0402	6.1	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R1WA01	General	0402	6.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E6R2DA01	General	0402	6.2	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R2BA01	General	0402	6.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R2CA01	General	0402	6.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R2DA01	General	0402	6.2	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R2WA01	General	0402	6.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R2BA01	General	0402	6.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1555C2A6R2CA01	General	0402	6.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R2DA01	General	0402	6.2	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R2WA01	General	0402	6.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R3BA01	General	0402	6.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R3CA01	General	0402	6.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R3DA01	General	0402	6.3	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R3WA01	General	0402	6.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R3BA01	General	0402	6.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R3CA01	General	0402	6.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R3DA01	General	0402	6.3	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R3WA01	General	0402	6.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R4BA01	General	0402	6.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R4CA01	General	0402	6.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R4DA01	General	0402	6.4	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R4WA01	General	0402	6.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R4BA01	General	0402	6.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R4CA01	General	0402	6.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R4DA01	General	0402	6.4	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R4WA01	General	0402	6.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R5BA01	General	0402	6.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R5CA01	General	0402	6.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R5DA01	General	0402	6.5	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R5WA01	General	0402	6.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R5BA01	General	0402	6.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R5CA01	General	0402	6.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R5DA01	General	0402	6.5	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R5WA01	General	0402	6.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R6BA01	General	0402	6.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R6CA01	General	0402	6.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R6DA01	General	0402	6.6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R6WA01	General	0402	6.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R6BA01	General	0402	6.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R6CA01	General	0402	6.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R6DA01	General	0402	6.6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R6WA01	General	0402	6.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R7BA01	General	0402	6.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R7CA01	General	0402	6.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R7DA01	General	0402	6.7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R7WA01	General	0402	6.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R7BA01	General	0402	6.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R7CA01	General	0402	6.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R7DA01	General	0402	6.7	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R7WA01	General	0402	6.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E6R8DA01	General	0402	6.8	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R8BA01	General	0402	6.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R8CA01	General	0402	6.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R8DA01	General	0402	6.8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R8WA01	General	0402	6.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R8BA01	General	0402	6.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R8CA01	General	0402	6.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R8DA01	General	0402	6.8	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R8WA01	General	0402	6.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R9BA01	General	0402	6.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R9CA01	General	0402	6.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R9DA01	General	0402	6.9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H6R9WA01	General	0402	6.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]



Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1555C2A6R9BA01	General	0402	6.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R9CA01	General	0402	6.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R9DA01	General	0402	6.9	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A6R9WA01	General	0402	6.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R0BA01	General	0402	7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R0CA01	General	0402	7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R0DA01	General	0402	7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R0WA01	General	0402	7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R0BA01	General	0402	7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R0CA01	General	0402	7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R0DA01	General	0402	7	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R0WA01	General	0402	7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R1BA01	General	0402	7.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R1CA01	General	0402	7.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R1DA01	General	0402	7.1	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R1WA01	General	0402	7.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R1BA01	General	0402	7.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R1CA01	General	0402	7.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R1DA01	General	0402	7.1	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R1WA01	General	0402	7.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R2BA01	General	0402	7.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R2CA01	General	0402	7.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R2DA01	General	0402	7.2	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R2WA01	General	0402	7.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R2BA01	General	0402	7.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R2CA01	General	0402	7.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R2DA01	General	0402	7.2	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R2WA01	General	0402	7.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R3BA01	General	0402	7.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R3CA01	General	0402	7.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R3DA01	General	0402	7.3	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R3WA01	General	0402	7.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R3BA01	General	0402	7.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R3CA01	General	0402	7.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R3DA01	General	0402	7.3	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R3WA01	General	0402	7.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R4BA01	General	0402	7.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R4CA01	General	0402	7.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R4DA01	General	0402	7.4	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R4WA01	General	0402	7.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R4BA01	General	0402	7.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R4CA01	General	0402	7.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R4DA01	General	0402	7.4	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R4WA01	General	0402	7.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E7R5DA01	General	0402	7.5	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R5BA01	General	0402	7.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R5CA01	General	0402	7.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R5DA01	General	0402	7.5	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R5WA01	General	0402	7.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R5BA01	General	0402	7.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R5CA01	General	0402	7.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R5DA01	General	0402	7.5	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R5WA01	General	0402	7.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R6BA01	General	0402	7.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R6CA01	General	0402	7.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R6DA01	General	0402	7.6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1555C1H7R6WA01	General	0402	7.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R6BA01	General	0402	7.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R6CA01	General	0402	7.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R6DA01	General	0402	7.6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R6WA01	General	0402	7.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R7BA01	General	0402	7.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R7CA01	General	0402	7.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R7DA01	General	0402	7.7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R7WA01	General	0402	7.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R7BA01	General	0402	7.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R7CA01	General	0402	7.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R7DA01	General	0402	7.7	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R7WA01	General	0402	7.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R8BA01	General	0402	7.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R8CA01	General	0402	7.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R8DA01	General	0402	7.8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R8WA01	General	0402	7.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R8BA01	General	0402	7.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R8CA01	General	0402	7.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R8DA01	General	0402	7.8	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R8WA01	General	0402	7.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R9BA01	General	0402	7.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R9CA01	General	0402	7.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R9DA01	General	0402	7.9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H7R9WA01	General	0402	7.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R9BA01	General	0402	7.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R9CA01	General	0402	7.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R9DA01	General	0402	7.9	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A7R9WA01	General	0402	7.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R0BA01	General	0402	8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R0CA01	General	0402	8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R0DA01	General	0402	8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R0WA01	General	0402	8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R0BA01	General	0402	8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R0CA01	General	0402	8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R0DA01	General	0402	8	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R0WA01	General	0402	8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R1BA01	General	0402	8.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R1CA01	General	0402	8.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R1DA01	General	0402	8.1	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R1WA01	General	0402	8.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R1BA01	General	0402	8.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R1CA01	General	0402	8.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R1DA01	General	0402	8.1	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R1WA01	General	0402	8.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E8R2DA01	General	0402	8.2	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R2BA01	General	0402	8.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R2CA01	General	0402	8.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R2DA01	General	0402	8.2	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R2WA01	General	0402	8.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R2BA01	General	0402	8.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R2CA01	General	0402	8.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R2DA01	General	0402	8.2	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R2WA01	General	0402	8.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R3BA01	General	0402	8.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R3CA01	General	0402	8.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1555C1H8R3DA01	General	0402	8.3	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R3WA01	General	0402	8.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R3BA01	General	0402	8.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R3CA01	General	0402	8.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R3DA01	General	0402	8.3	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R3WA01	General	0402	8.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R4BA01	General	0402	8.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R4CA01	General	0402	8.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R4DA01	General	0402	8.4	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R4WA01	General	0402	8.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R4BA01	General	0402	8.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R4CA01	General	0402	8.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R4DA01	General	0402	8.4	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R4WA01	General	0402	8.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R5BA01	General	0402	8.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R5CA01	General	0402	8.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R5DA01	General	0402	8.5	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R5WA01	General	0402	8.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R5BA01	General	0402	8.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R5CA01	General	0402	8.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R5DA01	General	0402	8.5	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R5WA01	General	0402	8.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R6BA01	General	0402	8.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R6CA01	General	0402	8.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R6DA01	General	0402	8.6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R6WA01	General	0402	8.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R6BA01	General	0402	8.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R6CA01	General	0402	8.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R6DA01	General	0402	8.6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R6WA01	General	0402	8.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R7BA01	General	0402	8.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R7CA01	General	0402	8.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R7DA01	General	0402	8.7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R7WA01	General	0402	8.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R7BA01	General	0402	8.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R7CA01	General	0402	8.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R7DA01	General	0402	8.7	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R7WA01	General	0402	8.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R8BA01	General	0402	8.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R8CA01	General	0402	8.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R8DA01	General	0402	8.8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R8WA01	General	0402	8.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R8BA01	General	0402	8.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R8CA01	General	0402	8.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R8DA01	General	0402	8.8	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R8WA01	General	0402	8.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R9BA01	General	0402	8.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R9CA01	General	0402	8.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R9DA01	General	0402	8.9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H8R9WA01	General	0402	8.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R9BA01	General	0402	8.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R9CA01	General	0402	8.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R9DA01	General	0402	8.9	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A8R9WA01	General	0402	8.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R0BA01	General	0402	9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R0CA01	General	0402	9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1555C1H9R0DA01	General	0402	9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R0WA01	General	0402	9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R0BA01	General	0402	9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R0CA01	General	0402	9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R0DA01	General	0402	9	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R0WA01	General	0402	9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E9R1DA01	General	0402	9.1	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R1BA01	General	0402	9.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R1CA01	General	0402	9.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R1DA01	General	0402	9.1	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R1WA01	General	0402	9.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R1BA01	General	0402	9.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R1CA01	General	0402	9.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R1DA01	General	0402	9.1	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R1WA01	General	0402	9.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R2BA01	General	0402	9.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R2CA01	General	0402	9.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R2DA01	General	0402	9.2	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R2WA01	General	0402	9.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R2BA01	General	0402	9.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R2CA01	General	0402	9.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R2DA01	General	0402	9.2	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R2WA01	General	0402	9.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R3BA01	General	0402	9.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R3CA01	General	0402	9.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R3DA01	General	0402	9.3	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R3WA01	General	0402	9.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R3BA01	General	0402	9.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R3CA01	General	0402	9.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R3DA01	General	0402	9.3	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R3WA01	General	0402	9.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R4BA01	General	0402	9.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R4CA01	General	0402	9.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R4DA01	General	0402	9.4	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R4WA01	General	0402	9.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R4BA01	General	0402	9.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R4CA01	General	0402	9.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R4DA01	General	0402	9.4	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R4WA01	General	0402	9.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R5BA01	General	0402	9.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R5CA01	General	0402	9.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R5DA01	General	0402	9.5	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R5WA01	General	0402	9.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R5BA01	General	0402	9.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R5CA01	General	0402	9.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R5DA01	General	0402	9.5	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R5WA01	General	0402	9.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R6BA01	General	0402	9.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R6CA01	General	0402	9.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R6DA01	General	0402	9.6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R6WA01	General	0402	9.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R6BA01	General	0402	9.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R6CA01	General	0402	9.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R6DA01	General	0402	9.6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R6WA01	General	0402	9.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R7BA01	General	0402	9.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1555C1H9R7CA01	General	0402	9.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R7DA01	General	0402	9.7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R7WA01	General	0402	9.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R7BA01	General	0402	9.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R7CA01	General	0402	9.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R7DA01	General	0402	9.7	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R7WA01	General	0402	9.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R8BA01	General	0402	9.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R8CA01	General	0402	9.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R8DA01	General	0402	9.8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R8WA01	General	0402	9.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R8BA01	General	0402	9.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R8CA01	General	0402	9.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R8DA01	General	0402	9.8	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R8WA01	General	0402	9.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R9BA01	General	0402	9.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R9CA01	General	0402	9.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R9DA01	General	0402	9.9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H9R9WA01	General	0402	9.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R9BA01	General	0402	9.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R9CA01	General	0402	9.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R9DA01	General	0402	9.9	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A9R9WA01	General	0402	9.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E100JA01	General	0402	10	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H100GA01	General	0402	10	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H100JA01	General	0402	10	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A100GA01	General	0402	10	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A100JA01	General	0402	10	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H110JA01	General	0402	11	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1E120JA01	General	0402	12	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H120GA01	General	0402	12	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H120JA01	General	0402	12	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A120GA01	General	0402	12	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A120JA01	General	0402	12	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H130JA01	General	0402	13	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1E150JA01	General	0402	15	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H150GA01	General	0402	15	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H150JA01	General	0402	15	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A150GA01	General	0402	15	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A150JA01	General	0402	15	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H160JA01	General	0402	16	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1E180JA01	General	0402	18	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H180GA01	General	0402	18	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H180JA01	General	0402	18	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A180GA01	General	0402	18	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A180JA01	General	0402	18	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H200JA01	General	0402	20	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1E220JA01	General	0402	22	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H220GA01	General	0402	22	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H220JA01	General	0402	22	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A220GA01	General	0402	22	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A220JA01	General	0402	22	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H240JA01	General	0402	24	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1E270JA01	General	0402	27	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H270GA01	General	0402	27	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H270JA01	General	0402	27	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1555C2A270GA01	General	0402	27	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A270JA01	General	0402	27	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H300JA01	General	0402	30	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1E330JA01	General	0402	33	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H330GA01	General	0402	33	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H330JA01	General	0402	33	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A330GA01	General	0402	33	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A330JA01	General	0402	33	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H360JA01	General	0402	36	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1E390JA01	General	0402	39	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H390GA01	General	0402	39	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H390JA01	General	0402	39	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A390GA01	General	0402	39	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A390JA01	General	0402	39	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H430JA01	General	0402	43	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1E470JA01	General	0402	47	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H470GA01	General	0402	47	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H470JA01	General	0402	47	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A470GA01	General	0402	47	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A470JA01	General	0402	47	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H510JA01	General	0402	51	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1E560JA01	General	0402	56	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H560GA01	General	0402	56	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H560JA01	General	0402	56	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A560GA01	General	0402	56	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A560JA01	General	0402	56	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H620JA01	General	0402	62	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1E680JA01	General	0402	68	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H680GA01	General	0402	68	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H680JA01	General	0402	68	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A680GA01	General	0402	68	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A680JA01	General	0402	68	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H750JA01	General	0402	75	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1E820JA01	General	0402	82	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H820GA01	General	0402	82	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H820JA01	General	0402	82	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A820GA01	General	0402	82	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A820JA01	General	0402	82	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1H910JA01	General	0402	91	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1E101JA01	General	0402	100	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H101GA01	General	0402	100	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H101JA01	General	0402	100	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C2A101GA01	General	0402	100	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C2A101JA01	General	0402	100	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1555C1E121JA01	General	0402	120	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H121GA01	General	0402	120	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H121JA01	General	0402	120	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1E151JA01	General	0402	150	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H151GA01	General	0402	150	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H151JA01	General	0402	150	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1E181JA01	General	0402	180	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H181GA01	General	0402	180	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H181JA01	General	0402	180	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1E221JA01	General	0402	220	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H221GA01	General	0402	220	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H221JA01	General	0402	220	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM155R71H221KA01	General	0402	220	+/-10[%]	50	X7R	2[MHz]-6[GHz]
GRM15XR71H221KA86	General	0402	220	+/-10[%]	50	X7R	3[MHz]-6[GHz]
GRM155R72A221KA01	General	0402	220	+/-10[%]	100	X7R	2[MHz]-6[GHz]
GRM1555C1E271JA01	General	0402	270	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H271GA01	General	0402	270	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H271JA01	General	0402	270	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM155R71H271KA01	General	0402	270	+/-10[%]	50	X7R	300[kHz]-6[GHz]
GRM1555C1E331JA01	General	0402	330	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H331GA01	General	0402	330	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H331JA01	General	0402	330	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM155R71H331KA01	General	0402	330	+/-10[%]	50	X7R	300[kHz]-6[GHz]
GRM15XR71H331KA86	General	0402	330	+/-10[%]	50	X7R	1[MHz]-6[GHz]
GRM155R72A331KA01	General	0402	330	+/-10[%]	100	X7R	300[kHz]-6[GHz]
GRM1555C1E391JA01	General	0402	390	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H391GA01	General	0402	390	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H391JA01	General	0402	390	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM155R71H391KA01	General	0402	390	+/-10[%]	50	X7R	300[kHz]-6[GHz]
GRM1555C1E471JA01	General	0402	470	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H471GA01	General	0402	470	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H471JA01	General	0402	470	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM155R71H471KA01	General	0402	470	+/-10[%]	50	X7R	1[MHz]-6[GHz]
GRM15XR71H471KA86	General	0402	470	+/-10[%]	50	X7R	1[MHz]-6[GHz]
GRM155R72A471KA01	General	0402	470	+/-10[%]	100	X7R	1[MHz]-6[GHz]
GRM1555C1E561JA01	General	0402	560	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H561GA01	General	0402	560	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H561JA01	General	0402	560	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM155R71H561KA01	General	0402	560	+/-10[%]	50	X7R	300[kHz]-6[GHz]
GRM1555C1E681JA01	General	0402	680	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H681GA01	General	0402	680	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H681JA01	General	0402	680	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM155R71H681KA01	General	0402	680	+/-10[%]	50	X7R	300[kHz]-6[GHz]
GRM15XR71H681KA86	General	0402	680	+/-10[%]	50	X7R	1[MHz]-6[GHz]
GRM155R72A681KA01	General	0402	680	+/-10[%]	100	X7R	300[kHz]-6[GHz]
GRM1555C1E821JA01	General	0402	820	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1555C1H821GA01	General	0402	820	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1555C1H821JA01	General	0402	820	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM155R71H821KA01	General	0402	820	+/-10[%]	50	X7R	300[kHz]-6[GHz]
GRM1555C1E102JA01	General	0402	1000	+/-5[%]	25	C0G	1[MHz]-6[GHz]
GRM155R61E102KA01	General	0402	1000	+/-10[%]	25	X5R	400[kHz]-6[GHz]
GRM1555C1H102GA01	General	0402	1000	+/-2[%]	50	C0G	1[MHz]-6[GHz]
GRM1555C1H102JA01	General	0402	1000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM155R61H102KA01	General	0402	1000	+/-10[%]	50	X5R	400[kHz]-6[GHz]
GRM155R71H102KA01	General	0402	1000	+/-10[%]	50	X7R	400[kHz]-6[GHz]
GRM155R71H102MA01	General	0402	1000	+/-20[%]	50	X7R	400[kHz]-6[GHz]
GRM15XR71H102KA86	General	0402	1000	+/-10[%]	50	X7R	1[MHz]-6[GHz]
GRM155R72A102KA01	General	0402	1000	+/-10[%]	100	X7R	400[kHz]-6[GHz]
GRM1557U1A122JA01	General	0402	1200	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM1557U1A152JA01	General	0402	1500	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM155R71H152KA01	General	0402	1500	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM15XR71H152KA86	General	0402	1500	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM155R72A152KA01	General	0402	1500	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM1557U1A182JA01	General	0402	1800	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM155R71H182KA01	General	0402	1800	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM1557U1A222JA01	General	0402	2200	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM155R61E222KA01	General	0402	2200	+/-10[%]	25	X5R	200[kHz]-6[GHz]
GRM155R71E222KA01	General	0402	2200	+/-10[%]	25	X7R	200[kHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM15XR71E222KA86	General	0402	2200	+/-10[%]	25	X7R	300[kHz]-6[GHz]
GRM15XR71E222MA86	General	0402	2200	+/-20[%]	25	X7R	300[kHz]-6[GHz]
GRM155R61H222KA01	General	0402	2200	+/-10[%]	50	X5R	200[kHz]-6[GHz]
GRM155R71H222KA01	General	0402	2200	+/-10[%]	50	X7R	200[kHz]-6[GHz]
GRM155R72A222KA01	General	0402	2200	+/-10[%]	100	X7R	200[kHz]-6[GHz]
GRM1557U1A272JA01	General	0402	2700	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM155R71H272KA01	General	0402	2700	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM1557U1A332JA01	General	0402	3300	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM15XR71C332KA86	General	0402	3300	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM15XR71C332MA86	General	0402	3300	+/-20[%]	16	X7R	100[kHz]-6[GHz]
GRM155R71H332KA01	General	0402	3300	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM155R72A332KA01	General	0402	3300	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM1557U1A392JA01	General	0402	3900	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM1557U1A472JA01	General	0402	4700	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM15XR71C472KA86	General	0402	4700	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM15XR71C472MA86	General	0402	4700	+/-20[%]	16	X7R	100[kHz]-6[GHz]
GRM155R61E472KA01	General	0402	4700	+/-10[%]	25	X5R	100[kHz]-6[GHz]
GRM155R71E472KA01	General	0402	4700	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM155R61H472KA01	General	0402	4700	+/-10[%]	50	X5R	100[kHz]-6[GHz]
GRM155R71H472KA01	General	0402	4700	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM155R72A472KA01	General	0402	4700	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM15XR71C682KA86	General	0402	6800	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM15XR71C682MA86	General	0402	6800	+/-20[%]	16	X7R	100[kHz]-6[GHz]
GRM155R71E682KA01	General	0402	6800	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM155R71H682KA88	General	0402	6800	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM155R71E822KA01	General	0402	8200	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM155R61C103KA01	General	0402	10000	+/-10[%]	16	X5R	100[kHz]-6[GHz]
GRM155R71C103KA01	General	0402	10000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM155R71C103MA01	General	0402	10000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
GRM15XR71C103KA86	General	0402	10000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM15XR71C103MA86	General	0402	10000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
GRM155R71E103KA01	General	0402	10000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM155R71H103KA88	General	0402	10000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM155R71E123KA61	General	0402	12000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM15XR61A153KA86	General	0402	15000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM15XR61A153MA86	General	0402	15000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM155R71C153KA01	General	0402	15000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM155R71E153KA61	General	0402	15000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM155R71H153KA12	General	0402	15000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM155R71C183KA01	General	0402	18000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM15XR61A223KA86	General	0402	22000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM15XR61A223MA86	General	0402	22000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM155R61C223KA01	General	0402	22000	+/-10[%]	16	X5R	100[kHz]-6[GHz]
GRM155R71C223KA01	General	0402	22000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM155R71C223MA01	General	0402	22000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
GRM155R71E223KA61	General	0402	22000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM155R71H223KA12	General	0402	22000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM15XR61A333KA86	General	0402	33000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM15XR61A333MA86	General	0402	33000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM155R61C333KA01	General	0402	33000	+/-10[%]	16	X5R	100[kHz]-6[GHz]
GRM155R71C333KA01	General	0402	33000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM155R71E333KA88	General	0402	33000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM155R61H333KE19	General	0402	33000	+/-10[%]	50	X5R	100[kHz]-6[GHz]
GRM155R61H333ME19	General	0402	33000	+/-20[%]	50	X5R	100[kHz]-6[GHz]
GRM155R71H333KE14	General	0402	33000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM155R71H333ME14	General	0402	33000	+/-20[%]	50	X7R	100[kHz]-6[GHz]



Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM155C71H333KE19	General	0402	33000	+/-10[%]	50	X7S	100[kHz]-6[GHz]
GRM155C71H333ME19	General	0402	33000	+/-20[%]	50	X7S	100[kHz]-6[GHz]
GRM155R61C473KA01	General	0402	47000	+/-10[%]	16	X5R	100[kHz]-6[GHz]
GRM155R71C473KA01	General	0402	47000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM155R71E473KA88	General	0402	47000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM155R61H473KE19	General	0402	47000	+/-10[%]	50	X5R	100[kHz]-6[GHz]
GRM155R61H473ME19	General	0402	47000	+/-20[%]	50	X5R	100[kHz]-6[GHz]
GRM155C81H473KE19	General	0402	47000	+/-10[%]	50	X6S	100[kHz]-6[GHz]
GRM155R71H473KE14	General	0402	47000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM155R71H473ME14	General	0402	47000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
GRM155C71H473KE19	General	0402	47000	+/-10[%]	50	X7S	100[kHz]-6[GHz]
GRM155C71H473ME19	General	0402	47000	+/-20[%]	50	X7S	100[kHz]-6[GHz]
GRM155R61A683KA01	General	0402	68000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM155R71A683KA01	General	0402	68000	+/-10[%]	10	X7R	100[kHz]-6[GHz]
GRM155R71A683MA01	General	0402	68000	+/-20[%]	10	X7R	100[kHz]-6[GHz]
GRM155R61C683KA88	General	0402	68000	+/-10[%]	16	X5R	100[kHz]-6[GHz]
GRM155R71C683KA88	General	0402	68000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM155R61E683KA87	General	0402	68000	+/-10[%]	25	X5R	100[kHz]-6[GHz]
GRM155R61E683MA87	General	0402	68000	+/-20[%]	25	X5R	100[kHz]-6[GHz]
GRM155C81E683KA12	General	0402	68000	+/-10[%]	25	X6S	100[kHz]-6[GHz]
GRM155R71E683KE14	General	0402	68000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM155R71E683ME14	General	0402	68000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
GRM155R61H683KE19	General	0402	68000	+/-10[%]	50	X5R	100[kHz]-6[GHz]
GRM155R61H683ME19	General	0402	68000	+/-20[%]	50	X5R	100[kHz]-6[GHz]
GRM155R71H683KE14	General	0402	68000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM155R71H683ME14	General	0402	68000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
GRM155C71H683KE19	General	0402	68000	+/-10[%]	50	X7S	100[kHz]-6[GHz]
GRM155C71H683ME19	General	0402	68000	+/-20[%]	50	X7S	100[kHz]-6[GHz]
GRM152D70E104KE19	General	0402	100000	+/-10[%]	2.5	X7T	100[kHz]-6[GHz]
GRM152D70E104ME19	General	0402	100000	+/-20[%]	2.5	X7T	100[kHz]-6[GHz]
GRM152C80G104KE19	General	0402	100000	+/-10[%]	4	X6S	100[kHz]-6[GHz]
GRM152C80G104ME19	General	0402	100000	+/-20[%]	4	X6S	100[kHz]-6[GHz]
GRM152D70G104KE15	General	0402	100000	+/-10[%]	4	X7T	100[kHz]-6[GHz]
GRM152D70G104ME15	General	0402	100000	+/-20[%]	4	X7T	100[kHz]-6[GHz]
GRM155R60J104KA01	General	0402	100000	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM152R60J104KE19	General	0402	100000	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM152R60J104ME19	General	0402	100000	+/-20[%]	6.3	X5R	100[kHz]-6[GHz]
GRM152C80J104KE19	General	0402	100000	+/-10[%]	6.3	X6S	100[kHz]-6[GHz]
GRM152C80J104ME19	General	0402	100000	+/-20[%]	6.3	X6S	100[kHz]-6[GHz]
GRM155R70J104KA01	General	0402	100000	+/-10[%]	6.3	X7R	100[kHz]-6[GHz]
GRM155R61A104KA01	General	0402	100000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM155R61A104MA01	General	0402	100000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM152R61A104KE19	General	0402	100000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM152R61A104ME19	General	0402	100000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM155R71A104KA01	General	0402	100000	+/-10[%]	10	X7R	100[kHz]-6[GHz]
GRM155R61C104KA88	General	0402	100000	+/-10[%]	16	X5R	100[kHz]-6[GHz]
GRM155R71C104KA88	General	0402	100000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM155R61E104KA87	General	0402	100000	+/-10[%]	25	X5R	100[kHz]-6[GHz]
GRM155R61E104MA87	General	0402	100000	+/-20[%]	25	X5R	100[kHz]-6[GHz]
GRM155C81E104KA12	General	0402	100000	+/-10[%]	25	X6S	100[kHz]-6[GHz]
GRM155C81E104MA12	General	0402	100000	+/-20[%]	25	X6S	100[kHz]-6[GHz]
GRM155R71E104KE14	General	0402	100000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM155R71E104ME14	General	0402	100000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
GRM155R61H104KE19	General	0402	100000	+/-10[%]	50	X5R	100[kHz]-6[GHz]
GRM155R61H104KE14	General	0402	100000	+/-10[%]	50	X5R	100[kHz]-6[GHz]
GRM155R61H104ME14	General	0402	100000	+/-20[%]	50	X5R	100[kHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM155C81H104KE19	General	0402	100000	+/-10[%]	50	X6S	100[kHz]-6[GHz]
GRM155C81H104KE14	General	0402	100000	+/-10[%]	50	X6S	100[kHz]-6[GHz]
GRM155C81H104ME14	General	0402	100000	+/-20[%]	50	X6S	100[kHz]-6[GHz]
GRM155R71H104KE14	General	0402	100000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM155R71H104ME14	General	0402	100000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
GRM155C71H104KE19	General	0402	100000	+/-10[%]	50	X7S	100[kHz]-6[GHz]
GRM155R61A124KE19	General	0402	120000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM155C80G154KE01	General	0402	150000	+/-10[%]	4	X6S	100[kHz]-6[GHz]
GRM155C80G154ME01	General	0402	150000	+/-20[%]	4	X6S	100[kHz]-6[GHz]
GRM155R60J154KE01	General	0402	150000	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM155R60J154ME01	General	0402	150000	+/-20[%]	6.3	X5R	100[kHz]-6[GHz]
GRM155C80J154KE01	General	0402	150000	+/-10[%]	6.3	X6S	100[kHz]-6[GHz]
GRM155C80J154ME01	General	0402	150000	+/-20[%]	6.3	X6S	100[kHz]-6[GHz]
GRM155R61A154KE19	General	0402	150000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM155R61A154ME19	General	0402	150000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM155R71C154KA12	General	0402	150000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM155R61A184KE19	General	0402	180000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM152D70E224KE19	General	0402	220000	+/-10[%]	2.5	X7T	100[kHz]-6[GHz]
GRM152D70E224ME19	General	0402	220000	+/-20[%]	2.5	X7T	100[kHz]-6[GHz]
GRM152C80G224KE19	General	0402	220000	+/-10[%]	4	X6S	100[kHz]-6[GHz]
GRM152C80G224ME19	General	0402	220000	+/-20[%]	4	X6S	100[kHz]-6[GHz]
GRM155C80G224KE01	General	0402	220000	+/-10[%]	4	X6S	100[kHz]-6[GHz]
GRM155C80G224ME01	General	0402	220000	+/-20[%]	4	X6S	100[kHz]-6[GHz]
GRM152D70G224KE15	General	0402	220000	+/-10[%]	4	X7T	100[kHz]-6[GHz]
GRM152D70G224ME15	General	0402	220000	+/-20[%]	4	X7T	100[kHz]-6[GHz]
GRM152R60J224KE19	General	0402	220000	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM152R60J224ME19	General	0402	220000	+/-20[%]	6.3	X5R	100[kHz]-6[GHz]
GRM155R60J224KE01	General	0402	220000	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM155R60J224ME01	General	0402	220000	+/-20[%]	6.3	X5R	100[kHz]-6[GHz]
GRM152C80J224KE19	General	0402	220000	+/-10[%]	6.3	X6S	100[kHz]-6[GHz]
GRM152C80J224ME19	General	0402	220000	+/-20[%]	6.3	X6S	100[kHz]-6[GHz]
GRM155C80J224KE01	General	0402	220000	+/-10[%]	6.3	X6S	100[kHz]-6[GHz]
GRM155C80J224ME01	General	0402	220000	+/-20[%]	6.3	X6S	100[kHz]-6[GHz]
GRM152R61A224KE19	General	0402	220000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM152R61A224ME19	General	0402	220000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM155R61A224KE19	General	0402	220000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM155R61A224ME19	General	0402	220000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM155R61C224KA12	General	0402	220000	+/-10[%]	16	X5R	100[kHz]-6[GHz]
GRM155R61C224MA12	General	0402	220000	+/-20[%]	16	X5R	100[kHz]-6[GHz]
GRM155R71C224KA12	General	0402	220000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM155C80G334KE01	General	0402	330000	+/-10[%]	4	X6S	100[kHz]-6[GHz]
GRM155C80G334ME01	General	0402	330000	+/-20[%]	4	X6S	100[kHz]-6[GHz]
GRM155R60J334KE01	General	0402	330000	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM155R60J334ME01	General	0402	330000	+/-20[%]	6.3	X5R	100[kHz]-6[GHz]
GRM155C80J334KE01	General	0402	330000	+/-10[%]	6.3	X6S	100[kHz]-6[GHz]
GRM155C80J334ME01	General	0402	330000	+/-20[%]	6.3	X6S	100[kHz]-6[GHz]
GRM155R61A334KE15	General	0402	330000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM155R61A334ME15	General	0402	330000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM155C80G474KE01	General	0402	470000	+/-10[%]	4	X6S	100[kHz]-6[GHz]
GRM155C80G474ME01	General	0402	470000	+/-20[%]	4	X6S	100[kHz]-6[GHz]
GRM152D80G474ME15	General	0402	470000	+/-20[%]	4	X6T	100[kHz]-6[GHz]
GRM152R60J474ME15	General	0402	470000	+/-20[%]	6.3	X5R	100[kHz]-6[GHz]
GRM155R60J474KE19	General	0402	470000	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM155R60J474ME19	General	0402	470000	+/-20[%]	6.3	X5R	100[kHz]-6[GHz]
GRM155C80J474KE19	General	0402	470000	+/-10[%]	6.3	X6S	100[kHz]-6[GHz]
GRM155C80J474ME19	General	0402	470000	+/-20[%]	6.3	X6S	100[kHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM155R61A474KE15	General	0402	470000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM155R61A474ME15	General	0402	470000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM155R60J684KE19	General	0402	680000	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM155R60J684ME19	General	0402	680000	+/-20[%]	6.3	X5R	100[kHz]-6[GHz]
GRM155R61A684KE15	General	0402	680000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM155R61A684ME15	General	0402	680000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM153R60G105ME95	General	0402	1000000	+/-20[%]	4	X5R	100[Hz]-6[GHz]
GRM152R60G105ME15	General	0402	1000000	+/-20[%]	4	X5R	100[Hz]-6[GHz]
GRM155C80G105KE19	General	0402	1000000	+/-10[%]	4	X6S	100[Hz]-6[GHz]
GRM153D80G105ME95	General	0402	1000000	+/-20[%]	4	X6T	100[Hz]-6[GHz]
GRM152D80G105ME15	General	0402	1000000	+/-20[%]	4	X6T	100[Hz]-6[GHz]
GRM155R70G105KA12	General	0402	1000000	+/-10[%]	4	X7R	100[Hz]-6[GHz]
GRM155R70G105MA12	General	0402	1000000	+/-20[%]	4	X7R	100[Hz]-6[GHz]
GRM155R60J105KE19	General	0402	1000000	+/-10[%]	6.3	X5R	100[Hz]-6[GHz]
GRM153R60J105ME95	General	0402	1000000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM152R60J105ME15	General	0402	1000000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM155C80J105KE15	General	0402	1000000	+/-10[%]	6.3	X6S	100[Hz]-6[GHz]
GRM153D80J105ME95	General	0402	1000000	+/-20[%]	6.3	X6T	100[Hz]-6[GHz]
GRM155R70J105KA12	General	0402	1000000	+/-10[%]	6.3	X7R	100[Hz]-6[GHz]
GRM155R70J105MA12	General	0402	1000000	+/-20[%]	6.3	X7R	100[Hz]-6[GHz]
GRM153R61A105ME95	General	0402	1000000	+/-20[%]	10	X5R	100[Hz]-6[GHz]
GRM155R61A105KE15	General	0402	1000000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM155C81A105KA12	General	0402	1000000	+/-10[%]	10	X6S	100[Hz]-6[GHz]
GRM155C81A105MA12	General	0402	1000000	+/-20[%]	10	X6S	100[Hz]-6[GHz]
GRM155R61C105KA12	General	0402	1000000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM155R61C105MA12	General	0402	1000000	+/-20[%]	16	X5R	100[Hz]-6[GHz]
GRM155C81C105KE11	General	0402	1000000	+/-10[%]	16	X6S	100[Hz]-6[GHz]
GRM155C81C105ME11	General	0402	1000000	+/-20[%]	16	X6S	100[Hz]-6[GHz]
GRM155R61E105KA12	General	0402	1000000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM155R61E105MA12	General	0402	1000000	+/-20[%]	25	X5R	100[Hz]-6[GHz]
GRM155C81E105KE11	General	0402	1000000	+/-10[%]	25	X6S	100[Hz]-6[GHz]
GRM155C81E105ME11	General	0402	1000000	+/-20[%]	25	X6S	100[Hz]-6[GHz]
GRM155R6YA105KE11	General	0402	1000000	+/-10[%]	35	X5R	100[Hz]-6[GHz]
GRM155R6YA105ME11	General	0402	1000000	+/-20[%]	35	X5R	100[Hz]-6[GHz]
GRM155D80G225KE95	General	0402	2200000	+/-10[%]	4	X6T	100[Hz]-6[GHz]
GRM155D80G225ME95	General	0402	2200000	+/-20[%]	4	X6T	100[Hz]-6[GHz]
GRM153R60J225ME95	General	0402	2200000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM155R60J225KE95	General	0402	2200000	+/-10[%]	6.3	X5R	100[Hz]-6[GHz]
GRM155R60J225ME95	General	0402	2200000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM155C80J225KE95	General	0402	2200000	+/-10[%]	6.3	X6S	100[Hz]-6[GHz]
GRM155C80J225ME95	General	0402	2200000	+/-20[%]	6.3	X6S	100[Hz]-6[GHz]
GRM155D80J225KE95	General	0402	2200000	+/-10[%]	6.3	X6T	100[Hz]-6[GHz]
GRM155D80J225ME95	General	0402	2200000	+/-20[%]	6.3	X6T	100[Hz]-6[GHz]
GRM155C70J225ME11	General	0402	2200000	+/-20[%]	6.3	X7S	100[Hz]-6[GHz]
GRM155C70J225KE11	General	0402	2200000	+/-10[%]	6.3	X7S	100[Hz]-6[GHz]
GRM155R61A225KE95	General	0402	2200000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM155R61A225ME95	General	0402	2200000	+/-20[%]	10	X5R	100[Hz]-6[GHz]
GRM155C81A225KE11	General	0402	2200000	+/-10[%]	10	X6S	100[Hz]-6[GHz]
GRM155C81A225ME11	General	0402	2200000	+/-20[%]	10	X6S	100[Hz]-6[GHz]
GRM155C71A225KE11	General	0402	2200000	+/-10[%]	10	X7S	100[Hz]-6[GHz]
GRM155C71A225ME11	General	0402	2200000	+/-20[%]	10	X7S	100[Hz]-6[GHz]
GRM155R61C225KE11	General	0402	2200000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM155R61C225ME11	General	0402	2200000	+/-20[%]	16	X5R	100[Hz]-6[GHz]
GRM155C81C225KE11	General	0402	2200000	+/-10[%]	16	X6S	100[Hz]-6[GHz]
GRM155C81C225ME11	General	0402	2200000	+/-20[%]	16	X6S	100[Hz]-6[GHz]
GRM155R61E225KE11	General	0402	2200000	+/-10[%]	25	X5R	100[Hz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM155R61E225ME11	General	0402	2200000	+/-20[%]	25	X5R	100[Hz]-6[GHz]
GRM155D80E475ME47	General	0402	4700000	+/-20[%]	2.5	X6T	100[Hz]-6[GHz]
GRM155R60G475ME47	General	0402	4700000	+/-20[%]	4	X5R	100[Hz]-6[GHz]
GRM155R60G475ME87	General	0402	4700000	+/-20[%]	4	X5R	100[Hz]-6[GHz]
GRM155R60J475ME47	General	0402	4700000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM155R60J475ME87	General	0402	4700000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM155R60E106ME16	General	0402	10000000	+/-20[%]	2.5	X5R	100[Hz]-6[GHz]
GRM155R60G106ME44	General	0402	10000000	+/-20[%]	4	X5R	100[Hz]-6[GHz]
GRM1885C1HR50BA01	General	0603	0.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1HR50WA01	General	0603	0.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2AR50BA01	General	0603	0.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2AR50WA01	General	0603	0.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1HR60BA01	General	0603	0.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1HR60WA01	General	0603	0.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2AR60BA01	General	0603	0.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2AR60WA01	General	0603	0.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1HR70BA01	General	0603	0.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1HR70WA01	General	0603	0.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2AR70BA01	General	0603	0.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2AR70WA01	General	0603	0.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1HR80BA01	General	0603	0.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1HR80WA01	General	0603	0.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2AR80BA01	General	0603	0.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2AR80WA01	General	0603	0.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1HR90BA01	General	0603	0.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1HR90WA01	General	0603	0.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2AR90BA01	General	0603	0.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2AR90WA01	General	0603	0.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R0BA01	General	0603	1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R0CA01	General	0603	1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R0WA01	General	0603	1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R0BA01	General	0603	1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R0CA01	General	0603	1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R0WA01	General	0603	1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R1BA01	General	0603	1.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R1CA01	General	0603	1.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R1WA01	General	0603	1.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R1BA01	General	0603	1.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R1CA01	General	0603	1.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R1WA01	General	0603	1.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R2BA01	General	0603	1.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R2CA01	General	0603	1.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R2WA01	General	0603	1.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R2BA01	General	0603	1.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R2CA01	General	0603	1.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R2WA01	General	0603	1.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R3BA01	General	0603	1.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R3CA01	General	0603	1.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R3WA01	General	0603	1.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R3BA01	General	0603	1.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R3CA01	General	0603	1.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R3WA01	General	0603	1.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R4BA01	General	0603	1.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R4CA01	General	0603	1.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R4WA01	General	0603	1.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R4BA01	General	0603	1.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1885C2A1R4CA01	General	0603	1.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R4WA01	General	0603	1.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R5BA01	General	0603	1.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R5CA01	General	0603	1.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R5WA01	General	0603	1.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R5BA01	General	0603	1.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R5CA01	General	0603	1.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R5WA01	General	0603	1.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R6BA01	General	0603	1.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R6CA01	General	0603	1.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R6WA01	General	0603	1.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R6BA01	General	0603	1.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R6CA01	General	0603	1.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R6WA01	General	0603	1.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R7BA01	General	0603	1.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R7CA01	General	0603	1.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R7WA01	General	0603	1.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R7BA01	General	0603	1.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R7CA01	General	0603	1.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R7WA01	General	0603	1.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R8BA01	General	0603	1.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R8CA01	General	0603	1.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R8WA01	General	0603	1.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R8BA01	General	0603	1.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R8CA01	General	0603	1.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R8WA01	General	0603	1.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R9BA01	General	0603	1.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R9CA01	General	0603	1.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H1R9WA01	General	0603	1.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R9BA01	General	0603	1.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R9CA01	General	0603	1.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A1R9WA01	General	0603	1.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R0BA01	General	0603	2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R0CA01	General	0603	2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R0WA01	General	0603	2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R0BA01	General	0603	2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R0CA01	General	0603	2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R0WA01	General	0603	2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R1BA01	General	0603	2.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R1CA01	General	0603	2.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R1WA01	General	0603	2.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R1BA01	General	0603	2.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R1CA01	General	0603	2.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R1WA01	General	0603	2.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R2BA01	General	0603	2.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R2CA01	General	0603	2.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R2WA01	General	0603	2.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R2BA01	General	0603	2.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R2CA01	General	0603	2.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R2WA01	General	0603	2.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R3BA01	General	0603	2.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R3CA01	General	0603	2.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R3WA01	General	0603	2.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R3BA01	General	0603	2.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R3CA01	General	0603	2.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R3WA01	General	0603	2.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1885C1H2R4BA01	General	0603	2.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R4CA01	General	0603	2.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R4WA01	General	0603	2.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R4BA01	General	0603	2.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R4CA01	General	0603	2.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R4WA01	General	0603	2.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R5BA01	General	0603	2.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R5CA01	General	0603	2.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R5WA01	General	0603	2.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R5BA01	General	0603	2.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R5CA01	General	0603	2.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R5WA01	General	0603	2.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R6BA01	General	0603	2.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R6CA01	General	0603	2.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R6WA01	General	0603	2.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R6BA01	General	0603	2.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R6CA01	General	0603	2.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R6WA01	General	0603	2.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R7BA01	General	0603	2.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R7CA01	General	0603	2.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R7WA01	General	0603	2.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R7BA01	General	0603	2.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R7CA01	General	0603	2.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R7WA01	General	0603	2.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R8BA01	General	0603	2.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R8CA01	General	0603	2.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R8WA01	General	0603	2.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R8BA01	General	0603	2.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R8CA01	General	0603	2.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R8WA01	General	0603	2.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R9BA01	General	0603	2.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R9CA01	General	0603	2.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H2R9WA01	General	0603	2.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R9BA01	General	0603	2.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R9CA01	General	0603	2.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A2R9WA01	General	0603	2.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R0BA01	General	0603	3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R0CA01	General	0603	3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R0WA01	General	0603	3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R0BA01	General	0603	3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R0CA01	General	0603	3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R0WA01	General	0603	3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R1BA01	General	0603	3.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R1CA01	General	0603	3.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R1WA01	General	0603	3.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R1BA01	General	0603	3.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R1CA01	General	0603	3.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R1WA01	General	0603	3.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R2BA01	General	0603	3.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R2CA01	General	0603	3.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R2WA01	General	0603	3.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R2BA01	General	0603	3.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R2CA01	General	0603	3.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R2WA01	General	0603	3.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R3BA01	General	0603	3.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R3CA01	General	0603	3.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1885C1H3R3WA01	General	0603	3.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R3BA01	General	0603	3.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R3CA01	General	0603	3.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R3WA01	General	0603	3.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R4BA01	General	0603	3.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R4CA01	General	0603	3.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R4WA01	General	0603	3.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R4BA01	General	0603	3.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R4CA01	General	0603	3.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R4WA01	General	0603	3.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R5BA01	General	0603	3.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R5CA01	General	0603	3.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R5WA01	General	0603	3.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R5BA01	General	0603	3.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R5CA01	General	0603	3.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R5WA01	General	0603	3.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R6BA01	General	0603	3.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R6CA01	General	0603	3.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R6WA01	General	0603	3.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R6BA01	General	0603	3.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R6CA01	General	0603	3.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R6WA01	General	0603	3.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R7BA01	General	0603	3.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R7CA01	General	0603	3.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R7WA01	General	0603	3.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R7BA01	General	0603	3.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R7CA01	General	0603	3.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R7WA01	General	0603	3.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R8BA01	General	0603	3.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R8CA01	General	0603	3.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R8WA01	General	0603	3.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R8BA01	General	0603	3.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R8CA01	General	0603	3.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R8WA01	General	0603	3.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R9BA01	General	0603	3.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R9CA01	General	0603	3.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H3R9WA01	General	0603	3.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R9BA01	General	0603	3.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R9CA01	General	0603	3.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A3R9WA01	General	0603	3.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R0BA01	General	0603	4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R0CA01	General	0603	4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R0WA01	General	0603	4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R0BA01	General	0603	4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R0CA01	General	0603	4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R0WA01	General	0603	4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R1BA01	General	0603	4.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R1CA01	General	0603	4.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R1WA01	General	0603	4.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R1BA01	General	0603	4.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R1CA01	General	0603	4.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R1WA01	General	0603	4.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R2BA01	General	0603	4.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R2CA01	General	0603	4.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R2WA01	General	0603	4.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R2BA01	General	0603	4.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1885C2A4R2CA01	General	0603	4.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R2WA01	General	0603	4.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R3BA01	General	0603	4.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R3CA01	General	0603	4.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R3WA01	General	0603	4.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R3BA01	General	0603	4.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R3CA01	General	0603	4.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R3WA01	General	0603	4.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R4BA01	General	0603	4.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R4CA01	General	0603	4.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R4WA01	General	0603	4.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R4BA01	General	0603	4.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R4CA01	General	0603	4.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R4WA01	General	0603	4.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R5BA01	General	0603	4.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R5CA01	General	0603	4.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R5WA01	General	0603	4.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R5BA01	General	0603	4.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R5CA01	General	0603	4.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R5WA01	General	0603	4.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R6BA01	General	0603	4.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R6CA01	General	0603	4.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R6WA01	General	0603	4.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R6BA01	General	0603	4.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R6CA01	General	0603	4.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R6WA01	General	0603	4.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R7BA01	General	0603	4.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R7CA01	General	0603	4.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R7WA01	General	0603	4.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R7BA01	General	0603	4.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R7CA01	General	0603	4.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R7WA01	General	0603	4.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R8BA01	General	0603	4.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R8CA01	General	0603	4.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R8WA01	General	0603	4.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R8BA01	General	0603	4.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R8CA01	General	0603	4.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R8WA01	General	0603	4.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R9BA01	General	0603	4.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R9CA01	General	0603	4.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H4R9WA01	General	0603	4.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R9BA01	General	0603	4.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R9CA01	General	0603	4.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A4R9WA01	General	0603	4.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R0BA01	General	0603	5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R0CA01	General	0603	5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R0WA01	General	0603	5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R0BA01	General	0603	5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R0CA01	General	0603	5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R0WA01	General	0603	5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R1BA01	General	0603	5.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R1CA01	General	0603	5.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R1DA01	General	0603	5.1	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R1WA01	General	0603	5.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R1BA01	General	0603	5.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R1CA01	General	0603	5.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]



Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1885C2A5R1DA01	General	0603	5.1	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R1WA01	General	0603	5.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R2BA01	General	0603	5.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R2CA01	General	0603	5.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R2DA01	General	0603	5.2	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R2WA01	General	0603	5.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R2BA01	General	0603	5.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R2CA01	General	0603	5.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R2DA01	General	0603	5.2	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R2WA01	General	0603	5.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R3BA01	General	0603	5.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R3CA01	General	0603	5.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R3DA01	General	0603	5.3	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R3WA01	General	0603	5.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R3BA01	General	0603	5.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R3CA01	General	0603	5.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R3DA01	General	0603	5.3	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R3WA01	General	0603	5.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R4BA01	General	0603	5.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R4CA01	General	0603	5.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R4DA01	General	0603	5.4	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R4WA01	General	0603	5.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R4BA01	General	0603	5.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R4CA01	General	0603	5.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R4DA01	General	0603	5.4	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R4WA01	General	0603	5.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R5BA01	General	0603	5.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R5CA01	General	0603	5.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R5DA01	General	0603	5.5	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R5WA01	General	0603	5.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R5BA01	General	0603	5.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R5CA01	General	0603	5.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R5DA01	General	0603	5.5	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R5WA01	General	0603	5.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R6BA01	General	0603	5.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R6CA01	General	0603	5.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R6DA01	General	0603	5.6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R6WA01	General	0603	5.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R6BA01	General	0603	5.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R6CA01	General	0603	5.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R6DA01	General	0603	5.6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R6WA01	General	0603	5.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R7BA01	General	0603	5.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R7CA01	General	0603	5.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R7DA01	General	0603	5.7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R7WA01	General	0603	5.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R7BA01	General	0603	5.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R7CA01	General	0603	5.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R7DA01	General	0603	5.7	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R7WA01	General	0603	5.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R8BA01	General	0603	5.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R8CA01	General	0603	5.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R8DA01	General	0603	5.8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R8WA01	General	0603	5.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R8BA01	General	0603	5.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R8CA01	General	0603	5.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1885C2A5R8DA01	General	0603	5.8	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R8WA01	General	0603	5.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R9BA01	General	0603	5.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R9CA01	General	0603	5.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R9DA01	General	0603	5.9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H5R9WA01	General	0603	5.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R9BA01	General	0603	5.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R9CA01	General	0603	5.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R9DA01	General	0603	5.9	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A5R9WA01	General	0603	5.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R0BA01	General	0603	6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R0CA01	General	0603	6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R0DA01	General	0603	6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R0WA01	General	0603	6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R0BA01	General	0603	6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R0CA01	General	0603	6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R0DA01	General	0603	6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R0WA01	General	0603	6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R1BA01	General	0603	6.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R1CA01	General	0603	6.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R1DA01	General	0603	6.1	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R1WA01	General	0603	6.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R1BA01	General	0603	6.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R1CA01	General	0603	6.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R1DA01	General	0603	6.1	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R1WA01	General	0603	6.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R2BA01	General	0603	6.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R2CA01	General	0603	6.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R2DA01	General	0603	6.2	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R2WA01	General	0603	6.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R2BA01	General	0603	6.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R2CA01	General	0603	6.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R2DA01	General	0603	6.2	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R2WA01	General	0603	6.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R3BA01	General	0603	6.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R3CA01	General	0603	6.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R3DA01	General	0603	6.3	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R3WA01	General	0603	6.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R3BA01	General	0603	6.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R3CA01	General	0603	6.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R3DA01	General	0603	6.3	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R3WA01	General	0603	6.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R4BA01	General	0603	6.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R4CA01	General	0603	6.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R4DA01	General	0603	6.4	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R4WA01	General	0603	6.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R4BA01	General	0603	6.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R4CA01	General	0603	6.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R4DA01	General	0603	6.4	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R4WA01	General	0603	6.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R5BA01	General	0603	6.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R5CA01	General	0603	6.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R5DA01	General	0603	6.5	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R5WA01	General	0603	6.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R5BA01	General	0603	6.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R5CA01	General	0603	6.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1885C2A6R5DA01	General	0603	6.5	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R5WA01	General	0603	6.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R6BA01	General	0603	6.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R6CA01	General	0603	6.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R6DA01	General	0603	6.6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R6WA01	General	0603	6.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R6BA01	General	0603	6.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R6CA01	General	0603	6.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R6DA01	General	0603	6.6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R6WA01	General	0603	6.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R7BA01	General	0603	6.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R7CA01	General	0603	6.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R7DA01	General	0603	6.7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R7WA01	General	0603	6.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R7BA01	General	0603	6.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R7CA01	General	0603	6.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R7DA01	General	0603	6.7	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R7WA01	General	0603	6.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R8BA01	General	0603	6.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R8CA01	General	0603	6.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R8DA01	General	0603	6.8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R8WA01	General	0603	6.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R8BA01	General	0603	6.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R8CA01	General	0603	6.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R8DA01	General	0603	6.8	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R8WA01	General	0603	6.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R9BA01	General	0603	6.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R9CA01	General	0603	6.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R9DA01	General	0603	6.9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H6R9WA01	General	0603	6.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R9BA01	General	0603	6.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R9CA01	General	0603	6.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R9DA01	General	0603	6.9	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A6R9WA01	General	0603	6.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R0BA01	General	0603	7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R0CA01	General	0603	7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R0DA01	General	0603	7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R0WA01	General	0603	7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R0BA01	General	0603	7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R0CA01	General	0603	7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R0DA01	General	0603	7	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R0WA01	General	0603	7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R1BA01	General	0603	7.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R1CA01	General	0603	7.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R1DA01	General	0603	7.1	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R1WA01	General	0603	7.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R1BA01	General	0603	7.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R1CA01	General	0603	7.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R1DA01	General	0603	7.1	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R1WA01	General	0603	7.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R2BA01	General	0603	7.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R2CA01	General	0603	7.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R2DA01	General	0603	7.2	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R2WA01	General	0603	7.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R2BA01	General	0603	7.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R2CA01	General	0603	7.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1885C2A7R2DA01	General	0603	7.2	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R2WA01	General	0603	7.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R3BA01	General	0603	7.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R3CA01	General	0603	7.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R3DA01	General	0603	7.3	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R3WA01	General	0603	7.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R3BA01	General	0603	7.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R3CA01	General	0603	7.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R3DA01	General	0603	7.3	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R3WA01	General	0603	7.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R4BA01	General	0603	7.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R4CA01	General	0603	7.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R4DA01	General	0603	7.4	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R4WA01	General	0603	7.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R4BA01	General	0603	7.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R4CA01	General	0603	7.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R4DA01	General	0603	7.4	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R4WA01	General	0603	7.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R5BA01	General	0603	7.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R5CA01	General	0603	7.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R5DA01	General	0603	7.5	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R5WA01	General	0603	7.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R5BA01	General	0603	7.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R5CA01	General	0603	7.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R5DA01	General	0603	7.5	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R5WA01	General	0603	7.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R6BA01	General	0603	7.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R6CA01	General	0603	7.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R6DA01	General	0603	7.6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R6WA01	General	0603	7.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R6BA01	General	0603	7.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R6CA01	General	0603	7.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R6DA01	General	0603	7.6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R6WA01	General	0603	7.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R7BA01	General	0603	7.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R7CA01	General	0603	7.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R7DA01	General	0603	7.7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R7WA01	General	0603	7.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R7BA01	General	0603	7.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R7CA01	General	0603	7.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R7DA01	General	0603	7.7	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R7WA01	General	0603	7.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R8BA01	General	0603	7.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R8CA01	General	0603	7.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R8DA01	General	0603	7.8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R8WA01	General	0603	7.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R8BA01	General	0603	7.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R8CA01	General	0603	7.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R8DA01	General	0603	7.8	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R8WA01	General	0603	7.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R9BA01	General	0603	7.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R9CA01	General	0603	7.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R9DA01	General	0603	7.9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H7R9WA01	General	0603	7.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R9BA01	General	0603	7.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R9CA01	General	0603	7.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1885C2A7R9DA01	General	0603	7.9	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A7R9WA01	General	0603	7.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R0BA01	General	0603	8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R0CA01	General	0603	8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R0DA01	General	0603	8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R0WA01	General	0603	8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R0BA01	General	0603	8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R0CA01	General	0603	8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R0DA01	General	0603	8	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R0WA01	General	0603	8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R1BA01	General	0603	8.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R1CA01	General	0603	8.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R1DA01	General	0603	8.1	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R1WA01	General	0603	8.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R1BA01	General	0603	8.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R1CA01	General	0603	8.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R1DA01	General	0603	8.1	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R1WA01	General	0603	8.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R2BA01	General	0603	8.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R2CA01	General	0603	8.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R2DA01	General	0603	8.2	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R2WA01	General	0603	8.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R2BA01	General	0603	8.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R2CA01	General	0603	8.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R2DA01	General	0603	8.2	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R2WA01	General	0603	8.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R3BA01	General	0603	8.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R3CA01	General	0603	8.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R3DA01	General	0603	8.3	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R3WA01	General	0603	8.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R3BA01	General	0603	8.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R3CA01	General	0603	8.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R3DA01	General	0603	8.3	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R3WA01	General	0603	8.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R4BA01	General	0603	8.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R4CA01	General	0603	8.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R4DA01	General	0603	8.4	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R4WA01	General	0603	8.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R4BA01	General	0603	8.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R4CA01	General	0603	8.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R4DA01	General	0603	8.4	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R4WA01	General	0603	8.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R5BA01	General	0603	8.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R5CA01	General	0603	8.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R5DA01	General	0603	8.5	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R5WA01	General	0603	8.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R5BA01	General	0603	8.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R5CA01	General	0603	8.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R5DA01	General	0603	8.5	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R5WA01	General	0603	8.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R6BA01	General	0603	8.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R6CA01	General	0603	8.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R6DA01	General	0603	8.6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R6WA01	General	0603	8.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R6BA01	General	0603	8.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R6CA01	General	0603	8.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1885C2A8R6DA01	General	0603	8.6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R6WA01	General	0603	8.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R7BA01	General	0603	8.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R7CA01	General	0603	8.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R7DA01	General	0603	8.7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R7WA01	General	0603	8.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R7BA01	General	0603	8.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R7CA01	General	0603	8.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R7DA01	General	0603	8.7	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R7WA01	General	0603	8.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R8BA01	General	0603	8.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R8CA01	General	0603	8.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R8DA01	General	0603	8.8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R8WA01	General	0603	8.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R8BA01	General	0603	8.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R8CA01	General	0603	8.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R8DA01	General	0603	8.8	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R8WA01	General	0603	8.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R9BA01	General	0603	8.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R9CA01	General	0603	8.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R9DA01	General	0603	8.9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H8R9WA01	General	0603	8.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R9BA01	General	0603	8.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R9CA01	General	0603	8.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R9DA01	General	0603	8.9	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A8R9WA01	General	0603	8.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R0BA01	General	0603	9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R0CA01	General	0603	9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R0DA01	General	0603	9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R0WA01	General	0603	9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R0BA01	General	0603	9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R0CA01	General	0603	9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R0DA01	General	0603	9	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R0WA01	General	0603	9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R1BA01	General	0603	9.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R1CA01	General	0603	9.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R1DA01	General	0603	9.1	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R1WA01	General	0603	9.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R1BA01	General	0603	9.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R1CA01	General	0603	9.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R1DA01	General	0603	9.1	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R1WA01	General	0603	9.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R2BA01	General	0603	9.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R2CA01	General	0603	9.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R2DA01	General	0603	9.2	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R2WA01	General	0603	9.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R2BA01	General	0603	9.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R2CA01	General	0603	9.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R2DA01	General	0603	9.2	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R2WA01	General	0603	9.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R3BA01	General	0603	9.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R3CA01	General	0603	9.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R3DA01	General	0603	9.3	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R3WA01	General	0603	9.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R3BA01	General	0603	9.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R3CA01	General	0603	9.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1885C2A9R3DA01	General	0603	9.3	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R3WA01	General	0603	9.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R4BA01	General	0603	9.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R4CA01	General	0603	9.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R4DA01	General	0603	9.4	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R4WA01	General	0603	9.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R4BA01	General	0603	9.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R4CA01	General	0603	9.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R4DA01	General	0603	9.4	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R4WA01	General	0603	9.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R5BA01	General	0603	9.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R5CA01	General	0603	9.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R5DA01	General	0603	9.5	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R5WA01	General	0603	9.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R5BA01	General	0603	9.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R5CA01	General	0603	9.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R5DA01	General	0603	9.5	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R5WA01	General	0603	9.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R6BA01	General	0603	9.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R6CA01	General	0603	9.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R6DA01	General	0603	9.6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R6WA01	General	0603	9.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R6BA01	General	0603	9.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R6CA01	General	0603	9.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R6DA01	General	0603	9.6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R6WA01	General	0603	9.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R7BA01	General	0603	9.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R7CA01	General	0603	9.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R7DA01	General	0603	9.7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R7WA01	General	0603	9.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R7BA01	General	0603	9.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R7CA01	General	0603	9.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R7DA01	General	0603	9.7	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R7WA01	General	0603	9.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R8BA01	General	0603	9.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R8CA01	General	0603	9.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R8DA01	General	0603	9.8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R8WA01	General	0603	9.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R8BA01	General	0603	9.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R8CA01	General	0603	9.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R8DA01	General	0603	9.8	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R8WA01	General	0603	9.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R9BA01	General	0603	9.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R9CA01	General	0603	9.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R9DA01	General	0603	9.9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H9R9WA01	General	0603	9.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R9BA01	General	0603	9.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R9CA01	General	0603	9.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R9DA01	General	0603	9.9	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C2A9R9WA01	General	0603	9.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H100JA01	General	0603	10	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A100JA01	General	0603	10	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H120JA01	General	0603	12	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A120JA01	General	0603	12	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H150JA01	General	0603	15	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A150JA01	General	0603	15	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1885C1H180JA01	General	0603	18	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A180JA01	General	0603	18	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H220JA01	General	0603	22	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A220JA01	General	0603	22	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H270JA01	General	0603	27	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A270JA01	General	0603	27	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H330GA01	General	0603	33	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H330JA01	General	0603	33	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A330JA01	General	0603	33	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H390JA01	General	0603	39	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A390JA01	General	0603	39	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H470JA01	General	0603	47	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A470JA01	General	0603	47	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H560JA01	General	0603	56	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A560JA01	General	0603	56	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H680JA01	General	0603	68	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A680JA01	General	0603	68	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H820JA01	General	0603	82	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A820JA01	General	0603	82	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H101JA01	General	0603	100	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A101JA01	General	0603	100	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H121JA01	General	0603	120	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A121JA01	General	0603	120	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H151JA01	General	0603	150	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A151JA01	General	0603	150	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H181JA01	General	0603	180	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A181JA01	General	0603	180	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H221JA01	General	0603	220	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM188R71H221KA01	General	0603	220	+/-10[%]	50	X7R	500[kHz]-6[GHz]
GRM188R71H221MA01	General	0603	220	+/-20[%]	50	X7R	500[kHz]-6[GHz]
GRM1885C2A221JA01	General	0603	220	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM188R72A221KA01	General	0603	220	+/-10[%]	100	X7R	500[kHz]-6[GHz]
GRM188R72A221MA01	General	0603	220	+/-20[%]	100	X7R	500[kHz]-6[GHz]
GRM1885C1H271GA01	General	0603	270	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C1H271JA01	General	0603	270	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A271JA01	General	0603	270	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H331JA01	General	0603	330	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM188R71H331KA01	General	0603	330	+/-10[%]	50	X7R	1[MHz]-6[GHz]
GRM1885C2A331JA01	General	0603	330	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM188R72A331KA01	General	0603	330	+/-10[%]	100	X7R	1[MHz]-6[GHz]
GRM1885C1H391JA01	General	0603	390	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A391JA01	General	0603	390	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1H471JA01	General	0603	470	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM188R71H471KA01	General	0603	470	+/-10[%]	50	X7R	500[kHz]-6[GHz]
GRM188R71H471MA01	General	0603	470	+/-20[%]	50	X7R	500[kHz]-6[GHz]
GRM1885C2A471JA01	General	0603	470	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM188R72A471KA01	General	0603	470	+/-10[%]	100	X7R	500[kHz]-6[GHz]
GRM188R72A471MA01	General	0603	470	+/-20[%]	100	X7R	500[kHz]-6[GHz]
GRM1885C1E561JA01	General	0603	560	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1885C1H561JA01	General	0603	560	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A561JA01	General	0603	560	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1E681JA01	General	0603	680	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1885C1H681JA01	General	0603	680	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM188R71H681KA01	General	0603	680	+/-10[%]	50	X7R	1[MHz]-6[GHz]
GRM1885C2A681JA01	General	0603	680	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM188R72A681KA01	General	0603	680	+/-10[%]	100	X7R	1[MHz]-6[GHz]



Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1885C1E821JA01	General	0603	820	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GRM1885C1H821JA01	General	0603	820	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM1885C2A821JA01	General	0603	820	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM1885C1E102JA01	General	0603	1000	+/-5[%]	25	C0G	1[MHz]-6[GHz]
GRM188R71E102KA01	General	0603	1000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM1885C1H102JA01	General	0603	1000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM188R61H102KA01	General	0603	1000	+/-10[%]	50	X5R	100[kHz]-6[GHz]
GRM188R71H102KA01	General	0603	1000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM188R71H102MA01	General	0603	1000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
GRM1885C2A102JA01	General	0603	1000	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM188R72A102KA01	General	0603	1000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM188R72A102MA01	General	0603	1000	+/-20[%]	100	X7R	100[kHz]-6[GHz]
GRM1885C1H122JA01	General	0603	1200	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM1887U1H122JA01	General	0603	1200	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM1885C2A122JA01	General	0603	1200	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM1885C1E152JA01	General	0603	1500	+/-5[%]	25	C0G	1[MHz]-6[GHz]
GRM188R71E152KA01	General	0603	1500	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM1885C1H152JA01	General	0603	1500	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM1887U1H152JA01	General	0603	1500	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM188R71H152KA01	General	0603	1500	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM1885C2A152JA01	General	0603	1500	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM188R72A152KA01	General	0603	1500	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM1885C1H182JA01	General	0603	1800	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM1887U1H182JA01	General	0603	1800	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM188R71E222KA01	General	0603	2200	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM188R71E222MA01	General	0603	2200	+/-20[%]	25	X7R	100[kHz]-6[GHz]
GRM1885C1H222JA01	General	0603	2200	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM1857U1H222JA44	General	0603	2200	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM1887U1H222JA01	General	0603	2200	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM188R61H222KA01	General	0603	2200	+/-10[%]	50	X5R	100[kHz]-6[GHz]
GRM188R71H222KA01	General	0603	2200	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM188R71H222MA01	General	0603	2200	+/-20[%]	50	X7R	100[kHz]-6[GHz]
GRM188R72A222KA01	General	0603	2200	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM188R72A222MA01	General	0603	2200	+/-20[%]	100	X7R	100[kHz]-6[GHz]
GRM1885C1H272JA01	General	0603	2700	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM1857U1H272JA44	General	0603	2700	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM1887U1H272JA01	General	0603	2700	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM188R71E332KA01	General	0603	3300	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM1885C1H332JA01	General	0603	3300	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM1857U1H332JA44	General	0603	3300	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM1887U1H332JA01	General	0603	3300	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM188R71H332KA01	General	0603	3300	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM188R72A332KA01	General	0603	3300	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM1885C1H392JA01	General	0603	3900	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM1857U1H392JA44	General	0603	3900	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM1887U1H392JA01	General	0603	3900	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM188R71E472KA01	General	0603	4700	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM188R71E472MA01	General	0603	4700	+/-20[%]	25	X7R	100[kHz]-6[GHz]
GRM1885C1H472JA01	General	0603	4700	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM1857U1H472JA44	General	0603	4700	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM1887U1H472JA01	General	0603	4700	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM188R61H472KA01	General	0603	4700	+/-10[%]	50	X5R	100[kHz]-6[GHz]
GRM188R71H472KA01	General	0603	4700	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM188R71H472MA01	General	0603	4700	+/-20[%]	50	X7R	100[kHz]-6[GHz]
GRM188R72A472KA01	General	0603	4700	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM188R72A472MA01	General	0603	4700	+/-20[%]	100	X7R	100[kHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM1857U1A562JA44	General	0603	5600	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM1885C1H562JA01	General	0603	5600	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM1887U1H562JA01	General	0603	5600	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM188R71E682KA01	General	0603	6800	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM1885C1H682JA01	General	0603	6800	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM1887U1H682JA01	General	0603	6800	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM188R71H682KA01	General	0603	6800	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM188R72A682KA01	General	0603	6800	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM1857U1A822JA44	General	0603	8200	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM1885C1H822JA01	General	0603	8200	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM1887U1H822JA01	General	0603	8200	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM188R71H822KA01	General	0603	8200	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM1857U1A103JA44	General	0603	10000	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM188R71E103KA01	General	0603	10000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM188R71E103MA01	General	0603	10000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
GRM1885C1H103JA01	General	0603	10000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM1887U1H103JA01	General	0603	10000	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM188R61H103KA01	General	0603	10000	+/-10[%]	50	X5R	100[kHz]-6[GHz]
GRM188R71H103KA01	General	0603	10000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM188R71H103MA01	General	0603	10000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
GRM188R72A103KA01	General	0603	10000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM188R72A103MA01	General	0603	10000	+/-20[%]	100	X7R	100[kHz]-6[GHz]
GRM1887U1A123JA01	General	0603	12000	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM1887U1A153JA01	General	0603	15000	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM188R71E153KA01	General	0603	15000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM188R71H153KA01	General	0603	15000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM188R72A153KAC4	General	0603	15000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM188R72A153MAC4	General	0603	15000	+/-20[%]	100	X7R	100[kHz]-6[GHz]
GRM1887U1A183JA01	General	0603	18000	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM1887U1A223JA01	General	0603	22000	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM188R71E223KA01	General	0603	22000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM188R71E223MA01	General	0603	22000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
GRM188R61H223KA01	General	0603	22000	+/-10[%]	50	X5R	100[kHz]-6[GHz]
GRM188R71H223KA01	General	0603	22000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM188R71H223MA01	General	0603	22000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
GRM188R72A223KAC4	General	0603	22000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM188R72A223MAC4	General	0603	22000	+/-20[%]	100	X7R	100[kHz]-6[GHz]
GRM1887U0J333JA01	General	0603	33000	+/-5[%]	6.3	U2J	1[MHz]-6[GHz]
GRM1887U1A333JA01	General	0603	33000	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM188R71E333KA01	General	0603	33000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM188R71H333KA61	General	0603	33000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM188R71C473JA01	General	0603	47000	+/-5[%]	16	X7R	100[kHz]-6[GHz]
GRM188R71E473KA01	General	0603	47000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM188R71E473MA01	General	0603	47000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
GRM188R71H473KA61	General	0603	47000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM188R71H473MA61	General	0603	47000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
GRM188R71E683KA01	General	0603	68000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM188R71H683KA93	General	0603	68000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM188R70J104KA01	General	0603	100000	+/-10[%]	6.3	X7R	100[kHz]-6[GHz]
GRM188R61C104KA01	General	0603	100000	+/-10[%]	16	X5R	100[kHz]-6[GHz]
GRM188R71C104KA01	General	0603	100000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM188R61E104KA01	General	0603	100000	+/-10[%]	25	X5R	100[kHz]-6[GHz]
GRM188R71E104KA01	General	0603	100000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM188R71E104MA01	General	0603	100000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
GRM188R71H104KA93	General	0603	100000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM188R71H104MA93	General	0603	100000	+/-20[%]	50	X7R	100[kHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM188R72A104KA35	General	0603	100000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM188R72A104MA35	General	0603	100000	+/-20[%]	100	X7R	100[kHz]-6[GHz]
GRM188R71A154KA01	General	0603	150000	+/-10[%]	10	X7R	100[kHz]-6[GHz]
GRM188R71C154KA01	General	0603	150000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM188R71E154KA01	General	0603	150000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM188R70J224KA88	General	0603	220000	+/-10[%]	6.3	X7R	100[kHz]-6[GHz]
GRM188R61A224KA01	General	0603	220000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM188R71A224JA01	General	0603	220000	+/-5[%]	10	X7R	100[kHz]-6[GHz]
GRM188R71A224KA01	General	0603	220000	+/-10[%]	10	X7R	100[kHz]-6[GHz]
GRM188R61C224KA88	General	0603	220000	+/-10[%]	16	X5R	100[kHz]-6[GHz]
GRM188R71C224KA01	General	0603	220000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM188R71C224MA01	General	0603	220000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
GRM188R61E224KA88	General	0603	220000	+/-10[%]	25	X5R	100[kHz]-6[GHz]
GRM188R71E224KA88	General	0603	220000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM188R71E224MA88	General	0603	220000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
GRM188R61H224KAC4	General	0603	220000	+/-10[%]	50	X5R	100[kHz]-6[GHz]
GRM188R61A334KA61	General	0603	330000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM188R61A334MA61	General	0603	330000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM188R71A334KA61	General	0603	330000	+/-10[%]	10	X7R	100[kHz]-6[GHz]
GRM188R71A334MA61	General	0603	330000	+/-20[%]	10	X7R	100[kHz]-6[GHz]
GRM188R71C334KA01	General	0603	330000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM188R60J474KA01	General	0603	470000	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM188R70J474KA01	General	0603	470000	+/-10[%]	6.3	X7R	100[kHz]-6[GHz]
GRM188R61A474KA61	General	0603	470000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM188R71A474KA61	General	0603	470000	+/-10[%]	10	X7R	100[kHz]-6[GHz]
GRM188R71A474MA61	General	0603	470000	+/-20[%]	10	X7R	100[kHz]-6[GHz]
GRM188R61C474KA12	General	0603	470000	+/-10[%]	16	X5R	100[kHz]-6[GHz]
GRM188R61C474KA93	General	0603	470000	+/-10[%]	16	X5R	100[kHz]-6[GHz]
GRM188R61C474MA12	General	0603	470000	+/-20[%]	16	X5R	100[kHz]-6[GHz]
GRM188R61C474MA93	General	0603	470000	+/-20[%]	16	X5R	100[kHz]-6[GHz]
GRM188R71C474KA88	General	0603	470000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM188R71C474MA88	General	0603	470000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
GRM188R61E474KA12	General	0603	470000	+/-10[%]	25	X5R	100[kHz]-6[GHz]
GRM188R61E474MA12	General	0603	470000	+/-20[%]	25	X5R	100[kHz]-6[GHz]
GRM188R71E474KA12	General	0603	470000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM188R71E474MA12	General	0603	470000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
GRM188R61H474KA12	General	0603	470000	+/-10[%]	50	X5R	100[kHz]-6[GHz]
GRM188R61H474MA12	General	0603	470000	+/-20[%]	50	X5R	100[kHz]-6[GHz]
GRM188R61A684KA61	General	0603	680000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM188R61A684MA61	General	0603	680000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM188R71A684KA61	General	0603	680000	+/-10[%]	10	X7R	100[kHz]-6[GHz]
GRM188R71A684MA61	General	0603	680000	+/-20[%]	10	X7R	100[kHz]-6[GHz]
GRM188R61C684KA75	General	0603	680000	+/-10[%]	16	X5R	100[kHz]-6[GHz]
GRM188R61C684MA75	General	0603	680000	+/-20[%]	16	X5R	100[kHz]-6[GHz]
GRM188R61E684KA75	General	0603	680000	+/-10[%]	25	X5R	100[kHz]-6[GHz]
GRM188R61E684MA75	General	0603	680000	+/-20[%]	25	X5R	100[kHz]-6[GHz]
GRM188C80G105MA01	General	0603	1000000	+/-20[%]	4	X6S	100[Hz]-6[GHz]
GRM185R60J105KE26	General	0603	1000000	+/-10[%]	6.3	X5R	100[Hz]-6[GHz]
GRM188R60J105KA01	General	0603	1000000	+/-10[%]	6.3	X5R	100[Hz]-6[GHz]
GRM185C80J105KE26	General	0603	1000000	+/-10[%]	6.3	X6S	100[Hz]-6[GHz]
GRM188R70J105KA01	General	0603	1000000	+/-10[%]	6.3	X7R	100[Hz]-6[GHz]
GRM188R70J105MA01	General	0603	1000000	+/-20[%]	6.3	X7R	100[Hz]-6[GHz]
GRM188R61A105KA61	General	0603	1000000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM185C81A105KE36	General	0603	1000000	+/-10[%]	10	X6S	100[Hz]-6[GHz]
GRM188R71A105KA61	General	0603	1000000	+/-10[%]	10	X7R	100[Hz]-6[GHz]
GRM185D71A105KE36	General	0603	1000000	+/-10[%]	10	X7T	100[Hz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM185R61C105KE44	General	0603	1000000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM188R61C105KA12	General	0603	1000000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM188R61C105MA12	General	0603	1000000	+/-20[%]	16	X5R	100[Hz]-6[GHz]
GRM185R61C105ME44	General	0603	1000000	+/-20[%]	16	X5R	100[Hz]-6[GHz]
GRM188R61C105KA93	General	0603	1000000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM188C81C105KA12	General	0603	1000000	+/-10[%]	16	X6S	100[Hz]-6[GHz]
GRM188C81C105MA12	General	0603	1000000	+/-20[%]	16	X6S	100[Hz]-6[GHz]
GRM188R71C105KA12	General	0603	1000000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GRM188R71C105MA12	General	0603	1000000	+/-20[%]	16	X7R	100[Hz]-6[GHz]
GRM188R71C105KE15	General	0603	1000000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GRM188R71C105ME15	General	0603	1000000	+/-20[%]	16	X7R	100[Hz]-6[GHz]
GRM185R61E105KA12	General	0603	1000000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM185R61E105MA12	General	0603	1000000	+/-20[%]	25	X5R	100[Hz]-6[GHz]
GRM188R61E105KAAD	General	0603	1000000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM188R61E105KA12	General	0603	1000000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM188R61E105MA12	General	0603	1000000	+/-20[%]	25	X5R	100[Hz]-6[GHz]
GRM188C81E105KAAD	General	0603	1000000	+/-10[%]	25	X6S	100[Hz]-6[GHz]
GRM188C81E105MAAD	General	0603	1000000	+/-20[%]	25	X6S	100[Hz]-6[GHz]
GRM188R71E105KA12	General	0603	1000000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GRM188R71E105MA12	General	0603	1000000	+/-20[%]	25	X7R	100[Hz]-6[GHz]
GRM188R6YA105KA12	General	0603	1000000	+/-10[%]	35	X5R	100[Hz]-6[GHz]
GRM188R7YA105KA12	General	0603	1000000	+/-10[%]	35	X7R	100[Hz]-6[GHz]
GRM188R7YA105MA12	General	0603	1000000	+/-20[%]	35	X7R	100[Hz]-6[GHz]
GRM188R61H105KAAL	General	0603	1000000	+/-10[%]	50	X5R	100[Hz]-6[GHz]
GRM188R61H105MAAL	General	0603	1000000	+/-20[%]	50	X5R	100[Hz]-6[GHz]
GRM188C70G225KE20	General	0603	2200000	+/-10[%]	4	X7S	100[Hz]-6[GHz]
GRM188C70G225ME20	General	0603	2200000	+/-20[%]	4	X7S	100[Hz]-6[GHz]
GRM185R60J225KE26	General	0603	2200000	+/-10[%]	6.3	X5R	100[Hz]-6[GHz]
GRM188R60J225KE19	General	0603	2200000	+/-10[%]	6.3	X5R	100[Hz]-6[GHz]
GRM188C80J225KE19	General	0603	2200000	+/-10[%]	6.3	X6S	100[Hz]-6[GHz]
GRM188C80J225ME19	General	0603	2200000	+/-20[%]	6.3	X6S	100[Hz]-6[GHz]
GRM188C70J225KE20	General	0603	2200000	+/-10[%]	6.3	X7S	100[Hz]-6[GHz]
GRM188C70J225ME20	General	0603	2200000	+/-20[%]	6.3	X7S	100[Hz]-6[GHz]
GRM188R61A225KE34	General	0603	2200000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM188R61A225ME34	General	0603	2200000	+/-20[%]	10	X5R	100[Hz]-6[GHz]
GRM188C81A225KAAD	General	0603	2200000	+/-10[%]	10	X6S	100[Hz]-6[GHz]
GRM188C81A225KE34	General	0603	2200000	+/-10[%]	10	X6S	100[Hz]-6[GHz]
GRM188C81A225ME34	General	0603	2200000	+/-20[%]	10	X6S	100[Hz]-6[GHz]
GRM188R71A225KE15	General	0603	2200000	+/-10[%]	10	X7R	100[Hz]-6[GHz]
GRM188R71A225ME15	General	0603	2200000	+/-20[%]	10	X7R	100[Hz]-6[GHz]
GRM188D71A225KE34	General	0603	2200000	+/-10[%]	10	X7T	100[Hz]-6[GHz]
GRM188D71A225ME34	General	0603	2200000	+/-20[%]	10	X7T	100[Hz]-6[GHz]
GRM188R61C225KAAD	General	0603	2200000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM188R61C225KE15	General	0603	2200000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM188C81C225KA12	General	0603	2200000	+/-10[%]	16	X6S	100[Hz]-6[GHz]
GRM188C81C225MA12	General	0603	2200000	+/-20[%]	16	X6S	100[Hz]-6[GHz]
GRM188C71C225KE11	General	0603	2200000	+/-10[%]	16	X7S	100[Hz]-6[GHz]
GRM188C71C225ME11	General	0603	2200000	+/-20[%]	16	X7S	100[Hz]-6[GHz]
GRM188R61E225KA12	General	0603	2200000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM188R61E225MA12	General	0603	2200000	+/-20[%]	25	X5R	100[Hz]-6[GHz]
GRM188C81E225KE11	General	0603	2200000	+/-10[%]	25	X6S	100[Hz]-6[GHz]
GRM188C81E225ME11	General	0603	2200000	+/-20[%]	25	X6S	100[Hz]-6[GHz]
GRM188C71E225KE11	General	0603	2200000	+/-10[%]	25	X7S	100[Hz]-6[GHz]
GRM188C71E225ME11	General	0603	2200000	+/-20[%]	25	X7S	100[Hz]-6[GHz]
GRM188C8YA225KE11	General	0603	2200000	+/-10[%]	35	X6S	100[Hz]-6[GHz]
GRM188C8YA225ME11	General	0603	2200000	+/-20[%]	35	X6S	100[Hz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM188R61H225KE11	General	0603	2200000	+/-10[%]	50	X5R	100[Hz]-6[GHz]
GRM188R61H225ME11	General	0603	2200000	+/-20[%]	50	X5R	100[Hz]-6[GHz]
GRM188C80G475KE19	General	0603	4700000	+/-10[%]	4	X6S	100[Hz]-6[GHz]
GRM188C80G475ME19	General	0603	4700000	+/-20[%]	4	X6S	100[Hz]-6[GHz]
GRM188R60J475KE19	General	0603	4700000	+/-10[%]	6.3	X5R	100[Hz]-6[GHz]
GRM188R60J475ME19	General	0603	4700000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM188R60J475ME84	General	0603	4700000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM188C80J475KE15	General	0603	4700000	+/-10[%]	6.3	X6S	100[Hz]-6[GHz]
GRM188C80J475ME15	General	0603	4700000	+/-20[%]	6.3	X6S	100[Hz]-6[GHz]
GRM188R61A475KAAJ	General	0603	4700000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM188R61A475KE15	General	0603	4700000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM188R61A475MAAJ	General	0603	4700000	+/-20[%]	10	X5R	100[Hz]-6[GHz]
GRM188R61A475ME15	General	0603	4700000	+/-20[%]	10	X5R	100[Hz]-6[GHz]
GRM188C71A475KE11	General	0603	4700000	+/-10[%]	10	X7S	100[Hz]-6[GHz]
GRM188C71A475ME11	General	0603	4700000	+/-20[%]	10	X7S	100[Hz]-6[GHz]
GRM188R61C475KAAJ	General	0603	4700000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM188R61C475MAAJ	General	0603	4700000	+/-20[%]	16	X5R	100[Hz]-6[GHz]
GRM188R61C475KE11	General	0603	4700000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM188R61C475ME11	General	0603	4700000	+/-20[%]	16	X5R	100[Hz]-6[GHz]
GRM188C81C475KE11	General	0603	4700000	+/-10[%]	16	X6S	100[Hz]-6[GHz]
GRM188C81C475ME11	General	0603	4700000	+/-20[%]	16	X6S	100[Hz]-6[GHz]
GRM188R61E475KE15	General	0603	4700000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM188R61E475ME15	General	0603	4700000	+/-20[%]	25	X5R	100[Hz]-6[GHz]
GRM188R61E475KE11	General	0603	4700000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM188R61E475ME11	General	0603	4700000	+/-20[%]	25	X5R	100[Hz]-6[GHz]
GRM188C81E475KE11	General	0603	4700000	+/-10[%]	25	X6S	100[Hz]-6[GHz]
GRM188C81E475ME11	General	0603	4700000	+/-20[%]	25	X6S	100[Hz]-6[GHz]
GRM188R6YA475KE15	General	0603	4700000	+/-10[%]	35	X5R	100[Hz]-6[GHz]
GRM188R6YA475ME15	General	0603	4700000	+/-20[%]	35	X5R	100[Hz]-6[GHz]
GRM188C80E106ME47	General	0603	10000000	+/-20[%]	2.5	X6S	100[Hz]-6[GHz]
GRM188R60G106ME47	General	0603	10000000	+/-20[%]	4	X5R	100[Hz]-6[GHz]
GRM188C80G106ME47	General	0603	10000000	+/-20[%]	4	X6S	100[Hz]-6[GHz]
GRM188R60J106ME47	General	0603	10000000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM188R60J106ME84	General	0603	10000000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM188D70J106MA73	General	0603	10000000	+/-20[%]	6.3	X7T	100[Hz]-6[GHz]
GRM188R61A106KE69	General	0603	10000000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM188R61A106ME69	General	0603	10000000	+/-20[%]	10	X5R	100[Hz]-6[GHz]
GRM188C81A106MA73	General	0603	10000000	+/-20[%]	10	X6S	100[Hz]-6[GHz]
GRM188D71A106MA73	General	0603	10000000	+/-20[%]	10	X7T	100[Hz]-6[GHz]
GRM188R61C106MA73	General	0603	10000000	+/-20[%]	16	X5R	100[Hz]-6[GHz]
GRM188R61C106KAAL	General	0603	10000000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM188R61C106MAAL	General	0603	10000000	+/-20[%]	16	X5R	100[Hz]-6[GHz]
GRM188C81C106MA73	General	0603	10000000	+/-20[%]	16	X6S	100[Hz]-6[GHz]
GRM188R61E106MA73	General	0603	10000000	+/-20[%]	25	X5R	100[Hz]-6[GHz]
GRM188R60G226MEA0	General	0603	22000000	+/-20[%]	4	X5R	100[Hz]-6[GHz]
GRM188C80G226MEA0	General	0603	22000000	+/-20[%]	4	X6S	100[Hz]-6[GHz]
GRM188R60J226MEA0	General	0603	22000000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM188C60J226MEA0	General	0603	22000000	+/-20[%]	6.3	X5S	100[Hz]-6[GHz]
GRM2165C2A101JA01	General	0805	100	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM2165C2A121JA01	General	0805	120	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM2165C2A151JA01	General	0805	150	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM2165C2A181JA01	General	0805	180	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM2165C2A221JA01	General	0805	220	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM2165C2A271JA01	General	0805	270	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM2165C2A331JA01	General	0805	330	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM2165C2A391JA01	General	0805	390	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM2165C2A471JA01	General	0805	470	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM2165C2A561JA01	General	0805	560	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM2165C2A681JA01	General	0805	680	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM2165C2A821JA01	General	0805	820	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM2165C1H102JA01	General	0805	1000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM2165C2A102JA01	General	0805	1000	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM2165C1H122JA01	General	0805	1200	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM2165C2A122JA01	General	0805	1200	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM2165C1H152JA01	General	0805	1500	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM2165C2A152JA01	General	0805	1500	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM2165C1H182JA01	General	0805	1800	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM2165C2A182JA01	General	0805	1800	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM2165C1H222JA01	General	0805	2200	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM2165C2A222JA01	General	0805	2200	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM2165C1H272JA01	General	0805	2700	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM2165C2A272JA01	General	0805	2700	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM2165C1H332JA01	General	0805	3300	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM2165C2A332JA01	General	0805	3300	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM2165C1H392JA01	General	0805	3900	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM2165C1H472JA01	General	0805	4700	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM2195C1H562JA01	General	0805	5600	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM2195C1H682JA01	General	0805	6800	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM219R72A682KA01	General	0805	6800	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM2195C1H822JA01	General	0805	8200	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM2195C1H103JA01	General	0805	10000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM2167U1H103JA01	General	0805	10000	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM219R71H103KA01	General	0805	10000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM219R71H103MA01	General	0805	10000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
GRM21BR72A103KA01	General	0805	10000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM21BR72A103MA01	General	0805	10000	+/-20[%]	100	X7R	100[kHz]-6[GHz]
GRM219R72A103KA01	General	0805	10000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM219R72A103MA01	General	0805	10000	+/-20[%]	100	X7R	100[kHz]-6[GHz]
GRM2195C1H123JA01	General	0805	12000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM2167U1H123JA01	General	0805	12000	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM2195C1H153JA01	General	0805	15000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM2167U1H153JA01	General	0805	15000	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM219R71H153KA01	General	0805	15000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM219R71H153MA01	General	0805	15000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
GRM21BR72A153KA01	General	0805	15000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM21B5C1H183JA01	General	0805	18000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM2167U1H183JA01	General	0805	18000	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM2167U1A223JA01	General	0805	22000	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM21B5C1H223JA01	General	0805	22000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM2197U1H223JA01	General	0805	22000	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM219R71H223KA17	General	0805	22000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM219R71H223MA17	General	0805	22000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
GRM21BR72A223KA01	General	0805	22000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM21BR72A223MA01	General	0805	22000	+/-20[%]	100	X7R	100[kHz]-6[GHz]
GRM2197U1H273JA01	General	0805	27000	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM2167U1A333JA01	General	0805	33000	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM21A7U1H333JA39	General	0805	33000	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM219R71H333KA01	General	0805	33000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM21BR72A333KA01	General	0805	33000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM21B7U1H393JA01	General	0805	39000	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM2197U1A473JA01	General	0805	47000	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM21B7U1H473JA01	General	0805	47000	+/-5[%]	50	U2J	1[MHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM21BR71H473KA01	General	0805	47000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM21BR71H473MA01	General	0805	47000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
GRM21BR72A473KA01	General	0805	47000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM21BR72A473MA01	General	0805	47000	+/-20[%]	100	X7R	100[kHz]-6[GHz]
GRM2197U1A563JA01	General	0805	56000	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM21B7U1A683JA01	General	0805	68000	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM219R71E683KA01	General	0805	68000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM21BR71H683KA01	General	0805	68000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM21BR72A683KAC4	General	0805	68000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM21BR72A683MAC4	General	0805	68000	+/-20[%]	100	X7R	100[kHz]-6[GHz]
GRM21B7U1A823JA01	General	0805	82000	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM21B7U1A104JA01	General	0805	100000	+/-5[%]	10	U2J	1[MHz]-6[GHz]
GRM21BR71E104KA01	General	0805	100000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM21BR71E104MA01	General	0805	100000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
GRM219R71E104KA01	General	0805	100000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM219R71E104MA01	General	0805	100000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
GRM21BR71H104KA01	General	0805	100000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM21BR71H104MA01	General	0805	100000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
GRM21BR72A104KAC4	General	0805	100000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM21BR72A104MAC4	General	0805	100000	+/-20[%]	100	X7R	100[kHz]-6[GHz]
GRM21BR71E154KA01	General	0805	150000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM21BR71H154KA01	General	0805	150000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM21BR71C224KA01	General	0805	220000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM21BR71C224MA01	General	0805	220000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
GRM21BR71E224KA01	General	0805	220000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM21BR71E224MA01	General	0805	220000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
GRM21BR71H224KA01	General	0805	220000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM21BR71H224MA01	General	0805	220000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
GRM21AR72A224KAC5	General	0805	220000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM21AR72A224MAC5	General	0805	220000	+/-20[%]	100	X7R	100[kHz]-6[GHz]
GRM219R71C334KA88	General	0805	330000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM21BR71E334KA01	General	0805	330000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM219R71H334KA88	General	0805	330000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM21AR72A334KAC5	General	0805	330000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM21BR71C474MA01	General	0805	470000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
GRM219R71E474KA88	General	0805	470000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM219R71E474MA88	General	0805	470000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
GRM21BR71H474KA88	General	0805	470000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM21BR71H474MA88	General	0805	470000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
GRM21BR72A474KA73	General	0805	470000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM21BR72A474MA73	General	0805	470000	+/-20[%]	100	X7R	100[kHz]-6[GHz]
GRM219R71C684KA01	General	0805	680000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM219R71E684KA88	General	0805	680000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM219R61A105KA01	General	0805	1000000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM21BR61A105KA01	General	0805	1000000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM21BR71A105KA01	General	0805	1000000	+/-10[%]	10	X7R	100[Hz]-6[GHz]
GRM216R61C105KA88	General	0805	1000000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM21BR61C105KA01	General	0805	1000000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM216C81C105KA12	General	0805	1000000	+/-10[%]	16	X6S	100[Hz]-6[GHz]
GRM21BR71C105KA01	General	0805	1000000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GRM216D71C105KA12	General	0805	1000000	+/-10[%]	16	X7T	100[Hz]-6[GHz]
GRM216D71C105MA12	General	0805	1000000	+/-20[%]	16	X7T	100[Hz]-6[GHz]
GRM216R61E105KA12	General	0805	1000000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM219R71E105KA88	General	0805	1000000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GRM21BR71E105KA99	General	0805	1000000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GRM219R7YA105KA12	General	0805	1000000	+/-10[%]	35	X7R	100[Hz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM219R61H105KA73	General	0805	1000000	+/-10[%]	50	X5R	100[Hz]-6[GHz]
GRM219R61H105MA73	General	0805	1000000	+/-20[%]	50	X5R	100[Hz]-6[GHz]
GRM21BR61H105KA12	General	0805	1000000	+/-10[%]	50	X5R	100[Hz]-6[GHz]
GJ821BR71H105KA12	General	0805	1000000	+/-10[%]	50	X7R	100[Hz]-6[GHz]
GRM21BR71H105KA12	General	0805	1000000	+/-10[%]	50	X7R	100[Hz]-6[GHz]
GRM21BR60J225KA01	General	0805	2200000	+/-10[%]	6.3	X5R	100[Hz]-6[GHz]
GRM21BR70J225KA01	General	0805	2200000	+/-10[%]	6.3	X7R	100[Hz]-6[GHz]
GRM219R61A225KA01	General	0805	2200000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM21BR61A225KA01	General	0805	2200000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM21BR61A225MA01	General	0805	2200000	+/-20[%]	10	X5R	100[Hz]-6[GHz]
GRM21BR71A225KA01	General	0805	2200000	+/-10[%]	10	X7R	100[Hz]-6[GHz]
GRM21BR71A225MA01	General	0805	2200000	+/-20[%]	10	X7R	100[Hz]-6[GHz]
GRM219R71A225KE15	General	0805	2200000	+/-10[%]	10	X7R	100[Hz]-6[GHz]
GRM219R71A225ME15	General	0805	2200000	+/-20[%]	10	X7R	100[Hz]-6[GHz]
GRM219R61C225KA88	General	0805	2200000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM21BR61C225KA88	General	0805	2200000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM219C81C225KA12	General	0805	2200000	+/-10[%]	16	X6S	100[Hz]-6[GHz]
GRM21BR71C225KA12	General	0805	2200000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GRM219R71C225KE15	General	0805	2200000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GRM21BR71C225MA12	General	0805	2200000	+/-20[%]	16	X7R	100[Hz]-6[GHz]
GRM219R71C225ME15	General	0805	2200000	+/-20[%]	16	X7R	100[Hz]-6[GHz]
GRM219D71C225KA12	General	0805	2200000	+/-10[%]	16	X7T	100[Hz]-6[GHz]
GRM219D71C225MA12	General	0805	2200000	+/-20[%]	16	X7T	100[Hz]-6[GHz]
GRM219R61E225KA12	General	0805	2200000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM21BR61E225KA12	General	0805	2200000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM219R61E225MA12	General	0805	2200000	+/-20[%]	25	X5R	100[Hz]-6[GHz]
GRM219C81E225KE15	General	0805	2200000	+/-10[%]	25	X6S	100[Hz]-6[GHz]
GRM219C81E225ME15	General	0805	2200000	+/-20[%]	25	X6S	100[Hz]-6[GHz]
GRM21BR71E225KA73	General	0805	2200000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GRM21BC8YA225KA73	General	0805	2200000	+/-10[%]	35	X6S	100[Hz]-6[GHz]
GRM21BC8YA225MA73	General	0805	2200000	+/-20[%]	35	X6S	100[Hz]-6[GHz]
GRM219C8YA225KE15	General	0805	2200000	+/-10[%]	35	X6S	100[Hz]-6[GHz]
GRM219C8YA225ME15	General	0805	2200000	+/-20[%]	35	X6S	100[Hz]-6[GHz]
GRM21BR61H225KA73	General	0805	2200000	+/-10[%]	50	X5R	100[Hz]-6[GHz]
GRM21BR61H225MA73	General	0805	2200000	+/-20[%]	50	X5R	100[Hz]-6[GHz]
GRM219R61H225KE15	General	0805	2200000	+/-10[%]	50	X5R	100[Hz]-6[GHz]
GRM219R61H225ME15	General	0805	2200000	+/-20[%]	50	X5R	100[Hz]-6[GHz]
GRM219R61A335KE19	General	0805	3300000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM219R60J475KE19	General	0805	4700000	+/-10[%]	6.3	X5R	100[Hz]-6[GHz]
GRM21BR60J475KA11	General	0805	4700000	+/-10[%]	6.3	X5R	100[Hz]-6[GHz]
GRM21BR60J475MA11	General	0805	4700000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM219C80J475KE19	General	0805	4700000	+/-10[%]	6.3	X6S	100[Hz]-6[GHz]
GRM219R61A475KE34	General	0805	4700000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM21BR61A475KA73	General	0805	4700000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM219R61A475ME34	General	0805	4700000	+/-20[%]	10	X5R	100[Hz]-6[GHz]
GRM21BR61A475MA73	General	0805	4700000	+/-20[%]	10	X5R	100[Hz]-6[GHz]
GRM219C81A475KE34	General	0805	4700000	+/-10[%]	10	X6S	100[Hz]-6[GHz]
GRM219C81A475ME34	General	0805	4700000	+/-20[%]	10	X6S	100[Hz]-6[GHz]
GRM21BR71A475KA73	General	0805	4700000	+/-10[%]	10	X7R	100[Hz]-6[GHz]
GRM21BR71A475MA73	General	0805	4700000	+/-20[%]	10	X7R	100[Hz]-6[GHz]
GRM219D71A475KE15	General	0805	4700000	+/-10[%]	10	X7T	100[Hz]-6[GHz]
GRM219D71A475ME15	General	0805	4700000	+/-20[%]	10	X7T	100[Hz]-6[GHz]
GRM219R61C475KE15	General	0805	4700000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM21BR61C475KA88	General	0805	4700000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM21BC81C475KA88	General	0805	4700000	+/-10[%]	16	X6S	100[Hz]-6[GHz]
GRM219C81C475KA73	General	0805	4700000	+/-10[%]	16	X6S	100[Hz]-6[GHz]



Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM219C81C475MA73	General	0805	4700000	+/-20[%]	16	X6S	100[Hz]-6[GHz]
GRM21BR71C475KA73	General	0805	4700000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GRM21BR71C475MA73	General	0805	4700000	+/-20[%]	16	X7R	100[Hz]-6[GHz]
GRM21BD71C475KA12	General	0805	4700000	+/-10[%]	16	X7T	100[Hz]-6[GHz]
GRM21BD71C475MA12	General	0805	4700000	+/-20[%]	16	X7T	100[Hz]-6[GHz]
GRM21BE71C475KA12	General	0805	4700000	+/-10[%]	16	X7U	100[Hz]-6[GHz]
GRM21BE71C475MA12	General	0805	4700000	+/-20[%]	16	X7U	100[Hz]-6[GHz]
GRM21BR61E475KA12	General	0805	4700000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM219R61E475KA73	General	0805	4700000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM219R61E475MA73	General	0805	4700000	+/-20[%]	25	X5R	100[Hz]-6[GHz]
GRM21BR61E475MA12	General	0805	4700000	+/-20[%]	25	X5R	100[Hz]-6[GHz]
GRM21BC81E475KA12	General	0805	4700000	+/-10[%]	25	X6S	100[Hz]-6[GHz]
GRM21BC81E475MA12	General	0805	4700000	+/-20[%]	25	X6S	100[Hz]-6[GHz]
GRM21BR71E475KA73	General	0805	4700000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GRM21BR71E475MA73	General	0805	4700000	+/-20[%]	25	X7R	100[Hz]-6[GHz]
GRM219R6YA475KA73	General	0805	4700000	+/-10[%]	35	X5R	100[Hz]-6[GHz]
GRM219R6YA475MA73	General	0805	4700000	+/-20[%]	35	X5R	100[Hz]-6[GHz]
GRM21BR61H475KE51	General	0805	4700000	+/-10[%]	50	X5R	100[Hz]-6[GHz]
GRM21BR61H475ME51	General	0805	4700000	+/-20[%]	50	X5R	100[Hz]-6[GHz]
GRM219C80G106KE19	General	0805	10000000	+/-10[%]	4	X6S	100[Hz]-6[GHz]
GRM21BC80G106ME19	General	0805	10000000	+/-20[%]	4	X6S	100[Hz]-6[GHz]
GRM219C80G106ME19	General	0805	10000000	+/-20[%]	4	X6S	100[Hz]-6[GHz]
GRM21BC70G106KE45	General	0805	10000000	+/-10[%]	4	X7S	100[Hz]-6[GHz]
GRM219R60J106KE19	General	0805	10000000	+/-10[%]	6.3	X5R	100[Hz]-6[GHz]
GRM21BR60J106KE19	General	0805	10000000	+/-10[%]	6.3	X5R	100[Hz]-6[GHz]
GRM219R60J106ME19	General	0805	10000000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM21BR60J106ME19	General	0805	10000000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM219C80J106KE39	General	0805	10000000	+/-10[%]	6.3	X6S	100[Hz]-6[GHz]
GRM21BC80J106KE19	General	0805	10000000	+/-10[%]	6.3	X6S	100[Hz]-6[GHz]
GRM219C80J106ME39	General	0805	10000000	+/-20[%]	6.3	X6S	100[Hz]-6[GHz]
GRM21BC80J106ME19	General	0805	10000000	+/-20[%]	6.3	X6S	100[Hz]-6[GHz]
GRM21BR70J106KE76	General	0805	10000000	+/-10[%]	6.3	X7R	100[Hz]-6[GHz]
GRM21BR70J106ME76	General	0805	10000000	+/-20[%]	6.3	X7R	100[Hz]-6[GHz]
GRM219R61A106KE44	General	0805	10000000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM219R61A106ME47	General	0805	10000000	+/-20[%]	10	X5R	100[Hz]-6[GHz]
GRM21BR61A106KE19	General	0805	10000000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM219R61A106ME44	General	0805	10000000	+/-20[%]	10	X5R	100[Hz]-6[GHz]
GRM21BR61A106ME19	General	0805	10000000	+/-20[%]	10	X5R	100[Hz]-6[GHz]
GRM21BC81A106KE18	General	0805	10000000	+/-10[%]	10	X6S	100[Hz]-6[GHz]
GRM21BC81A106ME18	General	0805	10000000	+/-20[%]	10	X6S	100[Hz]-6[GHz]
GRM21BR71A106KA73	General	0805	10000000	+/-10[%]	10	X7R	100[Hz]-6[GHz]
GRM21BR71A106KE51	General	0805	10000000	+/-10[%]	10	X7R	100[Hz]-6[GHz]
GRM21BR71A106MA73	General	0805	10000000	+/-20[%]	10	X7R	100[Hz]-6[GHz]
GRM21BR71A106ME51	General	0805	10000000	+/-20[%]	10	X7R	100[Hz]-6[GHz]
GRM219R61C106KA73	General	0805	10000000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM219R61C106MA73	General	0805	10000000	+/-20[%]	16	X5R	100[Hz]-6[GHz]
GRM21BR61C106KE15	General	0805	10000000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM21BR61C106ME15	General	0805	10000000	+/-20[%]	16	X5R	100[Hz]-6[GHz]
GRM21BC81C106KA73	General	0805	10000000	+/-10[%]	16	X6S	100[Hz]-6[GHz]
GRM21BC81C106KE15	General	0805	10000000	+/-10[%]	16	X6S	100[Hz]-6[GHz]
GRM21BC81C106MA73	General	0805	10000000	+/-20[%]	16	X6S	100[Hz]-6[GHz]
GRM21BC81C106ME15	General	0805	10000000	+/-20[%]	16	X6S	100[Hz]-6[GHz]
GRM21BC71C106KE11	General	0805	10000000	+/-10[%]	16	X7S	100[Hz]-6[GHz]
GRM21BC71C106ME11	General	0805	10000000	+/-20[%]	16	X7S	100[Hz]-6[GHz]
GRM21BR61D106KE15	General	0805	10000000	+/-10[%]	20	X5R	100[Hz]-6[GHz]
GRM21BR61D106ME15	General	0805	10000000	+/-20[%]	20	X5R	100[Hz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM21BR61E106KA73	General	0805	10000000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM21BR61E106MA73	General	0805	10000000	+/-20[%]	25	X5R	100[Hz]-6[GHz]
GRM219R61E106KA12	General	0805	10000000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM219R61E106MA12	General	0805	10000000	+/-20[%]	25	X5R	100[Hz]-6[GHz]
GRM21BC81E106KE11	General	0805	10000000	+/-10[%]	25	X6S	100[Hz]-6[GHz]
GRM21BC81E106ME11	General	0805	10000000	+/-20[%]	25	X6S	100[Hz]-6[GHz]
GRM219R60G226ME66	General	0805	22000000	+/-20[%]	4	X5R	100[Hz]-6[GHz]
GRM21BC80G226ME39	General	0805	22000000	+/-20[%]	4	X6S	100[Hz]-6[GHz]
GRM21BE70G226ME51	General	0805	22000000	+/-20[%]	4	X7U	100[Hz]-6[GHz]
GRM219R60J226ME47	General	0805	22000000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM219R60J226MEA0	General	0805	22000000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM21BR60J226ME39	General	0805	22000000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM21BC80J226ME51	General	0805	22000000	+/-20[%]	6.3	X6S	100[Hz]-6[GHz]
GRM21BD70J226ME44	General	0805	22000000	+/-20[%]	6.3	X7T	100[Hz]-6[GHz]
GRM219R61A226MEA0	General	0805	22000000	+/-20[%]	10	X5R	100[Hz]-6[GHz]
GRM21BR61A226ME51	General	0805	22000000	+/-20[%]	10	X5R	100[Hz]-6[GHz]
GRM21BR61A226ME44	General	0805	22000000	+/-20[%]	10	X5R	100[Hz]-6[GHz]
GRM21BC81A226ME44	General	0805	22000000	+/-20[%]	10	X6S	100[Hz]-6[GHz]
GRM21BD71A226ME44	General	0805	22000000	+/-20[%]	10	X7T	100[Hz]-6[GHz]
GRM21BR61C226ME44	General	0805	22000000	+/-20[%]	16	X5R	100[Hz]-6[GHz]
GRM219R61C226ME15	General	0805	22000000	+/-20[%]	16	X5R	100[Hz]-6[GHz]
GRM21BC81C226ME44	General	0805	22000000	+/-20[%]	16	X6S	100[Hz]-6[GHz]
GRM21BR61E226ME44	General	0805	22000000	+/-20[%]	25	X5R	100[Hz]-6[GHz]
GRM219D80E476ME44	General	0805	47000000	+/-20[%]	2.5	X6T	100[Hz]-6[GHz]
GRM219R60G476ME44	General	0805	47000000	+/-20[%]	4	X5R	100[Hz]-6[GHz]
GRM21BR60G476ME15	General	0805	47000000	+/-20[%]	4	X5R	100[Hz]-6[GHz]
GRM21BC80G476ME15	General	0805	47000000	+/-20[%]	4	X6S	100[Hz]-6[GHz]
GRM21BR60J476ME15	General	0805	47000000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM21BR61A476ME15	General	0805	47000000	+/-20[%]	10	X5R	100[Hz]-6[GHz]
GRM3195C2A182JA01	General	1206	1800	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM3195C2A222JA01	General	1206	2200	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM319R72A222KA01	General	1206	2200	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM3195C2A272JA01	General	1206	2700	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM3195C2A332JA01	General	1206	3300	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM3195C2A392JA01	General	1206	3900	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM3195C1H472JA01	General	1206	4700	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM3195C2A472JA01	General	1206	4700	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM3195C1H562JA01	General	1206	5600	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM3195C2A562JA01	General	1206	5600	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM3195C1H682JA01	General	1206	6800	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM3195C2A682JA01	General	1206	6800	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM3195C1H822JA01	General	1206	8200	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM3195C2A822JA01	General	1206	8200	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM3195C1H103JA01	General	1206	10000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM3195C2A103JA01	General	1206	10000	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM3195C1H123JA01	General	1206	12000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM3195C2A123JA01	General	1206	12000	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM3195C1H153JA01	General	1206	15000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM3195C2A153JA01	General	1206	15000	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM319R72A153KA01	General	1206	15000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM3195C1H183JA01	General	1206	18000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM3195C2A183JA01	General	1206	18000	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM3195C1H223JA01	General	1206	22000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM3195C2A223JA01	General	1206	22000	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GRM31MR72A223KA01	General	1206	22000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM31MR72A223MA01	General	1206	22000	+/-20[%]	100	X7R	100[kHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM3195C1H273JA01	General	1206	27000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM3195C1H333JA01	General	1206	33000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM31MR72A333KA01	General	1206	33000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM31M5C1H393JA01	General	1206	39000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM3195C1H393JA01	General	1206	39000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM31M5C1H473JA01	General	1206	47000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM31MR72A473KA01	General	1206	47000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM31MR72A473MA01	General	1206	47000	+/-20[%]	100	X7R	100[kHz]-6[GHz]
GRM31M5C1H563JA01	General	1206	56000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM3197U1H563JA01	General	1206	56000	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM31C5C1H683JA01	General	1206	68000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM31M7U1H683JA01	General	1206	68000	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM31C7U2A683JA01	General	1206	68000	+/-5[%]	100	U2J	1[MHz]-6[GHz]
GRM31MR72A683KA01	General	1206	68000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM31C5C1H823JA01	General	1206	82000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM31M7U1H823JA01	General	1206	82000	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM31C5C1H104JA01	General	1206	100000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GRM31M7U1H104JA01	General	1206	100000	+/-5[%]	50	U2J	1[MHz]-6[GHz]
GRM319R71H104JA01	General	1206	100000	+/-5[%]	50	X7R	100[kHz]-6[GHz]
GRM31C7U2A104JA01	General	1206	100000	+/-5[%]	100	U2J	1[MHz]-6[GHz]
GRM319R72A104KA01	General	1206	100000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM31MR71H154KA01	General	1206	150000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM31MR72A154KA01	General	1206	150000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM31MR71H224KA01	General	1206	220000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM31MR71H224MA01	General	1206	220000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
GRM31MR72A224KA01	General	1206	220000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM319R71E334KA01	General	1206	330000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM319R71H334KA01	General	1206	330000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM319R71E474KA01	General	1206	470000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM31MR71E474KA01	General	1206	470000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM31MR71H474KA01	General	1206	470000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM31MR71H474MA01	General	1206	470000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
GRM31MR72A474KA35	General	1206	470000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM31MR72A474MA35	General	1206	470000	+/-20[%]	100	X7R	100[kHz]-6[GHz]
GRM31MR71H684KA88	General	1206	680000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM31MR72A684KA35	General	1206	680000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM319R61A105KA01	General	1206	1000000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM319R71A105KA01	General	1206	1000000	+/-10[%]	10	X7R	100[Hz]-6[GHz]
GRM319R61C105KAA3	General	1206	1000000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM31MR61C105KA01	General	1206	1000000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM319R71C105KAA3	General	1206	1000000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GRM31MR71C105KA01	General	1206	1000000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GJ431CC81E105KA01	General	1206	1000000	+/-10[%]	25	X6S	100[Hz]-6[GHz]
GJ831CC81E105KA01	General	1206	1000000	+/-10[%]	25	X6S	100[Hz]-6[GHz]
GRM31MR71E105KA01	General	1206	1000000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GRM31MR71H105KA88	General	1206	1000000	+/-10[%]	50	X7R	100[Hz]-6[GHz]
GRM31CR72A105KA01	General	1206	1000000	+/-10[%]	100	X7R	100[Hz]-6[GHz]
GRM319R61A225KA01	General	1206	2200000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM31MR61A225KA01	General	1206	2200000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM31MR71A225KA01	General	1206	2200000	+/-10[%]	10	X7R	100[Hz]-6[GHz]
GRM316R61C225KA88	General	1206	2200000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM31MR61C225KA35	General	1206	2200000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM316C81C225KA12	General	1206	2200000	+/-10[%]	16	X6S	100[Hz]-6[GHz]
GRM31MR71C225KA35	General	1206	2200000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GRM31MR71C225MA35	General	1206	2200000	+/-20[%]	16	X7R	100[Hz]-6[GHz]
GRM316D71C225KA12	General	1206	2200000	+/-10[%]	16	X7T	100[Hz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM316D71C225MA12	General	1206	2200000	+/-20[%]	16	X7T	100[Hz]-6[GHz]
GRM316R61E225KA12	General	1206	2200000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM31MR71E225KA93	General	1206	2200000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GRM319C8YA225KA12	General	1206	2200000	+/-10[%]	35	X6S	100[Hz]-6[GHz]
GRM319C8YA225MA12	General	1206	2200000	+/-20[%]	35	X6S	100[Hz]-6[GHz]
GRM319R61H225KA12	General	1206	2200000	+/-10[%]	50	X5R	100[Hz]-6[GHz]
GRM319R61H225MA12	General	1206	2200000	+/-20[%]	50	X5R	100[Hz]-6[GHz]
GRM31CR61H225KA88	General	1206	2200000	+/-10[%]	50	X5R	100[Hz]-6[GHz]
GRM31CR71H225KA88	General	1206	2200000	+/-10[%]	50	X7R	100[Hz]-6[GHz]
GRM31CR72A225KA73	General	1206	2200000	+/-10[%]	100	X7R	100[Hz]-6[GHz]
GRM31CR72A225MA73	General	1206	2200000	+/-20[%]	100	X7R	100[Hz]-6[GHz]
GRM319R61C335KA12	General	1206	3300000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM31CR60J475KA01	General	1206	4700000	+/-10[%]	6.3	X5R	100[Hz]-6[GHz]
GRM319R61A475KA01	General	1206	4700000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM31CR61A475KA01	General	1206	4700000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM316R61A475KE19	General	1206	4700000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM31CR71A475KA01	General	1206	4700000	+/-10[%]	10	X7R	100[Hz]-6[GHz]
GRM319R61C475KA88	General	1206	4700000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM31CR61C475KA01	General	1206	4700000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM31CR61C475MA01	General	1206	4700000	+/-20[%]	16	X5R	100[Hz]-6[GHz]
GRM319C81C475KA12	General	1206	4700000	+/-10[%]	16	X6S	100[Hz]-6[GHz]
GRM31CR71C475KA01	General	1206	4700000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GRM31CR71C475MA01	General	1206	4700000	+/-20[%]	16	X7R	100[Hz]-6[GHz]
GRM319D71C475KA12	General	1206	4700000	+/-10[%]	16	X7T	100[Hz]-6[GHz]
GRM319D71C475MA12	General	1206	4700000	+/-20[%]	16	X7T	100[Hz]-6[GHz]
GRM319R61E475KA12	General	1206	4700000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM31CR61E475KA88	General	1206	4700000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM31CR71E475KA88	General	1206	4700000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GRM319R61H475KA12	General	1206	4700000	+/-10[%]	50	X5R	100[Hz]-6[GHz]
GRM319R61H475MA12	General	1206	4700000	+/-20[%]	50	X5R	100[Hz]-6[GHz]
GJ831CR71H475KA12	General	1206	4700000	+/-10[%]	50	X7R	100[Hz]-6[GHz]
GRM31CR71H475KA12	General	1206	4700000	+/-10[%]	50	X7R	100[Hz]-6[GHz]
GRM31CR71H475MA12	General	1206	4700000	+/-20[%]	50	X7R	100[Hz]-6[GHz]
GRM31MC81C685KA12	General	1206	6800000	+/-10[%]	16	X6S	100[Hz]-6[GHz]
GRM31MC81C685MA12	General	1206	6800000	+/-20[%]	16	X6S	100[Hz]-6[GHz]
GRM319R60J106KE19	General	1206	10000000	+/-10[%]	6.3	X5R	100[Hz]-6[GHz]
GRM31CR60J106KA01	General	1206	10000000	+/-10[%]	6.3	X5R	100[Hz]-6[GHz]
GRM319C80J106KE19	General	1206	10000000	+/-10[%]	6.3	X6S	100[Hz]-6[GHz]
GRM319C80J106ME19	General	1206	10000000	+/-20[%]	6.3	X6S	100[Hz]-6[GHz]
GRM31CR70J106KA01	General	1206	10000000	+/-10[%]	6.3	X7R	100[Hz]-6[GHz]
GRM319R61A106KE19	General	1206	10000000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM31CR61A106KA01	General	1206	10000000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM31MR61A106KE19	General	1206	10000000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM319R61A106ME19	General	1206	10000000	+/-20[%]	10	X5R	100[Hz]-6[GHz]
GRM319C81A106KA12	General	1206	10000000	+/-10[%]	10	X6S	100[Hz]-6[GHz]
GRM31MC81A106KE19	General	1206	10000000	+/-10[%]	10	X6S	100[Hz]-6[GHz]
GRM31MC81A106ME19	General	1206	10000000	+/-20[%]	10	X6S	100[Hz]-6[GHz]
GRM319C81A106MA12	General	1206	10000000	+/-20[%]	10	X6S	100[Hz]-6[GHz]
GRM31CR71A106KA01	General	1206	10000000	+/-10[%]	10	X7R	100[Hz]-6[GHz]
GRM31CR71A106MA01	General	1206	10000000	+/-20[%]	10	X7R	100[Hz]-6[GHz]
GRM319R61C106KE15	General	1206	10000000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM31CR61C106KA88	General	1206	10000000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM31MR61C106KA12	General	1206	10000000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM319R61C106ME15	General	1206	10000000	+/-20[%]	16	X5R	100[Hz]-6[GHz]
GRM319C81C106KA12	General	1206	10000000	+/-10[%]	16	X6S	100[Hz]-6[GHz]
GRM319C81C106MA12	General	1206	10000000	+/-20[%]	16	X6S	100[Hz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM31MC81C106KA12	General	1206	10000000	+/-10[%]	16	X6S	100[Hz]-6[GHz]
GRM31CR71C106KA12	General	1206	10000000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GRM31CR71C106KAC7	General	1206	10000000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GRM31CR71C106MA12	General	1206	10000000	+/-20[%]	16	X7R	100[Hz]-6[GHz]
GRM31CR71C106MAC7	General	1206	10000000	+/-20[%]	16	X7R	100[Hz]-6[GHz]
GJ831CR61E106KE83	General	1206	10000000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM319R61E106KA12	General	1206	10000000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM319R61E106MA12	General	1206	10000000	+/-20[%]	25	X5R	100[Hz]-6[GHz]
GRM31CR61E106KA12	General	1206	10000000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM31MR61E106KA12	General	1206	10000000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM31MR61E106MA12	General	1206	10000000	+/-20[%]	25	X5R	100[Hz]-6[GHz]
GRM31CC81E106KE15	General	1206	10000000	+/-10[%]	25	X6S	100[Hz]-6[GHz]
GRM31MC81E106KA12	General	1206	10000000	+/-10[%]	25	X6S	100[Hz]-6[GHz]
GRM31MC81E106MA12	General	1206	10000000	+/-20[%]	25	X6S	100[Hz]-6[GHz]
GRM31CC81E106MA12	General	1206	10000000	+/-20[%]	25	X6S	100[Hz]-6[GHz]
GRM31CR71E106KA12	General	1206	10000000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GRM31CR71E106MA12	General	1206	10000000	+/-20[%]	25	X7R	100[Hz]-6[GHz]
GRM31CR6YA106KA12	General	1206	10000000	+/-10[%]	35	X5R	100[Hz]-6[GHz]
GRM31CR6YA106MA12	General	1206	10000000	+/-20[%]	35	X5R	100[Hz]-6[GHz]
GRM319R6YA106KA12	General	1206	10000000	+/-10[%]	35	X5R	100[Hz]-6[GHz]
GRM319R6YA106MA12	General	1206	10000000	+/-20[%]	35	X5R	100[Hz]-6[GHz]
GRM31CC8YA106KA12	General	1206	10000000	+/-10[%]	35	X6S	100[Hz]-6[GHz]
GRM31CC8YA106MA12	General	1206	10000000	+/-20[%]	35	X6S	100[Hz]-6[GHz]
GRM31CR61H106KA12	General	1206	10000000	+/-10[%]	50	X5R	100[Hz]-6[GHz]
GRM31CR61H106MA12	General	1206	10000000	+/-20[%]	50	X5R	100[Hz]-6[GHz]
GRM31CC80G226ME19	General	1206	22000000	+/-20[%]	4	X6S	100[Hz]-6[GHz]
GRM31CC70G226ME01	General	1206	22000000	+/-20[%]	4	X7S	100[Hz]-6[GHz]
GRM31CR60J226ME19	General	1206	22000000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM319R60J226ME15	General	1206	22000000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM31CC80J226KE19	General	1206	22000000	+/-10[%]	6.3	X6S	100[Hz]-6[GHz]
GRM31CC80J226ME19	General	1206	22000000	+/-20[%]	6.3	X6S	100[Hz]-6[GHz]
GRM319C80J226ME15	General	1206	22000000	+/-20[%]	6.3	X6S	100[Hz]-6[GHz]
GRM31CR70J226KE19	General	1206	22000000	+/-10[%]	6.3	X7R	100[Hz]-6[GHz]
GRM31CR70J226ME19	General	1206	22000000	+/-20[%]	6.3	X7R	100[Hz]-6[GHz]
GRM31CC70J226KE15	General	1206	22000000	+/-10[%]	6.3	X7S	100[Hz]-6[GHz]
GRM31CR61A226KE19	General	1206	22000000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM31CR61A226ME19	General	1206	22000000	+/-20[%]	10	X5R	100[Hz]-6[GHz]
GRM319R61A226ME15	General	1206	22000000	+/-20[%]	10	X5R	100[Hz]-6[GHz]
GRM31CC81A226KE19	General	1206	22000000	+/-10[%]	10	X6S	100[Hz]-6[GHz]
GRM31CC81A226ME19	General	1206	22000000	+/-20[%]	10	X6S	100[Hz]-6[GHz]
GRM31CR71A226KE15	General	1206	22000000	+/-10[%]	10	X7R	100[Hz]-6[GHz]
GRM31CR71A226ME15	General	1206	22000000	+/-20[%]	10	X7R	100[Hz]-6[GHz]
GRM31CD71A226KE15	General	1206	22000000	+/-10[%]	10	X7T	100[Hz]-6[GHz]
GRM31CD71A226ME15	General	1206	22000000	+/-20[%]	10	X7T	100[Hz]-6[GHz]
GRM31CR61C226ME15	General	1206	22000000	+/-20[%]	16	X5R	100[Hz]-6[GHz]
GRM319R61C226ME15	General	1206	22000000	+/-20[%]	16	X5R	100[Hz]-6[GHz]
GRM31CC81C226ME15	General	1206	22000000	+/-20[%]	16	X6S	100[Hz]-6[GHz]
GRM31CR61E226KE15	General	1206	22000000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM31CR61E226ME15	General	1206	22000000	+/-20[%]	25	X5R	100[Hz]-6[GHz]
GRM31CC80G476ME19	General	1206	47000000	+/-20[%]	4	X6S	100[Hz]-6[GHz]
GRM31CE70G476ME15	General	1206	47000000	+/-20[%]	4	X7U	100[Hz]-6[GHz]
GRM31CR60J476ME19	General	1206	47000000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM31CC80J476ME18	General	1206	47000000	+/-20[%]	6.3	X6S	100[Hz]-6[GHz]
GRM31CE70J476ME15	General	1206	47000000	+/-20[%]	6.3	X7U	100[Hz]-6[GHz]
GRM31CR61A476KE15	General	1206	47000000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM31CR61A476ME15	General	1206	47000000	+/-20[%]	10	X5R	100[Hz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM31CR60G107ME39	General	1206	100000000	+/-20[%]	4	X5R	100[Hz]-6[GHz]
GRM31CD80G107ME39	General	1206	100000000	+/-20[%]	4	X6T	100[Hz]-6[GHz]
GRM31CE70G107ME39	General	1206	100000000	+/-20[%]	4	X7U	100[Hz]-6[GHz]
GRM31CR60J107ME39	General	1206	100000000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM31CD80J107ME39	General	1206	100000000	+/-20[%]	6.3	X6T	100[Hz]-6[GHz]
GRM32NR71H684KA01	General	1210	680000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM32CR72A684KA01	General	1210	680000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GRM32RR71H105KA01	General	1210	1000000	+/-10[%]	50	X7R	100[Hz]-6[GHz]
GRM32CR72A105KA35	General	1210	1000000	+/-10[%]	100	X7R	100[Hz]-6[GHz]
GRM32CR72A105MA35	General	1210	1000000	+/-20[%]	100	X7R	100[Hz]-6[GHz]
GRM32MR71C225KA01	General	1210	2200000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GRM32RR71E225KA01	General	1210	2200000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GRM32ER72A225KA35	General	1210	2200000	+/-10[%]	100	X7R	100[Hz]-6[GHz]
GRM32ER72A225MA35	General	1210	2200000	+/-20[%]	100	X7R	100[Hz]-6[GHz]
GRM32RR61C475KA01	General	1210	4700000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM32RR71C475KA01	General	1210	4700000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GRM32RR61E475KA12	General	1210	4700000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM32DR71E475KA61	General	1210	4700000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GRM32ER71H475KA88	General	1210	4700000	+/-10[%]	50	X7R	100[Hz]-6[GHz]
GRM32ER71K475KE14	General	1210	4700000	+/-10[%]	80	X7R	100[Hz]-6[GHz]
GRM32ER71K475ME14	General	1210	4700000	+/-20[%]	80	X7R	100[Hz]-6[GHz]
GRM32ER61A106KA01	General	1210	10000000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM32DR71A106KA01	General	1210	10000000	+/-10[%]	10	X7R	100[Hz]-6[GHz]
GRM32AR61C106KAB7	General	1210	10000000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM32DR61C106KA01	General	1210	10000000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM32DR71C106KA01	General	1210	10000000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GRM32DR61E106KA12	General	1210	10000000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM32DC81E106KA12	General	1210	10000000	+/-10[%]	25	X6S	100[Hz]-6[GHz]
GRM32DR71E106KA12	General	1210	10000000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GRM32ER6YA106KA12	General	1210	10000000	+/-10[%]	35	X5R	100[Hz]-6[GHz]
GRM32ER6YA106MA12	General	1210	10000000	+/-20[%]	35	X5R	100[Hz]-6[GHz]
GJ832ER7YA106KA12	General	1210	10000000	+/-10[%]	35	X7R	100[Hz]-6[GHz]
GRM32ER7YA106KA12	General	1210	10000000	+/-10[%]	35	X7R	100[Hz]-6[GHz]
GRM32ER7YA106MA12	General	1210	10000000	+/-20[%]	35	X7R	100[Hz]-6[GHz]
GRM32ER61H106KA12	General	1210	10000000	+/-10[%]	50	X5R	100[Hz]-6[GHz]
GRM32ER61H106MA12	General	1210	10000000	+/-20[%]	50	X5R	100[Hz]-6[GHz]
GRM32ER71H106KA12	General	1210	10000000	+/-10[%]	50	X7R	100[Hz]-6[GHz]
GRM32ER71H106MA12	General	1210	10000000	+/-20[%]	50	X7R	100[Hz]-6[GHz]
GRM32ER71J106KA12	General	1210	10000000	+/-10[%]	63	X7R	100[Hz]-6[GHz]
GRM32ER71J106MA12	General	1210	10000000	+/-20[%]	63	X7R	100[Hz]-6[GHz]
GRM32DR60J226MA01	General	1210	22000000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM32ND70J226ME19	General	1210	22000000	+/-20[%]	6.3	X7T	100[Hz]-6[GHz]
GRM32NR61A226KE19	General	1210	22000000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM32NR61A226ME19	General	1210	22000000	+/-20[%]	10	X5R	100[Hz]-6[GHz]
GRM32NC81A226ME19	General	1210	22000000	+/-20[%]	10	X6S	100[Hz]-6[GHz]
GRM32ER71A226ME20	General	1210	22000000	+/-20[%]	10	X7R	100[Hz]-6[GHz]
GRM32ND71A226KE15	General	1210	22000000	+/-10[%]	10	X7T	100[Hz]-6[GHz]
GRM32ND71A226ME15	General	1210	22000000	+/-20[%]	10	X7T	100[Hz]-6[GHz]
GRM32ER61C226ME20	General	1210	22000000	+/-20[%]	16	X5R	100[Hz]-6[GHz]
GRM32NC81C226KE15	General	1210	22000000	+/-10[%]	16	X6S	100[Hz]-6[GHz]
GRM32NC81C226ME15	General	1210	22000000	+/-20[%]	16	X6S	100[Hz]-6[GHz]
GRM32ER71C226MEA8	General	1210	22000000	+/-20[%]	16	X7R	100[Hz]-6[GHz]
GRM32ER71C226KEA8	General	1210	22000000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GRM32ER61E226KE15	General	1210	22000000	+/-10[%]	25	X5R	100[Hz]-6[GHz]
GRM32ER61E226ME15	General	1210	22000000	+/-20[%]	25	X5R	100[Hz]-6[GHz]
GRM32EC81E226KE15	General	1210	22000000	+/-10[%]	25	X6S	100[Hz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM32EC81E226ME15	General	1210	22000000	+/-20[%]	25	X6S	100[Hz]-6[GHz]
GRM32ER71E226ME15	General	1210	22000000	+/-20[%]	25	X7R	100[Hz]-6[GHz]
GRM32EC80J476ME64	General	1210	47000000	+/-20[%]	6.3	X6S	100[Hz]-6[GHz]
GRM32ER70J476KE20	General	1210	47000000	+/-10[%]	6.3	X7R	100[Hz]-6[GHz]
GRM32ER70J476ME20	General	1210	47000000	+/-20[%]	6.3	X7R	100[Hz]-6[GHz]
GRM32ER61A476KE20	General	1210	47000000	+/-10[%]	10	X5R	100[Hz]-6[GHz]
GRM32ER61A476ME20	General	1210	47000000	+/-20[%]	10	X5R	100[Hz]-6[GHz]
GRM32EC81A476KE19	General	1210	47000000	+/-10[%]	10	X6S	100[Hz]-6[GHz]
GRM32EC81A476ME19	General	1210	47000000	+/-20[%]	10	X6S	100[Hz]-6[GHz]
GRM32ER71A476KE15	General	1210	47000000	+/-10[%]	10	X7R	100[Hz]-6[GHz]
GRM32ER71A476ME15	General	1210	47000000	+/-20[%]	10	X7R	100[Hz]-6[GHz]
GRM32ED71A476KE15	General	1210	47000000	+/-10[%]	10	X7T	100[Hz]-6[GHz]
GRM32ED71A476ME15	General	1210	47000000	+/-20[%]	10	X7T	100[Hz]-6[GHz]
GRM32ER61C476KE15	General	1210	47000000	+/-10[%]	16	X5R	100[Hz]-6[GHz]
GRM32ER61C476ME15	General	1210	47000000	+/-20[%]	16	X5R	100[Hz]-6[GHz]
GRM32EC81C476KE15	General	1210	47000000	+/-10[%]	16	X6S	100[Hz]-6[GHz]
GRM32EC81C476ME15	General	1210	47000000	+/-20[%]	16	X6S	100[Hz]-6[GHz]
GRM32EC80G107ME20	General	1210	100000000	+/-20[%]	4	X6S	100[Hz]-6[GHz]
GRM32EE70G107ME19	General	1210	100000000	+/-20[%]	4	X7U	100[Hz]-6[GHz]
GRM32ER60J107ME20	General	1210	100000000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
GRM32EC80J107ME20	General	1210	100000000	+/-20[%]	6.3	X6S	100[Hz]-6[GHz]
GRM32EE70J107ME15	General	1210	100000000	+/-20[%]	6.3	X7U	100[Hz]-6[GHz]
GRM32ER61A107ME20	General	1210	100000000	+/-20[%]	10	X5R	100[Hz]-6[GHz]
GRM0335C1HR10WA01	Ultra-small	0201	0.1	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GRM0335C2AR10WA01	Ultra-small	0201	0.1	+/-0.05[pF]	100	C0G	100[MHz]-20[GHz]
GRM0335C1HR20WA01	Ultra-small	0201	0.2	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GRM0335C1HR20BA01	Ultra-small	0201	0.2	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GRM0335C2AR20BA01	Ultra-small	0201	0.2	+/-0.1[pF]	100	C0G	100[MHz]-20[GHz]
GRM0335C2AR20WA01	Ultra-small	0201	0.2	+/-0.05[pF]	100	C0G	100[MHz]-20[GHz]
GRM0335C1HR30WA01	Ultra-small	0201	0.3	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GRM0335C1HR30BA01	Ultra-small	0201	0.3	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GRM0335C2AR30BA01	Ultra-small	0201	0.3	+/-0.1[pF]	100	C0G	100[MHz]-20[GHz]
GRM0335C2AR30WA01	Ultra-small	0201	0.3	+/-0.05[pF]	100	C0G	100[MHz]-20[GHz]
GRM0335C1HR40WA01	Ultra-small	0201	0.4	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GRM0335C1HR40BA01	Ultra-small	0201	0.4	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GRM0335C2AR40BA01	Ultra-small	0201	0.4	+/-0.1[pF]	100	C0G	100[MHz]-20[GHz]
GRM0335C2AR40WA01	Ultra-small	0201	0.4	+/-0.05[pF]	100	C0G	100[MHz]-20[GHz]
GRM0335C1HR50WA01	Ultra-small	0201	0.5	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GRM0335C1HR50BA01	Ultra-small	0201	0.5	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GRM0335C2AR50BA01	Ultra-small	0201	0.5	+/-0.1[pF]	100	C0G	100[MHz]-20[GHz]
GRM0335C2AR50WA01	Ultra-small	0201	0.5	+/-0.05[pF]	100	C0G	100[MHz]-20[GHz]
GRM0335C1HR60WA01	Ultra-small	0201	0.6	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GRM0335C1HR60BA01	Ultra-small	0201	0.6	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GRM0335C2AR60BA01	Ultra-small	0201	0.6	+/-0.1[pF]	100	C0G	100[MHz]-20[GHz]
GRM0335C2AR60WA01	Ultra-small	0201	0.6	+/-0.05[pF]	100	C0G	100[MHz]-20[GHz]
GRM0335C1HR70WA01	Ultra-small	0201	0.7	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GRM0335C1HR70BA01	Ultra-small	0201	0.7	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GRM0335C2AR70BA01	Ultra-small	0201	0.7	+/-0.1[pF]	100	C0G	100[MHz]-20[GHz]
GRM0335C2AR70WA01	Ultra-small	0201	0.7	+/-0.05[pF]	100	C0G	100[MHz]-20[GHz]
GRM0335C1HR80WA01	Ultra-small	0201	0.8	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GRM0335C1HR80BA01	Ultra-small	0201	0.8	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GRM0335C2AR80BA01	Ultra-small	0201	0.8	+/-0.1[pF]	100	C0G	100[MHz]-20[GHz]
GRM0335C2AR80WA01	Ultra-small	0201	0.8	+/-0.05[pF]	100	C0G	100[MHz]-20[GHz]
GRM0335C1HR90WA01	Ultra-small	0201	0.9	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GRM0335C1HR90BA01	Ultra-small	0201	0.9	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GRM0335C2AR90BA01	Ultra-small	0201	0.9	+/-0.1[pF]	100	C0G	100[MHz]-20[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM0335C2AR90WA01	Ultra-small	0201	0.9	+/-0.05[pF]	100	C0G	100[MHz]-20[GHz]
GRM0335C1H1R0CA01	Ultra-small	0201	1	+/-0.25[pF]	50	C0G	100[MHz]-20[GHz]
GRM0335C1H1R0WA01	Ultra-small	0201	1	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GRM0335C1H1R0BA01	Ultra-small	0201	1	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GRM0335C2A1R0BA01	Ultra-small	0201	1	+/-0.1[pF]	100	C0G	100[MHz]-20[GHz]
GRM0335C2A1R0CA01	Ultra-small	0201	1	+/-0.25[pF]	100	C0G	100[MHz]-20[GHz]
GRM0335C2A1R0WA01	Ultra-small	0201	1	+/-0.05[pF]	100	C0G	100[MHz]-20[GHz]
GRM0335C1H1R1WA01	Ultra-small	0201	1.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R1BA01	Ultra-small	0201	1.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R1CA01	Ultra-small	0201	1.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R1BA01	Ultra-small	0201	1.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R1CA01	Ultra-small	0201	1.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R1WA01	Ultra-small	0201	1.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R2BA01	Ultra-small	0201	1.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R2WA01	Ultra-small	0201	1.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R2CA01	Ultra-small	0201	1.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R2BA01	Ultra-small	0201	1.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R2CA01	Ultra-small	0201	1.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R2WA01	Ultra-small	0201	1.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R3WA01	Ultra-small	0201	1.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R3BA01	Ultra-small	0201	1.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R3CA01	Ultra-small	0201	1.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R3BA01	Ultra-small	0201	1.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R3CA01	Ultra-small	0201	1.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R3WA01	Ultra-small	0201	1.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R4BA01	Ultra-small	0201	1.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R4CA01	Ultra-small	0201	1.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R4WA01	Ultra-small	0201	1.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R4BA01	Ultra-small	0201	1.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R4CA01	Ultra-small	0201	1.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R4WA01	Ultra-small	0201	1.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R5CA01	Ultra-small	0201	1.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R5WA01	Ultra-small	0201	1.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R5BA01	Ultra-small	0201	1.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R5BA01	Ultra-small	0201	1.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R5CA01	Ultra-small	0201	1.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R5WA01	Ultra-small	0201	1.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R6WA01	Ultra-small	0201	1.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R6BA01	Ultra-small	0201	1.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R6CA01	Ultra-small	0201	1.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R6BA01	Ultra-small	0201	1.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R6CA01	Ultra-small	0201	1.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R6WA01	Ultra-small	0201	1.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R7BA01	Ultra-small	0201	1.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R7CA01	Ultra-small	0201	1.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R7WA01	Ultra-small	0201	1.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R7BA01	Ultra-small	0201	1.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R7CA01	Ultra-small	0201	1.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R7WA01	Ultra-small	0201	1.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R8BA01	Ultra-small	0201	1.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R8WA01	Ultra-small	0201	1.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R8CA01	Ultra-small	0201	1.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R8BA01	Ultra-small	0201	1.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R8CA01	Ultra-small	0201	1.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R8WA01	Ultra-small	0201	1.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R9BA01	Ultra-small	0201	1.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]



Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM0335C1H1R9CA01	Ultra-small	0201	1.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H1R9WA01	Ultra-small	0201	1.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R9BA01	Ultra-small	0201	1.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R9CA01	Ultra-small	0201	1.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A1R9WA01	Ultra-small	0201	1.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R0CA01	Ultra-small	0201	2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R0WA01	Ultra-small	0201	2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R0BA01	Ultra-small	0201	2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R0BA01	Ultra-small	0201	2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R0CA01	Ultra-small	0201	2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R0WA01	Ultra-small	0201	2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R1BA01	Ultra-small	0201	2.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R1CA01	Ultra-small	0201	2.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R1WA01	Ultra-small	0201	2.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R1BA01	Ultra-small	0201	2.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R1CA01	Ultra-small	0201	2.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R1WA01	Ultra-small	0201	2.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R2BA01	Ultra-small	0201	2.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R2WA01	Ultra-small	0201	2.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R2CA01	Ultra-small	0201	2.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R2BA01	Ultra-small	0201	2.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R2CA01	Ultra-small	0201	2.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R2WA01	Ultra-small	0201	2.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R3BA01	Ultra-small	0201	2.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R3CA01	Ultra-small	0201	2.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R3WA01	Ultra-small	0201	2.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R3BA01	Ultra-small	0201	2.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R3CA01	Ultra-small	0201	2.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R3WA01	Ultra-small	0201	2.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R4BA01	Ultra-small	0201	2.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R4WA01	Ultra-small	0201	2.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R4CA01	Ultra-small	0201	2.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R4BA01	Ultra-small	0201	2.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R4CA01	Ultra-small	0201	2.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R4WA01	Ultra-small	0201	2.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R5BA01	Ultra-small	0201	2.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R5CA01	Ultra-small	0201	2.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R5WA01	Ultra-small	0201	2.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R5BA01	Ultra-small	0201	2.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R5CA01	Ultra-small	0201	2.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R5WA01	Ultra-small	0201	2.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R6BA01	Ultra-small	0201	2.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R6CA01	Ultra-small	0201	2.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R6WA01	Ultra-small	0201	2.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R6BA01	Ultra-small	0201	2.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R6CA01	Ultra-small	0201	2.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R6WA01	Ultra-small	0201	2.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R7BA01	Ultra-small	0201	2.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R7WA01	Ultra-small	0201	2.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R7CA01	Ultra-small	0201	2.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R7BA01	Ultra-small	0201	2.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R7CA01	Ultra-small	0201	2.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R7WA01	Ultra-small	0201	2.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R8BA01	Ultra-small	0201	2.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R8CA01	Ultra-small	0201	2.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R8WA01	Ultra-small	0201	2.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM0335C2A2R8BA01	Ultra-small	0201	2.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R8CA01	Ultra-small	0201	2.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R8WA01	Ultra-small	0201	2.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R9BA01	Ultra-small	0201	2.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R9CA01	Ultra-small	0201	2.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H2R9WA01	Ultra-small	0201	2.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R9BA01	Ultra-small	0201	2.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R9CA01	Ultra-small	0201	2.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A2R9WA01	Ultra-small	0201	2.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R0CA01	Ultra-small	0201	3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R0WA01	Ultra-small	0201	3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R0BA01	Ultra-small	0201	3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R0BA01	Ultra-small	0201	3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R0CA01	Ultra-small	0201	3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R0WA01	Ultra-small	0201	3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R1BA01	Ultra-small	0201	3.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R1CA01	Ultra-small	0201	3.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R1WA01	Ultra-small	0201	3.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R1BA01	Ultra-small	0201	3.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R1CA01	Ultra-small	0201	3.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R1WA01	Ultra-small	0201	3.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R2BA01	Ultra-small	0201	3.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R2CA01	Ultra-small	0201	3.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R2WA01	Ultra-small	0201	3.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R2BA01	Ultra-small	0201	3.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R2CA01	Ultra-small	0201	3.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R2WA01	Ultra-small	0201	3.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R3BA01	Ultra-small	0201	3.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R3WA01	Ultra-small	0201	3.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R3CA01	Ultra-small	0201	3.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R3BA01	Ultra-small	0201	3.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R3CA01	Ultra-small	0201	3.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R3WA01	Ultra-small	0201	3.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R4BA01	Ultra-small	0201	3.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R4CA01	Ultra-small	0201	3.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R4WA01	Ultra-small	0201	3.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R4BA01	Ultra-small	0201	3.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R4CA01	Ultra-small	0201	3.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R4WA01	Ultra-small	0201	3.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R5BA01	Ultra-small	0201	3.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R5CA01	Ultra-small	0201	3.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R5WA01	Ultra-small	0201	3.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R5BA01	Ultra-small	0201	3.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R5CA01	Ultra-small	0201	3.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R5WA01	Ultra-small	0201	3.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R6BA01	Ultra-small	0201	3.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R6WA01	Ultra-small	0201	3.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R6CA01	Ultra-small	0201	3.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R6BA01	Ultra-small	0201	3.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R6CA01	Ultra-small	0201	3.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R6WA01	Ultra-small	0201	3.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R7BA01	Ultra-small	0201	3.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R7CA01	Ultra-small	0201	3.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R7WA01	Ultra-small	0201	3.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R7BA01	Ultra-small	0201	3.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R7CA01	Ultra-small	0201	3.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM0335C2A3R7WA01	Ultra-small	0201	3.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R8BA01	Ultra-small	0201	3.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R8CA01	Ultra-small	0201	3.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R8WA01	Ultra-small	0201	3.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R8BA01	Ultra-small	0201	3.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R8CA01	Ultra-small	0201	3.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R8WA01	Ultra-small	0201	3.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R9BA01	Ultra-small	0201	3.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R9WA01	Ultra-small	0201	3.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H3R9CA01	Ultra-small	0201	3.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R9BA01	Ultra-small	0201	3.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R9CA01	Ultra-small	0201	3.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A3R9WA01	Ultra-small	0201	3.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R0CA01	Ultra-small	0201	4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R0WA01	Ultra-small	0201	4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R0BA01	Ultra-small	0201	4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R0BA01	Ultra-small	0201	4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R0CA01	Ultra-small	0201	4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R0WA01	Ultra-small	0201	4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R1BA01	Ultra-small	0201	4.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R1CA01	Ultra-small	0201	4.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R1WA01	Ultra-small	0201	4.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R1BA01	Ultra-small	0201	4.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R1CA01	Ultra-small	0201	4.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R1WA01	Ultra-small	0201	4.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R2BA01	Ultra-small	0201	4.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R2CA01	Ultra-small	0201	4.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R2WA01	Ultra-small	0201	4.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R2BA01	Ultra-small	0201	4.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R2CA01	Ultra-small	0201	4.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R2WA01	Ultra-small	0201	4.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R3BA01	Ultra-small	0201	4.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R3WA01	Ultra-small	0201	4.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R3CA01	Ultra-small	0201	4.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R3BA01	Ultra-small	0201	4.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R3CA01	Ultra-small	0201	4.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R3WA01	Ultra-small	0201	4.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R4BA01	Ultra-small	0201	4.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R4CA01	Ultra-small	0201	4.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R4WA01	Ultra-small	0201	4.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R4BA01	Ultra-small	0201	4.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R4CA01	Ultra-small	0201	4.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R4WA01	Ultra-small	0201	4.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R5BA01	Ultra-small	0201	4.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R5CA01	Ultra-small	0201	4.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R5WA01	Ultra-small	0201	4.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R5BA01	Ultra-small	0201	4.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R5CA01	Ultra-small	0201	4.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R5WA01	Ultra-small	0201	4.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R6BA01	Ultra-small	0201	4.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R6CA01	Ultra-small	0201	4.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R6WA01	Ultra-small	0201	4.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R6BA01	Ultra-small	0201	4.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R6CA01	Ultra-small	0201	4.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R6WA01	Ultra-small	0201	4.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R7BA01	Ultra-small	0201	4.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM0335C1H4R7WA01	Ultra-small	0201	4.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R7CA01	Ultra-small	0201	4.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R7BA01	Ultra-small	0201	4.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R7CA01	Ultra-small	0201	4.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R7WA01	Ultra-small	0201	4.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R8BA01	Ultra-small	0201	4.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R8CA01	Ultra-small	0201	4.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R8WA01	Ultra-small	0201	4.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R8BA01	Ultra-small	0201	4.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R8CA01	Ultra-small	0201	4.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R8WA01	Ultra-small	0201	4.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R9BA01	Ultra-small	0201	4.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R9CA01	Ultra-small	0201	4.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H4R9WA01	Ultra-small	0201	4.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R9BA01	Ultra-small	0201	4.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R9CA01	Ultra-small	0201	4.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A4R9WA01	Ultra-small	0201	4.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R0BA01	Ultra-small	0201	5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R0CA01	Ultra-small	0201	5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R0WA01	Ultra-small	0201	5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R0BA01	Ultra-small	0201	5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R0CA01	Ultra-small	0201	5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R0WA01	Ultra-small	0201	5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R1BA01	Ultra-small	0201	5.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R1WA01	Ultra-small	0201	5.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R1CA01	Ultra-small	0201	5.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R1DA01	Ultra-small	0201	5.1	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R1BA01	Ultra-small	0201	5.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R1CA01	Ultra-small	0201	5.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R1DA01	Ultra-small	0201	5.1	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R1WA01	Ultra-small	0201	5.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R2BA01	Ultra-small	0201	5.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R2CA01	Ultra-small	0201	5.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R2DA01	Ultra-small	0201	5.2	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R2WA01	Ultra-small	0201	5.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R2BA01	Ultra-small	0201	5.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R2CA01	Ultra-small	0201	5.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R2DA01	Ultra-small	0201	5.2	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R2WA01	Ultra-small	0201	5.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R3BA01	Ultra-small	0201	5.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R3CA01	Ultra-small	0201	5.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R3DA01	Ultra-small	0201	5.3	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R3WA01	Ultra-small	0201	5.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R3BA01	Ultra-small	0201	5.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R3CA01	Ultra-small	0201	5.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R3DA01	Ultra-small	0201	5.3	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R3WA01	Ultra-small	0201	5.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R4BA01	Ultra-small	0201	5.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R4CA01	Ultra-small	0201	5.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R4DA01	Ultra-small	0201	5.4	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R4WA01	Ultra-small	0201	5.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R4BA01	Ultra-small	0201	5.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R4CA01	Ultra-small	0201	5.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R4DA01	Ultra-small	0201	5.4	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R4WA01	Ultra-small	0201	5.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R5BA01	Ultra-small	0201	5.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM0335C1H5R5CA01	Ultra-small	0201	5.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R5DA01	Ultra-small	0201	5.5	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R5WA01	Ultra-small	0201	5.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R5BA01	Ultra-small	0201	5.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R5CA01	Ultra-small	0201	5.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R5DA01	Ultra-small	0201	5.5	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R5WA01	Ultra-small	0201	5.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R6BA01	Ultra-small	0201	5.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R6WA01	Ultra-small	0201	5.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R6CA01	Ultra-small	0201	5.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R6DA01	Ultra-small	0201	5.6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R6BA01	Ultra-small	0201	5.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R6CA01	Ultra-small	0201	5.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R6DA01	Ultra-small	0201	5.6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R6WA01	Ultra-small	0201	5.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R7BA01	Ultra-small	0201	5.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R7CA01	Ultra-small	0201	5.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R7DA01	Ultra-small	0201	5.7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R7WA01	Ultra-small	0201	5.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R7BA01	Ultra-small	0201	5.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R7CA01	Ultra-small	0201	5.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R7DA01	Ultra-small	0201	5.7	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R7WA01	Ultra-small	0201	5.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R8BA01	Ultra-small	0201	5.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R8CA01	Ultra-small	0201	5.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R8DA01	Ultra-small	0201	5.8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R8WA01	Ultra-small	0201	5.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R8BA01	Ultra-small	0201	5.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R8CA01	Ultra-small	0201	5.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R8DA01	Ultra-small	0201	5.8	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R8WA01	Ultra-small	0201	5.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R9BA01	Ultra-small	0201	5.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R9CA01	Ultra-small	0201	5.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R9DA01	Ultra-small	0201	5.9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H5R9WA01	Ultra-small	0201	5.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R9BA01	Ultra-small	0201	5.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R9CA01	Ultra-small	0201	5.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R9DA01	Ultra-small	0201	5.9	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A5R9WA01	Ultra-small	0201	5.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R0BA01	Ultra-small	0201	6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R0CA01	Ultra-small	0201	6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R0DA01	Ultra-small	0201	6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R0WA01	Ultra-small	0201	6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R0BA01	Ultra-small	0201	6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R0CA01	Ultra-small	0201	6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R0DA01	Ultra-small	0201	6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R0WA01	Ultra-small	0201	6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R1BA01	Ultra-small	0201	6.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R1CA01	Ultra-small	0201	6.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R1DA01	Ultra-small	0201	6.1	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R1WA01	Ultra-small	0201	6.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R1BA01	Ultra-small	0201	6.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R1CA01	Ultra-small	0201	6.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R1DA01	Ultra-small	0201	6.1	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R1WA01	Ultra-small	0201	6.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R2WA01	Ultra-small	0201	6.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM0335C1H6R2BA01	Ultra-small	0201	6.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R2CA01	Ultra-small	0201	6.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R2DA01	Ultra-small	0201	6.2	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R2BA01	Ultra-small	0201	6.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R2CA01	Ultra-small	0201	6.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R2DA01	Ultra-small	0201	6.2	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R2WA01	Ultra-small	0201	6.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R3BA01	Ultra-small	0201	6.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R3CA01	Ultra-small	0201	6.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R3DA01	Ultra-small	0201	6.3	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R3WA01	Ultra-small	0201	6.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R3BA01	Ultra-small	0201	6.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R3CA01	Ultra-small	0201	6.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R3DA01	Ultra-small	0201	6.3	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R3WA01	Ultra-small	0201	6.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R4BA01	Ultra-small	0201	6.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R4CA01	Ultra-small	0201	6.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R4DA01	Ultra-small	0201	6.4	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R4WA01	Ultra-small	0201	6.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R4BA01	Ultra-small	0201	6.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R4CA01	Ultra-small	0201	6.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R4DA01	Ultra-small	0201	6.4	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R4WA01	Ultra-small	0201	6.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R5BA01	Ultra-small	0201	6.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R5CA01	Ultra-small	0201	6.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R5DA01	Ultra-small	0201	6.5	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R5WA01	Ultra-small	0201	6.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R5BA01	Ultra-small	0201	6.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R5CA01	Ultra-small	0201	6.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R5DA01	Ultra-small	0201	6.5	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R5WA01	Ultra-small	0201	6.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R6BA01	Ultra-small	0201	6.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R6CA01	Ultra-small	0201	6.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R6DA01	Ultra-small	0201	6.6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R6WA01	Ultra-small	0201	6.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R6BA01	Ultra-small	0201	6.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R6CA01	Ultra-small	0201	6.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R6DA01	Ultra-small	0201	6.6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R6WA01	Ultra-small	0201	6.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R7BA01	Ultra-small	0201	6.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R7CA01	Ultra-small	0201	6.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R7DA01	Ultra-small	0201	6.7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R7WA01	Ultra-small	0201	6.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R7BA01	Ultra-small	0201	6.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R7CA01	Ultra-small	0201	6.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R7DA01	Ultra-small	0201	6.7	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R7WA01	Ultra-small	0201	6.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R8BA01	Ultra-small	0201	6.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R8WA01	Ultra-small	0201	6.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R8CA01	Ultra-small	0201	6.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R8DA01	Ultra-small	0201	6.8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R8BA01	Ultra-small	0201	6.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R8CA01	Ultra-small	0201	6.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R8DA01	Ultra-small	0201	6.8	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R8WA01	Ultra-small	0201	6.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R9BA01	Ultra-small	0201	6.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM0335C1H6R9CA01	Ultra-small	0201	6.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R9DA01	Ultra-small	0201	6.9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H6R9WA01	Ultra-small	0201	6.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R9BA01	Ultra-small	0201	6.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R9CA01	Ultra-small	0201	6.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R9DA01	Ultra-small	0201	6.9	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A6R9WA01	Ultra-small	0201	6.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R0BA01	Ultra-small	0201	7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R0CA01	Ultra-small	0201	7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R0DA01	Ultra-small	0201	7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R0WA01	Ultra-small	0201	7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R0BA01	Ultra-small	0201	7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R0CA01	Ultra-small	0201	7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R0DA01	Ultra-small	0201	7	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R0WA01	Ultra-small	0201	7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R1BA01	Ultra-small	0201	7.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R1CA01	Ultra-small	0201	7.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R1DA01	Ultra-small	0201	7.1	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R1WA01	Ultra-small	0201	7.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R1BA01	Ultra-small	0201	7.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R1CA01	Ultra-small	0201	7.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R1DA01	Ultra-small	0201	7.1	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R1WA01	Ultra-small	0201	7.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R2BA01	Ultra-small	0201	7.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R2CA01	Ultra-small	0201	7.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R2DA01	Ultra-small	0201	7.2	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R2WA01	Ultra-small	0201	7.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R2BA01	Ultra-small	0201	7.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R2CA01	Ultra-small	0201	7.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R2DA01	Ultra-small	0201	7.2	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R2WA01	Ultra-small	0201	7.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R3BA01	Ultra-small	0201	7.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R3CA01	Ultra-small	0201	7.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R3DA01	Ultra-small	0201	7.3	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R3WA01	Ultra-small	0201	7.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R3BA01	Ultra-small	0201	7.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R3CA01	Ultra-small	0201	7.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R3DA01	Ultra-small	0201	7.3	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R3WA01	Ultra-small	0201	7.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R4BA01	Ultra-small	0201	7.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R4CA01	Ultra-small	0201	7.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R4DA01	Ultra-small	0201	7.4	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R4WA01	Ultra-small	0201	7.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R4BA01	Ultra-small	0201	7.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R4CA01	Ultra-small	0201	7.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R4DA01	Ultra-small	0201	7.4	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R4WA01	Ultra-small	0201	7.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R5WA01	Ultra-small	0201	7.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R5BA01	Ultra-small	0201	7.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R5CA01	Ultra-small	0201	7.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R5DA01	Ultra-small	0201	7.5	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R5BA01	Ultra-small	0201	7.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R5CA01	Ultra-small	0201	7.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R5DA01	Ultra-small	0201	7.5	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R5WA01	Ultra-small	0201	7.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R6BA01	Ultra-small	0201	7.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM0335C1H7R6CA01	Ultra-small	0201	7.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R6DA01	Ultra-small	0201	7.6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R6WA01	Ultra-small	0201	7.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R6BA01	Ultra-small	0201	7.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R6CA01	Ultra-small	0201	7.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R6DA01	Ultra-small	0201	7.6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R6WA01	Ultra-small	0201	7.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R7BA01	Ultra-small	0201	7.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R7CA01	Ultra-small	0201	7.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R7DA01	Ultra-small	0201	7.7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R7WA01	Ultra-small	0201	7.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R7BA01	Ultra-small	0201	7.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R7CA01	Ultra-small	0201	7.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R7DA01	Ultra-small	0201	7.7	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R7WA01	Ultra-small	0201	7.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R8BA01	Ultra-small	0201	7.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R8CA01	Ultra-small	0201	7.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R8DA01	Ultra-small	0201	7.8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R8WA01	Ultra-small	0201	7.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R8BA01	Ultra-small	0201	7.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R8CA01	Ultra-small	0201	7.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R8DA01	Ultra-small	0201	7.8	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R8WA01	Ultra-small	0201	7.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R9BA01	Ultra-small	0201	7.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R9CA01	Ultra-small	0201	7.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R9DA01	Ultra-small	0201	7.9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H7R9WA01	Ultra-small	0201	7.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R9BA01	Ultra-small	0201	7.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R9CA01	Ultra-small	0201	7.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R9DA01	Ultra-small	0201	7.9	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A7R9WA01	Ultra-small	0201	7.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R0BA01	Ultra-small	0201	8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R0CA01	Ultra-small	0201	8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R0DA01	Ultra-small	0201	8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R0WA01	Ultra-small	0201	8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R0BA01	Ultra-small	0201	8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R0CA01	Ultra-small	0201	8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R0DA01	Ultra-small	0201	8	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R0WA01	Ultra-small	0201	8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R1BA01	Ultra-small	0201	8.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R1CA01	Ultra-small	0201	8.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R1DA01	Ultra-small	0201	8.1	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R1WA01	Ultra-small	0201	8.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R1BA01	Ultra-small	0201	8.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R1CA01	Ultra-small	0201	8.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R1DA01	Ultra-small	0201	8.1	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R1WA01	Ultra-small	0201	8.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R2BA01	Ultra-small	0201	8.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R2WA01	Ultra-small	0201	8.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R2CA01	Ultra-small	0201	8.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R2DA01	Ultra-small	0201	8.2	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R2BA01	Ultra-small	0201	8.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R2CA01	Ultra-small	0201	8.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R2DA01	Ultra-small	0201	8.2	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R2WA01	Ultra-small	0201	8.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R3BA01	Ultra-small	0201	8.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]



Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM0335C1H8R3CA01	Ultra-small	0201	8.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R3DA01	Ultra-small	0201	8.3	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R3WA01	Ultra-small	0201	8.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R3BA01	Ultra-small	0201	8.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R3CA01	Ultra-small	0201	8.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R3DA01	Ultra-small	0201	8.3	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R3WA01	Ultra-small	0201	8.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R4BA01	Ultra-small	0201	8.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R4CA01	Ultra-small	0201	8.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R4DA01	Ultra-small	0201	8.4	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R4WA01	Ultra-small	0201	8.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R4BA01	Ultra-small	0201	8.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R4CA01	Ultra-small	0201	8.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R4DA01	Ultra-small	0201	8.4	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R4WA01	Ultra-small	0201	8.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R5BA01	Ultra-small	0201	8.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R5CA01	Ultra-small	0201	8.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R5DA01	Ultra-small	0201	8.5	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R5WA01	Ultra-small	0201	8.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R5BA01	Ultra-small	0201	8.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R5CA01	Ultra-small	0201	8.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R5DA01	Ultra-small	0201	8.5	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R5WA01	Ultra-small	0201	8.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R6BA01	Ultra-small	0201	8.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R6CA01	Ultra-small	0201	8.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R6DA01	Ultra-small	0201	8.6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R6WA01	Ultra-small	0201	8.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R6BA01	Ultra-small	0201	8.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R6CA01	Ultra-small	0201	8.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R6DA01	Ultra-small	0201	8.6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R6WA01	Ultra-small	0201	8.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R7BA01	Ultra-small	0201	8.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R7CA01	Ultra-small	0201	8.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R7DA01	Ultra-small	0201	8.7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R7WA01	Ultra-small	0201	8.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R7BA01	Ultra-small	0201	8.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R7CA01	Ultra-small	0201	8.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R7DA01	Ultra-small	0201	8.7	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R7WA01	Ultra-small	0201	8.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R8BA01	Ultra-small	0201	8.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R8CA01	Ultra-small	0201	8.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R8DA01	Ultra-small	0201	8.8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R8WA01	Ultra-small	0201	8.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R8BA01	Ultra-small	0201	8.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R8CA01	Ultra-small	0201	8.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R8DA01	Ultra-small	0201	8.8	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R8WA01	Ultra-small	0201	8.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R9BA01	Ultra-small	0201	8.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R9CA01	Ultra-small	0201	8.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R9DA01	Ultra-small	0201	8.9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H8R9WA01	Ultra-small	0201	8.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R9BA01	Ultra-small	0201	8.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R9CA01	Ultra-small	0201	8.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R9DA01	Ultra-small	0201	8.9	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A8R9WA01	Ultra-small	0201	8.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R0BA01	Ultra-small	0201	9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM0335C1H9R0CA01	Ultra-small	0201	9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R0DA01	Ultra-small	0201	9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R0WA01	Ultra-small	0201	9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R0BA01	Ultra-small	0201	9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R0CA01	Ultra-small	0201	9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R0DA01	Ultra-small	0201	9	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R0WA01	Ultra-small	0201	9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R1WA01	Ultra-small	0201	9.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R1BA01	Ultra-small	0201	9.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R1CA01	Ultra-small	0201	9.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R1DA01	Ultra-small	0201	9.1	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R1BA01	Ultra-small	0201	9.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R1CA01	Ultra-small	0201	9.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R1DA01	Ultra-small	0201	9.1	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R1WA01	Ultra-small	0201	9.1	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R2BA01	Ultra-small	0201	9.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R2CA01	Ultra-small	0201	9.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R2DA01	Ultra-small	0201	9.2	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R2WA01	Ultra-small	0201	9.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R2BA01	Ultra-small	0201	9.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R2CA01	Ultra-small	0201	9.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R2DA01	Ultra-small	0201	9.2	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R2WA01	Ultra-small	0201	9.2	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R3BA01	Ultra-small	0201	9.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R3CA01	Ultra-small	0201	9.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R3DA01	Ultra-small	0201	9.3	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R3WA01	Ultra-small	0201	9.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R3BA01	Ultra-small	0201	9.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R3CA01	Ultra-small	0201	9.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R3DA01	Ultra-small	0201	9.3	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R3WA01	Ultra-small	0201	9.3	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R4BA01	Ultra-small	0201	9.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R4CA01	Ultra-small	0201	9.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R4DA01	Ultra-small	0201	9.4	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R4WA01	Ultra-small	0201	9.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R4BA01	Ultra-small	0201	9.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R4CA01	Ultra-small	0201	9.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R4DA01	Ultra-small	0201	9.4	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R4WA01	Ultra-small	0201	9.4	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R5BA01	Ultra-small	0201	9.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R5CA01	Ultra-small	0201	9.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R5DA01	Ultra-small	0201	9.5	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R5WA01	Ultra-small	0201	9.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R5BA01	Ultra-small	0201	9.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R5CA01	Ultra-small	0201	9.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R5DA01	Ultra-small	0201	9.5	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R5WA01	Ultra-small	0201	9.5	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R6BA01	Ultra-small	0201	9.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R6CA01	Ultra-small	0201	9.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R6DA01	Ultra-small	0201	9.6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R6WA01	Ultra-small	0201	9.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R6BA01	Ultra-small	0201	9.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R6CA01	Ultra-small	0201	9.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R6DA01	Ultra-small	0201	9.6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R6WA01	Ultra-small	0201	9.6	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R7BA01	Ultra-small	0201	9.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM0335C1H9R7CA01	Ultra-small	0201	9.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R7DA01	Ultra-small	0201	9.7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R7WA01	Ultra-small	0201	9.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R7BA01	Ultra-small	0201	9.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R7CA01	Ultra-small	0201	9.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R7DA01	Ultra-small	0201	9.7	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R7WA01	Ultra-small	0201	9.7	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R8BA01	Ultra-small	0201	9.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R8CA01	Ultra-small	0201	9.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R8DA01	Ultra-small	0201	9.8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R8WA01	Ultra-small	0201	9.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R8BA01	Ultra-small	0201	9.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R8CA01	Ultra-small	0201	9.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R8DA01	Ultra-small	0201	9.8	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R8WA01	Ultra-small	0201	9.8	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R9BA01	Ultra-small	0201	9.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R9CA01	Ultra-small	0201	9.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R9DA01	Ultra-small	0201	9.9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H9R9WA01	Ultra-small	0201	9.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R9BA01	Ultra-small	0201	9.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R9CA01	Ultra-small	0201	9.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R9DA01	Ultra-small	0201	9.9	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A9R9WA01	Ultra-small	0201	9.9	+/-0.05[pF]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H100JA01	Ultra-small	0201	10	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H100GA01	Ultra-small	0201	10	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A100GA01	Ultra-small	0201	10	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A100JA01	Ultra-small	0201	10	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H110GA01	Ultra-small	0201	11	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H110JA01	Ultra-small	0201	11	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H120JA01	Ultra-small	0201	12	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H120GA01	Ultra-small	0201	12	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A120GA01	Ultra-small	0201	12	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A120JA01	Ultra-small	0201	12	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H130GA01	Ultra-small	0201	13	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H130JA01	Ultra-small	0201	13	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H150JA01	Ultra-small	0201	15	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H150GA01	Ultra-small	0201	15	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C2A150GA01	Ultra-small	0201	15	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C2A150JA01	Ultra-small	0201	15	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GRM0335C1H160GA01	Ultra-small	0201	16	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H160JA01	Ultra-small	0201	16	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H180GA01	Ultra-small	0201	18	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H180JA01	Ultra-small	0201	18	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H200GA01	Ultra-small	0201	20	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H200JA01	Ultra-small	0201	20	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H220JA01	Ultra-small	0201	22	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H220GA01	Ultra-small	0201	22	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H240GA01	Ultra-small	0201	24	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H240JA01	Ultra-small	0201	24	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H270JA01	Ultra-small	0201	27	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H270GA01	Ultra-small	0201	27	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H300GA01	Ultra-small	0201	30	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H300JA01	Ultra-small	0201	30	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H330JA01	Ultra-small	0201	33	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H330GA01	Ultra-small	0201	33	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H360GA01	Ultra-small	0201	36	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM0335C1H360JA01	Ultra-small	0201	36	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H390JA01	Ultra-small	0201	39	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H390GA01	Ultra-small	0201	39	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H430GA01	Ultra-small	0201	43	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H430JA01	Ultra-small	0201	43	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H470JA01	Ultra-small	0201	47	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H470GA01	Ultra-small	0201	47	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H510JA01	Ultra-small	0201	51	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H510GA01	Ultra-small	0201	51	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H560JA01	Ultra-small	0201	56	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H560GA01	Ultra-small	0201	56	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H620JA01	Ultra-small	0201	62	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H620GA01	Ultra-small	0201	62	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H680JA01	Ultra-small	0201	68	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H680GA01	Ultra-small	0201	68	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H750GA01	Ultra-small	0201	75	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H750JA01	Ultra-small	0201	75	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H820JA01	Ultra-small	0201	82	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H820GA01	Ultra-small	0201	82	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H910GA01	Ultra-small	0201	91	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H910JA01	Ultra-small	0201	91	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM033R71C101KA01	Ultra-small	0201	100	+/-10[%]	16	X7R	5[MHz]-6[GHz]
GRM033R61E101KA01	Ultra-small	0201	100	+/-10[%]	25	X5R	5[MHz]-6[GHz]
GRM033R71E101KA01	Ultra-small	0201	100	+/-10[%]	25	X7R	5[MHz]-6[GHz]
GRM0335C1H101JA01	Ultra-small	0201	100	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H101GA01	Ultra-small	0201	100	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM033R71H101KA12	Ultra-small	0201	100	+/-10[%]	50	X7R	5[MHz]-6[GHz]
GRM033R71H101MA12	Ultra-small	0201	100	+/-20[%]	50	X7R	5[MHz]-6[GHz]
GRM0335C1H121JA01	Ultra-small	0201	120	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GRM0335C1H121GA01	Ultra-small	0201	120	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GRM033R71C151KA01	Ultra-small	0201	150	+/-10[%]	16	X7R	1[MHz]-6[GHz]
GRM033R61E151KA01	Ultra-small	0201	150	+/-10[%]	25	X5R	1[MHz]-6[GHz]
GRM033R71E151KA01	Ultra-small	0201	150	+/-10[%]	25	X7R	1[MHz]-6[GHz]
GRM033R71H151KA12	Ultra-small	0201	150	+/-10[%]	50	X7R	1[MHz]-6[GHz]
GRM033R71H151MA12	Ultra-small	0201	150	+/-20[%]	50	X7R	1[MHz]-6[GHz]
GRM033R71C221KA01	Ultra-small	0201	220	+/-10[%]	16	X7R	2[MHz]-6[GHz]
GRM033R61E221KA01	Ultra-small	0201	220	+/-10[%]	25	X5R	2[MHz]-6[GHz]
GRM033R71E221KA01	Ultra-small	0201	220	+/-10[%]	25	X7R	2[MHz]-6[GHz]
GRM033R71H221KA12	Ultra-small	0201	220	+/-10[%]	50	X7R	2[MHz]-6[GHz]
GRM033R71H221MA12	Ultra-small	0201	220	+/-20[%]	50	X7R	2[MHz]-6[GHz]
GRM033R71C331KA01	Ultra-small	0201	330	+/-10[%]	16	X7R	1[MHz]-6[GHz]
GRM033R61E331KA01	Ultra-small	0201	330	+/-10[%]	25	X5R	1[MHz]-6[GHz]
GRM033R71E331KA01	Ultra-small	0201	330	+/-10[%]	25	X7R	1[MHz]-6[GHz]
GRM033R71H331KA12	Ultra-small	0201	330	+/-10[%]	50	X7R	1[MHz]-6[GHz]
GRM033R71H331MA12	Ultra-small	0201	330	+/-20[%]	50	X7R	1[MHz]-6[GHz]
GRM033R71C471KA01	Ultra-small	0201	470	+/-10[%]	16	X7R	1[MHz]-6[GHz]
GRM033R61E471KA01	Ultra-small	0201	470	+/-10[%]	25	X5R	1[MHz]-6[GHz]
GRM033R71E471KA01	Ultra-small	0201	470	+/-10[%]	25	X7R	1[MHz]-6[GHz]
GRM033R71H471KA12	Ultra-small	0201	470	+/-10[%]	50	X7R	1[MHz]-6[GHz]
GRM033R71H471MA12	Ultra-small	0201	470	+/-20[%]	50	X7R	1[MHz]-6[GHz]
GRM033R71C681KA01	Ultra-small	0201	680	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM033R61E681KA01	Ultra-small	0201	680	+/-10[%]	25	X5R	100[kHz]-6[GHz]
GRM033R71E681KA01	Ultra-small	0201	680	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM033R71H681KA12	Ultra-small	0201	680	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM033R71H681MA12	Ultra-small	0201	680	+/-20[%]	50	X7R	100[kHz]-6[GHz]
GRM033R71C102KA01	Ultra-small	0201	1000	+/-10[%]	16	X7R	500[kHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM033R61E102KA01	Ultra-small	0201	1000	+/-10[%]	25	X5R	500[kHz]-6[GHz]
GRM033R71E102KA01	Ultra-small	0201	1000	+/-10[%]	25	X7R	500[kHz]-6[GHz]
GRM033R71H102KA12	Ultra-small	0201	1000	+/-10[%]	50	X7R	500[kHz]-6[GHz]
GRM033R71H102MA12	Ultra-small	0201	1000	+/-20[%]	50	X7R	500[kHz]-6[GHz]
GRM033R70J152KA01	Ultra-small	0201	1500	+/-10[%]	6.3	X7R	100[kHz]-6[GHz]
GRM033R61A152KA01	Ultra-small	0201	1500	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM033R71A152KA01	Ultra-small	0201	1500	+/-10[%]	10	X7R	100[kHz]-6[GHz]
GRM033R71C152KA01	Ultra-small	0201	1500	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM033R71E152KA01	Ultra-small	0201	1500	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM033R71H152KA12	Ultra-small	0201	1500	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GRM033R71H152MA12	Ultra-small	0201	1500	+/-20[%]	50	X7R	100[kHz]-6[GHz]
GRM033R70J222KA01	Ultra-small	0201	2200	+/-10[%]	6.3	X7R	300[kHz]-6[GHz]
GRM033R61A222KA01	Ultra-small	0201	2200	+/-10[%]	10	X5R	300[kHz]-6[GHz]
GRM033R71A222KA01	Ultra-small	0201	2200	+/-10[%]	10	X7R	300[kHz]-6[GHz]
GRM033R71C222KA88	Ultra-small	0201	2200	+/-10[%]	16	X7R	300[kHz]-6[GHz]
GRM033R71E222KA12	Ultra-small	0201	2200	+/-10[%]	25	X7R	300[kHz]-6[GHz]
GRM033R71E222MA12	Ultra-small	0201	2200	+/-20[%]	25	X7R	300[kHz]-6[GHz]
GRM033R70J332KA01	Ultra-small	0201	3300	+/-10[%]	6.3	X7R	100[kHz]-6[GHz]
GRM033R61A332KA01	Ultra-small	0201	3300	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM033R71A332KA01	Ultra-small	0201	3300	+/-10[%]	10	X7R	100[kHz]-6[GHz]
GRM033R71C332KA88	Ultra-small	0201	3300	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GRM033R71E332KA12	Ultra-small	0201	3300	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GRM033R71E332MA12	Ultra-small	0201	3300	+/-20[%]	25	X7R	100[kHz]-6[GHz]
GRM033R70J472KA01	Ultra-small	0201	4700	+/-10[%]	6.3	X7R	100[kHz]-6[GHz]
GRM033R61A472KA01	Ultra-small	0201	4700	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM033R61A472MA01	Ultra-small	0201	4700	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM033R71A472KA01	Ultra-small	0201	4700	+/-10[%]	10	X7R	100[kHz]-6[GHz]
GRM033R71A472MA01	Ultra-small	0201	4700	+/-20[%]	10	X7R	100[kHz]-6[GHz]
GRM033R61E472KA12	Ultra-small	0201	4700	+/-10[%]	25	X5R	100[kHz]-6[GHz]
GRM033R61E472MA12	Ultra-small	0201	4700	+/-20[%]	25	X5R	100[kHz]-6[GHz]
GRM033R71A562KA01	Ultra-small	0201	5600	+/-10[%]	10	X7R	100[kHz]-6[GHz]
GRM033R70J682KA01	Ultra-small	0201	6800	+/-10[%]	6.3	X7R	100[kHz]-6[GHz]
GRM033R61A682KA01	Ultra-small	0201	6800	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM033R61A682MA01	Ultra-small	0201	6800	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM033R71A682KA01	Ultra-small	0201	6800	+/-10[%]	10	X7R	100[kHz]-6[GHz]
GRM033R71A682MA01	Ultra-small	0201	6800	+/-20[%]	10	X7R	100[kHz]-6[GHz]
GRM033R61E682KA12	Ultra-small	0201	6800	+/-10[%]	25	X5R	100[kHz]-6[GHz]
GRM033R61E682MA12	Ultra-small	0201	6800	+/-20[%]	25	X5R	100[kHz]-6[GHz]
GRM033R60J103KA01	Ultra-small	0201	10000	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM033R70J103KA01	Ultra-small	0201	10000	+/-10[%]	6.3	X7R	100[kHz]-6[GHz]
GRM033R61A103KA01	Ultra-small	0201	10000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM033R61A103MA01	Ultra-small	0201	10000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM033R71A103KA01	Ultra-small	0201	10000	+/-10[%]	10	X7R	100[kHz]-6[GHz]
GRM033R71A103MA01	Ultra-small	0201	10000	+/-20[%]	10	X7R	100[kHz]-6[GHz]
GRM033R61C103KA12	Ultra-small	0201	10000	+/-10[%]	16	X5R	100[kHz]-6[GHz]
GRM033R61C103MA12	Ultra-small	0201	10000	+/-20[%]	16	X5R	100[kHz]-6[GHz]
GRM033R61E103KA12	Ultra-small	0201	10000	+/-10[%]	25	X5R	100[kHz]-6[GHz]
GRM033R61E103MA12	Ultra-small	0201	10000	+/-20[%]	25	X5R	100[kHz]-6[GHz]
GRM033R61A123KE84	Ultra-small	0201	12000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM033R61A123ME84	Ultra-small	0201	12000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM033C80G153KE01	Ultra-small	0201	15000	+/-10[%]	4	X6S	100[kHz]-6[GHz]
GRM033R60J153KE01	Ultra-small	0201	15000	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM033C80J153ME01	Ultra-small	0201	15000	+/-20[%]	6.3	X6S	100[kHz]-6[GHz]
GRM033C80J153KE01	Ultra-small	0201	15000	+/-10[%]	6.3	X6S	100[kHz]-6[GHz]
GRM033R61A153KE84	Ultra-small	0201	15000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM033R61A153ME84	Ultra-small	0201	15000	+/-20[%]	10	X5R	100[kHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM033R61C153KE84	Ultra-small	0201	15000	+/-10[%]	16	X5R	100[kHz]-6[GHz]
GRM033R61C153ME84	Ultra-small	0201	15000	+/-20[%]	16	X5R	100[kHz]-6[GHz]
GRM033R61A183KE84	Ultra-small	0201	18000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM033R61A183ME84	Ultra-small	0201	18000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM033C80G223KE01	Ultra-small	0201	22000	+/-10[%]	4	X6S	100[kHz]-6[GHz]
GRM033R60J223KE01	Ultra-small	0201	22000	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM033C80J223ME01	Ultra-small	0201	22000	+/-20[%]	6.3	X6S	100[kHz]-6[GHz]
GRM033C80J223KE01	Ultra-small	0201	22000	+/-10[%]	6.3	X6S	100[kHz]-6[GHz]
GRM033R61A223KE84	Ultra-small	0201	22000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM033R61A223ME84	Ultra-small	0201	22000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM033R61C223KE84	Ultra-small	0201	22000	+/-10[%]	16	X5R	100[kHz]-6[GHz]
GRM033R61C223ME84	Ultra-small	0201	22000	+/-20[%]	16	X5R	100[kHz]-6[GHz]
GRM033R61A273KE84	Ultra-small	0201	27000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM033R61A273ME84	Ultra-small	0201	27000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM033C80G333KE01	Ultra-small	0201	33000	+/-10[%]	4	X6S	100[kHz]-6[GHz]
GRM033R60J333KE01	Ultra-small	0201	33000	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM033C80J333ME01	Ultra-small	0201	33000	+/-20[%]	6.3	X6S	100[kHz]-6[GHz]
GRM033C80J333KE01	Ultra-small	0201	33000	+/-10[%]	6.3	X6S	100[kHz]-6[GHz]
GRM033R61A333KE84	Ultra-small	0201	33000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM033R61A333ME84	Ultra-small	0201	33000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM033R61C333KE84	Ultra-small	0201	33000	+/-10[%]	16	X5R	100[kHz]-6[GHz]
GRM033R61C333ME84	Ultra-small	0201	33000	+/-20[%]	16	X5R	100[kHz]-6[GHz]
GRM033R61A393KE84	Ultra-small	0201	39000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM033R61A393ME84	Ultra-small	0201	39000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM033C80G473KE01	Ultra-small	0201	47000	+/-10[%]	4	X6S	100[kHz]-6[GHz]
GRM033R60J473KE19	Ultra-small	0201	47000	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM033C80J473ME19	Ultra-small	0201	47000	+/-20[%]	6.3	X6S	100[kHz]-6[GHz]
GRM033C80J473KE19	Ultra-small	0201	47000	+/-10[%]	6.3	X6S	100[kHz]-6[GHz]
GRM033R61A473KE84	Ultra-small	0201	47000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM033R61A473ME84	Ultra-small	0201	47000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM033R61C473KE84	Ultra-small	0201	47000	+/-10[%]	16	X5R	100[kHz]-6[GHz]
GRM033R61C473ME84	Ultra-small	0201	47000	+/-20[%]	16	X5R	100[kHz]-6[GHz]
GRM033C80J683KE84	Ultra-small	0201	68000	+/-10[%]	6.3	X6S	100[kHz]-6[GHz]
GRM033C80J683ME84	Ultra-small	0201	68000	+/-20[%]	6.3	X6S	100[kHz]-6[GHz]
GRM033R61A683KE84	Ultra-small	0201	68000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM033R61A683ME84	Ultra-small	0201	68000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM033R61C683KE84	Ultra-small	0201	68000	+/-10[%]	16	X5R	100[kHz]-6[GHz]
GRM033R61C683ME84	Ultra-small	0201	68000	+/-20[%]	16	X5R	100[kHz]-6[GHz]
GRM033C80G104KE19	Ultra-small	0201	100000	+/-10[%]	4	X6S	100[kHz]-6[GHz]
GRM033R60J104KE19	Ultra-small	0201	100000	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM033R60J104KE84	Ultra-small	0201	100000	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM033C80J104KE84	Ultra-small	0201	100000	+/-10[%]	6.3	X6S	100[kHz]-6[GHz]
GRM033C80J104ME84	Ultra-small	0201	100000	+/-20[%]	6.3	X6S	100[kHz]-6[GHz]
GRM033R61A104KE84	Ultra-small	0201	100000	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM033R61A104ME84	Ultra-small	0201	100000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM033R61C104KE84	Ultra-small	0201	100000	+/-10[%]	16	X5R	100[kHz]-6[GHz]
GRM033R61C104ME84	Ultra-small	0201	100000	+/-20[%]	16	X5R	100[kHz]-6[GHz]
GRM033C80E224ME15	Ultra-small	0201	220000	+/-20[%]	2.5	X6S	100[kHz]-6[GHz]
GRM033R60G224ME15	Ultra-small	0201	220000	+/-20[%]	4	X5R	100[kHz]-6[GHz]
GRM033C80G224ME15	Ultra-small	0201	220000	+/-20[%]	4	X6S	100[kHz]-6[GHz]
GRM033C80G224ME90	Ultra-small	0201	220000	+/-20[%]	4	X6S	100[kHz]-6[GHz]
GRM033R60J224ME15	Ultra-small	0201	220000	+/-20[%]	6.3	X5R	100[kHz]-6[GHz]
GRM033R60J224ME90	Ultra-small	0201	220000	+/-20[%]	6.3	X5R	100[kHz]-6[GHz]
GRM033C80J224ME90	Ultra-small	0201	220000	+/-20[%]	6.3	X6S	100[kHz]-6[GHz]
GRM033R61A224ME90	Ultra-small	0201	220000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM033R60G474ME90	Ultra-small	0201	470000	+/-20[%]	4	X5R	100[kHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM0225C1CR20BD05	Ultra-small	01005	0.2	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GRM0225C1CR20WD05	Ultra-small	01005	0.2	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GRM0225C1CR30BD05	Ultra-small	01005	0.3	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GRM0225C1CR30WD05	Ultra-small	01005	0.3	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GRM0225C1CR40BD05	Ultra-small	01005	0.4	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GRM0225C1CR40WD05	Ultra-small	01005	0.4	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GRM0225C1CR50BD05	Ultra-small	01005	0.5	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GRM0225C1CR50WD05	Ultra-small	01005	0.5	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GRM0225C1CR60BD05	Ultra-small	01005	0.6	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GRM0225C1CR60WD05	Ultra-small	01005	0.6	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GRM0225C1CR70BD05	Ultra-small	01005	0.7	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GRM0225C1CR70WD05	Ultra-small	01005	0.7	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GRM0225C1CR80BD05	Ultra-small	01005	0.8	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GRM0225C1CR80WD05	Ultra-small	01005	0.8	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GRM0225C1CR90BD05	Ultra-small	01005	0.9	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GRM0225C1CR90WD05	Ultra-small	01005	0.9	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GRM0225C1C1R0BD05	Ultra-small	01005	1	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GRM0225C1C1R0CD05	Ultra-small	01005	1	+/-0.25[pF]	16	C0G	100[MHz]-20[GHz]
GRM0225C1C1R0WD05	Ultra-small	01005	1	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GRM0225C1C1R1BD05	Ultra-small	01005	1.1	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R1CD05	Ultra-small	01005	1.1	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R1WD05	Ultra-small	01005	1.1	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R2BD05	Ultra-small	01005	1.2	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R2CD05	Ultra-small	01005	1.2	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R2WD05	Ultra-small	01005	1.2	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R3BD05	Ultra-small	01005	1.3	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R3CD05	Ultra-small	01005	1.3	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R3WD05	Ultra-small	01005	1.3	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R4BD05	Ultra-small	01005	1.4	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R4CD05	Ultra-small	01005	1.4	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R4WD05	Ultra-small	01005	1.4	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R5BD05	Ultra-small	01005	1.5	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R5CD05	Ultra-small	01005	1.5	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R5WD05	Ultra-small	01005	1.5	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R6BD05	Ultra-small	01005	1.6	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R6CD05	Ultra-small	01005	1.6	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R6WD05	Ultra-small	01005	1.6	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R7BD05	Ultra-small	01005	1.7	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R7CD05	Ultra-small	01005	1.7	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R7WD05	Ultra-small	01005	1.7	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R8BD05	Ultra-small	01005	1.8	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R8CD05	Ultra-small	01005	1.8	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R8WD05	Ultra-small	01005	1.8	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R9BD05	Ultra-small	01005	1.9	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R9CD05	Ultra-small	01005	1.9	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C1R9WD05	Ultra-small	01005	1.9	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R0BD05	Ultra-small	01005	2	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R0CD05	Ultra-small	01005	2	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R0WD05	Ultra-small	01005	2	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R1BD05	Ultra-small	01005	2.1	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R1CD05	Ultra-small	01005	2.1	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R1WD05	Ultra-small	01005	2.1	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R2BD05	Ultra-small	01005	2.2	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R2CD05	Ultra-small	01005	2.2	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R2WD05	Ultra-small	01005	2.2	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R3BD05	Ultra-small	01005	2.3	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM0225C1C2R3CD05	Ultra-small	01005	2.3	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R3WD05	Ultra-small	01005	2.3	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R4BD05	Ultra-small	01005	2.4	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R4CD05	Ultra-small	01005	2.4	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R4WD05	Ultra-small	01005	2.4	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R5BD05	Ultra-small	01005	2.5	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R5CD05	Ultra-small	01005	2.5	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R5WD05	Ultra-small	01005	2.5	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R6BD05	Ultra-small	01005	2.6	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R6CD05	Ultra-small	01005	2.6	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R6WD05	Ultra-small	01005	2.6	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R7BD05	Ultra-small	01005	2.7	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R7CD05	Ultra-small	01005	2.7	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R7WD05	Ultra-small	01005	2.7	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R8BD05	Ultra-small	01005	2.8	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R8CD05	Ultra-small	01005	2.8	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R8WD05	Ultra-small	01005	2.8	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R9BD05	Ultra-small	01005	2.9	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R9CD05	Ultra-small	01005	2.9	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C2R9WD05	Ultra-small	01005	2.9	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R0BD05	Ultra-small	01005	3	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R0CD05	Ultra-small	01005	3	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R0WD05	Ultra-small	01005	3	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R1BD05	Ultra-small	01005	3.1	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R1CD05	Ultra-small	01005	3.1	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R1WD05	Ultra-small	01005	3.1	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R2BD05	Ultra-small	01005	3.2	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R2CD05	Ultra-small	01005	3.2	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R2WD05	Ultra-small	01005	3.2	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R3BD05	Ultra-small	01005	3.3	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R3CD05	Ultra-small	01005	3.3	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R3WD05	Ultra-small	01005	3.3	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R4BD05	Ultra-small	01005	3.4	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R4CD05	Ultra-small	01005	3.4	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R4WD05	Ultra-small	01005	3.4	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R5BD05	Ultra-small	01005	3.5	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R5CD05	Ultra-small	01005	3.5	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R5WD05	Ultra-small	01005	3.5	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R6BD05	Ultra-small	01005	3.6	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R6CD05	Ultra-small	01005	3.6	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R6WD05	Ultra-small	01005	3.6	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R7BD05	Ultra-small	01005	3.7	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R7CD05	Ultra-small	01005	3.7	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R7WD05	Ultra-small	01005	3.7	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R8BD05	Ultra-small	01005	3.8	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R8CD05	Ultra-small	01005	3.8	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R8WD05	Ultra-small	01005	3.8	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R9BD05	Ultra-small	01005	3.9	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R9CD05	Ultra-small	01005	3.9	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C3R9WD05	Ultra-small	01005	3.9	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R0BD05	Ultra-small	01005	4	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R0CD05	Ultra-small	01005	4	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R0WD05	Ultra-small	01005	4	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R1BD05	Ultra-small	01005	4.1	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R1CD05	Ultra-small	01005	4.1	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R1WD05	Ultra-small	01005	4.1	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]



Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM0225C1C4R2BD05	Ultra-small	01005	4.2	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R2CD05	Ultra-small	01005	4.2	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R2WD05	Ultra-small	01005	4.2	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R3BD05	Ultra-small	01005	4.3	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R3CD05	Ultra-small	01005	4.3	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R3WD05	Ultra-small	01005	4.3	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R4BD05	Ultra-small	01005	4.4	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R4CD05	Ultra-small	01005	4.4	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R4WD05	Ultra-small	01005	4.4	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R5BD05	Ultra-small	01005	4.5	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R5CD05	Ultra-small	01005	4.5	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R5WD05	Ultra-small	01005	4.5	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R6BD05	Ultra-small	01005	4.6	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R6CD05	Ultra-small	01005	4.6	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R6WD05	Ultra-small	01005	4.6	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R7BD05	Ultra-small	01005	4.7	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R7CD05	Ultra-small	01005	4.7	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R7WD05	Ultra-small	01005	4.7	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R8BD05	Ultra-small	01005	4.8	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R8CD05	Ultra-small	01005	4.8	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R8WD05	Ultra-small	01005	4.8	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R9BD05	Ultra-small	01005	4.9	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R9CD05	Ultra-small	01005	4.9	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C4R9WD05	Ultra-small	01005	4.9	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R0BD05	Ultra-small	01005	5	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R0CD05	Ultra-small	01005	5	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R0WD05	Ultra-small	01005	5	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R1BD05	Ultra-small	01005	5.1	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R1CD05	Ultra-small	01005	5.1	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R1DD05	Ultra-small	01005	5.1	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R1WD05	Ultra-small	01005	5.1	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R2BD05	Ultra-small	01005	5.2	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R2CD05	Ultra-small	01005	5.2	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R2DD05	Ultra-small	01005	5.2	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R2WD05	Ultra-small	01005	5.2	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R3BD05	Ultra-small	01005	5.3	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R3CD05	Ultra-small	01005	5.3	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R3DD05	Ultra-small	01005	5.3	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R3WD05	Ultra-small	01005	5.3	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R4BD05	Ultra-small	01005	5.4	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R4CD05	Ultra-small	01005	5.4	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R4DD05	Ultra-small	01005	5.4	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R4WD05	Ultra-small	01005	5.4	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R5BD05	Ultra-small	01005	5.5	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R5CD05	Ultra-small	01005	5.5	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R5DD05	Ultra-small	01005	5.5	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R5WD05	Ultra-small	01005	5.5	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R6BD05	Ultra-small	01005	5.6	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R6CD05	Ultra-small	01005	5.6	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R6DD05	Ultra-small	01005	5.6	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R6WD05	Ultra-small	01005	5.6	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R7BD05	Ultra-small	01005	5.7	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R7CD05	Ultra-small	01005	5.7	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R7DD05	Ultra-small	01005	5.7	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R7WD05	Ultra-small	01005	5.7	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R8BD05	Ultra-small	01005	5.8	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM0225C1C5R8CD05	Ultra-small	01005	5.8	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R8DD05	Ultra-small	01005	5.8	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R8WD05	Ultra-small	01005	5.8	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R9BD05	Ultra-small	01005	5.9	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R9CD05	Ultra-small	01005	5.9	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R9DD05	Ultra-small	01005	5.9	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C5R9WD05	Ultra-small	01005	5.9	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R0BD05	Ultra-small	01005	6	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R0CD05	Ultra-small	01005	6	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R0DD05	Ultra-small	01005	6	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R0WD05	Ultra-small	01005	6	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R1BD05	Ultra-small	01005	6.1	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R1CD05	Ultra-small	01005	6.1	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R1DD05	Ultra-small	01005	6.1	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R1WD05	Ultra-small	01005	6.1	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R2BD05	Ultra-small	01005	6.2	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R2CD05	Ultra-small	01005	6.2	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R2DD05	Ultra-small	01005	6.2	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R2WD05	Ultra-small	01005	6.2	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R3BD05	Ultra-small	01005	6.3	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R3CD05	Ultra-small	01005	6.3	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R3DD05	Ultra-small	01005	6.3	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R3WD05	Ultra-small	01005	6.3	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R4BD05	Ultra-small	01005	6.4	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R4CD05	Ultra-small	01005	6.4	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R4DD05	Ultra-small	01005	6.4	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R4WD05	Ultra-small	01005	6.4	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R5BD05	Ultra-small	01005	6.5	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R5CD05	Ultra-small	01005	6.5	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R5DD05	Ultra-small	01005	6.5	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R5WD05	Ultra-small	01005	6.5	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R6BD05	Ultra-small	01005	6.6	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R6CD05	Ultra-small	01005	6.6	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R6DD05	Ultra-small	01005	6.6	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R6WD05	Ultra-small	01005	6.6	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R7BD05	Ultra-small	01005	6.7	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R7CD05	Ultra-small	01005	6.7	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R7DD05	Ultra-small	01005	6.7	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R7WD05	Ultra-small	01005	6.7	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R8BD05	Ultra-small	01005	6.8	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R8CD05	Ultra-small	01005	6.8	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R8DD05	Ultra-small	01005	6.8	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R8WD05	Ultra-small	01005	6.8	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R9BD05	Ultra-small	01005	6.9	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R9CD05	Ultra-small	01005	6.9	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R9DD05	Ultra-small	01005	6.9	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C6R9WD05	Ultra-small	01005	6.9	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R0BD05	Ultra-small	01005	7	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R0CD05	Ultra-small	01005	7	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R0DD05	Ultra-small	01005	7	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R0WD05	Ultra-small	01005	7	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R1BD05	Ultra-small	01005	7.1	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R1CD05	Ultra-small	01005	7.1	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R1DD05	Ultra-small	01005	7.1	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R1WD05	Ultra-small	01005	7.1	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R2BD05	Ultra-small	01005	7.2	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM0225C1C7R2CD05	Ultra-small	01005	7.2	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R2DD05	Ultra-small	01005	7.2	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R2WD05	Ultra-small	01005	7.2	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R3BD05	Ultra-small	01005	7.3	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R3CD05	Ultra-small	01005	7.3	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R3DD05	Ultra-small	01005	7.3	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R3WD05	Ultra-small	01005	7.3	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R4BD05	Ultra-small	01005	7.4	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R4CD05	Ultra-small	01005	7.4	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R4DD05	Ultra-small	01005	7.4	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R4WD05	Ultra-small	01005	7.4	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R5BD05	Ultra-small	01005	7.5	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R5CD05	Ultra-small	01005	7.5	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R5DD05	Ultra-small	01005	7.5	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R5WD05	Ultra-small	01005	7.5	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R6BD05	Ultra-small	01005	7.6	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R6CD05	Ultra-small	01005	7.6	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R6DD05	Ultra-small	01005	7.6	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R6WD05	Ultra-small	01005	7.6	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R7BD05	Ultra-small	01005	7.7	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R7CD05	Ultra-small	01005	7.7	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R7DD05	Ultra-small	01005	7.7	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R7WD05	Ultra-small	01005	7.7	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R8BD05	Ultra-small	01005	7.8	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R8CD05	Ultra-small	01005	7.8	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R8DD05	Ultra-small	01005	7.8	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R8WD05	Ultra-small	01005	7.8	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R9BD05	Ultra-small	01005	7.9	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R9CD05	Ultra-small	01005	7.9	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R9DD05	Ultra-small	01005	7.9	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C7R9WD05	Ultra-small	01005	7.9	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R0BD05	Ultra-small	01005	8	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R0CD05	Ultra-small	01005	8	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R0DD05	Ultra-small	01005	8	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R0WD05	Ultra-small	01005	8	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R1BD05	Ultra-small	01005	8.1	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R1CD05	Ultra-small	01005	8.1	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R1DD05	Ultra-small	01005	8.1	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R1WD05	Ultra-small	01005	8.1	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R2BD05	Ultra-small	01005	8.2	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R2CD05	Ultra-small	01005	8.2	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R2DD05	Ultra-small	01005	8.2	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R2WD05	Ultra-small	01005	8.2	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R3BD05	Ultra-small	01005	8.3	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R3CD05	Ultra-small	01005	8.3	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R3DD05	Ultra-small	01005	8.3	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R3WD05	Ultra-small	01005	8.3	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R4BD05	Ultra-small	01005	8.4	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R4CD05	Ultra-small	01005	8.4	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R4DD05	Ultra-small	01005	8.4	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R4WD05	Ultra-small	01005	8.4	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R5BD05	Ultra-small	01005	8.5	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R5CD05	Ultra-small	01005	8.5	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R5DD05	Ultra-small	01005	8.5	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R5WD05	Ultra-small	01005	8.5	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R6BD05	Ultra-small	01005	8.6	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM0225C1C8R6CD05	Ultra-small	01005	8.6	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R6DD05	Ultra-small	01005	8.6	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R6WD05	Ultra-small	01005	8.6	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R7BD05	Ultra-small	01005	8.7	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R7CD05	Ultra-small	01005	8.7	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R7DD05	Ultra-small	01005	8.7	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R7WD05	Ultra-small	01005	8.7	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R8BD05	Ultra-small	01005	8.8	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R8CD05	Ultra-small	01005	8.8	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R8DD05	Ultra-small	01005	8.8	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R8WD05	Ultra-small	01005	8.8	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R9BD05	Ultra-small	01005	8.9	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R9CD05	Ultra-small	01005	8.9	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R9DD05	Ultra-small	01005	8.9	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C8R9WD05	Ultra-small	01005	8.9	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R0BD05	Ultra-small	01005	9	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R0CD05	Ultra-small	01005	9	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R0DD05	Ultra-small	01005	9	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R0WD05	Ultra-small	01005	9	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R1BD05	Ultra-small	01005	9.1	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R1CD05	Ultra-small	01005	9.1	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R1DD05	Ultra-small	01005	9.1	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R1WD05	Ultra-small	01005	9.1	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R2BD05	Ultra-small	01005	9.2	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R2CD05	Ultra-small	01005	9.2	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R2DD05	Ultra-small	01005	9.2	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R2WD05	Ultra-small	01005	9.2	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R3BD05	Ultra-small	01005	9.3	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R3CD05	Ultra-small	01005	9.3	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R3DD05	Ultra-small	01005	9.3	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R3WD05	Ultra-small	01005	9.3	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R4BD05	Ultra-small	01005	9.4	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R4CD05	Ultra-small	01005	9.4	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R4DD05	Ultra-small	01005	9.4	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R4WD05	Ultra-small	01005	9.4	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R5BD05	Ultra-small	01005	9.5	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R5CD05	Ultra-small	01005	9.5	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R5DD05	Ultra-small	01005	9.5	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R5WD05	Ultra-small	01005	9.5	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R6BD05	Ultra-small	01005	9.6	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R6CD05	Ultra-small	01005	9.6	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R6DD05	Ultra-small	01005	9.6	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R6WD05	Ultra-small	01005	9.6	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R7BD05	Ultra-small	01005	9.7	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R7CD05	Ultra-small	01005	9.7	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R7DD05	Ultra-small	01005	9.7	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R7WD05	Ultra-small	01005	9.7	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R8BD05	Ultra-small	01005	9.8	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R8CD05	Ultra-small	01005	9.8	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R8DD05	Ultra-small	01005	9.8	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R8WD05	Ultra-small	01005	9.8	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R9BD05	Ultra-small	01005	9.9	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R9CD05	Ultra-small	01005	9.9	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R9DD05	Ultra-small	01005	9.9	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C9R9WD05	Ultra-small	01005	9.9	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C100GD05	Ultra-small	01005	10	+/-2[%]	16	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM0225C1C100JD05	Ultra-small	01005	10	+/-5[%]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C120GD05	Ultra-small	01005	12	+/-2[%]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C120JD05	Ultra-small	01005	12	+/-5[%]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C150GD05	Ultra-small	01005	15	+/-2[%]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C150JD05	Ultra-small	01005	15	+/-5[%]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C180GD05	Ultra-small	01005	18	+/-2[%]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C180JD05	Ultra-small	01005	18	+/-5[%]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C220GD05	Ultra-small	01005	22	+/-2[%]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C220JD05	Ultra-small	01005	22	+/-5[%]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C270GD05	Ultra-small	01005	27	+/-2[%]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C270JD05	Ultra-small	01005	27	+/-5[%]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C330GD05	Ultra-small	01005	33	+/-2[%]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C330JD05	Ultra-small	01005	33	+/-5[%]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C390GD05	Ultra-small	01005	39	+/-2[%]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C390JD05	Ultra-small	01005	39	+/-5[%]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C470GD05	Ultra-small	01005	47	+/-2[%]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C1C470JD05	Ultra-small	01005	47	+/-5[%]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C0J560GD05	Ultra-small	01005	56	+/-2[%]	6.3	C0G	100[MHz]-8.5[GHz]
GRM0225C0J560JD05	Ultra-small	01005	56	+/-5[%]	6.3	C0G	100[MHz]-8.5[GHz]
GRM0225C1A560GD05	Ultra-small	01005	56	+/-2[%]	10	C0G	100[MHz]-8.5[GHz]
GRM0225C1A560JD05	Ultra-small	01005	56	+/-5[%]	10	C0G	100[MHz]-8.5[GHz]
GRM0225C1C560JDAE	Ultra-small	01005	56	+/-5[%]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C0J680GD05	Ultra-small	01005	68	+/-2[%]	6.3	C0G	100[MHz]-8.5[GHz]
GRM0225C0J680JD05	Ultra-small	01005	68	+/-5[%]	6.3	C0G	100[MHz]-8.5[GHz]
GRM0225C1A680GD05	Ultra-small	01005	68	+/-2[%]	10	C0G	100[MHz]-8.5[GHz]
GRM0225C1A680JD05	Ultra-small	01005	68	+/-5[%]	10	C0G	100[MHz]-8.5[GHz]
GRM022R61A680KA01	Ultra-small	01005	68	+/-10[%]	10	X5R	5[MHz]-6[GHz]
GRM022R61A680MA01	Ultra-small	01005	68	+/-20[%]	10	X5R	5[MHz]-6[GHz]
GRM022R71A680KA01	Ultra-small	01005	68	+/-10[%]	10	X7R	5[MHz]-6[GHz]
GRM022R71A680MA01	Ultra-small	01005	68	+/-20[%]	10	X7R	5[MHz]-6[GHz]
GRM0225C1C680JDAE	Ultra-small	01005	68	+/-5[%]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C0J820GD05	Ultra-small	01005	82	+/-2[%]	6.3	C0G	100[MHz]-8.5[GHz]
GRM0225C0J820JD05	Ultra-small	01005	82	+/-5[%]	6.3	C0G	100[MHz]-8.5[GHz]
GRM0225C1A820GD05	Ultra-small	01005	82	+/-2[%]	10	C0G	100[MHz]-8.5[GHz]
GRM0225C1A820JD05	Ultra-small	01005	82	+/-5[%]	10	C0G	100[MHz]-8.5[GHz]
GRM0225C1C820JDAE	Ultra-small	01005	82	+/-5[%]	16	C0G	100[MHz]-8.5[GHz]
GRM0225C0J101GD05	Ultra-small	01005	100	+/-2[%]	6.3	C0G	100[MHz]-8.5[GHz]
GRM0225C0J101JD05	Ultra-small	01005	100	+/-5[%]	6.3	C0G	100[MHz]-8.5[GHz]
GRM0225C1A101GD05	Ultra-small	01005	100	+/-2[%]	10	C0G	100[MHz]-8.5[GHz]
GRM0225C1A101JD05	Ultra-small	01005	100	+/-5[%]	10	C0G	100[MHz]-8.5[GHz]
GRM022R61A101KA01	Ultra-small	01005	100	+/-10[%]	10	X5R	5[MHz]-6[GHz]
GRM022R61A101MA01	Ultra-small	01005	100	+/-20[%]	10	X5R	5[MHz]-6[GHz]
GRM022R71A101KA01	Ultra-small	01005	100	+/-10[%]	10	X7R	5[MHz]-6[GHz]
GRM022R71A101MA01	Ultra-small	01005	100	+/-20[%]	10	X7R	5[MHz]-6[GHz]
GRM0225C1C101JDAE	Ultra-small	01005	100	+/-5[%]	16	C0G	100[MHz]-8.5[GHz]
GRM022R61A151KA01	Ultra-small	01005	150	+/-10[%]	10	X5R	1[MHz]-6[GHz]
GRM022R61A151MA01	Ultra-small	01005	150	+/-20[%]	10	X5R	1[MHz]-6[GHz]
GRM022R71A151KA01	Ultra-small	01005	150	+/-10[%]	10	X7R	1[MHz]-6[GHz]
GRM022R71A151MA01	Ultra-small	01005	150	+/-20[%]	10	X7R	1[MHz]-6[GHz]
GRM022R71A181KA01	Ultra-small	01005	180	+/-10[%]	10	X7R	1[MHz]-6[GHz]
GRM022R61A221KA01	Ultra-small	01005	220	+/-10[%]	10	X5R	3[MHz]-6[GHz]
GRM022R61A221MA01	Ultra-small	01005	220	+/-20[%]	10	X5R	3[MHz]-6[GHz]
GRM022R71A221KA01	Ultra-small	01005	220	+/-10[%]	10	X7R	3[MHz]-6[GHz]
GRM022R71A221MA01	Ultra-small	01005	220	+/-20[%]	10	X7R	3[MHz]-6[GHz]
GRM022R61A331KA01	Ultra-small	01005	330	+/-10[%]	10	X5R	1[MHz]-6[GHz]
GRM022R61A331MA01	Ultra-small	01005	330	+/-20[%]	10	X5R	1[MHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM022R71A331KA01	Ultra-small	01005	330	+/-10[%]	10	X7R	1[MHz]-6[GHz]
GRM022R71A331MA01	Ultra-small	01005	330	+/-20[%]	10	X7R	1[MHz]-6[GHz]
GRM022R61A471KA01	Ultra-small	01005	470	+/-10[%]	10	X5R	1[MHz]-6[GHz]
GRM022R61A471MA01	Ultra-small	01005	470	+/-20[%]	10	X5R	1[MHz]-6[GHz]
GRM022R71A471KA01	Ultra-small	01005	470	+/-10[%]	10	X7R	1[MHz]-6[GHz]
GRM022R71A471MA01	Ultra-small	01005	470	+/-20[%]	10	X7R	1[MHz]-6[GHz]
GRM022R60J681KE19	Ultra-small	01005	680	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM022R60J681ME19	Ultra-small	01005	680	+/-20[%]	6.3	X5R	100[kHz]-6[GHz]
GRM022R61A681KE19	Ultra-small	01005	680	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM022R61A681ME19	Ultra-small	01005	680	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM022R71A681KA12	Ultra-small	01005	680	+/-10[%]	10	X7R	1[MHz]-6[GHz]
GRM022R71A681MA12	Ultra-small	01005	680	+/-20[%]	10	X7R	1[MHz]-6[GHz]
GRM022R71A821KA12	Ultra-small	01005	820	+/-10[%]	10	X7R	1[MHz]-6[GHz]
GRM022R71A821MA12	Ultra-small	01005	820	+/-20[%]	10	X7R	1[MHz]-6[GHz]
GRM022R60J102KE19	Ultra-small	01005	1000	+/-10[%]	6.3	X5R	300[kHz]-6[GHz]
GRM022R60J102ME19	Ultra-small	01005	1000	+/-20[%]	6.3	X5R	300[kHz]-6[GHz]
GRM022R61A102KE19	Ultra-small	01005	1000	+/-10[%]	10	X5R	300[kHz]-6[GHz]
GRM022R61A102ME19	Ultra-small	01005	1000	+/-20[%]	10	X5R	300[kHz]-6[GHz]
GRM022R71A102KA12	Ultra-small	01005	1000	+/-10[%]	10	X7R	300[kHz]-6[GHz]
GRM022R71A102MA12	Ultra-small	01005	1000	+/-20[%]	10	X7R	300[kHz]-6[GHz]
GRM022R60J152KE19	Ultra-small	01005	1500	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM022R60J152ME19	Ultra-small	01005	1500	+/-20[%]	6.3	X5R	100[kHz]-6[GHz]
GRM022R61A152KE19	Ultra-small	01005	1500	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM022R61A152ME19	Ultra-small	01005	1500	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM022R60J222KE19	Ultra-small	01005	2200	+/-10[%]	6.3	X5R	300[kHz]-6[GHz]
GRM022R60J222ME19	Ultra-small	01005	2200	+/-20[%]	6.3	X5R	300[kHz]-6[GHz]
GRM022R61A222KE19	Ultra-small	01005	2200	+/-10[%]	10	X5R	300[kHz]-6[GHz]
GRM022R61A222ME19	Ultra-small	01005	2200	+/-20[%]	10	X5R	300[kHz]-6[GHz]
GRM022R60J332KE19	Ultra-small	01005	3300	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM022R60J332ME19	Ultra-small	01005	3300	+/-20[%]	6.3	X5R	100[kHz]-6[GHz]
GRM022R61A332KE19	Ultra-small	01005	3300	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM022R61A332ME19	Ultra-small	01005	3300	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM022R60J472KE19	Ultra-small	01005	4700	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM022R60J472ME19	Ultra-small	01005	4700	+/-20[%]	6.3	X5R	100[kHz]-6[GHz]
GRM022R61A472KE19	Ultra-small	01005	4700	+/-10[%]	10	X5R	3[MHz]-6[GHz]
GRM022R61A472ME19	Ultra-small	01005	4700	+/-20[%]	10	X5R	3[MHz]-6[GHz]
GRM022R61A562KE19	Ultra-small	01005	5600	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM022R60J682KE19	Ultra-small	01005	6800	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM022R60J682ME19	Ultra-small	01005	6800	+/-20[%]	6.3	X5R	100[kHz]-6[GHz]
GRM022R61A682KE19	Ultra-small	01005	6800	+/-10[%]	10	X5R	100[kHz]-6[GHz]
GRM022R61A682ME19	Ultra-small	01005	6800	+/-20[%]	10	X5R	100[kHz]-6[GHz]
GRM022R60J103KE19	Ultra-small	01005	10000	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM022R60J103ME19	Ultra-small	01005	10000	+/-20[%]	6.3	X5R	100[kHz]-6[GHz]
GRM022R61A103KE19	Ultra-small	01005	10000	+/-10[%]	10	X5R	1[MHz]-6[GHz]
GRM022R61A103ME19	Ultra-small	01005	10000	+/-20[%]	10	X5R	1[MHz]-6[GHz]
GRM022R60G153KE15	Ultra-small	01005	15000	+/-10[%]	4	X5R	100[kHz]-6[GHz]
GRM022R60G153ME15	Ultra-small	01005	15000	+/-20[%]	4	X5R	100[kHz]-6[GHz]
GRM022R60J153ME15	Ultra-small	01005	15000	+/-20[%]	6.3	X5R	100[kHz]-6[GHz]
GRM022R60G223KE15	Ultra-small	01005	22000	+/-10[%]	4	X5R	100[kHz]-6[GHz]
GRM022R60G223ME15	Ultra-small	01005	22000	+/-20[%]	4	X5R	100[kHz]-6[GHz]
GRM022R60J223ME15	Ultra-small	01005	22000	+/-20[%]	6.3	X5R	100[kHz]-6[GHz]
GRM022R60J223KE15	Ultra-small	01005	22000	+/-10[%]	6.3	X5R	100[kHz]-6[GHz]
GRM022R60G333ME15	Ultra-small	01005	33000	+/-20[%]	4	X5R	100[kHz]-6[GHz]
GRM022R60G333KE15	Ultra-small	01005	33000	+/-10[%]	4	X5R	100[kHz]-6[GHz]
GRM022R60J333ME15	Ultra-small	01005	33000	+/-20[%]	6.3	X5R	100[kHz]-6[GHz]
GRM022R60G473ME15	Ultra-small	01005	47000	+/-20[%]	4	X5R	100[kHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM022R60G473KE15	Ultra-small	01005	47000	+/-10[%]	4	X5R	100[kHz]-6[GHz]
GRM022R60J473ME15	Ultra-small	01005	47000	+/-20[%]	6.3	X5R	100[kHz]-6[GHz]
GRM022R60G683ME15	Ultra-small	01005	68000	+/-20[%]	4	X5R	100[kHz]-6[GHz]
GRM022R60J683ME15	Ultra-small	01005	68000	+/-20[%]	6.3	X5R	100[kHz]-6[GHz]
GRM022R60G104ME15	Ultra-small	01005	100000	+/-20[%]	4	X5R	100[kHz]-6[GHz]
GRM022R60J104ME15	Ultra-small	01005	100000	+/-20[%]	6.3	X5R	100[kHz]-6[GHz]
GJM0335C1ER20BB01	High-Q	0201	0.2	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0335C1ER20WB01	High-Q	0201	0.2	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0335C1ER30BB01	High-Q	0201	0.3	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0335C1ER30WB01	High-Q	0201	0.3	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0335C1ER40BB01	High-Q	0201	0.4	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0335C1ER40WB01	High-Q	0201	0.4	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0335C1ER50BB01	High-Q	0201	0.5	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0335C1ER50WB01	High-Q	0201	0.5	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0335C1ER60BB01	High-Q	0201	0.6	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0335C1ER60WB01	High-Q	0201	0.6	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0335C1ER70BB01	High-Q	0201	0.7	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0335C1ER70WB01	High-Q	0201	0.7	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0335C1ER75BB01	High-Q	0201	0.75	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1ER80BB01	High-Q	0201	0.8	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0335C1ER80WB01	High-Q	0201	0.8	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0335C1ER90BB01	High-Q	0201	0.9	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0335C1ER90WB01	High-Q	0201	0.9	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0335C1E1R0BB01	High-Q	0201	1	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0335C1E1R0CB01	High-Q	0201	1	+/-0.25[pF]	25	C0G	100[MHz]-20[GHz]
GJM0335C1E1R0WB01	High-Q	0201	1	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0335C1E1R1BB01	High-Q	0201	1.1	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R1CB01	High-Q	0201	1.1	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R1WB01	High-Q	0201	1.1	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R2BB01	High-Q	0201	1.2	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R2CB01	High-Q	0201	1.2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R2WB01	High-Q	0201	1.2	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R3BB01	High-Q	0201	1.3	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R3CB01	High-Q	0201	1.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R3WB01	High-Q	0201	1.3	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R4BB01	High-Q	0201	1.4	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R4CB01	High-Q	0201	1.4	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R4WB01	High-Q	0201	1.4	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R5BB01	High-Q	0201	1.5	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R5CB01	High-Q	0201	1.5	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R5WB01	High-Q	0201	1.5	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R6BB01	High-Q	0201	1.6	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R6CB01	High-Q	0201	1.6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R6WB01	High-Q	0201	1.6	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R7BB01	High-Q	0201	1.7	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R7CB01	High-Q	0201	1.7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R7WB01	High-Q	0201	1.7	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R8BB01	High-Q	0201	1.8	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R8CB01	High-Q	0201	1.8	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R8WB01	High-Q	0201	1.8	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R9BB01	High-Q	0201	1.9	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R9CB01	High-Q	0201	1.9	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E1R9WB01	High-Q	0201	1.9	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R0BB01	High-Q	0201	2	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R0CB01	High-Q	0201	2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R0WB01	High-Q	0201	2	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM0335C1E2R1BB01	High-Q	0201	2.1	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R1CB01	High-Q	0201	2.1	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R1WB01	High-Q	0201	2.1	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R2BB01	High-Q	0201	2.2	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R2CB01	High-Q	0201	2.2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R2WB01	High-Q	0201	2.2	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R3BB01	High-Q	0201	2.3	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R3CB01	High-Q	0201	2.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R3WB01	High-Q	0201	2.3	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R4BB01	High-Q	0201	2.4	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R4CB01	High-Q	0201	2.4	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R4WB01	High-Q	0201	2.4	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R5BB01	High-Q	0201	2.5	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R5CB01	High-Q	0201	2.5	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R5WB01	High-Q	0201	2.5	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R6BB01	High-Q	0201	2.6	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R6CB01	High-Q	0201	2.6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R6WB01	High-Q	0201	2.6	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R7BB01	High-Q	0201	2.7	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R7CB01	High-Q	0201	2.7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R7WB01	High-Q	0201	2.7	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R8BB01	High-Q	0201	2.8	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R8CB01	High-Q	0201	2.8	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R8WB01	High-Q	0201	2.8	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R9BB01	High-Q	0201	2.9	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R9CB01	High-Q	0201	2.9	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E2R9WB01	High-Q	0201	2.9	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R0BB01	High-Q	0201	3	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R0CB01	High-Q	0201	3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R0WB01	High-Q	0201	3	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R1BB01	High-Q	0201	3.1	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R1CB01	High-Q	0201	3.1	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R1WB01	High-Q	0201	3.1	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R2BB01	High-Q	0201	3.2	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R2CB01	High-Q	0201	3.2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R2WB01	High-Q	0201	3.2	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R3BB01	High-Q	0201	3.3	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R3CB01	High-Q	0201	3.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R3WB01	High-Q	0201	3.3	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R4BB01	High-Q	0201	3.4	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R4CB01	High-Q	0201	3.4	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R4WB01	High-Q	0201	3.4	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R5BB01	High-Q	0201	3.5	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R5CB01	High-Q	0201	3.5	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R5WB01	High-Q	0201	3.5	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R6BB01	High-Q	0201	3.6	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R6CB01	High-Q	0201	3.6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R6WB01	High-Q	0201	3.6	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R7BB01	High-Q	0201	3.7	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R7CB01	High-Q	0201	3.7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R7WB01	High-Q	0201	3.7	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R8BB01	High-Q	0201	3.8	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R8CB01	High-Q	0201	3.8	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R8WB01	High-Q	0201	3.8	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R9BB01	High-Q	0201	3.9	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E3R9CB01	High-Q	0201	3.9	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]



Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM0335C1E3R9WB01	High-Q	0201	3.9	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R0BB01	High-Q	0201	4	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R0CB01	High-Q	0201	4	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R0WB01	High-Q	0201	4	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R1BB01	High-Q	0201	4.1	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R1CB01	High-Q	0201	4.1	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R1WB01	High-Q	0201	4.1	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R2BB01	High-Q	0201	4.2	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R2CB01	High-Q	0201	4.2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R2WB01	High-Q	0201	4.2	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R3BB01	High-Q	0201	4.3	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R3CB01	High-Q	0201	4.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R3WB01	High-Q	0201	4.3	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R4BB01	High-Q	0201	4.4	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R4CB01	High-Q	0201	4.4	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R4WB01	High-Q	0201	4.4	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R5BB01	High-Q	0201	4.5	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R5CB01	High-Q	0201	4.5	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R5WB01	High-Q	0201	4.5	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R6BB01	High-Q	0201	4.6	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R6CB01	High-Q	0201	4.6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R6WB01	High-Q	0201	4.6	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R7BB01	High-Q	0201	4.7	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R7CB01	High-Q	0201	4.7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R7WB01	High-Q	0201	4.7	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R8BB01	High-Q	0201	4.8	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R8CB01	High-Q	0201	4.8	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R8WB01	High-Q	0201	4.8	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R9BB01	High-Q	0201	4.9	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R9CB01	High-Q	0201	4.9	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E4R9WB01	High-Q	0201	4.9	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R0BB01	High-Q	0201	5	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R0CB01	High-Q	0201	5	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R0WB01	High-Q	0201	5	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R1BB01	High-Q	0201	5.1	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R1CB01	High-Q	0201	5.1	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R1DB01	High-Q	0201	5.1	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R1WB01	High-Q	0201	5.1	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R2BB01	High-Q	0201	5.2	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R2CB01	High-Q	0201	5.2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R2DB01	High-Q	0201	5.2	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R2WB01	High-Q	0201	5.2	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R3BB01	High-Q	0201	5.3	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R3CB01	High-Q	0201	5.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R3DB01	High-Q	0201	5.3	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R3WB01	High-Q	0201	5.3	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R4BB01	High-Q	0201	5.4	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R4CB01	High-Q	0201	5.4	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R4DB01	High-Q	0201	5.4	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R4WB01	High-Q	0201	5.4	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R5BB01	High-Q	0201	5.5	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R5CB01	High-Q	0201	5.5	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R5DB01	High-Q	0201	5.5	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R5WB01	High-Q	0201	5.5	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R6BB01	High-Q	0201	5.6	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R6CB01	High-Q	0201	5.6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM0335C1E5R6DB01	High-Q	0201	5.6	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R6WB01	High-Q	0201	5.6	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R7BB01	High-Q	0201	5.7	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R7CB01	High-Q	0201	5.7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R7DB01	High-Q	0201	5.7	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R7WB01	High-Q	0201	5.7	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R8BB01	High-Q	0201	5.8	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R8CB01	High-Q	0201	5.8	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R8DB01	High-Q	0201	5.8	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R8WB01	High-Q	0201	5.8	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R9BB01	High-Q	0201	5.9	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R9CB01	High-Q	0201	5.9	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R9DB01	High-Q	0201	5.9	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E5R9WB01	High-Q	0201	5.9	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R0BB01	High-Q	0201	6	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R0CB01	High-Q	0201	6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R0DB01	High-Q	0201	6	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R0WB01	High-Q	0201	6	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R1BB01	High-Q	0201	6.1	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R1CB01	High-Q	0201	6.1	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R1DB01	High-Q	0201	6.1	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R1WB01	High-Q	0201	6.1	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R2BB01	High-Q	0201	6.2	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R2CB01	High-Q	0201	6.2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R2DB01	High-Q	0201	6.2	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R2WB01	High-Q	0201	6.2	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R3BB01	High-Q	0201	6.3	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R3CB01	High-Q	0201	6.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R3DB01	High-Q	0201	6.3	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R3WB01	High-Q	0201	6.3	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R4BB01	High-Q	0201	6.4	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R4CB01	High-Q	0201	6.4	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R4DB01	High-Q	0201	6.4	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R4WB01	High-Q	0201	6.4	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R5BB01	High-Q	0201	6.5	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R5CB01	High-Q	0201	6.5	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R5DB01	High-Q	0201	6.5	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R5WB01	High-Q	0201	6.5	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R6BB01	High-Q	0201	6.6	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R6CB01	High-Q	0201	6.6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R6DB01	High-Q	0201	6.6	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R6WB01	High-Q	0201	6.6	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R7BB01	High-Q	0201	6.7	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R7CB01	High-Q	0201	6.7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R7DB01	High-Q	0201	6.7	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R7WB01	High-Q	0201	6.7	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R8BB01	High-Q	0201	6.8	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R8CB01	High-Q	0201	6.8	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R8DB01	High-Q	0201	6.8	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R8WB01	High-Q	0201	6.8	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R9BB01	High-Q	0201	6.9	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R9CB01	High-Q	0201	6.9	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R9DB01	High-Q	0201	6.9	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E6R9WB01	High-Q	0201	6.9	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R0BB01	High-Q	0201	7	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R0CB01	High-Q	0201	7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM0335C1E7R0DB01	High-Q	0201	7	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R0WB01	High-Q	0201	7	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0336C1E7R0BB01	High-Q	0201	7	+/-0.1[pF]	25	C0H	100[MHz]-8.5[GHz]
GJM0336C1E7R0CB01	High-Q	0201	7	+/-0.25[pF]	25	C0H	100[MHz]-8.5[GHz]
GJM0336C1E7R0DB01	High-Q	0201	7	+/-0.5[pF]	25	C0H	100[MHz]-8.5[GHz]
GJM0336C1E7R0WB01	High-Q	0201	7	+/-0.05[pF]	25	C0H	100[MHz]-8.5[GHz]
GJM0335C1E7R1BB01	High-Q	0201	7.1	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R1CB01	High-Q	0201	7.1	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R1DB01	High-Q	0201	7.1	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R1WB01	High-Q	0201	7.1	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R2BB01	High-Q	0201	7.2	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R2CB01	High-Q	0201	7.2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R2DB01	High-Q	0201	7.2	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R2WB01	High-Q	0201	7.2	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R3BB01	High-Q	0201	7.3	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R3CB01	High-Q	0201	7.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R3DB01	High-Q	0201	7.3	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R3WB01	High-Q	0201	7.3	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R4BB01	High-Q	0201	7.4	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R4CB01	High-Q	0201	7.4	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R4DB01	High-Q	0201	7.4	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R4WB01	High-Q	0201	7.4	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R5BB01	High-Q	0201	7.5	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R5CB01	High-Q	0201	7.5	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R5DB01	High-Q	0201	7.5	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R5WB01	High-Q	0201	7.5	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0336C1E7R5BB01	High-Q	0201	7.5	+/-0.1[pF]	25	C0H	100[MHz]-8.5[GHz]
GJM0335C1E7R6BB01	High-Q	0201	7.6	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R6CB01	High-Q	0201	7.6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R6DB01	High-Q	0201	7.6	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R6WB01	High-Q	0201	7.6	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R7BB01	High-Q	0201	7.7	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R7CB01	High-Q	0201	7.7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R7DB01	High-Q	0201	7.7	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R7WB01	High-Q	0201	7.7	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R8BB01	High-Q	0201	7.8	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R8CB01	High-Q	0201	7.8	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R8DB01	High-Q	0201	7.8	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R8WB01	High-Q	0201	7.8	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R9BB01	High-Q	0201	7.9	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R9CB01	High-Q	0201	7.9	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R9DB01	High-Q	0201	7.9	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E7R9WB01	High-Q	0201	7.9	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R0BB01	High-Q	0201	8	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R0CB01	High-Q	0201	8	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R0DB01	High-Q	0201	8	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R0WB01	High-Q	0201	8	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0336C1E8R0BB01	High-Q	0201	8	+/-0.1[pF]	25	C0H	100[MHz]-8.5[GHz]
GJM0336C1E8R0CB01	High-Q	0201	8	+/-0.25[pF]	25	C0H	100[MHz]-8.5[GHz]
GJM0336C1E8R0DB01	High-Q	0201	8	+/-0.5[pF]	25	C0H	100[MHz]-8.5[GHz]
GJM0336C1E8R0WB01	High-Q	0201	8	+/-0.05[pF]	25	C0H	100[MHz]-8.5[GHz]
GJM0335C1E8R1BB01	High-Q	0201	8.1	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R1CB01	High-Q	0201	8.1	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R1DB01	High-Q	0201	8.1	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R1WB01	High-Q	0201	8.1	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R2BB01	High-Q	0201	8.2	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM0335C1E8R2CB01	High-Q	0201	8.2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R2DB01	High-Q	0201	8.2	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R2WB01	High-Q	0201	8.2	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0336C1E8R2BB01	High-Q	0201	8.2	+/-0.1[pF]	25	C0H	100[MHz]-8.5[GHz]
GJM0335C1E8R3BB01	High-Q	0201	8.3	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R3CB01	High-Q	0201	8.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R3DB01	High-Q	0201	8.3	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R3WB01	High-Q	0201	8.3	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R4BB01	High-Q	0201	8.4	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R4CB01	High-Q	0201	8.4	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R4DB01	High-Q	0201	8.4	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R4WB01	High-Q	0201	8.4	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R5BB01	High-Q	0201	8.5	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R5CB01	High-Q	0201	8.5	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R5DB01	High-Q	0201	8.5	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R5WB01	High-Q	0201	8.5	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R6BB01	High-Q	0201	8.6	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R6CB01	High-Q	0201	8.6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R6DB01	High-Q	0201	8.6	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R6WB01	High-Q	0201	8.6	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R7BB01	High-Q	0201	8.7	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R7CB01	High-Q	0201	8.7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R7DB01	High-Q	0201	8.7	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R7WB01	High-Q	0201	8.7	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R8BB01	High-Q	0201	8.8	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R8CB01	High-Q	0201	8.8	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R8DB01	High-Q	0201	8.8	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R8WB01	High-Q	0201	8.8	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R9BB01	High-Q	0201	8.9	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R9CB01	High-Q	0201	8.9	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R9DB01	High-Q	0201	8.9	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E8R9WB01	High-Q	0201	8.9	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R0BB01	High-Q	0201	9	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R0CB01	High-Q	0201	9	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R0DB01	High-Q	0201	9	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R0WB01	High-Q	0201	9	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0336C1E9R0BB01	High-Q	0201	9	+/-0.1[pF]	25	C0H	100[MHz]-8.5[GHz]
GJM0336C1E9R0CB01	High-Q	0201	9	+/-0.25[pF]	25	C0H	100[MHz]-8.5[GHz]
GJM0336C1E9R0DB01	High-Q	0201	9	+/-0.5[pF]	25	C0H	100[MHz]-8.5[GHz]
GJM0336C1E9R0WB01	High-Q	0201	9	+/-0.05[pF]	25	C0H	100[MHz]-8.5[GHz]
GJM0335C1E9R1BB01	High-Q	0201	9.1	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R1CB01	High-Q	0201	9.1	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R1DB01	High-Q	0201	9.1	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R1WB01	High-Q	0201	9.1	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0336C1E9R1BB01	High-Q	0201	9.1	+/-0.1[pF]	25	C0H	100[MHz]-8.5[GHz]
GJM0336C1E9R1CB01	High-Q	0201	9.1	+/-0.25[pF]	25	C0H	100[MHz]-8.5[GHz]
GJM0336C1E9R1DB01	High-Q	0201	9.1	+/-0.5[pF]	25	C0H	100[MHz]-8.5[GHz]
GJM0336C1E9R1WB01	High-Q	0201	9.1	+/-0.05[pF]	25	C0H	100[MHz]-8.5[GHz]
GJM0335C1E9R2BB01	High-Q	0201	9.2	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R2CB01	High-Q	0201	9.2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R2DB01	High-Q	0201	9.2	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R2WB01	High-Q	0201	9.2	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R3BB01	High-Q	0201	9.3	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R3CB01	High-Q	0201	9.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R3DB01	High-Q	0201	9.3	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R3WB01	High-Q	0201	9.3	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM0335C1E9R4BB01	High-Q	0201	9.4	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R4CB01	High-Q	0201	9.4	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R4DB01	High-Q	0201	9.4	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R4WB01	High-Q	0201	9.4	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R5BB01	High-Q	0201	9.5	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R5CB01	High-Q	0201	9.5	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R5DB01	High-Q	0201	9.5	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R5WB01	High-Q	0201	9.5	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R6BB01	High-Q	0201	9.6	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R6CB01	High-Q	0201	9.6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R6DB01	High-Q	0201	9.6	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R6WB01	High-Q	0201	9.6	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R7BB01	High-Q	0201	9.7	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R7CB01	High-Q	0201	9.7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R7DB01	High-Q	0201	9.7	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R7WB01	High-Q	0201	9.7	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R8BB01	High-Q	0201	9.8	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R8CB01	High-Q	0201	9.8	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R8DB01	High-Q	0201	9.8	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R8WB01	High-Q	0201	9.8	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R9BB01	High-Q	0201	9.9	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R9CB01	High-Q	0201	9.9	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R9DB01	High-Q	0201	9.9	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E9R9WB01	High-Q	0201	9.9	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E100GB01	High-Q	0201	10	+/-2[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E100JB01	High-Q	0201	10	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0336C1E100GB01	High-Q	0201	10	+/-2[%]	25	C0H	100[MHz]-8.5[GHz]
GJM0336C1E100JB01	High-Q	0201	10	+/-5[%]	25	C0H	100[MHz]-8.5[GHz]
GJM0335C1E110GB01	High-Q	0201	11	+/-2[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E110JB01	High-Q	0201	11	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E120GB01	High-Q	0201	12	+/-2[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E120JB01	High-Q	0201	12	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E130GB01	High-Q	0201	13	+/-2[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E130JB01	High-Q	0201	13	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E150GB01	High-Q	0201	15	+/-2[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E150JB01	High-Q	0201	15	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0336C1E150GB01	High-Q	0201	15	+/-2[%]	25	C0H	100[MHz]-8.5[GHz]
GJM0336C1E150JB01	High-Q	0201	15	+/-5[%]	25	C0H	100[MHz]-8.5[GHz]
GJM0335C1E160GB01	High-Q	0201	16	+/-2[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E160JB01	High-Q	0201	16	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E180GB01	High-Q	0201	18	+/-2[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E180JB01	High-Q	0201	18	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E200GB01	High-Q	0201	20	+/-2[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E200JB01	High-Q	0201	20	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0336C1E200JB01	High-Q	0201	20	+/-5[%]	25	C0H	100[MHz]-8.5[GHz]
GJM0335C0J220GB01	High-Q	0201	22	+/-2[%]	6.3	C0G	100[MHz]-8.5[GHz]
GJM0335C0J220JB01	High-Q	0201	22	+/-5[%]	6.3	C0G	100[MHz]-8.5[GHz]
GJM0335C1E220GB01	High-Q	0201	22	+/-2[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E220JB01	High-Q	0201	22	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C0J240GB01	High-Q	0201	24	+/-2[%]	6.3	C0G	100[MHz]-8.5[GHz]
GJM0335C0J240JB01	High-Q	0201	24	+/-5[%]	6.3	C0G	100[MHz]-8.5[GHz]
GJM0335C1E240GB01	High-Q	0201	24	+/-2[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E240JB01	High-Q	0201	24	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C0J270GB01	High-Q	0201	27	+/-2[%]	6.3	C0G	100[MHz]-8.5[GHz]
GJM0335C0J270JB01	High-Q	0201	27	+/-5[%]	6.3	C0G	100[MHz]-8.5[GHz]
GJM0335C1E270GB01	High-Q	0201	27	+/-2[%]	25	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM0335C1E270JB01	High-Q	0201	27	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C0J300GB01	High-Q	0201	30	+/-2[%]	6.3	C0G	100[MHz]-8.5[GHz]
GJM0335C0J300JB01	High-Q	0201	30	+/-5[%]	6.3	C0G	100[MHz]-8.5[GHz]
GJM0335C1E300GB01	High-Q	0201	30	+/-2[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E300JB01	High-Q	0201	30	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C0J330GB01	High-Q	0201	33	+/-2[%]	6.3	C0G	100[MHz]-8.5[GHz]
GJM0335C0J330JB01	High-Q	0201	33	+/-5[%]	6.3	C0G	100[MHz]-8.5[GHz]
GJM0335C1E330GB01	High-Q	0201	33	+/-2[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0335C1E330JB01	High-Q	0201	33	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GJM1555C1HR10BB01	High-Q	0402	0.1	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GJM1555C1HR10WB01	High-Q	0402	0.1	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GJM1555C1HR20BB01	High-Q	0402	0.2	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GJM1555C1HR20WB01	High-Q	0402	0.2	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GJM1555C1HR30BB01	High-Q	0402	0.3	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GJM1555C1HR30WB01	High-Q	0402	0.3	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GJM1555C1HR40BB01	High-Q	0402	0.4	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GJM1555C1HR40WB01	High-Q	0402	0.4	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GJM1555C1HR50BB01	High-Q	0402	0.5	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GJM1555C1HR50WB01	High-Q	0402	0.5	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GJM1555C1HR60BB01	High-Q	0402	0.6	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GJM1555C1HR60WB01	High-Q	0402	0.6	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GJM1555C1HR70BB01	High-Q	0402	0.7	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GJM1555C1HR70WB01	High-Q	0402	0.7	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GJM1555C1HR80BB01	High-Q	0402	0.8	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GJM1555C1HR80WB01	High-Q	0402	0.8	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GJM1555C1HR90BB01	High-Q	0402	0.9	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GJM1555C1HR90WB01	High-Q	0402	0.9	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GJM1555C1H1R0BB01	High-Q	0402	1	+/-0.1[pF]	50	C0G	100[MHz]-20[GHz]
GJM1555C1H1R0CB01	High-Q	0402	1	+/-0.25[pF]	50	C0G	100[MHz]-20[GHz]
GJM1555C1H1R0WB01	High-Q	0402	1	+/-0.05[pF]	50	C0G	100[MHz]-20[GHz]
GJM1555C1H1R1BB01	High-Q	0402	1.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R1CB01	High-Q	0402	1.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R1JB01	High-Q	0402	1.1	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R1WB01	High-Q	0402	1.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R2BB01	High-Q	0402	1.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R2CB01	High-Q	0402	1.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R2JB01	High-Q	0402	1.2	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R2WB01	High-Q	0402	1.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R3BB01	High-Q	0402	1.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R3CB01	High-Q	0402	1.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R3JB01	High-Q	0402	1.3	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R3WB01	High-Q	0402	1.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R4BB01	High-Q	0402	1.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R4CB01	High-Q	0402	1.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R4WB01	High-Q	0402	1.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R5BB01	High-Q	0402	1.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R5CB01	High-Q	0402	1.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R5JB01	High-Q	0402	1.5	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R5WB01	High-Q	0402	1.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R6BB01	High-Q	0402	1.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R6CB01	High-Q	0402	1.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R6JB01	High-Q	0402	1.6	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R6WB01	High-Q	0402	1.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R7BB01	High-Q	0402	1.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R7CB01	High-Q	0402	1.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R7WB01	High-Q	0402	1.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM1555C1H1R8BB01	High-Q	0402	1.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R8CB01	High-Q	0402	1.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R8JB01	High-Q	0402	1.8	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R8WB01	High-Q	0402	1.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R9BB01	High-Q	0402	1.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R9CB01	High-Q	0402	1.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H1R9WB01	High-Q	0402	1.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R0BB01	High-Q	0402	2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R0CB01	High-Q	0402	2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R0GB01	High-Q	0402	2	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R0WB01	High-Q	0402	2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R1BB01	High-Q	0402	2.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R1CB01	High-Q	0402	2.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R1WB01	High-Q	0402	2.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R2BB01	High-Q	0402	2.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R2CB01	High-Q	0402	2.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R2GB01	High-Q	0402	2.2	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R2WB01	High-Q	0402	2.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R3BB01	High-Q	0402	2.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R3CB01	High-Q	0402	2.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R3WB01	High-Q	0402	2.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R4BB01	High-Q	0402	2.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R4CB01	High-Q	0402	2.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R4GB01	High-Q	0402	2.4	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R4WB01	High-Q	0402	2.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R5BB01	High-Q	0402	2.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R5CB01	High-Q	0402	2.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R5WB01	High-Q	0402	2.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R6BB01	High-Q	0402	2.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R6CB01	High-Q	0402	2.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R6WB01	High-Q	0402	2.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R7BB01	High-Q	0402	2.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R7CB01	High-Q	0402	2.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R7GB01	High-Q	0402	2.7	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R7WB01	High-Q	0402	2.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R8BB01	High-Q	0402	2.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R8CB01	High-Q	0402	2.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R8WB01	High-Q	0402	2.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R9BB01	High-Q	0402	2.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R9CB01	High-Q	0402	2.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H2R9WB01	High-Q	0402	2.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R0BB01	High-Q	0402	3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R0CB01	High-Q	0402	3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R0GB01	High-Q	0402	3	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R0WB01	High-Q	0402	3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R1BB01	High-Q	0402	3.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R1CB01	High-Q	0402	3.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R1WB01	High-Q	0402	3.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R2BB01	High-Q	0402	3.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R2CB01	High-Q	0402	3.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R2WB01	High-Q	0402	3.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R3BB01	High-Q	0402	3.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R3CB01	High-Q	0402	3.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R3GB01	High-Q	0402	3.3	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R3WB01	High-Q	0402	3.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R4BB01	High-Q	0402	3.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM1555C1H3R4CB01	High-Q	0402	3.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R4WB01	High-Q	0402	3.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R5BB01	High-Q	0402	3.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R5CB01	High-Q	0402	3.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R5WB01	High-Q	0402	3.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R6BB01	High-Q	0402	3.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R6CB01	High-Q	0402	3.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R6GB01	High-Q	0402	3.6	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R6WB01	High-Q	0402	3.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R7BB01	High-Q	0402	3.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R7CB01	High-Q	0402	3.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R7WB01	High-Q	0402	3.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R8BB01	High-Q	0402	3.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R8CB01	High-Q	0402	3.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R8WB01	High-Q	0402	3.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R9BB01	High-Q	0402	3.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R9CB01	High-Q	0402	3.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R9GB01	High-Q	0402	3.9	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H3R9WB01	High-Q	0402	3.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R0BB01	High-Q	0402	4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R0CB01	High-Q	0402	4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R0WB01	High-Q	0402	4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R1BB01	High-Q	0402	4.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R1CB01	High-Q	0402	4.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R1WB01	High-Q	0402	4.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R2BB01	High-Q	0402	4.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R2CB01	High-Q	0402	4.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R2WB01	High-Q	0402	4.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R3BB01	High-Q	0402	4.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R3CB01	High-Q	0402	4.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R3GB01	High-Q	0402	4.3	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R3WB01	High-Q	0402	4.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R4BB01	High-Q	0402	4.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R4CB01	High-Q	0402	4.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R4WB01	High-Q	0402	4.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R5BB01	High-Q	0402	4.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R5CB01	High-Q	0402	4.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R5WB01	High-Q	0402	4.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R6BB01	High-Q	0402	4.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R6CB01	High-Q	0402	4.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R6WB01	High-Q	0402	4.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R7BB01	High-Q	0402	4.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R7CB01	High-Q	0402	4.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R7GB01	High-Q	0402	4.7	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R7WB01	High-Q	0402	4.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R8BB01	High-Q	0402	4.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R8CB01	High-Q	0402	4.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R8WB01	High-Q	0402	4.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R9BB01	High-Q	0402	4.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R9CB01	High-Q	0402	4.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H4R9WB01	High-Q	0402	4.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R0BB01	High-Q	0402	5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R0CB01	High-Q	0402	5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R0WB01	High-Q	0402	5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R1BB01	High-Q	0402	5.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R1CB01	High-Q	0402	5.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]



Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM1555C1H5R1DB01	High-Q	0402	5.1	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R1FB01	High-Q	0402	5.1	+/-1[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R1WB01	High-Q	0402	5.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R2BB01	High-Q	0402	5.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R2CB01	High-Q	0402	5.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R2DB01	High-Q	0402	5.2	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R2WB01	High-Q	0402	5.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R3BB01	High-Q	0402	5.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R3CB01	High-Q	0402	5.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R3DB01	High-Q	0402	5.3	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R3WB01	High-Q	0402	5.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R4BB01	High-Q	0402	5.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R4CB01	High-Q	0402	5.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R4DB01	High-Q	0402	5.4	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R4WB01	High-Q	0402	5.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R5BB01	High-Q	0402	5.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R5CB01	High-Q	0402	5.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R5DB01	High-Q	0402	5.5	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R5WB01	High-Q	0402	5.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R6BB01	High-Q	0402	5.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R6CB01	High-Q	0402	5.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R6DB01	High-Q	0402	5.6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R6FB01	High-Q	0402	5.6	+/-1[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R6WB01	High-Q	0402	5.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R7BB01	High-Q	0402	5.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R7CB01	High-Q	0402	5.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R7DB01	High-Q	0402	5.7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R7WB01	High-Q	0402	5.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R8BB01	High-Q	0402	5.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R8CB01	High-Q	0402	5.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R8DB01	High-Q	0402	5.8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R8WB01	High-Q	0402	5.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R9BB01	High-Q	0402	5.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R9CB01	High-Q	0402	5.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R9DB01	High-Q	0402	5.9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H5R9WB01	High-Q	0402	5.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R0BB01	High-Q	0402	6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R0CB01	High-Q	0402	6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R0DB01	High-Q	0402	6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R0WB01	High-Q	0402	6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R1BB01	High-Q	0402	6.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R1CB01	High-Q	0402	6.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R1DB01	High-Q	0402	6.1	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R1WB01	High-Q	0402	6.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R2BB01	High-Q	0402	6.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R2CB01	High-Q	0402	6.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R2DB01	High-Q	0402	6.2	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R2FB01	High-Q	0402	6.2	+/-1[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R2WB01	High-Q	0402	6.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R3BB01	High-Q	0402	6.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R3CB01	High-Q	0402	6.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R3DB01	High-Q	0402	6.3	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R3WB01	High-Q	0402	6.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R4BB01	High-Q	0402	6.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R4CB01	High-Q	0402	6.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R4DB01	High-Q	0402	6.4	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM1555C1H6R4WB01	High-Q	0402	6.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R5BB01	High-Q	0402	6.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R5CB01	High-Q	0402	6.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R5DB01	High-Q	0402	6.5	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R5WB01	High-Q	0402	6.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R6BB01	High-Q	0402	6.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R6CB01	High-Q	0402	6.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R6DB01	High-Q	0402	6.6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R6WB01	High-Q	0402	6.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R7BB01	High-Q	0402	6.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R7CB01	High-Q	0402	6.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R7DB01	High-Q	0402	6.7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R7WB01	High-Q	0402	6.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R8BB01	High-Q	0402	6.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R8CB01	High-Q	0402	6.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R8DB01	High-Q	0402	6.8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R8FB01	High-Q	0402	6.8	+/-1[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R8WB01	High-Q	0402	6.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R9BB01	High-Q	0402	6.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R9CB01	High-Q	0402	6.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R9DB01	High-Q	0402	6.9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H6R9WB01	High-Q	0402	6.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R0BB01	High-Q	0402	7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R0CB01	High-Q	0402	7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R0DB01	High-Q	0402	7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R0WB01	High-Q	0402	7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R1BB01	High-Q	0402	7.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R1CB01	High-Q	0402	7.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R1DB01	High-Q	0402	7.1	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R1WB01	High-Q	0402	7.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R2BB01	High-Q	0402	7.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R2CB01	High-Q	0402	7.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R2DB01	High-Q	0402	7.2	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R2WB01	High-Q	0402	7.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R3BB01	High-Q	0402	7.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R3CB01	High-Q	0402	7.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R3DB01	High-Q	0402	7.3	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R3WB01	High-Q	0402	7.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R4BB01	High-Q	0402	7.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R4CB01	High-Q	0402	7.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R4DB01	High-Q	0402	7.4	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R4WB01	High-Q	0402	7.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R5BB01	High-Q	0402	7.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R5CB01	High-Q	0402	7.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R5DB01	High-Q	0402	7.5	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R5FB01	High-Q	0402	7.5	+/-1[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R5WB01	High-Q	0402	7.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R6BB01	High-Q	0402	7.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R6CB01	High-Q	0402	7.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R6DB01	High-Q	0402	7.6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R6WB01	High-Q	0402	7.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R7BB01	High-Q	0402	7.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R7CB01	High-Q	0402	7.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R7DB01	High-Q	0402	7.7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R7WB01	High-Q	0402	7.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R8BB01	High-Q	0402	7.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM1555C1H7R8CB01	High-Q	0402	7.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R8DB01	High-Q	0402	7.8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R8WB01	High-Q	0402	7.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R9BB01	High-Q	0402	7.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R9CB01	High-Q	0402	7.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R9DB01	High-Q	0402	7.9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H7R9WB01	High-Q	0402	7.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R0BB01	High-Q	0402	8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R0CB01	High-Q	0402	8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R0DB01	High-Q	0402	8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R0WB01	High-Q	0402	8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R1BB01	High-Q	0402	8.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R1CB01	High-Q	0402	8.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R1DB01	High-Q	0402	8.1	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R1WB01	High-Q	0402	8.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R2BB01	High-Q	0402	8.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R2CB01	High-Q	0402	8.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R2DB01	High-Q	0402	8.2	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R2FB01	High-Q	0402	8.2	+/-1[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R2WB01	High-Q	0402	8.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R3BB01	High-Q	0402	8.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R3CB01	High-Q	0402	8.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R3DB01	High-Q	0402	8.3	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R3WB01	High-Q	0402	8.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R4BB01	High-Q	0402	8.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R4CB01	High-Q	0402	8.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R4DB01	High-Q	0402	8.4	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R4WB01	High-Q	0402	8.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R5BB01	High-Q	0402	8.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R5CB01	High-Q	0402	8.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R5DB01	High-Q	0402	8.5	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R5WB01	High-Q	0402	8.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R6BB01	High-Q	0402	8.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R6CB01	High-Q	0402	8.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R6DB01	High-Q	0402	8.6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R6WB01	High-Q	0402	8.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R7BB01	High-Q	0402	8.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R7CB01	High-Q	0402	8.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R7DB01	High-Q	0402	8.7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R7WB01	High-Q	0402	8.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R8BB01	High-Q	0402	8.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R8CB01	High-Q	0402	8.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R8DB01	High-Q	0402	8.8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R8WB01	High-Q	0402	8.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R9BB01	High-Q	0402	8.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R9CB01	High-Q	0402	8.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R9DB01	High-Q	0402	8.9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H8R9WB01	High-Q	0402	8.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R0BB01	High-Q	0402	9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R0CB01	High-Q	0402	9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R0DB01	High-Q	0402	9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R0WB01	High-Q	0402	9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R1BB01	High-Q	0402	9.1	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R1CB01	High-Q	0402	9.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R1DB01	High-Q	0402	9.1	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R1FB01	High-Q	0402	9.1	+/-1[%]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM1555C1H9R1WB01	High-Q	0402	9.1	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R2BB01	High-Q	0402	9.2	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R2CB01	High-Q	0402	9.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R2DB01	High-Q	0402	9.2	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R2WB01	High-Q	0402	9.2	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R3BB01	High-Q	0402	9.3	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R3CB01	High-Q	0402	9.3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R3DB01	High-Q	0402	9.3	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R3WB01	High-Q	0402	9.3	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R4BB01	High-Q	0402	9.4	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R4CB01	High-Q	0402	9.4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R4DB01	High-Q	0402	9.4	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R4WB01	High-Q	0402	9.4	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R5BB01	High-Q	0402	9.5	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R5CB01	High-Q	0402	9.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R5DB01	High-Q	0402	9.5	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R5WB01	High-Q	0402	9.5	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R6BB01	High-Q	0402	9.6	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R6CB01	High-Q	0402	9.6	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R6DB01	High-Q	0402	9.6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R6WB01	High-Q	0402	9.6	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R7BB01	High-Q	0402	9.7	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R7CB01	High-Q	0402	9.7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R7DB01	High-Q	0402	9.7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R7WB01	High-Q	0402	9.7	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R8BB01	High-Q	0402	9.8	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R8CB01	High-Q	0402	9.8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R8DB01	High-Q	0402	9.8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R8WB01	High-Q	0402	9.8	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R9BB01	High-Q	0402	9.9	+/-0.1[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R9CB01	High-Q	0402	9.9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R9DB01	High-Q	0402	9.9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H9R9WB01	High-Q	0402	9.9	+/-0.05[pF]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H100FB01	High-Q	0402	10	+/-1[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H100GB01	High-Q	0402	10	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H100JB01	High-Q	0402	10	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H110GB01	High-Q	0402	11	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H110JB01	High-Q	0402	11	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H120FB01	High-Q	0402	12	+/-1[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H120GB01	High-Q	0402	12	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H120JB01	High-Q	0402	12	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H130GB01	High-Q	0402	13	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H130JB01	High-Q	0402	13	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H150FB01	High-Q	0402	15	+/-1[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H150GB01	High-Q	0402	15	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H150JB01	High-Q	0402	15	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H160GB01	High-Q	0402	16	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H160JB01	High-Q	0402	16	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H180FB01	High-Q	0402	18	+/-1[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H180GB01	High-Q	0402	18	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H180JB01	High-Q	0402	18	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H200GB01	High-Q	0402	20	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H200JB01	High-Q	0402	20	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H220JB01	High-Q	0402	22	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H220FB01	High-Q	0402	22	+/-1[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H220GB01	High-Q	0402	22	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM1555C1H240JB01	High-Q	0402	24	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H240FB01	High-Q	0402	24	+/-1[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H240GB01	High-Q	0402	24	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H270JB01	High-Q	0402	27	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H270FB01	High-Q	0402	27	+/-1[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H270GB01	High-Q	0402	27	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H300JB01	High-Q	0402	30	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H300FB01	High-Q	0402	30	+/-1[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H300GB01	High-Q	0402	30	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H330JB01	High-Q	0402	33	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H330FB01	High-Q	0402	33	+/-1[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H330GB01	High-Q	0402	33	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H360JB01	High-Q	0402	36	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H360FB01	High-Q	0402	36	+/-1[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H360GB01	High-Q	0402	36	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H390JB01	High-Q	0402	39	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H390FB01	High-Q	0402	39	+/-1[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H390GB01	High-Q	0402	39	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H430JB01	High-Q	0402	43	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H430FB01	High-Q	0402	43	+/-1[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H430GB01	High-Q	0402	43	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H470JB01	High-Q	0402	47	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H470FB01	High-Q	0402	47	+/-1[%]	50	C0G	100[MHz]-8.5[GHz]
GJM1555C1H470GB01	High-Q	0402	47	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GJM0225C1CR20WB01	High-Q	01005	0.2	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1CR20BB01	High-Q	01005	0.2	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1ER20BB01	High-Q	01005	0.2	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1ER20WB01	High-Q	01005	0.2	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1CR30WB01	High-Q	01005	0.3	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1CR30BB01	High-Q	01005	0.3	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1ER30BB01	High-Q	01005	0.3	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1ER30WB01	High-Q	01005	0.3	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1CR40WB01	High-Q	01005	0.4	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1CR40BB01	High-Q	01005	0.4	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1ER40BB01	High-Q	01005	0.4	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1ER40WB01	High-Q	01005	0.4	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1CR50WB01	High-Q	01005	0.5	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1CR50BB01	High-Q	01005	0.5	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1ER50BB01	High-Q	01005	0.5	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1ER50WB01	High-Q	01005	0.5	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1CR60WB01	High-Q	01005	0.6	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1CR60BB01	High-Q	01005	0.6	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1ER60BB01	High-Q	01005	0.6	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1ER60WB01	High-Q	01005	0.6	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1CR70WB01	High-Q	01005	0.7	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1CR70BB01	High-Q	01005	0.7	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1ER70BB01	High-Q	01005	0.7	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1ER70WB01	High-Q	01005	0.7	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1CR80WB01	High-Q	01005	0.8	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1CR80BB01	High-Q	01005	0.8	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1ER80BB01	High-Q	01005	0.8	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1ER80WB01	High-Q	01005	0.8	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1CR90WB01	High-Q	01005	0.9	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1CR90BB01	High-Q	01005	0.9	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1ER90BB01	High-Q	01005	0.9	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1ER90WB01	High-Q	01005	0.9	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM0225C1C1R0BB01	High-Q	01005	1	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1C1R0WB01	High-Q	01005	1	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1C1R0CB01	High-Q	01005	1	+/-0.25[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1E1R0BB01	High-Q	01005	1	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1E1R0CB01	High-Q	01005	1	+/-0.25[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1E1R0WB01	High-Q	01005	1	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1C1R1BB01	High-Q	01005	1.1	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1C1R1WB01	High-Q	01005	1.1	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1C1R1CB01	High-Q	01005	1.1	+/-0.25[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1E1R1BB01	High-Q	01005	1.1	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1E1R1CB01	High-Q	01005	1.1	+/-0.25[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1E1R1WB01	High-Q	01005	1.1	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1C1R2BB01	High-Q	01005	1.2	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1C1R2WB01	High-Q	01005	1.2	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1C1R2CB01	High-Q	01005	1.2	+/-0.25[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1E1R2BB01	High-Q	01005	1.2	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1E1R2CB01	High-Q	01005	1.2	+/-0.25[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1E1R2WB01	High-Q	01005	1.2	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1C1R3BB01	High-Q	01005	1.3	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1C1R3WB01	High-Q	01005	1.3	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1C1R3CB01	High-Q	01005	1.3	+/-0.25[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1E1R3BB01	High-Q	01005	1.3	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1E1R3CB01	High-Q	01005	1.3	+/-0.25[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1E1R3WB01	High-Q	01005	1.3	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1C1R4BB01	High-Q	01005	1.4	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1C1R4CB01	High-Q	01005	1.4	+/-0.25[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1C1R4WB01	High-Q	01005	1.4	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1E1R4BB01	High-Q	01005	1.4	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1E1R4CB01	High-Q	01005	1.4	+/-0.25[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1E1R4WB01	High-Q	01005	1.4	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1C1R5BB01	High-Q	01005	1.5	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1C1R5WB01	High-Q	01005	1.5	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1C1R5CB01	High-Q	01005	1.5	+/-0.25[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1E1R5BB01	High-Q	01005	1.5	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1E1R5CB01	High-Q	01005	1.5	+/-0.25[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1E1R5WB01	High-Q	01005	1.5	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1C1R6BB01	High-Q	01005	1.6	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1C1R6WB01	High-Q	01005	1.6	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1C1R6CB01	High-Q	01005	1.6	+/-0.25[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1E1R6BB01	High-Q	01005	1.6	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1E1R6CB01	High-Q	01005	1.6	+/-0.25[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1E1R6WB01	High-Q	01005	1.6	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1C1R7BB01	High-Q	01005	1.7	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1C1R7CB01	High-Q	01005	1.7	+/-0.25[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1C1R7WB01	High-Q	01005	1.7	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1E1R7BB01	High-Q	01005	1.7	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1E1R7CB01	High-Q	01005	1.7	+/-0.25[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1E1R7WB01	High-Q	01005	1.7	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1C1R8BB01	High-Q	01005	1.8	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1C1R8WB01	High-Q	01005	1.8	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1C1R8CB01	High-Q	01005	1.8	+/-0.25[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1E1R8BB01	High-Q	01005	1.8	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1E1R8CB01	High-Q	01005	1.8	+/-0.25[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1E1R8WB01	High-Q	01005	1.8	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1C1R9BB01	High-Q	01005	1.9	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1C1R9CB01	High-Q	01005	1.9	+/-0.25[pF]	16	C0G	100[MHz]-20[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM0225C1C1R9WB01	High-Q	01005	1.9	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1E1R9BB01	High-Q	01005	1.9	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1E1R9CB01	High-Q	01005	1.9	+/-0.25[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1E1R9WB01	High-Q	01005	1.9	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1C2R0BB01	High-Q	01005	2	+/-0.1[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1C2R0WB01	High-Q	01005	2	+/-0.05[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1C2R0CB01	High-Q	01005	2	+/-0.25[pF]	16	C0G	100[MHz]-20[GHz]
GJM0225C1E2R0BB01	High-Q	01005	2	+/-0.1[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1E2R0CB01	High-Q	01005	2	+/-0.25[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1E2R0WB01	High-Q	01005	2	+/-0.05[pF]	25	C0G	100[MHz]-20[GHz]
GJM0225C1C2R1BB01	High-Q	01005	2.1	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R1CB01	High-Q	01005	2.1	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R1WB01	High-Q	01005	2.1	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R1BB01	High-Q	01005	2.1	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R1CB01	High-Q	01005	2.1	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R1WB01	High-Q	01005	2.1	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R2BB01	High-Q	01005	2.2	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R2WB01	High-Q	01005	2.2	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R2CB01	High-Q	01005	2.2	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R2BB01	High-Q	01005	2.2	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R2CB01	High-Q	01005	2.2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R2WB01	High-Q	01005	2.2	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R3BB01	High-Q	01005	2.3	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R3CB01	High-Q	01005	2.3	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R3WB01	High-Q	01005	2.3	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R3BB01	High-Q	01005	2.3	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R3CB01	High-Q	01005	2.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R3WB01	High-Q	01005	2.3	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R4BB01	High-Q	01005	2.4	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R4WB01	High-Q	01005	2.4	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R4CB01	High-Q	01005	2.4	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R4BB01	High-Q	01005	2.4	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R4CB01	High-Q	01005	2.4	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R4WB01	High-Q	01005	2.4	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R5BB01	High-Q	01005	2.5	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R5CB01	High-Q	01005	2.5	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R5WB01	High-Q	01005	2.5	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R5BB01	High-Q	01005	2.5	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R5CB01	High-Q	01005	2.5	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R5WB01	High-Q	01005	2.5	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R6BB01	High-Q	01005	2.6	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R6CB01	High-Q	01005	2.6	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R6WB01	High-Q	01005	2.6	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R6BB01	High-Q	01005	2.6	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R6CB01	High-Q	01005	2.6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R6WB01	High-Q	01005	2.6	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R7BB01	High-Q	01005	2.7	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R7WB01	High-Q	01005	2.7	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R7CB01	High-Q	01005	2.7	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R7BB01	High-Q	01005	2.7	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R7CB01	High-Q	01005	2.7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R7WB01	High-Q	01005	2.7	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R8BB01	High-Q	01005	2.8	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R8CB01	High-Q	01005	2.8	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R8WB01	High-Q	01005	2.8	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R8BB01	High-Q	01005	2.8	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM0225C1E2R8CB01	High-Q	01005	2.8	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R8WB01	High-Q	01005	2.8	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R9BB01	High-Q	01005	2.9	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R9CB01	High-Q	01005	2.9	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C2R9WB01	High-Q	01005	2.9	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R9BB01	High-Q	01005	2.9	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R9CB01	High-Q	01005	2.9	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E2R9WB01	High-Q	01005	2.9	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R0BB01	High-Q	01005	3	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R0WB01	High-Q	01005	3	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R0CB01	High-Q	01005	3	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R0BB01	High-Q	01005	3	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R0CB01	High-Q	01005	3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R0WB01	High-Q	01005	3	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R1BB01	High-Q	01005	3.1	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R1CB01	High-Q	01005	3.1	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R1WB01	High-Q	01005	3.1	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R1BB01	High-Q	01005	3.1	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R1CB01	High-Q	01005	3.1	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R1WB01	High-Q	01005	3.1	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R2BB01	High-Q	01005	3.2	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R2CB01	High-Q	01005	3.2	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R2WB01	High-Q	01005	3.2	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R2BB01	High-Q	01005	3.2	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R2CB01	High-Q	01005	3.2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R2WB01	High-Q	01005	3.2	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R3BB01	High-Q	01005	3.3	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R3WB01	High-Q	01005	3.3	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R3CB01	High-Q	01005	3.3	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R3BB01	High-Q	01005	3.3	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R3CB01	High-Q	01005	3.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R3WB01	High-Q	01005	3.3	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R4BB01	High-Q	01005	3.4	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R4CB01	High-Q	01005	3.4	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R4WB01	High-Q	01005	3.4	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R4BB01	High-Q	01005	3.4	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R4CB01	High-Q	01005	3.4	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R4WB01	High-Q	01005	3.4	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R5BB01	High-Q	01005	3.5	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R5CB01	High-Q	01005	3.5	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R5WB01	High-Q	01005	3.5	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R5BB01	High-Q	01005	3.5	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R5CB01	High-Q	01005	3.5	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R5WB01	High-Q	01005	3.5	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R6BB01	High-Q	01005	3.6	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R6WB01	High-Q	01005	3.6	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R6CB01	High-Q	01005	3.6	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R6BB01	High-Q	01005	3.6	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R6CB01	High-Q	01005	3.6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R6WB01	High-Q	01005	3.6	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R7BB01	High-Q	01005	3.7	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R7CB01	High-Q	01005	3.7	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R7WB01	High-Q	01005	3.7	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R7BB01	High-Q	01005	3.7	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R7CB01	High-Q	01005	3.7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R7WB01	High-Q	01005	3.7	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]



Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM0225C1C3R8BB01	High-Q	01005	3.8	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R8CB01	High-Q	01005	3.8	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R8WB01	High-Q	01005	3.8	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R8BB01	High-Q	01005	3.8	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R8CB01	High-Q	01005	3.8	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R8WB01	High-Q	01005	3.8	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R9BB01	High-Q	01005	3.9	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R9WB01	High-Q	01005	3.9	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C3R9CB01	High-Q	01005	3.9	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R9BB01	High-Q	01005	3.9	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R9CB01	High-Q	01005	3.9	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E3R9WB01	High-Q	01005	3.9	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R0BB01	High-Q	01005	4	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R0WB01	High-Q	01005	4	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R0CB01	High-Q	01005	4	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R0BB01	High-Q	01005	4	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R0CB01	High-Q	01005	4	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R0WB01	High-Q	01005	4	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R1BB01	High-Q	01005	4.1	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R1CB01	High-Q	01005	4.1	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R1WB01	High-Q	01005	4.1	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R1BB01	High-Q	01005	4.1	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R1CB01	High-Q	01005	4.1	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R1WB01	High-Q	01005	4.1	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R2BB01	High-Q	01005	4.2	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R2CB01	High-Q	01005	4.2	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R2WB01	High-Q	01005	4.2	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R2BB01	High-Q	01005	4.2	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R2CB01	High-Q	01005	4.2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R2WB01	High-Q	01005	4.2	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R3BB01	High-Q	01005	4.3	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R3WB01	High-Q	01005	4.3	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R3CB01	High-Q	01005	4.3	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R3BB01	High-Q	01005	4.3	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R3CB01	High-Q	01005	4.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R3WB01	High-Q	01005	4.3	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R4BB01	High-Q	01005	4.4	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R4CB01	High-Q	01005	4.4	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R4WB01	High-Q	01005	4.4	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R4BB01	High-Q	01005	4.4	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R4CB01	High-Q	01005	4.4	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R4WB01	High-Q	01005	4.4	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R5BB01	High-Q	01005	4.5	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R5CB01	High-Q	01005	4.5	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R5WB01	High-Q	01005	4.5	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R5BB01	High-Q	01005	4.5	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R5CB01	High-Q	01005	4.5	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R5WB01	High-Q	01005	4.5	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R6BB01	High-Q	01005	4.6	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R6CB01	High-Q	01005	4.6	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R6WB01	High-Q	01005	4.6	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R6BB01	High-Q	01005	4.6	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R6CB01	High-Q	01005	4.6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R6WB01	High-Q	01005	4.6	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R7BB01	High-Q	01005	4.7	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R7WB01	High-Q	01005	4.7	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM0225C1C4R7CB01	High-Q	01005	4.7	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R7BB01	High-Q	01005	4.7	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R7CB01	High-Q	01005	4.7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R7WB01	High-Q	01005	4.7	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R8BB01	High-Q	01005	4.8	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R8CB01	High-Q	01005	4.8	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R8WB01	High-Q	01005	4.8	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R8BB01	High-Q	01005	4.8	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R8CB01	High-Q	01005	4.8	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R8WB01	High-Q	01005	4.8	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R9BB01	High-Q	01005	4.9	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R9CB01	High-Q	01005	4.9	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C4R9WB01	High-Q	01005	4.9	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R9BB01	High-Q	01005	4.9	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R9CB01	High-Q	01005	4.9	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E4R9WB01	High-Q	01005	4.9	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R0BB01	High-Q	01005	5	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R0WB01	High-Q	01005	5	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R0CB01	High-Q	01005	5	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R0BB01	High-Q	01005	5	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R0CB01	High-Q	01005	5	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R0WB01	High-Q	01005	5	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R1BB01	High-Q	01005	5.1	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R1WB01	High-Q	01005	5.1	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R1CB01	High-Q	01005	5.1	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R1DB01	High-Q	01005	5.1	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R1BB01	High-Q	01005	5.1	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R1CB01	High-Q	01005	5.1	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R1DB01	High-Q	01005	5.1	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R1WB01	High-Q	01005	5.1	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R2BB01	High-Q	01005	5.2	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R2CB01	High-Q	01005	5.2	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R2DB01	High-Q	01005	5.2	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R2WB01	High-Q	01005	5.2	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R2BB01	High-Q	01005	5.2	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R2CB01	High-Q	01005	5.2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R2DB01	High-Q	01005	5.2	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R2WB01	High-Q	01005	5.2	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R3BB01	High-Q	01005	5.3	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R3CB01	High-Q	01005	5.3	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R3DB01	High-Q	01005	5.3	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R3WB01	High-Q	01005	5.3	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R3BB01	High-Q	01005	5.3	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R3CB01	High-Q	01005	5.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R3DB01	High-Q	01005	5.3	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R3WB01	High-Q	01005	5.3	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R4BB01	High-Q	01005	5.4	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R4CB01	High-Q	01005	5.4	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R4DB01	High-Q	01005	5.4	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R4WB01	High-Q	01005	5.4	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R4BB01	High-Q	01005	5.4	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R4CB01	High-Q	01005	5.4	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R4DB01	High-Q	01005	5.4	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R4WB01	High-Q	01005	5.4	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R5BB01	High-Q	01005	5.5	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R5CB01	High-Q	01005	5.5	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM0225C1C5R5DB01	High-Q	01005	5.5	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R5WB01	High-Q	01005	5.5	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R5BB01	High-Q	01005	5.5	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R5CB01	High-Q	01005	5.5	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R5DB01	High-Q	01005	5.5	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R5WB01	High-Q	01005	5.5	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R6BB01	High-Q	01005	5.6	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R6WB01	High-Q	01005	5.6	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R6CB01	High-Q	01005	5.6	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R6DB01	High-Q	01005	5.6	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R6BB01	High-Q	01005	5.6	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R6CB01	High-Q	01005	5.6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R6DB01	High-Q	01005	5.6	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R6WB01	High-Q	01005	5.6	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R7BB01	High-Q	01005	5.7	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R7CB01	High-Q	01005	5.7	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R7DB01	High-Q	01005	5.7	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R7WB01	High-Q	01005	5.7	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R7BB01	High-Q	01005	5.7	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R7CB01	High-Q	01005	5.7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R7DB01	High-Q	01005	5.7	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R7WB01	High-Q	01005	5.7	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R8BB01	High-Q	01005	5.8	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R8CB01	High-Q	01005	5.8	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R8DB01	High-Q	01005	5.8	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R8WB01	High-Q	01005	5.8	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R8BB01	High-Q	01005	5.8	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R8CB01	High-Q	01005	5.8	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R8DB01	High-Q	01005	5.8	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R8WB01	High-Q	01005	5.8	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R9BB01	High-Q	01005	5.9	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R9CB01	High-Q	01005	5.9	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R9DB01	High-Q	01005	5.9	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C5R9WB01	High-Q	01005	5.9	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R9BB01	High-Q	01005	5.9	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R9CB01	High-Q	01005	5.9	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R9DB01	High-Q	01005	5.9	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E5R9WB01	High-Q	01005	5.9	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R0BB01	High-Q	01005	6	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R0WB01	High-Q	01005	6	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R0CB01	High-Q	01005	6	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R0DB01	High-Q	01005	6	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R0BB01	High-Q	01005	6	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R0CB01	High-Q	01005	6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R0DB01	High-Q	01005	6	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R0WB01	High-Q	01005	6	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R1BB01	High-Q	01005	6.1	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R1CB01	High-Q	01005	6.1	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R1DB01	High-Q	01005	6.1	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R1WB01	High-Q	01005	6.1	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R1BB01	High-Q	01005	6.1	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R1CB01	High-Q	01005	6.1	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R1DB01	High-Q	01005	6.1	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R1WB01	High-Q	01005	6.1	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R2BB01	High-Q	01005	6.2	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R2WB01	High-Q	01005	6.2	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM0225C1C6R2CB01	High-Q	01005	6.2	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R2DB01	High-Q	01005	6.2	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R2BB01	High-Q	01005	6.2	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R2CB01	High-Q	01005	6.2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R2DB01	High-Q	01005	6.2	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R2WB01	High-Q	01005	6.2	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R3BB01	High-Q	01005	6.3	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R3CB01	High-Q	01005	6.3	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R3DB01	High-Q	01005	6.3	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R3WB01	High-Q	01005	6.3	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R3BB01	High-Q	01005	6.3	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R3CB01	High-Q	01005	6.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R3DB01	High-Q	01005	6.3	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R3WB01	High-Q	01005	6.3	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R4BB01	High-Q	01005	6.4	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R4CB01	High-Q	01005	6.4	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R4DB01	High-Q	01005	6.4	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R4WB01	High-Q	01005	6.4	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R4BB01	High-Q	01005	6.4	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R4CB01	High-Q	01005	6.4	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R4DB01	High-Q	01005	6.4	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R4WB01	High-Q	01005	6.4	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R5BB01	High-Q	01005	6.5	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R5CB01	High-Q	01005	6.5	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R5DB01	High-Q	01005	6.5	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R5WB01	High-Q	01005	6.5	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R5BB01	High-Q	01005	6.5	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R5CB01	High-Q	01005	6.5	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R5DB01	High-Q	01005	6.5	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R5WB01	High-Q	01005	6.5	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R6BB01	High-Q	01005	6.6	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R6CB01	High-Q	01005	6.6	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R6DB01	High-Q	01005	6.6	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R6WB01	High-Q	01005	6.6	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R6BB01	High-Q	01005	6.6	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R6CB01	High-Q	01005	6.6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R6DB01	High-Q	01005	6.6	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R6WB01	High-Q	01005	6.6	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R7BB01	High-Q	01005	6.7	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R7CB01	High-Q	01005	6.7	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R7DB01	High-Q	01005	6.7	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R7WB01	High-Q	01005	6.7	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R7BB01	High-Q	01005	6.7	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R7CB01	High-Q	01005	6.7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R7DB01	High-Q	01005	6.7	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R7WB01	High-Q	01005	6.7	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R8BB01	High-Q	01005	6.8	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R8WB01	High-Q	01005	6.8	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R8CB01	High-Q	01005	6.8	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R8DB01	High-Q	01005	6.8	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R8BB01	High-Q	01005	6.8	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R8CB01	High-Q	01005	6.8	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R8DB01	High-Q	01005	6.8	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R8WB01	High-Q	01005	6.8	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R9BB01	High-Q	01005	6.9	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R9CB01	High-Q	01005	6.9	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM0225C1C6R9DB01	High-Q	01005	6.9	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C6R9WB01	High-Q	01005	6.9	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R9BB01	High-Q	01005	6.9	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R9CB01	High-Q	01005	6.9	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R9DB01	High-Q	01005	6.9	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E6R9WB01	High-Q	01005	6.9	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R0BB01	High-Q	01005	7	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R0WB01	High-Q	01005	7	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R0CB01	High-Q	01005	7	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R0DB01	High-Q	01005	7	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R0BB01	High-Q	01005	7	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R0CB01	High-Q	01005	7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R0DB01	High-Q	01005	7	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R0WB01	High-Q	01005	7	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R1BB01	High-Q	01005	7.1	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R1CB01	High-Q	01005	7.1	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R1DB01	High-Q	01005	7.1	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R1WB01	High-Q	01005	7.1	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R1BB01	High-Q	01005	7.1	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R1CB01	High-Q	01005	7.1	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R1DB01	High-Q	01005	7.1	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R1WB01	High-Q	01005	7.1	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R2BB01	High-Q	01005	7.2	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R2CB01	High-Q	01005	7.2	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R2DB01	High-Q	01005	7.2	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R2WB01	High-Q	01005	7.2	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R2BB01	High-Q	01005	7.2	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R2CB01	High-Q	01005	7.2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R2DB01	High-Q	01005	7.2	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R2WB01	High-Q	01005	7.2	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R3BB01	High-Q	01005	7.3	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R3CB01	High-Q	01005	7.3	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R3DB01	High-Q	01005	7.3	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R3WB01	High-Q	01005	7.3	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R3BB01	High-Q	01005	7.3	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R3CB01	High-Q	01005	7.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R3DB01	High-Q	01005	7.3	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R3WB01	High-Q	01005	7.3	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R4BB01	High-Q	01005	7.4	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R4CB01	High-Q	01005	7.4	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R4DB01	High-Q	01005	7.4	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R4WB01	High-Q	01005	7.4	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R4BB01	High-Q	01005	7.4	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R4CB01	High-Q	01005	7.4	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R4DB01	High-Q	01005	7.4	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R4WB01	High-Q	01005	7.4	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R5BB01	High-Q	01005	7.5	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R5WB01	High-Q	01005	7.5	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R5CB01	High-Q	01005	7.5	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R5DB01	High-Q	01005	7.5	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R5BB01	High-Q	01005	7.5	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R5CB01	High-Q	01005	7.5	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R5DB01	High-Q	01005	7.5	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R5WB01	High-Q	01005	7.5	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R6BB01	High-Q	01005	7.6	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R6CB01	High-Q	01005	7.6	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM0225C1C7R6DB01	High-Q	01005	7.6	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R6WB01	High-Q	01005	7.6	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R6BB01	High-Q	01005	7.6	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R6CB01	High-Q	01005	7.6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R6DB01	High-Q	01005	7.6	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R6WB01	High-Q	01005	7.6	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R7BB01	High-Q	01005	7.7	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R7CB01	High-Q	01005	7.7	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R7DB01	High-Q	01005	7.7	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R7WB01	High-Q	01005	7.7	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R7BB01	High-Q	01005	7.7	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R7CB01	High-Q	01005	7.7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R7DB01	High-Q	01005	7.7	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R7WB01	High-Q	01005	7.7	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R8BB01	High-Q	01005	7.8	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R8CB01	High-Q	01005	7.8	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R8DB01	High-Q	01005	7.8	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R8WB01	High-Q	01005	7.8	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R8BB01	High-Q	01005	7.8	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R8CB01	High-Q	01005	7.8	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R8DB01	High-Q	01005	7.8	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R8WB01	High-Q	01005	7.8	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R9BB01	High-Q	01005	7.9	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R9CB01	High-Q	01005	7.9	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R9DB01	High-Q	01005	7.9	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C7R9WB01	High-Q	01005	7.9	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R9BB01	High-Q	01005	7.9	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R9CB01	High-Q	01005	7.9	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R9DB01	High-Q	01005	7.9	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E7R9WB01	High-Q	01005	7.9	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R0BB01	High-Q	01005	8	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R0WB01	High-Q	01005	8	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R0CB01	High-Q	01005	8	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R0DB01	High-Q	01005	8	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R0BB01	High-Q	01005	8	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R0CB01	High-Q	01005	8	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R0DB01	High-Q	01005	8	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R0WB01	High-Q	01005	8	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R1BB01	High-Q	01005	8.1	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R1CB01	High-Q	01005	8.1	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R1DB01	High-Q	01005	8.1	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R1WB01	High-Q	01005	8.1	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R1BB01	High-Q	01005	8.1	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R1CB01	High-Q	01005	8.1	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R1DB01	High-Q	01005	8.1	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R1WB01	High-Q	01005	8.1	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R2BB01	High-Q	01005	8.2	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R2WB01	High-Q	01005	8.2	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R2CB01	High-Q	01005	8.2	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R2DB01	High-Q	01005	8.2	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R2BB01	High-Q	01005	8.2	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R2CB01	High-Q	01005	8.2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R2DB01	High-Q	01005	8.2	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R2WB01	High-Q	01005	8.2	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R3BB01	High-Q	01005	8.3	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R3CB01	High-Q	01005	8.3	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM0225C1C8R3DB01	High-Q	01005	8.3	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R3WB01	High-Q	01005	8.3	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R3BB01	High-Q	01005	8.3	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R3CB01	High-Q	01005	8.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R3DB01	High-Q	01005	8.3	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R3WB01	High-Q	01005	8.3	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R4BB01	High-Q	01005	8.4	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R4CB01	High-Q	01005	8.4	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R4DB01	High-Q	01005	8.4	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R4WB01	High-Q	01005	8.4	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R4BB01	High-Q	01005	8.4	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R4CB01	High-Q	01005	8.4	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R4DB01	High-Q	01005	8.4	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R4WB01	High-Q	01005	8.4	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R5BB01	High-Q	01005	8.5	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R5CB01	High-Q	01005	8.5	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R5DB01	High-Q	01005	8.5	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R5WB01	High-Q	01005	8.5	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R5BB01	High-Q	01005	8.5	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R5CB01	High-Q	01005	8.5	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R5DB01	High-Q	01005	8.5	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R5WB01	High-Q	01005	8.5	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R6BB01	High-Q	01005	8.6	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R6CB01	High-Q	01005	8.6	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R6DB01	High-Q	01005	8.6	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R6WB01	High-Q	01005	8.6	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R6BB01	High-Q	01005	8.6	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R6CB01	High-Q	01005	8.6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R6DB01	High-Q	01005	8.6	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R6WB01	High-Q	01005	8.6	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R7BB01	High-Q	01005	8.7	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R7CB01	High-Q	01005	8.7	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R7DB01	High-Q	01005	8.7	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R7WB01	High-Q	01005	8.7	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R7BB01	High-Q	01005	8.7	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R7CB01	High-Q	01005	8.7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R7DB01	High-Q	01005	8.7	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R7WB01	High-Q	01005	8.7	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R8BB01	High-Q	01005	8.8	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R8CB01	High-Q	01005	8.8	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R8DB01	High-Q	01005	8.8	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R8WB01	High-Q	01005	8.8	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R8BB01	High-Q	01005	8.8	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R8CB01	High-Q	01005	8.8	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R8DB01	High-Q	01005	8.8	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R8WB01	High-Q	01005	8.8	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R9BB01	High-Q	01005	8.9	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R9CB01	High-Q	01005	8.9	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R9DB01	High-Q	01005	8.9	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C8R9WB01	High-Q	01005	8.9	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R9BB01	High-Q	01005	8.9	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R9CB01	High-Q	01005	8.9	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R9DB01	High-Q	01005	8.9	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E8R9WB01	High-Q	01005	8.9	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R0BB01	High-Q	01005	9	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R0WB01	High-Q	01005	9	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM0225C1C9R0CB01	High-Q	01005	9	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R0DB01	High-Q	01005	9	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R0BB01	High-Q	01005	9	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R0CB01	High-Q	01005	9	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R0DB01	High-Q	01005	9	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R0WB01	High-Q	01005	9	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R1BB01	High-Q	01005	9.1	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R1WB01	High-Q	01005	9.1	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R1CB01	High-Q	01005	9.1	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R1DB01	High-Q	01005	9.1	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R1BB01	High-Q	01005	9.1	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R1CB01	High-Q	01005	9.1	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R1DB01	High-Q	01005	9.1	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R1WB01	High-Q	01005	9.1	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R2BB01	High-Q	01005	9.2	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R2CB01	High-Q	01005	9.2	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R2DB01	High-Q	01005	9.2	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R2WB01	High-Q	01005	9.2	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R2BB01	High-Q	01005	9.2	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R2CB01	High-Q	01005	9.2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R2DB01	High-Q	01005	9.2	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R2WB01	High-Q	01005	9.2	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R3BB01	High-Q	01005	9.3	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R3CB01	High-Q	01005	9.3	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R3DB01	High-Q	01005	9.3	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R3WB01	High-Q	01005	9.3	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R3BB01	High-Q	01005	9.3	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R3CB01	High-Q	01005	9.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R3DB01	High-Q	01005	9.3	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R3WB01	High-Q	01005	9.3	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R4BB01	High-Q	01005	9.4	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R4CB01	High-Q	01005	9.4	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R4DB01	High-Q	01005	9.4	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R4WB01	High-Q	01005	9.4	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R4BB01	High-Q	01005	9.4	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R4CB01	High-Q	01005	9.4	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R4DB01	High-Q	01005	9.4	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R4WB01	High-Q	01005	9.4	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R5BB01	High-Q	01005	9.5	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R5CB01	High-Q	01005	9.5	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R5DB01	High-Q	01005	9.5	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R5WB01	High-Q	01005	9.5	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R5BB01	High-Q	01005	9.5	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R5CB01	High-Q	01005	9.5	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R5DB01	High-Q	01005	9.5	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R5WB01	High-Q	01005	9.5	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R6BB01	High-Q	01005	9.6	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R6CB01	High-Q	01005	9.6	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R6DB01	High-Q	01005	9.6	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R6WB01	High-Q	01005	9.6	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R6BB01	High-Q	01005	9.6	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R6CB01	High-Q	01005	9.6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R6DB01	High-Q	01005	9.6	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R6WB01	High-Q	01005	9.6	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R7BB01	High-Q	01005	9.7	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R7CB01	High-Q	01005	9.7	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]



Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM0225C1C9R7DB01	High-Q	01005	9.7	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R7WB01	High-Q	01005	9.7	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R7BB01	High-Q	01005	9.7	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R7CB01	High-Q	01005	9.7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R7DB01	High-Q	01005	9.7	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R7WB01	High-Q	01005	9.7	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R8BB01	High-Q	01005	9.8	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R8CB01	High-Q	01005	9.8	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R8DB01	High-Q	01005	9.8	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R8WB01	High-Q	01005	9.8	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R8BB01	High-Q	01005	9.8	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R8CB01	High-Q	01005	9.8	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R8DB01	High-Q	01005	9.8	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R8WB01	High-Q	01005	9.8	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R9BB01	High-Q	01005	9.9	+/-0.1[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R9CB01	High-Q	01005	9.9	+/-0.25[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R9DB01	High-Q	01005	9.9	+/-0.5[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C9R9WB01	High-Q	01005	9.9	+/-0.05[pF]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R9BB01	High-Q	01005	9.9	+/-0.1[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R9CB01	High-Q	01005	9.9	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R9DB01	High-Q	01005	9.9	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E9R9WB01	High-Q	01005	9.9	+/-0.05[pF]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C100JB01	High-Q	01005	10	+/-5[%]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C100GB01	High-Q	01005	10	+/-2[%]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E100GB01	High-Q	01005	10	+/-2[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E100JB01	High-Q	01005	10	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C110GB01	High-Q	01005	11	+/-2[%]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C110JB01	High-Q	01005	11	+/-5[%]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E110GB01	High-Q	01005	11	+/-2[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E110JB01	High-Q	01005	11	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C120GB01	High-Q	01005	12	+/-2[%]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C120JB01	High-Q	01005	12	+/-5[%]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E120GB01	High-Q	01005	12	+/-2[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E120JB01	High-Q	01005	12	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C130GB01	High-Q	01005	13	+/-2[%]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C130JB01	High-Q	01005	13	+/-5[%]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E130GB01	High-Q	01005	13	+/-2[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E130JB01	High-Q	01005	13	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C150JB01	High-Q	01005	15	+/-5[%]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C150GB01	High-Q	01005	15	+/-2[%]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E150GB01	High-Q	01005	15	+/-2[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E150JB01	High-Q	01005	15	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C160GB01	High-Q	01005	16	+/-2[%]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C160JB01	High-Q	01005	16	+/-5[%]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E160GB01	High-Q	01005	16	+/-2[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E160JB01	High-Q	01005	16	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C180JB01	High-Q	01005	18	+/-5[%]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C180GB01	High-Q	01005	18	+/-2[%]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E180GB01	High-Q	01005	18	+/-2[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E180JB01	High-Q	01005	18	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C200JB01	High-Q	01005	20	+/-5[%]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C200GB01	High-Q	01005	20	+/-2[%]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1E200GB01	High-Q	01005	20	+/-2[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E200JB01	High-Q	01005	20	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1C220JB01	High-Q	01005	22	+/-5[%]	16	C0G	100[MHz]-8.5[GHz]
GJM0225C1C220GB01	High-Q	01005	22	+/-2[%]	16	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GJM0225C1E220GB01	High-Q	01005	22	+/-2[%]	25	C0G	100[MHz]-8.5[GHz]
GJM0225C1E220JB01	High-Q	01005	22	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E1R0CD03	Automotive	0201	1	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E1R1CD03	Automotive	0201	1.1	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E1R2CD03	Automotive	0201	1.2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E1R3CD03	Automotive	0201	1.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E1R5CD03	Automotive	0201	1.5	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E1R6CD03	Automotive	0201	1.6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E1R8CD03	Automotive	0201	1.8	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E2R0CD03	Automotive	0201	2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E2R2CD03	Automotive	0201	2.2	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E2R4CD03	Automotive	0201	2.4	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E2R7CD03	Automotive	0201	2.7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E3R0CD03	Automotive	0201	3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E3R3CD03	Automotive	0201	3.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E3R6CD03	Automotive	0201	3.6	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E3R9CD03	Automotive	0201	3.9	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E4R0CD03	Automotive	0201	4	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E4R3CD03	Automotive	0201	4.3	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E4R7CD03	Automotive	0201	4.7	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E5R0CD03	Automotive	0201	5	+/-0.25[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E5R1DD03	Automotive	0201	5.1	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E5R6DD03	Automotive	0201	5.6	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E6R0DD03	Automotive	0201	6	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E6R2DD03	Automotive	0201	6.2	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E6R8DD03	Automotive	0201	6.8	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E7R0DD03	Automotive	0201	7	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E7R5DD03	Automotive	0201	7.5	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E8R0DD03	Automotive	0201	8	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E8R2DD03	Automotive	0201	8.2	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E9R0DD03	Automotive	0201	9	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E9R1DD03	Automotive	0201	9.1	+/-0.5[pF]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E100JD03	Automotive	0201	10	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E120JD03	Automotive	0201	12	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E150JD03	Automotive	0201	15	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E180JD03	Automotive	0201	18	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E220JD03	Automotive	0201	22	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E270JD03	Automotive	0201	27	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E330JD03	Automotive	0201	33	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E390JD03	Automotive	0201	39	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E470JD03	Automotive	0201	47	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E560JD03	Automotive	0201	56	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E680JD03	Automotive	0201	68	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E820JD03	Automotive	0201	82	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GCM0335C1E101JD03	Automotive	0201	100	+/-5[%]	25	C0G	100[MHz]-8.5[GHz]
GCM033R71E101KA03	Automotive	0201	100	+/-10[%]	25	X7R	5[MHz]-6[GHz]
GCM033R71E151KA03	Automotive	0201	150	+/-10[%]	25	X7R	1[MHz]-6[GHz]
GCM033R71E221KA03	Automotive	0201	220	+/-10[%]	25	X7R	1[MHz]-6[GHz]
GCM033R71E331KA03	Automotive	0201	330	+/-10[%]	25	X7R	1[MHz]-6[GHz]
GCM033R71E471KA03	Automotive	0201	470	+/-10[%]	25	X7R	1[MHz]-6[GHz]
GCM033R71E681KA03	Automotive	0201	680	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM033R71E102KA03	Automotive	0201	1000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM033R71A152KA03	Automotive	0201	1500	+/-10[%]	10	X7R	100[kHz]-6[GHz]
GCM033R71E152KA03	Automotive	0201	1500	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM033R71A222KA03	Automotive	0201	2200	+/-10[%]	10	X7R	100[kHz]-6[GHz]
GCM033R71C222KA55	Automotive	0201	2200	+/-10[%]	16	X7R	100[kHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GCM033R71A332KA03	Automotive	0201	3300	+/-10[%]	10	X7R	100[kHz]-6[GHz]
GCM033R71C332KA55	Automotive	0201	3300	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GCM033R71A472KA03	Automotive	0201	4700	+/-10[%]	10	X7R	100[kHz]-6[GHz]
GCM033R71A682KA03	Automotive	0201	6800	+/-10[%]	10	X7R	100[kHz]-6[GHz]
GCM033R71A103KA03	Automotive	0201	10000	+/-10[%]	10	X7R	100[kHz]-6[GHz]
GCM1555C1H1R0CA16	Automotive	0402	1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H2R0CA16	Automotive	0402	2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H3R0CA16	Automotive	0402	3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H4R0CA16	Automotive	0402	4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H5R0CA16	Automotive	0402	5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H6R0DA16	Automotive	0402	6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H7R0DA16	Automotive	0402	7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H8R0DA16	Automotive	0402	8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H9R0DA16	Automotive	0402	9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H100JA16	Automotive	0402	10	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H120JA16	Automotive	0402	12	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H150JA16	Automotive	0402	15	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H180JA16	Automotive	0402	18	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H220JA16	Automotive	0402	22	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H270JA16	Automotive	0402	27	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H330JA16	Automotive	0402	33	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H390JA16	Automotive	0402	39	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H470JA16	Automotive	0402	47	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H560JA16	Automotive	0402	56	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H680JA16	Automotive	0402	68	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H820JA16	Automotive	0402	82	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H101JA16	Automotive	0402	100	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H121JA16	Automotive	0402	120	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H151JA16	Automotive	0402	150	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H181JA16	Automotive	0402	180	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H221JA16	Automotive	0402	220	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM155R71H221KA37	Automotive	0402	220	+/-10[%]	50	X7R	500[kHz]-6[GHz]
GCM155L81H221KA37	Automotive	0402	220	+/-10[%]	50	X8L	3[MHz]-6[GHz]
GCM155L81H221KA01	Automotive	0402	220	+/-10[%]	50	X8L	3[MHz]-6[GHz]
GCM155R72A221KA37	Automotive	0402	220	+/-10[%]	100	X7R	500[kHz]-6[GHz]
GCM155R72A221KA01	Automotive	0402	220	+/-10[%]	100	X7R	500[kHz]-6[GHz]
GCM1555C1H271JA16	Automotive	0402	270	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H331JA16	Automotive	0402	330	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM155R71H331KA37	Automotive	0402	330	+/-10[%]	50	X7R	300[kHz]-6[GHz]
GCM155R72A331KA01	Automotive	0402	330	+/-10[%]	100	X7R	300[kHz]-6[GHz]
GCM155R72A331KA37	Automotive	0402	330	+/-10[%]	100	X7R	300[kHz]-6[GHz]
GCM1555C1H391JA16	Automotive	0402	390	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1555C1H471JA16	Automotive	0402	470	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM155R71H471KA37	Automotive	0402	470	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM155L81H471KA37	Automotive	0402	470	+/-10[%]	50	X8L	100[kHz]-6[GHz]
GCM155L81H471KA01	Automotive	0402	470	+/-10[%]	50	X8L	100[kHz]-6[GHz]
GCM155R72A471KA37	Automotive	0402	470	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM155R72A471KA01	Automotive	0402	470	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM155R71H681KA37	Automotive	0402	680	+/-10[%]	50	X7R	1[MHz]-6[GHz]
GCM155R72A681KA01	Automotive	0402	680	+/-10[%]	100	X7R	1[MHz]-6[GHz]
GCM155R72A681KA37	Automotive	0402	680	+/-10[%]	100	X7R	1[MHz]-6[GHz]
GCM155R71H102KA37	Automotive	0402	1000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM155L81H102KA37	Automotive	0402	1000	+/-10[%]	50	X8L	100[kHz]-6[GHz]
GCM155L81H102KA01	Automotive	0402	1000	+/-10[%]	50	X8L	100[kHz]-6[GHz]
GCM155R72A102KA37	Automotive	0402	1000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM155R72A102KA01	Automotive	0402	1000	+/-10[%]	100	X7R	100[kHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GCM155R71H152KA37	Automotive	0402	1500	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM155R72A152KA01	Automotive	0402	1500	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM155R72A152KA37	Automotive	0402	1500	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM155R71H222KA37	Automotive	0402	2200	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM155L81H222KA37	Automotive	0402	2200	+/-10[%]	50	X8L	100[kHz]-6[GHz]
GCM155L81H222KA01	Automotive	0402	2200	+/-10[%]	50	X8L	100[kHz]-6[GHz]
GCM155R72A222KA37	Automotive	0402	2200	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM155R72A222KA01	Automotive	0402	2200	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM155R71H332KA37	Automotive	0402	3300	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM155R72A332KA01	Automotive	0402	3300	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM155R72A332KA37	Automotive	0402	3300	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM155R71H472KA37	Automotive	0402	4700	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM155L81H472KA37	Automotive	0402	4700	+/-10[%]	50	X8L	100[kHz]-6[GHz]
GCM155L81H472KA01	Automotive	0402	4700	+/-10[%]	50	X8L	100[kHz]-6[GHz]
GCM155R72A472KA37	Automotive	0402	4700	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM155R72A472KA01	Automotive	0402	4700	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM155R71E682KA37	Automotive	0402	6800	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM155R71H682KA55	Automotive	0402	6800	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM155R71E103KA37	Automotive	0402	10000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM155L81E103KA37	Automotive	0402	10000	+/-10[%]	25	X8L	100[kHz]-6[GHz]
GCM155L81E103KA01	Automotive	0402	10000	+/-10[%]	25	X8L	100[kHz]-6[GHz]
GCM155R71H103KA55	Automotive	0402	10000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM155R71E153KA55	Automotive	0402	15000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM155R71H153KA40	Automotive	0402	15000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM155R71H153KA55	Automotive	0402	15000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM155L81C223KA37	Automotive	0402	22000	+/-10[%]	16	X8L	100[kHz]-6[GHz]
GCM155L81C223KA01	Automotive	0402	22000	+/-10[%]	16	X8L	100[kHz]-6[GHz]
GCM155R71E223KA55	Automotive	0402	22000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM155R71H223KA55	Automotive	0402	22000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM155R71H223KA40	Automotive	0402	22000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM155R71C333KA37	Automotive	0402	33000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GCM155R71E333KA55	Automotive	0402	33000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM155R71C473KA37	Automotive	0402	47000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GCM155L81C473KA37	Automotive	0402	47000	+/-10[%]	16	X8L	100[kHz]-6[GHz]
GCM155L81C473KA01	Automotive	0402	47000	+/-10[%]	16	X8L	100[kHz]-6[GHz]
GCM155R71E473KA55	Automotive	0402	47000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM155R71C683KA55	Automotive	0402	68000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GCM155R71C104KA55	Automotive	0402	100000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GCM155R71H104KE02	Automotive	0402	100000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM155R71H104KE37	Automotive	0402	100000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM1885C1H1R0CA16	Automotive	0603	1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A1R0CA16	Automotive	0603	1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H2R0CA16	Automotive	0603	2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A2R0CA16	Automotive	0603	2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H3R0CA16	Automotive	0603	3	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A3R0CA16	Automotive	0603	3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H4R0CA16	Automotive	0603	4	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A4R0CA16	Automotive	0603	4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H5R0CA16	Automotive	0603	5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A5R0CA16	Automotive	0603	5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H6R0DA16	Automotive	0603	6	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A6R0DA16	Automotive	0603	6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H7R0DA16	Automotive	0603	7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A7R0DA16	Automotive	0603	7	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H8R0DA16	Automotive	0603	8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A8R0DA16	Automotive	0603	8	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GCM1885C1H9R0DA16	Automotive	0603	9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A9R0DA16	Automotive	0603	9	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H100JA16	Automotive	0603	10	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A100JA16	Automotive	0603	10	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H120JA16	Automotive	0603	12	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A120JA16	Automotive	0603	12	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H150JA16	Automotive	0603	15	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A150JA16	Automotive	0603	15	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H180JA16	Automotive	0603	18	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A180JA16	Automotive	0603	18	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H220JA16	Automotive	0603	22	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A220JA16	Automotive	0603	22	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H270JA16	Automotive	0603	27	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A270JA16	Automotive	0603	27	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H330JA16	Automotive	0603	33	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A330JA16	Automotive	0603	33	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H390JA16	Automotive	0603	39	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A390JA16	Automotive	0603	39	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H470JA16	Automotive	0603	47	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A470JA16	Automotive	0603	47	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H560JA16	Automotive	0603	56	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A560JA16	Automotive	0603	56	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H680JA16	Automotive	0603	68	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A680JA16	Automotive	0603	68	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H820JA16	Automotive	0603	82	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A820JA16	Automotive	0603	82	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H101JA16	Automotive	0603	100	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A101JA16	Automotive	0603	100	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H121JA16	Automotive	0603	120	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A121JA16	Automotive	0603	120	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H151JA16	Automotive	0603	150	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A151JA16	Automotive	0603	150	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H181JA16	Automotive	0603	180	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A181JA16	Automotive	0603	180	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H221JA16	Automotive	0603	220	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A221JA16	Automotive	0603	220	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H271JA16	Automotive	0603	270	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A271JA16	Automotive	0603	270	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H331JA16	Automotive	0603	330	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A331JA16	Automotive	0603	330	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H391JA16	Automotive	0603	390	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A391JA16	Automotive	0603	390	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H471JA16	Automotive	0603	470	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A471JA16	Automotive	0603	470	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H561JA16	Automotive	0603	560	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A561JA16	Automotive	0603	560	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H681JA16	Automotive	0603	680	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A681JA16	Automotive	0603	680	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM1885C1H821JA16	Automotive	0603	820	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM1885C2A821JA16	Automotive	0603	820	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM188R71E102KA37	Automotive	0603	1000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM1885C1H102JA16	Automotive	0603	1000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM188R71H102KA37	Automotive	0603	1000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCD188R71H102KA01	Automotive	0603	1000	+/-10[%]	50	X7R	300[kHz]-6[GHz]
GCM1885C2A102JA16	Automotive	0603	1000	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GCM188R72A102KA37	Automotive	0603	1000	+/-10[%]	100	X7R	100[kHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GCM188R72A102KA01	Automotive	0603	1000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCD188R72A102KA01	Automotive	0603	1000	+/-10[%]	100	X7R	300[kHz]-6[GHz]
GCM1885C1H122JA16	Automotive	0603	1200	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCD188R71H122KA01	Automotive	0603	1200	+/-10[%]	50	X7R	300[kHz]-6[GHz]
GCM1885C2A122JA16	Automotive	0603	1200	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GCD188R72A122KA01	Automotive	0603	1200	+/-10[%]	100	X7R	300[kHz]-6[GHz]
GCM188R71E152KA37	Automotive	0603	1500	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM1885C1H152JA16	Automotive	0603	1500	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM188R71H152KA37	Automotive	0603	1500	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCD188R71H152KA01	Automotive	0603	1500	+/-10[%]	50	X7R	300[kHz]-6[GHz]
GCM1885C2A152JA16	Automotive	0603	1500	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GCM188R72A152KA01	Automotive	0603	1500	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM188R72A152KA37	Automotive	0603	1500	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCD188R72A152KA01	Automotive	0603	1500	+/-10[%]	100	X7R	300[kHz]-6[GHz]
GCM1885C1H182JA16	Automotive	0603	1800	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCD188R71H182KA01	Automotive	0603	1800	+/-10[%]	50	X7R	300[kHz]-6[GHz]
GCD188R72A182KA01	Automotive	0603	1800	+/-10[%]	100	X7R	300[kHz]-6[GHz]
GCM188R71E222KA37	Automotive	0603	2200	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM1885C1H222JA16	Automotive	0603	2200	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM188R71H222KA37	Automotive	0603	2200	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCD188R71H222KA01	Automotive	0603	2200	+/-10[%]	50	X7R	300[kHz]-6[GHz]
GCM188R72A222KA37	Automotive	0603	2200	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM188R72A222KA01	Automotive	0603	2200	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCD188R72A222KA01	Automotive	0603	2200	+/-10[%]	100	X7R	300[kHz]-6[GHz]
GCM1885C1H272JA16	Automotive	0603	2700	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCD188R71H272KA01	Automotive	0603	2700	+/-10[%]	50	X7R	300[kHz]-6[GHz]
GCD188R72A272KA01	Automotive	0603	2700	+/-10[%]	100	X7R	300[kHz]-6[GHz]
GCM188R71E332KA37	Automotive	0603	3300	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM1885C1H332JA16	Automotive	0603	3300	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM188R71H332KA37	Automotive	0603	3300	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCD188R71H332KA01	Automotive	0603	3300	+/-10[%]	50	X7R	300[kHz]-6[GHz]
GCM188R72A332KA01	Automotive	0603	3300	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM188R72A332KA37	Automotive	0603	3300	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCD188R72A332KA01	Automotive	0603	3300	+/-10[%]	100	X7R	300[kHz]-6[GHz]
GCM1885C1H392JA16	Automotive	0603	3900	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCD188R71H392KA01	Automotive	0603	3900	+/-10[%]	50	X7R	300[kHz]-6[GHz]
GCD188R72A392KA01	Automotive	0603	3900	+/-10[%]	100	X7R	300[kHz]-6[GHz]
GCM188R71E472KA37	Automotive	0603	4700	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM188R71H472KA37	Automotive	0603	4700	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCD188R71H472KA01	Automotive	0603	4700	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM188R72A472KA37	Automotive	0603	4700	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM188R72A472KA01	Automotive	0603	4700	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCD188R72A472KA01	Automotive	0603	4700	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM188R71E682KA37	Automotive	0603	6800	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM188R71H682KA37	Automotive	0603	6800	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM188R72A682KA01	Automotive	0603	6800	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM188R72A682KA37	Automotive	0603	6800	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM188R71E103KA37	Automotive	0603	10000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM188R71H103KA37	Automotive	0603	10000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCD188R71H103KA01	Automotive	0603	10000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM188R72A103KA37	Automotive	0603	10000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM188R72A103KA01	Automotive	0603	10000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCD188R72A103KA01	Automotive	0603	10000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM188R71E153KA37	Automotive	0603	15000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM188R71H153KA37	Automotive	0603	15000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM188R72A153KA01	Automotive	0603	15000	+/-10[%]	100	X7R	100[kHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GCM188R72A153KA37	Automotive	0603	15000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM188R71E223KA37	Automotive	0603	22000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM188R71H223KA37	Automotive	0603	22000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCD188R71H223KA01	Automotive	0603	22000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM188L81H223KA37	Automotive	0603	22000	+/-10[%]	50	X8L	100[kHz]-6[GHz]
GCM188R72A223KA37	Automotive	0603	22000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM188R72A223KA01	Automotive	0603	22000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCD188R72A223KA01	Automotive	0603	22000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM188R71E333KA37	Automotive	0603	33000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM188R71H333KA55	Automotive	0603	33000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM188R71E473KA37	Automotive	0603	47000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCD188R71E473KA01	Automotive	0603	47000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM188R71H473KA55	Automotive	0603	47000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM188L81H473KA55	Automotive	0603	47000	+/-10[%]	50	X8L	100[kHz]-6[GHz]
GCM188L81H473KA40	Automotive	0603	47000	+/-10[%]	50	X8L	100[kHz]-6[GHz]
GCM188R71E683KA57	Automotive	0603	68000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM188R71H683KA57	Automotive	0603	68000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM188R71C104KA37	Automotive	0603	100000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GCM188R71E104KA57	Automotive	0603	100000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM188R71H104KA57	Automotive	0603	100000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM188L81H104KA57	Automotive	0603	100000	+/-10[%]	50	X8L	100[kHz]-6[GHz]
GCM188R71E154KA37	Automotive	0603	150000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM188R71H154KA49	Automotive	0603	150000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM188R71H154KA64	Automotive	0603	150000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM188L81C224KA37	Automotive	0603	220000	+/-10[%]	16	X8L	100[kHz]-6[GHz]
GCM188L81C224KA01	Automotive	0603	220000	+/-10[%]	16	X8L	100[kHz]-6[GHz]
GCM188R71E224KA55	Automotive	0603	220000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM188R71H224KA64	Automotive	0603	220000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM188R71H224KA49	Automotive	0603	220000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM188R71C334KA37	Automotive	0603	330000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GCM188R71C474KA55	Automotive	0603	470000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GCM188R71E474KA64	Automotive	0603	470000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM188R71E474KA49	Automotive	0603	470000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM188R71C105KA64	Automotive	0603	1000000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GCM188R71C105KA49	Automotive	0603	1000000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GCM188R71E105KA64	Automotive	0603	1000000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GCM188R71E105KA49	Automotive	0603	1000000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GCM188R70J225KE22	Automotive	0603	2200000	+/-10[%]	6.3	X7R	100[Hz]-6[GHz]
GCM188R70J225KE21	Automotive	0603	2200000	+/-10[%]	6.3	X7R	100[Hz]-6[GHz]
GCM2165C2A101JA16	Automotive	0805	100	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM2165C2A121JA16	Automotive	0805	120	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM2165C2A151JA16	Automotive	0805	150	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM2165C2A181JA16	Automotive	0805	180	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM2165C2A221JA16	Automotive	0805	220	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM2165C2A271JA16	Automotive	0805	270	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM2165C2A331JA16	Automotive	0805	330	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM2165C2A391JA16	Automotive	0805	390	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM2165C2A471JA16	Automotive	0805	470	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM2165C1H561JA16	Automotive	0805	560	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM2165C2A561JA16	Automotive	0805	560	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM2165C1H681JA16	Automotive	0805	680	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM2165C2A681JA16	Automotive	0805	680	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM2165C1H821JA16	Automotive	0805	820	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GCM2165C2A821JA16	Automotive	0805	820	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GCM2165C1H102JA16	Automotive	0805	1000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCD216R71H102KA01	Automotive	0805	1000	+/-10[%]	50	X7R	1[MHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GCM2165C2A102JA16	Automotive	0805	1000	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GCD216R72A102KA01	Automotive	0805	1000	+/-10[%]	100	X7R	1[MHz]-6[GHz]
GCM2165C1H122JA16	Automotive	0805	1200	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCD216R71H122KA01	Automotive	0805	1200	+/-10[%]	50	X7R	1[MHz]-6[GHz]
GCM2165C2A122JA16	Automotive	0805	1200	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GCD216R72A122KA01	Automotive	0805	1200	+/-10[%]	100	X7R	1[MHz]-6[GHz]
GCM2165C1H152JA16	Automotive	0805	1500	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCD216R71H152KA01	Automotive	0805	1500	+/-10[%]	50	X7R	300[kHz]-6[GHz]
GCM2165C2A152JA16	Automotive	0805	1500	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GCD216R72A152KA01	Automotive	0805	1500	+/-10[%]	100	X7R	300[kHz]-6[GHz]
GCM2165C1H182JA16	Automotive	0805	1800	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCD216R71H182KA01	Automotive	0805	1800	+/-10[%]	50	X7R	300[kHz]-6[GHz]
GCM2165C2A182JA16	Automotive	0805	1800	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GCD216R72A182KA01	Automotive	0805	1800	+/-10[%]	100	X7R	300[kHz]-6[GHz]
GCM2165C1H222JA16	Automotive	0805	2200	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCD216R71H222KA01	Automotive	0805	2200	+/-10[%]	50	X7R	300[kHz]-6[GHz]
GCM2165C2A222JA16	Automotive	0805	2200	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GCD216R72A222KA01	Automotive	0805	2200	+/-10[%]	100	X7R	300[kHz]-6[GHz]
GCM2165C1H272JA16	Automotive	0805	2700	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCD216R71H272KA01	Automotive	0805	2700	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM2165C2A272JA16	Automotive	0805	2700	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GCD216R72A272KA01	Automotive	0805	2700	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM2165C1H332JA16	Automotive	0805	3300	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCD216R71H332KA01	Automotive	0805	3300	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM2165C2A332JA16	Automotive	0805	3300	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GCD216R72A332KA01	Automotive	0805	3300	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM2165C1H392JA16	Automotive	0805	3900	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCD216R71H392KA01	Automotive	0805	3900	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCD216R72A392KA01	Automotive	0805	3900	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM2165C1H472JA16	Automotive	0805	4700	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCD216R71H472KA01	Automotive	0805	4700	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCD216R72A472KA01	Automotive	0805	4700	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM2195C1H562JA16	Automotive	0805	5600	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCD216R71H562KA01	Automotive	0805	5600	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCD216R72A562KA01	Automotive	0805	5600	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM2195C1H682JA16	Automotive	0805	6800	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM219R72A682KA01	Automotive	0805	6800	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM216R72A682KA37	Automotive	0805	6800	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCD219R72A682KA01	Automotive	0805	6800	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM2195C1H822JA16	Automotive	0805	8200	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCD21BR72A822KA01	Automotive	0805	8200	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM2195C1H103JA16	Automotive	0805	10000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM216R72A103KA37	Automotive	0805	10000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM21BR72A103KA01	Automotive	0805	10000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCD21BR72A103KA01	Automotive	0805	10000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM2195C1H123JA16	Automotive	0805	12000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCD21BR72A123KA01	Automotive	0805	12000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM2195C1H153JA16	Automotive	0805	15000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM216R72A153KA37	Automotive	0805	15000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM21BR72A153KA01	Automotive	0805	15000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM21B5C1H183JA16	Automotive	0805	18000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM21B5C1H223JA16	Automotive	0805	22000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCD21BR71H223KA01	Automotive	0805	22000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM216R72A223KA37	Automotive	0805	22000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM21BR72A223KA01	Automotive	0805	22000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCD21BR72A223KA01	Automotive	0805	22000	+/-10[%]	100	X7R	100[kHz]-6[GHz]



Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GCM219R71H333KA37	Automotive	0805	33000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM219R72A333KA37	Automotive	0805	33000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM21BR72A333KA01	Automotive	0805	33000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM21BR71H473KA37	Automotive	0805	47000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM21BR72A473KA01	Automotive	0805	47000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM21BR72A473KA37	Automotive	0805	47000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM21BR71H683KA37	Automotive	0805	68000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM21BR72A683KA01	Automotive	0805	68000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM21BR72A683KA37	Automotive	0805	68000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM21BR71E104KA37	Automotive	0805	100000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM21BR71H104KA37	Automotive	0805	100000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCD21BR71H104KA01	Automotive	0805	100000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM21BR72A104KA01	Automotive	0805	100000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM21BR72A104KA37	Automotive	0805	100000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCD21BR72A104KA01	Automotive	0805	100000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM21BR71E154KA37	Automotive	0805	150000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM21BR71H154KA37	Automotive	0805	150000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM219R71C224KA37	Automotive	0805	220000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GCM21BR71E224KA37	Automotive	0805	220000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM21BR71H224KA37	Automotive	0805	220000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM21BR71E334KA37	Automotive	0805	330000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM219R71H334KA40	Automotive	0805	330000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM219R71H334KA55	Automotive	0805	330000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM21BR71C474KA37	Automotive	0805	470000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GCM219R71E474KA55	Automotive	0805	470000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM21BR71H474KA40	Automotive	0805	470000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM21BR71H474KA55	Automotive	0805	470000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM219R71C684KA37	Automotive	0805	680000	+/-10[%]	16	X7R	100[kHz]-6[GHz]
GCM21BR71E684KA55	Automotive	0805	680000	+/-10[%]	25	X7R	100[kHz]-6[GHz]
GCM21BR7YA684KA40	Automotive	0805	680000	+/-10[%]	35	X7R	100[kHz]-6[GHz]
GCM21BR7YA684KA55	Automotive	0805	680000	+/-10[%]	35	X7R	100[kHz]-6[GHz]
GCM219R71C105KA37	Automotive	0805	1000000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GCM21BR71E105KA56	Automotive	0805	1000000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GCM21BR7YA105KA40	Automotive	0805	1000000	+/-10[%]	35	X7R	100[Hz]-6[GHz]
GCM21BR7YA105KA55	Automotive	0805	1000000	+/-10[%]	35	X7R	100[Hz]-6[GHz]
GCM21BR71H105KA01	Automotive	0805	1000000	+/-10[%]	50	X7R	100[Hz]-6[GHz]
GCM21BR71H105KA03	Automotive	0805	1000000	+/-10[%]	50	X7R	100[Hz]-6[GHz]
GCM21BR7YA155KA54	Automotive	0805	1500000	+/-10[%]	35	X7R	100[Hz]-6[GHz]
GCM21BR71A225KA01	Automotive	0805	2200000	+/-10[%]	10	X7R	100[Hz]-6[GHz]
GCM21BR71A225KA37	Automotive	0805	2200000	+/-10[%]	10	X7R	100[Hz]-6[GHz]
GCM21BR71C225KA49	Automotive	0805	2200000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GCM21BR71C225KA64	Automotive	0805	2200000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GCM21BR71E225KA67	Automotive	0805	2200000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GCM21BR71E225KA73	Automotive	0805	2200000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GCM21BC71A475KA67	Automotive	0805	4700000	+/-10[%]	10	X7S	100[Hz]-6[GHz]
GCM21BC71A475KA73	Automotive	0805	4700000	+/-10[%]	10	X7S	100[Hz]-6[GHz]
GCM21BR71C475KA67	Automotive	0805	4700000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GCM21BR71C475KA73	Automotive	0805	4700000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GCM21BR70J106KE21	Automotive	0805	10000000	+/-10[%]	6.3	X7R	100[Hz]-6[GHz]
GCM21BR70J106KE22	Automotive	0805	10000000	+/-10[%]	6.3	X7R	100[Hz]-6[GHz]
GCM21BR71A106KE21	Automotive	0805	10000000	+/-10[%]	10	X7R	100[Hz]-6[GHz]
GCM21BR71A106KE22	Automotive	0805	10000000	+/-10[%]	10	X7R	100[Hz]-6[GHz]
GCM3195C2A182JA16	Automotive	1206	1800	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GCM3195C2A222JA16	Automotive	1206	2200	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GCM3195C2A272JA16	Automotive	1206	2700	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GCM3195C2A332JA16	Automotive	1206	3300	+/-5[%]	100	C0G	1[MHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GCM3195C1H392JA16	Automotive	1206	3900	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM3195C2A392JA16	Automotive	1206	3900	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GCM3195C1H472JA16	Automotive	1206	4700	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM3195C2A472JA16	Automotive	1206	4700	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GCM3195C1H562JA16	Automotive	1206	5600	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM3195C2A562JA16	Automotive	1206	5600	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GCM3195C1H682JA16	Automotive	1206	6800	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM3195C2A682JA16	Automotive	1206	6800	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GCM3195C1H822JA16	Automotive	1206	8200	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM3195C2A822JA16	Automotive	1206	8200	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GCM3195C1H103JA16	Automotive	1206	10000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM3195C2A103JA16	Automotive	1206	10000	+/-5[%]	100	C0G	1[MHz]-6[GHz]
GCM3195C1H123JA16	Automotive	1206	12000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM3195C1H153JA16	Automotive	1206	15000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM3195C1H183JA16	Automotive	1206	18000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM3195C1H223JA16	Automotive	1206	22000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM3195C1H273JA16	Automotive	1206	27000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM3195C1H333JA16	Automotive	1206	33000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM3195C1H393JA16	Automotive	1206	39000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM31M5C1H473JA16	Automotive	1206	47000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM31M5C1H563JA16	Automotive	1206	56000	+/-5[%]	50	C0G	1[MHz]-6[GHz]
GCM319R72A104KA01	Automotive	1206	100000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM319R72A104KA37	Automotive	1206	100000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM31MR72A154KA01	Automotive	1206	150000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM31MR72A154KA37	Automotive	1206	150000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM31MR72A224KA01	Automotive	1206	220000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM31MR72A224KA37	Automotive	1206	220000	+/-10[%]	100	X7R	100[kHz]-6[GHz]
GCM31MR71H334KA37	Automotive	1206	330000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM31MR71H474KA37	Automotive	1206	470000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM31MR71H684KA55	Automotive	1206	680000	+/-10[%]	50	X7R	100[kHz]-6[GHz]
GCM31MR71E105KA37	Automotive	1206	1000000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GCM31MR71H105KA40	Automotive	1206	1000000	+/-10[%]	50	X7R	100[Hz]-6[GHz]
GCM31MR71H105KA55	Automotive	1206	1000000	+/-10[%]	50	X7R	100[Hz]-6[GHz]
GCM31CR72A105KA01	Automotive	1206	1000000	+/-10[%]	100	X7R	100[Hz]-6[GHz]
GCM31CR72A105KA03	Automotive	1206	1000000	+/-10[%]	100	X7R	100[Hz]-6[GHz]
GCM31MR71E225KA57	Automotive	1206	2200000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GCM31CR71H225KA40	Automotive	1206	2200000	+/-10[%]	50	X7R	100[Hz]-6[GHz]
GCM31CR71H225KA55	Automotive	1206	2200000	+/-10[%]	50	X7R	100[Hz]-6[GHz]
GCM31CR71C475KA37	Automotive	1206	4700000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GCM31CR71E475KA40	Automotive	1206	4700000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GCM31CR71E475KA55	Automotive	1206	4700000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GCM31CC71H475KA03	Automotive	1206	4700000	+/-10[%]	50	X7S	100[Hz]-6[GHz]
GCM31CC71H475KA49	Automotive	1206	4700000	+/-10[%]	50	X7S	100[Hz]-6[GHz]
GCM31CR71A106KA64	Automotive	1206	10000000	+/-10[%]	10	X7R	100[Hz]-6[GHz]
GCM31CR71C106KA49	Automotive	1206	10000000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GCM31CR71C106KA64	Automotive	1206	10000000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GCM31CC71E106KA01	Automotive	1206	10000000	+/-10[%]	25	X7S	100[Hz]-6[GHz]
GCM31CC71E106KA03	Automotive	1206	10000000	+/-10[%]	25	X7S	100[Hz]-6[GHz]
GCM31CR70J226ME23	Automotive	1206	22000000	+/-20[%]	6.3	X7R	100[Hz]-6[GHz]
GCM31CR70J226ME26	Automotive	1206	22000000	+/-20[%]	6.3	X7R	100[Hz]-6[GHz]
GCM32ER71H105KA37	Automotive	1210	1000000	+/-10[%]	50	X7R	100[Hz]-6[GHz]
GCM32DR71E475KA55	Automotive	1210	4700000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GCM32ER71H475KA40	Automotive	1210	4700000	+/-10[%]	50	X7R	100[Hz]-6[GHz]
GCM32ER71H475KA55	Automotive	1210	4700000	+/-10[%]	50	X7R	100[Hz]-6[GHz]
GCM32DR71C106KA37	Automotive	1210	10000000	+/-10[%]	16	X7R	100[Hz]-6[GHz]
GCM32ER71E106KA42	Automotive	1210	10000000	+/-10[%]	25	X7R	100[Hz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GCM32ER71E106KA57	Automotive	1210	10000000	+/-10[%]	25	X7R	100[Hz]-6[GHz]
GCM32EC7YA106KA01	Automotive	1210	10000000	+/-10[%]	35	X7S	100[Hz]-6[GHz]
GCM32EC7YA106KA03	Automotive	1210	10000000	+/-10[%]	35	X7S	100[Hz]-6[GHz]
GCM32EC71H106KA01	Automotive	1210	10000000	+/-10[%]	50	X7S	100[Hz]-6[GHz]
GCM32EC71H106KA03	Automotive	1210	10000000	+/-10[%]	50	X7S	100[Hz]-6[GHz]
GCM32ER71A226KE12	Automotive	1210	22000000	+/-10[%]	10	X7R	100[Hz]-6[GHz]
GCM32ER71A226ME12	Automotive	1210	22000000	+/-20[%]	10	X7R	100[Hz]-6[GHz]
GCM32ER71C226ME15	Automotive	1210	22000000	+/-20[%]	16	X7R	100[Hz]-6[GHz]
GCM32ER71C226ME19	Automotive	1210	22000000	+/-20[%]	16	X7R	100[Hz]-6[GHz]
GCM32ER70J476ME16	Automotive	1210	47000000	+/-20[%]	6.3	X7R	100[Hz]-6[GHz]
GCM32ER70J476ME19	Automotive	1210	47000000	+/-20[%]	6.3	X7R	100[Hz]-6[GHz]
GCM21A7U2E101JX01	200V and over/ Automotive	0805	100	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GCM21A7U2E121JX01	200V and over/ Automotive	0805	120	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GCM21A7U2E151JX01	200V and over/ Automotive	0805	150	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GCM21A7U2E181JX01	200V and over/ Automotive	0805	180	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GCM21A7U2E221JX01	200V and over/ Automotive	0805	220	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GCM21A7U2E271JX01	200V and over/ Automotive	0805	270	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GCM21A7U2E331JX01	200V and over/ Automotive	0805	330	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GCM21A7U2E391JX01	200V and over/ Automotive	0805	390	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GCM21A7U2E471JX01	200V and over/ Automotive	0805	470	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GCM21A7U2E561JX01	200V and over/ Automotive	0805	560	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GCM21A7U2E681JX01	200V and over/ Automotive	0805	680	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GCM21A7U2E821JX01	200V and over/ Automotive	0805	820	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GCM21A7U2E102JX01	200V and over/ Automotive	0805	1000	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GCM21AR72E102KX01	200V and over/ Automotive	0805	1000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GCJ21AR72E102KXJ1	200V and over/ Automotive	0805	1000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GCM21A7U2E122JX01	200V and over/ Automotive	0805	1200	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GCM21A7U2E152JX01	200V and over/ Automotive	0805	1500	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GCM21AR72E152KX01	200V and over/ Automotive	0805	1500	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GCJ21AR72E152KXJ1	200V and over/ Automotive	0805	1500	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GCM21A7U2E182JX01	200V and over/ Automotive	0805	1800	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GCM21A7U2E222JX01	200V and over/ Automotive	0805	2200	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GCM21AR72E222KX01	200V and over/ Automotive	0805	2200	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GCJ21AR72E222KXJ1	200V and over/ Automotive	0805	2200	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GCM21B7U2E272JX03	200V and over/ Automotive	0805	2700	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GCM21B7U2E332JX03	200V and over/ Automotive	0805	3300	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GCM21AR72E332KX01	200V and over/ Automotive	0805	3300	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GCJ21AR72E332KXJ1	200V and over/ Automotive	0805	3300	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GCM21B7U2E392JX03	200V and over/ Automotive	0805	3900	+/-5[%]	250	U2J	1[MHz]-3[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GCM21B7U2E472JX03	200V and over/ Automotive	0805	4700	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GCM21AR72E472KX01	200V and over/ Automotive	0805	4700	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GCJ21AR72E472KXJ1	200V and over/ Automotive	0805	4700	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GCM21B7U2E562JX03	200V and over/ Automotive	0805	5600	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GCM21AR72E682KX01	200V and over/ Automotive	0805	6800	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GCJ21AR72E682KXJ1	200V and over/ Automotive	0805	6800	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GCM21BR72E103KX03	200V and over/ Automotive	0805	10000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GCJ21BR72E103KXJ3	200V and over/ Automotive	0805	10000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GC321AD72E103KX01	200V and over/ Automotive	0805	10000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GCJ21BR72E153KXJ3	200V and over/ Automotive	0805	15000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GCM21BR72E153KX03	200V and over/ Automotive	0805	15000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GC321AD72E153KX01	200V and over/ Automotive	0805	15000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GCJ21BR72E223KXJ3	200V and over/ Automotive	0805	22000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GCM21BR72E223KX03	200V and over/ Automotive	0805	22000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GC321BD72E223KX03	200V and over/ Automotive	0805	22000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GCM31A7U2J100JX01	200V and over/ Automotive	1206	10	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31A7U3A100JX01	200V and over/ Automotive	1206	10	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J120JX01	200V and over/ Automotive	1206	12	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31A7U3A120JX01	200V and over/ Automotive	1206	12	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J150JX01	200V and over/ Automotive	1206	15	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31A7U3A150JX01	200V and over/ Automotive	1206	15	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J180JX01	200V and over/ Automotive	1206	18	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31A7U3A180JX01	200V and over/ Automotive	1206	18	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J220JX01	200V and over/ Automotive	1206	22	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31A7U3A220JX01	200V and over/ Automotive	1206	22	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J270JX01	200V and over/ Automotive	1206	27	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31A7U3A270JX01	200V and over/ Automotive	1206	27	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J330JX01	200V and over/ Automotive	1206	33	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31A7U3A330JX01	200V and over/ Automotive	1206	33	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J390JX01	200V and over/ Automotive	1206	39	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31A7U3A390JX01	200V and over/ Automotive	1206	39	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J470JX01	200V and over/ Automotive	1206	47	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31A7U3A470JX01	200V and over/ Automotive	1206	47	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J560JX01	200V and over/ Automotive	1206	56	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31A7U3A560JX01	200V and over/ Automotive	1206	56	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J680JX01	200V and over/ Automotive	1206	68	+/-5[%]	630	U2J	100[MHz]-3[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GCM31A7U3A680JX01	200V and over/ Automotive	1206	68	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J820JX01	200V and over/ Automotive	1206	82	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31A7U3A820JX01	200V and over/ Automotive	1206	82	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J101JX01	200V and over/ Automotive	1206	100	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31A7U3A101JX01	200V and over/ Automotive	1206	100	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J121JX01	200V and over/ Automotive	1206	120	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31A7U3A121JX01	200V and over/ Automotive	1206	120	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J151JX01	200V and over/ Automotive	1206	150	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31A7U3A151JX01	200V and over/ Automotive	1206	150	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J181JX01	200V and over/ Automotive	1206	180	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31A7U3A181JX01	200V and over/ Automotive	1206	180	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J221JX01	200V and over/ Automotive	1206	220	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31A7U3A221JX01	200V and over/ Automotive	1206	220	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J271JX01	200V and over/ Automotive	1206	270	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31A7U3A271JX01	200V and over/ Automotive	1206	270	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J331JX01	200V and over/ Automotive	1206	330	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31A7U3A331JX01	200V and over/ Automotive	1206	330	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J391JX01	200V and over/ Automotive	1206	390	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31B7U3A391JX01	200V and over/ Automotive	1206	390	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J471JX01	200V and over/ Automotive	1206	470	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31B7U3A471JX01	200V and over/ Automotive	1206	470	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J561JX01	200V and over/ Automotive	1206	560	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31B7U3A561JX01	200V and over/ Automotive	1206	560	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J681JX01	200V and over/ Automotive	1206	680	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31B7U3A681JX01	200V and over/ Automotive	1206	680	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J821JX01	200V and over/ Automotive	1206	820	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GCM31C7U3A821JX03	200V and over/ Automotive	1206	820	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GCM31A7U2J102JX01	200V and over/ Automotive	1206	1000	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM31BR72J102KX01	200V and over/ Automotive	1206	1000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GCJ31BR72J102KXJ1	200V and over/ Automotive	1206	1000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GCM31C7U3A102JX03	200V and over/ Automotive	1206	1000	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GCJ31BR73A102KXJ1	200V and over/ Automotive	1206	1000	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GCM31BR73A102KX01	200V and over/ Automotive	1206	1000	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GCM31A7U2J122JX01	200V and over/ Automotive	1206	1200	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM31A7U2J152JX01	200V and over/ Automotive	1206	1500	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM31BR72J152KX01	200V and over/ Automotive	1206	1500	+/-10[%]	630	X7R	100[kHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GCJ31BR72J152KXJ1	200V and over/ Automotive	1206	1500	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GCJ31BR73A152KXJ1	200V and over/ Automotive	1206	1500	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GCM31BR73A152KX01	200V and over/ Automotive	1206	1500	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GCM31A7U2J182JX01	200V and over/ Automotive	1206	1800	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM31A7U2J222JX01	200V and over/ Automotive	1206	2200	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM31BR72J222KX01	200V and over/ Automotive	1206	2200	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GCJ31BR72J222KXJ1	200V and over/ Automotive	1206	2200	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GCJ31BR73A222KXJ1	200V and over/ Automotive	1206	2200	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GCM31BR73A222KX01	200V and over/ Automotive	1206	2200	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GCM31A7U2E272JX01	200V and over/ Automotive	1206	2700	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GCM31B7U2J272JX01	200V and over/ Automotive	1206	2700	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM31A7U2E332JX01	200V and over/ Automotive	1206	3300	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GCM31B7U2J332JX01	200V and over/ Automotive	1206	3300	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM31BR72J332KX01	200V and over/ Automotive	1206	3300	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GCJ31BR72J332KXJ1	200V and over/ Automotive	1206	3300	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GCJ31BR73A332KXJ1	200V and over/ Automotive	1206	3300	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GCM31BR73A332KX01	200V and over/ Automotive	1206	3300	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GCM31A7U2E392JX01	200V and over/ Automotive	1206	3900	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GCM31C7U2J392JX03	200V and over/ Automotive	1206	3900	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM31A7U2E472JX01	200V and over/ Automotive	1206	4700	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GCM31C7U2J472JX03	200V and over/ Automotive	1206	4700	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM31BR72J472KX01	200V and over/ Automotive	1206	4700	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GCJ31BR72J472KXJ1	200V and over/ Automotive	1206	4700	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GCJ31BR73A472KXJ1	200V and over/ Automotive	1206	4700	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GCM31BR73A472KX01	200V and over/ Automotive	1206	4700	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GCM31A7U2E562JX01	200V and over/ Automotive	1206	5600	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GCM31B7U2E682JX01	200V and over/ Automotive	1206	6800	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GCJ31BR72J682KXJ1	200V and over/ Automotive	1206	6800	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GCM31BR72J682KX01	200V and over/ Automotive	1206	6800	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GCJ31CR73A682KXJ3	200V and over/ Automotive	1206	6800	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GCM31CR73A682KX03	200V and over/ Automotive	1206	6800	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GCM31B7U2E822JX01	200V and over/ Automotive	1206	8200	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GCM31B7U2E103JX01	200V and over/ Automotive	1206	10000	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GC331AD72W103KX01	200V and over/ Automotive	1206	10000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GCJ31BR72J103KXJ1	200V and over/ Automotive	1206	10000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GCM31BR72J103KX01	200V and over/ Automotive	1206	10000	+/-10[%]	630	X7R	100[kHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GC331BD72J103KX01	200V and over/ Automotive	1206	10000	+/-10[%]	630	X7T	100[kHz]-3[GHz]
GCJ31CR73A103KXJ3	200V and over/ Automotive	1206	10000	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GCM31CR73A103KX03	200V and over/ Automotive	1206	10000	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GCM31BR72E153KX01	200V and over/ Automotive	1206	15000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GCJ31BR72E153KXJ1	200V and over/ Automotive	1206	15000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GC331AD72W153KX01	200V and over/ Automotive	1206	15000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GCJ31CR72J153KXJ3	200V and over/ Automotive	1206	15000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GCM31CR72J153KX03	200V and over/ Automotive	1206	15000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GC331CD72J153KX03	200V and over/ Automotive	1206	15000	+/-10[%]	630	X7T	100[kHz]-3[GHz]
GCM31BR72E223KX01	200V and over/ Automotive	1206	22000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GCJ31BR72E223KXJ1	200V and over/ Automotive	1206	22000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GC331BD72W223KX01	200V and over/ Automotive	1206	22000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GCJ31CR72J223KXJ3	200V and over/ Automotive	1206	22000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GCM31CR72J223KX03	200V and over/ Automotive	1206	22000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GCM31CR72E333KX03	200V and over/ Automotive	1206	33000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GCJ31CR72E333KXJ3	200V and over/ Automotive	1206	33000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GC331AD72E333KX01	200V and over/ Automotive	1206	33000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GC331BD72W333KX01	200V and over/ Automotive	1206	33000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GCM31CR72E473KX03	200V and over/ Automotive	1206	47000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GCJ31CR72E473KXJ3	200V and over/ Automotive	1206	47000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GC331BD72E473KX01	200V and over/ Automotive	1206	47000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GC331CD72W473KX03	200V and over/ Automotive	1206	47000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GCJ31BR72E683KXJ1	200V and over/ Automotive	1206	68000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GCM31BR72E683KX01	200V and over/ Automotive	1206	68000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GC331CD72E683KX03	200V and over/ Automotive	1206	68000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GCJ31CR72E104KXJ3	200V and over/ Automotive	1206	100000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GCM31CR72E104KX03	200V and over/ Automotive	1206	100000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GCM32A7U2J122JX01	200V and over/ Automotive	1210	1200	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM32B7U3A122JX01	200V and over/ Automotive	1210	1200	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GCM32A7U2J152JX01	200V and over/ Automotive	1210	1500	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM32Q7U3A152JX01	200V and over/ Automotive	1210	1500	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GCM32A7U2J182JX01	200V and over/ Automotive	1210	1800	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM32D7U3A182JX01	200V and over/ Automotive	1210	1800	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GCM32A7U2J222JX01	200V and over/ Automotive	1210	2200	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM32D7U3A222JX01	200V and over/ Automotive	1210	2200	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GCM32B7U2J562JX01	200V and over/ Automotive	1210	5600	+/-5[%]	630	U2J	1[MHz]-3[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GCM32Q7U2J682JX01	200V and over/ Automotive	1210	6800	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM32QR72J682KX01	200V and over/ Automotive	1210	6800	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GCJ32QR72J682KXJ1	200V and over/ Automotive	1210	6800	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GCM32D7U2J822JX01	200V and over/ Automotive	1210	8200	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM32D7U2J103JX01	200V and over/ Automotive	1210	10000	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM32QR72J103KX01	200V and over/ Automotive	1210	10000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GCJ32QR72J103KXJ1	200V and over/ Automotive	1210	10000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GCM32DR72J153KX01	200V and over/ Automotive	1210	15000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GCJ32DR72J153KXJ1	200V and over/ Automotive	1210	15000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GCJ32DR73A153KXJ1	200V and over/ Automotive	1210	15000	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GCM32DR73A153KX01	200V and over/ Automotive	1210	15000	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GCM32DR72J223KX01	200V and over/ Automotive	1210	22000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GCJ32DR72J223KXJ1	200V and over/ Automotive	1210	22000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GC332QD72J223KX01	200V and over/ Automotive	1210	22000	+/-10[%]	630	X7T	100[kHz]-3[GHz]
GCJ32DR73A223KXJ1	200V and over/ Automotive	1210	22000	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GCM32DR73A223KX01	200V and over/ Automotive	1210	22000	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GCJ32DR72J333KXJ1	200V and over/ Automotive	1210	33000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GCM32DR72J333KX01	200V and over/ Automotive	1210	33000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GC332DD72J333KX01	200V and over/ Automotive	1210	33000	+/-10[%]	630	X7T	100[kHz]-3[GHz]
GCJ32DR72J473KXJ1	200V and over/ Automotive	1210	47000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GCM32DR72J473KX01	200V and over/ Automotive	1210	47000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GC332DD72J473KX01	200V and over/ Automotive	1210	47000	+/-10[%]	630	X7T	100[kHz]-3[GHz]
GCM32QR72E683KX01	200V and over/ Automotive	1210	68000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GCJ32QR72E683KXJ1	200V and over/ Automotive	1210	68000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GC332DD72W683KX01	200V and over/ Automotive	1210	68000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GCM32DR72E104KX01	200V and over/ Automotive	1210	100000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GCJ32DR72E104KXJ1	200V and over/ Automotive	1210	100000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GC332QD72E104KX01	200V and over/ Automotive	1210	100000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GC332DD72W104KX01	200V and over/ Automotive	1210	100000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GCJ32QR72E154KXJ1	200V and over/ Automotive	1210	150000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GCM32QR72E154KX01	200V and over/ Automotive	1210	150000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GC332DD72E154KX01	200V and over/ Automotive	1210	150000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GCJ32DR72E224KXJ1	200V and over/ Automotive	1210	220000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GCM32DR72E224KX01	200V and over/ Automotive	1210	220000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GCM43Q7U3A272JX01	200V and over/ Automotive	1812	2700	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GCM43Q7U3A332JX01	200V and over/ Automotive	1812	3300	+/-5[%]	1000	U2J	1[MHz]-3[GHz]



Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GCM43D7U3A392JX01	200V and over/ Automotive	1812	3900	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GCM43D7U3A472JX01	200V and over/ Automotive	1812	4700	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GCM43Q7U2J123JX01	200V and over/ Automotive	1812	12000	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM43D7U2J153JX01	200V and over/ Automotive	1812	15000	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM43D7U2J183JX01	200V and over/ Automotive	1812	18000	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM43D7U2J223JX01	200V and over/ Automotive	1812	22000	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM43DR72J333KX01	200V and over/ Automotive	1812	33000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GCJ43DR72J333KXJ1	200V and over/ Automotive	1812	33000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GCJ43DR73A333KXJ1	200V and over/ Automotive	1812	33000	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GCM43DR73A333KX01	200V and over/ Automotive	1812	33000	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GCM43DR72J473KX01	200V and over/ Automotive	1812	47000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GCJ43DR72J473KXJ1	200V and over/ Automotive	1812	47000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GCJ43DR73A473KXJ1	200V and over/ Automotive	1812	47000	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GCM43DR73A473KX01	200V and over/ Automotive	1812	47000	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GCJ43QR72J683KXJ1	200V and over/ Automotive	1812	68000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GCM43QR72J683KX01	200V and over/ Automotive	1812	68000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GC343DD72J683KX01	200V and over/ Automotive	1812	68000	+/-10[%]	630	X7T	100[kHz]-3[GHz]
GCJ43DR72J104KXJ1	200V and over/ Automotive	1812	100000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GCM43DR72J104KX01	200V and over/ Automotive	1812	100000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GCM43QR72E154KX01	200V and over/ Automotive	1812	150000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GC343DD72W154KX01	200V and over/ Automotive	1812	150000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GCM43DR72E224KX01	200V and over/ Automotive	1812	220000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GC343QD72E224KX01	200V and over/ Automotive	1812	220000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GCJ43DR72E334KXJ1	200V and over/ Automotive	1812	330000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GCM43DR72E334KX01	200V and over/ Automotive	1812	330000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GC343DD72E334KX01	200V and over/ Automotive	1812	330000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GCJ43DR72E474KXJ1	200V and over/ Automotive	1812	470000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GCM43DR72E474KX01	200V and over/ Automotive	1812	470000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GCM55Q7U3A562JX01	200V and over/ Automotive	2220	5600	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GCM55Q7U3A682JX01	200V and over/ Automotive	2220	6800	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GCM55D7U3A822JX01	200V and over/ Automotive	2220	8200	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GCM55D7U3A103JX01	200V and over/ Automotive	2220	10000	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GCM55Q7U2J273JX01	200V and over/ Automotive	2220	27000	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM55D7U2J333JX01	200V and over/ Automotive	2220	33000	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM55D7U2J393JX01	200V and over/ Automotive	2220	39000	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GCM55D7U2J473JX01	200V and over/ Automotive	2220	47000	+/-5[%]	630	U2J	1[MHz]-3[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GCJ55DR73A683KXJ1	200V and over/ Automotive	2220	68000	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GCM55DR73A683KX01	200V and over/ Automotive	2220	68000	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GCM55DR72J104KX01	200V and over/ Automotive	2220	100000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GCJ55DR72J104KXJ1	200V and over/ Automotive	2220	100000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GC355DD72J104KX01	200V and over/ Automotive	2220	100000	+/-10[%]	630	X7T	100[kHz]-3[GHz]
GCJ55DR73A104KXJ1	200V and over/ Automotive	2220	100000	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GCM55DR73A104KX01	200V and over/ Automotive	2220	100000	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GCJ55DR72J154KXJ1	200V and over/ Automotive	2220	150000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GCM55DR72J154KX01	200V and over/ Automotive	2220	150000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GC355DD72J154KX01	200V and over/ Automotive	2220	150000	+/-10[%]	630	X7T	100[kHz]-3[GHz]
GC355DD72W224KX01	200V and over/ Automotive	2220	220000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GCJ55DR72J224KXJ1	200V and over/ Automotive	2220	220000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GCM55DR72J224KX01	200V and over/ Automotive	2220	220000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GC355XD72J224KX05	200V and over/ Automotive	2220	220000	+/-10[%]	630	X7T	100[kHz]-3[GHz]
GC355XD72J274KX05	200V and over/ Automotive	2220	270000	+/-10[%]	630	X7T	100[kHz]-3[GHz]
GCM55DR72E334KX01	200V and over/ Automotive	2220	330000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GC355DD72W334KX01	200V and over/ Automotive	2220	330000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GCM55DR72E474KX01	200V and over/ Automotive	2220	470000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GC355DD72E474KX01	200V and over/ Automotive	2220	470000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GC355DD72W474KX01	200V and over/ Automotive	2220	470000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GC355XD72W564KX05	200V and over/ Automotive	2220	560000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GCJ55DR72E684KXJ1	200V and over/ Automotive	2220	680000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GCM55DR72E684KX01	200V and over/ Automotive	2220	680000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GC355DD72E684KX01	200V and over/ Automotive	2220	680000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GCJ55DR72E105KXJ1	200V and over/ Automotive	2220	1000000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GCM55DR72E105KX01	200V and over/ Automotive	2220	1000000	+/-10[%]	250	X7R	100[Hz]-6[GHz]
GC355XD72E105KX05	200V and over/ Automotive	2220	1000000	+/-10[%]	250	X7T	100[Hz]-3[GHz]
GR721AW0BB103KW01	200V and over/ Camera Flash Units	0805	10000	+/-10[%]	350	-	100[kHz]-3[GHz]
GR721AW0BB153KW01	200V and over/ Camera Flash Units	0805	15000	+/-10[%]	350	-	100[kHz]-3[GHz]
GR721BW0BB223KW03	200V and over/ Camera Flash Units	0805	22000	+/-10[%]	350	-	100[kHz]-3[GHz]
GR721BW0BB273KW03	200V and over/ Camera Flash Units	0805	27000	+/-10[%]	350	-	100[kHz]-3[GHz]
GR731AW0BB103KW01	200V and over/ Camera Flash Units	1206	10000	+/-10[%]	350	-	100[kHz]-3[GHz]
GR731AW0BB153KW01	200V and over/ Camera Flash Units	1206	15000	+/-10[%]	350	-	100[kHz]-3[GHz]
GR731AW0BB223KW01	200V and over/ Camera Flash Units	1206	22000	+/-10[%]	350	-	100[kHz]-3[GHz]
GR731BW0BB223KW01	200V and over/ Camera Flash Units	1206	22000	+/-10[%]	350	-	100[kHz]-3[GHz]
GR731AW0BB273KW01	200V and over/ Camera Flash Units	1206	27000	+/-10[%]	350	-	100[kHz]-3[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GR731AW0BB333KW01	200V and over/ Camera Flash Units	1206	33000	+/-10[%]	350	-	100[kHz]-3[GHz]
GR731BW0BB333KW01	200V and over/ Camera Flash Units	1206	33000	+/-10[%]	350	-	100[kHz]-3[GHz]
GR731CW0BB473KW03	200V and over/ Camera Flash Units	1206	47000	+/-10[%]	350	-	100[kHz]-3[GHz]
GR442QR73D101KW01	200V and over/ Information Devices	1808	100	+/-10[%]	2000	X7R	5[MHz]-3[GHz]
GR442QR73D121KW01	200V and over/ Information Devices	1808	120	+/-10[%]	2000	X7R	5[MHz]-3[GHz]
GR442QR73D151KW01	200V and over/ Information Devices	1808	150	+/-10[%]	2000	X7R	5[MHz]-3[GHz]
GR442QR73D181KW01	200V and over/ Information Devices	1808	180	+/-10[%]	2000	X7R	3[MHz]-3[GHz]
GR442QR73D221KW01	200V and over/ Information Devices	1808	220	+/-10[%]	2000	X7R	3[MHz]-3[GHz]
GR442QR73D271KW01	200V and over/ Information Devices	1808	270	+/-10[%]	2000	X7R	3[MHz]-3[GHz]
GR442QR73D331KW01	200V and over/ Information Devices	1808	330	+/-10[%]	2000	X7R	1[MHz]-3[GHz]
GR442QR73D391KW01	200V and over/ Information Devices	1808	390	+/-10[%]	2000	X7R	1[MHz]-3[GHz]
GR442QR73D471KW01	200V and over/ Information Devices	1808	470	+/-10[%]	2000	X7R	500[kHz]-3[GHz]
GR442QR73D561KW01	200V and over/ Information Devices	1808	560	+/-10[%]	2000	X7R	300[kHz]-3[GHz]
GR442QR73D681KW01	200V and over/ Information Devices	1808	680	+/-10[%]	2000	X7R	300[kHz]-3[GHz]
GR442QR73D821KW01	200V and over/ Information Devices	1808	820	+/-10[%]	2000	X7R	300[kHz]-3[GHz]
GR442QR73D102KW01	200V and over/ Information Devices	1808	1000	+/-10[%]	2000	X7R	100[kHz]-3[GHz]
GR442QR73D122KW01	200V and over/ Information Devices	1808	1200	+/-10[%]	2000	X7R	100[kHz]-3[GHz]
GR442QR73D152KW01	200V and over/ Information Devices	1808	1500	+/-10[%]	2000	X7R	100[kHz]-3[GHz]
GR443QR73D102KW01	200V and over/ Information Devices	1812	1000	+/-10[%]	2000	X7R	100[kHz]-3[GHz]
GR443QR73D182KW01	200V and over/ Information Devices	1812	1800	+/-10[%]	2000	X7R	100[kHz]-3[GHz]
GR443QR73D222KW01	200V and over/ Information Devices	1812	2200	+/-10[%]	2000	X7R	100[kHz]-3[GHz]
GR443QR73D272KW01	200V and over/ Information Devices	1812	2700	+/-10[%]	2000	X7R	100[kHz]-3[GHz]
GR443QR73D332KW01	200V and over/ Information Devices	1812	3300	+/-10[%]	2000	X7R	100[kHz]-3[GHz]
GR443QR73D392KW01	200V and over/ Information Devices	1812	3900	+/-10[%]	2000	X7R	100[kHz]-3[GHz]
GR443DR73D472KW01	200V and over/ Information Devices	1812	4700	+/-10[%]	2000	X7R	100[kHz]-3[GHz]
GR455DR73D103KW01	200V and over/ Information Devices	2220	10000	+/-10[%]	2000	X7R	100[kHz]-3[GHz]
GRM42A5C3F050DW01	200V and over/ LCD Backlight Inverter Circuit	1808	5	+/-0.5[pF]	3150	C0G	100[MHz]-3[GHz]
GRM42A5C3F100JW01	200V and over/ LCD Backlight Inverter Circuit	1808	10	+/-5[%]	3150	C0G	100[MHz]-3[GHz]
GRM42A5C3F120JW01	200V and over/ LCD Backlight Inverter Circuit	1808	12	+/-5[%]	3150	C0G	100[MHz]-3[GHz]
GRM42A5C3F150JW01	200V and over/ LCD Backlight Inverter Circuit	1808	15	+/-5[%]	3150	C0G	100[MHz]-3[GHz]
GRM42A5C3F180JW01	200V and over/ LCD Backlight Inverter Circuit	1808	18	+/-5[%]	3150	C0G	100[MHz]-3[GHz]
GRM42A5C3F220JW01	200V and over/ LCD Backlight Inverter Circuit	1808	22	+/-5[%]	3150	C0G	100[MHz]-3[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM42A5C3F270JW01	200V and over/ LCD Backlight Inverter Circuit	1808	27	+/-5[%]	3150	C0G	100[MHz]-3[GHz]
GRM42A5C3F330JW01	200V and over/ LCD Backlight Inverter Circuit	1808	33	+/-5[%]	3150	C0G	100[MHz]-3[GHz]
GRM42A5C3F390JW01	200V and over/ LCD Backlight Inverter Circuit	1808	39	+/-5[%]	3150	C0G	100[MHz]-3[GHz]
GRM42A5C3F470JW01	200V and over/ LCD Backlight Inverter Circuit	1808	47	+/-5[%]	3150	C0G	100[MHz]-3[GHz]
GA242QR7E2471MW01	200V and over/ under Japanese Law	1808	470	+/-20[%]	250ac	X7R	500[kHz]-3[GHz]
GA242QR7E2102MW01	200V and over/ under Japanese Law	1808	1000	+/-20[%]	250ac	X7R	100[kHz]-3[GHz]
GA243QR7E2222MW01	200V and over/ under Japanese Law	1812	2200	+/-20[%]	250ac	X7R	100[kHz]-3[GHz]
GA243QR7E2332MW01	200V and over/ under Japanese Law	1812	3300	+/-20[%]	250ac	X7R	100[kHz]-3[GHz]
GA243DR7E2472MW01	200V and over/ under Japanese Law	1812	4700	+/-20[%]	250ac	X7R	100[kHz]-3[GHz]
GA243QR7E2103MW01	200V and over/ under Japanese Law	1812	10000	+/-20[%]	250ac	X7R	100[kHz]-3[GHz]
GA243QR7E2223MW01	200V and over/ under Japanese Law	1812	22000	+/-20[%]	250ac	X7R	100[kHz]-3[GHz]
GA243DR7E2473MW01	200V and over/ under Japanese Law	1812	47000	+/-20[%]	250ac	X7R	100[kHz]-3[GHz]
GA255DR7E2104MW01	200V and over/ under Japanese Law	2220	100000	+/-20[%]	250ac	X7R	100[kHz]-3[GHz]
GRM188R72D221KW07	200V and over/General	0603	220	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRM188R72E221KW07	200V and over/General	0603	220	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GRM188R72D331KW07	200V and over/General	0603	330	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRM188R72E331KW07	200V and over/General	0603	330	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GRM188R72D471KW07	200V and over/General	0603	470	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRM188R72E471KW07	200V and over/General	0603	470	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GRM188R72D681KW07	200V and over/General	0603	680	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRM188R72E681KW07	200V and over/General	0603	680	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GRM188R72D102KW07	200V and over/General	0603	1000	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRM188R72E102KW07	200V and over/General	0603	1000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GRM188R72D152KW07	200V and over/General	0603	1500	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRM188R72E152KW07	200V and over/General	0603	1500	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GRM188R72D222KW07	200V and over/General	0603	2200	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRM188R72E222KW07	200V and over/General	0603	2200	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GRM21A5C2D100JW01	200V and over/General	0805	10	+/-5[%]	200	C0G	100[MHz]-3[GHz]
GRM21A5C2E100JW01	200V and over/General	0805	10	+/-5[%]	250	C0G	100[MHz]-3[GHz]
GRM21A5C2D120JW01	200V and over/General	0805	12	+/-5[%]	200	C0G	100[MHz]-3[GHz]
GRM21A5C2E120JW01	200V and over/General	0805	12	+/-5[%]	250	C0G	100[MHz]-3[GHz]
GRM21A5C2D150JW01	200V and over/General	0805	15	+/-5[%]	200	C0G	100[MHz]-3[GHz]
GRM21A5C2E150JW01	200V and over/General	0805	15	+/-5[%]	250	C0G	100[MHz]-3[GHz]
GRM21A5C2D180JW01	200V and over/General	0805	18	+/-5[%]	200	C0G	100[MHz]-3[GHz]
GRM21A5C2E180JW01	200V and over/General	0805	18	+/-5[%]	250	C0G	100[MHz]-3[GHz]
GRM21A5C2D220JW01	200V and over/General	0805	22	+/-5[%]	200	C0G	100[MHz]-3[GHz]
GRM21A5C2E220JW01	200V and over/General	0805	22	+/-5[%]	250	C0G	100[MHz]-3[GHz]
GRM21A5C2D270JW01	200V and over/General	0805	27	+/-5[%]	200	C0G	100[MHz]-3[GHz]
GRM21A5C2E270JW01	200V and over/General	0805	27	+/-5[%]	250	C0G	100[MHz]-3[GHz]
GRM21A5C2D330JW01	200V and over/General	0805	33	+/-5[%]	200	C0G	100[MHz]-3[GHz]
GRM21A5C2E330JW01	200V and over/General	0805	33	+/-5[%]	250	C0G	100[MHz]-3[GHz]
GRM21A5C2D390JW01	200V and over/General	0805	39	+/-5[%]	200	C0G	100[MHz]-3[GHz]
GRM21A5C2E390JW01	200V and over/General	0805	39	+/-5[%]	250	C0G	100[MHz]-3[GHz]
GRM21A5C2D470JW01	200V and over/General	0805	47	+/-5[%]	200	C0G	100[MHz]-3[GHz]
GRM21A5C2E470JW01	200V and over/General	0805	47	+/-5[%]	250	C0G	100[MHz]-3[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM21A5C2D560JW01	200V and over/General	0805	56	+/-5[%]	200	C0G	100[MHz]-3[GHz]
GRM21A5C2E560JW01	200V and over/General	0805	56	+/-5[%]	250	C0G	100[MHz]-3[GHz]
GRM21A5C2D680JW01	200V and over/General	0805	68	+/-5[%]	200	C0G	100[MHz]-3[GHz]
GRM21A5C2E680JW01	200V and over/General	0805	68	+/-5[%]	250	C0G	100[MHz]-3[GHz]
GRM21A5C2D820JW01	200V and over/General	0805	82	+/-5[%]	200	C0G	100[MHz]-3[GHz]
GRM21A5C2E820JW01	200V and over/General	0805	82	+/-5[%]	250	C0G	100[MHz]-3[GHz]
GRM21A5C2D101JW01	200V and over/General	0805	100	+/-5[%]	200	C0G	100[MHz]-3[GHz]
GRM21A7U2D101JW31	200V and over/General	0805	100	+/-5[%]	200	U2J	100[MHz]-3[GHz]
GRM21A5C2E101JW01	200V and over/General	0805	100	+/-5[%]	250	C0G	100[MHz]-3[GHz]
GRM21A7U2E101JW31	200V and over/General	0805	100	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GRM21A5C2D121JW01	200V and over/General	0805	120	+/-5[%]	200	C0G	100[MHz]-3[GHz]
GRM21A7U2D121JW31	200V and over/General	0805	120	+/-5[%]	200	U2J	100[MHz]-3[GHz]
GRM21A5C2E121JW01	200V and over/General	0805	120	+/-5[%]	250	C0G	100[MHz]-3[GHz]
GRM21A7U2E121JW31	200V and over/General	0805	120	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GRM21A5C2D151JW01	200V and over/General	0805	150	+/-5[%]	200	C0G	100[MHz]-3[GHz]
GRM21A7U2D151JW31	200V and over/General	0805	150	+/-5[%]	200	U2J	100[MHz]-3[GHz]
GRM21A5C2E151JW01	200V and over/General	0805	150	+/-5[%]	250	C0G	100[MHz]-3[GHz]
GRM21A7U2E151JW31	200V and over/General	0805	150	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GRM21A5C2D181JW01	200V and over/General	0805	180	+/-5[%]	200	C0G	100[MHz]-3[GHz]
GRM21A7U2D181JW31	200V and over/General	0805	180	+/-5[%]	200	U2J	100[MHz]-3[GHz]
GRM21A5C2E181JW01	200V and over/General	0805	180	+/-5[%]	250	C0G	100[MHz]-3[GHz]
GRM21A7U2E181JW31	200V and over/General	0805	180	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GRM21A5C2D221JW01	200V and over/General	0805	220	+/-5[%]	200	C0G	100[MHz]-3[GHz]
GRM21A7U2D221JW31	200V and over/General	0805	220	+/-5[%]	200	U2J	100[MHz]-3[GHz]
GRM21A5C2E221JW01	200V and over/General	0805	220	+/-5[%]	250	C0G	100[MHz]-3[GHz]
GRM21A7U2E221JW31	200V and over/General	0805	220	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GRM21A5C2D271JW01	200V and over/General	0805	270	+/-5[%]	200	C0G	100[MHz]-3[GHz]
GRM21A7U2D271JW31	200V and over/General	0805	270	+/-5[%]	200	U2J	100[MHz]-3[GHz]
GRM21A5C2E271JW01	200V and over/General	0805	270	+/-5[%]	250	C0G	100[MHz]-3[GHz]
GRM21A7U2E271JW31	200V and over/General	0805	270	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GRM21A5C2D331JW01	200V and over/General	0805	330	+/-5[%]	200	C0G	100[MHz]-3[GHz]
GRM21A7U2D331JW31	200V and over/General	0805	330	+/-5[%]	200	U2J	100[MHz]-3[GHz]
GRM21A5C2E331JW01	200V and over/General	0805	330	+/-5[%]	250	C0G	100[MHz]-3[GHz]
GRM21A7U2E331JW31	200V and over/General	0805	330	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GRM21A7U2D391JW31	200V and over/General	0805	390	+/-5[%]	200	U2J	100[MHz]-3[GHz]
GRM21A7U2E391JW31	200V and over/General	0805	390	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GRM21A7U2D471JW31	200V and over/General	0805	470	+/-5[%]	200	U2J	100[MHz]-3[GHz]
GRM21A7U2E471JW31	200V and over/General	0805	470	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GRM21A7U2D561JW31	200V and over/General	0805	560	+/-5[%]	200	U2J	100[MHz]-3[GHz]
GRM21A7U2E561JW31	200V and over/General	0805	560	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GRM21A7U2D681JW31	200V and over/General	0805	680	+/-5[%]	200	U2J	100[MHz]-3[GHz]
GRM21A7U2E681JW31	200V and over/General	0805	680	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GRM21A7U2D821JW31	200V and over/General	0805	820	+/-5[%]	200	U2J	100[MHz]-3[GHz]
GRM21A7U2E821JW31	200V and over/General	0805	820	+/-5[%]	250	U2J	100[MHz]-3[GHz]
GRM21A7U2D102JW31	200V and over/General	0805	1000	+/-5[%]	200	U2J	1[MHz]-3[GHz]
GRM21AR72D102KW01	200V and over/General	0805	1000	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRM21A7U2E102JW31	200V and over/General	0805	1000	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRJ21AR72E102KWJ1	200V and over/General	0805	1000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM21AR72E102KW01	200V and over/General	0805	1000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GRM21A7U2D122JW31	200V and over/General	0805	1200	+/-5[%]	200	U2J	1[MHz]-3[GHz]
GRM21A7U2E122JW31	200V and over/General	0805	1200	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRM21A7U2D152JW31	200V and over/General	0805	1500	+/-5[%]	200	U2J	1[MHz]-3[GHz]
GRM21AR72D152KW01	200V and over/General	0805	1500	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRM21A7U2E152JW31	200V and over/General	0805	1500	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRJ21AR72E152KWJ1	200V and over/General	0805	1500	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM21AR72E152KW01	200V and over/General	0805	1500	+/-10[%]	250	X7R	100[kHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM21A7U2D182JW31	200V and over/General	0805	1800	+/-5[%]	200	U2J	1[MHz]-3[GHz]
GRM21A7U2E182JW31	200V and over/General	0805	1800	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRM21A7U2D222JW31	200V and over/General	0805	2200	+/-5[%]	200	U2J	1[MHz]-3[GHz]
GRM21AR72D222KW01	200V and over/General	0805	2200	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRM21A7U2E222JW31	200V and over/General	0805	2200	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRJ21AR72E222KWJ1	200V and over/General	0805	2200	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM21AR72E222KW01	200V and over/General	0805	2200	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GRM21B7U2D272JW32	200V and over/General	0805	2700	+/-5[%]	200	U2J	1[MHz]-3[GHz]
GRM21B7U2E272JW32	200V and over/General	0805	2700	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRM21B7U2D332JW32	200V and over/General	0805	3300	+/-5[%]	200	U2J	1[MHz]-3[GHz]
GRM21AR72D332KW01	200V and over/General	0805	3300	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRM21B7U2E332JW32	200V and over/General	0805	3300	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRJ21AR72E332KWJ1	200V and over/General	0805	3300	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM21AR72E332KW01	200V and over/General	0805	3300	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GRM21B7U2D392JW32	200V and over/General	0805	3900	+/-5[%]	200	U2J	1[MHz]-3[GHz]
GRM21B7U2E392JW32	200V and over/General	0805	3900	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRM21B7U2D472JW32	200V and over/General	0805	4700	+/-5[%]	200	U2J	1[MHz]-3[GHz]
GRM21AR72D472KW01	200V and over/General	0805	4700	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRM21B7U2E472JW32	200V and over/General	0805	4700	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRJ21AR72E472KWJ1	200V and over/General	0805	4700	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM21AR72E472KW01	200V and over/General	0805	4700	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GRM21B7U2D562JW32	200V and over/General	0805	5600	+/-5[%]	200	U2J	1[MHz]-3[GHz]
GRM21B7U2E562JW32	200V and over/General	0805	5600	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRM21AR72D682KW01	200V and over/General	0805	6800	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRJ21AR72E682KWJ1	200V and over/General	0805	6800	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM21AR72E682KW01	200V and over/General	0805	6800	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GRM21BR72D103KW03	200V and over/General	0805	10000	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRJ21BR72E103KWJ3	200V and over/General	0805	10000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM21BR72E103KW03	200V and over/General	0805	10000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GR321AD72E103KW01	200V and over/General	0805	10000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GRM21BR72D153KW03	200V and over/General	0805	15000	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRJ21BR72E153KWJ3	200V and over/General	0805	15000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM21BR72E153KW03	200V and over/General	0805	15000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GR321AD72E153KW01	200V and over/General	0805	15000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GRM21BR72D223KW03	200V and over/General	0805	22000	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRJ21BR72E223KWJ3	200V and over/General	0805	22000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM21BR72E223KW03	200V and over/General	0805	22000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GR321BD72E223KW03	200V and over/General	0805	22000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GRM31A5C2H100JW01	200V and over/General	1206	10	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H100JW31	200V and over/General	1206	10	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31A5C2J100JW01	200V and over/General	1206	10	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J100JW31	200V and over/General	1206	10	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GRM31A5C3A100JW01	200V and over/General	1206	10	+/-5[%]	1000	C0G	100[MHz]-3[GHz]
GRM31A7U3A100JW31	200V and over/General	1206	10	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRM31A7U3D100JW31	200V and over/General	1206	10	+/-5[%]	2000	U2J	100[MHz]-3[GHz]
GRM31A5C2H120JW01	200V and over/General	1206	12	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H120JW31	200V and over/General	1206	12	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31A5C2J120JW01	200V and over/General	1206	12	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J120JW31	200V and over/General	1206	12	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GRM31A5C3A120JW01	200V and over/General	1206	12	+/-5[%]	1000	C0G	100[MHz]-3[GHz]
GRM31A7U3A120JW31	200V and over/General	1206	12	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRM31A7U3D120JW31	200V and over/General	1206	12	+/-5[%]	2000	U2J	100[MHz]-3[GHz]
GRM31A5C2H150JW01	200V and over/General	1206	15	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H150JW31	200V and over/General	1206	15	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31A5C2J150JW01	200V and over/General	1206	15	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J150JW31	200V and over/General	1206	15	+/-5[%]	630	U2J	100[MHz]-3[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM31A5C3A150JW01	200V and over/General	1206	15	+/-5[%]	1000	C0G	100[MHz]-3[GHz]
GRM31A7U3A150JW31	200V and over/General	1206	15	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRM31A7U3D150JW31	200V and over/General	1206	15	+/-5[%]	2000	U2J	100[MHz]-3[GHz]
GRM31A5C2H180JW01	200V and over/General	1206	18	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H180JW31	200V and over/General	1206	18	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31A5C2J180JW01	200V and over/General	1206	18	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J180JW31	200V and over/General	1206	18	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GRM31A5C3A180JW01	200V and over/General	1206	18	+/-5[%]	1000	C0G	100[MHz]-3[GHz]
GRM31A7U3A180JW31	200V and over/General	1206	18	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRM31A7U3D180JW31	200V and over/General	1206	18	+/-5[%]	2000	U2J	100[MHz]-3[GHz]
GRM31A5C2H220JW01	200V and over/General	1206	22	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H220JW31	200V and over/General	1206	22	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31A5C2J220JW01	200V and over/General	1206	22	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J220JW31	200V and over/General	1206	22	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GRM31A5C3A220JW01	200V and over/General	1206	22	+/-5[%]	1000	C0G	100[MHz]-3[GHz]
GRM31A7U3A220JW31	200V and over/General	1206	22	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRM31A7U3D220JW31	200V and over/General	1206	22	+/-5[%]	2000	U2J	100[MHz]-3[GHz]
GRM31A5C2H270JW01	200V and over/General	1206	27	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H270JW31	200V and over/General	1206	27	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31A5C2J270JW01	200V and over/General	1206	27	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J270JW31	200V and over/General	1206	27	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GRM31A5C3A270JW01	200V and over/General	1206	27	+/-5[%]	1000	C0G	100[MHz]-3[GHz]
GRM31A7U3A270JW31	200V and over/General	1206	27	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRM31A7U3D270JW31	200V and over/General	1206	27	+/-5[%]	2000	U2J	100[MHz]-3[GHz]
GRM31A5C2H330JW01	200V and over/General	1206	33	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H330JW31	200V and over/General	1206	33	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31A5C2J330JW01	200V and over/General	1206	33	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J330JW31	200V and over/General	1206	33	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GRM31A5C3A330JW01	200V and over/General	1206	33	+/-5[%]	1000	C0G	100[MHz]-3[GHz]
GRM31A7U3A330JW31	200V and over/General	1206	33	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRM31A7U3D330JW31	200V and over/General	1206	33	+/-5[%]	2000	U2J	100[MHz]-3[GHz]
GRM31A5C2H390JW01	200V and over/General	1206	39	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H390JW31	200V and over/General	1206	39	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31A5C2J390JW01	200V and over/General	1206	39	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J390JW31	200V and over/General	1206	39	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GRM31A5C3A390JW01	200V and over/General	1206	39	+/-5[%]	1000	C0G	100[MHz]-3[GHz]
GRM31A7U3A390JW31	200V and over/General	1206	39	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRM31A7U3D390JW31	200V and over/General	1206	39	+/-5[%]	2000	U2J	100[MHz]-3[GHz]
GRM31A5C2H470JW01	200V and over/General	1206	47	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H470JW31	200V and over/General	1206	47	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31A5C2J470JW01	200V and over/General	1206	47	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J470JW31	200V and over/General	1206	47	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GRM31A5C3A470JW01	200V and over/General	1206	47	+/-5[%]	1000	C0G	100[MHz]-3[GHz]
GRM31A7U3A470JW31	200V and over/General	1206	47	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRM31A7U3D470JW31	200V and over/General	1206	47	+/-5[%]	2000	U2J	100[MHz]-3[GHz]
GRM31A5C2H560JW01	200V and over/General	1206	56	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H560JW31	200V and over/General	1206	56	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31A5C2J560JW01	200V and over/General	1206	56	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J560JW31	200V and over/General	1206	56	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GRM31A5C3A560JW01	200V and over/General	1206	56	+/-5[%]	1000	C0G	100[MHz]-3[GHz]
GRM31A7U3A560JW31	200V and over/General	1206	56	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRM31A7U3D560JW31	200V and over/General	1206	56	+/-5[%]	2000	U2J	100[MHz]-3[GHz]
GRM31A5C2H680JW01	200V and over/General	1206	68	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H680JW31	200V and over/General	1206	68	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31A5C2J680JW01	200V and over/General	1206	68	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J680JW31	200V and over/General	1206	68	+/-5[%]	630	U2J	100[MHz]-3[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM31A5C3A680JW01	200V and over/General	1206	68	+/-5[%]	1000	C0G	100[MHz]-3[GHz]
GRM31A7U3A680JW31	200V and over/General	1206	68	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRM31A7U3D680JW31	200V and over/General	1206	68	+/-5[%]	2000	U2J	100[MHz]-3[GHz]
GRM31A5C2H820JW01	200V and over/General	1206	82	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H820JW31	200V and over/General	1206	82	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31A5C2J820JW01	200V and over/General	1206	82	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J820JW31	200V and over/General	1206	82	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GRM31A5C3A820JW01	200V and over/General	1206	82	+/-5[%]	1000	C0G	100[MHz]-3[GHz]
GRM31A7U3A820JW31	200V and over/General	1206	82	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRM31A5C2H101JW01	200V and over/General	1206	100	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H101JW31	200V and over/General	1206	100	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31A5C2J101JW01	200V and over/General	1206	100	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J101JW31	200V and over/General	1206	100	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GRM31A5C3A101JW01	200V and over/General	1206	100	+/-5[%]	1000	C0G	100[MHz]-3[GHz]
GRM31A7U3A101JW31	200V and over/General	1206	100	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRM31A5C2H121JW01	200V and over/General	1206	120	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H121JW31	200V and over/General	1206	120	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31A5C2J121JW01	200V and over/General	1206	120	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J121JW31	200V and over/General	1206	120	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GRM31A5C3A121JW01	200V and over/General	1206	120	+/-5[%]	1000	C0G	100[MHz]-3[GHz]
GRM31A7U3A121JW31	200V and over/General	1206	120	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRM31A5C2H151JW01	200V and over/General	1206	150	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H151JW31	200V and over/General	1206	150	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31A5C2J151JW01	200V and over/General	1206	150	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J151JW31	200V and over/General	1206	150	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GRM31A5C3A151JW01	200V and over/General	1206	150	+/-5[%]	1000	C0G	100[MHz]-3[GHz]
GRM31A7U3A151JW31	200V and over/General	1206	150	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRM31A5C2H181JW01	200V and over/General	1206	180	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H181JW31	200V and over/General	1206	180	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31A5C2J181JW01	200V and over/General	1206	180	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J181JW31	200V and over/General	1206	180	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GRM31A5C3A181JW01	200V and over/General	1206	180	+/-5[%]	1000	C0G	100[MHz]-3[GHz]
GRM31A7U3A181JW31	200V and over/General	1206	180	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRM31A5C2H221JW01	200V and over/General	1206	220	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H221JW31	200V and over/General	1206	220	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31A5C2J221JW01	200V and over/General	1206	220	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J221JW31	200V and over/General	1206	220	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GRM31A5C3A221JW01	200V and over/General	1206	220	+/-5[%]	1000	C0G	100[MHz]-3[GHz]
GRM31A7U3A221JW31	200V and over/General	1206	220	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRM31A5C2H271JW01	200V and over/General	1206	270	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H271JW31	200V and over/General	1206	270	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31A5C2J271JW01	200V and over/General	1206	270	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J271JW31	200V and over/General	1206	270	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GRM31A7U3A271JW31	200V and over/General	1206	270	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRM31A5C2H331JW01	200V and over/General	1206	330	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H331JW31	200V and over/General	1206	330	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31A5C2J331JW01	200V and over/General	1206	330	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J331JW31	200V and over/General	1206	330	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GRM31A7U3A331JW31	200V and over/General	1206	330	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRM31A5C2H391JW01	200V and over/General	1206	390	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H391JW31	200V and over/General	1206	390	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31A5C2J391JW01	200V and over/General	1206	390	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J391JW31	200V and over/General	1206	390	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GRM31B7U3A391JW31	200V and over/General	1206	390	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRM31A5C2H471JW01	200V and over/General	1206	470	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H471JW31	200V and over/General	1206	470	+/-5[%]	500	U2J	100[MHz]-3[GHz]



Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM31A5C2J471JW01	200V and over/General	1206	470	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J471JW31	200V and over/General	1206	470	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GRM31B7U3A471JW31	200V and over/General	1206	470	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRJ31BR73A471KWJ1	200V and over/General	1206	470	+/-10[%]	1000	X7R	500[kHz]-3[GHz]
GRM31BR73A471KW01	200V and over/General	1206	470	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GRM31A5C2H561JW01	200V and over/General	1206	560	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H561JW31	200V and over/General	1206	560	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31A5C2J561JW01	200V and over/General	1206	560	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J561JW31	200V and over/General	1206	560	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GRM31B7U3A561JW31	200V and over/General	1206	560	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRM31B5C2H681JW01	200V and over/General	1206	680	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H681JW31	200V and over/General	1206	680	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31B5C2J681JW01	200V and over/General	1206	680	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J681JW31	200V and over/General	1206	680	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GRM31B7U3A681JW31	200V and over/General	1206	680	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRJ31BR73A681KWJ1	200V and over/General	1206	680	+/-10[%]	1000	X7R	500[kHz]-3[GHz]
GRM31BR73A681KW01	200V and over/General	1206	680	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GRM31B5C2H821JW01	200V and over/General	1206	820	+/-5[%]	500	C0G	100[MHz]-3[GHz]
GRM31A7U2H821JW31	200V and over/General	1206	820	+/-5[%]	500	U2J	100[MHz]-3[GHz]
GRM31B5C2J821JW01	200V and over/General	1206	820	+/-5[%]	630	C0G	100[MHz]-3[GHz]
GRM31A7U2J821JW31	200V and over/General	1206	820	+/-5[%]	630	U2J	100[MHz]-3[GHz]
GRM31C7U3A821JW32	200V and over/General	1206	820	+/-5[%]	1000	U2J	100[MHz]-3[GHz]
GRM31B5C2H102JW01	200V and over/General	1206	1000	+/-5[%]	500	C0G	1[MHz]-3[GHz]
GRM31A7U2H102JW31	200V and over/General	1206	1000	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM31B5C2J102JW01	200V and over/General	1206	1000	+/-5[%]	630	C0G	1[MHz]-3[GHz]
GRM31A7U2J102JW31	200V and over/General	1206	1000	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRJ31BR72J102KWJ1	200V and over/General	1206	1000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GRM31BR72J102KW01	200V and over/General	1206	1000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GRM31AR72J102KW01	200V and over/General	1206	1000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GRM31C7U3A102JW32	200V and over/General	1206	1000	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GRJ31BR73A102KWJ1	200V and over/General	1206	1000	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GRM31BR73A102KW01	200V and over/General	1206	1000	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GRM31A7U2H122JW31	200V and over/General	1206	1200	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM31A7U2J122JW31	200V and over/General	1206	1200	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRM31A7U2H152JW31	200V and over/General	1206	1500	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM31A7U2J152JW31	200V and over/General	1206	1500	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRJ31BR72J152KWJ1	200V and over/General	1206	1500	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GRM31BR72J152KW01	200V and over/General	1206	1500	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GRM31AR72J152KW01	200V and over/General	1206	1500	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GRJ31BR73A152KWJ1	200V and over/General	1206	1500	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GRM31BR73A152KW01	200V and over/General	1206	1500	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GRM31A7U2H182JW31	200V and over/General	1206	1800	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM31A7U2J182JW31	200V and over/General	1206	1800	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRM31A7U2H222JW31	200V and over/General	1206	2200	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM31A7U2J222JW31	200V and over/General	1206	2200	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRJ31BR72J222KWJ1	200V and over/General	1206	2200	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GRM31BR72J222KW01	200V and over/General	1206	2200	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GRM31AR72J222KW01	200V and over/General	1206	2200	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GRJ31BR73A222KWJ1	200V and over/General	1206	2200	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GRM31BR73A222KW01	200V and over/General	1206	2200	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GRM31A7U2D272JW31	200V and over/General	1206	2700	+/-5[%]	200	U2J	1[MHz]-3[GHz]
GRM31A7U2E272JW31	200V and over/General	1206	2700	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRM31B7U2H272JW31	200V and over/General	1206	2700	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM31B7U2J272JW31	200V and over/General	1206	2700	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRM31A7U2D332JW31	200V and over/General	1206	3300	+/-5[%]	200	U2J	1[MHz]-3[GHz]
GRM31A7U2E332JW31	200V and over/General	1206	3300	+/-5[%]	250	U2J	1[MHz]-3[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM31B7U2H332JW31	200V and over/General	1206	3300	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM31B7U2J332JW31	200V and over/General	1206	3300	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRJ31BR72J332KWJ1	200V and over/General	1206	3300	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GRM31BR72J332KW01	200V and over/General	1206	3300	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GRM31AR72J332KW01	200V and over/General	1206	3300	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GRJ31BR73A332KWJ1	200V and over/General	1206	3300	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GRM31BR73A332KW01	200V and over/General	1206	3300	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GRM31A7U2D392JW31	200V and over/General	1206	3900	+/-5[%]	200	U2J	1[MHz]-3[GHz]
GRM31A7U2E392JW31	200V and over/General	1206	3900	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRM31C7U2H392JW32	200V and over/General	1206	3900	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM31C7U2J392JW32	200V and over/General	1206	3900	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRM31A7U2D472JW31	200V and over/General	1206	4700	+/-5[%]	200	U2J	1[MHz]-3[GHz]
GRM31A7U2E472JW31	200V and over/General	1206	4700	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRM31C7U2H472JW32	200V and over/General	1206	4700	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM31C7U2J472JW32	200V and over/General	1206	4700	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRJ31BR72J472KWJ1	200V and over/General	1206	4700	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GRM31BR72J472KW01	200V and over/General	1206	4700	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GRM31AR72J472KW01	200V and over/General	1206	4700	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GRJ31BR73A472KWJ1	200V and over/General	1206	4700	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GRM31BR73A472KW01	200V and over/General	1206	4700	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GRM31A7U2D562JW31	200V and over/General	1206	5600	+/-5[%]	200	U2J	1[MHz]-3[GHz]
GRM31A7U2E562JW31	200V and over/General	1206	5600	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRM31B7U2D682JW31	200V and over/General	1206	6800	+/-5[%]	200	U2J	1[MHz]-3[GHz]
GRM31B7U2E682JW31	200V and over/General	1206	6800	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRJ31BR72J682KWJ1	200V and over/General	1206	6800	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GRM31BR72J682KW01	200V and over/General	1206	6800	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GRJ31CR73A682KWJ3	200V and over/General	1206	6800	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GRM31CR73A682KW03	200V and over/General	1206	6800	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GRM31B7U2D822JW31	200V and over/General	1206	8200	+/-5[%]	200	U2J	1[MHz]-3[GHz]
GRM31B7U2E822JW31	200V and over/General	1206	8200	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRM31B7U2D103JW31	200V and over/General	1206	10000	+/-5[%]	200	U2J	1[MHz]-3[GHz]
GRM31B7U2E103JW31	200V and over/General	1206	10000	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GR331AD72W103KW01	200V and over/General	1206	10000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GRJ31BR72J103KWJ1	200V and over/General	1206	10000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GRM31BR72J103KW01	200V and over/General	1206	10000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GR331BD72J103KW01	200V and over/General	1206	10000	+/-10[%]	630	X7T	100[kHz]-3[GHz]
GRJ31CR73A103KWJ3	200V and over/General	1206	10000	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GRM31CR73A103KW03	200V and over/General	1206	10000	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GRM31B7U2E123JW31	200V and over/General	1206	12000	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRM31BR72D153KW01	200V and over/General	1206	15000	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRM31C7U2E153JW32	200V and over/General	1206	15000	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRJ31BR72E153KWJ1	200V and over/General	1206	15000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM31BR72E153KW01	200V and over/General	1206	15000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GR331AD72W153KW01	200V and over/General	1206	15000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GRJ31CR72J153KWJ3	200V and over/General	1206	15000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GRM31CR72J153KW03	200V and over/General	1206	15000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GR331CD72J153KW03	200V and over/General	1206	15000	+/-10[%]	630	X7T	100[kHz]-3[GHz]
GRM31C7U2E183JW32	200V and over/General	1206	18000	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRM31BR72D223KW01	200V and over/General	1206	22000	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRM31C7U2E223JW32	200V and over/General	1206	22000	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRJ31BR72E223KWJ1	200V and over/General	1206	22000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM31BR72E223KW01	200V and over/General	1206	22000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GR331BD72W223KW01	200V and over/General	1206	22000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GRJ31CR72J223KWJ3	200V and over/General	1206	22000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GRM31CR72J223KW03	200V and over/General	1206	22000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GRM31CR72D333KW03	200V and over/General	1206	33000	+/-10[%]	200	X7R	100[kHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRJ31CR72E333KWJ3	200V and over/General	1206	33000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM31CR72E333KW03	200V and over/General	1206	33000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GR331AD72E333KW01	200V and over/General	1206	33000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GR331BD72W333KW01	200V and over/General	1206	33000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GRM31CR72D473KW03	200V and over/General	1206	47000	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRJ31CR72E473KWJ3	200V and over/General	1206	47000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM31CR72E473KW03	200V and over/General	1206	47000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GR331BD72E473KW01	200V and over/General	1206	47000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GR331CD72W473KW03	200V and over/General	1206	47000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GRM31BR72D683KW01	200V and over/General	1206	68000	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRJ31BR72E683KWJ1	200V and over/General	1206	68000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM31BR72E683KW01	200V and over/General	1206	68000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GR331CD72E683KW03	200V and over/General	1206	68000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GRM31CR72D104KW03	200V and over/General	1206	100000	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRJ31CR72E104KWJ3	200V and over/General	1206	100000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM31CR72E104KW03	200V and over/General	1206	100000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GRM32A7U3D820JW31	200V and over/General	1210	82	+/-5[%]	2000	U2J	100[MHz]-3[GHz]
GRM32A7U3D101JW31	200V and over/General	1210	100	+/-5[%]	2000	U2J	100[MHz]-3[GHz]
GRM32A7U3D121JW31	200V and over/General	1210	120	+/-5[%]	2000	U2J	100[MHz]-3[GHz]
GRM32A7U3D151JW31	200V and over/General	1210	150	+/-5[%]	2000	U2J	100[MHz]-3[GHz]
GRM32B7U3D181JW31	200V and over/General	1210	180	+/-5[%]	2000	U2J	100[MHz]-3[GHz]
GRM32B7U3D221JW31	200V and over/General	1210	220	+/-5[%]	2000	U2J	100[MHz]-3[GHz]
GRM32A7U2H122JW31	200V and over/General	1210	1200	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM32A7U2J122JW31	200V and over/General	1210	1200	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRM32B7U3A122JW31	200V and over/General	1210	1200	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GRM32A7U2H152JW31	200V and over/General	1210	1500	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM32A7U2J152JW31	200V and over/General	1210	1500	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRM32Q7U3A152JW31	200V and over/General	1210	1500	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GRM32A7U2H182JW31	200V and over/General	1210	1800	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM32A7U2J182JW31	200V and over/General	1210	1800	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRM32D7U3A182JW31	200V and over/General	1210	1800	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GRM32A7U2H222JW31	200V and over/General	1210	2200	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM32A7U2J222JW31	200V and over/General	1210	2200	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRM32D7U3A222JW31	200V and over/General	1210	2200	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GRM32B7U2H562JW31	200V and over/General	1210	5600	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM32B7U2J562JW31	200V and over/General	1210	5600	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRM32Q7U2H682JW31	200V and over/General	1210	6800	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM32Q7U2J682JW31	200V and over/General	1210	6800	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRJ32QR73A682KWJ1	200V and over/General	1210	6800	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GRM32QR73A682KW01	200V and over/General	1210	6800	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GRM32D7U2H822JW31	200V and over/General	1210	8200	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM32D7U2J822JW31	200V and over/General	1210	8200	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRM32D7U2H103JW31	200V and over/General	1210	10000	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM32D7U2J103JW31	200V and over/General	1210	10000	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRJ32QR73A103KWJ1	200V and over/General	1210	10000	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GRM32QR73A103KW01	200V and over/General	1210	10000	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GRJ32DR73A153KWJ1	200V and over/General	1210	15000	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GRM32DR73A153KW01	200V and over/General	1210	15000	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GRJ32QR72J223KWJ1	200V and over/General	1210	22000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GRM32QR72J223KW01	200V and over/General	1210	22000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GR332QD72J223KW01	200V and over/General	1210	22000	+/-10[%]	630	X7T	100[kHz]-3[GHz]
GRJ32DR73A223KWJ1	200V and over/General	1210	22000	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GRM32DR73A223KW01	200V and over/General	1210	22000	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GRM32Q7U2E273JW31	200V and over/General	1210	27000	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRM32D7U2E333JW31	200V and over/General	1210	33000	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRJ32DR72J333KWJ1	200V and over/General	1210	33000	+/-10[%]	630	X7R	100[kHz]-3[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM32DR72J333KW01	200V and over/General	1210	33000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GR332DD72J333KW01	200V and over/General	1210	33000	+/-10[%]	630	X7T	100[kHz]-3[GHz]
GRM32D7U2E393JW31	200V and over/General	1210	39000	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRM32D7U2E473JW31	200V and over/General	1210	47000	+/-5[%]	250	U2J	1[MHz]-3[GHz]
GRJ32DR72J473KWJ1	200V and over/General	1210	47000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GRM32DR72J473KW01	200V and over/General	1210	47000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GR332DD72J473KW01	200V and over/General	1210	47000	+/-10[%]	630	X7T	100[kHz]-3[GHz]
GRM32QR72D683KW01	200V and over/General	1210	68000	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRJ32QR72E683KWJ1	200V and over/General	1210	68000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM32QR72E683KW01	200V and over/General	1210	68000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GR332DD72W683KW01	200V and over/General	1210	68000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GRM32DR72D104KW01	200V and over/General	1210	100000	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRJ32DR72E104KWJ1	200V and over/General	1210	100000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM32DR72E104KW01	200V and over/General	1210	100000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GR332QD72E104KW01	200V and over/General	1210	100000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GR332DD72W104KW01	200V and over/General	1210	100000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GRM32QR72D154KW01	200V and over/General	1210	150000	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRJ32QR72E154KWJ1	200V and over/General	1210	150000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM32QR72E154KW01	200V and over/General	1210	150000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GR332DD72E154KW01	200V and over/General	1210	150000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GRM32DR72D224KW01	200V and over/General	1210	220000	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRJ32DR72E224KWJ1	200V and over/General	1210	220000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM32DR72E224KW01	200V and over/General	1210	220000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GRM42A7U3F270JW31	200V and over/General	1808	27	+/-5[%]	3150	U2J	100[MHz]-3[GHz]
GRM42A7U3F330JW31	200V and over/General	1808	33	+/-5[%]	3150	U2J	100[MHz]-3[GHz]
GRM42A7U3F390JW31	200V and over/General	1808	39	+/-5[%]	3150	U2J	100[MHz]-3[GHz]
GRM42A7U3F470JW31	200V and over/General	1808	47	+/-5[%]	3150	U2J	100[MHz]-3[GHz]
GRM42A7U3F560JW31	200V and over/General	1808	56	+/-5[%]	3150	U2J	100[MHz]-3[GHz]
GRM42A7U3F680JW31	200V and over/General	1808	68	+/-5[%]	3150	U2J	100[MHz]-3[GHz]
GRM42A7U3F820JW31	200V and over/General	1808	82	+/-5[%]	3150	U2J	100[MHz]-3[GHz]
GRM42A7U3F101JW31	200V and over/General	1808	100	+/-5[%]	3150	U2J	100[MHz]-3[GHz]
GRM43Q7U3A272JW31	200V and over/General	1812	2700	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GRM43Q7U3A332JW31	200V and over/General	1812	3300	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GRM43D7U3A392JW31	200V and over/General	1812	3900	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GRM43D7U3A472JW31	200V and over/General	1812	4700	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GRM43Q7U2H123JW31	200V and over/General	1812	12000	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM43Q7U2J123JW31	200V and over/General	1812	12000	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRM43D7U2H153JW31	200V and over/General	1812	15000	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM43D7U2J153JW31	200V and over/General	1812	15000	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRM43D7U2H183JW31	200V and over/General	1812	18000	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM43D7U2J183JW31	200V and over/General	1812	18000	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRM43D7U2H223JW31	200V and over/General	1812	22000	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM43D7U2J223JW31	200V and over/General	1812	22000	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRJ43DR73A333KWJ1	200V and over/General	1812	33000	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GRM43DR73A333KW01	200V and over/General	1812	33000	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GRJ43DR73A473KWJ1	200V and over/General	1812	47000	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GRM43DR73A473KW01	200V and over/General	1812	47000	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GRJ43QR72J683KWJ1	200V and over/General	1812	68000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GRM43QR72J683KW01	200V and over/General	1812	68000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GR343DD72J683KW01	200V and over/General	1812	68000	+/-10[%]	630	X7T	100[kHz]-3[GHz]
GRJ43DR72J104KWJ1	200V and over/General	1812	100000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GRM43DR72J104KW01	200V and over/General	1812	100000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GRM43QR72D154KW01	200V and over/General	1812	150000	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRJ43QR72E154KWJ1	200V and over/General	1812	150000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM43QR72E154KW01	200V and over/General	1812	150000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GR343DD72W154KW01	200V and over/General	1812	150000	+/-10[%]	450	X7T	100[kHz]-3[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GRM43DR72D224KW01	200V and over/General	1812	220000	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRJ43DR72E224KWJ1	200V and over/General	1812	220000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM43DR72E224KW01	200V and over/General	1812	220000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GR343QD72E224KW01	200V and over/General	1812	220000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GRM43DR72D334KW01	200V and over/General	1812	330000	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRJ43DR72E334KWJ1	200V and over/General	1812	330000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM43DR72E334KW01	200V and over/General	1812	330000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GR343DD72E334KW01	200V and over/General	1812	330000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GRM43DR72D474KW01	200V and over/General	1812	470000	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRJ43DR72E474KWJ1	200V and over/General	1812	470000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM43DR72E474KW01	200V and over/General	1812	470000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GRM55Q7U3A562JW31	200V and over/General	2220	5600	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GRM55Q7U3A682JW31	200V and over/General	2220	6800	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GRM55D7U3A822JW31	200V and over/General	2220	8200	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GRM55D7U3A103JW31	200V and over/General	2220	10000	+/-5[%]	1000	U2J	1[MHz]-3[GHz]
GRM55Q7U2H273JW31	200V and over/General	2220	27000	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM55Q7U2J273JW31	200V and over/General	2220	27000	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRM55D7U2H333JW31	200V and over/General	2220	33000	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM55D7U2J333JW31	200V and over/General	2220	33000	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRM55D7U2H393JW31	200V and over/General	2220	39000	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM55D7U2J393JW31	200V and over/General	2220	39000	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRM55D7U2H473JW31	200V and over/General	2220	47000	+/-5[%]	500	U2J	1[MHz]-3[GHz]
GRM55D7U2J473JW31	200V and over/General	2220	47000	+/-5[%]	630	U2J	1[MHz]-3[GHz]
GRJ55DR73A683KWJ1	200V and over/General	2220	68000	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GRM55DR73A683KW01	200V and over/General	2220	68000	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GR355DD72J104KW01	200V and over/General	2220	100000	+/-10[%]	630	X7T	100[kHz]-3[GHz]
GRJ55DR73A104KWJ1	200V and over/General	2220	100000	+/-10[%]	1000	X7R	100[kHz]-3[GHz]
GRM55DR73A104KW01	200V and over/General	2220	100000	+/-10[%]	1000	X7R	100[kHz]-6[GHz]
GRJ55DR72J154KWJ1	200V and over/General	2220	150000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GRM55DR72J154KW01	200V and over/General	2220	150000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GR355DD72J154KW01	200V and over/General	2220	150000	+/-10[%]	630	X7T	100[kHz]-3[GHz]
GR355DD72W224KW01	200V and over/General	2220	220000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GRJ55DR72J224KWJ1	200V and over/General	2220	220000	+/-10[%]	630	X7R	100[kHz]-3[GHz]
GRM55DR72J224KW01	200V and over/General	2220	220000	+/-10[%]	630	X7R	100[kHz]-6[GHz]
GR355XD72J224KW05	200V and over/General	2220	220000	+/-10[%]	630	X7T	100[kHz]-3[GHz]
GR355XD72J274KW05	200V and over/General	2220	270000	+/-10[%]	630	X7T	100[kHz]-3[GHz]
GRM55DR72D334KW01	200V and over/General	2220	330000	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRJ55DR72E334KWJ1	200V and over/General	2220	330000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM55DR72E334KW01	200V and over/General	2220	330000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GR355DD72W334KW01	200V and over/General	2220	330000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GRM55DR72D474KW01	200V and over/General	2220	470000	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRJ55DR72E474KWJ1	200V and over/General	2220	470000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM55DR72E474KW01	200V and over/General	2220	470000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GR355DD72E474KW01	200V and over/General	2220	470000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GR355DD72W474KW01	200V and over/General	2220	470000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GR355XD72W564KW05	200V and over/General	2220	560000	+/-10[%]	450	X7T	100[kHz]-3[GHz]
GRM55DR72D684KW01	200V and over/General	2220	680000	+/-10[%]	200	X7R	100[kHz]-6[GHz]
GRJ55DR72E684KWJ1	200V and over/General	2220	680000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM55DR72E684KW01	200V and over/General	2220	680000	+/-10[%]	250	X7R	100[kHz]-6[GHz]
GR355DD72E684KW01	200V and over/General	2220	680000	+/-10[%]	250	X7T	100[kHz]-3[GHz]
GRM55DR72D105KW01	200V and over/General	2220	1000000	+/-10[%]	200	X7R	100[Hz]-6[GHz]
GRJ55DR72E105KWJ1	200V and over/General	2220	1000000	+/-10[%]	250	X7R	100[kHz]-3[GHz]
GRM55DR72E105KW01	200V and over/General	2220	1000000	+/-10[%]	250	X7R	100[Hz]-6[GHz]
GR355XD72E105KW05	200V and over/General	2220	1000000	+/-10[%]	250	X7T	100[Hz]-3[GHz]
GQM1885C2A1R0BB01	High Frequency	0603	1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A1R0CB01	High Frequency	0603	1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GQM1875C2E1R0BB12	High Frequency	0603	1	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E1R0CB12	High Frequency	0603	1	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A1R1BB01	High Frequency	0603	1.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A1R1CB01	High Frequency	0603	1.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1875C2E1R1BB12	High Frequency	0603	1.1	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E1R1CB12	High Frequency	0603	1.1	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A1R2BB01	High Frequency	0603	1.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A1R2CB01	High Frequency	0603	1.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1875C2E1R2BB12	High Frequency	0603	1.2	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E1R2CB12	High Frequency	0603	1.2	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A1R3BB01	High Frequency	0603	1.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A1R3CB01	High Frequency	0603	1.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1875C2E1R3BB12	High Frequency	0603	1.3	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E1R3CB12	High Frequency	0603	1.3	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A1R5BB01	High Frequency	0603	1.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A1R5CB01	High Frequency	0603	1.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1875C2E1R5BB12	High Frequency	0603	1.5	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E1R5CB12	High Frequency	0603	1.5	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A1R6BB01	High Frequency	0603	1.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A1R6CB01	High Frequency	0603	1.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1875C2E1R6BB12	High Frequency	0603	1.6	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E1R6CB12	High Frequency	0603	1.6	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A1R8BB01	High Frequency	0603	1.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A1R8CB01	High Frequency	0603	1.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1875C2E1R8BB12	High Frequency	0603	1.8	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E1R8CB12	High Frequency	0603	1.8	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A2R0BB01	High Frequency	0603	2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A2R0CB01	High Frequency	0603	2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1875C2E2R0BB12	High Frequency	0603	2	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E2R0CB12	High Frequency	0603	2	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A2R2BB01	High Frequency	0603	2.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A2R2CB01	High Frequency	0603	2.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1875C2E2R2BB12	High Frequency	0603	2.2	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E2R2CB12	High Frequency	0603	2.2	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A2R4BB01	High Frequency	0603	2.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A2R4CB01	High Frequency	0603	2.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1875C2E2R4BB12	High Frequency	0603	2.4	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E2R4CB12	High Frequency	0603	2.4	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A2R7BB01	High Frequency	0603	2.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A2R7CB01	High Frequency	0603	2.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1875C2E2R7BB12	High Frequency	0603	2.7	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E2R7CB12	High Frequency	0603	2.7	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A3R0BB01	High Frequency	0603	3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A3R0CB01	High Frequency	0603	3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1875C2E3R0BB12	High Frequency	0603	3	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E3R0CB12	High Frequency	0603	3	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A3R3BB01	High Frequency	0603	3.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A3R3CB01	High Frequency	0603	3.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1875C2E3R3BB12	High Frequency	0603	3.3	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E3R3CB12	High Frequency	0603	3.3	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A3R6BB01	High Frequency	0603	3.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A3R6CB01	High Frequency	0603	3.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1875C2E3R6BB12	High Frequency	0603	3.6	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E3R6CB12	High Frequency	0603	3.6	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A3R9BB01	High Frequency	0603	3.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A3R9CB01	High Frequency	0603	3.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GQM1875C2E3R9BB12	High Frequency	0603	3.9	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E3R9CB12	High Frequency	0603	3.9	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A4R0BB01	High Frequency	0603	4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A4R0CB01	High Frequency	0603	4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1875C2E4R0BB12	High Frequency	0603	4	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E4R0CB12	High Frequency	0603	4	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A4R3BB01	High Frequency	0603	4.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A4R3CB01	High Frequency	0603	4.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1875C2E4R3BB12	High Frequency	0603	4.3	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E4R3CB12	High Frequency	0603	4.3	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A4R7BB01	High Frequency	0603	4.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A4R7CB01	High Frequency	0603	4.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1875C2E4R7BB12	High Frequency	0603	4.7	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E4R7CB12	High Frequency	0603	4.7	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A5R0BB01	High Frequency	0603	5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A5R0CB01	High Frequency	0603	5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1875C2E5R0BB12	High Frequency	0603	5	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E5R0CB12	High Frequency	0603	5	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A5R1CB01	High Frequency	0603	5.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A5R1DB01	High Frequency	0603	5.1	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1875C2E5R1CB12	High Frequency	0603	5.1	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E5R1DB12	High Frequency	0603	5.1	+/-0.5[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A5R6CB01	High Frequency	0603	5.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A5R6DB01	High Frequency	0603	5.6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1875C2E5R6CB12	High Frequency	0603	5.6	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E5R6DB12	High Frequency	0603	5.6	+/-0.5[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A6R0CB01	High Frequency	0603	6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A6R0DB01	High Frequency	0603	6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1875C2E6R0CB12	High Frequency	0603	6	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E6R0DB12	High Frequency	0603	6	+/-0.5[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A6R2CB01	High Frequency	0603	6.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A6R2DB01	High Frequency	0603	6.2	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1875C2E6R2CB12	High Frequency	0603	6.2	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E6R2DB12	High Frequency	0603	6.2	+/-0.5[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C2A6R8CB01	High Frequency	0603	6.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1885C2A6R8DB01	High Frequency	0603	6.8	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM1875C2E6R8CB12	High Frequency	0603	6.8	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E6R8DB12	High Frequency	0603	6.8	+/-0.5[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H7R0CB01	High Frequency	0603	7	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H7R0DB01	High Frequency	0603	7	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E7R0CB12	High Frequency	0603	7	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E7R0DB12	High Frequency	0603	7	+/-0.5[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H7R5CB01	High Frequency	0603	7.5	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H7R5DB01	High Frequency	0603	7.5	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E7R5CB12	High Frequency	0603	7.5	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E7R5DB12	High Frequency	0603	7.5	+/-0.5[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H8R0CB01	High Frequency	0603	8	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H8R0DB01	High Frequency	0603	8	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E8R0CB12	High Frequency	0603	8	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E8R0DB12	High Frequency	0603	8	+/-0.5[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H8R2CB01	High Frequency	0603	8.2	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H8R2DB01	High Frequency	0603	8.2	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E8R2CB12	High Frequency	0603	8.2	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E8R2DB12	High Frequency	0603	8.2	+/-0.5[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H9R0CB01	High Frequency	0603	9	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H9R0DB01	High Frequency	0603	9	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GQM1875C2E9R0CB12	High Frequency	0603	9	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E9R0DB12	High Frequency	0603	9	+/-0.5[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H9R1CB01	High Frequency	0603	9.1	+/-0.25[pF]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H9R1DB01	High Frequency	0603	9.1	+/-0.5[pF]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E9R1CB12	High Frequency	0603	9.1	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E9R1DB12	High Frequency	0603	9.1	+/-0.5[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H100GB01	High Frequency	0603	10	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H100JB01	High Frequency	0603	10	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E100GB12	High Frequency	0603	10	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E100JB12	High Frequency	0603	10	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H110GB01	High Frequency	0603	11	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H110JB01	High Frequency	0603	11	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E110GB12	High Frequency	0603	11	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E110JB12	High Frequency	0603	11	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H120GB01	High Frequency	0603	12	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H120JB01	High Frequency	0603	12	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E120GB12	High Frequency	0603	12	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E120JB12	High Frequency	0603	12	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H130GB01	High Frequency	0603	13	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H130JB01	High Frequency	0603	13	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E130GB12	High Frequency	0603	13	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E130JB12	High Frequency	0603	13	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H150GB01	High Frequency	0603	15	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H150JB01	High Frequency	0603	15	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E150GB12	High Frequency	0603	15	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E150JB12	High Frequency	0603	15	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H160GB01	High Frequency	0603	16	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H160JB01	High Frequency	0603	16	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E160GB12	High Frequency	0603	16	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E160JB12	High Frequency	0603	16	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H180GB01	High Frequency	0603	18	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H180JB01	High Frequency	0603	18	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E180GB12	High Frequency	0603	18	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E180JB12	High Frequency	0603	18	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H200GB01	High Frequency	0603	20	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H200JB01	High Frequency	0603	20	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E200GB12	High Frequency	0603	20	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E200JB12	High Frequency	0603	20	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H220GB01	High Frequency	0603	22	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H220JB01	High Frequency	0603	22	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E220GB12	High Frequency	0603	22	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E220JB12	High Frequency	0603	22	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H240GB01	High Frequency	0603	24	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H240JB01	High Frequency	0603	24	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E240GB12	High Frequency	0603	24	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E240JB12	High Frequency	0603	24	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H270GB01	High Frequency	0603	27	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H270JB01	High Frequency	0603	27	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E270GB12	High Frequency	0603	27	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E270JB12	High Frequency	0603	27	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H300GB01	High Frequency	0603	30	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H300JB01	High Frequency	0603	30	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E300GB12	High Frequency	0603	30	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E300JB12	High Frequency	0603	30	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H330GB01	High Frequency	0603	33	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H330JB01	High Frequency	0603	33	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]



Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GQM1875C2E330GB12	High Frequency	0603	33	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E330JB12	High Frequency	0603	33	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H360GB01	High Frequency	0603	36	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H360JB01	High Frequency	0603	36	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E360GB12	High Frequency	0603	36	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E360JB12	High Frequency	0603	36	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H390GB01	High Frequency	0603	39	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H390JB01	High Frequency	0603	39	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E390GB12	High Frequency	0603	39	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E390JB12	High Frequency	0603	39	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H430GB01	High Frequency	0603	43	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H430JB01	High Frequency	0603	43	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E430GB12	High Frequency	0603	43	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E430JB12	High Frequency	0603	43	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H470GB01	High Frequency	0603	47	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H470JB01	High Frequency	0603	47	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E470GB12	High Frequency	0603	47	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E470JB12	High Frequency	0603	47	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H510GB01	High Frequency	0603	51	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H510JB01	High Frequency	0603	51	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H560GB01	High Frequency	0603	56	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H560JB01	High Frequency	0603	56	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E560GB12	High Frequency	0603	56	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E560JB12	High Frequency	0603	56	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H620GB01	High Frequency	0603	62	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H620JB01	High Frequency	0603	62	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H680GB01	High Frequency	0603	68	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H680JB01	High Frequency	0603	68	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E680GB12	High Frequency	0603	68	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E680JB12	High Frequency	0603	68	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H750GB01	High Frequency	0603	75	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H750JB01	High Frequency	0603	75	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H820GB01	High Frequency	0603	82	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H820JB01	High Frequency	0603	82	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E820GB12	High Frequency	0603	82	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E820JB12	High Frequency	0603	82	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1885C1H910GB01	High Frequency	0603	91	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H910JB01	High Frequency	0603	91	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H101GB01	High Frequency	0603	100	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1885C1H101JB01	High Frequency	0603	100	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM1875C2E101GB12	High Frequency	0603	100	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM1875C2E101JB12	High Frequency	0603	100	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A1R0BB01	High Frequency	0805	1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A1R0CB01	High Frequency	0805	1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E1R0BB12	High Frequency	0805	1	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E1R0CB12	High Frequency	0805	1	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A1R1BB01	High Frequency	0805	1.1	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A1R1CB01	High Frequency	0805	1.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E1R1BB12	High Frequency	0805	1.1	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E1R1CB12	High Frequency	0805	1.1	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A1R2BB01	High Frequency	0805	1.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A1R2CB01	High Frequency	0805	1.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E1R2BB12	High Frequency	0805	1.2	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E1R2CB12	High Frequency	0805	1.2	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A1R3BB01	High Frequency	0805	1.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A1R3CB01	High Frequency	0805	1.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GQM2195C2E1R3BB12	High Frequency	0805	1.3	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E1R3CB12	High Frequency	0805	1.3	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A1R5BB01	High Frequency	0805	1.5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A1R5CB01	High Frequency	0805	1.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E1R5BB12	High Frequency	0805	1.5	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E1R5CB12	High Frequency	0805	1.5	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A1R6BB01	High Frequency	0805	1.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A1R6CB01	High Frequency	0805	1.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E1R6BB12	High Frequency	0805	1.6	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E1R6CB12	High Frequency	0805	1.6	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A1R8BB01	High Frequency	0805	1.8	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A1R8CB01	High Frequency	0805	1.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E1R8BB12	High Frequency	0805	1.8	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E1R8CB12	High Frequency	0805	1.8	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A2R0BB01	High Frequency	0805	2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A2R0CB01	High Frequency	0805	2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E2R0BB12	High Frequency	0805	2	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E2R0CB12	High Frequency	0805	2	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A2R2BB01	High Frequency	0805	2.2	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A2R2CB01	High Frequency	0805	2.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E2R2BB12	High Frequency	0805	2.2	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E2R2CB12	High Frequency	0805	2.2	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A2R4BB01	High Frequency	0805	2.4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A2R4CB01	High Frequency	0805	2.4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E2R4BB12	High Frequency	0805	2.4	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E2R4CB12	High Frequency	0805	2.4	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A2R7BB01	High Frequency	0805	2.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A2R7CB01	High Frequency	0805	2.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E2R7BB12	High Frequency	0805	2.7	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E2R7CB12	High Frequency	0805	2.7	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A3R0BB01	High Frequency	0805	3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A3R0CB01	High Frequency	0805	3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E3R0BB12	High Frequency	0805	3	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E3R0CB12	High Frequency	0805	3	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A3R3BB01	High Frequency	0805	3.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A3R3CB01	High Frequency	0805	3.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E3R3BB12	High Frequency	0805	3.3	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E3R3CB12	High Frequency	0805	3.3	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A3R6BB01	High Frequency	0805	3.6	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A3R6CB01	High Frequency	0805	3.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E3R6BB12	High Frequency	0805	3.6	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E3R6CB12	High Frequency	0805	3.6	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A3R9BB01	High Frequency	0805	3.9	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A3R9CB01	High Frequency	0805	3.9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E3R9BB12	High Frequency	0805	3.9	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E3R9CB12	High Frequency	0805	3.9	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A4R0BB01	High Frequency	0805	4	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A4R0CB01	High Frequency	0805	4	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E4R0BB12	High Frequency	0805	4	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E4R0CB12	High Frequency	0805	4	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A4R3BB01	High Frequency	0805	4.3	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A4R3CB01	High Frequency	0805	4.3	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E4R3BB12	High Frequency	0805	4.3	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E4R3CB12	High Frequency	0805	4.3	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A4R7BB01	High Frequency	0805	4.7	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A4R7CB01	High Frequency	0805	4.7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GQM2195C2E4R7BB12	High Frequency	0805	4.7	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E4R7CB12	High Frequency	0805	4.7	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A5R0BB01	High Frequency	0805	5	+/-0.1[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A5R0CB01	High Frequency	0805	5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E5R0BB12	High Frequency	0805	5	+/-0.1[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E5R0CB12	High Frequency	0805	5	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A5R1CB01	High Frequency	0805	5.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A5R1DB01	High Frequency	0805	5.1	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E5R1CB12	High Frequency	0805	5.1	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E5R1DB12	High Frequency	0805	5.1	+/-0.5[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A5R6CB01	High Frequency	0805	5.6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A5R6DB01	High Frequency	0805	5.6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E5R6CB12	High Frequency	0805	5.6	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E5R6DB12	High Frequency	0805	5.6	+/-0.5[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A6R0CB01	High Frequency	0805	6	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A6R0DB01	High Frequency	0805	6	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E6R0CB12	High Frequency	0805	6	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E6R0DB12	High Frequency	0805	6	+/-0.5[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A6R2CB01	High Frequency	0805	6.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A6R2DB01	High Frequency	0805	6.2	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E6R2CB12	High Frequency	0805	6.2	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E6R2DB12	High Frequency	0805	6.2	+/-0.5[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A6R8CB01	High Frequency	0805	6.8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A6R8DB01	High Frequency	0805	6.8	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E6R8CB12	High Frequency	0805	6.8	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E6R8DB12	High Frequency	0805	6.8	+/-0.5[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A7R0CB01	High Frequency	0805	7	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A7R0DB01	High Frequency	0805	7	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E7R0CB12	High Frequency	0805	7	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E7R0DB12	High Frequency	0805	7	+/-0.5[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A7R5CB01	High Frequency	0805	7.5	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A7R5DB01	High Frequency	0805	7.5	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E7R5CB12	High Frequency	0805	7.5	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E7R5DB12	High Frequency	0805	7.5	+/-0.5[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A8R0CB01	High Frequency	0805	8	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A8R0DB01	High Frequency	0805	8	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E8R0CB12	High Frequency	0805	8	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E8R0DB12	High Frequency	0805	8	+/-0.5[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A8R2CB01	High Frequency	0805	8.2	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A8R2DB01	High Frequency	0805	8.2	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E8R2CB12	High Frequency	0805	8.2	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E8R2DB12	High Frequency	0805	8.2	+/-0.5[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A9R0CB01	High Frequency	0805	9	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A9R0DB01	High Frequency	0805	9	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E9R0CB12	High Frequency	0805	9	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E9R0DB12	High Frequency	0805	9	+/-0.5[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A9R1CB01	High Frequency	0805	9.1	+/-0.25[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A9R1DB01	High Frequency	0805	9.1	+/-0.5[pF]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E9R1CB12	High Frequency	0805	9.1	+/-0.25[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E9R1DB12	High Frequency	0805	9.1	+/-0.5[pF]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A100GB01	High Frequency	0805	10	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A100JB01	High Frequency	0805	10	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E100GB12	High Frequency	0805	10	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E100JB12	High Frequency	0805	10	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A110GB01	High Frequency	0805	11	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A110JB01	High Frequency	0805	11	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GQM2195C2E110GB12	High Frequency	0805	11	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E110JB12	High Frequency	0805	11	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A120GB01	High Frequency	0805	12	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A120JB01	High Frequency	0805	12	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E120GB12	High Frequency	0805	12	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E120JB12	High Frequency	0805	12	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A130GB01	High Frequency	0805	13	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A130JB01	High Frequency	0805	13	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E130GB12	High Frequency	0805	13	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E130JB12	High Frequency	0805	13	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A150GB01	High Frequency	0805	15	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A150JB01	High Frequency	0805	15	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E150GB12	High Frequency	0805	15	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E150JB12	High Frequency	0805	15	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A160GB01	High Frequency	0805	16	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A160JB01	High Frequency	0805	16	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E160GB12	High Frequency	0805	16	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E160JB12	High Frequency	0805	16	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2A180GB01	High Frequency	0805	18	+/-2[%]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2A180JB01	High Frequency	0805	18	+/-5[%]	100	C0G	100[MHz]-8.5[GHz]
GQM2195C2E180GB12	High Frequency	0805	18	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E180JB12	High Frequency	0805	18	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C1H200GB01	High Frequency	0805	20	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C1H200JB01	High Frequency	0805	20	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C2E200GB12	High Frequency	0805	20	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E200JB12	High Frequency	0805	20	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C1H220GB01	High Frequency	0805	22	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C1H220JB01	High Frequency	0805	22	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C2E220GB12	High Frequency	0805	22	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E220JB12	High Frequency	0805	22	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C1H240GB01	High Frequency	0805	24	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C1H240JB01	High Frequency	0805	24	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C2E240GB12	High Frequency	0805	24	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E240JB12	High Frequency	0805	24	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C1H270GB01	High Frequency	0805	27	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C1H270JB01	High Frequency	0805	27	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C2E270GB12	High Frequency	0805	27	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E270JB12	High Frequency	0805	27	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C1H300GB01	High Frequency	0805	30	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C1H300JB01	High Frequency	0805	30	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C2E300GB12	High Frequency	0805	30	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E300JB12	High Frequency	0805	30	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C1H330GB01	High Frequency	0805	33	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C1H330JB01	High Frequency	0805	33	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C2E330GB12	High Frequency	0805	33	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E330JB12	High Frequency	0805	33	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C1H360GB01	High Frequency	0805	36	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C1H360JB01	High Frequency	0805	36	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C2E360GB12	High Frequency	0805	36	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E360JB12	High Frequency	0805	36	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C1H390GB01	High Frequency	0805	39	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C1H390JB01	High Frequency	0805	39	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C2E390GB12	High Frequency	0805	39	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E390JB12	High Frequency	0805	39	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C1H430GB01	High Frequency	0805	43	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C1H430JB01	High Frequency	0805	43	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GQM2195C2E430GB12	High Frequency	0805	43	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E430JB12	High Frequency	0805	43	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C1H470GB01	High Frequency	0805	47	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C1H470JB01	High Frequency	0805	47	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C2E470GB12	High Frequency	0805	47	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E470JB12	High Frequency	0805	47	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C1H510GB01	High Frequency	0805	51	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C1H510JB01	High Frequency	0805	51	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C2E510GB12	High Frequency	0805	51	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E510JB12	High Frequency	0805	51	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C1H560GB01	High Frequency	0805	56	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C1H560JB01	High Frequency	0805	56	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C2E560GB12	High Frequency	0805	56	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E560JB12	High Frequency	0805	56	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C1H620GB01	High Frequency	0805	62	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C1H620JB01	High Frequency	0805	62	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C2E620GB12	High Frequency	0805	62	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E620JB12	High Frequency	0805	62	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C1H680GB01	High Frequency	0805	68	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C1H680JB01	High Frequency	0805	68	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C2E680GB12	High Frequency	0805	68	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E680JB12	High Frequency	0805	68	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C1H750GB01	High Frequency	0805	75	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C1H750JB01	High Frequency	0805	75	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C2E750GB12	High Frequency	0805	75	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E750JB12	High Frequency	0805	75	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C1H820GB01	High Frequency	0805	82	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C1H820JB01	High Frequency	0805	82	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C2E820GB12	High Frequency	0805	82	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E820JB12	High Frequency	0805	82	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C1H910GB01	High Frequency	0805	91	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C1H910JB01	High Frequency	0805	91	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C2E910GB12	High Frequency	0805	91	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E910JB12	High Frequency	0805	91	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C1H101GB01	High Frequency	0805	100	+/-2[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C1H101JB01	High Frequency	0805	100	+/-5[%]	50	C0G	100[MHz]-8.5[GHz]
GQM2195C2E101GB12	High Frequency	0805	100	+/-2[%]	250	C0G	100[MHz]-8.5[GHz]
GQM2195C2E101JB12	High Frequency	0805	100	+/-5[%]	250	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H1R0BB01	High Frequency	1111	1	+/-0.1[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H1R0CB01	High Frequency	1111	1	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H1R1BB01	High Frequency	1111	1.1	+/-0.1[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H1R1CB01	High Frequency	1111	1.1	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H1R2BB01	High Frequency	1111	1.2	+/-0.1[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H1R2CB01	High Frequency	1111	1.2	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H1R3BB01	High Frequency	1111	1.3	+/-0.1[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H1R3CB01	High Frequency	1111	1.3	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H1R5BB01	High Frequency	1111	1.5	+/-0.1[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H1R5CB01	High Frequency	1111	1.5	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H1R6BB01	High Frequency	1111	1.6	+/-0.1[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H1R6CB01	High Frequency	1111	1.6	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H1R8BB01	High Frequency	1111	1.8	+/-0.1[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H1R8CB01	High Frequency	1111	1.8	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H2R0BB01	High Frequency	1111	2	+/-0.1[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H2R0CB01	High Frequency	1111	2	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H2R2BB01	High Frequency	1111	2.2	+/-0.1[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H2R2CB01	High Frequency	1111	2.2	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GQM22M5C2H2R4BB01	High Frequency	1111	2.4	+/-0.1[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H2R4CB01	High Frequency	1111	2.4	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H2R7BB01	High Frequency	1111	2.7	+/-0.1[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H2R7CB01	High Frequency	1111	2.7	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H3R0BB01	High Frequency	1111	3	+/-0.1[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H3R0CB01	High Frequency	1111	3	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H3R3BB01	High Frequency	1111	3.3	+/-0.1[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H3R3CB01	High Frequency	1111	3.3	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H3R6BB01	High Frequency	1111	3.6	+/-0.1[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H3R6CB01	High Frequency	1111	3.6	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H3R9BB01	High Frequency	1111	3.9	+/-0.1[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H3R9CB01	High Frequency	1111	3.9	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H4R0BB01	High Frequency	1111	4	+/-0.1[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H4R0CB01	High Frequency	1111	4	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H4R3BB01	High Frequency	1111	4.3	+/-0.1[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H4R3CB01	High Frequency	1111	4.3	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H4R7BB01	High Frequency	1111	4.7	+/-0.1[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H4R7CB01	High Frequency	1111	4.7	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H5R0BB01	High Frequency	1111	5	+/-0.1[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H5R0CB01	High Frequency	1111	5	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H5R1CB01	High Frequency	1111	5.1	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H5R1DB01	High Frequency	1111	5.1	+/-0.5[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H5R6CB01	High Frequency	1111	5.6	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H5R6DB01	High Frequency	1111	5.6	+/-0.5[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H6R0CB01	High Frequency	1111	6	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H6R0DB01	High Frequency	1111	6	+/-0.5[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H6R2CB01	High Frequency	1111	6.2	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H6R2DB01	High Frequency	1111	6.2	+/-0.5[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H6R8CB01	High Frequency	1111	6.8	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H6R8DB01	High Frequency	1111	6.8	+/-0.5[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H7R0CB01	High Frequency	1111	7	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H7R0DB01	High Frequency	1111	7	+/-0.5[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H7R5CB01	High Frequency	1111	7.5	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H7R5DB01	High Frequency	1111	7.5	+/-0.5[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H8R0CB01	High Frequency	1111	8	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H8R0DB01	High Frequency	1111	8	+/-0.5[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H8R2CB01	High Frequency	1111	8.2	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H8R2DB01	High Frequency	1111	8.2	+/-0.5[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H9R0CB01	High Frequency	1111	9	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H9R0DB01	High Frequency	1111	9	+/-0.5[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H9R1CB01	High Frequency	1111	9.1	+/-0.25[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H9R1DB01	High Frequency	1111	9.1	+/-0.5[pF]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H100GB01	High Frequency	1111	10	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H100JB01	High Frequency	1111	10	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H110GB01	High Frequency	1111	11	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H110JB01	High Frequency	1111	11	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H120GB01	High Frequency	1111	12	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H120JB01	High Frequency	1111	12	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H130GB01	High Frequency	1111	13	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H130JB01	High Frequency	1111	13	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H150GB01	High Frequency	1111	15	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H150JB01	High Frequency	1111	15	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H160GB01	High Frequency	1111	16	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H160JB01	High Frequency	1111	16	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H180GB01	High Frequency	1111	18	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H180JB01	High Frequency	1111	18	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
GQM22M5C2H200GB01	High Frequency	1111	20	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H200JB01	High Frequency	1111	20	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H220GB01	High Frequency	1111	22	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H220JB01	High Frequency	1111	22	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H240GB01	High Frequency	1111	24	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H240JB01	High Frequency	1111	24	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H270GB01	High Frequency	1111	27	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H270JB01	High Frequency	1111	27	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H300GB01	High Frequency	1111	30	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H300JB01	High Frequency	1111	30	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H330GB01	High Frequency	1111	33	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H330JB01	High Frequency	1111	33	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H360GB01	High Frequency	1111	36	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H360JB01	High Frequency	1111	36	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H390GB01	High Frequency	1111	39	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H390JB01	High Frequency	1111	39	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H430GB01	High Frequency	1111	43	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H430JB01	High Frequency	1111	43	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H470GB01	High Frequency	1111	47	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H470JB01	High Frequency	1111	47	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H510GB01	High Frequency	1111	51	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H510JB01	High Frequency	1111	51	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H560GB01	High Frequency	1111	56	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H560JB01	High Frequency	1111	56	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H620GB01	High Frequency	1111	62	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H620JB01	High Frequency	1111	62	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H680GB01	High Frequency	1111	68	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H680JB01	High Frequency	1111	68	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H750GB01	High Frequency	1111	75	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H750JB01	High Frequency	1111	75	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H820GB01	High Frequency	1111	82	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H820JB01	High Frequency	1111	82	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H910GB01	High Frequency	1111	91	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H910JB01	High Frequency	1111	91	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H101GB01	High Frequency	1111	100	+/-2[%]	500	C0G	100[MHz]-8.5[GHz]
GQM22M5C2H101JB01	High Frequency	1111	100	+/-5[%]	500	C0G	100[MHz]-8.5[GHz]
LLL153C80J104ME01	Low ESL	0402	100000	+/-20[%]	6.3	X6S	100[kHz]-6[GHz]
LLL153R61A104ME01	Low ESL	0402	100000	+/-20[%]	10	X5R	100[kHz]-6[GHz]
LLL153C80J224ME14	Low ESL	0402	220000	+/-20[%]	6.3	X6S	100[kHz]-6[GHz]
LLL153C70G474ME17	Low ESL	0402	470000	+/-20[%]	4	X7S	100[kHz]-6[GHz]
LLL153C70E105ME21	Low ESL	0402	1000000	+/-20[%]	2.5	X7S	100[Hz]-6[GHz]
LLL153C80G105ME21	Low ESL	0402	1000000	+/-20[%]	4	X6S	100[Hz]-6[GHz]
LLL185R71H222MA01	Low ESL	0603	2200	+/-20[%]	50	X7R	100[kHz]-6[GHz]
LLL185R71H472MA01	Low ESL	0603	4700	+/-20[%]	50	X7R	100[kHz]-6[GHz]
LLL185R71C103MA01	Low ESL	0603	10000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
LLL185R71E103MA01	Low ESL	0603	10000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
LLL185R71E103MA11	Low ESL	0603	10000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
LLL185R71C223MA01	Low ESL	0603	22000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
LLL185R71C223MA11	Low ESL	0603	22000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
LLL185R71E223MA01	Low ESL	0603	22000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
LLL185R71C473MA01	Low ESL	0603	47000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
LLL185R71C473MA11	Low ESL	0603	47000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
LLL185R71A104MA01	Low ESL	0603	100000	+/-20[%]	10	X7R	100[kHz]-6[GHz]
LLL185R71A104MA11	Low ESL	0603	100000	+/-20[%]	10	X7R	100[kHz]-6[GHz]
LLL185C70G224MA11	Low ESL	0603	220000	+/-20[%]	4	X7S	100[kHz]-6[GHz]
LLL185R71A224MA01	Low ESL	0603	220000	+/-20[%]	10	X7R	100[kHz]-6[GHz]

Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
LLL185C70G474MA01	Low ESL	0603	470000	+/-20[%]	4	X7S	100[kHz]-6[GHz]
LLR185C70G105ME01	Low ESL	0603	1000000	+/-20[%]	4	X7S	100[Hz]-6[GHz]
LLR185C70G105ME03	Low ESL	0603	1000000	+/-20[%]	4	X7S	100[Hz]-6[GHz]
LLR185C70G105ME05	Low ESL	0603	1000000	+/-20[%]	4	X7S	100[Hz]-6[GHz]
LLR185C70G105ME07	Low ESL	0603	1000000	+/-20[%]	4	X7S	100[Hz]-6[GHz]
LLL185C70J105ME14	Low ESL	0603	1000000	+/-20[%]	6.3	X7S	100[Hz]-6[GHz]
LLL185C70G225ME01	Low ESL	0603	2200000	+/-20[%]	4	X7S	100[Hz]-6[GHz]
LLL215R71E103MA11	Low ESL	0805	10000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
LLL215R71H103MA11	Low ESL	0805	10000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
LLL216R71H103MA01	Low ESL	0805	10000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
LLL215R71C223MA11	Low ESL	0805	22000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
LLL215R71E223MA11	Low ESL	0805	22000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
LLL216R71E223MA01	Low ESL	0805	22000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
LLL216R71H223MA01	Low ESL	0805	22000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
LLL215R71C473MA11	Low ESL	0805	47000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
LLL216R71C473MA01	Low ESL	0805	47000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
LLL216R71E473MA01	Low ESL	0805	47000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
LLL216R71C104MA01	Low ESL	0805	100000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
LLL215R71C104MA11	Low ESL	0805	100000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
LLL216R71E104MA01	Low ESL	0805	100000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
LLL215R71A224MA11	Low ESL	0805	220000	+/-20[%]	10	X7R	100[kHz]-6[GHz]
LLL216R71A224MA01	Low ESL	0805	220000	+/-20[%]	10	X7R	100[kHz]-6[GHz]
LLL219R71C224MA01	Low ESL	0805	220000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
LLL215R70J474MA11	Low ESL	0805	470000	+/-20[%]	6.3	X7R	100[kHz]-6[GHz]
LLL219R71A474MA01	Low ESL	0805	470000	+/-20[%]	10	X7R	100[kHz]-6[GHz]
LLL215C70G105MA11	Low ESL	0805	1000000	+/-20[%]	4	X7S	100[Hz]-6[GHz]
LLL219R70J105MA01	Low ESL	0805	1000000	+/-20[%]	6.3	X7R	100[Hz]-6[GHz]
LLL219R71A105MA01	Low ESL	0805	1000000	+/-20[%]	10	X7R	100[Hz]-6[GHz]
LLL219C70G225MA01	Low ESL	0805	2200000	+/-20[%]	4	X7S	100[Hz]-6[GHz]
LLL315R71H103MA11	Low ESL	1206	10000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
LLL317R71H103MA01	Low ESL	1206	10000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
LLL315R71C223MA11	Low ESL	1206	22000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
LLL315R71E223MA11	Low ESL	1206	22000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
LLL317R71E223MA01	Low ESL	1206	22000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
LLL315R71H223MA11	Low ESL	1206	22000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
LLL317R71H223MA01	Low ESL	1206	22000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
LLL315R71C473MA11	Low ESL	1206	47000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
LLL315R71E473MA11	Low ESL	1206	47000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
LLL317R71E473MA01	Low ESL	1206	47000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
LLL317R71H473MA01	Low ESL	1206	47000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
LLL315R71C104MA11	Low ESL	1206	100000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
LLL317R71C104MA01	Low ESL	1206	100000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
LLL315R71E104MA11	Low ESL	1206	100000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
LLL317R71E104MA01	Low ESL	1206	100000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
LLL31MR71H104MA01	Low ESL	1206	100000	+/-20[%]	50	X7R	100[kHz]-6[GHz]
LLL315R71C224MA11	Low ESL	1206	220000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
LLL317R71C224MA01	Low ESL	1206	220000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
LLL31MR71E224MA01	Low ESL	1206	220000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
LLL315R71A474MA11	Low ESL	1206	470000	+/-20[%]	10	X7R	100[kHz]-6[GHz]
LLL317R71A474MA01	Low ESL	1206	470000	+/-20[%]	10	X7R	100[kHz]-6[GHz]
LLL317R71C474MA01	Low ESL	1206	470000	+/-20[%]	16	X7R	100[kHz]-6[GHz]
LLL31MR71E474MA01	Low ESL	1206	470000	+/-20[%]	25	X7R	100[kHz]-6[GHz]
LLL317R71A105MA01	Low ESL	1206	1000000	+/-20[%]	10	X7R	100[Hz]-6[GHz]
LLL31MR71C105MA01	Low ESL	1206	1000000	+/-20[%]	16	X7R	100[Hz]-6[GHz]
LLL317R70J225MA01	Low ESL	1206	2200000	+/-20[%]	6.3	X7R	100[Hz]-6[GHz]
LLL31MR71A225MA01	Low ESL	1206	2200000	+/-20[%]	10	X7R	100[Hz]-6[GHz]



Part Number	Type	Size Code [inch]	Capacitance [pF]	Tolerance	Rated Voltage [V]	Temp. Characteristics (EIA)	Frequency Range
LLL31MR70J475MA01	Low ESL	1206	4700000	+/-20[%]	6.3	X7R	100[Hz]-6[GHz]
LLL31MR60J106ME01	Low ESL	1206	10000000	+/-20[%]	6.3	X5R	100[Hz]-6[GHz]
LLL1U4R60G435ME22	Low ESL	02404	4300000	+/-20[%]	4	X5R	100[Hz]-6[GHz]
GA342QR7GF101KW01	Safety Standard Certified	1808	100	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA342QR7GD101KW01	Safety Standard Certified	1808	100	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA342QR7GF151KW01	Safety Standard Certified	1808	150	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA342QR7GD151KW01	Safety Standard Certified	1808	150	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA342DR7GF221KW02	Safety Standard Certified	1808	220	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA342QR7GD221KW01	Safety Standard Certified	1808	220	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA342DR7GF331KW02	Safety Standard Certified	1808	330	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA342QR7GD331KW01	Safety Standard Certified	1808	330	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA342QR7GF471KW01	Safety Standard Certified	1808	470	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA342QR7GD471KW01	Safety Standard Certified	1808	470	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA342QR7GF681KW01	Safety Standard Certified	1808	680	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA342QR7GD681KW01	Safety Standard Certified	1808	680	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA342DR7GF102KW02	Safety Standard Certified	1808	1000	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA342QR7GD102KW01	Safety Standard Certified	1808	1000	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA342QR7GD152KW01	Safety Standard Certified	1808	1500	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA343QR7GD182KW01	Safety Standard Certified	1812	1800	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA343QR7GD222KW01	Safety Standard Certified	1812	2200	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA343DR7GD472KW01	Safety Standard Certified	1812	4700	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA352QR7GF101KW31	Safety Standard Certified	2211	100	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA352QR7GF151KW31	Safety Standard Certified	2211	150	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA352QR7GF221KW31	Safety Standard Certified	2211	220	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA352QR7GF331KW31	Safety Standard Certified	2211	330	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA352QR7GF471KW01	Safety Standard Certified	2211	470	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA352QR7GF681KW01	Safety Standard Certified	2211	680	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA352QR7GF102KW01	Safety Standard Certified	2211	1000	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA352QR7GF152KW01	Safety Standard Certified	2211	1500	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA355DR7GC101KY02	Safety Standard Certified	2220	100	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA355DR7GC151KY02	Safety Standard Certified	2220	150	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA355DR7GC221KY02	Safety Standard Certified	2220	220	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA355DR7GC331KY02	Safety Standard Certified	2220	330	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA355QR7GF182KW01	Safety Standard Certified	2220	1800	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA355QR7GF222KW01	Safety Standard Certified	2220	2200	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA355QR7GF332KW01	Safety Standard Certified	2220	3300	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA355DR7GF472KW01	Safety Standard Certified	2220	4700	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA355QR7GB103KW01	Safety Standard Certified	2220	10000	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA355QR7GB153KW01	Safety Standard Certified	2220	15000	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA355DR7GB223KW01	Safety Standard Certified	2220	22000	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA355ER7GB333KW01	Safety Standard Certified	2220	33000	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA355ER7GB473KW01	Safety Standard Certified	2220	47000	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]
GA355XR7GB563KW06	Safety Standard Certified	2220	56000	+/-10[%]	250ac	X7R	100[kHz]-3[GHz]

Part Number	Type	Size Code [inch/mm]	Inductance [nH]	Tolerance	Rated Current [mA]	Frequency Range
LQP02TN0N2B02	Film	01005/0402	0.2	+/-0.1[nH]	320	50[MHz]-10[GHz]
LQP02TN0N2C02	Film	01005/0402	0.2	+/-0.2[nH]	320	50[MHz]-10[GHz]
LQP02TN0N3B02	Film	01005/0402	0.3	+/-0.1[nH]	320	50[MHz]-10[GHz]
LQP02TN0N3C02	Film	01005/0402	0.3	+/-0.2[nH]	320	50[MHz]-10[GHz]
LQP02TN0N4B02	Film	01005/0402	0.4	+/-0.1[nH]	320	50[MHz]-10[GHz]
LQP02TN0N4C02	Film	01005/0402	0.4	+/-0.2[nH]	320	50[MHz]-10[GHz]
LQP02TN0N4S02	Film	01005/0402	0.4	+/-0.3[nH]	320	50[MHz]-10[GHz]
LQP02TQ0N4B02	Film	01005/0402	0.4	+/-0.1[nH]	990	50[MHz]-10[GHz]
LQP02TQ0N4C02	Film	01005/0402	0.4	+/-0.2[nH]	990	50[MHz]-10[GHz]
LQP02TN0N5B02	Film	01005/0402	0.5	+/-0.1[nH]	320	50[MHz]-10[GHz]
LQP02TN0N5C02	Film	01005/0402	0.5	+/-0.2[nH]	320	50[MHz]-10[GHz]
LQP02TN0N5S02	Film	01005/0402	0.5	+/-0.3[nH]	320	50[MHz]-10[GHz]
LQP02TQ0N5B02	Film	01005/0402	0.5	+/-0.1[nH]	730	50[MHz]-10[GHz]
LQP02TQ0N5C02	Film	01005/0402	0.5	+/-0.2[nH]	730	50[MHz]-10[GHz]
LQP02TN0N6B02	Film	01005/0402	0.6	+/-0.1[nH]	320	50[MHz]-10[GHz]
LQP02TN0N6C02	Film	01005/0402	0.6	+/-0.2[nH]	320	50[MHz]-10[GHz]
LQP02TN0N6S02	Film	01005/0402	0.6	+/-0.3[nH]	320	50[MHz]-10[GHz]
LQP02TQ0N6B02	Film	01005/0402	0.6	+/-0.1[nH]	730	50[MHz]-10[GHz]
LQP02TQ0N6C02	Film	01005/0402	0.6	+/-0.2[nH]	730	50[MHz]-10[GHz]
LQP02TN0N7B02	Film	01005/0402	0.7	+/-0.1[nH]	320	50[MHz]-10[GHz]
LQP02TN0N7C02	Film	01005/0402	0.7	+/-0.2[nH]	320	50[MHz]-10[GHz]
LQP02TN0N7S02	Film	01005/0402	0.7	+/-0.3[nH]	320	50[MHz]-10[GHz]
LQP02TQ0N7B02	Film	01005/0402	0.7	+/-0.1[nH]	630	50[MHz]-10[GHz]
LQP02TQ0N7C02	Film	01005/0402	0.7	+/-0.2[nH]	630	50[MHz]-10[GHz]
LQP02TN0N8B02	Film	01005/0402	0.8	+/-0.1[nH]	320	50[MHz]-10[GHz]
LQP02TN0N8C02	Film	01005/0402	0.8	+/-0.2[nH]	320	50[MHz]-10[GHz]
LQP02TN0N8S02	Film	01005/0402	0.8	+/-0.3[nH]	320	50[MHz]-10[GHz]
LQP02TQ0N8B02	Film	01005/0402	0.8	+/-0.1[nH]	630	50[MHz]-10[GHz]
LQP02TQ0N8C02	Film	01005/0402	0.8	+/-0.2[nH]	630	50[MHz]-10[GHz]
LQP02TN0N9B02	Film	01005/0402	0.9	+/-0.1[nH]	320	50[MHz]-10[GHz]
LQP02TN0N9C02	Film	01005/0402	0.9	+/-0.2[nH]	320	50[MHz]-10[GHz]
LQP02TN0N9S02	Film	01005/0402	0.9	+/-0.3[nH]	320	50[MHz]-10[GHz]
LQP02TQ0N9B02	Film	01005/0402	0.9	+/-0.1[nH]	580	50[MHz]-10[GHz]
LQP02TQ0N9C02	Film	01005/0402	0.9	+/-0.2[nH]	580	50[MHz]-10[GHz]
LQP02TN1N0B02	Film	01005/0402	1	+/-0.1[nH]	220	50[MHz]-10[GHz]
LQP02TN1N0C02	Film	01005/0402	1	+/-0.2[nH]	220	50[MHz]-10[GHz]
LQP02TN1N0S02	Film	01005/0402	1	+/-0.3[nH]	220	50[MHz]-10[GHz]
LQP02TQ1N0B02	Film	01005/0402	1	+/-0.1[nH]	580	50[MHz]-10[GHz]
LQP02TQ1N0C02	Film	01005/0402	1	+/-0.2[nH]	580	50[MHz]-10[GHz]
LQP02TN1N1B02	Film	01005/0402	1.1	+/-0.1[nH]	220	50[MHz]-10[GHz]
LQP02TN1N1C02	Film	01005/0402	1.1	+/-0.2[nH]	220	50[MHz]-10[GHz]
LQP02TN1N1S02	Film	01005/0402	1.1	+/-0.3[nH]	220	50[MHz]-10[GHz]
LQP02TQ1N1B02	Film	01005/0402	1.1	+/-0.1[nH]	570	50[MHz]-10[GHz]
LQP02TQ1N1C02	Film	01005/0402	1.1	+/-0.2[nH]	570	50[MHz]-10[GHz]
LQP02TN1N2B02	Film	01005/0402	1.2	+/-0.1[nH]	220	50[MHz]-10[GHz]
LQP02TN1N2C02	Film	01005/0402	1.2	+/-0.2[nH]	220	50[MHz]-10[GHz]
LQP02TN1N2S02	Film	01005/0402	1.2	+/-0.3[nH]	220	50[MHz]-10[GHz]
LQP02TQ1N2B02	Film	01005/0402	1.2	+/-0.1[nH]	550	50[MHz]-10[GHz]
LQP02TQ1N2C02	Film	01005/0402	1.2	+/-0.2[nH]	550	50[MHz]-10[GHz]
LQP02TN1N3B02	Film	01005/0402	1.3	+/-0.1[nH]	220	50[MHz]-10[GHz]
LQP02TN1N3C02	Film	01005/0402	1.3	+/-0.2[nH]	220	50[MHz]-10[GHz]
LQP02TN1N3S02	Film	01005/0402	1.3	+/-0.3[nH]	220	50[MHz]-10[GHz]
LQP02TQ1N3B02	Film	01005/0402	1.3	+/-0.1[nH]	400	50[MHz]-10[GHz]
LQP02TQ1N3C02	Film	01005/0402	1.3	+/-0.2[nH]	400	50[MHz]-10[GHz]
LQP02TN1N4B02	Film	01005/0402	1.4	+/-0.1[nH]	220	50[MHz]-10[GHz]
LQP02TN1N4C02	Film	01005/0402	1.4	+/-0.2[nH]	220	50[MHz]-10[GHz]

Part Number	Type	Size Code [inch/mm]	Inductance [nH]	Tolerance	Rated Current [mA]	Frequency Range
LQP02TN1N4S02	Film	01005/0402	1.4	+/-0.3[nH]	220	50[MHz]-10[GHz]
LQP02TQ1N4B02	Film	01005/0402	1.4	+/-0.1[nH]	400	50[MHz]-10[GHz]
LQP02TQ1N4C02	Film	01005/0402	1.4	+/-0.2[nH]	400	50[MHz]-10[GHz]
LQP02TN1N5B02	Film	01005/0402	1.5	+/-0.1[nH]	220	50[MHz]-10[GHz]
LQP02TN1N5C02	Film	01005/0402	1.5	+/-0.2[nH]	220	50[MHz]-10[GHz]
LQP02TN1N5S02	Film	01005/0402	1.5	+/-0.3[nH]	220	50[MHz]-10[GHz]
LQP02TQ1N5B02	Film	01005/0402	1.5	+/-0.1[nH]	400	50[MHz]-10[GHz]
LQP02TQ1N5C02	Film	01005/0402	1.5	+/-0.2[nH]	400	50[MHz]-10[GHz]
LQP02TN1N6B02	Film	01005/0402	1.6	+/-0.1[nH]	220	50[MHz]-10[GHz]
LQP02TN1N6C02	Film	01005/0402	1.6	+/-0.2[nH]	220	50[MHz]-10[GHz]
LQP02TN1N6S02	Film	01005/0402	1.6	+/-0.3[nH]	220	50[MHz]-10[GHz]
LQP02TQ1N6B02	Film	01005/0402	1.6	+/-0.1[nH]	390	50[MHz]-10[GHz]
LQP02TQ1N6C02	Film	01005/0402	1.6	+/-0.2[nH]	390	50[MHz]-10[GHz]
LQP02TN1N7B02	Film	01005/0402	1.7	+/-0.1[nH]	200	50[MHz]-10[GHz]
LQP02TN1N7C02	Film	01005/0402	1.7	+/-0.2[nH]	200	50[MHz]-10[GHz]
LQP02TN1N7S02	Film	01005/0402	1.7	+/-0.3[nH]	200	50[MHz]-10[GHz]
LQP02TQ1N7B02	Film	01005/0402	1.7	+/-0.1[nH]	380	50[MHz]-10[GHz]
LQP02TQ1N7C02	Film	01005/0402	1.7	+/-0.2[nH]	380	50[MHz]-10[GHz]
LQP02TN1N8B02	Film	01005/0402	1.8	+/-0.1[nH]	200	50[MHz]-10[GHz]
LQP02TN1N8C02	Film	01005/0402	1.8	+/-0.2[nH]	200	50[MHz]-10[GHz]
LQP02TN1N8S02	Film	01005/0402	1.8	+/-0.3[nH]	200	50[MHz]-10[GHz]
LQP02TQ1N8B02	Film	01005/0402	1.8	+/-0.1[nH]	380	50[MHz]-10[GHz]
LQP02TQ1N8C02	Film	01005/0402	1.8	+/-0.2[nH]	380	50[MHz]-10[GHz]
LQP02TN1N9B02	Film	01005/0402	1.9	+/-0.1[nH]	200	50[MHz]-10[GHz]
LQP02TN1N9C02	Film	01005/0402	1.9	+/-0.2[nH]	200	50[MHz]-10[GHz]
LQP02TN1N9S02	Film	01005/0402	1.9	+/-0.3[nH]	200	50[MHz]-10[GHz]
LQP02TQ1N9B02	Film	01005/0402	1.9	+/-0.1[nH]	380	50[MHz]-10[GHz]
LQP02TQ1N9C02	Film	01005/0402	1.9	+/-0.2[nH]	380	50[MHz]-10[GHz]
LQP02TN2N0B02	Film	01005/0402	2	+/-0.1[nH]	200	50[MHz]-10[GHz]
LQP02TN2N0C02	Film	01005/0402	2	+/-0.2[nH]	200	50[MHz]-10[GHz]
LQP02TN2N0S02	Film	01005/0402	2	+/-0.3[nH]	200	50[MHz]-10[GHz]
LQP02TQ2N0B02	Film	01005/0402	2	+/-0.1[nH]	380	50[MHz]-10[GHz]
LQP02TQ2N0C02	Film	01005/0402	2	+/-0.2[nH]	380	50[MHz]-10[GHz]
LQP02TN2N1B02	Film	01005/0402	2.1	+/-0.1[nH]	200	50[MHz]-10[GHz]
LQP02TN2N1C02	Film	01005/0402	2.1	+/-0.2[nH]	200	50[MHz]-10[GHz]
LQP02TN2N1S02	Film	01005/0402	2.1	+/-0.3[nH]	200	50[MHz]-10[GHz]
LQP02TQ2N1B02	Film	01005/0402	2.1	+/-0.1[nH]	380	50[MHz]-10[GHz]
LQP02TQ2N1C02	Film	01005/0402	2.1	+/-0.2[nH]	380	50[MHz]-10[GHz]
LQP02TN2N2B02	Film	01005/0402	2.2	+/-0.1[nH]	200	50[MHz]-10[GHz]
LQP02TN2N2C02	Film	01005/0402	2.2	+/-0.2[nH]	200	50[MHz]-10[GHz]
LQP02TN2N2S02	Film	01005/0402	2.2	+/-0.3[nH]	200	50[MHz]-10[GHz]
LQP02TQ2N2B02	Film	01005/0402	2.2	+/-0.1[nH]	380	50[MHz]-10[GHz]
LQP02TQ2N2C02	Film	01005/0402	2.2	+/-0.2[nH]	380	50[MHz]-10[GHz]
LQP02TN2N3B02	Film	01005/0402	2.3	+/-0.1[nH]	200	50[MHz]-10[GHz]
LQP02TN2N3C02	Film	01005/0402	2.3	+/-0.2[nH]	200	50[MHz]-10[GHz]
LQP02TN2N3S02	Film	01005/0402	2.3	+/-0.3[nH]	200	50[MHz]-10[GHz]
LQP02TQ2N3B02	Film	01005/0402	2.3	+/-0.1[nH]	370	50[MHz]-10[GHz]
LQP02TQ2N3C02	Film	01005/0402	2.3	+/-0.2[nH]	370	50[MHz]-10[GHz]
LQP02TN2N4B02	Film	01005/0402	2.4	+/-0.1[nH]	200	50[MHz]-10[GHz]
LQP02TN2N4C02	Film	01005/0402	2.4	+/-0.2[nH]	200	50[MHz]-10[GHz]
LQP02TN2N4S02	Film	01005/0402	2.4	+/-0.3[nH]	200	50[MHz]-10[GHz]
LQP02TQ2N4B02	Film	01005/0402	2.4	+/-0.1[nH]	370	50[MHz]-10[GHz]
LQP02TQ2N4C02	Film	01005/0402	2.4	+/-0.2[nH]	370	50[MHz]-10[GHz]
LQP02TN2N5B02	Film	01005/0402	2.5	+/-0.1[nH]	200	50[MHz]-10[GHz]
LQP02TN2N5C02	Film	01005/0402	2.5	+/-0.2[nH]	200	50[MHz]-10[GHz]
LQP02TN2N5S02	Film	01005/0402	2.5	+/-0.3[nH]	200	50[MHz]-10[GHz]

Part Number	Type	Size Code [inch/mm]	Inductance [nH]	Tolerance	Rated Current [mA]	Frequency Range
LQP02TQ2N5B02	Film	01005/0402	2.5	+/-0.1[nH]	370	50[MHz]-10[GHz]
LQP02TQ2N5C02	Film	01005/0402	2.5	+/-0.2[nH]	370	50[MHz]-10[GHz]
LQP02TN2N6B02	Film	01005/0402	2.6	+/-0.1[nH]	200	50[MHz]-10[GHz]
LQP02TN2N6C02	Film	01005/0402	2.6	+/-0.2[nH]	200	50[MHz]-10[GHz]
LQP02TN2N6S02	Film	01005/0402	2.6	+/-0.3[nH]	200	50[MHz]-10[GHz]
LQP02TQ2N6B02	Film	01005/0402	2.6	+/-0.1[nH]	370	50[MHz]-10[GHz]
LQP02TQ2N6C02	Film	01005/0402	2.6	+/-0.2[nH]	370	50[MHz]-10[GHz]
LQP02TN2N7B02	Film	01005/0402	2.7	+/-0.1[nH]	200	50[MHz]-10[GHz]
LQP02TN2N7C02	Film	01005/0402	2.7	+/-0.2[nH]	200	50[MHz]-10[GHz]
LQP02TN2N7S02	Film	01005/0402	2.7	+/-0.3[nH]	200	50[MHz]-10[GHz]
LQP02TQ2N7B02	Film	01005/0402	2.7	+/-0.1[nH]	370	50[MHz]-10[GHz]
LQP02TQ2N7C02	Film	01005/0402	2.7	+/-0.2[nH]	370	50[MHz]-10[GHz]
LQP02TN2N8B02	Film	01005/0402	2.8	+/-0.1[nH]	200	50[MHz]-10[GHz]
LQP02TN2N8C02	Film	01005/0402	2.8	+/-0.2[nH]	200	50[MHz]-10[GHz]
LQP02TN2N8S02	Film	01005/0402	2.8	+/-0.3[nH]	200	50[MHz]-10[GHz]
LQP02TQ2N8B02	Film	01005/0402	2.8	+/-0.1[nH]	360	50[MHz]-10[GHz]
LQP02TQ2N8C02	Film	01005/0402	2.8	+/-0.2[nH]	360	50[MHz]-10[GHz]
LQP02TN2N9B02	Film	01005/0402	2.9	+/-0.1[nH]	200	50[MHz]-10[GHz]
LQP02TN2N9C02	Film	01005/0402	2.9	+/-0.2[nH]	200	50[MHz]-10[GHz]
LQP02TN2N9S02	Film	01005/0402	2.9	+/-0.3[nH]	200	50[MHz]-10[GHz]
LQP02TQ2N9B02	Film	01005/0402	2.9	+/-0.1[nH]	360	50[MHz]-10[GHz]
LQP02TQ2N9C02	Film	01005/0402	2.9	+/-0.2[nH]	360	50[MHz]-10[GHz]
LQP02TN3N0B02	Film	01005/0402	3	+/-0.1[nH]	200	50[MHz]-10[GHz]
LQP02TN3N0C02	Film	01005/0402	3	+/-0.2[nH]	200	50[MHz]-10[GHz]
LQP02TN3N0S02	Film	01005/0402	3	+/-0.3[nH]	200	50[MHz]-10[GHz]
LQP02TQ3N0B02	Film	01005/0402	3	+/-0.1[nH]	360	50[MHz]-10[GHz]
LQP02TQ3N0C02	Film	01005/0402	3	+/-0.2[nH]	360	50[MHz]-10[GHz]
LQP02TN3N1B02	Film	01005/0402	3.1	+/-0.1[nH]	180	50[MHz]-10[GHz]
LQP02TN3N1C02	Film	01005/0402	3.1	+/-0.2[nH]	180	50[MHz]-10[GHz]
LQP02TN3N1S02	Film	01005/0402	3.1	+/-0.3[nH]	180	50[MHz]-10[GHz]
LQP02TQ3N1B02	Film	01005/0402	3.1	+/-0.1[nH]	290	50[MHz]-10[GHz]
LQP02TQ3N1C02	Film	01005/0402	3.1	+/-0.2[nH]	290	50[MHz]-10[GHz]
LQP02TN3N2B02	Film	01005/0402	3.2	+/-0.1[nH]	180	50[MHz]-10[GHz]
LQP02TN3N2C02	Film	01005/0402	3.2	+/-0.2[nH]	180	50[MHz]-10[GHz]
LQP02TN3N2S02	Film	01005/0402	3.2	+/-0.3[nH]	180	50[MHz]-10[GHz]
LQP02TQ3N2B02	Film	01005/0402	3.2	+/-0.1[nH]	290	50[MHz]-10[GHz]
LQP02TQ3N2C02	Film	01005/0402	3.2	+/-0.2[nH]	290	50[MHz]-10[GHz]
LQP02TN3N3B02	Film	01005/0402	3.3	+/-0.1[nH]	180	50[MHz]-10[GHz]
LQP02TN3N3C02	Film	01005/0402	3.3	+/-0.2[nH]	180	50[MHz]-10[GHz]
LQP02TN3N3S02	Film	01005/0402	3.3	+/-0.3[nH]	180	50[MHz]-10[GHz]
LQP02TQ3N3B02	Film	01005/0402	3.3	+/-0.1[nH]	290	50[MHz]-10[GHz]
LQP02TQ3N3C02	Film	01005/0402	3.3	+/-0.2[nH]	290	50[MHz]-10[GHz]
LQP02TN3N4B02	Film	01005/0402	3.4	+/-0.1[nH]	180	50[MHz]-10[GHz]
LQP02TN3N4C02	Film	01005/0402	3.4	+/-0.2[nH]	180	50[MHz]-10[GHz]
LQP02TN3N4S02	Film	01005/0402	3.4	+/-0.3[nH]	180	50[MHz]-10[GHz]
LQP02TQ3N4B02	Film	01005/0402	3.4	+/-0.1[nH]	270	50[MHz]-10[GHz]
LQP02TQ3N4C02	Film	01005/0402	3.4	+/-0.2[nH]	270	50[MHz]-10[GHz]
LQP02TN3N5B02	Film	01005/0402	3.5	+/-0.1[nH]	180	50[MHz]-10[GHz]
LQP02TN3N5C02	Film	01005/0402	3.5	+/-0.2[nH]	180	50[MHz]-10[GHz]
LQP02TN3N5S02	Film	01005/0402	3.5	+/-0.3[nH]	180	50[MHz]-10[GHz]
LQP02TQ3N5B02	Film	01005/0402	3.5	+/-0.1[nH]	270	50[MHz]-10[GHz]
LQP02TQ3N5C02	Film	01005/0402	3.5	+/-0.2[nH]	270	50[MHz]-10[GHz]
LQP02TN3N6B02	Film	01005/0402	3.6	+/-0.1[nH]	180	50[MHz]-10[GHz]
LQP02TN3N6C02	Film	01005/0402	3.6	+/-0.2[nH]	180	50[MHz]-10[GHz]
LQP02TN3N6S02	Film	01005/0402	3.6	+/-0.3[nH]	180	50[MHz]-10[GHz]
LQP02TQ3N6B02	Film	01005/0402	3.6	+/-0.1[nH]	280	50[MHz]-10[GHz]

Part Number	Type	Size Code [inch/mm]	Inductance [nH]	Tolerance	Rated Current [mA]	Frequency Range
LQP02TQ3N6C02	Film	01005/0402	3.6	+/-0.2[nH]	280	50[MHz]-10[GHz]
LQP02TN3N7B02	Film	01005/0402	3.7	+/-0.1[nH]	180	50[MHz]-10[GHz]
LQP02TN3N7C02	Film	01005/0402	3.7	+/-0.2[nH]	180	50[MHz]-10[GHz]
LQP02TN3N7S02	Film	01005/0402	3.7	+/-0.3[nH]	180	50[MHz]-10[GHz]
LQP02TQ3N7B02	Film	01005/0402	3.7	+/-0.1[nH]	270	50[MHz]-10[GHz]
LQP02TQ3N7C02	Film	01005/0402	3.7	+/-0.2[nH]	270	50[MHz]-10[GHz]
LQP02TN3N8B02	Film	01005/0402	3.8	+/-0.1[nH]	180	50[MHz]-10[GHz]
LQP02TN3N8C02	Film	01005/0402	3.8	+/-0.2[nH]	180	50[MHz]-10[GHz]
LQP02TN3N8S02	Film	01005/0402	3.8	+/-0.3[nH]	180	50[MHz]-10[GHz]
LQP02TQ3N8B02	Film	01005/0402	3.8	+/-0.1[nH]	270	50[MHz]-10[GHz]
LQP02TQ3N8C02	Film	01005/0402	3.8	+/-0.2[nH]	270	50[MHz]-10[GHz]
LQP02TN3N9B02	Film	01005/0402	3.9	+/-0.1[nH]	180	50[MHz]-10[GHz]
LQP02TN3N9C02	Film	01005/0402	3.9	+/-0.2[nH]	180	50[MHz]-10[GHz]
LQP02TN3N9S02	Film	01005/0402	3.9	+/-0.3[nH]	180	50[MHz]-10[GHz]
LQP02TQ3N9B02	Film	01005/0402	3.9	+/-0.1[nH]	270	50[MHz]-10[GHz]
LQP02TQ3N9C02	Film	01005/0402	3.9	+/-0.2[nH]	270	50[MHz]-10[GHz]
LQP02TN4N0B02	Film	01005/0402	4	+/-0.1[nH]	180	50[MHz]-10[GHz]
LQP02TN4N0C02	Film	01005/0402	4	+/-0.2[nH]	180	50[MHz]-10[GHz]
LQP02TN4N0S02	Film	01005/0402	4	+/-0.3[nH]	180	50[MHz]-10[GHz]
LQP02TQ4N0H02	Film	01005/0402	4	+/-3[%]	270	50[MHz]-10[GHz]
LQP02TQ4N0J02	Film	01005/0402	4	+/-5[%]	270	50[MHz]-10[GHz]
LQP02TN4N1B02	Film	01005/0402	4.1	+/-0.1[nH]	180	50[MHz]-10[GHz]
LQP02TN4N1C02	Film	01005/0402	4.1	+/-0.2[nH]	180	50[MHz]-10[GHz]
LQP02TN4N1S02	Film	01005/0402	4.1	+/-0.3[nH]	180	50[MHz]-10[GHz]
LQP02TQ4N1H02	Film	01005/0402	4.1	+/-3[%]	270	50[MHz]-10[GHz]
LQP02TQ4N1J02	Film	01005/0402	4.1	+/-5[%]	270	50[MHz]-10[GHz]
LQP02TN4N2B02	Film	01005/0402	4.2	+/-0.1[nH]	180	50[MHz]-10[GHz]
LQP02TN4N2C02	Film	01005/0402	4.2	+/-0.2[nH]	180	50[MHz]-10[GHz]
LQP02TN4N2S02	Film	01005/0402	4.2	+/-0.3[nH]	180	50[MHz]-10[GHz]
LQP02TQ4N2H02	Film	01005/0402	4.2	+/-3[%]	270	50[MHz]-10[GHz]
LQP02TQ4N2J02	Film	01005/0402	4.2	+/-5[%]	270	50[MHz]-10[GHz]
LQP02TN4N3H02	Film	01005/0402	4.3	+/-3[%]	180	50[MHz]-10[GHz]
LQP02TN4N3J02	Film	01005/0402	4.3	+/-5[%]	180	50[MHz]-10[GHz]
LQP02TN4N3S02	Film	01005/0402	4.3	+/-0.3[nH]	180	50[MHz]-10[GHz]
LQP02TQ4N3H02	Film	01005/0402	4.3	+/-3[%]	270	50[MHz]-10[GHz]
LQP02TQ4N3J02	Film	01005/0402	4.3	+/-5[%]	270	50[MHz]-10[GHz]
LQP02TN4N7H02	Film	01005/0402	4.7	+/-3[%]	160	50[MHz]-10[GHz]
LQP02TN4N7J02	Film	01005/0402	4.7	+/-5[%]	160	50[MHz]-10[GHz]
LQP02TN4N7S02	Film	01005/0402	4.7	+/-0.3[nH]	160	50[MHz]-10[GHz]
LQP02TQ4N7H02	Film	01005/0402	4.7	+/-3[%]	270	50[MHz]-10[GHz]
LQP02TQ4N7J02	Film	01005/0402	4.7	+/-5[%]	270	50[MHz]-10[GHz]
LQP02TN5N1H02	Film	01005/0402	5.1	+/-3[%]	160	50[MHz]-10[GHz]
LQP02TN5N1J02	Film	01005/0402	5.1	+/-5[%]	160	50[MHz]-10[GHz]
LQP02TN5N1S02	Film	01005/0402	5.1	+/-0.3[nH]	160	50[MHz]-10[GHz]
LQP02TQ5N1H02	Film	01005/0402	5.1	+/-3[%]	250	50[MHz]-10[GHz]
LQP02TQ5N1J02	Film	01005/0402	5.1	+/-5[%]	250	50[MHz]-10[GHz]
LQP02TN5N6H02	Film	01005/0402	5.6	+/-3[%]	140	50[MHz]-10[GHz]
LQP02TN5N6J02	Film	01005/0402	5.6	+/-5[%]	140	50[MHz]-10[GHz]
LQP02TN5N6S02	Film	01005/0402	5.6	+/-0.3[nH]	140	50[MHz]-10[GHz]
LQP02TQ5N6H02	Film	01005/0402	5.6	+/-3[%]	230	50[MHz]-10[GHz]
LQP02TQ5N6J02	Film	01005/0402	5.6	+/-5[%]	230	50[MHz]-10[GHz]
LQP02TN6N2H02	Film	01005/0402	6.2	+/-3[%]	140	50[MHz]-10[GHz]
LQP02TN6N2J02	Film	01005/0402	6.2	+/-5[%]	140	50[MHz]-10[GHz]
LQP02TQ6N2H02	Film	01005/0402	6.2	+/-3[%]	220	50[MHz]-10[GHz]
LQP02TQ6N2J02	Film	01005/0402	6.2	+/-5[%]	220	50[MHz]-10[GHz]
LQP02TN6N8H02	Film	01005/0402	6.8	+/-3[%]	140	50[MHz]-10[GHz]

Part Number	Type	Size Code [inch/mm]	Inductance [nH]	Tolerance	Rated Current [mA]	Frequency Range
LQP02TN6N8J02	Film	01005/0402	6.8	+/-5[%]	140	50[MHz]-10[GHz]
LQP02TQ6N8H02	Film	01005/0402	6.8	+/-3[%]	210	50[MHz]-10[GHz]
LQP02TQ6N8J02	Film	01005/0402	6.8	+/-5[%]	210	50[MHz]-10[GHz]
LQP02TN7N5H02	Film	01005/0402	7.5	+/-3[%]	140	50[MHz]-10[GHz]
LQP02TN7N5J02	Film	01005/0402	7.5	+/-5[%]	140	50[MHz]-10[GHz]
LQP02TQ7N5H02	Film	01005/0402	7.5	+/-3[%]	200	50[MHz]-10[GHz]
LQP02TQ7N5J02	Film	01005/0402	7.5	+/-5[%]	200	50[MHz]-10[GHz]
LQP02TN8N2H02	Film	01005/0402	8.2	+/-3[%]	140	50[MHz]-10[GHz]
LQP02TN8N2J02	Film	01005/0402	8.2	+/-5[%]	140	50[MHz]-10[GHz]
LQP02TQ8N2H02	Film	01005/0402	8.2	+/-3[%]	190	50[MHz]-10[GHz]
LQP02TQ8N2J02	Film	01005/0402	8.2	+/-5[%]	190	50[MHz]-10[GHz]
LQP02TN9N1H02	Film	01005/0402	9.1	+/-3[%]	140	50[MHz]-10[GHz]
LQP02TN9N1J02	Film	01005/0402	9.1	+/-5[%]	140	50[MHz]-10[GHz]
LQP02TQ9N1H02	Film	01005/0402	9.1	+/-3[%]	170	50[MHz]-10[GHz]
LQP02TQ9N1J02	Film	01005/0402	9.1	+/-5[%]	170	50[MHz]-10[GHz]
LQP02TN10NH02	Film	01005/0402	10	+/-3[%]	140	50[MHz]-10[GHz]
LQP02TN10NJ02	Film	01005/0402	10	+/-5[%]	140	50[MHz]-10[GHz]
LQP02TQ10NH02	Film	01005/0402	10	+/-3[%]	170	50[MHz]-10[GHz]
LQP02TQ10NJ02	Film	01005/0402	10	+/-5[%]	170	50[MHz]-10[GHz]
LQP02TN11NH02	Film	01005/0402	11	+/-3[%]	140	50[MHz]-10[GHz]
LQP02TN11NJ02	Film	01005/0402	11	+/-5[%]	140	50[MHz]-10[GHz]
LQP02TN12NH02	Film	01005/0402	12	+/-3[%]	140	50[MHz]-10[GHz]
LQP02TN12NJ02	Film	01005/0402	12	+/-5[%]	140	50[MHz]-10[GHz]
LQP02TN13NH02	Film	01005/0402	13	+/-3[%]	140	50[MHz]-10[GHz]
LQP02TN13NJ02	Film	01005/0402	13	+/-5[%]	140	50[MHz]-10[GHz]
LQP02TN15NH02	Film	01005/0402	15	+/-3[%]	140	50[MHz]-10[GHz]
LQP02TN15NJ02	Film	01005/0402	15	+/-5[%]	140	50[MHz]-10[GHz]
LQP02TN16NH02	Film	01005/0402	16	+/-3[%]	140	50[MHz]-10[GHz]
LQP02TN16NJ02	Film	01005/0402	16	+/-5[%]	140	50[MHz]-10[GHz]
LQP02TN18NH02	Film	01005/0402	18	+/-3[%]	140	50[MHz]-10[GHz]
LQP02TN18NJ02	Film	01005/0402	18	+/-5[%]	140	50[MHz]-10[GHz]
LQP02TN20NH02	Film	01005/0402	20	+/-3[%]	120	50[MHz]-10[GHz]
LQP02TN20NJ02	Film	01005/0402	20	+/-5[%]	120	50[MHz]-10[GHz]
LQP02TN22NH02	Film	01005/0402	22	+/-3[%]	120	50[MHz]-10[GHz]
LQP02TN22NJ02	Film	01005/0402	22	+/-5[%]	120	50[MHz]-10[GHz]
LQP02TN27NH02	Film	01005/0402	27	+/-3[%]	120	50[MHz]-10[GHz]
LQP02TN27NJ02	Film	01005/0402	27	+/-5[%]	120	50[MHz]-10[GHz]
LQP02TN33NH02	Film	01005/0402	33	+/-3[%]	90	50[MHz]-10[GHz]
LQP02TN33NJ02	Film	01005/0402	33	+/-5[%]	90	50[MHz]-10[GHz]
LQP02TN39NH02	Film	01005/0402	39	+/-3[%]	90	50[MHz]-10[GHz]
LQP02TN39NJ02	Film	01005/0402	39	+/-5[%]	90	50[MHz]-10[GHz]
LQP03TG0N1B02	Film	0201/0603	0.1	+/-0.1[nH]	850	50[MHz]-10[GHz]
LQP03TG0N2B02	Film	0201/0603	0.2	+/-0.1[nH]	850	50[MHz]-10[GHz]
LQP03TG0N2C02	Film	0201/0603	0.2	+/-0.2[nH]	850	50[MHz]-10[GHz]
LQP03TG0N3B02	Film	0201/0603	0.3	+/-0.1[nH]	850	50[MHz]-10[GHz]
LQP03TG0N3C02	Film	0201/0603	0.3	+/-0.2[nH]	850	50[MHz]-10[GHz]
LQP03TG0N4B02	Film	0201/0603	0.4	+/-0.1[nH]	850	50[MHz]-10[GHz]
LQP03TG0N4C02	Film	0201/0603	0.4	+/-0.2[nH]	850	50[MHz]-10[GHz]
LQP03TG0N5B02	Film	0201/0603	0.5	+/-0.1[nH]	850	50[MHz]-10[GHz]
LQP03TG0N5C02	Film	0201/0603	0.5	+/-0.2[nH]	850	50[MHz]-10[GHz]
LQP03TG0N6B02	Film	0201/0603	0.6	+/-0.1[nH]	850	50[MHz]-10[GHz]
LQP03TG0N6C02	Film	0201/0603	0.6	+/-0.2[nH]	850	50[MHz]-10[GHz]
LQP03TN0N6B02	Film	0201/0603	0.6	+/-0.1[nH]	850	50[MHz]-10[GHz]
LQP03TN0N6C02	Film	0201/0603	0.6	+/-0.2[nH]	850	50[MHz]-10[GHz]
LQP03TG0N7B02	Film	0201/0603	0.7	+/-0.1[nH]	750	50[MHz]-10[GHz]
LQP03TG0N7C02	Film	0201/0603	0.7	+/-0.2[nH]	750	50[MHz]-10[GHz]

Part Number	Type	Size Code [inch/mm]	Inductance [nH]	Tolerance	Rated Current [mA]	Frequency Range
LQP03TN0N7B02	Film	0201/0603	0.7	+/-0.1[nH]	800	50[MHz]-10[GHz]
LQP03TN0N7C02	Film	0201/0603	0.7	+/-0.2[nH]	800	50[MHz]-10[GHz]
LQP03TG0N8B02	Film	0201/0603	0.8	+/-0.1[nH]	750	50[MHz]-10[GHz]
LQP03TG0N8C02	Film	0201/0603	0.8	+/-0.2[nH]	750	50[MHz]-10[GHz]
LQP03TN0N8B02	Film	0201/0603	0.8	+/-0.1[nH]	800	50[MHz]-10[GHz]
LQP03TN0N8C02	Film	0201/0603	0.8	+/-0.2[nH]	800	50[MHz]-10[GHz]
LQP03TG0N9B02	Film	0201/0603	0.9	+/-0.1[nH]	700	50[MHz]-10[GHz]
LQP03TG0N9C02	Film	0201/0603	0.9	+/-0.2[nH]	700	50[MHz]-10[GHz]
LQP03TN0N9B02	Film	0201/0603	0.9	+/-0.1[nH]	750	50[MHz]-10[GHz]
LQP03TN0N9C02	Film	0201/0603	0.9	+/-0.2[nH]	750	50[MHz]-10[GHz]
LQP03TG1N0B02	Film	0201/0603	1	+/-0.1[nH]	600	50[MHz]-10[GHz]
LQP03TG1N0C02	Film	0201/0603	1	+/-0.2[nH]	600	50[MHz]-10[GHz]
LQP03TN1N0B02	Film	0201/0603	1	+/-0.1[nH]	750	50[MHz]-10[GHz]
LQP03TN1N0C02	Film	0201/0603	1	+/-0.2[nH]	750	50[MHz]-10[GHz]
LQP03TG1N1B02	Film	0201/0603	1.1	+/-0.1[nH]	600	50[MHz]-10[GHz]
LQP03TG1N1C02	Film	0201/0603	1.1	+/-0.2[nH]	600	50[MHz]-10[GHz]
LQP03TN1N1B02	Film	0201/0603	1.1	+/-0.1[nH]	750	50[MHz]-10[GHz]
LQP03TN1N1C02	Film	0201/0603	1.1	+/-0.2[nH]	750	50[MHz]-10[GHz]
LQP03TG1N2B02	Film	0201/0603	1.2	+/-0.1[nH]	600	50[MHz]-10[GHz]
LQP03TG1N2C02	Film	0201/0603	1.2	+/-0.2[nH]	600	50[MHz]-10[GHz]
LQP03TN1N2B02	Film	0201/0603	1.2	+/-0.1[nH]	750	50[MHz]-10[GHz]
LQP03TN1N2C02	Film	0201/0603	1.2	+/-0.2[nH]	750	50[MHz]-10[GHz]
LQP03TG1N3B02	Film	0201/0603	1.3	+/-0.1[nH]	600	50[MHz]-10[GHz]
LQP03TG1N3C02	Film	0201/0603	1.3	+/-0.2[nH]	600	50[MHz]-10[GHz]
LQP03TN1N3B02	Film	0201/0603	1.3	+/-0.1[nH]	600	50[MHz]-10[GHz]
LQP03TN1N3C02	Film	0201/0603	1.3	+/-0.2[nH]	600	50[MHz]-10[GHz]
LQP03TG1N4B02	Film	0201/0603	1.4	+/-0.1[nH]	600	50[MHz]-10[GHz]
LQP03TG1N4C02	Film	0201/0603	1.4	+/-0.2[nH]	600	50[MHz]-10[GHz]
LQP03TN1N4B02	Film	0201/0603	1.4	+/-0.1[nH]	600	50[MHz]-10[GHz]
LQP03TN1N4C02	Film	0201/0603	1.4	+/-0.2[nH]	600	50[MHz]-10[GHz]
LQP03TG1N5B02	Film	0201/0603	1.5	+/-0.1[nH]	600	50[MHz]-10[GHz]
LQP03TG1N5C02	Film	0201/0603	1.5	+/-0.2[nH]	600	50[MHz]-10[GHz]
LQP03TN1N5B02	Film	0201/0603	1.5	+/-0.1[nH]	600	50[MHz]-10[GHz]
LQP03TN1N5C02	Film	0201/0603	1.5	+/-0.2[nH]	600	50[MHz]-10[GHz]
LQP03TG1N6B02	Film	0201/0603	1.6	+/-0.1[nH]	600	50[MHz]-10[GHz]
LQP03TG1N6C02	Film	0201/0603	1.6	+/-0.2[nH]	600	50[MHz]-10[GHz]
LQP03TN1N6B02	Film	0201/0603	1.6	+/-0.1[nH]	600	50[MHz]-10[GHz]
LQP03TN1N6C02	Film	0201/0603	1.6	+/-0.2[nH]	600	50[MHz]-10[GHz]
LQP03TG1N7B02	Film	0201/0603	1.7	+/-0.1[nH]	500	50[MHz]-10[GHz]
LQP03TG1N7C02	Film	0201/0603	1.7	+/-0.2[nH]	500	50[MHz]-10[GHz]
LQP03TN1N7B02	Film	0201/0603	1.7	+/-0.1[nH]	600	50[MHz]-10[GHz]
LQP03TN1N7C02	Film	0201/0603	1.7	+/-0.2[nH]	600	50[MHz]-10[GHz]
LQP03TG1N8B02	Film	0201/0603	1.8	+/-0.1[nH]	500	50[MHz]-10[GHz]
LQP03TG1N8C02	Film	0201/0603	1.8	+/-0.2[nH]	500	50[MHz]-10[GHz]
LQP03TN1N8B02	Film	0201/0603	1.8	+/-0.1[nH]	600	50[MHz]-10[GHz]
LQP03TN1N8C02	Film	0201/0603	1.8	+/-0.2[nH]	600	50[MHz]-10[GHz]
LQP03TG1N9B02	Film	0201/0603	1.9	+/-0.1[nH]	450	50[MHz]-10[GHz]
LQP03TG1N9C02	Film	0201/0603	1.9	+/-0.2[nH]	450	50[MHz]-10[GHz]
LQP03TN1N9B02	Film	0201/0603	1.9	+/-0.1[nH]	600	50[MHz]-10[GHz]
LQP03TN1N9C02	Film	0201/0603	1.9	+/-0.2[nH]	600	50[MHz]-10[GHz]
LQP03TG2N0B02	Film	0201/0603	2	+/-0.1[nH]	450	50[MHz]-10[GHz]
LQP03TG2N0C02	Film	0201/0603	2	+/-0.2[nH]	450	50[MHz]-10[GHz]
LQP03TN2N0B02	Film	0201/0603	2	+/-0.1[nH]	600	50[MHz]-10[GHz]
LQP03TN2N0C02	Film	0201/0603	2	+/-0.2[nH]	600	50[MHz]-10[GHz]
LQP03TG2N1B02	Film	0201/0603	2.1	+/-0.1[nH]	450	50[MHz]-10[GHz]
LQP03TG2N1C02	Film	0201/0603	2.1	+/-0.2[nH]	450	50[MHz]-10[GHz]

Part Number	Type	Size Code [inch/mm]	Inductance [nH]	Tolerance	Rated Current [mA]	Frequency Range
LQP03TN2N1B02	Film	0201/0603	2.1	+/-0.1[nH]	600	50[MHz]-10[GHz]
LQP03TN2N1C02	Film	0201/0603	2.1	+/-0.2[nH]	600	50[MHz]-10[GHz]
LQP03TG2N2B02	Film	0201/0603	2.2	+/-0.1[nH]	450	50[MHz]-10[GHz]
LQP03TG2N2C02	Film	0201/0603	2.2	+/-0.2[nH]	450	50[MHz]-10[GHz]
LQP03TN2N2B02	Film	0201/0603	2.2	+/-0.1[nH]	600	50[MHz]-10[GHz]
LQP03TN2N2C02	Film	0201/0603	2.2	+/-0.2[nH]	600	50[MHz]-10[GHz]
LQP03PN2N2C02	Film	0201/0603	2.2	+/-0.2[nH]	1400	50[MHz]-10[GHz]
LQP03TG2N3B02	Film	0201/0603	2.3	+/-0.1[nH]	450	50[MHz]-10[GHz]
LQP03TG2N3C02	Film	0201/0603	2.3	+/-0.2[nH]	450	50[MHz]-10[GHz]
LQP03TN2N3B02	Film	0201/0603	2.3	+/-0.1[nH]	500	50[MHz]-10[GHz]
LQP03TN2N3C02	Film	0201/0603	2.3	+/-0.2[nH]	500	50[MHz]-10[GHz]
LQP03TG2N4B02	Film	0201/0603	2.4	+/-0.1[nH]	450	50[MHz]-10[GHz]
LQP03TG2N4C02	Film	0201/0603	2.4	+/-0.2[nH]	450	50[MHz]-10[GHz]
LQP03TN2N4B02	Film	0201/0603	2.4	+/-0.1[nH]	500	50[MHz]-10[GHz]
LQP03TN2N4C02	Film	0201/0603	2.4	+/-0.2[nH]	500	50[MHz]-10[GHz]
LQP03TG2N5B02	Film	0201/0603	2.5	+/-0.1[nH]	450	50[MHz]-10[GHz]
LQP03TG2N5C02	Film	0201/0603	2.5	+/-0.2[nH]	450	50[MHz]-10[GHz]
LQP03TN2N5B02	Film	0201/0603	2.5	+/-0.1[nH]	500	50[MHz]-10[GHz]
LQP03TN2N5C02	Film	0201/0603	2.5	+/-0.2[nH]	500	50[MHz]-10[GHz]
LQP03TG2N6B02	Film	0201/0603	2.6	+/-0.1[nH]	450	50[MHz]-10[GHz]
LQP03TG2N6C02	Film	0201/0603	2.6	+/-0.2[nH]	450	50[MHz]-10[GHz]
LQP03TN2N6B02	Film	0201/0603	2.6	+/-0.1[nH]	500	50[MHz]-10[GHz]
LQP03TN2N6C02	Film	0201/0603	2.6	+/-0.2[nH]	500	50[MHz]-10[GHz]
LQP03TG2N7B02	Film	0201/0603	2.7	+/-0.1[nH]	450	50[MHz]-10[GHz]
LQP03TG2N7C02	Film	0201/0603	2.7	+/-0.2[nH]	450	50[MHz]-10[GHz]
LQP03TN2N7B02	Film	0201/0603	2.7	+/-0.1[nH]	500	50[MHz]-10[GHz]
LQP03TN2N7C02	Film	0201/0603	2.7	+/-0.2[nH]	500	50[MHz]-10[GHz]
LQP03PN2N7C02	Film	0201/0603	2.7	+/-0.2[nH]	1300	50[MHz]-10[GHz]
LQP03TG2N8B02	Film	0201/0603	2.8	+/-0.1[nH]	450	50[MHz]-10[GHz]
LQP03TG2N8C02	Film	0201/0603	2.8	+/-0.2[nH]	450	50[MHz]-10[GHz]
LQP03TN2N8B02	Film	0201/0603	2.8	+/-0.1[nH]	500	50[MHz]-10[GHz]
LQP03TN2N8C02	Film	0201/0603	2.8	+/-0.2[nH]	500	50[MHz]-10[GHz]
LQP03TG2N9B02	Film	0201/0603	2.9	+/-0.1[nH]	450	50[MHz]-10[GHz]
LQP03TG2N9C02	Film	0201/0603	2.9	+/-0.2[nH]	450	50[MHz]-10[GHz]
LQP03TN2N9B02	Film	0201/0603	2.9	+/-0.1[nH]	500	50[MHz]-10[GHz]
LQP03TN2N9C02	Film	0201/0603	2.9	+/-0.2[nH]	500	50[MHz]-10[GHz]
LQP03TG3N0B02	Film	0201/0603	3	+/-0.1[nH]	450	50[MHz]-10[GHz]
LQP03TG3N0C02	Film	0201/0603	3	+/-0.2[nH]	450	50[MHz]-10[GHz]
LQP03TN3N0B02	Film	0201/0603	3	+/-0.1[nH]	450	50[MHz]-10[GHz]
LQP03TN3N0C02	Film	0201/0603	3	+/-0.2[nH]	450	50[MHz]-10[GHz]
LQP03TG3N1B02	Film	0201/0603	3.1	+/-0.1[nH]	400	50[MHz]-10[GHz]
LQP03TG3N1C02	Film	0201/0603	3.1	+/-0.2[nH]	400	50[MHz]-10[GHz]
LQP03TN3N1B02	Film	0201/0603	3.1	+/-0.1[nH]	450	50[MHz]-10[GHz]
LQP03TN3N1C02	Film	0201/0603	3.1	+/-0.2[nH]	450	50[MHz]-10[GHz]
LQP03TG3N2B02	Film	0201/0603	3.2	+/-0.1[nH]	400	50[MHz]-10[GHz]
LQP03TG3N2C02	Film	0201/0603	3.2	+/-0.2[nH]	400	50[MHz]-10[GHz]
LQP03TN3N2B02	Film	0201/0603	3.2	+/-0.1[nH]	450	50[MHz]-10[GHz]
LQP03TN3N2C02	Film	0201/0603	3.2	+/-0.2[nH]	450	50[MHz]-10[GHz]
LQP03TG3N3B02	Film	0201/0603	3.3	+/-0.1[nH]	400	50[MHz]-10[GHz]
LQP03TG3N3C02	Film	0201/0603	3.3	+/-0.2[nH]	400	50[MHz]-10[GHz]
LQP03TN3N3B02	Film	0201/0603	3.3	+/-0.1[nH]	450	50[MHz]-10[GHz]
LQP03TN3N3C02	Film	0201/0603	3.3	+/-0.2[nH]	450	50[MHz]-10[GHz]
LQP03PN3N3C02	Film	0201/0603	3.3	+/-0.2[nH]	1200	50[MHz]-10[GHz]
LQP03TG3N4B02	Film	0201/0603	3.4	+/-0.1[nH]	350	50[MHz]-10[GHz]
LQP03TG3N4C02	Film	0201/0603	3.4	+/-0.2[nH]	350	50[MHz]-10[GHz]
LQP03TN3N4B02	Film	0201/0603	3.4	+/-0.1[nH]	450	50[MHz]-10[GHz]



Part Number	Type	Size Code [inch/mm]	Inductance [nH]	Tolerance	Rated Current [mA]	Frequency Range
LQP03TN3N4C02	Film	0201/0603	3.4	+/-0.2[nH]	450	50[MHz]-10[GHz]
LQP03TG3N5B02	Film	0201/0603	3.5	+/-0.1[nH]	350	50[MHz]-10[GHz]
LQP03TG3N5C02	Film	0201/0603	3.5	+/-0.2[nH]	350	50[MHz]-10[GHz]
LQP03TN3N5B02	Film	0201/0603	3.5	+/-0.1[nH]	450	50[MHz]-10[GHz]
LQP03TN3N5C02	Film	0201/0603	3.5	+/-0.2[nH]	450	50[MHz]-10[GHz]
LQP03TG3N6B02	Film	0201/0603	3.6	+/-0.1[nH]	350	50[MHz]-10[GHz]
LQP03TG3N6C02	Film	0201/0603	3.6	+/-0.2[nH]	350	50[MHz]-10[GHz]
LQP03TN3N6B02	Film	0201/0603	3.6	+/-0.1[nH]	400	50[MHz]-10[GHz]
LQP03TN3N6C02	Film	0201/0603	3.6	+/-0.2[nH]	400	50[MHz]-10[GHz]
LQP03TG3N7B02	Film	0201/0603	3.7	+/-0.1[nH]	350	50[MHz]-10[GHz]
LQP03TG3N7C02	Film	0201/0603	3.7	+/-0.2[nH]	350	50[MHz]-10[GHz]
LQP03TN3N7B02	Film	0201/0603	3.7	+/-0.1[nH]	400	50[MHz]-10[GHz]
LQP03TN3N7C02	Film	0201/0603	3.7	+/-0.2[nH]	400	50[MHz]-10[GHz]
LQP03TG3N8B02	Film	0201/0603	3.8	+/-0.1[nH]	350	50[MHz]-10[GHz]
LQP03TG3N8C02	Film	0201/0603	3.8	+/-0.2[nH]	350	50[MHz]-10[GHz]
LQP03TN3N8B02	Film	0201/0603	3.8	+/-0.1[nH]	400	50[MHz]-10[GHz]
LQP03TN3N8C02	Film	0201/0603	3.8	+/-0.2[nH]	400	50[MHz]-10[GHz]
LQP03TG3N9B02	Film	0201/0603	3.9	+/-0.1[nH]	350	50[MHz]-10[GHz]
LQP03TG3N9C02	Film	0201/0603	3.9	+/-0.2[nH]	350	50[MHz]-10[GHz]
LQP03TN3N9B02	Film	0201/0603	3.9	+/-0.1[nH]	400	50[MHz]-10[GHz]
LQP03TN3N9C02	Film	0201/0603	3.9	+/-0.2[nH]	400	50[MHz]-10[GHz]
LQP03PN3N9C02	Film	0201/0603	3.9	+/-0.2[nH]	1000	50[MHz]-10[GHz]
LQP03TN4N0B02	Film	0201/0603	4	+/-0.1[nH]	350	50[MHz]-10[GHz]
LQP03TN4N0C02	Film	0201/0603	4	+/-0.2[nH]	350	50[MHz]-10[GHz]
LQP03TN4N1B02	Film	0201/0603	4.1	+/-0.1[nH]	350	50[MHz]-10[GHz]
LQP03TN4N1C02	Film	0201/0603	4.1	+/-0.2[nH]	350	50[MHz]-10[GHz]
LQP03TN4N2B02	Film	0201/0603	4.2	+/-0.1[nH]	350	50[MHz]-10[GHz]
LQP03TN4N2C02	Film	0201/0603	4.2	+/-0.2[nH]	350	50[MHz]-10[GHz]
LQP03TG4N3H02	Film	0201/0603	4.3	+/-3[%]	300	50[MHz]-10[GHz]
LQP03TG4N3J02	Film	0201/0603	4.3	+/-5[%]	300	50[MHz]-10[GHz]
LQP03TN4N3H02	Film	0201/0603	4.3	+/-3[%]	350	50[MHz]-10[GHz]
LQP03TN4N3J02	Film	0201/0603	4.3	+/-5[%]	350	50[MHz]-10[GHz]
LQP03TG4N7H02	Film	0201/0603	4.7	+/-3[%]	250	50[MHz]-10[GHz]
LQP03TG4N7J02	Film	0201/0603	4.7	+/-5[%]	250	50[MHz]-10[GHz]
LQP03TN4N7H02	Film	0201/0603	4.7	+/-3[%]	350	50[MHz]-10[GHz]
LQP03TN4N7J02	Film	0201/0603	4.7	+/-5[%]	350	50[MHz]-10[GHz]
LQP03PN4N7J02	Film	0201/0603	4.7	+/-5[%]	900	50[MHz]-10[GHz]
LQP03TG5N1H02	Film	0201/0603	5.1	+/-3[%]	250	50[MHz]-10[GHz]
LQP03TG5N1J02	Film	0201/0603	5.1	+/-5[%]	250	50[MHz]-10[GHz]
LQP03TN5N1H02	Film	0201/0603	5.1	+/-3[%]	350	50[MHz]-10[GHz]
LQP03TN5N1J02	Film	0201/0603	5.1	+/-5[%]	350	50[MHz]-10[GHz]
LQP03TG5N6H02	Film	0201/0603	5.6	+/-3[%]	250	50[MHz]-10[GHz]
LQP03TG5N6J02	Film	0201/0603	5.6	+/-5[%]	250	50[MHz]-10[GHz]
LQP03TN5N6H02	Film	0201/0603	5.6	+/-3[%]	350	50[MHz]-10[GHz]
LQP03TN5N6J02	Film	0201/0603	5.6	+/-5[%]	350	50[MHz]-10[GHz]
LQP03TG6N2H02	Film	0201/0603	6.2	+/-3[%]	200	50[MHz]-10[GHz]
LQP03TG6N2J02	Film	0201/0603	6.2	+/-5[%]	200	50[MHz]-10[GHz]
LQP03TN6N2H02	Film	0201/0603	6.2	+/-3[%]	300	50[MHz]-10[GHz]
LQP03TN6N2J02	Film	0201/0603	6.2	+/-5[%]	300	50[MHz]-10[GHz]
LQP03TG6N8H02	Film	0201/0603	6.8	+/-3[%]	200	50[MHz]-10[GHz]
LQP03TG6N8J02	Film	0201/0603	6.8	+/-5[%]	200	50[MHz]-10[GHz]
LQP03TN6N8H02	Film	0201/0603	6.8	+/-3[%]	300	50[MHz]-10[GHz]
LQP03TN6N8J02	Film	0201/0603	6.8	+/-5[%]	300	50[MHz]-10[GHz]
LQP03TG7N5H02	Film	0201/0603	7.5	+/-3[%]	200	50[MHz]-10[GHz]
LQP03TG7N5J02	Film	0201/0603	7.5	+/-5[%]	200	50[MHz]-10[GHz]
LQP03TN7N5H02	Film	0201/0603	7.5	+/-3[%]	300	50[MHz]-10[GHz]

Part Number	Type	Size Code [inch/mm]	Inductance [nH]	Tolerance	Rated Current [mA]	Frequency Range
LQP03TN7N5J02	Film	0201/0603	7.5	+/-5[%]	300	50[MHz]-10[GHz]
LQP03TG8N2H02	Film	0201/0603	8.2	+/-3[%]	200	50[MHz]-10[GHz]
LQP03TG8N2J02	Film	0201/0603	8.2	+/-5[%]	200	50[MHz]-10[GHz]
LQP03TN8N2H02	Film	0201/0603	8.2	+/-3[%]	250	50[MHz]-10[GHz]
LQP03TN8N2J02	Film	0201/0603	8.2	+/-5[%]	250	50[MHz]-10[GHz]
LQP03TG9N1H02	Film	0201/0603	9.1	+/-3[%]	200	50[MHz]-10[GHz]
LQP03TG9N1J02	Film	0201/0603	9.1	+/-5[%]	200	50[MHz]-10[GHz]
LQP03TN9N1H02	Film	0201/0603	9.1	+/-3[%]	250	50[MHz]-10[GHz]
LQP03TN9N1J02	Film	0201/0603	9.1	+/-5[%]	250	50[MHz]-10[GHz]
LQP03TG10NH02	Film	0201/0603	10	+/-3[%]	190	50[MHz]-10[GHz]
LQP03TG10NJ02	Film	0201/0603	10	+/-5[%]	190	50[MHz]-10[GHz]
LQP03TN10NH02	Film	0201/0603	10	+/-3[%]	250	50[MHz]-10[GHz]
LQP03TN10NJ02	Film	0201/0603	10	+/-5[%]	250	50[MHz]-10[GHz]
LQP03TN11NH02	Film	0201/0603	11	+/-3[%]	250	50[MHz]-10[GHz]
LQP03TN11NJ02	Film	0201/0603	11	+/-5[%]	250	50[MHz]-10[GHz]
LQP03TG12NH02	Film	0201/0603	12	+/-3[%]	180	50[MHz]-10[GHz]
LQP03TG12NJ02	Film	0201/0603	12	+/-5[%]	180	50[MHz]-10[GHz]
LQP03TN12NH02	Film	0201/0603	12	+/-3[%]	250	50[MHz]-10[GHz]
LQP03TN12NJ02	Film	0201/0603	12	+/-5[%]	250	50[MHz]-10[GHz]
LQP03TN13NH02	Film	0201/0603	13	+/-3[%]	250	50[MHz]-10[GHz]
LQP03TN13NJ02	Film	0201/0603	13	+/-5[%]	250	50[MHz]-10[GHz]
LQP03TG15NH02	Film	0201/0603	15	+/-3[%]	170	50[MHz]-10[GHz]
LQP03TG15NJ02	Film	0201/0603	15	+/-5[%]	170	50[MHz]-10[GHz]
LQP03TN15NH02	Film	0201/0603	15	+/-3[%]	250	50[MHz]-10[GHz]
LQP03TN15NJ02	Film	0201/0603	15	+/-5[%]	250	50[MHz]-10[GHz]
LQP03TN16NH02	Film	0201/0603	16	+/-3[%]	200	50[MHz]-10[GHz]
LQP03TN16NJ02	Film	0201/0603	16	+/-5[%]	200	50[MHz]-10[GHz]
LQP03TG18NH02	Film	0201/0603	18	+/-3[%]	160	50[MHz]-10[GHz]
LQP03TG18NJ02	Film	0201/0603	18	+/-5[%]	160	50[MHz]-10[GHz]
LQP03TN18NH02	Film	0201/0603	18	+/-3[%]	200	50[MHz]-10[GHz]
LQP03TN18NJ02	Film	0201/0603	18	+/-5[%]	200	50[MHz]-10[GHz]
LQP03TN20NH02	Film	0201/0603	20	+/-3[%]	150	50[MHz]-10[GHz]
LQP03TN20NJ02	Film	0201/0603	20	+/-5[%]	150	50[MHz]-10[GHz]
LQP03TG22NH02	Film	0201/0603	22	+/-3[%]	140	50[MHz]-10[GHz]
LQP03TG22NJ02	Film	0201/0603	22	+/-5[%]	140	50[MHz]-10[GHz]
LQP03TN22NH02	Film	0201/0603	22	+/-3[%]	150	50[MHz]-10[GHz]
LQP03TN22NJ02	Film	0201/0603	22	+/-5[%]	150	50[MHz]-10[GHz]
LQP03TN24NH02	Film	0201/0603	24	+/-3[%]	140	50[MHz]-10[GHz]
LQP03TN24NJ02	Film	0201/0603	24	+/-5[%]	140	50[MHz]-10[GHz]
LQP03TG27NH02	Film	0201/0603	27	+/-3[%]	120	50[MHz]-10[GHz]
LQP03TG27NJ02	Film	0201/0603	27	+/-5[%]	120	50[MHz]-10[GHz]
LQP03TN27NH02	Film	0201/0603	27	+/-3[%]	140	50[MHz]-10[GHz]
LQP03TN27NJ02	Film	0201/0603	27	+/-5[%]	140	50[MHz]-10[GHz]
LQP03TN30NH02	Film	0201/0603	30	+/-3[%]	120	50[MHz]-10[GHz]
LQP03TN30NJ02	Film	0201/0603	30	+/-5[%]	120	50[MHz]-10[GHz]
LQP03TG33NJ02	Film	0201/0603	33	+/-5[%]	110	50[MHz]-10[GHz]
LQP03TN33NH02	Film	0201/0603	33	+/-3[%]	120	50[MHz]-10[GHz]
LQP03TN33NJ02	Film	0201/0603	33	+/-5[%]	120	50[MHz]-10[GHz]
LQP03TN36NH02	Film	0201/0603	36	+/-3[%]	120	50[MHz]-10[GHz]
LQP03TN36NJ02	Film	0201/0603	36	+/-5[%]	120	50[MHz]-10[GHz]
LQP03TG39NJ02	Film	0201/0603	39	+/-5[%]	110	50[MHz]-10[GHz]
LQP03TN39NH02	Film	0201/0603	39	+/-3[%]	120	50[MHz]-10[GHz]
LQP03TN39NJ02	Film	0201/0603	39	+/-5[%]	120	50[MHz]-10[GHz]
LQP03TN43NH02	Film	0201/0603	43	+/-3[%]	100	50[MHz]-10[GHz]
LQP03TN43NJ02	Film	0201/0603	43	+/-5[%]	100	50[MHz]-10[GHz]
LQP03TG47NJ02	Film	0201/0603	47	+/-5[%]	100	50[MHz]-10[GHz]

Part Number	Type	Size Code [inch/mm]	Inductance [nH]	Tolerance	Rated Current [mA]	Frequency Range
LQP03TN47NH02	Film	0201/0603	47	+/-3[%]	100	50[MHz]-10[GHz]
LQP03TN47NJ02	Film	0201/0603	47	+/-5[%]	100	50[MHz]-10[GHz]
LQP03TN51NH02	Film	0201/0603	51	+/-3[%]	100	50[MHz]-10[GHz]
LQP03TN51NJ02	Film	0201/0603	51	+/-5[%]	100	50[MHz]-10[GHz]
LQP03TG56NJ02	Film	0201/0603	56	+/-5[%]	100	50[MHz]-10[GHz]
LQP03TN56NH02	Film	0201/0603	56	+/-3[%]	100	50[MHz]-10[GHz]
LQP03TN56NJ02	Film	0201/0603	56	+/-5[%]	100	50[MHz]-10[GHz]
LQP03TN62NH02	Film	0201/0603	62	+/-3[%]	100	50[MHz]-10[GHz]
LQP03TN62NJ02	Film	0201/0603	62	+/-5[%]	100	50[MHz]-10[GHz]
LQP03TG68NJ02	Film	0201/0603	68	+/-5[%]	90	50[MHz]-10[GHz]
LQP03TN68NH02	Film	0201/0603	68	+/-3[%]	100	50[MHz]-10[GHz]
LQP03TN68NJ02	Film	0201/0603	68	+/-5[%]	100	50[MHz]-10[GHz]
LQP03TN75NH02	Film	0201/0603	75	+/-3[%]	100	50[MHz]-10[GHz]
LQP03TN75NJ02	Film	0201/0603	75	+/-5[%]	100	50[MHz]-10[GHz]
LQP03TG82NJ02	Film	0201/0603	82	+/-5[%]	90	50[MHz]-10[GHz]
LQP03TN82NH02	Film	0201/0603	82	+/-3[%]	100	50[MHz]-10[GHz]
LQP03TN82NJ02	Film	0201/0603	82	+/-5[%]	100	50[MHz]-10[GHz]
LQP03TN91NH02	Film	0201/0603	91	+/-3[%]	80	50[MHz]-10[GHz]
LQP03TN91NJ02	Film	0201/0603	91	+/-5[%]	80	50[MHz]-10[GHz]
LQP03TGR10J02	Film	0201/0603	100	+/-5[%]	80	50[MHz]-10[GHz]
LQP03TNR10H02	Film	0201/0603	100	+/-3[%]	80	50[MHz]-10[GHz]
LQP03TNR10J02	Film	0201/0603	100	+/-5[%]	80	50[MHz]-10[GHz]
LQP03TNR11H02	Film	0201/0603	110	+/-3[%]	80	50[MHz]-10[GHz]
LQP03TNR11J02	Film	0201/0603	110	+/-5[%]	80	50[MHz]-10[GHz]
LQP03TGR12J02	Film	0201/0603	120	+/-5[%]	80	50[MHz]-10[GHz]
LQP03TNR12H02	Film	0201/0603	120	+/-3[%]	80	50[MHz]-10[GHz]
LQP03TNR12J02	Film	0201/0603	120	+/-5[%]	80	50[MHz]-10[GHz]
LQP03TNR13H02	Film	0201/0603	130	+/-3[%]	80	50[MHz]-10[GHz]
LQP03TNR13J02	Film	0201/0603	130	+/-5[%]	80	50[MHz]-10[GHz]
LQP03TNR15H02	Film	0201/0603	150	+/-3[%]	80	50[MHz]-10[GHz]
LQP03TNR15J02	Film	0201/0603	150	+/-5[%]	80	50[MHz]-10[GHz]
LQP03TNR16H02	Film	0201/0603	160	+/-3[%]	70	50[MHz]-10[GHz]
LQP03TNR16J02	Film	0201/0603	160	+/-5[%]	70	50[MHz]-10[GHz]
LQP03TNR18H02	Film	0201/0603	180	+/-3[%]	70	50[MHz]-10[GHz]
LQP03TNR18J02	Film	0201/0603	180	+/-5[%]	70	50[MHz]-10[GHz]
LQP03TNR20H02	Film	0201/0603	200	+/-3[%]	60	50[MHz]-10[GHz]
LQP03TNR20J02	Film	0201/0603	200	+/-5[%]	60	50[MHz]-10[GHz]
LQP03TNR22H02	Film	0201/0603	220	+/-3[%]	60	50[MHz]-10[GHz]
LQP03TNR22J02	Film	0201/0603	220	+/-5[%]	60	50[MHz]-10[GHz]
LQP03TNR24H02	Film	0201/0603	240	+/-3[%]	60	50[MHz]-10[GHz]
LQP03TNR24J02	Film	0201/0603	240	+/-5[%]	60	50[MHz]-10[GHz]
LQP03TNR27H02	Film	0201/0603	270	+/-3[%]	60	50[MHz]-10[GHz]
LQP03TNR27J02	Film	0201/0603	270	+/-5[%]	60	50[MHz]-10[GHz]
LQP15MN1N0B02	Film	0402/1005	1	+/-0.1[nH]	400	50[MHz]-10[GHz]
LQP15MN1N0W02	Film	0402/1005	1	+/-0.05[nH]	400	50[MHz]-10[GHz]
LQP15MN1N1B02	Film	0402/1005	1.1	+/-0.1[nH]	390	50[MHz]-10[GHz]
LQP15MN1N1W02	Film	0402/1005	1.1	+/-0.05[nH]	390	50[MHz]-10[GHz]
LQP15MN1N2B02	Film	0402/1005	1.2	+/-0.1[nH]	390	50[MHz]-10[GHz]
LQP15MN1N2W02	Film	0402/1005	1.2	+/-0.05[nH]	390	50[MHz]-10[GHz]
LQP15MN1N3B02	Film	0402/1005	1.3	+/-0.1[nH]	280	50[MHz]-10[GHz]
LQP15MN1N3W02	Film	0402/1005	1.3	+/-0.05[nH]	280	50[MHz]-10[GHz]
LQP15MN1N4W02	Film	0402/1005	1.4	+/-0.05[nH]	280	50[MHz]-10[GHz]
LQP15MN1N5B02	Film	0402/1005	1.5	+/-0.1[nH]	280	50[MHz]-10[GHz]
LQP15MN1N5W02	Film	0402/1005	1.5	+/-0.05[nH]	280	50[MHz]-10[GHz]
LQP15MN1N6B02	Film	0402/1005	1.6	+/-0.1[nH]	220	50[MHz]-10[GHz]
LQP15MN1N6W02	Film	0402/1005	1.6	+/-0.05[nH]	220	50[MHz]-10[GHz]

Part Number	Type	Size Code [inch/mm]	Inductance [nH]	Tolerance	Rated Current [mA]	Frequency Range
LQP15MN1N7W02	Film	0402/1005	1.7	+/-0.05[nH]	280	50[MHz]-10[GHz]
LQP15MN1N8B02	Film	0402/1005	1.8	+/-0.1[nH]	280	50[MHz]-10[GHz]
LQP15MN1N8W02	Film	0402/1005	1.8	+/-0.05[nH]	280	50[MHz]-10[GHz]
LQP15MN1N9W02	Film	0402/1005	1.9	+/-0.05[nH]	220	50[MHz]-10[GHz]
LQP15MN2N0B02	Film	0402/1005	2	+/-0.1[nH]	220	50[MHz]-10[GHz]
LQP15MN2N0W02	Film	0402/1005	2	+/-0.05[nH]	220	50[MHz]-10[GHz]
LQP15MN2N1W02	Film	0402/1005	2.1	+/-0.05[nH]	220	50[MHz]-10[GHz]
LQP15MN2N2B02	Film	0402/1005	2.2	+/-0.1[nH]	220	50[MHz]-10[GHz]
LQP15MN2N2W02	Film	0402/1005	2.2	+/-0.05[nH]	220	50[MHz]-10[GHz]
LQP15MN2N3W02	Film	0402/1005	2.3	+/-0.05[nH]	220	50[MHz]-10[GHz]
LQP15MN2N4B02	Film	0402/1005	2.4	+/-0.1[nH]	220	50[MHz]-10[GHz]
LQP15MN2N4W02	Film	0402/1005	2.4	+/-0.05[nH]	220	50[MHz]-10[GHz]
LQP15MN2N5W02	Film	0402/1005	2.5	+/-0.05[nH]	220	50[MHz]-10[GHz]
LQP15MN2N6W02	Film	0402/1005	2.6	+/-0.05[nH]	220	50[MHz]-10[GHz]
LQP15MN2N7B02	Film	0402/1005	2.7	+/-0.1[nH]	220	50[MHz]-10[GHz]
LQP15MN2N7W02	Film	0402/1005	2.7	+/-0.05[nH]	220	50[MHz]-10[GHz]
LQP15MN2N8W02	Film	0402/1005	2.8	+/-0.05[nH]	190	50[MHz]-10[GHz]
LQP15MN2N9W02	Film	0402/1005	2.9	+/-0.05[nH]	190	50[MHz]-10[GHz]
LQP15MN3N0B02	Film	0402/1005	3	+/-0.1[nH]	190	50[MHz]-10[GHz]
LQP15MN3N0W02	Film	0402/1005	3	+/-0.05[nH]	190	50[MHz]-10[GHz]
LQP15MN3N1W02	Film	0402/1005	3.1	+/-0.05[nH]	190	50[MHz]-10[GHz]
LQP15MN3N2W02	Film	0402/1005	3.2	+/-0.05[nH]	190	50[MHz]-10[GHz]
LQP15MN3N3B02	Film	0402/1005	3.3	+/-0.1[nH]	190	50[MHz]-10[GHz]
LQP15MN3N3W02	Film	0402/1005	3.3	+/-0.05[nH]	190	50[MHz]-10[GHz]
LQP15MN3N4W02	Film	0402/1005	3.4	+/-0.05[nH]	170	50[MHz]-10[GHz]
LQP15MN3N5W02	Film	0402/1005	3.5	+/-0.05[nH]	170	50[MHz]-10[GHz]
LQP15MN3N6B02	Film	0402/1005	3.6	+/-0.1[nH]	170	50[MHz]-10[GHz]
LQP15MN3N6W02	Film	0402/1005	3.6	+/-0.05[nH]	170	50[MHz]-10[GHz]
LQP15MN3N7W02	Film	0402/1005	3.7	+/-0.05[nH]	170	50[MHz]-10[GHz]
LQP15MN3N8W02	Film	0402/1005	3.8	+/-0.05[nH]	170	50[MHz]-10[GHz]
LQP15MN3N9B02	Film	0402/1005	3.9	+/-0.1[nH]	170	50[MHz]-10[GHz]
LQP15MN3N9W02	Film	0402/1005	3.9	+/-0.05[nH]	170	50[MHz]-10[GHz]
LQP15MN4N3B02	Film	0402/1005	4.3	+/-0.1[nH]	160	50[MHz]-10[GHz]
LQP15MN4N7B02	Film	0402/1005	4.7	+/-0.1[nH]	160	50[MHz]-10[GHz]
LQP15MN5N1B02	Film	0402/1005	5.1	+/-0.1[nH]	140	50[MHz]-10[GHz]
LQP15MN5N6B02	Film	0402/1005	5.6	+/-0.1[nH]	140	50[MHz]-10[GHz]
LQP15MN6N2B02	Film	0402/1005	6.2	+/-0.1[nH]	130	50[MHz]-10[GHz]
LQP15MN6N8B02	Film	0402/1005	6.8	+/-0.1[nH]	130	50[MHz]-10[GHz]
LQP15MN7N5B02	Film	0402/1005	7.5	+/-0.1[nH]	110	50[MHz]-10[GHz]
LQP15MN8N2B02	Film	0402/1005	8.2	+/-0.1[nH]	110	50[MHz]-10[GHz]
LQP15MN9N1B02	Film	0402/1005	9.1	+/-0.1[nH]	100	50[MHz]-10[GHz]
LQP15MN10NG02	Film	0402/1005	10	+/-2[%]	100	50[MHz]-10[GHz]
LQP15MN12NG02	Film	0402/1005	12	+/-2[%]	90	50[MHz]-10[GHz]
LQP15MN15NG02	Film	0402/1005	15	+/-2[%]	90	50[MHz]-10[GHz]
LQP15MN18NG02	Film	0402/1005	18	+/-2[%]	80	50[MHz]-10[GHz]
LQP15MN22NG02	Film	0402/1005	22	+/-2[%]	70	50[MHz]-10[GHz]
LQP15MN27NG02	Film	0402/1005	27	+/-2[%]	70	50[MHz]-10[GHz]
LQP15MN33NG02	Film	0402/1005	33	+/-2[%]	60	50[MHz]-10[GHz]
LQG15HH1N0S02	Monolithic	0402/1005	1	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HN1N0S02	Monolithic	0402/1005	1	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HS1N0S02	Monolithic	0402/1005	1	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HH1N1S02	Monolithic	0402/1005	1.1	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HN1N1S02	Monolithic	0402/1005	1.1	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HS1N1S02	Monolithic	0402/1005	1.1	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HH1N2S02	Monolithic	0402/1005	1.2	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HN1N2S02	Monolithic	0402/1005	1.2	+/-0.3[nH]	300	50[MHz]-10[GHz]

Part Number	Type	Size Code [inch/mm]	Inductance [nH]	Tolerance	Rated Current [mA]	Frequency Range
LQG15HS1N2S02	Monolithic	0402/1005	1.2	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HH1N3S02	Monolithic	0402/1005	1.3	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HN1N3S02	Monolithic	0402/1005	1.3	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HS1N3S02	Monolithic	0402/1005	1.3	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HH1N5S02	Monolithic	0402/1005	1.5	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HN1N5S02	Monolithic	0402/1005	1.5	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HS1N5S02	Monolithic	0402/1005	1.5	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HH1N6S02	Monolithic	0402/1005	1.6	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HN1N6S02	Monolithic	0402/1005	1.6	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HS1N6S02	Monolithic	0402/1005	1.6	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HH1N8S02	Monolithic	0402/1005	1.8	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HN1N8S02	Monolithic	0402/1005	1.8	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HS1N8S02	Monolithic	0402/1005	1.8	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HH2N0S02	Monolithic	0402/1005	2	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HN2N0S02	Monolithic	0402/1005	2	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HS2N0S02	Monolithic	0402/1005	2	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HH2N2S02	Monolithic	0402/1005	2.2	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HN2N2S02	Monolithic	0402/1005	2.2	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HS2N2S02	Monolithic	0402/1005	2.2	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HH2N4S02	Monolithic	0402/1005	2.4	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HN2N4S02	Monolithic	0402/1005	2.4	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HS2N4S02	Monolithic	0402/1005	2.4	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HH2N7S02	Monolithic	0402/1005	2.7	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HN2N7S02	Monolithic	0402/1005	2.7	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HS2N7S02	Monolithic	0402/1005	2.7	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HH3N0S02	Monolithic	0402/1005	3	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HN3N0S02	Monolithic	0402/1005	3	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HS3N0S02	Monolithic	0402/1005	3	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HH3N3S02	Monolithic	0402/1005	3.3	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HN3N3S02	Monolithic	0402/1005	3.3	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HS3N3S02	Monolithic	0402/1005	3.3	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HH3N6S02	Monolithic	0402/1005	3.6	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HN3N6S02	Monolithic	0402/1005	3.6	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HS3N6S02	Monolithic	0402/1005	3.6	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HH3N9S02	Monolithic	0402/1005	3.9	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HN3N9S02	Monolithic	0402/1005	3.9	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HS3N9S02	Monolithic	0402/1005	3.9	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HH4N3S02	Monolithic	0402/1005	4.3	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HN4N3S02	Monolithic	0402/1005	4.3	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HS4N3S02	Monolithic	0402/1005	4.3	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HH4N7S02	Monolithic	0402/1005	4.7	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HN4N7S02	Monolithic	0402/1005	4.7	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HS4N7S02	Monolithic	0402/1005	4.7	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HH5N1S02	Monolithic	0402/1005	5.1	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HN5N1S02	Monolithic	0402/1005	5.1	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HS5N1S02	Monolithic	0402/1005	5.1	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HH5N6S02	Monolithic	0402/1005	5.6	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HN5N6S02	Monolithic	0402/1005	5.6	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HS5N6S02	Monolithic	0402/1005	5.6	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HH6N2S02	Monolithic	0402/1005	6.2	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HN6N2S02	Monolithic	0402/1005	6.2	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HS6N2S02	Monolithic	0402/1005	6.2	+/-0.3[nH]	300	50[MHz]-10[GHz]
LQG15HH6N8J02	Monolithic	0402/1005	6.8	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HN6N8J02	Monolithic	0402/1005	6.8	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HS6N8J02	Monolithic	0402/1005	6.8	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HH7N5J02	Monolithic	0402/1005	7.5	+/-5[%]	300	50[MHz]-10[GHz]

Part Number	Type	Size Code [inch/mm]	Inductance [nH]	Tolerance	Rated Current [mA]	Frequency Range
LQG15HN7N5J02	Monolithic	0402/1005	7.5	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HS7N5J02	Monolithic	0402/1005	7.5	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HH8N2J02	Monolithic	0402/1005	8.2	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HN8N2J02	Monolithic	0402/1005	8.2	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HS8N2J02	Monolithic	0402/1005	8.2	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HH9N1J02	Monolithic	0402/1005	9.1	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HN9N1J02	Monolithic	0402/1005	9.1	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HS9N1J02	Monolithic	0402/1005	9.1	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HH10NJ02	Monolithic	0402/1005	10	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HN10NJ02	Monolithic	0402/1005	10	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HS10NJ02	Monolithic	0402/1005	10	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HH12NJ02	Monolithic	0402/1005	12	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HN12NJ02	Monolithic	0402/1005	12	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HS12NJ02	Monolithic	0402/1005	12	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HH15NJ02	Monolithic	0402/1005	15	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HN15NJ02	Monolithic	0402/1005	15	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HS15NJ02	Monolithic	0402/1005	15	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HH18NJ02	Monolithic	0402/1005	18	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HN18NJ02	Monolithic	0402/1005	18	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HS18NJ02	Monolithic	0402/1005	18	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HH22NJ02	Monolithic	0402/1005	22	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HN22NJ02	Monolithic	0402/1005	22	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HS22NJ02	Monolithic	0402/1005	22	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HH27NJ02	Monolithic	0402/1005	27	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HN27NJ02	Monolithic	0402/1005	27	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HS27NJ02	Monolithic	0402/1005	27	+/-5[%]	300	50[MHz]-10[GHz]
LQG15HH33NJ02	Monolithic	0402/1005	33	+/-5[%]	200	50[MHz]-10[GHz]
LQG15HN33NJ02	Monolithic	0402/1005	33	+/-5[%]	200	50[MHz]-10[GHz]
LQG15HS33NJ02	Monolithic	0402/1005	33	+/-5[%]	200	50[MHz]-10[GHz]
LQG15HH39NJ02	Monolithic	0402/1005	39	+/-5[%]	200	50[MHz]-10[GHz]
LQG15HN39NJ02	Monolithic	0402/1005	39	+/-5[%]	200	50[MHz]-10[GHz]
LQG15HS39NJ02	Monolithic	0402/1005	39	+/-5[%]	200	50[MHz]-10[GHz]
LQG15HH47NJ02	Monolithic	0402/1005	47	+/-5[%]	200	50[MHz]-10[GHz]
LQG15HN47NJ02	Monolithic	0402/1005	47	+/-5[%]	200	50[MHz]-10[GHz]
LQG15HS47NJ02	Monolithic	0402/1005	47	+/-5[%]	200	50[MHz]-10[GHz]
LQG15HH56NJ02	Monolithic	0402/1005	56	+/-5[%]	200	50[MHz]-10[GHz]
LQG15HN56NJ02	Monolithic	0402/1005	56	+/-5[%]	200	50[MHz]-10[GHz]
LQG15HS56NJ02	Monolithic	0402/1005	56	+/-5[%]	200	50[MHz]-10[GHz]
LQG15HH68NJ02	Monolithic	0402/1005	68	+/-5[%]	180	50[MHz]-10[GHz]
LQG15HN68NJ02	Monolithic	0402/1005	68	+/-5[%]	180	50[MHz]-10[GHz]
LQG15HS68NJ02	Monolithic	0402/1005	68	+/-5[%]	180	50[MHz]-10[GHz]
LQG15HH82NJ02	Monolithic	0402/1005	82	+/-5[%]	150	50[MHz]-10[GHz]
LQG15HN82NJ02	Monolithic	0402/1005	82	+/-5[%]	150	50[MHz]-10[GHz]
LQG15HS82NJ02	Monolithic	0402/1005	82	+/-5[%]	150	50[MHz]-10[GHz]
LQG15HHR10J02	Monolithic	0402/1005	100	+/-5[%]	150	50[MHz]-10[GHz]
LQG15HNR10J02	Monolithic	0402/1005	100	+/-5[%]	150	50[MHz]-10[GHz]
LQG15HSR10J02	Monolithic	0402/1005	100	+/-5[%]	150	50[MHz]-10[GHz]
LQG15HHR12J02	Monolithic	0402/1005	120	+/-5[%]	150	50[MHz]-10[GHz]
LQG15HNR12J02	Monolithic	0402/1005	120	+/-5[%]	150	50[MHz]-10[GHz]
LQG15HSR12J02	Monolithic	0402/1005	120	+/-5[%]	150	50[MHz]-10[GHz]
LQG15HHR15J02	Monolithic	0402/1005	150	+/-5[%]	140	50[MHz]-10[GHz]
LQG15HSR15J02	Monolithic	0402/1005	150	+/-5[%]	140	50[MHz]-10[GHz]
LQG15HHR18J02	Monolithic	0402/1005	180	+/-5[%]	130	50[MHz]-10[GHz]
LQG15HSR18J02	Monolithic	0402/1005	180	+/-5[%]	130	50[MHz]-10[GHz]
LQG15HHR22J02	Monolithic	0402/1005	220	+/-5[%]	120	50[MHz]-10[GHz]
LQG15HSR22J02	Monolithic	0402/1005	220	+/-5[%]	120	50[MHz]-10[GHz]

Part Number	Type	Size Code [inch/mm]	Inductance [nH]	Tolerance	Rated Current [mA]	Frequency Range
LQG15HHR27J02	Monolithic	0402/1005	270	+/-5[%]	110	50[MHz]-10[GHz]
LQG15HSR27J02	Monolithic	0402/1005	270	+/-5[%]	110	50[MHz]-10[GHz]
LQG18HN1N2S00	Monolithic	0603/1608	1.2	+/-0.3[nH]	500	50[MHz]-10[GHz]
LQG18HN1N5S00	Monolithic	0603/1608	1.5	+/-0.3[nH]	500	50[MHz]-10[GHz]
LQG18HN1N8S00	Monolithic	0603/1608	1.8	+/-0.3[nH]	500	50[MHz]-10[GHz]
LQG18HN2N2S00	Monolithic	0603/1608	2.2	+/-0.3[nH]	500	50[MHz]-10[GHz]
LQG18HN2N7S00	Monolithic	0603/1608	2.7	+/-0.3[nH]	500	50[MHz]-10[GHz]
LQG18HN3N3S00	Monolithic	0603/1608	3.3	+/-0.3[nH]	500	50[MHz]-10[GHz]
LQG18HN3N9S00	Monolithic	0603/1608	3.9	+/-0.3[nH]	450	50[MHz]-10[GHz]
LQG18HN4N7S00	Monolithic	0603/1608	4.7	+/-0.3[nH]	450	50[MHz]-10[GHz]
LQG18HN5N6S00	Monolithic	0603/1608	5.6	+/-0.3[nH]	430	50[MHz]-10[GHz]
LQG18HN6N8J00	Monolithic	0603/1608	6.8	+/-5[%]	430	50[MHz]-10[GHz]
LQG18HN8N2J00	Monolithic	0603/1608	8.2	+/-5[%]	400	50[MHz]-10[GHz]
LQG18HN10NJ00	Monolithic	0603/1608	10	+/-5[%]	400	50[MHz]-10[GHz]
LQG18HN12NJ00	Monolithic	0603/1608	12	+/-5[%]	400	50[MHz]-10[GHz]
LQG18HN15NJ00	Monolithic	0603/1608	15	+/-5[%]	350	50[MHz]-10[GHz]
LQG18HN18NJ00	Monolithic	0603/1608	18	+/-5[%]	350	50[MHz]-10[GHz]
LQG18HN22NJ00	Monolithic	0603/1608	22	+/-5[%]	300	50[MHz]-10[GHz]
LQG18HN27NJ00	Monolithic	0603/1608	27	+/-5[%]	300	50[MHz]-10[GHz]
LQG18HN33NJ00	Monolithic	0603/1608	33	+/-5[%]	300	50[MHz]-10[GHz]
LQG18HN39NJ00	Monolithic	0603/1608	39	+/-5[%]	300	50[MHz]-10[GHz]
LQG18HN47NJ00	Monolithic	0603/1608	47	+/-5[%]	300	50[MHz]-10[GHz]
LQG18HN56NJ00	Monolithic	0603/1608	56	+/-5[%]	300	50[MHz]-10[GHz]
LQG18HN68NJ00	Monolithic	0603/1608	68	+/-5[%]	300	50[MHz]-10[GHz]
LQG18HN82NJ00	Monolithic	0603/1608	82	+/-5[%]	300	50[MHz]-10[GHz]
LQG18HNR10J00	Monolithic	0603/1608	100	+/-5[%]	300	50[MHz]-10[GHz]
LQW04AN1N1C00	Wound	03015/0804	1.1	+/-0.2[nH]	990	50[MHz]-10[GHz]
LQW04AN1N1D00	Wound	03015/0804	1.1	+/-0.5[nH]	990	50[MHz]-10[GHz]
LQW04AN1N8C00	Wound	03015/0804	1.8	+/-0.2[nH]	700	50[MHz]-10[GHz]
LQW04AN1N8D00	Wound	03015/0804	1.8	+/-0.5[nH]	700	50[MHz]-10[GHz]
LQW04AN2N7C00	Wound	03015/0804	2.7	+/-0.2[nH]	570	50[MHz]-10[GHz]
LQW04AN2N7D00	Wound	03015/0804	2.7	+/-0.5[nH]	570	50[MHz]-10[GHz]
LQW04AN3N0C00	Wound	03015/0804	3	+/-0.2[nH]	620	50[MHz]-10[GHz]
LQW04AN3N0D00	Wound	03015/0804	3	+/-0.5[nH]	620	50[MHz]-10[GHz]
LQW04AN3N3C00	Wound	03015/0804	3.3	+/-0.2[nH]	440	50[MHz]-10[GHz]
LQW04AN3N3D00	Wound	03015/0804	3.3	+/-0.5[nH]	440	50[MHz]-10[GHz]
LQW04AN3N6C00	Wound	03015/0804	3.6	+/-0.2[nH]	530	50[MHz]-10[GHz]
LQW04AN3N6D00	Wound	03015/0804	3.6	+/-0.5[nH]	530	50[MHz]-10[GHz]
LQW04AN3N9C00	Wound	03015/0804	3.9	+/-0.2[nH]	530	50[MHz]-10[GHz]
LQW04AN3N9D00	Wound	03015/0804	3.9	+/-0.5[nH]	530	50[MHz]-10[GHz]
LQW04AN4N3C00	Wound	03015/0804	4.3	+/-0.2[nH]	530	50[MHz]-10[GHz]
LQW04AN4N3D00	Wound	03015/0804	4.3	+/-0.5[nH]	530	50[MHz]-10[GHz]
LQW04AN4N7C00	Wound	03015/0804	4.7	+/-0.2[nH]	440	50[MHz]-10[GHz]
LQW04AN4N7D00	Wound	03015/0804	4.7	+/-0.5[nH]	440	50[MHz]-10[GHz]
LQW04AN5N1C00	Wound	03015/0804	5.1	+/-0.2[nH]	470	50[MHz]-10[GHz]
LQW04AN5N1D00	Wound	03015/0804	5.1	+/-0.5[nH]	470	50[MHz]-10[GHz]
LQW04AN5N6C00	Wound	03015/0804	5.6	+/-0.2[nH]	470	50[MHz]-10[GHz]
LQW04AN5N6D00	Wound	03015/0804	5.6	+/-0.5[nH]	470	50[MHz]-10[GHz]
LQW04AN6N2C00	Wound	03015/0804	6.2	+/-0.2[nH]	390	50[MHz]-10[GHz]
LQW04AN6N2D00	Wound	03015/0804	6.2	+/-0.5[nH]	390	50[MHz]-10[GHz]
LQW04AN6N8C00	Wound	03015/0804	6.8	+/-0.2[nH]	440	50[MHz]-10[GHz]
LQW04AN6N8D00	Wound	03015/0804	6.8	+/-0.5[nH]	440	50[MHz]-10[GHz]
LQW04AN7N5C00	Wound	03015/0804	7.5	+/-0.2[nH]	440	50[MHz]-10[GHz]
LQW04AN7N5D00	Wound	03015/0804	7.5	+/-0.5[nH]	440	50[MHz]-10[GHz]
LQW04AN8N2C00	Wound	03015/0804	8.2	+/-0.2[nH]	350	50[MHz]-10[GHz]
LQW04AN8N2D00	Wound	03015/0804	8.2	+/-0.5[nH]	350	50[MHz]-10[GHz]

Part Number	Type	Size Code [inch/mm]	Inductance [nH]	Tolerance	Rated Current [mA]	Frequency Range
LQW04AN9N1C00	Wound	03015/0804	9.1	+/-0.2[nH]	400	50[MHz]-10[GHz]
LQW04AN9N1D00	Wound	03015/0804	9.1	+/-0.5[nH]	400	50[MHz]-10[GHz]
LQW04AN10NH00	Wound	03015/0804	10	+/-3[%]	330	50[MHz]-10[GHz]
LQW04AN10NJ00	Wound	03015/0804	10	+/-5[%]	330	50[MHz]-10[GHz]
LQW04AN11NH00	Wound	03015/0804	11	+/-3[%]	310	50[MHz]-10[GHz]
LQW04AN11NJ00	Wound	03015/0804	11	+/-5[%]	310	50[MHz]-10[GHz]
LQW04AN12NH00	Wound	03015/0804	12	+/-3[%]	310	50[MHz]-10[GHz]
LQW04AN12NJ00	Wound	03015/0804	12	+/-5[%]	310	50[MHz]-10[GHz]
LQW04AN13NH00	Wound	03015/0804	13	+/-3[%]	280	50[MHz]-10[GHz]
LQW04AN13NJ00	Wound	03015/0804	13	+/-5[%]	280	50[MHz]-10[GHz]
LQW04AN15NH00	Wound	03015/0804	15	+/-3[%]	240	50[MHz]-10[GHz]
LQW04AN15NJ00	Wound	03015/0804	15	+/-5[%]	240	50[MHz]-10[GHz]
LQW04AN16NH00	Wound	03015/0804	16	+/-3[%]	270	50[MHz]-10[GHz]
LQW04AN16NJ00	Wound	03015/0804	16	+/-5[%]	270	50[MHz]-10[GHz]
LQW04AN18NH00	Wound	03015/0804	18	+/-3[%]	220	50[MHz]-10[GHz]
LQW04AN18NJ00	Wound	03015/0804	18	+/-5[%]	220	50[MHz]-10[GHz]
LQW04AN19NH00	Wound	03015/0804	19	+/-3[%]	160	50[MHz]-10[GHz]
LQW04AN19NJ00	Wound	03015/0804	19	+/-5[%]	160	50[MHz]-10[GHz]
LQW04AN20NH00	Wound	03015/0804	20	+/-3[%]	210	50[MHz]-10[GHz]
LQW04AN20NJ00	Wound	03015/0804	20	+/-5[%]	210	50[MHz]-10[GHz]
LQW04AN22NH00	Wound	03015/0804	22	+/-3[%]	200	50[MHz]-10[GHz]
LQW04AN22NJ00	Wound	03015/0804	22	+/-5[%]	200	50[MHz]-10[GHz]
LQW04AN23NH00	Wound	03015/0804	23	+/-3[%]	160	50[MHz]-10[GHz]
LQW04AN23NJ00	Wound	03015/0804	23	+/-5[%]	160	50[MHz]-10[GHz]
LQW04AN24NH00	Wound	03015/0804	24	+/-3[%]	160	50[MHz]-10[GHz]
LQW04AN24NJ00	Wound	03015/0804	24	+/-5[%]	160	50[MHz]-10[GHz]
LQW04AN25NH00	Wound	03015/0804	25	+/-3[%]	160	50[MHz]-10[GHz]
LQW04AN25NJ00	Wound	03015/0804	25	+/-5[%]	160	50[MHz]-10[GHz]
LQW04AN27NH00	Wound	03015/0804	27	+/-3[%]	160	50[MHz]-10[GHz]
LQW04AN27NJ00	Wound	03015/0804	27	+/-5[%]	160	50[MHz]-10[GHz]
LQW15AN1N3C10	Wound	0402/1005	1.3	+/-0.2[nH]	1200	50[MHz]-10[GHz]
LQW15AN1N3D10	Wound	0402/1005	1.3	+/-0.5[nH]	1200	50[MHz]-10[GHz]
LQW15AN1N5B00	Wound	0402/1005	1.5	+/-0.1[nH]	1000	50[MHz]-10[GHz]
LQW15AN1N5C00	Wound	0402/1005	1.5	+/-0.2[nH]	1000	50[MHz]-10[GHz]
LQW15AN1N5D00	Wound	0402/1005	1.5	+/-0.5[nH]	1000	50[MHz]-10[GHz]
LQW15AN2N2C10	Wound	0402/1005	2.2	+/-0.2[nH]	1000	50[MHz]-10[GHz]
LQW15AN2N2D10	Wound	0402/1005	2.2	+/-0.5[nH]	1000	50[MHz]-10[GHz]
LQW15AN2N4B00	Wound	0402/1005	2.4	+/-0.1[nH]	850	50[MHz]-10[GHz]
LQW15AN2N4C00	Wound	0402/1005	2.4	+/-0.2[nH]	850	50[MHz]-10[GHz]
LQW15AN2N4D00	Wound	0402/1005	2.4	+/-0.5[nH]	850	50[MHz]-10[GHz]
LQW15AN2N4D10	Wound	0402/1005	2.4	+/-0.5[nH]	1000	50[MHz]-10[GHz]
LQW15AN2N5B00	Wound	0402/1005	2.5	+/-0.1[nH]	850	50[MHz]-10[GHz]
LQW15AN2N5C00	Wound	0402/1005	2.5	+/-0.2[nH]	850	50[MHz]-10[GHz]
LQW15AN2N5D00	Wound	0402/1005	2.5	+/-0.5[nH]	850	50[MHz]-10[GHz]
LQW15AN2N7B00	Wound	0402/1005	2.7	+/-0.1[nH]	850	50[MHz]-10[GHz]
LQW15AN2N7C00	Wound	0402/1005	2.7	+/-0.2[nH]	850	50[MHz]-10[GHz]
LQW15AN2N7D00	Wound	0402/1005	2.7	+/-0.5[nH]	850	50[MHz]-10[GHz]
LQW15AN2N9B00	Wound	0402/1005	2.9	+/-0.1[nH]	750	50[MHz]-10[GHz]
LQW15AN2N9C00	Wound	0402/1005	2.9	+/-0.2[nH]	750	50[MHz]-10[GHz]
LQW15AN2N9D00	Wound	0402/1005	2.9	+/-0.5[nH]	750	50[MHz]-10[GHz]
LQW15AN3N3D10	Wound	0402/1005	3.3	+/-0.5[nH]	900	50[MHz]-10[GHz]
LQW15AN3N4C10	Wound	0402/1005	3.4	+/-0.2[nH]	900	50[MHz]-10[GHz]
LQW15AN3N4D10	Wound	0402/1005	3.4	+/-0.5[nH]	900	50[MHz]-10[GHz]
LQW15AN3N6C10	Wound	0402/1005	3.6	+/-0.2[nH]	900	50[MHz]-10[GHz]
LQW15AN3N6D10	Wound	0402/1005	3.6	+/-0.5[nH]	900	50[MHz]-10[GHz]
LQW15AN3N9B00	Wound	0402/1005	3.9	+/-0.1[nH]	750	50[MHz]-10[GHz]



Part Number	Type	Size Code [inch/mm]	Inductance [nH]	Tolerance	Rated Current [mA]	Frequency Range
LQW15AN3N9C00	Wound	0402/1005	3.9	+/-0.2[nH]	750	50[MHz]-10[GHz]
LQW15AN3N9D00	Wound	0402/1005	3.9	+/-0.5[nH]	750	50[MHz]-10[GHz]
LQW15AN3N9D10	Wound	0402/1005	3.9	+/-0.5[nH]	900	50[MHz]-10[GHz]
LQW15AN4N1B00	Wound	0402/1005	4.1	+/-0.1[nH]	750	50[MHz]-10[GHz]
LQW15AN4N1C00	Wound	0402/1005	4.1	+/-0.2[nH]	750	50[MHz]-10[GHz]
LQW15AN4N1D00	Wound	0402/1005	4.1	+/-0.5[nH]	750	50[MHz]-10[GHz]
LQW15AN4N3B00	Wound	0402/1005	4.3	+/-0.1[nH]	750	50[MHz]-10[GHz]
LQW15AN4N3C00	Wound	0402/1005	4.3	+/-0.2[nH]	750	50[MHz]-10[GHz]
LQW15AN4N3D00	Wound	0402/1005	4.3	+/-0.5[nH]	750	50[MHz]-10[GHz]
LQW15AN4N7B00	Wound	0402/1005	4.7	+/-0.1[nH]	750	50[MHz]-10[GHz]
LQW15AN4N7C00	Wound	0402/1005	4.7	+/-0.2[nH]	750	50[MHz]-10[GHz]
LQW15AN4N7D00	Wound	0402/1005	4.7	+/-0.5[nH]	750	50[MHz]-10[GHz]
LQW15AN4N7D10	Wound	0402/1005	4.7	+/-0.5[nH]	800	50[MHz]-10[GHz]
LQW15AN5N1B00	Wound	0402/1005	5.1	+/-0.1[nH]	600	50[MHz]-10[GHz]
LQW15AN5N1C00	Wound	0402/1005	5.1	+/-0.2[nH]	600	50[MHz]-10[GHz]
LQW15AN5N1D00	Wound	0402/1005	5.1	+/-0.5[nH]	600	50[MHz]-10[GHz]
LQW15AN5N1C10	Wound	0402/1005	5.1	+/-0.2[nH]	800	50[MHz]-10[GHz]
LQW15AN5N1D10	Wound	0402/1005	5.1	+/-0.5[nH]	800	50[MHz]-10[GHz]
LQW15AN5N6C10	Wound	0402/1005	5.6	+/-0.2[nH]	800	50[MHz]-10[GHz]
LQW15AN5N6D10	Wound	0402/1005	5.6	+/-0.5[nH]	800	50[MHz]-10[GHz]
LQW15AN5N8B00	Wound	0402/1005	5.8	+/-0.1[nH]	700	50[MHz]-10[GHz]
LQW15AN5N8C00	Wound	0402/1005	5.8	+/-0.2[nH]	700	50[MHz]-10[GHz]
LQW15AN5N8D00	Wound	0402/1005	5.8	+/-0.5[nH]	700	50[MHz]-10[GHz]
LQW15AN6N2B00	Wound	0402/1005	6.2	+/-0.1[nH]	700	50[MHz]-10[GHz]
LQW15AN6N2C00	Wound	0402/1005	6.2	+/-0.2[nH]	700	50[MHz]-10[GHz]
LQW15AN6N2D00	Wound	0402/1005	6.2	+/-0.5[nH]	700	50[MHz]-10[GHz]
LQW15AN6N8G00	Wound	0402/1005	6.8	+/-2[%]	700	50[MHz]-10[GHz]
LQW15AN6N8H00	Wound	0402/1005	6.8	+/-3[%]	700	50[MHz]-10[GHz]
LQW15AN6N8J00	Wound	0402/1005	6.8	+/-5[%]	700	50[MHz]-10[GHz]
LQW15AN7N3G00	Wound	0402/1005	7.3	+/-2[%]	570	50[MHz]-10[GHz]
LQW15AN7N3H00	Wound	0402/1005	7.3	+/-3[%]	570	50[MHz]-10[GHz]
LQW15AN7N3J00	Wound	0402/1005	7.3	+/-5[%]	570	50[MHz]-10[GHz]
LQW15AN7N5G00	Wound	0402/1005	7.5	+/-2[%]	570	50[MHz]-10[GHz]
LQW15AN7N5H00	Wound	0402/1005	7.5	+/-3[%]	570	50[MHz]-10[GHz]
LQW15AN7N5J00	Wound	0402/1005	7.5	+/-5[%]	570	50[MHz]-10[GHz]
LQW15AN8N2G00	Wound	0402/1005	8.2	+/-2[%]	540	50[MHz]-10[GHz]
LQW15AN8N2H00	Wound	0402/1005	8.2	+/-3[%]	540	50[MHz]-10[GHz]
LQW15AN8N2J00	Wound	0402/1005	8.2	+/-5[%]	540	50[MHz]-10[GHz]
LQW15AN8N7G00	Wound	0402/1005	8.7	+/-2[%]	540	50[MHz]-10[GHz]
LQW15AN8N7H00	Wound	0402/1005	8.7	+/-3[%]	540	50[MHz]-10[GHz]
LQW15AN8N7J00	Wound	0402/1005	8.7	+/-5[%]	540	50[MHz]-10[GHz]
LQW15AN9N1G00	Wound	0402/1005	9.1	+/-2[%]	540	50[MHz]-10[GHz]
LQW15AN9N1H00	Wound	0402/1005	9.1	+/-3[%]	540	50[MHz]-10[GHz]
LQW15AN9N1J00	Wound	0402/1005	9.1	+/-5[%]	540	50[MHz]-10[GHz]
LQW15AN9N5G00	Wound	0402/1005	9.5	+/-2[%]	540	50[MHz]-10[GHz]
LQW15AN9N5H00	Wound	0402/1005	9.5	+/-3[%]	540	50[MHz]-10[GHz]
LQW15AN9N5J00	Wound	0402/1005	9.5	+/-5[%]	540	50[MHz]-10[GHz]
LQW15AN10NG00	Wound	0402/1005	10	+/-2[%]	500	50[MHz]-10[GHz]
LQW15AN10NH00	Wound	0402/1005	10	+/-3[%]	500	50[MHz]-10[GHz]
LQW15AN10NJ00	Wound	0402/1005	10	+/-5[%]	500	50[MHz]-10[GHz]
LQW15AN11NG00	Wound	0402/1005	11	+/-2[%]	500	50[MHz]-10[GHz]
LQW15AN11NH00	Wound	0402/1005	11	+/-3[%]	500	50[MHz]-10[GHz]
LQW15AN11NJ00	Wound	0402/1005	11	+/-5[%]	500	50[MHz]-10[GHz]
LQW15AN12NG00	Wound	0402/1005	12	+/-2[%]	500	50[MHz]-10[GHz]
LQW15AN12NH00	Wound	0402/1005	12	+/-3[%]	500	50[MHz]-10[GHz]
LQW15AN12NJ00	Wound	0402/1005	12	+/-5[%]	500	50[MHz]-10[GHz]

Part Number	Type	Size Code [inch/mm]	Inductance [nH]	Tolerance	Rated Current [mA]	Frequency Range
LQW15AN13NG00	Wound	0402/1005	13	+/-2[%]	430	50[MHz]-10[GHz]
LQW15AN13NH00	Wound	0402/1005	13	+/-3[%]	430	50[MHz]-10[GHz]
LQW15AN13NJ00	Wound	0402/1005	13	+/-5[%]	430	50[MHz]-10[GHz]
LQW15AN15NG00	Wound	0402/1005	15	+/-2[%]	460	50[MHz]-10[GHz]
LQW15AN15NH00	Wound	0402/1005	15	+/-3[%]	460	50[MHz]-10[GHz]
LQW15AN15NJ00	Wound	0402/1005	15	+/-5[%]	460	50[MHz]-10[GHz]
LQW15AN16NG00	Wound	0402/1005	16	+/-2[%]	370	50[MHz]-10[GHz]
LQW15AN16NH00	Wound	0402/1005	16	+/-3[%]	370	50[MHz]-10[GHz]
LQW15AN16NJ00	Wound	0402/1005	16	+/-5[%]	370	50[MHz]-10[GHz]
LQW15AN18NG00	Wound	0402/1005	18	+/-2[%]	370	50[MHz]-10[GHz]
LQW15AN18NH00	Wound	0402/1005	18	+/-3[%]	370	50[MHz]-10[GHz]
LQW15AN18NJ00	Wound	0402/1005	18	+/-5[%]	370	50[MHz]-10[GHz]
LQW15AN19NG00	Wound	0402/1005	19	+/-2[%]	370	50[MHz]-10[GHz]
LQW15AN19NH00	Wound	0402/1005	19	+/-3[%]	370	50[MHz]-10[GHz]
LQW15AN19NJ00	Wound	0402/1005	19	+/-5[%]	370	50[MHz]-10[GHz]
LQW15AN20NG00	Wound	0402/1005	20	+/-2[%]	370	50[MHz]-10[GHz]
LQW15AN20NH00	Wound	0402/1005	20	+/-3[%]	370	50[MHz]-10[GHz]
LQW15AN20NJ00	Wound	0402/1005	20	+/-5[%]	370	50[MHz]-10[GHz]
LQW15AN22NG00	Wound	0402/1005	22	+/-2[%]	310	50[MHz]-10[GHz]
LQW15AN22NH00	Wound	0402/1005	22	+/-3[%]	310	50[MHz]-10[GHz]
LQW15AN22NJ00	Wound	0402/1005	22	+/-5[%]	310	50[MHz]-10[GHz]
LQW15AN23NG00	Wound	0402/1005	23	+/-2[%]	310	50[MHz]-10[GHz]
LQW15AN23NH00	Wound	0402/1005	23	+/-3[%]	310	50[MHz]-10[GHz]
LQW15AN23NJ00	Wound	0402/1005	23	+/-5[%]	310	50[MHz]-10[GHz]
LQW15AN24NG00	Wound	0402/1005	24	+/-2[%]	280	50[MHz]-10[GHz]
LQW15AN24NH00	Wound	0402/1005	24	+/-3[%]	280	50[MHz]-10[GHz]
LQW15AN24NJ00	Wound	0402/1005	24	+/-5[%]	280	50[MHz]-10[GHz]
LQW15AN27NG00	Wound	0402/1005	27	+/-2[%]	280	50[MHz]-10[GHz]
LQW15AN27NH00	Wound	0402/1005	27	+/-3[%]	280	50[MHz]-10[GHz]
LQW15AN27NJ00	Wound	0402/1005	27	+/-5[%]	280	50[MHz]-10[GHz]
LQW15AN30NG00	Wound	0402/1005	30	+/-2[%]	270	50[MHz]-10[GHz]
LQW15AN30NH00	Wound	0402/1005	30	+/-3[%]	270	50[MHz]-10[GHz]
LQW15AN30NJ00	Wound	0402/1005	30	+/-5[%]	270	50[MHz]-10[GHz]
LQW15AN33NG00	Wound	0402/1005	33	+/-2[%]	260	50[MHz]-10[GHz]
LQW15AN33NH00	Wound	0402/1005	33	+/-3[%]	260	50[MHz]-10[GHz]
LQW15AN33NJ00	Wound	0402/1005	33	+/-5[%]	260	50[MHz]-10[GHz]
LQW15AN36NG00	Wound	0402/1005	36	+/-2[%]	260	50[MHz]-10[GHz]
LQW15AN36NH00	Wound	0402/1005	36	+/-3[%]	260	50[MHz]-10[GHz]
LQW15AN36NJ00	Wound	0402/1005	36	+/-5[%]	260	50[MHz]-10[GHz]
LQW15AN39NG00	Wound	0402/1005	39	+/-2[%]	250	50[MHz]-10[GHz]
LQW15AN39NH00	Wound	0402/1005	39	+/-3[%]	250	50[MHz]-10[GHz]
LQW15AN39NJ00	Wound	0402/1005	39	+/-5[%]	250	50[MHz]-10[GHz]
LQW15AN40NG00	Wound	0402/1005	40	+/-2[%]	250	50[MHz]-10[GHz]
LQW15AN40NH00	Wound	0402/1005	40	+/-3[%]	250	50[MHz]-10[GHz]
LQW15AN40NJ00	Wound	0402/1005	40	+/-5[%]	250	50[MHz]-10[GHz]
LQW15AN43NG00	Wound	0402/1005	43	+/-2[%]	250	50[MHz]-10[GHz]
LQW15AN43NH00	Wound	0402/1005	43	+/-3[%]	250	50[MHz]-10[GHz]
LQW15AN43NJ00	Wound	0402/1005	43	+/-5[%]	250	50[MHz]-10[GHz]
LQW15AN47NG00	Wound	0402/1005	47	+/-2[%]	210	50[MHz]-10[GHz]
LQW15AN47NH00	Wound	0402/1005	47	+/-3[%]	210	50[MHz]-10[GHz]
LQW15AN47NJ00	Wound	0402/1005	47	+/-5[%]	210	50[MHz]-10[GHz]
LQW15AN51NG00	Wound	0402/1005	51	+/-2[%]	210	50[MHz]-10[GHz]
LQW15AN51NH00	Wound	0402/1005	51	+/-3[%]	210	50[MHz]-10[GHz]
LQW15AN51NJ00	Wound	0402/1005	51	+/-5[%]	210	50[MHz]-10[GHz]
LQW15AN56NG00	Wound	0402/1005	56	+/-2[%]	200	50[MHz]-10[GHz]
LQW15AN56NH00	Wound	0402/1005	56	+/-3[%]	200	50[MHz]-10[GHz]

Part Number	Type	Size Code [inch/mm]	Inductance [nH]	Tolerance	Rated Current [mA]	Frequency Range
LQW15AN56NJ00	Wound	0402/1005	56	+/-5[%]	200	50[MHz]-10[GHz]
LQW15AN62NG00	Wound	0402/1005	62	+/-2[%]	145	50[MHz]-10[GHz]
LQW15AN62NH00	Wound	0402/1005	62	+/-3[%]	145	50[MHz]-10[GHz]
LQW15AN62NJ00	Wound	0402/1005	62	+/-5[%]	145	50[MHz]-10[GHz]
LQW15AN68NG00	Wound	0402/1005	68	+/-2[%]	140	50[MHz]-10[GHz]
LQW15AN68NJ00	Wound	0402/1005	68	+/-5[%]	140	50[MHz]-10[GHz]
LQW15AN72NG00	Wound	0402/1005	72	+/-2[%]	135	50[MHz]-10[GHz]
LQW15AN72NJ00	Wound	0402/1005	72	+/-5[%]	135	50[MHz]-10[GHz]
LQW15AN75NG00	Wound	0402/1005	75	+/-2[%]	135	50[MHz]-10[GHz]
LQW15AN75NJ00	Wound	0402/1005	75	+/-5[%]	135	50[MHz]-10[GHz]
LQW15AN82NG00	Wound	0402/1005	82	+/-2[%]	130	50[MHz]-10[GHz]
LQW15AN82NJ00	Wound	0402/1005	82	+/-5[%]	130	50[MHz]-10[GHz]
LQW15AN91NG00	Wound	0402/1005	91	+/-2[%]	125	50[MHz]-10[GHz]
LQW15AN91NJ00	Wound	0402/1005	91	+/-5[%]	125	50[MHz]-10[GHz]
LQW15ANR10J00	Wound	0402/1005	100	+/-5[%]	120	50[MHz]-10[GHz]
LQW15ANR12J00	Wound	0402/1005	120	+/-5[%]	110	50[MHz]-10[GHz]
LQW18AN2N2D00	Wound	0603/1608	2.2	+/-0.5[nH]	700	50[MHz]-10[GHz]
LQW18AN3N6C00	Wound	0603/1608	3.6	+/-0.2[nH]	850	50[MHz]-10[GHz]
LQW18AN3N6D00	Wound	0603/1608	3.6	+/-0.5[nH]	850	50[MHz]-10[GHz]
LQW18AN3N9C00	Wound	0603/1608	3.9	+/-0.2[nH]	850	50[MHz]-10[GHz]
LQW18AN3N9D00	Wound	0603/1608	3.9	+/-0.5[nH]	850	50[MHz]-10[GHz]
LQW18AN4N3C00	Wound	0603/1608	4.3	+/-0.2[nH]	850	50[MHz]-10[GHz]
LQW18AN4N3D00	Wound	0603/1608	4.3	+/-0.5[nH]	850	50[MHz]-10[GHz]
LQW18AN4N7D00	Wound	0603/1608	4.7	+/-0.5[nH]	850	50[MHz]-10[GHz]
LQW18AN5N6C00	Wound	0603/1608	5.6	+/-0.2[nH]	750	50[MHz]-10[GHz]
LQW18AN5N6D00	Wound	0603/1608	5.6	+/-0.5[nH]	750	50[MHz]-10[GHz]
LQW18AN6N2C00	Wound	0603/1608	6.2	+/-0.2[nH]	750	50[MHz]-10[GHz]
LQW18AN6N2D00	Wound	0603/1608	6.2	+/-0.5[nH]	750	50[MHz]-10[GHz]
LQW18AN6N8C00	Wound	0603/1608	6.8	+/-0.2[nH]	750	50[MHz]-10[GHz]
LQW18AN6N8D00	Wound	0603/1608	6.8	+/-0.5[nH]	750	50[MHz]-10[GHz]
LQW18AN7N5C00	Wound	0603/1608	7.5	+/-0.2[nH]	750	50[MHz]-10[GHz]
LQW18AN7N5D00	Wound	0603/1608	7.5	+/-0.5[nH]	750	50[MHz]-10[GHz]
LQW18AN8N2C00	Wound	0603/1608	8.2	+/-0.2[nH]	650	50[MHz]-10[GHz]
LQW18AN8N2D00	Wound	0603/1608	8.2	+/-0.5[nH]	650	50[MHz]-10[GHz]
LQW18AN8N7C00	Wound	0603/1608	8.7	+/-0.2[nH]	650	50[MHz]-10[GHz]
LQW18AN8N7D00	Wound	0603/1608	8.7	+/-0.5[nH]	650	50[MHz]-10[GHz]
LQW18AN9N1C00	Wound	0603/1608	9.1	+/-0.2[nH]	650	50[MHz]-10[GHz]
LQW18AN9N1D00	Wound	0603/1608	9.1	+/-0.5[nH]	650	50[MHz]-10[GHz]
LQW18AN9N5D00	Wound	0603/1608	9.5	+/-0.5[nH]	650	50[MHz]-10[GHz]
LQW18AN10NG00	Wound	0603/1608	10	+/-2[%]	650	50[MHz]-10[GHz]
LQW18AN10NJ00	Wound	0603/1608	10	+/-5[%]	650	50[MHz]-10[GHz]
LQW18AN11NG00	Wound	0603/1608	11	+/-2[%]	650	50[MHz]-10[GHz]
LQW18AN11NJ00	Wound	0603/1608	11	+/-5[%]	650	50[MHz]-10[GHz]
LQW18AN12NG00	Wound	0603/1608	12	+/-2[%]	600	50[MHz]-10[GHz]
LQW18AN12NJ00	Wound	0603/1608	12	+/-5[%]	600	50[MHz]-10[GHz]
LQW18AN13NG00	Wound	0603/1608	13	+/-2[%]	600	50[MHz]-10[GHz]
LQW18AN13NJ00	Wound	0603/1608	13	+/-5[%]	600	50[MHz]-10[GHz]
LQW18AN15NG00	Wound	0603/1608	15	+/-2[%]	600	50[MHz]-10[GHz]
LQW18AN15NJ00	Wound	0603/1608	15	+/-5[%]	600	50[MHz]-10[GHz]
LQW18AN16NG00	Wound	0603/1608	16	+/-2[%]	550	50[MHz]-10[GHz]
LQW18AN16NJ00	Wound	0603/1608	16	+/-5[%]	550	50[MHz]-10[GHz]
LQW18AN18NG00	Wound	0603/1608	18	+/-2[%]	550	50[MHz]-10[GHz]
LQW18AN18NJ00	Wound	0603/1608	18	+/-5[%]	550	50[MHz]-10[GHz]
LQW18AN20NG00	Wound	0603/1608	20	+/-2[%]	550	50[MHz]-10[GHz]
LQW18AN20NJ00	Wound	0603/1608	20	+/-5[%]	550	50[MHz]-10[GHz]
LQW18AN22NG00	Wound	0603/1608	22	+/-2[%]	500	50[MHz]-10[GHz]

Part Number	Type	Size Code [inch/mm]	Inductance [nH]	Tolerance	Rated Current [mA]	Frequency Range
LQW18AN22NJ00	Wound	0603/1608	22	+/-5[%]	500	50[MHz]-10[GHz]
LQW18AN24NG00	Wound	0603/1608	24	+/-2[%]	500	50[MHz]-10[GHz]
LQW18AN24NJ00	Wound	0603/1608	24	+/-5[%]	500	50[MHz]-10[GHz]
LQW18AN27NG00	Wound	0603/1608	27	+/-2[%]	440	50[MHz]-10[GHz]
LQW18AN27NJ00	Wound	0603/1608	27	+/-5[%]	440	50[MHz]-10[GHz]
LQW18AN30NG00	Wound	0603/1608	30	+/-2[%]	420	50[MHz]-10[GHz]
LQW18AN30NJ00	Wound	0603/1608	30	+/-5[%]	420	50[MHz]-10[GHz]
LQW18AN33NG00	Wound	0603/1608	33	+/-2[%]	420	50[MHz]-10[GHz]
LQW18AN33NJ00	Wound	0603/1608	33	+/-5[%]	420	50[MHz]-10[GHz]
LQW18AN36NG00	Wound	0603/1608	36	+/-2[%]	400	50[MHz]-10[GHz]
LQW18AN36NJ00	Wound	0603/1608	36	+/-5[%]	400	50[MHz]-10[GHz]
LQW18AN39NG00	Wound	0603/1608	39	+/-2[%]	400	50[MHz]-10[GHz]
LQW18AN39NJ00	Wound	0603/1608	39	+/-5[%]	400	50[MHz]-10[GHz]
LQW18AN43NG00	Wound	0603/1608	43	+/-2[%]	380	50[MHz]-10[GHz]
LQW18AN43NJ00	Wound	0603/1608	43	+/-5[%]	380	50[MHz]-10[GHz]
LQW18AN47NG00	Wound	0603/1608	47	+/-2[%]	380	50[MHz]-10[GHz]
LQW18AN47NJ00	Wound	0603/1608	47	+/-5[%]	380	50[MHz]-10[GHz]
LQW18AN51NG00	Wound	0603/1608	51	+/-2[%]	370	50[MHz]-10[GHz]
LQW18AN51NJ00	Wound	0603/1608	51	+/-5[%]	370	50[MHz]-10[GHz]
LQW18AN56NG00	Wound	0603/1608	56	+/-2[%]	360	50[MHz]-10[GHz]
LQW18AN56NJ00	Wound	0603/1608	56	+/-5[%]	360	50[MHz]-10[GHz]
LQW18AN62NG00	Wound	0603/1608	62	+/-2[%]	280	50[MHz]-10[GHz]
LQW18AN62NJ00	Wound	0603/1608	62	+/-5[%]	280	50[MHz]-10[GHz]
LQW18AN68NG00	Wound	0603/1608	68	+/-2[%]	340	50[MHz]-10[GHz]
LQW18AN68NJ00	Wound	0603/1608	68	+/-5[%]	340	50[MHz]-10[GHz]
LQW18AN72NG00	Wound	0603/1608	72	+/-2[%]	270	50[MHz]-10[GHz]
LQW18AN72NJ00	Wound	0603/1608	72	+/-5[%]	270	50[MHz]-10[GHz]
LQW18AN75NG00	Wound	0603/1608	75	+/-2[%]	270	50[MHz]-10[GHz]
LQW18AN75NJ00	Wound	0603/1608	75	+/-5[%]	270	50[MHz]-10[GHz]
LQW18AN82NG00	Wound	0603/1608	82	+/-2[%]	250	50[MHz]-10[GHz]
LQW18AN82NJ00	Wound	0603/1608	82	+/-5[%]	250	50[MHz]-10[GHz]
LQW18AN91NG00	Wound	0603/1608	91	+/-2[%]	230	50[MHz]-10[GHz]
LQW18AN91NJ00	Wound	0603/1608	91	+/-5[%]	230	50[MHz]-10[GHz]
LQW18ANR10G00	Wound	0603/1608	100	+/-2[%]	220	50[MHz]-10[GHz]
LQW18ANR10J00	Wound	0603/1608	100	+/-5[%]	220	50[MHz]-10[GHz]
LQW18ANR11G00	Wound	0603/1608	110	+/-2[%]	200	50[MHz]-10[GHz]
LQW18ANR11J00	Wound	0603/1608	110	+/-5[%]	200	50[MHz]-10[GHz]
LQW18ANR12G00	Wound	0603/1608	120	+/-2[%]	180	50[MHz]-10[GHz]
LQW18ANR12J00	Wound	0603/1608	120	+/-5[%]	180	50[MHz]-10[GHz]
LQW18ANR15G00	Wound	0603/1608	150	+/-2[%]	160	50[MHz]-10[GHz]
LQW18ANR15J00	Wound	0603/1608	150	+/-5[%]	160	50[MHz]-10[GHz]
LQW18ANR16G00	Wound	0603/1608	160	+/-2[%]	150	50[MHz]-10[GHz]
LQW18ANR16J00	Wound	0603/1608	160	+/-5[%]	150	50[MHz]-10[GHz]
LQW18ANR18G00	Wound	0603/1608	180	+/-2[%]	140	50[MHz]-10[GHz]
LQW18ANR18J00	Wound	0603/1608	180	+/-5[%]	140	50[MHz]-10[GHz]
LQW18ANR20G00	Wound	0603/1608	200	+/-2[%]	120	50[MHz]-10[GHz]
LQW18ANR20J00	Wound	0603/1608	200	+/-5[%]	120	50[MHz]-10[GHz]
LQW18ANR22G00	Wound	0603/1608	220	+/-2[%]	120	50[MHz]-10[GHz]
LQW18ANR22J00	Wound	0603/1608	220	+/-5[%]	120	50[MHz]-10[GHz]
LQW18ANR27G00	Wound	0603/1608	270	+/-2[%]	110	50[MHz]-10[GHz]
LQW18ANR27J00	Wound	0603/1608	270	+/-5[%]	110	50[MHz]-10[GHz]
LQW18ANR33G00	Wound	0603/1608	330	+/-2[%]	85	50[MHz]-10[GHz]
LQW18ANR33J00	Wound	0603/1608	330	+/-5[%]	85	50[MHz]-10[GHz]
LQW18ANR39G00	Wound	0603/1608	390	+/-2[%]	80	50[MHz]-10[GHz]
LQW18ANR39J00	Wound	0603/1608	390	+/-5[%]	80	50[MHz]-10[GHz]
LQW18ANR47G00	Wound	0603/1608	470	+/-2[%]	75	50[MHz]-10[GHz]

Part Number	Type	Size Code [inch/mm]	Inductance [nH]	Tolerance	Rated Current [mA]	Frequency Range
LQW18ANR47J00	Wound	0603/1608	470	+/-5[%]	75	50[MHz]-10[GHz]