

| Part Number | Type or Use | SizeCode (EIA) | Temp Characteristics (EIA) | Rated Voltage [V] | Capacitance [pF] | Tolerance | Frequency Range |
|-------------------|------------------|----------------|----------------------------|-------------------|------------------|-------------|------------------|
| GRM0225C1CR50BD01 | Ultra-small type | 01005 | C0G | 16 | 0.5 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1CR75BD01 | Ultra-small type | 01005 | C0G | 16 | 0.75 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C1R0BD01 | Ultra-small type | 01005 | C0G | 16 | 1 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C1R1BD01 | Ultra-small type | 01005 | C0G | 16 | 1.1 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C1R2BD01 | Ultra-small type | 01005 | C0G | 16 | 1.2 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C1R3BD01 | Ultra-small type | 01005 | C0G | 16 | 1.3 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C1R5BD01 | Ultra-small type | 01005 | C0G | 16 | 1.5 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C1R6BD01 | Ultra-small type | 01005 | C0G | 16 | 1.6 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C1R8BD01 | Ultra-small type | 01005 | C0G | 16 | 1.8 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C2R0BD01 | Ultra-small type | 01005 | C0G | 16 | 2 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C2R5BD01 | Ultra-small type | 01005 | C0G | 16 | 2.2 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C2R4BD01 | Ultra-small type | 01005 | C0G | 16 | 2.4 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C2R7BD01 | Ultra-small type | 01005 | C0G | 16 | 2.7 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C3R0BD01 | Ultra-small type | 01005 | C0G | 16 | 3 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C3R5BD01 | Ultra-small type | 01005 | C0G | 16 | 3.3 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C3R6BD01 | Ultra-small type | 01005 | C0G | 16 | 3.6 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C3R9BD01 | Ultra-small type | 01005 | C0G | 16 | 3.9 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C4R3BD01 | Ultra-small type | 01005 | C0G | 16 | 4.3 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C4R7BD01 | Ultra-small type | 01005 | C0G | 16 | 4.7 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C5R1BD01 | Ultra-small type | 01005 | C0G | 16 | 5.1 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C5R6BD01 | Ultra-small type | 01005 | C0G | 16 | 5.6 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C6R2BD01 | Ultra-small type | 01005 | C0G | 16 | 6.2 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C6R8BD01 | Ultra-small type | 01005 | C0G | 16 | 6.8 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C7R5BD01 | Ultra-small type | 01005 | C0G | 16 | 7.5 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C8R2BD01 | Ultra-small type | 01005 | C0G | 16 | 8.2 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C9R1BD01 | Ultra-small type | 01005 | C0G | 16 | 9.1 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0225C1C100GD01 | Ultra-small type | 01005 | C0G | 16 | 10 | +/-2[%] | 300[kHz]-20[GHz] |
| GRM0225C1C110JD01 | Ultra-small type | 01005 | C0G | 16 | 11 | +/-5[%] | 300[kHz]-20[GHz] |
| GRM0225C1C120JD01 | Ultra-small type | 01005 | C0G | 16 | 12 | +/-5[%] | 300[kHz]-20[GHz] |
| GRM0225C1C130JD01 | Ultra-small type | 01005 | C0G | 16 | 13 | +/-5[%] | 300[kHz]-20[GHz] |
| GRM0225C1C150JD01 | Ultra-small type | 01005 | C0G | 16 | 15 | +/-5[%] | 300[kHz]-20[GHz] |
| GRM0225C1C180JD01 | Ultra-small type | 01005 | C0G | 16 | 18 | +/-5[%] | 300[kHz]-20[GHz] |
| GRM0225C1C200JD01 | Ultra-small type | 01005 | C0G | 16 | 20 | +/-5[%] | 300[kHz]-20[GHz] |
| GRM0225C1C220JD01 | Ultra-small type | 01005 | C0G | 16 | 22 | +/-5[%] | 300[kHz]-20[GHz] |
| GRM0225C1C270JD01 | Ultra-small type | 01005 | C0G | 16 | 27 | +/-5[%] | 300[kHz]-20[GHz] |
| GRM0225C1C330JD01 | Ultra-small type | 01005 | C0G | 16 | 33 | +/-5[%] | 300[kHz]-20[GHz] |
| GRM0225C1C390JD01 | Ultra-small type | 01005 | C0G | 16 | 39 | +/-5[%] | 300[kHz]-20[GHz] |
| GRM0225C1C470JD01 | Ultra-small type | 01005 | C0G | 16 | 47 | +/-5[%] | 300[kHz]-20[GHz] |
| GRM0335C1HR50BD01 | Ultra-small type | 0201 | C0G | 50 | 0.5 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0335C1ER50CZ01 | Ultra-small type | 0201 | C0G | 25 | 0.5 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1ER75CZ01 | Ultra-small type | 0201 | C0G | 25 | 0.75 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1H1R0BD01 | Ultra-small type | 0201 | C0G | 50 | 1 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E1R0CD01 | Ultra-small type | 0201 | C0G | 25 | 1 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E1R1CD01 | Ultra-small type | 0201 | C0G | 25 | 1.1 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E1R2CD01 | Ultra-small type | 0201 | C0G | 25 | 1.2 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E1R3CD01 | Ultra-small type | 0201 | C0G | 25 | 1.3 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E1R5CD01 | Ultra-small type | 0201 | C0G | 25 | 1.5 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E1R6CD01 | Ultra-small type | 0201 | C0G | 25 | 1.6 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E1R8CD01 | Ultra-small type | 0201 | C0G | 25 | 1.8 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1H2R0BD01 | Ultra-small type | 0201 | C0G | 50 | 2 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E2R0CD01 | Ultra-small type | 0201 | C0G | 25 | 2 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E2R2CD01 | Ultra-small type | 0201 | C0G | 25 | 2.2 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E2R4CD01 | Ultra-small type | 0201 | C0G | 25 | 2.4 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E2R5CD01 | Ultra-small type | 0201 | C0G | 25 | 2.5 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1H3R0BD01 | Ultra-small type | 0201 | C0G | 50 | 3 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E3R0CD01 | Ultra-small type | 0201 | C0G | 25 | 3 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E3R3CD01 | Ultra-small type | 0201 | C0G | 25 | 3.3 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E3R6CD01 | Ultra-small type | 0201 | C0G | 25 | 3.6 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E3R9CD01 | Ultra-small type | 0201 | C0G | 25 | 3.9 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1H4R0BD01 | Ultra-small type | 0201 | C0G | 50 | 4 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E4R0CD01 | Ultra-small type | 0201 | C0G | 25 | 4 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E4R3CD01 | Ultra-small type | 0201 | C0G | 25 | 4.3 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E4R7CD01 | Ultra-small type | 0201 | C0G | 25 | 4.7 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1H5R0BD01 | Ultra-small type | 0201 | C0G | 50 | 5 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E5R0CD01 | Ultra-small type | 0201 | C0G | 25 | 5 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E5R1DD01 | Ultra-small type | 0201 | C0G | 25 | 5.1 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E5R6DD01 | Ultra-small type | 0201 | C0G | 25 | 5.6 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GRM0335C1H6R0BD01 | Ultra-small type | 0201 | C0G | 50 | 6 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E6R0DD01 | Ultra-small type | 0201 | C0G | 25 | 6 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E6R2DD01 | Ultra-small type | 0201 | C0G | 25 | 6.2 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E6R8DD01 | Ultra-small type | 0201 | C0G | 25 | 6.8 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GRM0335C1H7R0BD01 | Ultra-small type | 0201 | C0G | 50 | 7 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E7R0DD01 | Ultra-small type | 0201 | C0G | 25 | 7 | +/-0.5[pF] | 300[kHz]-20[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Temp Characteristics (EIA) | Rated Voltage [V] | Capacitance [pF] | Tolerance | Frequency Range |
|-------------------|------------------|----------------|----------------------------|-------------------|------------------|------------|------------------|
| GRM0335C1E7R5DD01 | Ultra-small type | 0201 | C0G | 25 | 7.5 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GRM0335C1H8R0BD01 | Ultra-small type | 0201 | C0G | 50 | 8 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E8R0DD01 | Ultra-small type | 0201 | C0G | 25 | 8 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E8R2DD01 | Ultra-small type | 0201 | C0G | 25 | 8.2 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GRM0335C1H9R0BD01 | Ultra-small type | 0201 | C0G | 50 | 9 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E9R0DD01 | Ultra-small type | 0201 | C0G | 25 | 9 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GRM0335C1E9R1DD01 | Ultra-small type | 0201 | C0G | 25 | 9.1 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GRM0335C1H100JD01 | Ultra-small type | 0201 | C0G | 50 | 10 | +/-5[%] | 300[kHz]-20[GHz] |
| GRM0335C1E100JD01 | Ultra-small type | 0201 | C0G | 25 | 10 | +/-5[%] | 300[kHz]-20[GHz] |
| GRM0335C1E110JD01 | Ultra-small type | 0201 | C0G | 25 | 11 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E120JD01 | Ultra-small type | 0201 | C0G | 25 | 12 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E130JD01 | Ultra-small type | 0201 | C0G | 25 | 13 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E140JD01 | Ultra-small type | 0201 | C0G | 25 | 14 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1H150JD01 | Ultra-small type | 0201 | C0G | 50 | 15 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E150JD01 | Ultra-small type | 0201 | C0G | 25 | 15 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E160JD01 | Ultra-small type | 0201 | C0G | 25 | 16 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E180JD01 | Ultra-small type | 0201 | C0G | 25 | 18 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E200JD01 | Ultra-small type | 0201 | C0G | 25 | 20 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1H220JD01 | Ultra-small type | 0201 | C0G | 50 | 22 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E220JD01 | Ultra-small type | 0201 | C0G | 25 | 22 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E240JD01 | Ultra-small type | 0201 | C0G | 25 | 24 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E270JD01 | Ultra-small type | 0201 | C0G | 25 | 27 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E300JD01 | Ultra-small type | 0201 | C0G | 25 | 30 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1H330JD01 | Ultra-small type | 0201 | C0G | 50 | 33 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E330JD01 | Ultra-small type | 0201 | C0G | 25 | 33 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E360JD01 | Ultra-small type | 0201 | C0G | 25 | 36 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E390JD01 | Ultra-small type | 0201 | C0G | 25 | 39 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E430JD01 | Ultra-small type | 0201 | C0G | 25 | 43 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1H470JD01 | Ultra-small type | 0201 | C0G | 50 | 47 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E470JD01 | Ultra-small type | 0201 | C0G | 25 | 47 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E510JD01 | Ultra-small type | 0201 | C0G | 25 | 51 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E560JD01 | Ultra-small type | 0201 | C0G | 25 | 56 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E620JD01 | Ultra-small type | 0201 | C0G | 25 | 62 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1H680JD01 | Ultra-small type | 0201 | C0G | 50 | 68 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E680JD01 | Ultra-small type | 0201 | C0G | 25 | 68 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E750JD01 | Ultra-small type | 0201 | C0G | 25 | 75 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E820JD01 | Ultra-small type | 0201 | C0G | 25 | 82 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E910JD01 | Ultra-small type | 0201 | C0G | 25 | 91 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1H101JD01 | Ultra-small type | 0201 | C0G | 50 | 100 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM0335C1E101JD01 | Ultra-small type | 0201 | C0G | 25 | 100 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM033R71E101KA01 | Ultra-small type | 0201 | X7R | 25 | 100 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71C101KD01 | Ultra-small type | 0201 | X7R | 16 | 100 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71E121KA01 | Ultra-small type | 0201 | X7R | 25 | 120 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71C121KD01 | Ultra-small type | 0201 | X7R | 16 | 120 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71E151KA01 | Ultra-small type | 0201 | X7R | 25 | 150 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71C151KD01 | Ultra-small type | 0201 | X7R | 16 | 150 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71E181KA01 | Ultra-small type | 0201 | X7R | 25 | 180 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71C181KD01 | Ultra-small type | 0201 | X7R | 16 | 180 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71E221KA01 | Ultra-small type | 0201 | X7R | 25 | 220 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71C221KD01 | Ultra-small type | 0201 | X7R | 16 | 220 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71E271KA01 | Ultra-small type | 0201 | X7R | 25 | 270 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71C271KD01 | Ultra-small type | 0201 | X7R | 16 | 270 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71E331KA01 | Ultra-small type | 0201 | X7R | 25 | 330 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71C331KD01 | Ultra-small type | 0201 | X7R | 16 | 330 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71E391KA01 | Ultra-small type | 0201 | X7R | 25 | 390 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71C391KD01 | Ultra-small type | 0201 | X7R | 16 | 390 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71E471KA01 | Ultra-small type | 0201 | X7R | 25 | 470 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71C471KD01 | Ultra-small type | 0201 | X7R | 16 | 470 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71E561KA01 | Ultra-small type | 0201 | X7R | 25 | 560 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71C561KD01 | Ultra-small type | 0201 | X7R | 16 | 560 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71E681KA01 | Ultra-small type | 0201 | X7R | 25 | 680 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71C681KD01 | Ultra-small type | 0201 | X7R | 16 | 680 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71E821KA01 | Ultra-small type | 0201 | X7R | 25 | 820 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71C821KD01 | Ultra-small type | 0201 | X7R | 16 | 820 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71E102KA01 | Ultra-small type | 0201 | X7R | 25 | 1000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71C102KD01 | Ultra-small type | 0201 | X7R | 16 | 1000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71E122KA01 | Ultra-small type | 0201 | X7R | 25 | 1200 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71E152KA01 | Ultra-small type | 0201 | X7R | 25 | 1500 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71A152KA01 | Ultra-small type | 0201 | X7R | 10 | 1500 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R70J152KA01 | Ultra-small type | 0201 | X7R | 6.3 | 1500 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71C222KA88 | Ultra-small type | 0201 | X7R | 16 | 2200 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71A222KA01 | Ultra-small type | 0201 | X7R | 10 | 2200 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R70J222KA01 | Ultra-small type | 0201 | X7R | 6.3 | 2200 | +/-10[%] | 30[kHz]-6[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Temp Characteristics (EIA) | Rated Voltage [V] | Capacitance [pF] | Tolerance | Frequency Range |
|-------------------|----------------------------------|----------------|----------------------------|-------------------|------------------|---------------|------------------|
| GRM033R71C332KA88 | Ultra-small type | 0201 | X7R | 16 | 3300 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71A332KA01 | Ultra-small type | 0201 | X7R | 10 | 3300 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R70J332KA01 | Ultra-small type | 0201 | X7R | 6.3 | 3300 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71A472KA01 | Ultra-small type | 0201 | X7R | 10 | 4700 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R70J472KA01 | Ultra-small type | 0201 | X7R | 6.3 | 4700 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71A682KA01 | Ultra-small type | 0201 | X7R | 10 | 6800 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R70J682KA01 | Ultra-small type | 0201 | X7R | 6.3 | 6800 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R71A103KA01 | Ultra-small type | 0201 | X7R | 10 | 10000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R70J103KA01 | Ultra-small type | 0201 | X7R | 6.3 | 10000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033C80J123KE01 | Ultra-small type | 0201 | X6S | 6.3 | 12000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033C80J153KE01 | Ultra-small type | 0201 | X6S | 6.3 | 15000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033C80J223KE01 | Ultra-small type | 0201 | X6S | 6.3 | 22000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033C80J333KE01 | Ultra-small type | 0201 | X6S | 6.3 | 33000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033C80J393KE19 | Ultra-small type | 0201 | X6S | 6.3 | 39000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033C80J473KE19 | Ultra-small type | 0201 | X6S | 6.3 | 47000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033C80G104KE19 | Ultra-small type | 0201 | X6S | 4 | 100000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R61A122KA01 | Ultra-small type | 0201 | X5R | 10 | 1200 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R61A152KA01 | Ultra-small type | 0201 | X5R | 10 | 1500 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R61A182KA01 | Ultra-small type | 0201 | X5R | 10 | 1800 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R61A222KA01 | Ultra-small type | 0201 | X5R | 10 | 2200 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R61A332KA01 | Ultra-small type | 0201 | X5R | 10 | 3300 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R61A472KA01 | Ultra-small type | 0201 | X5R | 10 | 4700 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R61A682KA01 | Ultra-small type | 0201 | X5R | 10 | 6800 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R61A103KA01 | Ultra-small type | 0201 | X5R | 10 | 10000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R60J153KE01 | Ultra-small type | 0201 | X5R | 6.3 | 15000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R60J223KE01 | Ultra-small type | 0201 | X5R | 6.3 | 22000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R60J333KE01 | Ultra-small type | 0201 | X5R | 6.3 | 33000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R60J683KE19 | Ultra-small type | 0201 | X5R | 6.3 | 68000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033R60J104KE19 | Ultra-small type | 0201 | X5R | 6.3 | 100000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM033F51A152ZD01 | Ultra-small type | 0201 | Y5V | 10 | 1500 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM033F51A222ZD01 | Ultra-small type | 0201 | Y5V | 10 | 2200 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM033F51A332ZD01 | Ultra-small type | 0201 | Y5V | 10 | 3300 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM033F51A472ZD01 | Ultra-small type | 0201 | Y5V | 10 | 4700 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM033F51A682ZD01 | Ultra-small type | 0201 | Y5V | 10 | 6800 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM033F51A103ZD01 | Ultra-small type | 0201 | Y5V | 10 | 10000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM0335C1HR20BD01 | Tight Tolerance | 0201 | C0G | 50 | 0.2 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0335C1ER20BZ01 | Tight Tolerance | 0201 | C0G | 25 | 0.2 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM0335C1ER30CZ01 | Tight Tolerance | 0201 | C0G | 25 | 0.3 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1ER40CZ01 | Tight Tolerance | 0201 | C0G | 25 | 0.4 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1ER60CZ01 | Tight Tolerance | 0201 | C0G | 25 | 0.6 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1ER70CZ01 | Tight Tolerance | 0201 | C0G | 25 | 0.7 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1ER80CZ01 | Tight Tolerance | 0201 | C0G | 25 | 0.8 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM0335C1ER90CZ01 | Tight Tolerance | 0201 | C0G | 25 | 0.9 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1HR20BZ01 | Tight Tolerance | 0402 | C0G | 50 | 0.2 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM1555C1HR30CZ01 | Tight Tolerance | 0402 | C0G | 50 | 0.3 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1HR40CZ01 | Tight Tolerance | 0402 | C0G | 50 | 0.4 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1HR60CZ01 | Tight Tolerance | 0402 | C0G | 50 | 0.6 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1HR70CZ01 | Tight Tolerance | 0402 | C0G | 50 | 0.7 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1HR80CZ01 | Tight Tolerance | 0402 | C0G | 50 | 0.8 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1HR90CZ01 | Tight Tolerance | 0402 | C0G | 50 | 0.9 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1HR50BZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 0.5 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GRM1555C1HR50CZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 0.5 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1HR75CZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 0.75 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1H1R0CZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 1 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1H1R1CZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 1.1 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1H1R2CZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 1.2 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1H1R3CZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 1.3 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1H1R5CZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 1.5 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1H1R6CZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 1.6 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1H1R8CZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 1.8 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1H2R0CZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 2 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1H2R2CZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 2.2 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1H2R4CZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 2.4 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1H2R7CZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 2.7 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1H3R0CZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 3 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1H3R3CZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 3.3 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1H3R6CZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 3.6 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1H3R9CZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 3.9 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1H4R0CZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 4 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1H4R3CZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 4.3 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1H4R7CZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 4.7 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1H5R0CZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 5 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1555C1H5R1CZ01 | for General Electronic Equipment | 0402 | C0G | 50 | 5.1 | +/-0.25[pF] | 300[kHz]-20[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Temp Characteristics (EIA) | Rated Voltage [V] | Capacitance [pF] | Tolerance | Frequency Range |
|-------------------|----------------------------------|----------------|----------------------------|-------------------|------------------|---------------|-----------------|
| GRM155R71H681KA01 | for General Electronic Equipment | 0402 | X7R | 50 | 680 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71H821KA01 | for General Electronic Equipment | 0402 | X7R | 50 | 820 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R72A102KA01 | for General Electronic Equipment | 0402 | X7R | 100 | 1000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71H102KA01 | for General Electronic Equipment | 0402 | X7R | 50 | 1000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71H122KA01 | for General Electronic Equipment | 0402 | X7R | 50 | 1200 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71H152KA01 | for General Electronic Equipment | 0402 | X7R | 50 | 1500 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71H182KA01 | for General Electronic Equipment | 0402 | X7R | 50 | 1800 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R72A222KA01 | for General Electronic Equipment | 0402 | X7R | 100 | 2200 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71H222KA01 | for General Electronic Equipment | 0402 | X7R | 50 | 2200 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71H272KA01 | for General Electronic Equipment | 0402 | X7R | 50 | 2700 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71H332KA01 | for General Electronic Equipment | 0402 | X7R | 50 | 3300 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71H392KA01 | for General Electronic Equipment | 0402 | X7R | 50 | 3900 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R72A472KA01 | for General Electronic Equipment | 0402 | X7R | 100 | 4700 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71E472KA01 | for General Electronic Equipment | 0402 | X7R | 25 | 4700 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71E562KA01 | for General Electronic Equipment | 0402 | X7R | 25 | 5600 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71H682KA88 | for General Electronic Equipment | 0402 | X7R | 50 | 6800 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71E682KA01 | for General Electronic Equipment | 0402 | X7R | 25 | 6800 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71C822KA01 | for General Electronic Equipment | 0402 | X7R | 16 | 8200 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71H103KA88 | for General Electronic Equipment | 0402 | X7R | 50 | 10000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71E103KA01 | for General Electronic Equipment | 0402 | X7R | 25 | 10000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71C103KA01 | for General Electronic Equipment | 0402 | X7R | 16 | 10000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71C123KA01 | for General Electronic Equipment | 0402 | X7R | 16 | 12000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71H153KA12 | for General Electronic Equipment | 0402 | X7R | 50 | 15000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71E153KA61 | for General Electronic Equipment | 0402 | X7R | 25 | 15000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71C153KA01 | for General Electronic Equipment | 0402 | X7R | 16 | 15000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71C183KA01 | for General Electronic Equipment | 0402 | X7R | 16 | 18000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71H233KA12 | for General Electronic Equipment | 0402 | X7R | 50 | 22000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71E223KA61 | for General Electronic Equipment | 0402 | X7R | 25 | 22000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71C223KA01 | for General Electronic Equipment | 0402 | X7R | 16 | 22000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71A273KA01 | for General Electronic Equipment | 0402 | X7R | 10 | 27000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71E333KA88 | for General Electronic Equipment | 0402 | X7R | 25 | 33000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71C333KA01 | for General Electronic Equipment | 0402 | X7R | 16 | 33000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71A333KA01 | for General Electronic Equipment | 0402 | X7R | 10 | 33000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71A393KA01 | for General Electronic Equipment | 0402 | X7R | 10 | 39000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71E473KA88 | for General Electronic Equipment | 0402 | X7R | 25 | 47000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71C473KA01 | for General Electronic Equipment | 0402 | X7R | 16 | 47000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71A473KA01 | for General Electronic Equipment | 0402 | X7R | 10 | 47000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71C683KA88 | for General Electronic Equipment | 0402 | X7R | 16 | 68000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R71C104KA88 | for General Electronic Equipment | 0402 | X7R | 16 | 100000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155C80J154KE01 | for General Electronic Equipment | 0402 | X6S | 6.3 | 150000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155C80J224KE01 | for General Electronic Equipment | 0402 | X6S | 6.3 | 220000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155C80J334KE01 | for General Electronic Equipment | 0402 | X6S | 6.3 | 330000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155C80J474KE19 | for General Electronic Equipment | 0402 | X6S | 6.3 | 470000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155C80G474KE01 | for General Electronic Equipment | 0402 | X6S | 4 | 470000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155C80G684KE19 | for General Electronic Equipment | 0402 | X6S | 4 | 680000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155C80G105KE19 | for General Electronic Equipment | 0402 | X6S | 4 | 1000000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R61H102KA01 | for General Electronic Equipment | 0402 | X5R | 50 | 1000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R61H222KA01 | for General Electronic Equipment | 0402 | X5R | 50 | 2200 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R61H472KA01 | for General Electronic Equipment | 0402 | X5R | 50 | 4700 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R61A563KA01 | for General Electronic Equipment | 0402 | X5R | 10 | 56000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R61A683KA01 | for General Electronic Equipment | 0402 | X5R | 10 | 68000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R61A823KA01 | for General Electronic Equipment | 0402 | X5R | 10 | 82000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R61C104KA88 | for General Electronic Equipment | 0402 | X5R | 16 | 100000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R61A104KA01 | for General Electronic Equipment | 0402 | X5R | 10 | 100000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R61A124KE19 | for General Electronic Equipment | 0402 | X5R | 10 | 120000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R61A154KE19 | for General Electronic Equipment | 0402 | X5R | 10 | 150000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R60J154KE01 | for General Electronic Equipment | 0402 | X5R | 6.3 | 150000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R61A224KE19 | for General Electronic Equipment | 0402 | X5R | 10 | 220000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R60J224KE01 | for General Electronic Equipment | 0402 | X5R | 6.3 | 220000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R61A334KE15 | for General Electronic Equipment | 0402 | X5R | 10 | 330000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R60J334KE01 | for General Electronic Equipment | 0402 | X5R | 6.3 | 330000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R60J394KE19 | for General Electronic Equipment | 0402 | X5R | 6.3 | 390000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R61A474KE15 | for General Electronic Equipment | 0402 | X5R | 10 | 470000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R60J474KE19 | for General Electronic Equipment | 0402 | X5R | 6.3 | 470000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R61A684KE15 | for General Electronic Equipment | 0402 | X5R | 10 | 680000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R60J684KE19 | for General Electronic Equipment | 0402 | X5R | 6.3 | 680000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R61A105KE15 | for General Electronic Equipment | 0402 | X5R | 10 | 1000000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R60J105KE19 | for General Electronic Equipment | 0402 | X5R | 6.3 | 1000000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM155R60G225ME15 | for General Electronic Equipment | 0402 | X5R | 4 | 2200000 | +/-20[%] | 30[kHz]-6[GHz] |
| GRM155F51H222ZA01 | for General Electronic Equipment | 0402 | Y5V | 50 | 2200 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM155F51H332ZA01 | for General Electronic Equipment | 0402 | Y5V | 50 | 3300 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM155F51H472ZA01 | for General Electronic Equipment | 0402 | Y5V | 50 | 4700 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM155F51H682ZA01 | for General Electronic Equipment | 0402 | Y5V | 50 | 6800 | +80[%]/-20[%] | 30[kHz]-6[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Temp Characteristics (EIA) | Rated Voltage [V] | Capacitance [pF] | Tolerance | Frequency Range |
|---------------------|----------------------------------|----------------|----------------------------|-------------------|------------------|-------------|------------------|
| GRM155F51H103ZA01 | for General Electronic Equipment | 0402 | Y5V | 50 | 10000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM155F51H153ZA01 | for General Electronic Equipment | 0402 | Y5V | 50 | 15000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM155F51E223ZA01 | for General Electronic Equipment | 0402 | Y5V | 25 | 22000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM155F51C333ZA01 | for General Electronic Equipment | 0402 | Y5V | 16 | 33000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM155F51E473ZA01 | for General Electronic Equipment | 0402 | Y5V | 25 | 47000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM155F51C473ZA01 | for General Electronic Equipment | 0402 | Y5V | 16 | 47000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM155F51C683ZA01 | for General Electronic Equipment | 0402 | Y5V | 16 | 68000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM155F51E104ZA01 | for General Electronic Equipment | 0402 | Y5V | 25 | 100000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM155F51C104ZA01 | for General Electronic Equipment | 0402 | Y5V | 16 | 100000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM155F51C224ZA01 | for General Electronic Equipment | 0402 | Y5V | 16 | 220000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM155F51A224ZE01 | for General Electronic Equipment | 0402 | Y5V | 10 | 220000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM155F51C474ZA01 | for General Electronic Equipment | 0402 | Y5V | 16 | 470000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM155F51A474ZE01 | for General Electronic Equipment | 0402 | Y5V | 10 | 470000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM155F51A105ZE01 | for General Electronic Equipment | 0402 | Y5V | 10 | 1000000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM155F50J105ZE01 | for General Electronic Equipment | 0402 | Y5V | 6.3 | 1000000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM1885C2AR50CZ01 | for General Electronic Equipment | 0603 | C0G | 100 | 0.5 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1885C1HR50CZ01 | for General Electronic Equipment | 0603 | C0G | 50 | 0.5 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GRM1885C1HR75CZ01 | for General Electronic Equipment | 0603 | C0G | 50 | 0.75 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GRM1885C2A1R2R0CZ01 | for General Electronic Equipment | 0603 | C0G | 100 | 1 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1885C1H1R0CZ01 | for General Electronic Equipment | 0603 | C0G | 50 | 1 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GRM1885C1H1R2CZ01 | for General Electronic Equipment | 0603 | C0G | 50 | 1.2 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GRM1885C1H1R5CZ01 | for General Electronic Equipment | 0603 | C0G | 50 | 1.5 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GRM1885C1H1R8CZ01 | for General Electronic Equipment | 0603 | C0G | 50 | 1.8 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GRM1885C2A2R0CZ01 | for General Electronic Equipment | 0603 | C0G | 100 | 2 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1885C1H2R0CZ01 | for General Electronic Equipment | 0603 | C0G | 50 | 2 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GRM1885C1H2R2CZ01 | for General Electronic Equipment | 0603 | C0G | 50 | 2.2 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GRM1885C1H2R7CZ01 | for General Electronic Equipment | 0603 | C0G | 50 | 2.7 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GRM1885C2A3R0CZ01 | for General Electronic Equipment | 0603 | C0G | 100 | 3 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1885C1H3R0CZ01 | for General Electronic Equipment | 0603 | C0G | 50 | 3 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GRM1885C1H3R3CZ01 | for General Electronic Equipment | 0603 | C0G | 50 | 3.3 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GRM1885C1H3R9CZ01 | for General Electronic Equipment | 0603 | C0G | 50 | 3.9 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GRM1885C2A4R0CZ01 | for General Electronic Equipment | 0603 | C0G | 100 | 4 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1885C1H4R0CZ01 | for General Electronic Equipment | 0603 | C0G | 50 | 4 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GRM1885C1H4R7CZ01 | for General Electronic Equipment | 0603 | C0G | 50 | 4.7 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GRM1885C2A5R0CZ01 | for General Electronic Equipment | 0603 | C0G | 100 | 5 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GRM1885C1H5R0CZ01 | for General Electronic Equipment | 0603 | C0G | 50 | 5 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GRM1885C1H5R6DZ01 | for General Electronic Equipment | 0603 | C0G | 50 | 5.6 | +/-0.5[pF] | 300[kHz]-6[GHz] |
| GRM1885C2A6R0DZ01 | for General Electronic Equipment | 0603 | C0G | 100 | 6 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GRM1885C1H6R0DZ01 | for General Electronic Equipment | 0603 | C0G | 50 | 6 | +/-0.5[pF] | 300[kHz]-6[GHz] |
| GRM1885C1H6R8DZ01 | for General Electronic Equipment | 0603 | C0G | 50 | 6.8 | +/-0.5[pF] | 300[kHz]-6[GHz] |
| GRM1885C2A7R0DZ01 | for General Electronic Equipment | 0603 | C0G | 100 | 7 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GRM1885C1H7R0DZ01 | for General Electronic Equipment | 0603 | C0G | 50 | 7 | +/-0.5[pF] | 300[kHz]-6[GHz] |
| GRM1885C2A8R0DZ01 | for General Electronic Equipment | 0603 | C0G | 100 | 8 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GRM1885C1H8R0DZ01 | for General Electronic Equipment | 0603 | C0G | 50 | 8 | +/-0.5[pF] | 300[kHz]-6[GHz] |
| GRM1885C1H8R2DZ01 | for General Electronic Equipment | 0603 | C0G | 50 | 8.2 | +/-0.5[pF] | 300[kHz]-6[GHz] |
| GRM1885C2A9R0DZ01 | for General Electronic Equipment | 0603 | C0G | 100 | 9 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GRM1885C1H9R0DZ01 | for General Electronic Equipment | 0603 | C0G | 50 | 9 | +/-0.5[pF] | 300[kHz]-6[GHz] |
| GRM1885C2A100JA01 | for General Electronic Equipment | 0603 | C0G | 100 | 10 | +/-5% | 300[kHz]-20[GHz] |
| GRM1885C1H100JA01 | for General Electronic Equipment | 0603 | C0G | 50 | 10 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C1H110JA01 | for General Electronic Equipment | 0603 | C0G | 50 | 11 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C1H120JA01 | for General Electronic Equipment | 0603 | C0G | 50 | 12 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C1H130JA01 | for General Electronic Equipment | 0603 | C0G | 50 | 13 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C2A150JA01 | for General Electronic Equipment | 0603 | C0G | 100 | 15 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C1H150JA01 | for General Electronic Equipment | 0603 | C0G | 50 | 15 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C1H160JA01 | for General Electronic Equipment | 0603 | C0G | 50 | 16 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C1H180JA01 | for General Electronic Equipment | 0603 | C0G | 50 | 18 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C1H200JA01 | for General Electronic Equipment | 0603 | C0G | 50 | 20 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C2A220JA01 | for General Electronic Equipment | 0603 | C0G | 100 | 22 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C1H220JA01 | for General Electronic Equipment | 0603 | C0G | 50 | 22 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C1H240JA01 | for General Electronic Equipment | 0603 | C0G | 50 | 24 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C1H270JA01 | for General Electronic Equipment | 0603 | C0G | 50 | 27 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C1H300JA01 | for General Electronic Equipment | 0603 | C0G | 50 | 30 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C2A330JA01 | for General Electronic Equipment | 0603 | C0G | 100 | 33 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C1H330JA01 | for General Electronic Equipment | 0603 | C0G | 50 | 33 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C1H360JA01 | for General Electronic Equipment | 0603 | C0G | 50 | 36 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C1H390JA01 | for General Electronic Equipment | 0603 | C0G | 50 | 39 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C1H430JA01 | for General Electronic Equipment | 0603 | C0G | 50 | 43 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C2A470JA01 | for General Electronic Equipment | 0603 | C0G | 100 | 47 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C1H470JA01 | for General Electronic Equipment | 0603 | C0G | 50 | 47 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C1H510JA01 | for General Electronic Equipment | 0603 | C0G | 50 | 51 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C1H560JA01 | for General Electronic Equipment | 0603 | C0G | 50 | 56 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C1H620JA01 | for General Electronic Equipment | 0603 | C0G | 50 | 62 | +/-5% | 300[kHz]-6[GHz] |
| GRM1885C2A680JA01 | for General Electronic Equipment | 0603 | C0G | 100 | 68 | +/-5% | 300[kHz]-6[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Temp Characteristics (EIA) | Rated Voltage [V] | Capacitance [pF] | Tolerance | Frequency Range |
|-------------------|----------------------------------|----------------|----------------------------|-------------------|------------------|-----------|-----------------|
| GRM188R71E103KA01 | for General Electronic Equipment | 0603 | X7R | 25 | 10000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71H123KA01 | for General Electronic Equipment | 0603 | X7R | 50 | 12000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71E123KA01 | for General Electronic Equipment | 0603 | X7R | 25 | 12000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71H153KA01 | for General Electronic Equipment | 0603 | X7R | 50 | 15000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71E153KA01 | for General Electronic Equipment | 0603 | X7R | 25 | 15000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71C153KA01 | for General Electronic Equipment | 0603 | X7R | 16 | 15000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71H183KA01 | for General Electronic Equipment | 0603 | X7R | 50 | 18000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71E183KA01 | for General Electronic Equipment | 0603 | X7R | 25 | 18000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71H223KA01 | for General Electronic Equipment | 0603 | X7R | 50 | 22000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71E223KA01 | for General Electronic Equipment | 0603 | X7R | 25 | 22000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71C223KA01 | for General Electronic Equipment | 0603 | X7R | 16 | 22000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71H273KA61 | for General Electronic Equipment | 0603 | X7R | 50 | 27000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71E273KD01 | for General Electronic Equipment | 0603 | X7R | 25 | 27000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71H333KA61 | for General Electronic Equipment | 0603 | X7R | 50 | 33000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71E333KA01 | for General Electronic Equipment | 0603 | X7R | 25 | 33000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71C333KA01 | for General Electronic Equipment | 0603 | X7R | 16 | 33000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71E393KD01 | for General Electronic Equipment | 0603 | X7R | 25 | 39000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71H473KA61 | for General Electronic Equipment | 0603 | X7R | 50 | 47000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71E473KA01 | for General Electronic Equipment | 0603 | X7R | 25 | 47000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71C473KA01 | for General Electronic Equipment | 0603 | X7R | 16 | 47000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71H683KA93 | for General Electronic Equipment | 0603 | X7R | 50 | 68000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71E683KA01 | for General Electronic Equipment | 0603 | X7R | 25 | 68000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R72A104KA35 | for General Electronic Equipment | 0603 | X7R | 100 | 100000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71H104KA93 | for General Electronic Equipment | 0603 | X7R | 50 | 100000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71E104KA01 | for General Electronic Equipment | 0603 | X7R | 25 | 100000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71C104KA01 | for General Electronic Equipment | 0603 | X7R | 16 | 100000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71A124KC01 | for General Electronic Equipment | 0603 | X7R | 10 | 120000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71E154KA01 | for General Electronic Equipment | 0603 | X7R | 25 | 150000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71C154KA01 | for General Electronic Equipment | 0603 | X7R | 16 | 150000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71A154KA01 | for General Electronic Equipment | 0603 | X7R | 10 | 150000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71E224KA88 | for General Electronic Equipment | 0603 | X7R | 25 | 220000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71C224KA01 | for General Electronic Equipment | 0603 | X7R | 16 | 220000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71A224KA01 | for General Electronic Equipment | 0603 | X7R | 10 | 220000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71C334KA01 | for General Electronic Equipment | 0603 | X7R | 16 | 330000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71A334KA61 | for General Electronic Equipment | 0603 | X7R | 10 | 330000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71E474KA12 | for General Electronic Equipment | 0603 | X7R | 25 | 470000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71C474KA88 | for General Electronic Equipment | 0603 | X7R | 16 | 470000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71A474KA61 | for General Electronic Equipment | 0603 | X7R | 10 | 470000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71E105KA12 | for General Electronic Equipment | 0603 | X7R | 25 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71C105KA12 | for General Electronic Equipment | 0603 | X7R | 16 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71A105KA61 | for General Electronic Equipment | 0603 | X7R | 10 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R70J105KA01 | for General Electronic Equipment | 0603 | X7R | 6.3 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R71A225KE15 | for General Electronic Equipment | 0603 | X7R | 10 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188C71C105KA12 | for General Electronic Equipment | 0603 | X7S | 16 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188C71A105KA12 | for General Electronic Equipment | 0603 | X7S | 10 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188C70J225KE20 | for General Electronic Equipment | 0603 | X7S | 6.3 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188C70G225KE20 | for General Electronic Equipment | 0603 | X7S | 4 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188C80G105MA01 | for General Electronic Equipment | 0603 | X6S | 4 | 1000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM188C80J225KE19 | for General Electronic Equipment | 0603 | X6S | 6.3 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188C80G475KE19 | for General Electronic Equipment | 0603 | X6S | 4 | 4700000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R61E224KA88 | for General Electronic Equipment | 0603 | X5R | 25 | 220000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R61A334KA61 | for General Electronic Equipment | 0603 | X5R | 10 | 330000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R60J334KA01 | for General Electronic Equipment | 0603 | X5R | 6.3 | 330000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R61C474KA93 | for General Electronic Equipment | 0603 | X5R | 16 | 470000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R61A474KA61 | for General Electronic Equipment | 0603 | X5R | 10 | 470000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R60J474KA01 | for General Electronic Equipment | 0603 | X5R | 6.3 | 470000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R61A684KA61 | for General Electronic Equipment | 0603 | X5R | 10 | 680000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R60J684KA01 | for General Electronic Equipment | 0603 | X5R | 6.3 | 680000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R61E105KA12 | for General Electronic Equipment | 0603 | X5R | 25 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM185R61C105KE44 | for General Electronic Equipment | 0603 | X5R | 16 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R61C105KA93 | for General Electronic Equipment | 0603 | X5R | 16 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM185R61A105KE36 | for General Electronic Equipment | 0603 | X5R | 10 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R61A105KA61 | for General Electronic Equipment | 0603 | X5R | 10 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM185R60J105KE21 | for General Electronic Equipment | 0603 | X5R | 6.3 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM185R60J105KE26 | for General Electronic Equipment | 0603 | X5R | 6.3 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R60J105KA01 | for General Electronic Equipment | 0603 | X5R | 6.3 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R61C225KE15 | for General Electronic Equipment | 0603 | X5R | 16 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R61A225KE34 | for General Electronic Equipment | 0603 | X5R | 10 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM185R60J225KE26 | for General Electronic Equipment | 0603 | X5R | 6.3 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R60J225KE01 | for General Electronic Equipment | 0603 | X5R | 6.3 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R60J225KE19 | for General Electronic Equipment | 0603 | X5R | 6.3 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R61A335KE15 | for General Electronic Equipment | 0603 | X5R | 10 | 3300000 | +/-10% | 30[kHz]-6[GHz] |
| GRM188R60J475KE19 | for General Electronic Equipment | 0603 | X5R | 6.3 | 4700000 | +/-10% | 30[kHz]-6[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Temp Characteristics (EIA) | Rated Voltage [V] | Capacitance [pF] | Tolerance | Frequency Range |
|-------------------|----------------------------------|----------------|----------------------------|-------------------|------------------|-----------|-----------------|
| GRM188F10J105ZA01 | for General Electronic Equipment | 0603 | F | 6.3 | 1000000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51H102ZA01 | for General Electronic Equipment | 0603 | Y5V | 50 | 1000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51H332ZA01 | for General Electronic Equipment | 0603 | Y5V | 50 | 3300 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51H103ZA01 | for General Electronic Equipment | 0603 | Y5V | 50 | 10000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51H153ZA01 | for General Electronic Equipment | 0603 | Y5V | 50 | 15000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51H223ZA01 | for General Electronic Equipment | 0603 | Y5V | 50 | 22000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51H333ZA01 | for General Electronic Equipment | 0603 | Y5V | 50 | 33000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51H473ZA01 | for General Electronic Equipment | 0603 | Y5V | 50 | 47000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51H683ZD01 | for General Electronic Equipment | 0603 | Y5V | 50 | 68000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51H104ZA01 | for General Electronic Equipment | 0603 | Y5V | 50 | 100000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51E104ZA01 | for General Electronic Equipment | 0603 | Y5V | 25 | 100000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51H154ZA01 | for General Electronic Equipment | 0603 | Y5V | 50 | 150000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51C154ZA01 | for General Electronic Equipment | 0603 | Y5V | 16 | 150000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51H224ZA01 | for General Electronic Equipment | 0603 | Y5V | 50 | 220000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51C224ZA01 | for General Electronic Equipment | 0603 | Y5V | 16 | 220000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51C334ZA01 | for General Electronic Equipment | 0603 | Y5V | 16 | 330000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51E474ZA01 | for General Electronic Equipment | 0603 | Y5V | 25 | 470000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51C474ZA01 | for General Electronic Equipment | 0603 | Y5V | 16 | 470000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51A474ZA01 | for General Electronic Equipment | 0603 | Y5V | 10 | 470000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51C564ZA01 | for General Electronic Equipment | 0603 | Y5V | 16 | 560000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51A684ZA01 | for General Electronic Equipment | 0603 | Y5V | 10 | 680000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51C105ZA01 | for General Electronic Equipment | 0603 | Y5V | 16 | 1000000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51A105ZA01 | for General Electronic Equipment | 0603 | Y5V | 10 | 1000000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51C225ZA01 | for General Electronic Equipment | 0603 | Y5V | 16 | 2200000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51A225ZE01 | for General Electronic Equipment | 0603 | Y5V | 10 | 2200000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F50J225ZE01 | for General Electronic Equipment | 0603 | Y5V | 6.3 | 2200000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F51A475ZE20 | for General Electronic Equipment | 0603 | Y5V | 10 | 4700000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM188F50J475ZE20 | for General Electronic Equipment | 0603 | Y5V | 6.3 | 4700000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM2165C1H102JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 1000 | +/-5% | 300[kHz]-6[GHz] |
| GRM2165C1H112JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 1100 | +/-5% | 300[kHz]-6[GHz] |
| GRM2165C1H122JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 1200 | +/-5% | 300[kHz]-6[GHz] |
| GRM2165C1H132JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 1300 | +/-5% | 300[kHz]-6[GHz] |
| GRM2165C1H152JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 1500 | +/-5% | 300[kHz]-6[GHz] |
| GRM2165C1H162JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 1600 | +/-5% | 300[kHz]-6[GHz] |
| GRM2165C1H182JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 1800 | +/-5% | 300[kHz]-6[GHz] |
| GRM2165C1H202JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 2000 | +/-5% | 300[kHz]-6[GHz] |
| GRM2165C1H222JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 2200 | +/-5% | 300[kHz]-6[GHz] |
| GRM2165C1H242JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 2400 | +/-5% | 300[kHz]-6[GHz] |
| GRM2165C1H272JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 2700 | +/-5% | 300[kHz]-6[GHz] |
| GRM2165C1H302JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 3000 | +/-5% | 300[kHz]-6[GHz] |
| GRM2165C1H332JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 3300 | +/-5% | 300[kHz]-6[GHz] |
| GRM2165C1H362JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 3600 | +/-5% | 300[kHz]-6[GHz] |
| GRM2165C1H392JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 3900 | +/-5% | 300[kHz]-6[GHz] |
| GRM2165C1H432JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 4300 | +/-5% | 300[kHz]-6[GHz] |
| GRM2165C1H472JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 4700 | +/-5% | 300[kHz]-6[GHz] |
| GRM2195C1H512JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 5100 | +/-5% | 300[kHz]-6[GHz] |
| GRM2195C1H562JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 5600 | +/-5% | 300[kHz]-6[GHz] |
| GRM2195C1H622JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 6200 | +/-5% | 300[kHz]-6[GHz] |
| GRM2195C1H682JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 6800 | +/-5% | 300[kHz]-6[GHz] |
| GRM2195C1H752JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 7500 | +/-5% | 300[kHz]-6[GHz] |
| GRM2195C1H822JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 8200 | +/-5% | 300[kHz]-6[GHz] |
| GRM2195C1H912JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 9100 | +/-5% | 300[kHz]-6[GHz] |
| GRM2195C1H103JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 10000 | +/-5% | 300[kHz]-6[GHz] |
| GRM2195C1H123JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 12000 | +/-5% | 300[kHz]-6[GHz] |
| GRM2195C1H153JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 15000 | +/-5% | 300[kHz]-6[GHz] |
| GRM21B5C1H183JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 18000 | +/-5% | 300[kHz]-6[GHz] |
| GRM21B5C1H223JA01 | for General Electronic Equipment | 0805 | C0G | 50 | 22000 | +/-5% | 300[kHz]-6[GHz] |
| GRM21BL81H154KA01 | for General Electronic Equipment | 0805 | X8L | 50 | 150000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BL81H224KA01 | for General Electronic Equipment | 0805 | X8L | 50 | 220000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BL81H334KA99 | for General Electronic Equipment | 0805 | X8L | 50 | 330000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BL81C334KA01 | for General Electronic Equipment | 0805 | X8L | 16 | 330000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BL81C474KA01 | for General Electronic Equipment | 0805 | X8L | 16 | 470000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BL81C684KA01 | for General Electronic Equipment | 0805 | X8L | 16 | 680000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR72A103KA01 | for General Electronic Equipment | 0805 | X7R | 100 | 10000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR72A223KA01 | for General Electronic Equipment | 0805 | X7R | 100 | 22000 | +/-10% | 30[kHz]-6[GHz] |
| GRM219R71H333KA01 | for General Electronic Equipment | 0805 | X7R | 50 | 33000 | +/-10% | 30[kHz]-6[GHz] |
| GRM219R71H393KA01 | for General Electronic Equipment | 0805 | X7R | 50 | 39000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR72A473KA01 | for General Electronic Equipment | 0805 | X7R | 100 | 47000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71H473KA01 | for General Electronic Equipment | 0805 | X7R | 50 | 47000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71H563KA01 | for General Electronic Equipment | 0805 | X7R | 50 | 56000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71H683KA01 | for General Electronic Equipment | 0805 | X7R | 50 | 68000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71E823KA01 | for General Electronic Equipment | 0805 | X7R | 25 | 82000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71H104KA01 | for General Electronic Equipment | 0805 | X7R | 50 | 100000 | +/-10% | 30[kHz]-6[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Temp Characteristics (EIA) | Rated Voltage [V] | Capacitance [pF] | Tolerance | Frequency Range |
|-------------------|----------------------------------|----------------|----------------------------|-------------------|------------------|-----------|-----------------|
| GRM21BR71H104KA11 | for General Electronic Equipment | 0805 | X7R | 50 | 100000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71E104KA01 | for General Electronic Equipment | 0805 | X7R | 25 | 100000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71E124KD01 | for General Electronic Equipment | 0805 | X7R | 25 | 120000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71H154KA01 | for General Electronic Equipment | 0805 | X7R | 50 | 150000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71E154KA01 | for General Electronic Equipment | 0805 | X7R | 25 | 150000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21AR72A224KAC5 | for General Electronic Equipment | 0805 | X7R | 100 | 220000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71H224KA01 | for General Electronic Equipment | 0805 | X7R | 50 | 220000 | +/-10% | 30[kHz]-6[GHz] |
| GRM219R71E224KA01 | for General Electronic Equipment | 0805 | X7R | 25 | 220000 | +/-10% | 30[kHz]-6[GHz] |
| GRM219R71H334KA88 | for General Electronic Equipment | 0805 | X7R | 50 | 330000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71E334KA01 | for General Electronic Equipment | 0805 | X7R | 25 | 330000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71C394KA01 | for General Electronic Equipment | 0805 | X7R | 16 | 390000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR72A474KA73 | for General Electronic Equipment | 0805 | X7R | 100 | 470000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71H474KA88 | for General Electronic Equipment | 0805 | X7R | 50 | 470000 | +/-10% | 30[kHz]-6[GHz] |
| GRM219R71E474KA88 | for General Electronic Equipment | 0805 | X7R | 25 | 470000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71E474KA01 | for General Electronic Equipment | 0805 | X7R | 25 | 470000 | +/-10% | 30[kHz]-6[GHz] |
| GRM219R71C474KA01 | for General Electronic Equipment | 0805 | X7R | 16 | 470000 | +/-10% | 30[kHz]-6[GHz] |
| GRM219R71C564KA01 | for General Electronic Equipment | 0805 | X7R | 16 | 560000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71E684KA88 | for General Electronic Equipment | 0805 | X7R | 25 | 680000 | +/-10% | 30[kHz]-6[GHz] |
| GRM219R71C684KA01 | for General Electronic Equipment | 0805 | X7R | 16 | 680000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71A684KA01 | for General Electronic Equipment | 0805 | X7R | 10 | 680000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71C824KA01 | for General Electronic Equipment | 0805 | X7R | 16 | 820000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71A824KA01 | for General Electronic Equipment | 0805 | X7R | 10 | 820000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71H105KA12 | for General Electronic Equipment | 0805 | X7R | 50 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM219R71E105KA88 | for General Electronic Equipment | 0805 | X7R | 25 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71E105KA99 | for General Electronic Equipment | 0805 | X7R | 25 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71C105KA01 | for General Electronic Equipment | 0805 | X7R | 16 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71A105KA01 | for General Electronic Equipment | 0805 | X7R | 10 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71E155KA88 | for General Electronic Equipment | 0805 | X7R | 25 | 1500000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71C155KA01 | for General Electronic Equipment | 0805 | X7R | 16 | 1500000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71E225KA73 | for General Electronic Equipment | 0805 | X7R | 25 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71C225KA12 | for General Electronic Equipment | 0805 | X7R | 16 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71C225KAA2 | for General Electronic Equipment | 0805 | X7R | 16 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71A225KA01 | for General Electronic Equipment | 0805 | X7R | 10 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR70J225KA01 | for General Electronic Equipment | 0805 | X7R | 6.3 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71A335KA73 | for General Electronic Equipment | 0805 | X7R | 16 | 4700000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71A475KA73 | for General Electronic Equipment | 0805 | X7R | 10 | 4700000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR71A106KE51 | for General Electronic Equipment | 0805 | X7R | 10 | 10000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR70J106KE76 | for General Electronic Equipment | 0805 | X7R | 6.3 | 10000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BC71A335KA73 | for General Electronic Equipment | 0805 | X7S | 10 | 3300000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BC71A475KA73 | for General Electronic Equipment | 0805 | X7S | 10 | 4700000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BC70G106KE45 | for General Electronic Equipment | 0805 | X7S | 4 | 10000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BC70G106ME45 | for General Electronic Equipment | 0805 | X7S | 4 | 10000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM21BE70G226ME51 | for General Electronic Equipment | 0805 | X7U | 4 | 22000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM21BC81E475KA12 | for General Electronic Equipment | 0805 | X6S | 25 | 4700000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BC80J106KE19 | for General Electronic Equipment | 0805 | X6S | 6.3 | 10000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BC80G226ME39 | for General Electronic Equipment | 0805 | X6S | 4 | 22000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM216R61E105KA12 | for General Electronic Equipment | 0805 | X5R | 25 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM216R61C105KA88 | for General Electronic Equipment | 0805 | X5R | 16 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR61C105KA01 | for General Electronic Equipment | 0805 | X5R | 16 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM216R61A105KA01 | for General Electronic Equipment | 0805 | X5R | 10 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM219R61A105KA01 | for General Electronic Equipment | 0805 | X5R | 10 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM219R60J155KC01 | for General Electronic Equipment | 0805 | X5R | 6.3 | 1500000 | +/-10% | 30[kHz]-6[GHz] |
| GRM219R61E225KA12 | for General Electronic Equipment | 0805 | X5R | 25 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR61E225KA12 | for General Electronic Equipment | 0805 | X5R | 25 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR61C225KA88 | for General Electronic Equipment | 0805 | X5R | 16 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM216R61A225KE24 | for General Electronic Equipment | 0805 | X5R | 10 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM219R61A225KA01 | for General Electronic Equipment | 0805 | X5R | 10 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR61E335KA12 | for General Electronic Equipment | 0805 | X5R | 25 | 3300000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR61C335KA88 | for General Electronic Equipment | 0805 | X5R | 16 | 3300000 | +/-10% | 30[kHz]-6[GHz] |
| GRM219R61A335KE19 | for General Electronic Equipment | 0805 | X5R | 10 | 3300000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR60J335KA11 | for General Electronic Equipment | 0805 | X5R | 6.3 | 3300000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR61E475KA12 | for General Electronic Equipment | 0805 | X5R | 25 | 4700000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR61C475KA88 | for General Electronic Equipment | 0805 | X5R | 16 | 4700000 | +/-10% | 30[kHz]-6[GHz] |
| GRM219R61A475KE19 | for General Electronic Equipment | 0805 | X5R | 10 | 4700000 | +/-10% | 30[kHz]-6[GHz] |
| GRM219R61A475KE34 | for General Electronic Equipment | 0805 | X5R | 10 | 4700000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR61A475KA73 | for General Electronic Equipment | 0805 | X5R | 10 | 4700000 | +/-10% | 30[kHz]-6[GHz] |
| GRM219R60J475KE19 | for General Electronic Equipment | 0805 | X5R | 6.3 | 4700000 | +/-10% | 30[kHz]-6[GHz] |
| GRM219R60J475KE32 | for General Electronic Equipment | 0805 | X5R | 6.3 | 4700000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR60J475KA11 | for General Electronic Equipment | 0805 | X5R | 6.3 | 4700000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR61C106KE15 | for General Electronic Equipment | 0805 | X5R | 16 | 10000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR61A106KE19 | for General Electronic Equipment | 0805 | X5R | 10 | 10000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM219R60J106KE19 | for General Electronic Equipment | 0805 | X5R | 6.3 | 10000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM21BR60J106KE01 | for General Electronic Equipment | 0805 | X5R | 6.3 | 10000000 | +/-10% | 30[kHz]-6[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Temp Characteristics (EIA) | Rated Voltage [V] | Capacitance [pF] | Tolerance | Frequency Range |
|-------------------|----------------------------------|----------------|----------------------------|-------------------|------------------|---------------|-----------------|
| GRM21BR60J106KE19 | for General Electronic Equipment | 0805 | X5R | 6.3 | 10000000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM21BR60J226ME39 | for General Electronic Equipment | 0805 | X5R | 6.3 | 22000000 | +/-20[%] | 30[kHz]-6[GHz] |
| GRM21BB11A225KA01 | for General Electronic Equipment | 0805 | B | 10 | 2200000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM21BB10J225KA01 | for General Electronic Equipment | 0805 | B | 6.3 | 2200000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM21BB31H105KA12 | for General Electronic Equipment | 0805 | B | 50 | 1000000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM216B31E105KA75 | for General Electronic Equipment | 0805 | B | 25 | 1000000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM216F51H102ZA01 | for General Electronic Equipment | 0805 | Y5V | 50 | 1000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM216F51H103ZA01 | for General Electronic Equipment | 0805 | Y5V | 50 | 10000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM216F51H153ZA01 | for General Electronic Equipment | 0805 | Y5V | 50 | 15000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM216F51H223ZA01 | for General Electronic Equipment | 0805 | Y5V | 50 | 22000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM216F51H333ZA01 | for General Electronic Equipment | 0805 | Y5V | 50 | 33000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM216F51H473ZA01 | for General Electronic Equipment | 0805 | Y5V | 50 | 47000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM216F51H683ZA01 | for General Electronic Equipment | 0805 | Y5V | 50 | 68000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM219F51H104ZA01 | for General Electronic Equipment | 0805 | Y5V | 50 | 100000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM216F51E104ZA01 | for General Electronic Equipment | 0805 | Y5V | 25 | 100000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM219F51H154ZA01 | for General Electronic Equipment | 0805 | Y5V | 50 | 150000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM216F51E154ZA01 | for General Electronic Equipment | 0805 | Y5V | 25 | 150000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM216F51H224ZA01 | for General Electronic Equipment | 0805 | Y5V | 50 | 220000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM21BF51H224ZA01 | for General Electronic Equipment | 0805 | Y5V | 50 | 220000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM219F51E224ZA01 | for General Electronic Equipment | 0805 | Y5V | 25 | 220000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM21BF51E334ZA01 | for General Electronic Equipment | 0805 | Y5V | 25 | 330000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM21BF51C334ZA01 | for General Electronic Equipment | 0805 | Y5V | 16 | 330000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM216F51H334ZA01 | for General Electronic Equipment | 0805 | Y5V | 10 | 330000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM219F51H474ZA01 | for General Electronic Equipment | 0805 | Y5V | 50 | 470000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM21BF51E474ZA01 | for General Electronic Equipment | 0805 | Y5V | 25 | 470000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM21BF51C474ZA01 | for General Electronic Equipment | 0805 | Y5V | 16 | 470000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM21BF51C684ZA01 | for General Electronic Equipment | 0805 | Y5V | 16 | 680000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM216F51A684ZA01 | for General Electronic Equipment | 0805 | Y5V | 10 | 680000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM219F51H105ZA01 | for General Electronic Equipment | 0805 | Y5V | 50 | 1000000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM219F51E105ZA01 | for General Electronic Equipment | 0805 | Y5V | 25 | 1000000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM21BF51E105ZA01 | for General Electronic Equipment | 0805 | Y5V | 25 | 1000000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM219F51C105ZA01 | for General Electronic Equipment | 0805 | Y5V | 16 | 1000000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM21BF51C105ZA01 | for General Electronic Equipment | 0805 | Y5V | 16 | 1000000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM219F51A105ZA01 | for General Electronic Equipment | 0805 | Y5V | 10 | 1000000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM21BF51E155ZA01 | for General Electronic Equipment | 0805 | Y5V | 25 | 1500000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM21BF51E225ZA01 | for General Electronic Equipment | 0805 | Y5V | 25 | 2200000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM21BF51C225ZA01 | for General Electronic Equipment | 0805 | Y5V | 16 | 2200000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM21BF51A225ZA01 | for General Electronic Equipment | 0805 | Y5V | 10 | 2200000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM219F51A335ZA01 | for General Electronic Equipment | 0805 | Y5V | 10 | 3300000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM21BF51E475ZA01 | for General Electronic Equipment | 0805 | Y5V | 25 | 4700000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM21BF51A475ZA01 | for General Electronic Equipment | 0805 | Y5V | 10 | 4700000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM21BF50J106ZE01 | for General Electronic Equipment | 0805 | Y5V | 6.3 | 10000000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM3195C1H272JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 2700 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM3195C1H332JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 3300 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM3195C1H362JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 3600 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM3195C1H392JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 3900 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM3195C1H432JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 4300 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM3195C1H472JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 4700 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM3195C1H512JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 5100 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM3195C1H562JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 5600 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM3195C1H622JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 6200 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM3195C1H682JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 6800 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM3195C1H752JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 7500 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM3195C1H822JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 8200 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM3195C1H912JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 9100 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM3195C1H103JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 10000 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM3195C1H113JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 11000 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM3195C1H123JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 12000 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM3195C1H133JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 13000 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM3195C1H153JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 15000 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM3195C1H183JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 18000 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM3195C1H203JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 20000 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM3195C1H223JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 22000 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM3195C1H273JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 27000 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM3195C1H333JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 33000 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM31M5C1H393JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 39000 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM31M5C1H473JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 47000 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM31C5C1H563JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 56000 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM31C5C1H683JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 68000 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM31C5C1H823JA01 | for General Electronic Equipment | 1206 | C0G | 50 | 82000 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM31C5C1E104JA01 | for General Electronic Equipment | 1206 | C0G | 25 | 100000 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM31ML81H474KA01 | for General Electronic Equipment | 1206 | X8L | 50 | 470000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM31CL81H684KA01 | for General Electronic Equipment | 1206 | X8L | 50 | 680000 | +/-10[%] | 30[kHz]-6[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Temp Characteristics (EIA) | Rated Voltage [V] | Capacitance [pF] | Tolerance | Frequency Range |
|-------------------|----------------------------------|----------------|----------------------------|-------------------|------------------|-----------|-----------------|
| GRM31CL81H105KA61 | for General Electronic Equipment | 1206 | X8L | 50 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31ML81C225KA35 | for General Electronic Equipment | 1206 | X8L | 16 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM319R71H104KA01 | for General Electronic Equipment | 1206 | X7R | 50 | 100000 | +/-10% | 30[kHz]-6[GHz] |
| GRM319R71E104KA01 | for General Electronic Equipment | 1206 | X7R | 25 | 100000 | +/-10% | 30[kHz]-6[GHz] |
| GRM319R71C104KA01 | for General Electronic Equipment | 1206 | X7R | 16 | 100000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31MR71H154KA01 | for General Electronic Equipment | 1206 | X7R | 50 | 150000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31MR71E184KD01 | for General Electronic Equipment | 1206 | X7R | 25 | 180000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31MR71H224KA01 | for General Electronic Equipment | 1206 | X7R | 50 | 220000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31MR71E224KA01 | for General Electronic Equipment | 1206 | X7R | 25 | 220000 | +/-10% | 30[kHz]-6[GHz] |
| GRM319R71C224KA01 | for General Electronic Equipment | 1206 | X7R | 16 | 220000 | +/-10% | 30[kHz]-6[GHz] |
| GRM319R71H334KA01 | for General Electronic Equipment | 1206 | X7R | 50 | 330000 | +/-10% | 30[kHz]-6[GHz] |
| GRM319R71E394KC01 | for General Electronic Equipment | 1206 | X7R | 25 | 390000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31MR71H474KA01 | for General Electronic Equipment | 1206 | X7R | 50 | 470000 | +/-10% | 30[kHz]-6[GHz] |
| GRM319R71C474KA01 | for General Electronic Equipment | 1206 | X7R | 16 | 470000 | +/-10% | 30[kHz]-6[GHz] |
| GRM319R71E564KA01 | for General Electronic Equipment | 1206 | X7R | 16 | 560000 | +/-10% | 30[kHz]-6[GHz] |
| GRM319R71E684KA01 | for General Electronic Equipment | 1206 | X7R | 25 | 680000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31MR71H105KA88 | for General Electronic Equipment | 1206 | X7R | 50 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31MR71E105KA01 | for General Electronic Equipment | 1206 | X7R | 25 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM319R71C155KA03 | for General Electronic Equipment | 1206 | X7R | 16 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM319R71A105KA01 | for General Electronic Equipment | 1206 | X7R | 10 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31CR71H155KA88 | for General Electronic Equipment | 1206 | X7R | 50 | 1500000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31MR71E155KA88 | for General Electronic Equipment | 1206 | X7R | 25 | 1500000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31MR71C155KA01 | for General Electronic Equipment | 1206 | X7R | 16 | 1500000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31MR71C155KA35 | for General Electronic Equipment | 1206 | X7R | 16 | 1500000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31MR71E225KA93 | for General Electronic Equipment | 1206 | X7R | 25 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31MR71C225KA35 | for General Electronic Equipment | 1206 | X7R | 16 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31MR71A225KA01 | for General Electronic Equipment | 1206 | X7R | 10 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31CR71E335KA88 | for General Electronic Equipment | 1206 | X7R | 25 | 3300000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31CR71C335KA01 | for General Electronic Equipment | 1206 | X7R | 16 | 3300000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31CR71C475KA01 | for General Electronic Equipment | 1206 | X7R | 16 | 4700000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31CR71A475KA01 | for General Electronic Equipment | 1206 | X7R | 10 | 4700000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31CR71C106KAC7 | for General Electronic Equipment | 1206 | X7R | 16 | 10000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31CR71A106KA01 | for General Electronic Equipment | 1206 | X7R | 10 | 10000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31CR70J106KA01 | for General Electronic Equipment | 1206 | X7R | 6.3 | 10000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31CC70G226KE01 | for General Electronic Equipment | 1206 | X7S | 4 | 22000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31CC70G226ME01 | for General Electronic Equipment | 1206 | X7S | 4 | 22000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM31CD70J226ME19 | for General Electronic Equipment | 1206 | X7T | 6.3 | 22000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM31CC80J226ME19 | for General Electronic Equipment | 1206 | X6S | 6.3 | 22000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM31CC80G476ME19 | for General Electronic Equipment | 1206 | X6S | 4 | 47000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM31CD80G107ME39 | for General Electronic Equipment | 1206 | X6T | 4 | 100000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM319R61E105KC36 | for General Electronic Equipment | 1206 | X5R | 25 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM316R61E225KA12 | for General Electronic Equipment | 1206 | X5R | 25 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM316R61C225KA88 | for General Electronic Equipment | 1206 | X5R | 16 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM319R61A225KA01 | for General Electronic Equipment | 1206 | X5R | 10 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31CR61C335KA88 | for General Electronic Equipment | 1206 | X5R | 16 | 3300000 | +/-10% | 30[kHz]-6[GHz] |
| GRM316R61A335KE19 | for General Electronic Equipment | 1206 | X5R | 10 | 3300000 | +/-10% | 30[kHz]-6[GHz] |
| GRM319R61A335KA01 | for General Electronic Equipment | 1206 | X5R | 10 | 3300000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31XR61A335KAA7 | for General Electronic Equipment | 1206 | X5R | 10 | 3300000 | +/-10% | 30[kHz]-6[GHz] |
| GRM319R61E475KA12 | for General Electronic Equipment | 1206 | X5R | 25 | 4700000 | +/-10% | 30[kHz]-6[GHz] |
| GRM316R61A475KE19 | for General Electronic Equipment | 1206 | X5R | 10 | 4700000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31CR61A475KA01 | for General Electronic Equipment | 1206 | X5R | 10 | 4700000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31CR61E106KA12 | for General Electronic Equipment | 1206 | X5R | 25 | 10000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31CR61C106KA88 | for General Electronic Equipment | 1206 | X5R | 16 | 10000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM319R61A106KE19 | for General Electronic Equipment | 1206 | X5R | 10 | 10000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31CR61A106KA01 | for General Electronic Equipment | 1206 | X5R | 10 | 10000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31MR61A106KE19 | for General Electronic Equipment | 1206 | X5R | 10 | 10000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM319R60J106KE19 | for General Electronic Equipment | 1206 | X5R | 6.3 | 10000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31MR60J106KE19 | for General Electronic Equipment | 1206 | X5R | 6.3 | 10000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31CR60J156KE19 | for General Electronic Equipment | 1206 | X5R | 6.3 | 15000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31CR61C226ME15 | for General Electronic Equipment | 1206 | X5R | 16 | 22000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM31CR61A226ME19 | for General Electronic Equipment | 1206 | X5R | 10 | 22000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM31CR60J226KE19 | for General Electronic Equipment | 1206 | X5R | 6.3 | 22000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31CR60J226ME19 | for General Electronic Equipment | 1206 | X5R | 6.3 | 22000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM31CR60J226ME20 | for General Electronic Equipment | 1206 | X5R | 6.3 | 22000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM31CR60J476ME19 | for General Electronic Equipment | 1206 | X5R | 6.3 | 47000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM31CR60J107ME39 | for General Electronic Equipment | 1206 | X5R | 6.3 | 100000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM31CR60G107ME39 | for General Electronic Equipment | 1206 | X5R | 4 | 100000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM319B11E474KA01 | for General Electronic Equipment | 1206 | B | 25 | 470000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31CB11C475KA01 | for General Electronic Equipment | 1206 | B | 16 | 4700000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31MB31H105KA87 | for General Electronic Equipment | 1206 | B | 50 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31CB31H225KA87 | for General Electronic Equipment | 1206 | B | 50 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM316B31E225KA75 | for General Electronic Equipment | 1206 | B | 25 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM31CB31C475KA87 | for General Electronic Equipment | 1206 | B | 16 | 4700000 | +/-10% | 30[kHz]-6[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Temp Characteristics (EIA) | Rated Voltage [V] | Capacitance [pF] | Tolerance | Frequency Range |
|-------------------|----------------------------------|----------------|----------------------------|-------------------|------------------|-----------|-----------------|
| GRM319F51H334ZA01 | for General Electronic Equipment | 1206 | Y5V | 50 | 330000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM31MF51H474ZA01 | for General Electronic Equipment | 1206 | Y5V | 50 | 470000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM31MF51E684ZA01 | for General Electronic Equipment | 1206 | Y5V | 25 | 680000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM319F51E105ZA01 | for General Electronic Equipment | 1206 | Y5V | 25 | 1000000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM31MF51E105ZA01 | for General Electronic Equipment | 1206 | Y5V | 25 | 1000000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM319F51C105ZA01 | for General Electronic Equipment | 1206 | Y5V | 16 | 1000000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM319F51E225ZA01 | for General Electronic Equipment | 1206 | Y5V | 25 | 2200000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM31MF51C225ZA01 | for General Electronic Equipment | 1206 | Y5V | 16 | 2200000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM319F51A225ZA01 | for General Electronic Equipment | 1206 | Y5V | 10 | 2200000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM319F51A335ZA01 | for General Electronic Equipment | 1206 | Y5V | 10 | 3300000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM31CF51H475ZA01 | for General Electronic Equipment | 1206 | Y5V | 50 | 4700000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM31MF51E475ZA01 | for General Electronic Equipment | 1206 | Y5V | 25 | 4700000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM31MF51C475ZA01 | for General Electronic Equipment | 1206 | Y5V | 16 | 4700000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM31MF51C475ZA44 | for General Electronic Equipment | 1206 | Y5V | 16 | 4700000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM31MF51A475ZA01 | for General Electronic Equipment | 1206 | Y5V | 10 | 4700000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM31CF51E106ZA01 | for General Electronic Equipment | 1206 | Y5V | 25 | 10000000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM31MF51A106ZA01 | for General Electronic Equipment | 1206 | Y5V | 10 | 10000000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM31MF50J106ZA01 | for General Electronic Equipment | 1206 | Y5V | 6.3 | 10000000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM31CF51A226ZE01 | for General Electronic Equipment | 1206 | Y5V | 10 | 22000000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM31CF50J226ZE01 | for General Electronic Equipment | 1206 | Y5V | 6.3 | 22000000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM31CF50J107ZE01 | for General Electronic Equipment | 1206 | Y5V | 6.3 | 100000000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM32N5C1H682JD01 | for General Electronic Equipment | 1210 | C0G | 50 | 6800 | +/-5% | 300[kHz]-6[GHz] |
| GRM32DL81A106KA01 | for General Electronic Equipment | 1210 | X8L | 10 | 10000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32MR71H474KA01 | for General Electronic Equipment | 1210 | X7R | 50 | 470000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32NR71H684KA01 | for General Electronic Equipment | 1210 | X7R | 50 | 680000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32ER71H105KA01 | for General Electronic Equipment | 1210 | X7R | 50 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32RR71H105KA01 | for General Electronic Equipment | 1210 | X7R | 50 | 1000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32NR71E155KA01 | for General Electronic Equipment | 1210 | X7R | 25 | 1500000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32ER72A225KA35 | for General Electronic Equipment | 1210 | X7R | 100 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32RR71E225KA01 | for General Electronic Equipment | 1210 | X7R | 25 | 2200000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32DR71H335KA88 | for General Electronic Equipment | 1210 | X7R | 50 | 3300000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32DR71E335KA01 | for General Electronic Equipment | 1210 | X7R | 25 | 3300000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32NR71C335KA01 | for General Electronic Equipment | 1210 | X7R | 16 | 3300000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32ER71H475KA88 | for General Electronic Equipment | 1210 | X7R | 50 | 4700000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32DR71E475KA61 | for General Electronic Equipment | 1210 | X7R | 25 | 4700000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32RR71C475KA01 | for General Electronic Equipment | 1210 | X7R | 16 | 4700000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32DR71C106KA01 | for General Electronic Equipment | 1210 | X7R | 16 | 10000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32ER71C226ME18 | for General Electronic Equipment | 1210 | X7R | 16 | 22000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM32ER71A226KE20 | for General Electronic Equipment | 1210 | X7R | 10 | 22000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32ER71A226ME20 | for General Electronic Equipment | 1210 | X7R | 10 | 22000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM32ND70J226ME19 | for General Electronic Equipment | 1210 | X7T | 6.3 | 22000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM32ED70J476ME20 | for General Electronic Equipment | 1210 | X7T | 6.3 | 47000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM32EE70G107ME19 | for General Electronic Equipment | 1210 | X7U | 4 | 100000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM32EC80J476ME64 | for General Electronic Equipment | 1210 | X6S | 6.3 | 47000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM32EC80G107KE20 | for General Electronic Equipment | 1210 | X6S | 4 | 100000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32EC80G107ME20 | for General Electronic Equipment | 1210 | X6S | 4 | 100000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM32DR61C106KA01 | for General Electronic Equipment | 1210 | X5R | 16 | 10000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32ER61A106KA01 | for General Electronic Equipment | 1210 | X5R | 10 | 10000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32ER61E226KE15 | for General Electronic Equipment | 1210 | X5R | 25 | 22000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32ER61E226ME15 | for General Electronic Equipment | 1210 | X5R | 25 | 22000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM32ER61C226KE20 | for General Electronic Equipment | 1210 | X5R | 16 | 22000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32ER61C226ME20 | for General Electronic Equipment | 1210 | X5R | 16 | 22000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM32ER61A226KE20 | for General Electronic Equipment | 1210 | X5R | 10 | 22000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32NR61A226KE19 | for General Electronic Equipment | 1210 | X5R | 10 | 22000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32DR60J226KA01 | for General Electronic Equipment | 1210 | X5R | 6.3 | 22000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32DR60J336ME19 | for General Electronic Equipment | 1210 | X5R | 6.3 | 33000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM32ER61C476KE15 | for General Electronic Equipment | 1210 | X5R | 16 | 47000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32ER61C476ME15 | for General Electronic Equipment | 1210 | X5R | 16 | 47000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM32ER61A476KE20 | for General Electronic Equipment | 1210 | X5R | 10 | 47000000 | +/-10% | 30[kHz]-6[GHz] |
| GRM32ER61A476ME20 | for General Electronic Equipment | 1210 | X5R | 10 | 47000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM32ER60J476ME20 | for General Electronic Equipment | 1210 | X5R | 6.3 | 47000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM32ER60J107ME20 | for General Electronic Equipment | 1210 | X5R | 6.3 | 100000000 | +/-20% | 30[kHz]-6[GHz] |
| GRM32RF51H105ZA01 | for General Electronic Equipment | 1210 | Y5V | 50 | 1000000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM329F51E475ZA01 | for General Electronic Equipment | 1210 | Y5V | 25 | 4700000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM32DF51H106ZA01 | for General Electronic Equipment | 1210 | Y5V | 50 | 10000000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM32NF51E106ZA01 | for General Electronic Equipment | 1210 | Y5V | 25 | 10000000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM32NF51C106ZA01 | for General Electronic Equipment | 1210 | Y5V | 16 | 10000000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM329F51A106ZA01 | for General Electronic Equipment | 1210 | Y5V | 10 | 10000000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM32CF51C226ZA12 | for General Electronic Equipment | 1210 | Y5V | 16 | 22000000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM32CF51A226ZA01 | for General Electronic Equipment | 1210 | Y5V | 10 | 22000000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM32EF50J107ZE20 | for General Electronic Equipment | 1210 | Y5V | 6.3 | 100000000 | +80%/-20% | 30[kHz]-6[GHz] |
| GRM43R5C1H103JD01 | for General Electronic Equipment | 1812 | C0G | 50 | 10000 | +/-5% | 300[kHz]-6[GHz] |
| GRM43R5C1H123JD01 | for General Electronic Equipment | 1812 | C0G | 50 | 12000 | +/-5% | 300[kHz]-6[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Temp Characteristics (EIA) | Rated Voltage [V] | Capacitance [pF] | Tolerance | Frequency Range |
|-------------------|----------------------------------|----------------|----------------------------|-------------------|------------------|---------------|------------------|
| GRM43RR71H334KA01 | for General Electronic Equipment | 1812 | X7R | 50 | 330000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM43RR71H474KA01 | for General Electronic Equipment | 1812 | X7R | 50 | 470000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM43DR71H155KA01 | for General Electronic Equipment | 1812 | X7R | 50 | 1500000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM43ER71H225KA01 | for General Electronic Equipment | 1812 | X7R | 50 | 2200000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM43ER71E475KA01 | for General Electronic Equipment | 1812 | X7R | 25 | 4700000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM43ER71A226KE01 | for General Electronic Equipment | 1812 | X7R | 10 | 22000000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM43DR61E105KA12 | for General Electronic Equipment | 1812 | X5R | 25 | 10000000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM43ER61C226KE01 | for General Electronic Equipment | 1812 | X5R | 16 | 22000000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM43DR61A336KE19 | for General Electronic Equipment | 1812 | X5R | 10 | 33000000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM43DR60J336KE01 | for General Electronic Equipment | 1812 | X5R | 6.3 | 33000000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM43ER61A476KA19 | for General Electronic Equipment | 1812 | X5R | 10 | 47000000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM43ER60J476KE01 | for General Electronic Equipment | 1812 | X5R | 6.3 | 47000000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM43SR60J107ME20 | for General Electronic Equipment | 1812 | X5R | 6.3 | 100000000 | +/-20[%] | 30[kHz]-6[GHz] |
| GRM43RF51H105ZD01 | for General Electronic Equipment | 1812 | Y5V | 50 | 1000000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM43DR61E155ZD01 | for General Electronic Equipment | 1812 | Y5V | 50 | 1500000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM43RF51H225ZD01 | for General Electronic Equipment | 1812 | Y5V | 50 | 2200000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM55N5C1H153JD01 | for General Electronic Equipment | 2220 | C0G | 50 | 15000 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM55N5C1H183JD01 | for General Electronic Equipment | 2220 | C0G | 50 | 18000 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM55R5C1H273JD01 | for General Electronic Equipment | 2220 | C0G | 50 | 27000 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM55R5C1H333JD01 | for General Electronic Equipment | 2220 | C0G | 50 | 33000 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM55R5C1H393JD01 | for General Electronic Equipment | 2220 | C0G | 50 | 39000 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM55R5C1H433JD01 | for General Electronic Equipment | 2220 | C0G | 50 | 43000 | +/-5[%] | 300[kHz]-6[GHz] |
| GRM55RR71H684KA01 | for General Electronic Equipment | 2220 | X7R | 50 | 680000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM55RR71H105KA01 | for General Electronic Equipment | 2220 | X7R | 50 | 1000000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM55RR71H155KA01 | for General Electronic Equipment | 2220 | X7R | 50 | 1500000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM55DR71H335KA01 | for General Electronic Equipment | 2220 | X7R | 50 | 3300000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM55ER71H475KA01 | for General Electronic Equipment | 2220 | X7R | 50 | 4700000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM55DR71E106KA01 | for General Electronic Equipment | 2220 | X7R | 25 | 10000000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM55ER71E156KA01 | for General Electronic Equipment | 2220 | X7R | 25 | 15000000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM55DR61H106KA88 | for General Electronic Equipment | 2220 | X5R | 50 | 10000000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM55FR60J107KA01 | for General Electronic Equipment | 2220 | X5R | 6.3 | 100000000 | +/-10[%] | 30[kHz]-6[GHz] |
| GRM55RF51H335ZD01 | for General Electronic Equipment | 2220 | Y5V | 50 | 3300000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GRM55RF51H475ZD01 | for General Electronic Equipment | 2220 | Y5V | 50 | 4700000 | +80[%]/-20[%] | 30[kHz]-6[GHz] |
| GCM0335C1E1R0CD03 | for Automotive | 0201 | C0G | 25 | 1 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GCM0335C1E2R0CD03 | for Automotive | 0201 | C0G | 25 | 2 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GCM0335C1E100JD03 | for Automotive | 0201 | C0G | 25 | 10 | +/-5[%] | 300[kHz]-20[GHz] |
| GCM0335C1E150JD03 | for Automotive | 0201 | C0G | 25 | 15 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM0335C1E220JD03 | for Automotive | 0201 | C0G | 25 | 22 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM0335C1E330JD03 | for Automotive | 0201 | C0G | 25 | 33 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM0335C1E101JD03 | for Automotive | 0201 | C0G | 25 | 100 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM033R71E101KA03 | for Automotive | 0201 | X7R | 25 | 100 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM033R71E221KA03 | for Automotive | 0201 | X7R | 25 | 220 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM033R71E471KA03 | for Automotive | 0201 | X7R | 25 | 470 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM033R71E102KA03 | for Automotive | 0201 | X7R | 25 | 1000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM033R71C222KA55 | for Automotive | 0201 | X7R | 16 | 2200 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM033R71A103KA03 | for Automotive | 0201 | X7R | 10 | 10000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM1555C1H3R0CZ13 | for Automotive | 0402 | C0G | 50 | 0.5 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GCM1555C1H1R0CZ13 | for Automotive | 0402 | C0G | 50 | 1 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GCM1555C1H1R2CZ13 | for Automotive | 0402 | C0G | 50 | 1.2 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GCM1555C1H1R5CZ13 | for Automotive | 0402 | C0G | 50 | 1.5 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GCM1555C1H1R8CZ13 | for Automotive | 0402 | C0G | 50 | 1.8 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GCM1555C1H2R0CZ13 | for Automotive | 0402 | C0G | 50 | 2 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GCM1555C1H2R2CZ13 | for Automotive | 0402 | C0G | 50 | 2.2 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GCM1555C1H2R7CZ13 | for Automotive | 0402 | C0G | 50 | 2.7 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GCM1555C1H3R0CZ13 | for Automotive | 0402 | C0G | 50 | 3 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GCM1555C1H3R3CZ13 | for Automotive | 0402 | C0G | 50 | 3.3 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GCM1555C1H3R9CZ13 | for Automotive | 0402 | C0G | 50 | 3.9 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GCM1555C1H4R0CZ13 | for Automotive | 0402 | C0G | 50 | 4 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GCM1555C1H4R7CZ13 | for Automotive | 0402 | C0G | 50 | 4.7 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GCM1555C1H5R0CZ13 | for Automotive | 0402 | C0G | 50 | 5 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GCM1555C1H5R6DZ13 | for Automotive | 0402 | C0G | 50 | 5.6 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GCM1555C1H6R0DZ13 | for Automotive | 0402 | C0G | 50 | 6 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GCM1555C1H6R8DZ13 | for Automotive | 0402 | C0G | 50 | 6.8 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GCM1555C1H7R0DZ13 | for Automotive | 0402 | C0G | 50 | 7 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GCM1555C1H8R0DZ13 | for Automotive | 0402 | C0G | 50 | 8 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GCM1555C1H8R2DZ13 | for Automotive | 0402 | C0G | 50 | 8.2 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GCM1555C1H9R0DZ13 | for Automotive | 0402 | C0G | 50 | 9 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GCM1555C1H100JZ13 | for Automotive | 0402 | C0G | 50 | 10 | +/-5[%] | 300[kHz]-20[GHz] |
| GCM1555C1H120JZ13 | for Automotive | 0402 | C0G | 50 | 12 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1555C1H150JZ13 | for Automotive | 0402 | C0G | 50 | 15 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1555C1H180JZ13 | for Automotive | 0402 | C0G | 50 | 18 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1555C1H220JZ13 | for Automotive | 0402 | C0G | 50 | 22 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1555C1H270JZ13 | for Automotive | 0402 | C0G | 50 | 27 | +/-5[%] | 300[kHz]-6[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Temp Characteristics (EIA) | Rated Voltage [V] | Capacitance [pF] | Tolerance | Frequency Range |
|-------------------|----------------|----------------|----------------------------|-------------------|------------------|-------------|------------------|
| GCM1555C1H330JZ13 | for Automotive | 0402 | C0G | 50 | 33 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1555C1H390JZ13 | for Automotive | 0402 | C0G | 50 | 39 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1555C1H470JZ13 | for Automotive | 0402 | C0G | 50 | 47 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1555C1H560JZ13 | for Automotive | 0402 | C0G | 50 | 56 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1555C1H680JZ13 | for Automotive | 0402 | C0G | 50 | 68 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1555C1H820JZ13 | for Automotive | 0402 | C0G | 50 | 82 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1555C1H101JZ13 | for Automotive | 0402 | C0G | 50 | 100 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1555C1H121JA16 | for Automotive | 0402 | C0G | 50 | 120 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1555C1H151JA16 | for Automotive | 0402 | C0G | 50 | 150 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1555C1H181JA16 | for Automotive | 0402 | C0G | 50 | 180 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1555C1H221JA16 | for Automotive | 0402 | C0G | 50 | 220 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1555C1H271JA16 | for Automotive | 0402 | C0G | 50 | 270 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1555C1H331JA16 | for Automotive | 0402 | C0G | 50 | 330 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1555C1H391JA16 | for Automotive | 0402 | C0G | 50 | 390 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1555C1H471JA16 | for Automotive | 0402 | C0G | 50 | 470 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM155R11C822KA01 | for Automotive | 0402 | R | 16 | 8200 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R11C103KA01 | for Automotive | 0402 | R | 16 | 10000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R11C123KA01 | for Automotive | 0402 | R | 16 | 12000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R11C153KA01 | for Automotive | 0402 | R | 16 | 15000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R11C183KA01 | for Automotive | 0402 | R | 16 | 18000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R11C223KA01 | for Automotive | 0402 | R | 16 | 22000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R11C473KA01 | for Automotive | 0402 | R | 16 | 47000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R72A221KA37 | for Automotive | 0402 | X7R | 100 | 220 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71H221KA37 | for Automotive | 0402 | X7R | 50 | 220 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71H271KA37 | for Automotive | 0402 | X7R | 50 | 270 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71H331KA37 | for Automotive | 0402 | X7R | 50 | 330 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71H391KA37 | for Automotive | 0402 | X7R | 50 | 390 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R72A471KA37 | for Automotive | 0402 | X7R | 100 | 470 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71H471KA37 | for Automotive | 0402 | X7R | 50 | 470 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71H561KA37 | for Automotive | 0402 | X7R | 50 | 560 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71H681KA37 | for Automotive | 0402 | X7R | 50 | 680 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71H821KA37 | for Automotive | 0402 | X7R | 50 | 820 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R72A102KA37 | for Automotive | 0402 | X7R | 100 | 1000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71H102KA37 | for Automotive | 0402 | X7R | 50 | 1000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71H122KA37 | for Automotive | 0402 | X7R | 50 | 1200 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71H152KA37 | for Automotive | 0402 | X7R | 50 | 1500 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71H182KA37 | for Automotive | 0402 | X7R | 50 | 1800 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R72A222KA37 | for Automotive | 0402 | X7R | 100 | 2200 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71H222KA37 | for Automotive | 0402 | X7R | 50 | 2200 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71H272KA37 | for Automotive | 0402 | X7R | 50 | 2700 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71H332KA37 | for Automotive | 0402 | X7R | 50 | 3300 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71H392KA37 | for Automotive | 0402 | X7R | 50 | 3900 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R72A472KA37 | for Automotive | 0402 | X7R | 100 | 4700 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71H472KA37 | for Automotive | 0402 | X7R | 50 | 4700 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71E562KA37 | for Automotive | 0402 | X7R | 25 | 5600 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71E682KA37 | for Automotive | 0402 | X7R | 25 | 6800 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71H103KA55 | for Automotive | 0402 | X7R | 50 | 10000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71E103KA37 | for Automotive | 0402 | X7R | 25 | 10000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71E153KA55 | for Automotive | 0402 | X7R | 25 | 15000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71H223KA55 | for Automotive | 0402 | X7R | 50 | 22000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71E223KA55 | for Automotive | 0402 | X7R | 25 | 22000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71E333KA41 | for Automotive | 0402 | X7R | 25 | 33000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71C333KA37 | for Automotive | 0402 | X7R | 16 | 33000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71E473KA55 | for Automotive | 0402 | X7R | 25 | 47000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71C683KA55 | for Automotive | 0402 | X7R | 16 | 68000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM155R71C104KA55 | for Automotive | 0402 | X7R | 16 | 100000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM1885C2AR50CZ13 | for Automotive | 0603 | C0G | 100 | 0.5 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GCM1885C2A1R0CZ13 | for Automotive | 0603 | C0G | 100 | 1 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GCM1885C1H1R0CZ13 | for Automotive | 0603 | C0G | 50 | 1 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GCM1885C1H1R2CZ13 | for Automotive | 0603 | C0G | 50 | 1.2 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GCM1885C1H1R5CZ13 | for Automotive | 0603 | C0G | 50 | 1.5 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GCM1885C1H1R8CZ13 | for Automotive | 0603 | C0G | 50 | 1.8 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GCM1885C2A2R0CZ13 | for Automotive | 0603 | C0G | 100 | 2 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GCM1885C1H2R0CZ13 | for Automotive | 0603 | C0G | 50 | 2 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GCM1885C1H2R2CZ13 | for Automotive | 0603 | C0G | 50 | 2.2 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GCM1885C1H2R7CZ13 | for Automotive | 0603 | C0G | 50 | 2.7 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GCM1885C2A3R0CZ13 | for Automotive | 0603 | C0G | 100 | 3 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GCM1885C1H3R0CZ13 | for Automotive | 0603 | C0G | 50 | 3 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GCM1885C1H3R3CZ13 | for Automotive | 0603 | C0G | 50 | 3.3 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GCM1885C1H3R9CZ13 | for Automotive | 0603 | C0G | 50 | 3.9 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GCM1885C2A4R0CZ13 | for Automotive | 0603 | C0G | 100 | 4 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GCM1885C1H4R0CZ13 | for Automotive | 0603 | C0G | 50 | 4 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GCM1885C1H4R7CZ13 | for Automotive | 0603 | C0G | 50 | 4.7 | +/-0.25[pF] | 300[kHz]-6[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Temp Characteristics (EIA) | Rated Voltage [V] | Capacitance [pF] | Tolerance | Frequency Range |
|-------------------|----------------|----------------|----------------------------|-------------------|------------------|-------------|------------------|
| GCM1885C2A5R0CZ13 | for Automotive | 0603 | C0G | 100 | 5 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GCM1885C1H5R0CZ13 | for Automotive | 0603 | C0G | 50 | 5 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| GCM1885C1H5R6DZ13 | for Automotive | 0603 | C0G | 50 | 5.6 | +/-0.5[pF] | 300[kHz]-6[GHz] |
| GCM1885C2A6R0DZ13 | for Automotive | 0603 | C0G | 100 | 6 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GCM1885C1H6R0DZ13 | for Automotive | 0603 | C0G | 50 | 6 | +/-0.5[pF] | 300[kHz]-6[GHz] |
| GCM1885C1H6R8DZ13 | for Automotive | 0603 | C0G | 50 | 6.8 | +/-0.5[pF] | 300[kHz]-6[GHz] |
| GCM1885C2A7R0DZ13 | for Automotive | 0603 | C0G | 100 | 7 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GCM1885C1H7R0DZ13 | for Automotive | 0603 | C0G | 50 | 7 | +/-0.5[pF] | 300[kHz]-6[GHz] |
| GCM1885C2A8R0DZ13 | for Automotive | 0603 | C0G | 100 | 8 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GCM1885C1H8R0DZ13 | for Automotive | 0603 | C0G | 50 | 8 | +/-0.5[pF] | 300[kHz]-6[GHz] |
| GCM1885C1H8R2DZ13 | for Automotive | 0603 | C0G | 50 | 8.2 | +/-0.5[pF] | 300[kHz]-6[GHz] |
| GCM1885C2A9R0DZ13 | for Automotive | 0603 | C0G | 100 | 9 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GCM1885C1H9R0DZ13 | for Automotive | 0603 | C0G | 50 | 9 | +/-0.5[pF] | 300[kHz]-6[GHz] |
| GCM1885C2A100JA16 | for Automotive | 0603 | C0G | 100 | 10 | +/-5[%] | 300[kHz]-20[GHz] |
| GCM1885C1H100JA16 | for Automotive | 0603 | C0G | 50 | 10 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H120JA16 | for Automotive | 0603 | C0G | 50 | 12 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C2A150JA16 | for Automotive | 0603 | C0G | 100 | 15 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H150JA16 | for Automotive | 0603 | C0G | 50 | 15 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H180JA16 | for Automotive | 0603 | C0G | 50 | 18 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C2A220JA16 | for Automotive | 0603 | C0G | 100 | 22 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H220JA16 | for Automotive | 0603 | C0G | 50 | 22 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H270JA16 | for Automotive | 0603 | C0G | 50 | 27 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C2A330JA16 | for Automotive | 0603 | C0G | 100 | 33 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H330JA16 | for Automotive | 0603 | C0G | 50 | 33 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H390JA16 | for Automotive | 0603 | C0G | 50 | 39 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C2A470JA16 | for Automotive | 0603 | C0G | 100 | 47 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H470JA16 | for Automotive | 0603 | C0G | 50 | 47 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H560JA16 | for Automotive | 0603 | C0G | 50 | 56 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C2A680JA16 | for Automotive | 0603 | C0G | 100 | 68 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H680JA16 | for Automotive | 0603 | C0G | 50 | 68 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H820JA16 | for Automotive | 0603 | C0G | 50 | 82 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C2A101JA16 | for Automotive | 0603 | C0G | 100 | 100 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H101JA16 | for Automotive | 0603 | C0G | 50 | 100 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H121JA16 | for Automotive | 0603 | C0G | 50 | 120 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H151JA16 | for Automotive | 0603 | C0G | 50 | 150 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H181JA16 | for Automotive | 0603 | C0G | 50 | 180 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H221JA16 | for Automotive | 0603 | C0G | 50 | 220 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H271JA16 | for Automotive | 0603 | C0G | 50 | 270 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H331JA16 | for Automotive | 0603 | C0G | 50 | 330 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H391JA16 | for Automotive | 0603 | C0G | 50 | 390 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H471JA16 | for Automotive | 0603 | C0G | 50 | 470 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H561JA16 | for Automotive | 0603 | C0G | 50 | 560 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H681JA16 | for Automotive | 0603 | C0G | 50 | 680 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H821JA16 | for Automotive | 0603 | C0G | 50 | 820 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H102JA16 | for Automotive | 0603 | C0G | 50 | 1000 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H122JA16 | for Automotive | 0603 | C0G | 50 | 1200 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H152JA16 | for Automotive | 0603 | C0G | 50 | 1500 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H182JA16 | for Automotive | 0603 | C0G | 50 | 1800 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H222JA16 | for Automotive | 0603 | C0G | 50 | 2200 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM1885C1H272JA16 | for Automotive | 0603 | C0G | 50 | 2700 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM188R72A103KA37 | for Automotive | 0603 | X7R | 100 | 10000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM188R71H223KA37 | for Automotive | 0603 | X7R | 50 | 22000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM188R71H333KA55 | for Automotive | 0603 | X7R | 50 | 33000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM188R71H473KA55 | for Automotive | 0603 | X7R | 50 | 47000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM188R71H683KA57 | for Automotive | 0603 | X7R | 50 | 68000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM188R71H104KA57 | for Automotive | 0603 | X7R | 50 | 100000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM188R71C104KA37 | for Automotive | 0603 | X7R | 16 | 100000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM188R71E224KA55 | for Automotive | 0603 | X7R | 25 | 220000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM188R71E474KA64 | for Automotive | 0603 | X7R | 25 | 470000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM188R71C474KA55 | for Automotive | 0603 | X7R | 16 | 470000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM2165C1H102JA16 | for Automotive | 0805 | C0G | 50 | 1000 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM2165C1H122JA16 | for Automotive | 0805 | C0G | 50 | 1200 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM2165C1H152JA16 | for Automotive | 0805 | C0G | 50 | 1500 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM2165C1H182JA16 | for Automotive | 0805 | C0G | 50 | 1800 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM2165C1H222JA16 | for Automotive | 0805 | C0G | 50 | 2200 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM2165C1H272JA16 | for Automotive | 0805 | C0G | 50 | 2700 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM2165C1H332JA16 | for Automotive | 0805 | C0G | 50 | 3300 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM2165C1H392JA16 | for Automotive | 0805 | C0G | 50 | 3900 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM2165C1H472JA16 | for Automotive | 0805 | C0G | 50 | 4700 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM2195C1H562JA16 | for Automotive | 0805 | C0G | 50 | 5600 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM2195C1H682JA16 | for Automotive | 0805 | C0G | 50 | 6800 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM2195C1H822JA16 | for Automotive | 0805 | C0G | 50 | 8200 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM2195C1H103JA16 | for Automotive | 0805 | C0G | 50 | 10000 | +/-5[%] | 300[kHz]-6[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Temp Characteristics (EIA) | Rated Voltage [V] | Capacitance [pF] | Tolerance | Frequency Range |
|-------------------|-----------------|----------------|----------------------------|-------------------|------------------|-------------|------------------|
| GCM216R71H102KA37 | for Automotive | 0805 | X7R | 50 | 1000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM216R71H152KA37 | for Automotive | 0805 | X7R | 50 | 1500 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM216R71H222KA37 | for Automotive | 0805 | X7R | 50 | 2200 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM216R71H332KA37 | for Automotive | 0805 | X7R | 50 | 3300 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM216R71H472KA37 | for Automotive | 0805 | X7R | 50 | 4700 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM216R71H682KA37 | for Automotive | 0805 | X7R | 50 | 6800 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM216R71H103KA37 | for Automotive | 0805 | X7R | 50 | 10000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM216R71H153KA37 | for Automotive | 0805 | X7R | 50 | 15000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM216R71H223KA37 | for Automotive | 0805 | X7R | 50 | 22000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM219R71H333KA37 | for Automotive | 0805 | X7R | 50 | 33000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM21BR72A473KA37 | for Automotive | 0805 | X7R | 100 | 47000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM21BR71H473KA37 | for Automotive | 0805 | X7R | 50 | 47000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM21BR71H683KA37 | for Automotive | 0805 | X7R | 50 | 68000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM21BR71H104KA37 | for Automotive | 0805 | X7R | 50 | 100000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM21BR71E104KA37 | for Automotive | 0805 | X7R | 25 | 100000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM21BR71H224KA37 | for Automotive | 0805 | X7R | 50 | 220000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM219R71H334KA55 | for Automotive | 0805 | X7R | 50 | 330000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM21BR71H474KA55 | for Automotive | 0805 | X7R | 50 | 470000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM21BR71E684KA55 | for Automotive | 0805 | X7R | 25 | 680000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM21BR71E105KA56 | for Automotive | 0805 | X7R | 25 | 1000000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM21BR71E225KA73 | for Automotive | 0805 | X7R | 25 | 2200000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM21BR71A225KA37 | for Automotive | 0805 | X7R | 10 | 2200000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM21BC71A475KA73 | for Automotive | 0805 | X7S | 10 | 4700000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM3195C1H272JA16 | for Automotive | 1206 | C0G | 50 | 2700 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM3195C1H332JA16 | for Automotive | 1206 | C0G | 50 | 3300 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM3195C1H392JA16 | for Automotive | 1206 | C0G | 50 | 3900 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM3195C1H472JA16 | for Automotive | 1206 | C0G | 50 | 4700 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM3195C1H562JA16 | for Automotive | 1206 | C0G | 50 | 5600 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM3195C1H682JA16 | for Automotive | 1206 | C0G | 50 | 6800 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM3195C1H822JA16 | for Automotive | 1206 | C0G | 50 | 8200 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM3195C1H103JA16 | for Automotive | 1206 | C0G | 50 | 10000 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM3195C1H123JA16 | for Automotive | 1206 | C0G | 50 | 12000 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM3195C1H153JA16 | for Automotive | 1206 | C0G | 50 | 15000 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM3195C1H183JA16 | for Automotive | 1206 | C0G | 50 | 18000 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM3195C1H223JA16 | for Automotive | 1206 | C0G | 50 | 22000 | +/-5[%] | 300[kHz]-6[GHz] |
| GCM319R72A104KA37 | for Automotive | 1206 | X7R | 100 | 100000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM31MR72A224KA37 | for Automotive | 1206 | X7R | 100 | 220000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM31MR71H105KA55 | for Automotive | 1206 | X7R | 50 | 1000000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM31CR71H225KA55 | for Automotive | 1206 | X7R | 50 | 2200000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM31CR71E475KA55 | for Automotive | 1206 | X7R | 25 | 4700000 | +/-10[%] | 30[kHz]-6[GHz] |
| GCM31CR71C106KA64 | for Automotive | 1206 | X7R | 16 | 10000000 | +/-10[%] | 30[kHz]-6[GHz] |
| GJM0335C1ER20BB01 | High-Power type | 0201 | C0G | 25 | 0.2 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GJM0335C1ER50CB01 | High-Power type | 0201 | C0G | 25 | 0.5 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM0335C1ER75CB01 | High-Power type | 0201 | C0G | 25 | 0.75 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E1R0CB01 | High-Power type | 0201 | C0G | 25 | 1 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E1R1CB01 | High-Power type | 0201 | C0G | 25 | 1.1 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E1R2CB01 | High-Power type | 0201 | C0G | 25 | 1.2 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E1R3CB01 | High-Power type | 0201 | C0G | 25 | 1.3 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E1R5CB01 | High-Power type | 0201 | C0G | 25 | 1.5 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E1R6CB01 | High-Power type | 0201 | C0G | 25 | 1.6 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E1R8CB01 | High-Power type | 0201 | C0G | 25 | 1.8 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E2R0CB01 | High-Power type | 0201 | C0G | 25 | 2 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E2R2BB01 | High-Power type | 0201 | C0G | 25 | 2.2 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E2R4BB01 | High-Power type | 0201 | C0G | 25 | 2.4 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E2R6BB01 | High-Power type | 0201 | C0G | 25 | 2.6 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E2R7CB01 | High-Power type | 0201 | C0G | 25 | 2.7 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E2R8BB01 | High-Power type | 0201 | C0G | 25 | 2.8 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E3R0CB01 | High-Power type | 0201 | C0G | 25 | 3 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E3R2BB01 | High-Power type | 0201 | C0G | 25 | 3.2 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E3R3CB01 | High-Power type | 0201 | C0G | 25 | 3.3 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E3R4BB01 | High-Power type | 0201 | C0G | 25 | 3.4 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E3R6BB01 | High-Power type | 0201 | C0G | 25 | 3.6 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E3R8BB01 | High-Power type | 0201 | C0G | 25 | 3.8 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E3R9CB01 | High-Power type | 0201 | C0G | 25 | 3.9 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E4R0CB01 | High-Power type | 0201 | C0G | 25 | 4 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E4R2BB01 | High-Power type | 0201 | C0G | 25 | 4.2 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E4R3CB01 | High-Power type | 0201 | C0G | 25 | 4.3 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E4R4BB01 | High-Power type | 0201 | C0G | 25 | 4.4 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E4R6BB01 | High-Power type | 0201 | C0G | 25 | 4.6 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E4R7CB01 | High-Power type | 0201 | C0G | 25 | 4.7 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E5R0CB01 | High-Power type | 0201 | C0G | 25 | 5 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E5R1DB01 | High-Power type | 0201 | C0G | 25 | 5.1 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E5R6DB01 | High-Power type | 0201 | C0G | 25 | 5.6 | +/-0.5[pF] | 300[kHz]-20[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Temp Characteristics (EIA) | Rated Voltage [V] | Capacitance [pF] | Tolerance | Frequency Range |
|-------------------|---------------------|----------------|----------------------------|-------------------|------------------|-------------|------------------|
| GJM0335C1E6R0DB01 | High-Power type | 0201 | C0G | 25 | 6 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E6R2DB01 | High-Power type | 0201 | C0G | 25 | 6.2 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E6R7BB01 | High-Power type | 0201 | C0G | 25 | 6.7 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E6R8BB01 | High-Power type | 0201 | C0G | 25 | 6.8 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E6R8DB01 | High-Power type | 0201 | C0G | 25 | 6.8 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GJM0335C1E200JB01 | High-Power type | 0201 | C0G | 25 | 20 | +/-5[%] | 300[kHz]-6[GHz] |
| GJM1555C1HR10BB01 | High-Power type | 0402 | C0G | 50 | 0.1 | +/-0.1[pF] | 300[kHz]-20[GHz] |
| GJM1555C1HR50CB01 | High-Power type | 0402 | C0G | 50 | 0.5 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM1555C1HR75CB01 | High-Power type | 0402 | C0G | 50 | 0.75 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H1R0CB01 | High-Power type | 0402 | C0G | 50 | 1 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H1R1CB01 | High-Power type | 0402 | C0G | 50 | 1.1 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H1R2CB01 | High-Power type | 0402 | C0G | 50 | 1.2 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H1R3CB01 | High-Power type | 0402 | C0G | 50 | 1.3 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H1R5CB01 | High-Power type | 0402 | C0G | 50 | 1.5 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H1R6CB01 | High-Power type | 0402 | C0G | 50 | 1.6 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H1R8CB01 | High-Power type | 0402 | C0G | 50 | 1.8 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H2R0CB01 | High-Power type | 0402 | C0G | 50 | 2 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H2R2CB01 | High-Power type | 0402 | C0G | 50 | 2.2 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H2R4CB01 | High-Power type | 0402 | C0G | 50 | 2.4 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H2R7CB01 | High-Power type | 0402 | C0G | 50 | 2.7 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H3R0CB01 | High-Power type | 0402 | C0G | 50 | 3 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H3R3CB01 | High-Power type | 0402 | C0G | 50 | 3.3 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H3R6CB01 | High-Power type | 0402 | C0G | 50 | 3.6 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H3R9CB01 | High-Power type | 0402 | C0G | 50 | 3.9 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H4R0CB01 | High-Power type | 0402 | C0G | 50 | 4 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H4R3CB01 | High-Power type | 0402 | C0G | 50 | 4.3 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H4R7CB01 | High-Power type | 0402 | C0G | 50 | 4.7 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H5R0CB01 | High-Power type | 0402 | C0G | 50 | 5 | +/-0.25[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H5R1DB01 | High-Power type | 0402 | C0G | 50 | 5.1 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H5R6DB01 | High-Power type | 0402 | C0G | 50 | 5.6 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H6R0DB01 | High-Power type | 0402 | C0G | 50 | 6 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H6R2DB01 | High-Power type | 0402 | C0G | 50 | 6.2 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H6R8DB01 | High-Power type | 0402 | C0G | 50 | 6.8 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H7R0DB01 | High-Power type | 0402 | C0G | 50 | 7 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H7R5DB01 | High-Power type | 0402 | C0G | 50 | 7.5 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H8R0DB01 | High-Power type | 0402 | C0G | 50 | 8 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H8R2DB01 | High-Power type | 0402 | C0G | 50 | 8.2 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H9R0DB01 | High-Power type | 0402 | C0G | 50 | 9 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H9R1DB01 | High-Power type | 0402 | C0G | 50 | 9.1 | +/-0.5[pF] | 300[kHz]-20[GHz] |
| GJM1555C1H100JB01 | High-Power type | 0402 | C0G | 50 | 10 | +/-5[%] | 300[kHz]-20[GHz] |
| GJM1555C1H110JB01 | High-Power type | 0402 | C0G | 50 | 11 | +/-5[%] | 300[kHz]-6[GHz] |
| GJM1555C1H120JB01 | High-Power type | 0402 | C0G | 50 | 12 | +/-5[%] | 300[kHz]-6[GHz] |
| GJM1555C1H130JB01 | High-Power type | 0402 | C0G | 50 | 13 | +/-5[%] | 300[kHz]-6[GHz] |
| GJM1555C1H150JB01 | High-Power type | 0402 | C0G | 50 | 15 | +/-5[%] | 300[kHz]-6[GHz] |
| GJM1555C1H160JB01 | High-Power type | 0402 | C0G | 50 | 16 | +/-5[%] | 300[kHz]-6[GHz] |
| GJM1555C1H180JB01 | High-Power type | 0402 | C0G | 50 | 18 | +/-5[%] | 300[kHz]-6[GHz] |
| GJM1555C1H200JB01 | High-Power type | 0402 | C0G | 50 | 20 | +/-5[%] | 300[kHz]-6[GHz] |
| GQM1875C2ER10BB12 | High Frequency type | 0603 | C0G | 250 | 0.1 | +/-0.1[pF] | 100[MHz]-6[GHz] |
| GQM1875C2ER20BB12 | High Frequency type | 0603 | C0G | 250 | 0.2 | +/-0.1[pF] | 100[MHz]-6[GHz] |
| GQM1875C2ER30BB12 | High Frequency type | 0603 | C0G | 250 | 0.3 | +/-0.1[pF] | 100[MHz]-6[GHz] |
| GQM1875C2ER40BB12 | High Frequency type | 0603 | C0G | 250 | 0.4 | +/-0.1[pF] | 100[MHz]-6[GHz] |
| GQM1875C2ER50BB12 | High Frequency type | 0603 | C0G | 250 | 0.5 | +/-0.1[pF] | 100[MHz]-6[GHz] |
| GQM1885C2AR50CB01 | High Frequency type | 0603 | C0G | 100 | 0.5 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1875C2ER60BB12 | High Frequency type | 0603 | C0G | 250 | 0.6 | +/-0.1[pF] | 100[MHz]-6[GHz] |
| GQM1875C2ER70BB12 | High Frequency type | 0603 | C0G | 250 | 0.7 | +/-0.1[pF] | 100[MHz]-6[GHz] |
| GQM1885C2AR75CB01 | High Frequency type | 0603 | C0G | 100 | 0.75 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1875C2ER80BB12 | High Frequency type | 0603 | C0G | 250 | 0.8 | +/-0.1[pF] | 100[MHz]-6[GHz] |
| GQM1875C2ER90BB12 | High Frequency type | 0603 | C0G | 250 | 0.9 | +/-0.1[pF] | 100[MHz]-6[GHz] |
| GQM1875C2E1R0BB12 | High Frequency type | 0603 | C0G | 250 | 1 | +/-0.1[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A1R0CB01 | High Frequency type | 0603 | C0G | 100 | 1 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A1R1CB01 | High Frequency type | 0603 | C0G | 100 | 1.1 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A1R2CB01 | High Frequency type | 0603 | C0G | 100 | 1.2 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A1R3CB01 | High Frequency type | 0603 | C0G | 100 | 1.3 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A1R4CB01 | High Frequency type | 0603 | C0G | 100 | 1.4 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A1R5CB01 | High Frequency type | 0603 | C0G | 100 | 1.5 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A1R6CB01 | High Frequency type | 0603 | C0G | 100 | 1.6 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A1R7CB01 | High Frequency type | 0603 | C0G | 100 | 1.7 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A1R8CB01 | High Frequency type | 0603 | C0G | 100 | 1.8 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A1R9CB01 | High Frequency type | 0603 | C0G | 100 | 1.9 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A2R0CB01 | High Frequency type | 0603 | C0G | 100 | 2 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A2R1CB01 | High Frequency type | 0603 | C0G | 100 | 2.1 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A2R2CB01 | High Frequency type | 0603 | C0G | 100 | 2.2 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A2R3CB01 | High Frequency type | 0603 | C0G | 100 | 2.3 | +/-0.25[pF] | 100[MHz]-6[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Temp Characteristics (EIA) | Rated Voltage [V] | Capacitance [pF] | Tolerance | Frequency Range |
|-------------------|---------------------|----------------|----------------------------|-------------------|------------------|-------------|-----------------|
| GQM1885C2A2R4CB01 | High Frequency type | 0603 | C0G | 100 | 2.4 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A2R5CB01 | High Frequency type | 0603 | C0G | 100 | 2.5 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A2R7CB01 | High Frequency type | 0603 | C0G | 100 | 2.7 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A2R9CB01 | High Frequency type | 0603 | C0G | 100 | 2.9 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A3R0CB01 | High Frequency type | 0603 | C0G | 100 | 3 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A3R1CB01 | High Frequency type | 0603 | C0G | 100 | 3.1 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A3R3CB01 | High Frequency type | 0603 | C0G | 100 | 3.3 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A3R6CB01 | High Frequency type | 0603 | C0G | 100 | 3.6 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A3R9CB01 | High Frequency type | 0603 | C0G | 100 | 3.9 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1875C2E4R3CB12 | High Frequency type | 0603 | C0G | 250 | 4.3 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A4R3CB01 | High Frequency type | 0603 | C0G | 100 | 4.3 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A4R7CB01 | High Frequency type | 0603 | C0G | 100 | 4.7 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A5R1DB01 | High Frequency type | 0603 | C0G | 100 | 5.1 | +/-0.5[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A5R6DB01 | High Frequency type | 0603 | C0G | 100 | 5.6 | +/-0.5[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A6R3DB01 | High Frequency type | 0603 | C0G | 100 | 6.2 | +/-0.5[pF] | 100[MHz]-6[GHz] |
| GQM1875C2E6R8CB12 | High Frequency type | 0603 | C0G | 250 | 6.8 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C2A6R8DB01 | High Frequency type | 0603 | C0G | 100 | 6.8 | +/-0.5[pF] | 100[MHz]-6[GHz] |
| GQM1875C2E7R5CB12 | High Frequency type | 0603 | C0G | 250 | 7.5 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM1885C1H7R5DB01 | High Frequency type | 0603 | C0G | 50 | 7.5 | +/-0.5[pF] | 100[MHz]-6[GHz] |
| GQM1885C1H8R2DB01 | High Frequency type | 0603 | C0G | 50 | 8.2 | +/-0.5[pF] | 100[MHz]-6[GHz] |
| GQM1885C1H9R1DB01 | High Frequency type | 0603 | C0G | 50 | 9.1 | +/-0.5[pF] | 100[MHz]-6[GHz] |
| GQM1875C2E100JB12 | High Frequency type | 0603 | C0G | 250 | 10 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H100JB01 | High Frequency type | 0603 | C0G | 50 | 10 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H110JB01 | High Frequency type | 0603 | C0G | 50 | 11 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H120JB01 | High Frequency type | 0603 | C0G | 50 | 12 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H130JB01 | High Frequency type | 0603 | C0G | 50 | 13 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H150JB01 | High Frequency type | 0603 | C0G | 50 | 15 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H160JB01 | High Frequency type | 0603 | C0G | 50 | 16 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H180JB01 | High Frequency type | 0603 | C0G | 50 | 18 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H200JB01 | High Frequency type | 0603 | C0G | 50 | 20 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H220JB01 | High Frequency type | 0603 | C0G | 50 | 22 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H240JB01 | High Frequency type | 0603 | C0G | 50 | 24 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H270JB01 | High Frequency type | 0603 | C0G | 50 | 27 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H300JB01 | High Frequency type | 0603 | C0G | 50 | 30 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H330JB01 | High Frequency type | 0603 | C0G | 50 | 33 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H360JB01 | High Frequency type | 0603 | C0G | 50 | 36 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H390JB01 | High Frequency type | 0603 | C0G | 50 | 39 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H430JB01 | High Frequency type | 0603 | C0G | 50 | 43 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1875C2E470JB12 | High Frequency type | 0603 | C0G | 250 | 47 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H470JB01 | High Frequency type | 0603 | C0G | 50 | 47 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H560JB01 | High Frequency type | 0603 | C0G | 50 | 56 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H620JB01 | High Frequency type | 0603 | C0G | 50 | 62 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H680JB01 | High Frequency type | 0603 | C0G | 50 | 68 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H750JB01 | High Frequency type | 0603 | C0G | 50 | 75 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H820JB01 | High Frequency type | 0603 | C0G | 50 | 82 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H910JB01 | High Frequency type | 0603 | C0G | 50 | 91 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM1885C1H101JB01 | High Frequency type | 0603 | C0G | 50 | 100 | +/-5[%] | 100[MHz]-6[GHz] |
| GQM2195C2AR50CB01 | High Frequency type | 0805 | C0G | 100 | 0.5 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM2195C2AR75CB01 | High Frequency type | 0805 | C0G | 100 | 0.75 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A1R0CB01 | High Frequency type | 0805 | C0G | 100 | 1 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A1R1CB01 | High Frequency type | 0805 | C0G | 100 | 1.1 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A1R2CB01 | High Frequency type | 0805 | C0G | 100 | 1.2 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A1R3CB01 | High Frequency type | 0805 | C0G | 100 | 1.3 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A1R5CB01 | High Frequency type | 0805 | C0G | 100 | 1.5 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A1R6CB01 | High Frequency type | 0805 | C0G | 100 | 1.6 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A1R8CB01 | High Frequency type | 0805 | C0G | 100 | 1.8 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A2R0CB01 | High Frequency type | 0805 | C0G | 100 | 2 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A2R2CB01 | High Frequency type | 0805 | C0G | 100 | 2.2 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A2R4CB01 | High Frequency type | 0805 | C0G | 100 | 2.4 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A2R7CB01 | High Frequency type | 0805 | C0G | 100 | 2.7 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A3R0CB01 | High Frequency type | 0805 | C0G | 100 | 3 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A3R3CB01 | High Frequency type | 0805 | C0G | 100 | 3.3 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A3R6CB01 | High Frequency type | 0805 | C0G | 100 | 3.6 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A3R9CB01 | High Frequency type | 0805 | C0G | 100 | 3.9 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A4R3CB01 | High Frequency type | 0805 | C0G | 100 | 4.3 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A4R7CB01 | High Frequency type | 0805 | C0G | 100 | 4.7 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A5R1DB01 | High Frequency type | 0805 | C0G | 100 | 5.1 | +/-0.5[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A5R6DB01 | High Frequency type | 0805 | C0G | 100 | 5.6 | +/-0.5[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A6R2DB01 | High Frequency type | 0805 | C0G | 100 | 6.2 | +/-0.5[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A6R8DB01 | High Frequency type | 0805 | C0G | 100 | 6.8 | +/-0.5[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A7R5DB01 | High Frequency type | 0805 | C0G | 100 | 7.5 | +/-0.5[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A8R2DB01 | High Frequency type | 0805 | C0G | 100 | 8.2 | +/-0.5[pF] | 100[MHz]-6[GHz] |
| GQM2195C2A9R1DB01 | High Frequency type | 0805 | C0G | 100 | 9.1 | +/-0.5[pF] | 100[MHz]-6[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Temp Characteristics (EIA) | Rated Voltage [V] | Capacitance [pF] | Tolerance | Frequency Range |
|-------------------|--------------------------|----------------|----------------------------|-------------------|------------------|-------------|-----------------|
| ERB32Q5C2H2R4CDX1 | High Frequency type | 1210 | C0G | 500 | 2.4 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| ERB32Q5C2H2R7CDX1 | High Frequency type | 1210 | C0G | 500 | 2.7 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| ERB32Q5C2H3R0CDX1 | High Frequency type | 1210 | C0G | 500 | 3 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| ERB32Q5C2H3R3CDX1 | High Frequency type | 1210 | C0G | 500 | 3.3 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| ERB32Q5C2H3R6CDX1 | High Frequency type | 1210 | C0G | 500 | 3.6 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| ERB32Q5C2H3R9CDX1 | High Frequency type | 1210 | C0G | 500 | 3.9 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| ERB32Q5C2H4R3CDX1 | High Frequency type | 1210 | C0G | 500 | 4.3 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| ERB32Q5C2H4R7CDX1 | High Frequency type | 1210 | C0G | 500 | 4.7 | +/-0.25[pF] | 100[MHz]-6[GHz] |
| ERB32Q5C2H5R1DDX1 | High Frequency type | 1210 | C0G | 500 | 5.1 | +/-0.5[pF] | 100[MHz]-6[GHz] |
| ERB32Q5C2H5R6DDX1 | High Frequency type | 1210 | C0G | 500 | 5.6 | +/-0.5[pF] | 100[MHz]-6[GHz] |
| ERB32Q5C2H6R3DDX1 | High Frequency type | 1210 | C0G | 500 | 6.2 | +/-0.5[pF] | 100[MHz]-6[GHz] |
| ERB32Q5C2H6R8DDX1 | High Frequency type | 1210 | C0G | 500 | 6.8 | +/-0.5[pF] | 100[MHz]-6[GHz] |
| ERB32Q5C2H7R5DDX1 | High Frequency type | 1210 | C0G | 500 | 7.5 | +/-0.5[pF] | 100[MHz]-6[GHz] |
| ERB32Q5C2H8R2DDX1 | High Frequency type | 1210 | C0G | 500 | 8.2 | +/-0.5[pF] | 100[MHz]-6[GHz] |
| ERB32Q5C2H9R1DDX1 | High Frequency type | 1210 | C0G | 500 | 9.1 | +/-0.5[pF] | 100[MHz]-6[GHz] |
| ERB32Q5C2H100JDX1 | High Frequency type | 1210 | C0G | 500 | 10 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H110JDX1 | High Frequency type | 1210 | C0G | 500 | 11 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H120JDX1 | High Frequency type | 1210 | C0G | 500 | 12 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H130JDX1 | High Frequency type | 1210 | C0G | 500 | 13 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H150JDX1 | High Frequency type | 1210 | C0G | 500 | 15 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H160JDX1 | High Frequency type | 1210 | C0G | 500 | 16 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H180JDX1 | High Frequency type | 1210 | C0G | 500 | 18 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H200JDX1 | High Frequency type | 1210 | C0G | 500 | 20 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H220JDX1 | High Frequency type | 1210 | C0G | 500 | 22 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H240JDX1 | High Frequency type | 1210 | C0G | 500 | 24 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H270JDX1 | High Frequency type | 1210 | C0G | 500 | 27 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H300JDX1 | High Frequency type | 1210 | C0G | 500 | 30 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H330JDX1 | High Frequency type | 1210 | C0G | 500 | 33 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H360JDX1 | High Frequency type | 1210 | C0G | 500 | 36 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H390JDX1 | High Frequency type | 1210 | C0G | 500 | 39 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H430JDX1 | High Frequency type | 1210 | C0G | 500 | 43 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H470JDX1 | High Frequency type | 1210 | C0G | 500 | 47 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H510JDX1 | High Frequency type | 1210 | C0G | 500 | 51 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H560JDX1 | High Frequency type | 1210 | C0G | 500 | 56 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H620JDX1 | High Frequency type | 1210 | C0G | 500 | 62 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H680JDX1 | High Frequency type | 1210 | C0G | 500 | 68 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H750JDX1 | High Frequency type | 1210 | C0G | 500 | 75 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H820JDX1 | High Frequency type | 1210 | C0G | 500 | 82 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H910JDX1 | High Frequency type | 1210 | C0G | 500 | 91 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H101JDX1 | High Frequency type | 1210 | C0G | 500 | 100 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2H121JDX1 | High Frequency type | 1210 | C0G | 500 | 120 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5CYD131JDX1 | High Frequency type | 1210 | C0G | 300 | 130 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5CYD151JDX1 | High Frequency type | 1210 | C0G | 300 | 150 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2E161JDX1 | High Frequency type | 1210 | C0G | 250 | 160 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2E181JDX1 | High Frequency type | 1210 | C0G | 250 | 180 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2E201JDX1 | High Frequency type | 1210 | C0G | 250 | 200 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2E221JDX1 | High Frequency type | 1210 | C0G | 250 | 220 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2A241JDX1 | High Frequency type | 1210 | C0G | 100 | 240 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2A271JDX1 | High Frequency type | 1210 | C0G | 100 | 270 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2A301JDX1 | High Frequency type | 1210 | C0G | 100 | 300 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2A331JDX1 | High Frequency type | 1210 | C0G | 100 | 330 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2A361JDX1 | High Frequency type | 1210 | C0G | 100 | 360 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2A391JDX1 | High Frequency type | 1210 | C0G | 100 | 390 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2A431JDX1 | High Frequency type | 1210 | C0G | 100 | 430 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C2A471JDX1 | High Frequency type | 1210 | C0G | 100 | 470 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C1H511JDX1 | High Frequency type | 1210 | C0G | 50 | 510 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C1H561JDX1 | High Frequency type | 1210 | C0G | 50 | 560 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C1H621JDX1 | High Frequency type | 1210 | C0G | 50 | 620 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C1H681JDX1 | High Frequency type | 1210 | C0G | 50 | 680 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C1H751JDX1 | High Frequency type | 1210 | C0G | 50 | 750 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C1H821JDX1 | High Frequency type | 1210 | C0G | 50 | 820 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C1H911JDX1 | High Frequency type | 1210 | C0G | 50 | 910 | +/-5[%] | 100[MHz]-6[GHz] |
| ERB32Q5C1H102JDX1 | High Frequency type | 1210 | C0G | 50 | 1000 | +/-5[%] | 100[MHz]-6[GHz] |
| ERF1DM6C1HR50CD01 | High-Q & High Power type | 0606 | CH | 50 | 0.5 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| ERF1DM6C1HR75CD01 | High-Q & High Power type | 0606 | CH | 50 | 0.75 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| ERF1DM6C1H1R0CD01 | High-Q & High Power type | 0606 | CH | 50 | 1 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| ERF1DM6C1H1R5CD01 | High-Q & High Power type | 0606 | CH | 50 | 1.5 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| ERF1DM6C1H2R0CD01 | High-Q & High Power type | 0606 | CH | 50 | 2 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| ERF1DM6C1H3R0CD01 | High-Q & High Power type | 0606 | CH | 50 | 3 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| ERF1DM6C1H4R0CD01 | High-Q & High Power type | 0606 | CH | 50 | 4 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| ERF1DM6C1H5R0CD01 | High-Q & High Power type | 0606 | CH | 50 | 5 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| ERF1DM6C1H6R0DD01 | High-Q & High Power type | 0606 | CH | 50 | 6 | +/-0.5[pF] | 300[kHz]-6[GHz] |
| ERF1DM6C1H7R0DD01 | High-Q & High Power type | 0606 | CH | 50 | 7 | +/-0.5[pF] | 300[kHz]-6[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Temp Characteristics (EIA) | Rated Voltage [V] | Capacitance [pF] | Tolerance | Frequency Range |
|-------------------|--------------------------|----------------|----------------------------|-------------------|------------------|-------------|-----------------|
| ERF1DM6C1H8R0DD01 | High-Q & High Power type | 0606 | CH | 50 | 8 | +/-0.5[pF] | 300[kHz]-6[GHz] |
| ERF1DM6C1H9R0DD01 | High-Q & High Power type | 0606 | CH | 50 | 9 | +/-0.5[pF] | 300[kHz]-6[GHz] |
| ERF1DM6C1H100JD01 | High-Q & High Power type | 0606 | CH | 50 | 10 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H110JD01 | High-Q & High Power type | 0606 | CH | 50 | 11 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H120JD01 | High-Q & High Power type | 0606 | CH | 50 | 12 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H130JD01 | High-Q & High Power type | 0606 | CH | 50 | 13 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H150JD01 | High-Q & High Power type | 0606 | CH | 50 | 15 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H160JD01 | High-Q & High Power type | 0606 | CH | 50 | 16 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H180JD01 | High-Q & High Power type | 0606 | CH | 50 | 18 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H200JD01 | High-Q & High Power type | 0606 | CH | 50 | 20 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H220JD01 | High-Q & High Power type | 0606 | CH | 50 | 22 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H240JD01 | High-Q & High Power type | 0606 | CH | 50 | 24 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H270JD01 | High-Q & High Power type | 0606 | CH | 50 | 27 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H300JD01 | High-Q & High Power type | 0606 | CH | 50 | 30 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H330JD01 | High-Q & High Power type | 0606 | CH | 50 | 33 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H360JD01 | High-Q & High Power type | 0606 | CH | 50 | 36 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H390JD01 | High-Q & High Power type | 0606 | CH | 50 | 39 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H430JD01 | High-Q & High Power type | 0606 | CH | 50 | 43 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H470JD01 | High-Q & High Power type | 0606 | CH | 50 | 47 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H510JD01 | High-Q & High Power type | 0606 | CH | 50 | 51 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H560JD01 | High-Q & High Power type | 0606 | CH | 50 | 56 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H620JD01 | High-Q & High Power type | 0606 | CH | 50 | 62 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H680JD01 | High-Q & High Power type | 0606 | CH | 50 | 68 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H750JD01 | High-Q & High Power type | 0606 | CH | 50 | 75 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H820JD01 | High-Q & High Power type | 0606 | CH | 50 | 82 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H910JD01 | High-Q & High Power type | 0606 | CH | 50 | 91 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF1DM6C1H101JD01 | High-Q & High Power type | 0606 | CH | 50 | 100 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2HR50CD01 | High-Q & High Power type | 1111 | CH | 500 | 0.5 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| ERF22X6C2HR75CD01 | High-Q & High Power type | 1111 | CH | 500 | 0.75 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| ERF22X6C2H1R0CD01 | High-Q & High Power type | 1111 | CH | 500 | 1 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| ERF22X6C2H1R5CD01 | High-Q & High Power type | 1111 | CH | 500 | 1.5 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| ERF22X6C2H2R0CD01 | High-Q & High Power type | 1111 | CH | 500 | 2 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| ERF22X6C2H3R0CD01 | High-Q & High Power type | 1111 | CH | 500 | 3 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| ERF22X6C2H4R0CD01 | High-Q & High Power type | 1111 | CH | 500 | 4 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| ERF22X6C2H5R0CD01 | High-Q & High Power type | 1111 | CH | 500 | 5 | +/-0.25[pF] | 300[kHz]-6[GHz] |
| ERF22X6C2H6R0DD01 | High-Q & High Power type | 1111 | CH | 500 | 6 | +/-0.5[pF] | 300[kHz]-6[GHz] |
| ERF22X6C2H7R0DD01 | High-Q & High Power type | 1111 | CH | 500 | 7 | +/-0.5[pF] | 300[kHz]-6[GHz] |
| ERF22X6C2H8R0DD01 | High-Q & High Power type | 1111 | CH | 500 | 8 | +/-0.5[pF] | 300[kHz]-6[GHz] |
| ERF22X6C2H9R0DD01 | High-Q & High Power type | 1111 | CH | 500 | 9 | +/-0.5[pF] | 300[kHz]-6[GHz] |
| ERF22X6C2H100JD01 | High-Q & High Power type | 1111 | CH | 500 | 10 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H110JD01 | High-Q & High Power type | 1111 | CH | 500 | 11 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H120JD01 | High-Q & High Power type | 1111 | CH | 500 | 12 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H130JD01 | High-Q & High Power type | 1111 | CH | 500 | 13 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H150JD01 | High-Q & High Power type | 1111 | CH | 500 | 15 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H160JD01 | High-Q & High Power type | 1111 | CH | 500 | 16 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H180JD01 | High-Q & High Power type | 1111 | CH | 500 | 18 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H200JD01 | High-Q & High Power type | 1111 | CH | 500 | 20 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H220JD01 | High-Q & High Power type | 1111 | CH | 500 | 22 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H240JD01 | High-Q & High Power type | 1111 | CH | 500 | 24 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H270JD01 | High-Q & High Power type | 1111 | CH | 500 | 27 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H300JD01 | High-Q & High Power type | 1111 | CH | 500 | 30 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H330JD01 | High-Q & High Power type | 1111 | CH | 500 | 33 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H360JD01 | High-Q & High Power type | 1111 | CH | 500 | 36 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H390JD01 | High-Q & High Power type | 1111 | CH | 500 | 39 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H430JD01 | High-Q & High Power type | 1111 | CH | 500 | 43 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H470JD01 | High-Q & High Power type | 1111 | CH | 500 | 47 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H510JD01 | High-Q & High Power type | 1111 | CH | 500 | 51 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H560JD01 | High-Q & High Power type | 1111 | CH | 500 | 56 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H620JD01 | High-Q & High Power type | 1111 | CH | 500 | 62 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H680JD01 | High-Q & High Power type | 1111 | CH | 500 | 68 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H750JD01 | High-Q & High Power type | 1111 | CH | 500 | 75 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H820JD01 | High-Q & High Power type | 1111 | CH | 500 | 82 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H910JD01 | High-Q & High Power type | 1111 | CH | 500 | 91 | +/-5[%] | 300[kHz]-6[GHz] |
| ERF22X6C2H101JD01 | High-Q & High Power type | 1111 | CH | 500 | 100 | +/-5[%] | 300[kHz]-6[GHz] |
| LLL153C80J104ME01 | Low ESL type | 0204 | X6S | 6.3 | 100000 | +/-20[%] | 300[kHz]-6[GHz] |
| LLL153C80J224ME14 | Low ESL type | 0204 | X6S | 6.3 | 220000 | +/-20[%] | 300[kHz]-6[GHz] |
| LLL185R71H222MA01 | Low ESL type | 0306 | X7R | 50 | 2200 | +/-20[%] | 300[kHz]-6[GHz] |
| LLL185R71H472MA01 | Low ESL type | 0306 | X7R | 50 | 4700 | +/-20[%] | 300[kHz]-6[GHz] |
| LLL185R71E103MA01 | Low ESL type | 0306 | X7R | 25 | 10000 | +/-20[%] | 300[kHz]-6[GHz] |
| LLL185R71E103MA11 | Low ESL type | 0306 | X7R | 25 | 10000 | +/-20[%] | 300[kHz]-6[GHz] |
| LLL185R71C103MA11 | Low ESL type | 0306 | X7R | 16 | 10000 | +/-20[%] | 300[kHz]-6[GHz] |
| LLL185R71E223MA01 | Low ESL type | 0306 | X7R | 25 | 22000 | +/-20[%] | 300[kHz]-6[GHz] |
| LLL185R71C223MA11 | Low ESL type | 0306 | X7R | 16 | 22000 | +/-20[%] | 300[kHz]-6[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Temp Characteristics (EIA) | Rated Voltage [V] | Capacitance [pF] | Tolerance | Frequency Range |
|-------------------|--------------|----------------|----------------------------|-------------------|------------------|-----------|-----------------|
| LLL185R71C473MA01 | Low ESL type | 0306 | X7R | 16 | 47000 | +/-20% | 300[kHz]-6[GHz] |
| LLL185R71A104MA01 | Low ESL type | 0306 | X7R | 10 | 100000 | +/-20% | 300[kHz]-6[GHz] |
| LLL185R71A104MA11 | Low ESL type | 0306 | X7R | 10 | 100000 | +/-20% | 300[kHz]-6[GHz] |
| LLL185R70J224MA01 | Low ESL type | 0306 | X7R | 6.3 | 220000 | +/-20% | 300[kHz]-6[GHz] |
| LLL185C70G224MA11 | Low ESL type | 0306 | X7S | 4 | 220000 | +/-20% | 300[kHz]-6[GHz] |
| LLL185C70G474MA01 | Low ESL type | 0306 | X7S | 4 | 470000 | +/-20% | 300[kHz]-6[GHz] |
| LLL185C70G105ME01 | Low ESL type | 0306 | X7S | 4 | 1000000 | +/-20% | 300[kHz]-6[GHz] |
| LLL185C70G225ME01 | Low ESL type | 0306 | X7S | 4 | 2200000 | +/-20% | 300[kHz]-6[GHz] |
| LLL216R71H472MA01 | Low ESL type | 0508 | X7R | 50 | 4700 | +/-20% | 300[kHz]-6[GHz] |
| LLL215R71H103MA11 | Low ESL type | 0508 | X7R | 50 | 10000 | +/-20% | 300[kHz]-6[GHz] |
| LLL216R71H103MA01 | Low ESL type | 0508 | X7R | 50 | 10000 | +/-20% | 300[kHz]-6[GHz] |
| LLL216R71H223MA01 | Low ESL type | 0508 | X7R | 50 | 22000 | +/-20% | 300[kHz]-6[GHz] |
| LLL215R71E223MA11 | Low ESL type | 0508 | X7R | 25 | 22000 | +/-20% | 300[kHz]-6[GHz] |
| LLL216R71E473MA01 | Low ESL type | 0508 | X7R | 25 | 47000 | +/-20% | 300[kHz]-6[GHz] |
| LLL215R71C473MA11 | Low ESL type | 0508 | X7R | 16 | 47000 | +/-20% | 300[kHz]-6[GHz] |
| LLL216R71E104MA01 | Low ESL type | 0508 | X7R | 25 | 100000 | +/-20% | 300[kHz]-6[GHz] |
| LLL215R71C104MA11 | Low ESL type | 0508 | X7R | 16 | 100000 | +/-20% | 300[kHz]-6[GHz] |
| LLL219R71C224MA01 | Low ESL type | 0508 | X7R | 16 | 220000 | +/-20% | 300[kHz]-6[GHz] |
| LLL215R71A224MA11 | Low ESL type | 0508 | X7R | 10 | 220000 | +/-20% | 300[kHz]-6[GHz] |
| LLL216R71A224MA01 | Low ESL type | 0508 | X7R | 10 | 220000 | +/-20% | 300[kHz]-6[GHz] |
| LLL219R71A474MA01 | Low ESL type | 0508 | X7R | 10 | 470000 | +/-20% | 300[kHz]-6[GHz] |
| LLL215R70J474MA11 | Low ESL type | 0508 | X7R | 6.3 | 470000 | +/-20% | 300[kHz]-6[GHz] |
| LLL219R70J105MA01 | Low ESL type | 0508 | X7R | 6.3 | 1000000 | +/-20% | 300[kHz]-6[GHz] |
| LLL215C70G105MA11 | Low ESL type | 0508 | X7S | 4 | 1000000 | +/-20% | 300[kHz]-6[GHz] |
| LLL219C70G225MA01 | Low ESL type | 0508 | X7S | 4 | 2200000 | +/-20% | 300[kHz]-6[GHz] |
| LLL317R71H103MA01 | Low ESL type | 0612 | X7R | 50 | 10000 | +/-20% | 300[kHz]-6[GHz] |
| LLL315R71H223MA11 | Low ESL type | 0612 | X7R | 50 | 22000 | +/-20% | 300[kHz]-6[GHz] |
| LLL317R71H223MA01 | Low ESL type | 0612 | X7R | 50 | 22000 | +/-20% | 300[kHz]-6[GHz] |
| LLL317R71H473MA01 | Low ESL type | 0612 | X7R | 50 | 47000 | +/-20% | 300[kHz]-6[GHz] |
| LLL315R71E473MA11 | Low ESL type | 0612 | X7R | 25 | 47000 | +/-20% | 300[kHz]-6[GHz] |
| LLL31MR71H104MA01 | Low ESL type | 0612 | X7R | 50 | 100000 | +/-20% | 300[kHz]-6[GHz] |
| LLL315R71E104MA11 | Low ESL type | 0612 | X7R | 25 | 100000 | +/-20% | 300[kHz]-6[GHz] |
| LLL317R71E104MA01 | Low ESL type | 0612 | X7R | 25 | 100000 | +/-20% | 300[kHz]-6[GHz] |
| LLL31MR71E224MA01 | Low ESL type | 0612 | X7R | 25 | 220000 | +/-20% | 300[kHz]-6[GHz] |
| LLL315R71C224MA11 | Low ESL type | 0612 | X7R | 16 | 220000 | +/-20% | 300[kHz]-6[GHz] |
| LLL317R71C224MA01 | Low ESL type | 0612 | X7R | 16 | 220000 | +/-20% | 300[kHz]-6[GHz] |
| LLL31MR71E474MA01 | Low ESL type | 0612 | X7R | 25 | 470000 | +/-20% | 300[kHz]-6[GHz] |
| LLL317R71C474MA01 | Low ESL type | 0612 | X7R | 16 | 470000 | +/-20% | 300[kHz]-6[GHz] |
| LLL315R71A474MA11 | Low ESL type | 0612 | X7R | 10 | 470000 | +/-20% | 300[kHz]-6[GHz] |
| LLL31MR71C105MA01 | Low ESL type | 0612 | X7R | 16 | 1000000 | +/-20% | 300[kHz]-6[GHz] |
| LLL317R71A105MA01 | Low ESL type | 0612 | X7R | 10 | 1000000 | +/-20% | 300[kHz]-6[GHz] |
| LLL31MR71A225MA01 | Low ESL type | 0612 | X7R | 10 | 2200000 | +/-20% | 300[kHz]-6[GHz] |
| LLL317R70J225MA01 | Low ESL type | 0612 | X7R | 6.3 | 2200000 | +/-20% | 300[kHz]-6[GHz] |
| LLL31MR70J475MA01 | Low ESL type | 0612 | X7R | 6.3 | 4700000 | +/-20% | 300[kHz]-6[GHz] |
| LLL31MR60J106ME01 | Low ESL type | 0612 | X5R | 6.3 | 10000000 | +/-20% | 300[kHz]-6[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Rated Current [V] | Inductance [nH] | Tolerance | Frequency Range |
|---------------|-----------------------------|----------------|-------------------|-----------------|------------|------------------|
| LQP02TN0N4S02 | High Frequency Film Type | 01005 | 160 | 0.4 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQP02TN0N6S02 | High Frequency Film Type | 01005 | 160 | 0.6 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQP02TN0N8S02 | High Frequency Film Type | 01005 | 160 | 0.8 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQP02TN1N0S02 | High Frequency Film Type | 01005 | 110 | 1 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQP02TN1N2S02 | High Frequency Film Type | 01005 | 110 | 1.2 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQP02TN1N5S02 | High Frequency Film Type | 01005 | 110 | 1.5 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQP02TN1N8S02 | High Frequency Film Type | 01005 | 100 | 1.8 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQP02TN2N2S02 | High Frequency Film Type | 01005 | 100 | 2.2 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQP02TN2N7S02 | High Frequency Film Type | 01005 | 100 | 2.7 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQP02TN3N3S02 | High Frequency Film Type | 01005 | 90 | 3.3 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQP02TN3N9S02 | High Frequency Film Type | 01005 | 90 | 3.9 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQP02TN4N7S02 | High Frequency Film Type | 01005 | 80 | 4.7 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQP02TN5N6S02 | High Frequency Film Type | 01005 | 70 | 5.6 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQP02TN6N8J02 | High Frequency Film Type | 01005 | 70 | 6.8 | +/-5[%] | 10[MHz]-6[GHz] |
| LQP02TN8N2J02 | High Frequency Film Type | 01005 | 70 | 8.2 | +/-5[%] | 10[MHz]-6[GHz] |
| LQP02TN10NJ02 | High Frequency Film Type | 01005 | 70 | 10 | +/-5[%] | 10[MHz]-6[GHz] |
| LQP03TN0N6B04 | High Frequency Film Type | 0201 | 420 | 0.6 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN0N7B04 | High Frequency Film Type | 0201 | 410 | 0.7 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN0N8B04 | High Frequency Film Type | 0201 | 410 | 0.8 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN0N9B04 | High Frequency Film Type | 0201 | 400 | 0.9 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN1N0B04 | High Frequency Film Type | 0201 | 400 | 1 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN1N1B04 | High Frequency Film Type | 0201 | 280 | 1.1 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN1N2B04 | High Frequency Film Type | 0201 | 280 | 1.2 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN1N3B04 | High Frequency Film Type | 0201 | 280 | 1.3 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN1N4B04 | High Frequency Film Type | 0201 | 280 | 1.4 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN1N5B04 | High Frequency Film Type | 0201 | 280 | 1.5 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN1N6B04 | High Frequency Film Type | 0201 | 280 | 1.6 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN1N7B04 | High Frequency Film Type | 0201 | 280 | 1.7 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN1N8B04 | High Frequency Film Type | 0201 | 280 | 1.8 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN1N9B04 | High Frequency Film Type | 0201 | 220 | 1.9 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN2N0B04 | High Frequency Film Type | 0201 | 220 | 2 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN2N1B04 | High Frequency Film Type | 0201 | 220 | 2.1 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN2N2B04 | High Frequency Film Type | 0201 | 220 | 2.2 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN2N3B04 | High Frequency Film Type | 0201 | 220 | 2.3 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN2N4B04 | High Frequency Film Type | 0201 | 220 | 2.4 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN2N5B04 | High Frequency Film Type | 0201 | 220 | 2.5 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN2N6B04 | High Frequency Film Type | 0201 | 220 | 2.6 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN2N7B04 | High Frequency Film Type | 0201 | 220 | 2.7 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN2N8B04 | High Frequency Film Type | 0201 | 220 | 2.8 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN2N9B04 | High Frequency Film Type | 0201 | 220 | 2.9 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN3N0B04 | High Frequency Film Type | 0201 | 190 | 3 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN3N1B04 | High Frequency Film Type | 0201 | 190 | 3.1 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN3N2B04 | High Frequency Film Type | 0201 | 190 | 3.2 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN3N3B04 | High Frequency Film Type | 0201 | 190 | 3.3 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN3N4B04 | High Frequency Film Type | 0201 | 190 | 3.4 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN3N5B04 | High Frequency Film Type | 0201 | 190 | 3.5 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN3N6B04 | High Frequency Film Type | 0201 | 170 | 3.6 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN3N7B04 | High Frequency Film Type | 0201 | 170 | 3.7 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN3N8B04 | High Frequency Film Type | 0201 | 170 | 3.8 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN3N9B04 | High Frequency Film Type | 0201 | 170 | 3.9 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP03TN4N3H04 | High Frequency Film Type | 0201 | 160 | 4.3 | +/-3[%] | 10[MHz]-6[GHz] |
| LQP03TN4N7H04 | High Frequency Film Type | 0201 | 160 | 4.7 | +/-3[%] | 10[MHz]-6[GHz] |
| LQP03TN5N1H04 | High Frequency Film Type | 0201 | 140 | 5.1 | +/-3[%] | 10[MHz]-6[GHz] |
| LQP03TN5N6H04 | High Frequency Film Type | 0201 | 140 | 5.6 | +/-3[%] | 10[MHz]-6[GHz] |
| LQP03TN6N8H04 | High Frequency Film Type | 0201 | 130 | 6.8 | +/-3[%] | 10[MHz]-6[GHz] |
| LQP03TN8N2H04 | High Frequency Film Type | 0201 | 110 | 8.2 | +/-3[%] | 10[MHz]-6[GHz] |
| LQP03TN10NH04 | High Frequency Film Type | 0201 | 100 | 10 | +/-3[%] | 10[MHz]-5.9[GHz] |
| LQP03TN12NJ04 | High Frequency Film Type | 0201 | 90 | 12 | +/-5[%] | 10[MHz]-5.6[GHz] |
| LQP03TN15NJ04 | High Frequency Film Type | 0201 | 90 | 15 | +/-5[%] | 10[MHz]-4.8[GHz] |
| LQP03TN18NH04 | High Frequency Film Type | 0201 | 80 | 18 | +/-3[%] | 10[MHz]-4.2[GHz] |
| LQP03TN22NH04 | High Frequency Film Type | 0201 | 70 | 22 | +/-3[%] | 10[MHz]-3.7[GHz] |
| LQP03TN27NH04 | High Frequency Film Type | 0201 | 70 | 27 | +/-3[%] | 10[MHz]-3.4[GHz] |
| LQP03TN33NJ04 | High Frequency Film Type | 0201 | 60 | 33 | +/-5[%] | 10[MHz]-2.9[GHz] |
| LQP03TN39NJ04 | High Frequency Film Type | 0201 | 60 | 39 | +/-5[%] | 10[MHz]-2.7[GHz] |
| LQP03TN47NJ04 | High Frequency Film Type | 0201 | 50 | 47 | +/-5[%] | 10[MHz]-2.4[GHz] |
| LQP03TN56NJ04 | High Frequency Film Type | 0201 | 50 | 56 | +/-5[%] | 10[MHz]-2.2[GHz] |
| LQW04AN1N1D00 | High Frequency Winding Type | 03015 | 990 | 1.1 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW04AN1N8D00 | High Frequency Winding Type | 03015 | 700 | 1.8 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW04AN2N7D00 | High Frequency Winding Type | 03015 | 570 | 2.7 | +/-0.5[nH] | 10[MHz]-6[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Rated Current [V] | Inductance [nH] | Tolerance | Frequency Range |
|---------------|--------------------------------|----------------|-------------------|-----------------|------------|------------------|
| LQW04AN3N0D00 | High Frequency Winding Type | 03015 | 620 | 3 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW04AN3N6D00 | High Frequency Winding Type | 03015 | 530 | 3.6 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW04AN3N9D00 | High Frequency Winding Type | 03015 | 530 | 3.9 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW04AN4N3D00 | High Frequency Winding Type | 03015 | 530 | 4.3 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW04AN4N7D00 | High Frequency Winding Type | 03015 | 440 | 4.7 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW04AN5N1D00 | High Frequency Winding Type | 03015 | 470 | 5.1 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW04AN5N6D00 | High Frequency Winding Type | 03015 | 470 | 5.6 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW04AN6N2D00 | High Frequency Winding Type | 03015 | 390 | 6.2 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW04AN6N8D00 | High Frequency Winding Type | 03015 | 440 | 6.8 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW04AN7N5D00 | High Frequency Winding Type | 03015 | 440 | 7.5 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW04AN8N2D00 | High Frequency Winding Type | 03015 | 350 | 8.2 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW04AN9N1D00 | High Frequency Winding Type | 03015 | 400 | 9.1 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW04AN10NJ00 | High Frequency Winding Type | 03015 | 330 | 10 | +/-5[%] | 10[MHz]-6[GHz] |
| LQW04AN11NJ00 | High Frequency Winding Type | 03015 | 310 | 11 | +/-5[%] | 10[MHz]-6[GHz] |
| LQW04AN12NJ00 | High Frequency Winding Type | 03015 | 310 | 12 | +/-5[%] | 10[MHz]-6[GHz] |
| LQW04AN13NJ00 | High Frequency Winding Type | 03015 | 280 | 13 | +/-5[%] | 10[MHz]-6[GHz] |
| LQW04AN15NJ00 | High Frequency Winding Type | 03015 | 240 | 15 | +/-5[%] | 10[MHz]-6[GHz] |
| LQW04AN16NJ00 | High Frequency Winding Type | 03015 | 270 | 16 | +/-5[%] | 10[MHz]-6[GHz] |
| LQW04AN18NJ00 | High Frequency Winding Type | 03015 | 220 | 18 | +/-5[%] | 10[MHz]-6[GHz] |
| LQW04AN20NJ00 | High Frequency Winding Type | 03015 | 210 | 20 | +/-5[%] | 10[MHz]-6[GHz] |
| LQW04AN22NJ00 | High Frequency Winding Type | 03015 | 200 | 22 | +/-5[%] | 10[MHz]-6[GHz] |
| LQG15HN1N0S02 | High Frequency Monolithic Type | 0402 | 300 | 1 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HN1N1S02 | High Frequency Monolithic Type | 0402 | 300 | 1.1 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HN1N2S02 | High Frequency Monolithic Type | 0402 | 300 | 1.2 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HN1N3S02 | High Frequency Monolithic Type | 0402 | 300 | 1.3 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HN1N5S02 | High Frequency Monolithic Type | 0402 | 300 | 1.5 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HN1N6S02 | High Frequency Monolithic Type | 0402 | 300 | 1.6 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HN1N8S02 | High Frequency Monolithic Type | 0402 | 300 | 1.8 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HN2N0S02 | High Frequency Monolithic Type | 0402 | 300 | 2 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HN2N2S02 | High Frequency Monolithic Type | 0402 | 300 | 2.2 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HN2N4S02 | High Frequency Monolithic Type | 0402 | 300 | 2.4 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HN2N7S02 | High Frequency Monolithic Type | 0402 | 300 | 2.7 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HN3N0S02 | High Frequency Monolithic Type | 0402 | 300 | 3 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HN3N3S02 | High Frequency Monolithic Type | 0402 | 300 | 3.3 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HN3N6S02 | High Frequency Monolithic Type | 0402 | 300 | 3.6 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HN3N9S02 | High Frequency Monolithic Type | 0402 | 300 | 3.9 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HN4N3S02 | High Frequency Monolithic Type | 0402 | 300 | 4.3 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HN4N7S02 | High Frequency Monolithic Type | 0402 | 300 | 4.7 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HN5N1S02 | High Frequency Monolithic Type | 0402 | 300 | 5.1 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HN5N6S02 | High Frequency Monolithic Type | 0402 | 300 | 5.6 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HN6N2S02 | High Frequency Monolithic Type | 0402 | 300 | 6.2 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HN6N8J02 | High Frequency Monolithic Type | 0402 | 300 | 6.8 | +/-5[%] | 10[MHz]-5.4[GHz] |
| LQG15HN7N5J02 | High Frequency Monolithic Type | 0402 | 300 | 7.5 | +/-5[%] | 10[MHz]-5.9[GHz] |
| LQG15HN8N2J02 | High Frequency Monolithic Type | 0402 | 300 | 8.2 | +/-5[%] | 10[MHz]-5.3[GHz] |
| LQG15HN9N1J02 | High Frequency Monolithic Type | 0402 | 300 | 9.1 | +/-5[%] | 10[MHz]-4.7[GHz] |
| LQG15HN10NJ02 | High Frequency Monolithic Type | 0402 | 300 | 10 | +/-5[%] | 10[MHz]-5[GHz] |
| LQG15HN12NJ02 | High Frequency Monolithic Type | 0402 | 300 | 12 | +/-5[%] | 10[MHz]-4.2[GHz] |
| LQG15HN15NJ02 | High Frequency Monolithic Type | 0402 | 300 | 15 | +/-5[%] | 10[MHz]-3.7[GHz] |
| LQG15HN18NJ02 | High Frequency Monolithic Type | 0402 | 300 | 18 | +/-5[%] | 10[MHz]-3.3[GHz] |
| LQG15HN22NJ02 | High Frequency Monolithic Type | 0402 | 300 | 22 | +/-5[%] | 10[MHz]-3[GHz] |
| LQG15HN27NJ02 | High Frequency Monolithic Type | 0402 | 300 | 27 | +/-5[%] | 10[MHz]-2.6[GHz] |
| LQG15HN33NJ02 | High Frequency Monolithic Type | 0402 | 200 | 33 | +/-5[%] | 10[MHz]-2.3[GHz] |
| LQG15HN39NJ02 | High Frequency Monolithic Type | 0402 | 200 | 39 | +/-5[%] | 10[MHz]-2.1[GHz] |
| LQG15HN47NJ02 | High Frequency Monolithic Type | 0402 | 200 | 47 | +/-5[%] | 10[MHz]-1.8[GHz] |
| LQG15HN56NJ02 | High Frequency Monolithic Type | 0402 | 200 | 56 | +/-5[%] | 10[MHz]-1.6[GHz] |
| LQG15HN68NJ02 | High Frequency Monolithic Type | 0402 | 180 | 68 | +/-5[%] | 10[MHz]-1.5[GHz] |
| LQG15HN82NJ02 | High Frequency Monolithic Type | 0402 | 150 | 82 | +/-5[%] | 10[MHz]-1.3[GHz] |
| LQG15HNR10J02 | High Frequency Monolithic Type | 0402 | 150 | 100 | +/-5[%] | 10[MHz]-1.1[GHz] |
| LQG15HNR12J02 | High Frequency Monolithic Type | 0402 | 150 | 120 | +/-5[%] | 10[MHz]-1[GHz] |
| LQG15HS1N0S02 | High Frequency Monolithic Type | 0402 | 300 | 1 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HS1N1S02 | High Frequency Monolithic Type | 0402 | 300 | 1.1 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HS1N2S02 | High Frequency Monolithic Type | 0402 | 300 | 1.2 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HS1N3S02 | High Frequency Monolithic Type | 0402 | 300 | 1.3 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HS1N5S02 | High Frequency Monolithic Type | 0402 | 300 | 1.5 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HS1N6S02 | High Frequency Monolithic Type | 0402 | 300 | 1.6 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HS1N8S02 | High Frequency Monolithic Type | 0402 | 300 | 1.8 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HS2N0S02 | High Frequency Monolithic Type | 0402 | 300 | 2 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HS2N2S02 | High Frequency Monolithic Type | 0402 | 300 | 2.2 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HS2N4S02 | High Frequency Monolithic Type | 0402 | 300 | 2.4 | +/-0.3[nH] | 10[MHz]-6[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Rated Current [V] | Inductance [nH] | Tolerance | Frequency Range |
|---------------|--------------------------------|----------------|-------------------|-----------------|-------------|------------------|
| LQG15HS2N7S02 | High Frequency Monolithic Type | 0402 | 300 | 2.7 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HS3N0S02 | High Frequency Monolithic Type | 0402 | 300 | 3 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HS3N3S02 | High Frequency Monolithic Type | 0402 | 300 | 3.3 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HS3N6S02 | High Frequency Monolithic Type | 0402 | 300 | 3.6 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HS3N9S02 | High Frequency Monolithic Type | 0402 | 300 | 3.9 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HS4N3S02 | High Frequency Monolithic Type | 0402 | 300 | 4.3 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HS4N7S02 | High Frequency Monolithic Type | 0402 | 300 | 4.7 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HS5N1S02 | High Frequency Monolithic Type | 0402 | 300 | 5.1 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HS5N6S02 | High Frequency Monolithic Type | 0402 | 300 | 5.6 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HS6N2S02 | High Frequency Monolithic Type | 0402 | 300 | 6.2 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG15HS6N8J02 | High Frequency Monolithic Type | 0402 | 300 | 6.8 | +/-5[%] | 10[MHz]-5.9[GHz] |
| LQG15HS7N5J02 | High Frequency Monolithic Type | 0402 | 300 | 7.5 | +/-5[%] | 10[MHz]-5.4[GHz] |
| LQG15HS8N2J02 | High Frequency Monolithic Type | 0402 | 300 | 8.2 | +/-5[%] | 10[MHz]-5[GHz] |
| LQG15HS9N1J02 | High Frequency Monolithic Type | 0402 | 300 | 9.1 | +/-5[%] | 10[MHz]-5[GHz] |
| LQG15HS10NJ02 | High Frequency Monolithic Type | 0402 | 300 | 10 | +/-5[%] | 10[MHz]-4.7[GHz] |
| LQG15HS12NJ02 | High Frequency Monolithic Type | 0402 | 300 | 12 | +/-5[%] | 10[MHz]-3.9[GHz] |
| LQG15HS15NJ02 | High Frequency Monolithic Type | 0402 | 300 | 15 | +/-5[%] | 10[MHz]-3.5[GHz] |
| LQG15HS18NJ02 | High Frequency Monolithic Type | 0402 | 300 | 18 | +/-5[%] | 10[MHz]-3.4[GHz] |
| LQG15HS22NJ02 | High Frequency Monolithic Type | 0402 | 300 | 22 | +/-5[%] | 10[MHz]-3[GHz] |
| LQG15HS27NJ02 | High Frequency Monolithic Type | 0402 | 300 | 27 | +/-5[%] | 10[MHz]-2.4[GHz] |
| LQG15HS33NJ02 | High Frequency Monolithic Type | 0402 | 200 | 33 | +/-5[%] | 10[MHz]-2.3[GHz] |
| LQG15HS39NJ02 | High Frequency Monolithic Type | 0402 | 200 | 39 | +/-5[%] | 10[MHz]-2.1[GHz] |
| LQG15HS47NJ02 | High Frequency Monolithic Type | 0402 | 200 | 47 | +/-5[%] | 10[MHz]-1.8[GHz] |
| LQG15HS56NJ02 | High Frequency Monolithic Type | 0402 | 200 | 56 | +/-5[%] | 10[MHz]-1.6[GHz] |
| LQG15HS68NJ02 | High Frequency Monolithic Type | 0402 | 180 | 68 | +/-5[%] | 10[MHz]-1.5[GHz] |
| LQG15HS82NJ02 | High Frequency Monolithic Type | 0402 | 150 | 82 | +/-5[%] | 10[MHz]-1.4[GHz] |
| LQG15HSR10J02 | High Frequency Monolithic Type | 0402 | 150 | 100 | +/-5[%] | 10[MHz]-1.1[GHz] |
| LQG15HSR12J02 | High Frequency Monolithic Type | 0402 | 150 | 120 | +/-5[%] | 10[MHz]-0.9[GHz] |
| LQG15HSR15J02 | High Frequency Monolithic Type | 0402 | 140 | 150 | +/-5[%] | 10[MHz]-1[GHz] |
| LQG15HSR18J02 | High Frequency Monolithic Type | 0402 | 130 | 180 | +/-5[%] | 10[MHz]-0.9[GHz] |
| LQG15HSR22J02 | High Frequency Monolithic Type | 0402 | 120 | 220 | +/-5[%] | 10[MHz]-0.8[GHz] |
| LQG15HSR27J02 | High Frequency Monolithic Type | 0402 | 110 | 270 | +/-5[%] | 10[MHz]-0.7[GHz] |
| LQP15MN1N0W02 | High Frequency Film Type | 0402 | 400 | 1 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN1N1W02 | High Frequency Film Type | 0402 | 390 | 1.1 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN1N2W02 | High Frequency Film Type | 0402 | 390 | 1.2 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN1N3W02 | High Frequency Film Type | 0402 | 280 | 1.3 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN1N4W02 | High Frequency Film Type | 0402 | 280 | 1.4 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN1N5W02 | High Frequency Film Type | 0402 | 280 | 1.5 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN1N6W02 | High Frequency Film Type | 0402 | 220 | 1.6 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN1N7W02 | High Frequency Film Type | 0402 | 280 | 1.7 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN1N8W02 | High Frequency Film Type | 0402 | 280 | 1.8 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN1N9W02 | High Frequency Film Type | 0402 | 220 | 1.9 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN2N0W02 | High Frequency Film Type | 0402 | 220 | 2 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN2N1W02 | High Frequency Film Type | 0402 | 220 | 2.1 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN2N2W02 | High Frequency Film Type | 0402 | 220 | 2.2 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN2N3W02 | High Frequency Film Type | 0402 | 220 | 2.3 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN2N4W02 | High Frequency Film Type | 0402 | 220 | 2.4 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN2N5W02 | High Frequency Film Type | 0402 | 220 | 2.5 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN2N6W02 | High Frequency Film Type | 0402 | 220 | 2.6 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN2N7W02 | High Frequency Film Type | 0402 | 220 | 2.7 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN2N8W02 | High Frequency Film Type | 0402 | 190 | 2.8 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN2N9W02 | High Frequency Film Type | 0402 | 190 | 2.9 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN3N0W02 | High Frequency Film Type | 0402 | 190 | 3 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN3N1W02 | High Frequency Film Type | 0402 | 190 | 3.1 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN3N2W02 | High Frequency Film Type | 0402 | 190 | 3.2 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN3N3W02 | High Frequency Film Type | 0402 | 190 | 3.3 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN3N4W02 | High Frequency Film Type | 0402 | 170 | 3.4 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN3N5W02 | High Frequency Film Type | 0402 | 170 | 3.5 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN3N6W02 | High Frequency Film Type | 0402 | 170 | 3.6 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN3N7W02 | High Frequency Film Type | 0402 | 170 | 3.7 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN3N8W02 | High Frequency Film Type | 0402 | 170 | 3.8 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN3N9W02 | High Frequency Film Type | 0402 | 170 | 3.9 | +/-0.05[nH] | 10[MHz]-6[GHz] |
| LQP15MN4N3B02 | High Frequency Film Type | 0402 | 160 | 4.3 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP15MN4N7B02 | High Frequency Film Type | 0402 | 160 | 4.7 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP15MN5N1B02 | High Frequency Film Type | 0402 | 140 | 5.1 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP15MN5N6B02 | High Frequency Film Type | 0402 | 140 | 5.6 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP15MN6N2B02 | High Frequency Film Type | 0402 | 130 | 6.2 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP15MN6N8B02 | High Frequency Film Type | 0402 | 130 | 6.8 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP15MN7N5B02 | High Frequency Film Type | 0402 | 110 | 7.5 | +/-0.1[nH] | 10[MHz]-6[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Rated Current [V] | Inductance [nH] | Tolerance | Frequency Range |
|---------------|-----------------------------|----------------|-------------------|-----------------|------------|------------------|
| LQP15MN8N2B02 | High Frequency Film Type | 0402 | 110 | 8.2 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP15MN9N1B02 | High Frequency Film Type | 0402 | 100 | 9.1 | +/-0.1[nH] | 10[MHz]-6[GHz] |
| LQP15MN10NG02 | High Frequency Film Type | 0402 | 100 | 10 | +/-2[%] | 10[MHz]-6[GHz] |
| LQP15MN12NG02 | High Frequency Film Type | 0402 | 90 | 12 | +/-2[%] | 10[MHz]-5.8[GHz] |
| LQP15MN15NG02 | High Frequency Film Type | 0402 | 90 | 15 | +/-2[%] | 10[MHz]-5.1[GHz] |
| LQP15MN18NG02 | High Frequency Film Type | 0402 | 80 | 18 | +/-2[%] | 10[MHz]-4.7[GHz] |
| LQP15MN22NG02 | High Frequency Film Type | 0402 | 70 | 22 | +/-2[%] | 10[MHz]-4.1[GHz] |
| LQP15MN27NG02 | High Frequency Film Type | 0402 | 70 | 27 | +/-2[%] | 10[MHz]-3.8[GHz] |
| LQP15MN33NG02 | High Frequency Film Type | 0402 | 60 | 33 | +/-2[%] | 10[MHz]-3.3[GHz] |
| LQP15TN2N0C02 | High Frequency Film Type | 0402 | 220 | 2 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQP15TN2N2C02 | High Frequency Film Type | 0402 | 220 | 2.2 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQP15TN2N4C02 | High Frequency Film Type | 0402 | 220 | 2.4 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQP15TN2N7C02 | High Frequency Film Type | 0402 | 220 | 2.7 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQP15TN3N3C02 | High Frequency Film Type | 0402 | 190 | 3.3 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQP15TN3N6C02 | High Frequency Film Type | 0402 | 170 | 3.6 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQP15TN3N9C02 | High Frequency Film Type | 0402 | 170 | 3.9 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQP15TN4N7C02 | High Frequency Film Type | 0402 | 160 | 4.7 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQP15TN5N6C02 | High Frequency Film Type | 0402 | 140 | 5.6 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQP15TN6N8H02 | High Frequency Film Type | 0402 | 130 | 6.8 | +/-3[%] | 10[MHz]-6[GHz] |
| LQP15TN8N2H02 | High Frequency Film Type | 0402 | 110 | 8.2 | +/-3[%] | 10[MHz]-5.2[GHz] |
| LQP15TN10NH02 | High Frequency Film Type | 0402 | 100 | 10 | +/-3[%] | 10[MHz]-4.8[GHz] |
| LQP15TN12NH02 | High Frequency Film Type | 0402 | 90 | 12 | +/-3[%] | 10[MHz]-3.8[GHz] |
| LQP15TN15NH02 | High Frequency Film Type | 0402 | 90 | 15 | +/-3[%] | 10[MHz]-3.4[GHz] |
| LQP15TN18NH02 | High Frequency Film Type | 0402 | 80 | 18 | +/-3[%] | 10[MHz]-3[GHz] |
| LQW15AN1N5C00 | High Frequency Winding Type | 0402 | 1000 | 1.5 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW15AN2N4C00 | High Frequency Winding Type | 0402 | 850 | 2.4 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW15AN2N5C00 | High Frequency Winding Type | 0402 | 850 | 2.5 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW15AN2N7C00 | High Frequency Winding Type | 0402 | 850 | 2.7 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW15AN2N9C00 | High Frequency Winding Type | 0402 | 750 | 2.9 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW15AN3N9C00 | High Frequency Winding Type | 0402 | 750 | 3.9 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW15AN4N1C00 | High Frequency Winding Type | 0402 | 750 | 4.1 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW15AN4N3C00 | High Frequency Winding Type | 0402 | 750 | 4.3 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW15AN4N7C00 | High Frequency Winding Type | 0402 | 750 | 4.7 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW15AN5N1C00 | High Frequency Winding Type | 0402 | 600 | 5.1 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW15AN5N8C00 | High Frequency Winding Type | 0402 | 700 | 5.8 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW15AN6N2C00 | High Frequency Winding Type | 0402 | 700 | 6.2 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW15AN6N8H00 | High Frequency Winding Type | 0402 | 700 | 6.8 | +/-3[%] | 10[MHz]-6[GHz] |
| LQW15AN7N3H00 | High Frequency Winding Type | 0402 | 570 | 7.3 | +/-3[%] | 10[MHz]-6[GHz] |
| LQW15AN7N5H00 | High Frequency Winding Type | 0402 | 570 | 7.5 | +/-3[%] | 10[MHz]-6[GHz] |
| LQW15AN8N2H00 | High Frequency Winding Type | 0402 | 540 | 8.2 | +/-3[%] | 10[MHz]-6[GHz] |
| LQW15AN8N7H00 | High Frequency Winding Type | 0402 | 540 | 8.7 | +/-3[%] | 10[MHz]-6[GHz] |
| LQW15AN9N1H00 | High Frequency Winding Type | 0402 | 540 | 9.1 | +/-3[%] | 10[MHz]-6[GHz] |
| LQW15AN9N5H00 | High Frequency Winding Type | 0402 | 540 | 9.5 | +/-3[%] | 10[MHz]-6[GHz] |
| LQW15AN10NH00 | High Frequency Winding Type | 0402 | 500 | 10 | +/-3[%] | 10[MHz]-6[GHz] |
| LQW15AN11NH00 | High Frequency Winding Type | 0402 | 500 | 11 | +/-3[%] | 10[MHz]-6[GHz] |
| LQW15AN12NH00 | High Frequency Winding Type | 0402 | 500 | 12 | +/-3[%] | 10[MHz]-6[GHz] |
| LQW15AN13NH00 | High Frequency Winding Type | 0402 | 430 | 13 | +/-3[%] | 10[MHz]-6[GHz] |
| LQW15AN15NH00 | High Frequency Winding Type | 0402 | 460 | 15 | +/-3[%] | 10[MHz]-6[GHz] |
| LQW15AN16NH00 | High Frequency Winding Type | 0402 | 370 | 16 | +/-3[%] | 10[MHz]-6[GHz] |
| LQW15AN18NH00 | High Frequency Winding Type | 0402 | 370 | 18 | +/-3[%] | 10[MHz]-6[GHz] |
| LQW15AN19NH00 | High Frequency Winding Type | 0402 | 370 | 19 | +/-3[%] | 10[MHz]-6[GHz] |
| LQW15AN20NH00 | High Frequency Winding Type | 0402 | 370 | 20 | +/-3[%] | 10[MHz]-6[GHz] |
| LQW15AN22NH00 | High Frequency Winding Type | 0402 | 310 | 22 | +/-3[%] | 10[MHz]-6[GHz] |
| LQW15AN23NH00 | High Frequency Winding Type | 0402 | 310 | 23 | +/-3[%] | 10[MHz]-6[GHz] |
| LQW15AN24NH00 | High Frequency Winding Type | 0402 | 280 | 24 | +/-3[%] | 10[MHz]-6[GHz] |
| LQW15AN27NH00 | High Frequency Winding Type | 0402 | 280 | 27 | +/-3[%] | 10[MHz]-5.9[GHz] |
| LQW15AN30NH00 | High Frequency Winding Type | 0402 | 270 | 30 | +/-3[%] | 10[MHz]-5.8[GHz] |
| LQW15AN33NH00 | High Frequency Winding Type | 0402 | 260 | 33 | +/-3[%] | 10[MHz]-5.8[GHz] |
| LQW15AN36NH00 | High Frequency Winding Type | 0402 | 260 | 36 | +/-3[%] | 10[MHz]-5.5[GHz] |
| LQW15AN39NH00 | High Frequency Winding Type | 0402 | 250 | 39 | +/-3[%] | 10[MHz]-5.2[GHz] |
| LQW15AN40NH00 | High Frequency Winding Type | 0402 | 250 | 40 | +/-3[%] | 10[MHz]-6[GHz] |
| LQW15AN43NH00 | High Frequency Winding Type | 0402 | 250 | 43 | +/-3[%] | 10[MHz]-5.7[GHz] |
| LQW15AN47NH00 | High Frequency Winding Type | 0402 | 210 | 47 | +/-3[%] | 10[MHz]-4.7[GHz] |
| LQW15AN51NH00 | High Frequency Winding Type | 0402 | 210 | 51 | +/-3[%] | 10[MHz]-5.2[GHz] |
| LQW15AN56NH00 | High Frequency Winding Type | 0402 | 200 | 56 | +/-3[%] | 10[MHz]-4.2[GHz] |
| LQW15AN62NH00 | High Frequency Winding Type | 0402 | 145 | 62 | +/-3[%] | 10[MHz]-4.6[GHz] |
| LQW15AN68NJ00 | High Frequency Winding Type | 0402 | 140 | 68 | +/-5[%] | 10[MHz]-3.5[GHz] |
| LQW15AN72NJ00 | High Frequency Winding Type | 0402 | 135 | 72 | +/-5[%] | 10[MHz]-4.5[GHz] |
| LQW15AN75NJ00 | High Frequency Winding Type | 0402 | 135 | 75 | +/-5[%] | 10[MHz]-4.4[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Rated Current [V] | Inductance [nH] | Tolerance | Frequency Range |
|---------------|--------------------------------|----------------|-------------------|-----------------|------------|------------------|
| LQW15AN82NJ00 | High Frequency Winding Type | 0402 | 130 | 82 | +/-5[%] | 10[MHz]-3.2[GHz] |
| LQW15AN91NJ00 | High Frequency Winding Type | 0402 | 125 | 91 | +/-5[%] | 10[MHz]-3.9[GHz] |
| LQW15ANR10J00 | High Frequency Winding Type | 0402 | 120 | 100 | +/-5[%] | 10[MHz]-2.9[GHz] |
| LQW15ANR12J00 | High Frequency Winding Type | 0402 | 110 | 120 | +/-5[%] | 10[MHz]-1.9[GHz] |
| LQW15AN1N3C10 | High Frequency Winding Type | 0402 | 1200 | 1.3 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW15AN2N2C10 | High Frequency Winding Type | 0402 | 1000 | 2.2 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW15AN2N4D10 | High Frequency Winding Type | 0402 | 1000 | 2.4 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW15AN3N3D10 | High Frequency Winding Type | 0402 | 900 | 3.3 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW15AN3N6C10 | High Frequency Winding Type | 0402 | 900 | 3.6 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW15AN3N9D10 | High Frequency Winding Type | 0402 | 900 | 3.9 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW15AN4N7D10 | High Frequency Winding Type | 0402 | 800 | 4.7 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW15AN5N1C10 | High Frequency Winding Type | 0402 | 800 | 5.1 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW15AN5N6C10 | High Frequency Winding Type | 0402 | 800 | 5.6 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQG18HN1N2S00 | High Frequency Monolithic Type | 0603 | 300 | 1.2 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG18HN1N5S00 | High Frequency Monolithic Type | 0603 | 300 | 1.5 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG18HN1N8S00 | High Frequency Monolithic Type | 0603 | 300 | 1.8 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG18HN2N2S00 | High Frequency Monolithic Type | 0603 | 300 | 2.2 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG18HN2N7S00 | High Frequency Monolithic Type | 0603 | 300 | 2.7 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG18HN3N3S00 | High Frequency Monolithic Type | 0603 | 300 | 3.3 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG18HN3N9S00 | High Frequency Monolithic Type | 0603 | 300 | 3.9 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG18HN4N7S00 | High Frequency Monolithic Type | 0603 | 300 | 4.7 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG18HN5N6S00 | High Frequency Monolithic Type | 0603 | 300 | 5.6 | +/-0.3[nH] | 10[MHz]-6[GHz] |
| LQG18HN6N8J00 | High Frequency Monolithic Type | 0603 | 300 | 6.8 | +/-5[%] | 10[MHz]-6[GHz] |
| LQG18HN8N2J00 | High Frequency Monolithic Type | 0603 | 300 | 8.2 | +/-5[%] | 10[MHz]-5.5[GHz] |
| LQG18HN10NJ00 | High Frequency Monolithic Type | 0603 | 300 | 10 | +/-5[%] | 10[MHz]-4.5[GHz] |
| LQG18HN12NJ00 | High Frequency Monolithic Type | 0603 | 300 | 12 | +/-5[%] | 10[MHz]-4.1[GHz] |
| LQG18HN15NJ00 | High Frequency Monolithic Type | 0603 | 300 | 15 | +/-5[%] | 10[MHz]-3.7[GHz] |
| LQG18HN18NJ00 | High Frequency Monolithic Type | 0603 | 300 | 18 | +/-5[%] | 10[MHz]-3.4[GHz] |
| LQG18HN22NJ00 | High Frequency Monolithic Type | 0603 | 300 | 22 | +/-5[%] | 10[MHz]-3.1[GHz] |
| LQG18HN27NJ00 | High Frequency Monolithic Type | 0603 | 300 | 27 | +/-5[%] | 10[MHz]-2.7[GHz] |
| LQG18HN33NJ00 | High Frequency Monolithic Type | 0603 | 300 | 33 | +/-5[%] | 10[MHz]-2.4[GHz] |
| LQG18HN39NJ00 | High Frequency Monolithic Type | 0603 | 300 | 39 | +/-5[%] | 10[MHz]-2.3[GHz] |
| LQG18HN47NJ00 | High Frequency Monolithic Type | 0603 | 300 | 47 | +/-5[%] | 10[MHz]-2.2[GHz] |
| LQG18HN56NJ00 | High Frequency Monolithic Type | 0603 | 300 | 56 | +/-5[%] | 10[MHz]-2.1[GHz] |
| LQG18HN68NJ00 | High Frequency Monolithic Type | 0603 | 300 | 68 | +/-5[%] | 10[MHz]-1.7[GHz] |
| LQG18HN82NJ00 | High Frequency Monolithic Type | 0603 | 300 | 82 | +/-5[%] | 10[MHz]-1.5[GHz] |
| LQG18HNR10J00 | High Frequency Monolithic Type | 0603 | 300 | 100 | +/-5[%] | 10[MHz]-1.4[GHz] |
| LQW18AN2N2D00 | High Frequency Winding Type | 0603 | 700 | 2.2 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW18AN3N6C00 | High Frequency Winding Type | 0603 | 850 | 3.6 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW18AN3N9C00 | High Frequency Winding Type | 0603 | 850 | 3.9 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW18AN4N3C00 | High Frequency Winding Type | 0603 | 850 | 4.3 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW18AN4N7D00 | High Frequency Winding Type | 0603 | 850 | 4.7 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW18AN5N6C00 | High Frequency Winding Type | 0603 | 750 | 5.6 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW18AN6N2C00 | High Frequency Winding Type | 0603 | 750 | 6.2 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW18AN6N8C00 | High Frequency Winding Type | 0603 | 750 | 6.8 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW18AN7N5D00 | High Frequency Winding Type | 0603 | 750 | 7.5 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW18AN8N2D00 | High Frequency Winding Type | 0603 | 650 | 8.2 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW18AN8N7D00 | High Frequency Winding Type | 0603 | 650 | 8.7 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW18AN9N1D00 | High Frequency Winding Type | 0603 | 650 | 9.1 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW18AN9N5D00 | High Frequency Winding Type | 0603 | 650 | 9.5 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW18AN10NG00 | High Frequency Winding Type | 0603 | 650 | 10 | +/-2[%] | 10[MHz]-6[GHz] |
| LQW18AN11NG00 | High Frequency Winding Type | 0603 | 650 | 11 | +/-2[%] | 10[MHz]-6[GHz] |
| LQW18AN12NG00 | High Frequency Winding Type | 0603 | 600 | 12 | +/-2[%] | 10[MHz]-6[GHz] |
| LQW18AN13NG00 | High Frequency Winding Type | 0603 | 600 | 13 | +/-2[%] | 10[MHz]-6[GHz] |
| LQW18AN15NG00 | High Frequency Winding Type | 0603 | 600 | 15 | +/-2[%] | 10[MHz]-6[GHz] |
| LQW18AN16NG00 | High Frequency Winding Type | 0603 | 550 | 16 | +/-2[%] | 10[MHz]-6[GHz] |
| LQW18AN18NG00 | High Frequency Winding Type | 0603 | 550 | 18 | +/-2[%] | 10[MHz]-6[GHz] |
| LQW18AN20NG00 | High Frequency Winding Type | 0603 | 550 | 20 | +/-2[%] | 10[MHz]-6[GHz] |
| LQW18AN22NG00 | High Frequency Winding Type | 0603 | 500 | 22 | +/-2[%] | 10[MHz]-6[GHz] |
| LQW18AN24NG00 | High Frequency Winding Type | 0603 | 500 | 24 | +/-2[%] | 10[MHz]-6[GHz] |
| LQW18AN27NG00 | High Frequency Winding Type | 0603 | 440 | 27 | +/-2[%] | 10[MHz]-5.6[GHz] |
| LQW18AN30NG00 | High Frequency Winding Type | 0603 | 420 | 30 | +/-2[%] | 10[MHz]-5.2[GHz] |
| LQW18AN33NG00 | High Frequency Winding Type | 0603 | 420 | 33 | +/-2[%] | 10[MHz]-5[GHz] |
| LQW18AN36NG00 | High Frequency Winding Type | 0603 | 400 | 36 | +/-2[%] | 10[MHz]-4.9[GHz] |
| LQW18AN39NG00 | High Frequency Winding Type | 0603 | 400 | 39 | +/-2[%] | 10[MHz]-4.9[GHz] |
| LQW18AN43NG00 | High Frequency Winding Type | 0603 | 380 | 43 | +/-2[%] | 10[MHz]-4.7[GHz] |
| LQW18AN47NG00 | High Frequency Winding Type | 0603 | 380 | 47 | +/-2[%] | 10[MHz]-4.5[GHz] |
| LQW18AN51NG00 | High Frequency Winding Type | 0603 | 370 | 51 | +/-2[%] | 10[MHz]-4.4[GHz] |
| LQW18AN56NG00 | High Frequency Winding Type | 0603 | 360 | 56 | +/-2[%] | 10[MHz]-4.2[GHz] |

| Part Number | Type or Use | SizeCode (EIA) | Rated Current [V] | Inductance [nH] | Tolerance | Frequency Range |
|---------------|-----------------------------|----------------|-------------------|-----------------|------------|------------------|
| LQW18AN62NG00 | High Frequency Winding Type | 0603 | 280 | 62 | +/-2[%] | 10[MHz]-4[GHz] |
| LQW18AN68NG00 | High Frequency Winding Type | 0603 | 340 | 68 | +/-2[%] | 10[MHz]-3.8[GHz] |
| LQW18AN72NG00 | High Frequency Winding Type | 0603 | 270 | 72 | +/-2[%] | 10[MHz]-3.7[GHz] |
| LQW18AN75NG00 | High Frequency Winding Type | 0603 | 270 | 75 | +/-2[%] | 10[MHz]-3.7[GHz] |
| LQW18AN82NG00 | High Frequency Winding Type | 0603 | 250 | 82 | +/-2[%] | 10[MHz]-3.4[GHz] |
| LQW18AN91NG00 | High Frequency Winding Type | 0603 | 230 | 91 | +/-2[%] | 10[MHz]-3.3[GHz] |
| LQW18ANR10G00 | High Frequency Winding Type | 0603 | 220 | 100 | +/-2[%] | 10[MHz]-3.3[GHz] |
| LQW18ANR11G00 | High Frequency Winding Type | 0603 | 200 | 110 | +/-2[%] | 10[MHz]-3.2[GHz] |
| LQW18ANR12G00 | High Frequency Winding Type | 0603 | 180 | 120 | +/-2[%] | 10[MHz]-3.1[GHz] |
| LQW18ANR13G00 | High Frequency Winding Type | 0603 | 170 | 130 | +/-2[%] | 10[MHz]-2.8[GHz] |
| LQW18ANR15G00 | High Frequency Winding Type | 0603 | 160 | 150 | +/-2[%] | 10[MHz]-2.6[GHz] |
| LQW18ANR16G00 | High Frequency Winding Type | 0603 | 150 | 160 | +/-2[%] | 10[MHz]-2.5[GHz] |
| LQW18ANR18G00 | High Frequency Winding Type | 0603 | 140 | 180 | +/-2[%] | 10[MHz]-2.4[GHz] |
| LQW18ANR20G00 | High Frequency Winding Type | 0603 | 120 | 200 | +/-2[%] | 10[MHz]-2.3[GHz] |
| LQW18ANR22G00 | High Frequency Winding Type | 0603 | 120 | 220 | +/-2[%] | 10[MHz]-2.2[GHz] |
| LQW18ANR27G00 | High Frequency Winding Type | 0603 | 110 | 270 | +/-2[%] | 10[MHz]-1.7[GHz] |
| LQW18ANR33G00 | High Frequency Winding Type | 0603 | 85 | 330 | +/-2[%] | 10[MHz]-1.5[GHz] |
| LQW18ANR39G00 | High Frequency Winding Type | 0603 | 80 | 390 | +/-2[%] | 10[MHz]-1.4[GHz] |
| LQW18ANR47G00 | High Frequency Winding Type | 0603 | 75 | 470 | +/-2[%] | 10[MHz]-1.3[GHz] |
| LQW18AN2N2D10 | High Frequency Winding Type | 0603 | 1400 | 2.2 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW18AN3N9C10 | High Frequency Winding Type | 0603 | 1000 | 3.9 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW18AN5N6D10 | High Frequency Winding Type | 0603 | 900 | 5.6 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW18AN6N8C10 | High Frequency Winding Type | 0603 | 900 | 6.8 | +/-0.2[nH] | 10[MHz]-6[GHz] |
| LQW18AN8N2D10 | High Frequency Winding Type | 0603 | 800 | 8.2 | +/-0.5[nH] | 10[MHz]-6[GHz] |
| LQW18AN10NG10 | High Frequency Winding Type | 0603 | 800 | 10 | +/-2[%] | 10[MHz]-6[GHz] |
| LQW18AN12NG10 | High Frequency Winding Type | 0603 | 750 | 12 | +/-2[%] | 10[MHz]-6[GHz] |
| LQW18AN15NJ10 | High Frequency Winding Type | 0603 | 700 | 15 | +/-5[%] | 10[MHz]-6[GHz] |
| LQW18AN18NG10 | High Frequency Winding Type | 0603 | 700 | 18 | +/-2[%] | 10[MHz]-6[GHz] |
| LQW18AN22NG10 | High Frequency Winding Type | 0603 | 640 | 22 | +/-2[%] | 10[MHz]-5.7[GHz] |
| LQW18AN27NG10 | High Frequency Winding Type | 0603 | 590 | 27 | +/-2[%] | 10[MHz]-4.9[GHz] |
| LQW18AN33NJ10 | High Frequency Winding Type | 0603 | 550 | 33 | +/-5[%] | 10[MHz]-4.5[GHz] |