

#### **FEATURES**

- Quick response to load change
- <u>Ultra small surface mount package</u> 11.9×15.0×2.4mm
- High efficiency of 91%
- Outstanding thermal derating performance
- Over current protection
- On/Off control (Positive logic)
- I2C communication function
- Power Good signal
- RoHS-6 hazardous substance compliance
- High Reliability / Heat Shock Testing


### PRODUCT OVERVIEW

The MYMGC3R32EFPF2RV is miniature MonoBK™ called "Mono Block", non-isolated Point-of-Load (POL) DC-DC power converters for embedded applications. The tiny form factor measures only 11.9x 15.0 x 2.4 mm. Applications include powering FPGA/CPU's, datacom/telecom systems, Distributed Bus Architectures (DBA), programmable logic and mixed voltage systems.

The converters have input voltage ranges of 4.3 to 5.5Vdc and a multiple output voltage. Based on a fixed frequency synchronous buck converter switching topology, this high power conversio efficient PoL module features On/Off control and Power Good signal output.

These converters also include under voltage lock out (UVLO), output short circuit protection and over-current protection.

## SIMPLIFIED APPLICATION



(Typical topology is shown. Murata recommends an external fuse.)






PERFORMANCE SPECIFICATIONS SUMMARY AND ORDERING GUIDE (Including series products)													
			OUT	ΓPUT				IN	PUT		Efficiency		PACKAGE
PART NUMBER	Vout	lout	Power	R/N(typ.)	Regulati	on(max.)	Vin(typ.)	Range	lin no load	lin full load	[%]	ON/OFF	[mm]
	[Vdc]	[A(max.)]	[W]	[% of Vout]	Line[%]	Load[%]	[Vdc]	[Vdc]	[mA]	[A]	[,0]		[111111]
	1.2	2.5	3.00	1	±1.0	±1.0							
MYMGC3R32EFPF2RV	1.8	1.0	1.80	1	±1.0	±1.0	5	4.3-5.5	127	3.3	91	Yes	12.0 x 15.0 x 2.4
WIIWGCSKSZLIFIZKV	3.3	2.0	6.60	1	±1.0	±1.0	3	4.5-5.5	121	5.5	91	(Positive)	12.0 X 13.0 X 2.4
	2.5	1.5	3.75	1	±1.0	±1.0							
	1.2	2.5	3.00	1	±1.0	±1.0							
MYMGC3R32EFPF2RVD	1.8	1.0	1.80	1	±1.0	±1.0	5	4.3-5.5	127	3.3	91	Yes	12.0 x 15.0 x 2.4
WITWOOJNJZLI FI ZNVD	3.3	2.0	6.60	1	±1.0	±1.0		4.0-0.0	121	5.5	91	(Positive)	12.0 X 13.0 X 2.4
	2.5	1.5	3.75	1	±1.0	±1.0							

<sup>1.</sup> Please refer to the Part Number Structure for additional ordering information and options.

<sup>3.</sup>Use adequate ground plane and copper thickness adjacent to the converter.



## **Product Marking**

Because of the small size of these products, the product marking contains a character-reduced code to indicate the model number and manufacturing date code. Not all items on the marking are always used. Please note that the marking differs from the product photograph. Here is the layout of the Marking.

Part Number	Product Code
MYMGC3R32EFPF2RV	MGC3R32EFPV
MYMGC3R32EFPF2RVD	MGC3R32EFPV



<sup>2.</sup>All specifications are at nominal line voltage, Vout=nominal and full load, +25degC unless otherwise noted. Output capacitors are 22uF x 2, for Vou2 are 22uF x 1, ceramic. Input cap is 22 uF x 2 ceramic and plenty electrolytic capacitors. See detailed specifications. I/O caps are necessary for our test equipment.



Startup Time (Remote ON)

PGood FALSE (LO)

# MYMGC3R32EFPF2RV Series MonoBK™, Multi output DC-DC Converter Series

ABSOLUTE MAXIMUM RATINGS	Conditions	Minimum	Typical	Maximum	Units
Input Voltage		-0.3		6	Vdc
ON/OFF Pin	Power on, referred to -Vin	-0.3		Vin+0.3V	Vdc
PGOOD/Trim Pins	Power on, referred to -Vin		Source ONLY		
Output Current Vout1 See Note2	Current-limited, no damage, short-circuit protected			2.5	Α
Output Current Vout2 See Note2				1	Α
Output Current Vout3 See Note2				2	Α
Output Current Vout4 See Note2				1.5	Α
Storage Temperature Range	Vin = Zero (no power)	-40		85	degC
Soldering / Reflow Temperature	Note 14			245	degC
Maximum Number of Reflows Allowed	Note 14			4	
Absolute maximums are stress ratings. Exposure of	devices to greater than any of these conditions may adversel	y affect long-term	reliability. Prope	r operation unde	r conditior
Absolute maximums are stress ratings. Exposure of	******	y affect long-term Minimum	reliability. Prope  Typical	1 r operation unde	
Absolute maximums are stress ratings. Exposure of other than those listed in the Performance/Function	devices to greater than any of these conditions may adversel al Specifications Table is not implied or recommended.				
Absolute maximums are stress ratings. Exposure of other than those listed in the Performance/Function INPUT	devices to greater than any of these conditions may adversel al Specifications Table is not implied or recommended.  Conditions	Minimum	Typical	Maximum	Units
Absolute maximums are stress ratings. Exposure of other than those listed in the Performance/Function INPUT Operating Voltage Range	devices to greater than any of these conditions may adversel al Specifications Table is not implied or recommended.  Conditions  Note9	Minimum	<b>Typical</b>	Maximum	<b>Units</b> Vdc
Absolute maximums are stress ratings. Exposure of other than those listed in the Performance/Function INPUT  Operating Voltage Range  Start-up threshold	devices to greater than any of these conditions may adversel al Specifications Table is not implied or recommended.  Conditions  Note9  Rising input voltage	Minimum	<b>Typical</b> 5 2.63	Maximum	Units Vdc Vdc
Absolute maximums are stress ratings. Exposure of other than those listed in the Performance/Function INPUT  Operating Voltage Range Start-up threshold Undervoltage shutdown	devices to greater than any of these conditions may adversel al Specifications Table is not implied or recommended.  Conditions  Note9  Rising input voltage	Minimum	7ypical 5 2.63 2.6	Maximum	Units Vdc Vdc
Absolute maximums are stress ratings. Exposure of other than those listed in the Performance/Function INPUT  Operating Voltage Range Start-up threshold Undervoltage shutdown Internal Filter Type	devices to greater than any of these conditions may adversel al Specifications Table is not implied or recommended.  Conditions  Note9  Rising input voltage	Minimum	7ypical 5 2.63 2.6	Maximum	Units Vdc Vdc
Absolute maximums are stress ratings. Exposure of other than those listed in the Performance/Function INPUT  Operating Voltage Range Start-up threshold Undervoltage shutdown Internal Filter Type Input current	devices to greater than any of these conditions may adversel al Specifications Table is not implied or recommended.  Conditions  Note9  Rising input voltage  Note 12	Minimum	Typical 5 2.63 2.6 Capacitive	Maximum	Vdc Vdc Vdc
Absolute maximums are stress ratings. Exposure of other than those listed in the Performance/Function INPUT  Operating Voltage Range Start-up threshold Undervoltage shutdown Internal Filter Type Input current Full Load Conditions	devices to greater than any of these conditions may adversel al Specifications Table is not implied or recommended.  Conditions  Note9  Rising input voltage  Note 12  Vin = nominal	Minimum	Typical 5 2.63 2.6 Capacitive	Maximum	Vdc Vdc Vdc
Absolute maximums are stress ratings. Exposure of other than those listed in the Performance/Function INPUT  Operating Voltage Range Start-up threshold Undervoltage shutdown Internal Filter Type Input current Full Load Conditions Low Line	devices to greater than any of these conditions may adversel al Specifications Table is not implied or recommended.  Conditions  Note9  Rising input voltage  Note 12  Vin = nominal  Vin = minimum	Minimum	7ypical 5 2.63 2.6 Capacitive 3.34 3.85	Maximum	Vdc Vdc Vdc A A
Absolute maximums are stress ratings. Exposure of other than those listed in the Performance/Function INPUT  Operating Voltage Range Start-up threshold Undervoltage shutdown Internal Filter Type Input current Full Load Conditions Low Line No Load Current	devices to greater than any of these conditions may adversel al Specifications Table is not implied or recommended.  Conditions  Note9  Rising input voltage  Note 12  Vin = nominal  Vin = minimum	Minimum	Typical 5 2.63 2.6 Capacitive 3.34 3.85 127	Maximum	Vdc Vdc Vdc A A MA

Full Load Conditions	Vin = nominal	3.34		А	
Low Line	Vin = minimum	3.85			Α
No Load Current	lout = minimum, unit = ON	127			mA
Shut-Down Mode Input Current			63		uA
GENERAL and SAFETY	Conditions	Minimum	Typical	Maximum	Units
Efficiency	Vin =5V, Io=MAX		91		%
Safety	Certified to UL-60950-1, CSA-C22.2 No. 60950-1, IEC/EN60950-1, 2nd edition(pending)	Pending			
Calculated MTBF (Note 3)	Ta=40degC,Vin=nom,Vo=nom,Io=50%	1,872,597		Hours	
DYNAMIC CHARACTERISTICS		Minimum	Typical	Maximum	Units
Fixed Switching Frequency			2		MHz
Startup Time (Vin ON)	Vout=nominal (Vin On to 90% of Vo)		see the graph		mS

Dynamic Load Response	(50-100% load step, di/dt)		2.5		A/uSec
Dynamic Load Peak Deviation	same as above		+/-3%		Voset
FUNCTIONS	Conditions	Minimum	Typical	Maximum	Units
Remote On/Off Control (Note 4)					
Logic					
ON state		1.3		Vin+0.3	V
OFF state		-0.3		0.4	V
Control Current	Open collector/drain				mA
Power-Good Output					
PGood TRUE (HI)		(Voset * 90°	%) < Vout < (Vo	set * 110%)	V

Vout=nominal (Remote On to 90% of Vo)

mS

see the graph

Out of above range



# FUNCTIONAL SPECIFICATIONS OF MYMGC3R32EFPF2RV (Note 1)

OUTPUT	Conditions	Minimum	Typical	Maximum	Units
Total Output Power	See Derating	0		15.15	W
Voltage	·	1			
Output Voltage Vout1	Note 9		1.2		Vdc
Output Voltage Vout2			1.8		Vdc
Output Voltage Vout3			3.3		Vdc
Output Voltage Vout4			2.5		Vdc
Minimum Loading			None		
Accuracy	Vin = 4.3~5.5V,lout = 0~Max,Ta=25degC	-2		2	% of Vout
Overvoltage Protection			-		Vdc
Undervoltage Protection			-		Vdc
Current		•			
Output Current Range Vout1	Note 2	0		2.5	Α
Current Limit Inception Vout1			3.6		Α
Output Current Range Vout2	Note 2	0		1	Α
Current Limit Inception Vout2			2.5		Α
Output Current Range Vout3	Note 2	0		2	Α
Current Limit Inception Vout3			3.1		Α
Output Current Range Vout4	Note 2	0		1.5	Α
Current Limit Inception Vout4		-	3.1		A
Short Circuit			0.1		,,
Short Circuit Duration (remove short for recovery)	Output shorted to ground, no damage		Latch-off		
` , , , , , , , , , , , , , , , , , , ,	Note 5		shut down		
Short circuit protection method	Note 5	0			
Prebias Start-up			is less than Vout	nal output voltage	
Regulation (Note8)					
Line Regulation	Vin = min. to max.,Vout = nom., lout = nom.	-1		1	% of Vout
Ripple and Noise (20MHz bandwidth)	Note 6		10	20	mV pk-pk
External Output Capacitance (Note 11) Vout1,Vout3,Vout4		40		90	uF
External Output Capacitance (Note 11) Vout2		20		90	uF
MECHANICAL(Common)	Conditions	Minimum	Typical	Maximum	Units
Mechanical Dimension	W*D*H		/p)x15.0(typ)x2.		mm
Weight		(	1.20	1	Grams
ENVIRONMENTAL(Common)	Conditions	Minimum	Typical	Maximum	Units
Operating Ambient Temperature Range	With Derating (Note 2,7)	-40		85	degC
Storage Temperature	Vin = Zero (no power)	-40		85	degC
Thermal Protection/Shutdown	Measured in center(Note10)		150		degC
Moisture Sensitivity Level			3		
RoHS rating			RoHS-6		



#### **Specification Notes**

(1)Specifications are typical at +25degC, Vin=nominal +5.0V, Vout=nominal (+1.2V, +1.8V,+3.3V,+2.5V), full load, external caps and natural convection unless otherwise indicated. Extended tests at full power must supply substantial natural airflow. All models are tested and specified with external 22uF\*1 or 2 ceramic output capacitors and a 22 uF\*2 ceramic and plenty electrolytic external input capacitors. All capacitors are low ESR types. These capacitors are necessary to accommodate our test equipment and may not be required to achieve specified performance in your applications. However, Murata recommends installation of these capacitors. All models are stable and regulate within spec under no-load conditions.

(2)Note that Maximum Power Derating curves indicate an average current at nominal input voltage. At higher temperatures and/or lower airflow, the DC/DC converter will tolerate brief full current outputs if the total RMS current over time does not exceed the Derating curve.

(3)Mean Time Between Failure is calculated using the MIL-HDBK-217, Tpcboard = +40degC, half output load, natural air convection.

(4)The On/Off Control Input should use either a switch or an open collector/open drain transistor referenced to Input Common. A logic gate may also be used by applying appropriate external voltages which do not exceed +Vin

(5)The Latch-off overcurrent operation stops the output of the converter when it detects an overcurrent condition.

After the failure has been removed, the converter will restore normal operation by restart.

(6)Output noise may be further reduced by adding an external filter. At zero output current, the output may contain low frequency components which exceed the ripple specification. The output may be operated indefinitely with no load.

(7)All models are fully operational and meet published specifications, including "cold start" at -40deqC.

(8)Regulation specifications describe the deviation as the line input voltage or output load current is varied from a nominal midpoint value to either extreme.

(9)Other input or output voltage ranges will be reviewed under scheduled quantity special order.


(10)Maximum PC board temperature is measured with the sensor in the center of the


(11)The maximum output capacitive loads depend on the Equivalent Series Resistance (ESR) of the external output capacitor and, to a lesser extent, the distance and series impedance to the load. Larger caps will reduce output noise but may change the transient response. Newer ceramic caps with very low ESR may require lower capacitor values to avoid instability. Thoroughly test your capacitors in the application. Please refer to the Output Capacitive Load Application Note.

(12)Do not allow the input voltage to degrade lower than the input under voltage shutdown voltage at all times. Otherwise, you risk having the converter turn off. The under voltage shutdown is not latching and will attempt to recover when the input is brought back into normal operating range.

(13)The outputs are not intended to sink appreciable reverse current.

(14) Recommended Reflow profile is written in "Soldering Guidelines".





## **Internal Circuit Diagrams**


## **ON/OFF** using guide

By using ON/OFF function, the operation of this product can be disabled without disconnection of input Voltage. Sequence of a power supply system and power-saving control can be easily achieved using this function.

### ON/OFF control uage

ON/OFF pin(9pin) are pull-up


: Output Voltage = ON



It is strongly recommended that on/off terminal should be used when you turn on/off this product. Characteristics may be affected by turning input voltage on/off.

Please check product operation on your application with turning input voltage on/off.

#### ON/OFF sequence






## PowerGood(P.G) using guide

PW Good terminal is pulled up to Vin terminal. The value of resistance of pull up is  $10k\Omega$ . When this product is in following situation, the No.48 pin is on open-drain.

- Input voltage is 3.3V to 5.0V and ON/OFF pin is Low.
- Output voltage is within voltage detection threshold (over 90% to under 110%)

When this product is in following situation, the No.48 pin is connected to GND.


- ON/OFF pin is High and Output Voltage is out of voltage detection threshold(Under 90% to over 110%)
- Between 11ms after output voltage4 is voltage detection threshold
- An under voltage condition exists for the DC-DC converter: PG is connected to GND.
- An overcurrent condition has been detected





Max impressed voltage at Power Good terminal.

MAX:-0.3V to (Vin+0.3V) with 6.0V
















## THERMAL DERATINGS OF MYMGC3R32EFPF2RV



Thermal deratings are evaluated in following condition.

• The above de-rating limits apply to this product soldered directly to 101.6\*50.0\*1.6mm PCB (4reyer, with 35um copper) in the natural air-cooling condition. Any adjacent parts of high temperature may cause overheating. For reliable operation, please ensure that the Top side temperature of this product (Tc) is maintained below 100degC.



#### TRANSIENT RESPONSE DATA OF MYMGC3R32EFPF2RV

Transient response data at various conditions are showed in following table.

Minimum output capacitance can serve less than 3% \* Vo(nom) of deviation for 50% load change.


Vout(V) Vin(V)		Cout1(uF)*	Cout2(uF)	Voltage Deviation(mV)		
voui(v)	viii(v)	Coult(ur) Coulz(ur)		50-100% Load Step		
1.2	4.3	22*2	-	32		
1.2	5.5	22 2	1	28		
1.8	4.3	22*1	-	18		
1.0	5.5	22 1	-	18		
3.3	4.3	22*2	-	30		
3.3	5.5	22 2	-	30		
2.5	4.3	22*2	-	24		
2.3	5.5	22 2	-	22		

<sup>\*</sup>Cout1 is minimum output capacitance for the products.



## **MECHANICAL SPECIFICATIONS**

#### **Dimension and Pin Assignment**




INPUT/OUTPUT CONNECTIONS					
Pin No.	Signal	Function			
1~6	Vout2	Output Voltage 2			
7~12,20,26,34~39	GND	GND			
13~18	Vout1	Output Voltage 1			
19	Sense2	Output Voltage 2 Sense			
21~25	Vin	Input			
27	Sense4	Output Voltage 4 Sense			
28~33	Vout4	Output Voltage 4			
40~45	Vout3	Output Voltage 3			
46	Sense3	Output Voltage 3 Sense			
47	nINT	State notification signal			
48	PW GOOD	Power Good			
49	SCL(I2C interface)	I2C interface			
50	SDA(I2C interface)	I2C interface			
51	ON/OFF	Remote ON/OFF			
52	Sense1	Output Voltage 1 Sense			
53~61	GND	Thermal PAD			

Tolerance:  $\pm 0.15$ 


Coplanarity: less than 0.12

[Unit:mm]







## **Recommended Board Land Pattern (Top View)**



Unit:mm


### **Example of Pattern Layout(Top View)**







# TAPE AND REEL INFORMATION

# **Tape Dimension**









Unit:mm


## **Reel Dimension**



Unit:mm

# TAPE SPECIFICATION





#### Note

- 1. The adhesive strength of the protective tape must be within 0.3-1.0N.
- 2.Each reel contains the quantities such as the table below.
- 3.Each reel set in moisture-proof packaging because of MSL 3.
- 4. No vacant pocket in "Module on tape" section.
- 5. The reel is labeled with Murata part number and quantity.
- 6. The color of reel is not specified.

Part Number	Qty
MYMGC3R32EFPF2RV	400
MYMGC3R32EFPF2RVD	100



## **TECHNICAL NOTES**

#### **Input Fuse**

Certain applications and/or safety agencies may require fuses at the inputs of power conversion components. Fuses should also be used when there is the possibility of sustained input voltage reversal which is not current limited. For greatest safety, we recommend a fast blow fuse installed in the ungrounded input supply line. The installer must observe all relevant safety standards and regulations. For safety agency approvals, install the converter in compliance with the enduser safety standard.

### Input Under-Voltage Shutdown and Start-Up Threshold

Under normal start-up conditions, converters will not begin to regulate properly until the ramping-up input voltage exceeds and remains at the Start-Up Threshold Voltage (see Specifications). Once operating, converters will not turn off until the input voltage drops below the Under-Voltage Shutdown Limit. Subsequent restart will not occur until the input voltage rises again above the Start-Up Threshold. This built-in hysteresis prevents any unstable on/off operation at a single input voltage.

Users should be aware however of input sources near the Under-Voltage Shutdown whose voltage decays as input current is consumed (such as capacitor inputs), the converter shuts off and then restarts as the external capacitor recharges. Such situations could oscillate. To prevent this, make sure the operating input voltage is well above the UV Shutdown voltage at all times.

#### Start-Up Time

Assuming that the output current is set at the rated maximum, the Vin to Vout Start-Up Time (see Specifications) is the time interval between the point when the ramping input voltage crosses the Start-Up Threshold and the fully loaded regulated output voltage enters and remains within its specified accuracy band. Actual measured times will vary with input source impedance, external input capacitance, input voltage slew rate and final value of the input voltage as it appears at the converter.

These converters include a soft start circuit to moderate the duty cycle of its PWM controller at power up, thereby limiting the input inrush current.

The On/Off Remote Control interval from On command to Vout regulated assumes that the converter already has its input voltage stabilized above the Start-Up Threshold before the On command. The interval is measured from the On command until the output enters and remains within its specified accuracy band. The specification assumes that the output is fully loaded at maximum rated current. Similar conditions apply to the On to Vout regulated specification such as external load capacitance and soft start circuitry.

#### **Recommended Input Filtering**


The user must assure that the input source has low AC impedance to provide dynamic stability and that the input supply has little or no inductive content, including long distributed wiring to a remote power supply. For best performance, we recommend installing a low-ESR capacitor immediately adjacent to the converter's input terminals. The capacitor should be a ceramic type such as the Murata GRM32 series. Initial suggested capacitor values are 22 uF x 2 ceramic type, rated at twice the expected maximum input voltage. Make sure that the input terminals do not go below the under voltage shutdown voltage at all times. More input bulk capacitance may be added in parallel (either electrolytic or tantalum) if needed.

#### **Recommended Output Filtering**

The converter will achieve its rated output ripple and noise with additional external capacitor. The user may install more external output capacitance reduce the ripple even further or for improved dynamic response. Again, use low-ESR ceramic (Murata GRM32 series). Initial values of 22 uF x 1 or 2 ceramic type may be tried, either single or multiple capacitors in parallel. Mount these close to the converter. Measure the output ripple under your load conditions. Use only as much capacitance as required to achieve your ripple and noise objectives. Excessive capacitance can make step load recovery sluggish or possibly introduce instability. Do not exceed the maximum rated output capacitance listed in the specifications.

#### **Output Noise**

All models in this converter series are tested and specified for output noise using designated external output components, circuits and layout as shown in the figures below. In the figure below, the two copper strips simulate real-world printed circuit impedances between the power supply and its load. In order to minimize circuit errors and standardize tests between units, scope measurements should be made using BNC connectors or the probe ground should not exceed one half inch and soldered directly to the test circuit.



C1=22uF x 1 or 2 CERAMIC

C2=OPEN

Figure : Measuring Output Ripple and Noise

## **Minimum Output Loading Requirements**

All models regulate within specification and are stable under no load to full load conditions. Operation under no load might however slightly increase output ripple and noise.

## Thermal Shutdown

To prevent many over temperature problems and damage, these converters include thermal shutdown circuitry. If environmental conditions cause the temperature of the converter's to rise above the Operating Temperature Range up to the shutdown temperature, an on-board electronic temperature sensor will power down the unit. When the temperature decreases below the turn-on threshold, the converter will automatically restart.



<u>CAUTION</u>: If you operate too close to the thermal limits, the converter may shut down suddenly without warning. Confirm thoroughly your application to avoid unplanned thermal shutdown. Temperature Derating Curves

The graphs in this data sheet illustrate typical operation under a variety of conditions. The derating curves show the maximum continuous ambient air temperature. Note that these are AVERAGE measurements.

Note that the temperatures are of the ambient airflow, not the converter itself which is obviously running at higher temperature than the outside air. Also note that very low flow rates (below about 25 LFM) are similar to "natural convection," that is, not using fan-forced airflow. Murata makes Characterization measurements in a closed cycle wind tunnel with calibrated airflow. We use both thermocouples and an infrared camera system to observe thermal performance. **CAUTION**: These graphs are all collected at slightly above Sea Level altitude. Be sure to reduce the derating for higher density altitude.

#### **Output Current Limiting**

Current limiting inception is defined as the point at which full power falls below the rated tolerance. See the Performance/Functional Specifications. Note particularly that the output current may briefly rise above its rated value in normal operation as long as the average output power is not exceeded. This enhances reliability and continued operation of your application. If the output current is too high, the converter will enter the short circuit condition.

#### **Output Short Circuit Condition**

When a converter detect over current, the output voltage will shutdown. And the converter maintains this state.

When the converter restarts, the output botage starts normally.

#### **Remote On/Off Control**

Please refer to the Connection Diagram on page 1 for On/Off connections.

Positive logic models are enabled when the On/Off pin is left open or is pulled high to Vin with respect to GND. An internal bias current causes the OVP open pin to rise to Vin. Positive-polarity devices are disabled when the On/Off is grounded or brought to within a low voltage (see Specifications) with respect to GND.

Dynamic control of the On/Off function should be able to sink appropriate signal current when brought low and withstand appropriate voltage when brought high. Be aware too that there is a finite time in milliseconds (see Specifications) between the time of On/Off Control activation and stable, regulated output. This time will vary slightly with output load type and current and input conditions.

Output Capacitive Load


Users should only consider adding capacitance to reduce switching noise and/or to handle spike current load steps. Install only enough capacitance to achieve noise objectives. Excess external capacitance may cause regulation problems, degraded transient response and possible oscillation or instability.

#### **Soldering Guidelines**


Murata recommends the specifications below when installing these converters. These specifications vary depending on the solder type. Exceeding these specifications may cause damage to the product. Your production environment may differ therefore please thoroughly review these guidelines with your process engineers.

Reflow Solder Operations for sur	face-mount products		
For Sn/Ag/Cu based solders:			
Preheat Temperature	Less than 1degC per second		
Time over Liquidus	45 to 75 seconds		
Maximum Peak Temperature	245degC		
Cooling Rate Less than 3degC per second			
For Sn/Pb based solders:			
Preheat Temperature	Less than 1degC per second		
Time over Liquidus	60 to 75 seconds		
Maximum Peak Temperature	235degC		
Cooling Rate	Less than 3degC per second		

#### Recommended Lead-free Solder Reflow Profile



CAUTION: Do not reflow the converter as follows, because the converter may fall from the substrate during reflowing.



# Pb-free solder processes

For Pb-free solder processes, the product is qualified for MSL 3 according to IPC/JEDEC standard J-STD-020C.

During reflow the converter must not exceed 245 degC at any time.

#### **Dry Pack Information**


Products intended for Pb-free reflow soldering processes are delivered in standard moisture barrier bags according to IPC/JEDEC standard J-STD-033.

(Handling, packing, shipping and use of moisture/reflow sensitivity surface mount devices.)

Using products in high temperature Pb-free soldering processes requires dry pack storage and handling. In case the products have been stored in an uncontrolled environment and no longer can be considered dry, the modules must be baked according to J-STD-033.

#### **APPENDIX**

#### **Test Circuit**



Vin: DC Power Supply RL: Electronic Load Device

\*It is strongly recommended that on/off terminal should be used when you turn on/off this product. Characteristics may be affected by turning input voltage on/off. Please check product operation on your application with turning input voltage on/off.

It is recommended that the reset IC would be used acceptably to the input voltage specification, because this product have wide input voltage range.

If there is a long inductive cable length between the input power source and converter, then some additional bulk decoupling capacitance (eg. up to 1000uF) may be necessary to ensure a low AC impedance power source.



#### **Notices**

#### Scope

This datasheet is applied to MYMGC3R32EFPF2RV and MYMGC3R32EFPF2RVD.

- Specific applications: Consumer Electronics, Industrial Equipment



CAUTION

#### **Limitation of Applications**

The products listed in the datasheet (hereinafter the product(s) is called the "Product(s)") are designed and manufactured for applications specified in the specification or the datasheet. (hereinafter called the "Specific Application"). We shall not warrant anything in connection with the Products including fitness, performance, adequateness, safety, or quality, in the case of applications listed in from (1) to (11) written at the end of this precautions, which may generally require high performance, function, quality, management of production or safety. Therefore, the Product shall be applied in compliance with the specific application.

We disclaim any loss and damages arising from or in connection with the products including but not limited to the case such loss and damages caused by the unexpected accident, in event that (i) the product is applied for the purpose which is not specified as the specific application for the product, and/or (ii) the product is applied for any following application purposes from (1) to (11) (except that such application purpose is unambiguously specified as specific application for the product in our catalog specification forms, datasheets, or other documents officially issued by us\*).

- Aircraft equipment (1)(2)Aerospace equipment
- (3)Undersea equipment
- (4) Power plant control equipment
- (5) Medical equipment
- (6)Transportation equipment (such as vehicles, trains, ships)
- (7)Traffic control equipment
- Disaster prevention / crime prevention equipment (8)
- (9)Industrial data-processing equipment
- (10)Combustion/explosion control equipment
- (11)Application of similar complexity and/or reliability requirements to the applications listed in the above

For exploring information of the Products which will be compatible with the particular purpose other than those specified in the datasheet, please contact our sales offices, distribution agents, or trading companies with which you make a deal, or via our web contact form.

Contact form: https://www.murata.com/contactform


\*We may design and manufacture particular Products for applications listed in (1) to (11). Provided that, in such case we shall unambiguously specify such Specific Application in specification or datasheet without any exception. Therefore, any other documents and/or performances, whether exist or non-exist, shall not be deemed as the evidence to imply that we accept the applications listed in (1) to (11).



#### Fail-safe function

Be sure to add an appropriate fail-safe function to your finished product to prevent secondary damage in the unlikely event of an abnormality function or malfunction in our product.

Please connect the input terminal by right polarity. If you mistake the connection, it may break the DC-DC converter. In the case of destruction of the DC-DC converter inside, over input current may flow. Please add a diode and fuse as following to protect



Please select diode and fuse after confirming the operation.

#### Note

- Please make sure that your product has been evaluated in view of your specifications with our product being mounted to your product.
- 2. You are requested not to use our product deviating from the reference specifications.
- 3. If you have any concerns about materials other than those listed in the RoHS directive, please contact us.
- 4. Please don't wash this product under any conditions.

#### **Product Specification**

Product Specification in this datasheet are as of November 2023. Specifications and features may change in any manner without notice. Please check with our sales representatives.

### **Contact form**

https://www.murata.com/contactform?Product=Power%20Device



#### **Disclaimers**

The information described in this data sheet was carefully crafted for accuracy. However this product is based on the assumption that it will be used after thoroughly verifying and confirming the characteristics and system compatibility. Therefore, Murata is not responsible for any damages caused by errors in the description of the datasheet.

Murata constantly strives improve the quality and reliability of our products, but it is inevitable that semiconductor products will fail with a certain probability. Therefore regardless of whether the use conditions are within the range of this data sheet, Murata is not responsible for any damage caused by the failure of this product., (for example, secondary damage, compensation for accidents, punitive damage, loss of opportunity, and etc.) Also, regardless of whether Murata can foresee the events caused by the failure of our product, Murata has no obligations or responsibilities.

The buyer of this product and developer of systems incorporating this product must analyze, evaluate, and make judgements at their own risk in designing applications using this product. The buyer and the developer are responsible for verifying the safety of this product and the applications, and complying with all applicable laws, regulations, and other requirements.

Furthermore, the buyer and developer are responsible for predicting hazards and taking adequate safeguards against potential events at your own risk in order to prevent personal accidents, fire accidents, or other social damage. When using this product, perform thorough evaluation and verification of the safety design designed at your own risk for this product and the application.

Murata assumes that the buyer and developer have the expertise to verify all necessary issues for proper use of the product as described above and to take corrective action. Therefore, Murata has no liability arising out of the use of the product. The buyer and developer should take all necessary evaluations, verifications, corrective actions and etc., in your own responsibility and judgment.

This data sheet does not guarantee or grant any license to the information, including patents, copyrights, and other intellectual property rights, of the Murata or third parties. Regardless of whether the information described in this datasheet is express or implied, Murata does not take any responsibility or liability for any claims, damages, costs, losses, etc. relating to intellectual property rights or other rights from third parties due to the use of these information.

#### **Patent Statement**

Murata products are protected to under one or more of the U.S. patents.

# **Copyright and Trademark**

©2023 Murata Manufacturing Co., Ltd. All rights reserved.



This product is subject to the following <u>operating requirements</u> and the <u>Life and Safety Critical Application Sales Policy</u>: Refer to: https://power.murata.com/en/requirements

Murata Manufacturing Co., Ltd makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not imply the granting of licenses to make, use,