

NCM6 Series

Isolated 6W Wide Input Single & Dual Output DC-DC Converters



FEATURES

- UL60950 reinforced insulation
- ANSI/AAMI ES60601-1, 1 MOPP/2 MOOP's recognised
- 4:1 wide range voltage input³
- Operating temperature range –40°C to 85°C
- 5.2kVDC isolation 'Hi Pot Test'
- Typical efficiency to 88%
- 5V, 12V & 48V nominal inputs
- Power density 0.94W/cm³
- 5mm creepage guaranteed
- Under voltage lock out
- Control pin option

PRODUCT OVERVIEW

The NCM6 series of DC-DC converters offers single & dual output voltages from wide input voltage ranges of 4.5-9, 9-36V & 18-75V. The NCM6 is housed in an industry standard package with a standard pinout. The NCM6 is encapsulated for superior thermal performance.

Applications include medical, telecommunication battery powered systems, process control and distributed power systems.

SELECTION GU	IDE									
Order Code ¹	Input Voltage	Output Voltage	Output Current	Effici	ency	Effici	iency	solation Capacitance	MTTF ²	Recommended Alternative
order oode	Nom.	Out	Out	5V/12V/4	18V Input	24V	Input	Isolatio		Recom
	V	V	Α	Min.	Typ.	Min. %	Typ.	pF	Hrs	
			Reco	mmen	ded Ir	n Produ	uction			
NCM6D0505EC	5	±5	±0.6	78	80			10	492,600	
NCM6D0512EC	5	±12	±0.25	81	83			15	537,754	
NCM6D0515EC	5	±15	±0.2	81	83			15	462,042	
NCM6S0505C	5	5	1.2	77	80			15	576,445	
NCM6D1205EC	12	±5	±0.6	81	83	79	80	15	285,466	
NCM6D1212C	12	±12	±0.25	86	88	81	84	25	412,808	
NCM6D1215C	12	±15	±0.2	85	87	82	84	25	366,356	
NCM6S1205EC	12	5	1.2	81	82	79	80	15	475,352	
NCM6S1212C	12	12	0.5	84	86	81	83	25	490,876	
NCM6S1212EC	12	12	0.5	84	86	81	83	25	490,876	
NCM6S1215C	12	15	0.4	85	87	82	84	25	457,651	
				Dis	scontin	ued				
NCM6D0505C	5	±5	±0.6	78	80			10	492,600	NCM6D0505EC
NCM6D0512C	5	±12	±0.25	81	83			15	537,754	Contact Murata
NCM6D0515C	5	±15	±0.2	81	83			15	462,042	Contact Murata
NCM6D1205C	12	±5	±0.6	81	83	79	80	15	285,466	NCM6D1205EC
NCM6D1212EC	12	±12	±0.25	86	88	81	84	25	412,808	NCM6D1212C
NCM6D1215EC	12	±15	±0.2	85	87	82	84	25	366,356	NCM6D1215C
NCM6D4805C	48	±5	±0.6	77	80	79	81	10	393,923	NCS6D4805C
NCM6D4805EC	48	±5	±0.6	77	80	79	81	10	393,923	NCS6D4805C
NCM6D4812C	48	±12	±0.25	78	82	82	84	22	444,419	NCS6D4812C
NCM6D4812EC	48	±12	±0.25	78	82	82	84	22	444,419	NCS6D4812C
NCM6D4815C	48	±15	±0.2	81	83	84	86	25	409,328	NCS6D4815C
NCM6D4815EC	48	±15	±0.2	81	83	84	86	25	409,328	NCS6D4815C
NCM6S0503C	5	3.3	1.52	73	75			15	548,686	Contact Murata
NCM6S0503EC	5	3.3	1.52	73	75			15	548,686	Contact Murata
NCM6S0505EC	5	5	1.2	77	80			15	576,445	NCM6S0505C
NCM6S0512C	5	12	0.5	80	82			20	608,806	Contact Murata
NCM6S0512EC	5	12	0.5	80	82				608,806	Contact Murata
NCM6S0515C	5	15	0.4	80	82			15	566,572	Contact Murata
NCM6S0515EC	5	15	0.4	80	82	7.4	77	15	566,572	Contact Murata
NCM6S1203C	12	3.3	1.52	75	79	74	77	12	685,045	NCS6S1203C
NCM6S1203EC	12	3.3	1.52	75	79	74	77	12	685,045	Contact Murata
NCM6S1205C	12	5	1.2	81	82	79	80	15	475,352	NCM6S1205EC
NCM6S1215EC	12	15	0.4	85	87	82	84	25	457,651	NCM6S1215C





- 1 To order with optional control pin insert an 'E' prior to the suffix C, i.e. NCM6S1205EC.
- 2 Calculated using MIL-HDBK-217F FN2, parts stress method with nominal input voltage at full load.
- 3. 5V inputs have a 2:1 input range.
- All specifications typical at Ta=25°C, nominal input voltage and rated output current unless otherwise specified.



SELECTION GUID	E (Continued)									
Order Code ¹	Input Voltage	Output Voltage	Output Current	Effic	iency	Effic	iency	Isolation Capacitance	MTT F2	Recommended Alternative
	Nom.			5V/12V/48V Input		24V Input		Isolatio		Recomi
	V	V	A	Min. %	Typ.	Min.	Typ.	pF	Hrs	
NONCCADOOO	40	0.0	1.50		scontinued		70	10	550.010	N000040000
NCM6S4803C NCM6S4803EC	48	3.3	1.52 1.52	71 71	74 74	71 71	76 76	12 12	552,818 552,818	NCS6S4803C NCS6S4803C
NCM6S4805C	48	5	1.2	74	78	75	80	15	467,793	NCS6S4805C
NCM6S4805EC	48	5	1.2	74	78	75	80	15	467,793	NCS6S4805C
NCM6S4812C	48	12	0.5	79	82	83	84	20	520,610	NCS6S4812C
NCM6S4812EC	48	12	0.5	79	82	83	84	20	520,610	NCS6S4812C
NCM6S4815C	48	15	0.4	81	83	85	86	25	499,288	NCS6S4815C
NCM6S4815EC	48	15	0.4	81	83	85	86	25	499,288	NCS6S4815C



SELECTION GUIDE	(00000000000000000000000000000000000000	Input C	urrent			8	
Order Code	0% Load	100% Load	0% Load	100% Load	Ripple & Noise	Recommended Alternative	
Order Code	Typ. 5V, 12V			4V Input	Typ.	- Iteri	
	mA	mA	mA	mA	mVp/p	Bec A	
				duction	P. P.		
NCM6D0505EC	20	1500			20		
NCM6D0512EC	25	1450			20		
NCM6D0515EC	30	1450			15		
NCM6S0505C	20	1500			20		
NCM6D1205EC	11	600	9	310	100		
NCM6D1203EC	13	560	12	300	100		
NCM6D1212C	15	570	13	300	100		
NCM6S1205EC	10	610	9	315	25		
NCM6S1203EC	15	575	12	300	70		
NCM6S1212EC	15	575	12	300	70		
	15	575	13	300	105		
NCM6S1215C	15	5/5		300	100		
			Discontinued				
NCM6D0505C	20	1500			20	NCM6D0505E	
NCM6D0512C	25	1450			20	Contact Murat	
NCM6D0515C	30	1450			15	Contact Murat	
NCM6D1205C	11	600	9	310	100	NCM6D1205E	
NCM6D1212EC	13	560	12	300	100	NCM6D12120	
NCM6D1215EC	15	570	13	300	100	NCM6D12150	
NCM6D4805C	6	160	7	310	150	NCS6D48050	
NCM6D4805EC	6	160	7	310	150	NCS6D48050	
NCM6D4812C	8	150	9	300	100	NCS6D48120	
NCM6D4812EC	8	150	9	300	100	NCS6D48120	
NCM6D4815C	8	150	10	300	150	NCS6D48150	
NCM6D4815EC	8	150	10	300	150	NCS6D48150	
NCM6S0503C	8	1300			10	Contact Murat	
NCM6S0503EC	8	1300			10	Contact Murat	
NCM6S0505EC	20	1500			20	NCM6S05050	
NCM6S0512C	25	1500			90	Contact Murat	
NCM6S0512EC	25	1500			90	Contact Murat	
NCM6S0515C	30	1500			90	Contact Murat	
NCM6S0515EC	30	1500			90	Contact Murat	
NCM6S1203C	10	525	9	270	60	NCS6S12030	
NCM6S1203EC	10	525	9	270	60	Contact Murat	
NCM6S1205C	10	610	9	315	25	NCM6S1205E	
NCM6S1215EC	15	575	13	300	105	NCM6S12150	
NCM6S4803C	10	140	7	275	30	NCS6S4803C	
NCM6S4803EC	10	140	7	275	30	NCS6S48030	
NCM6S4805C	10	160	7	300	25	NCS6S48050	
NCM6S4805EC	10	160	7	300	25	NCS6S48050	
NCM6S4812C	10	150	9	300	70	NCS6S48120	
NCM6S4812EC	10	150	9	300	70	NCS6S48120	
NCM6S4815C	10	150	10	300	95	NCS6S48150	
NCM6S4815EC	10	150	10	300	95	NCS6S48150	



INPUT CHARACTERISTICS					
Parameter	Conditions	Min.	Тур.	Max.	Units
	NCM6X05	4.5	5	9	
Voltage range	NCM6X12	9	12	36	V
	NCM6X48	18	48	75	
	Turn on threshold NCM6X05		4.2		
	Turn off threshold NCM6X05		3.6		
Under veltage leek out	Turn on threshold NCM6X12		8.2		V
Under voltage lock out	Turn off threshold NCM6X12		6.5		V
	Turn on threshold NCM6X48		14		
	Turn off threshold NCM6X48		13.7		
Reflected ripple current	All variants		10		mA p-p

GENERAL CHARACTERISTICS ¹	GENERAL CHARACTERISTICS ¹									
Parameter	Conditions	Min.	Тур.	Max.	Units					
Switching frequency			300		kHz					
Control nin input	Module on (or pin unconnected)			1.0	V					
Control pin input	Module off	3.0			V					

Parameter	Conditions		Min.	Typ.	Max.	Units	
Dated names	5V, 12V & 15V output types				6	W	
Rated power	3.3V output types				5	5 VV	
	D4812C & D4815C, SXX03C, SXX12			±2			
	SXX05C			±2.5			
Voltage set point accuracy	D1212C & D1215C			±3	%		
	D0505C, D0512C, D0515C,	Positive			±2		
	D1205C & D4805C	Negative			±3		
		Single		0.1	0.5	0,	
Line regulation	Low line to high line	Dual		0.1	0.75	%	
		NCM6xxx03C, D0512C & D0515C		0.5	1		
Load Regulation	10% total load to 100% total load	NCM6xxx05C		0.3	1	%	
Load negulation	10% total load to 100% total load	NCM6Sxx12C, NCM6Sxx15C, D1212C, D1215C, D4812C & D4815C		0.06	0.5		
	% voltage change on negative out-	5V	5		5		
Cross Regulation	put when positive load varies from 12.5% to 37.5% with negative load fixed at 50%	12V & 15V			3	%	
Minimum output load for specification (see application notes)	10% of rated load						
,	Peak deviation - Single Output (25-75% & 75-25% swing) - Dual Output (12.5-37.5% & 37.5-12.5% swing)						
	SXX03C	Ç,		10			
	SXX05C			8			
	S4815			2			
	D0505, S0512 & S0515			5		%Vou	
Transient Response	D0512 & D0515			2		%vou	
	D1205			6			
	D1212, D1215 & S4812		3				
	D4805 & D4815			9			
	D4812			1			
	S1212 & S1215		4				
	Settling time (within 1% Vout Nom.)		250		μs		





ISOLATION CHARACTERISTICS									
Parameter		Conditions		Тур.	Max.	Units			
la elektron kank volka na		Production tested for 1 second				VDC			
Isolation test voltage		Qualification tested for 1 minute	5200			VDC			
Resistance		Viso = 1kVDC	1			GΩ			
Cofoty atandard	UL60950-1	Reinforced			250	Vrms			
Safety standard	ANSI/AAMI ES60601-1	1 MOPP/ 2 MOOP			250	VIIIIS			

TEMPERATURE CHARACTERISTICS									
Parameter	Conditions	Min.	Тур.	Max.	Units				
Operation	Please refer to derating graphs	-40		85					
Storage		-50		125					
	D0515, D1212, D1215, D4815, S1212, S1215, S4812, S4815		35						
Case temperature rise above ambient	D0512, D4812, S1203, S1205		40		°C				
Case temperature rise above ambient	D0505, D1205, D4805, S0503, S0512, 0515, 4803, 4805		45						
	S0505C		47						
Thermal shutdown	Case Temperature		+105						

ABSOLUTE MAXIMUM RATINGS	
Short-circuit protection (for SELV input voltages)	Continuous
Lead temperature 1.0mm from case for 10 seconds (to JEDEC JESD22-B106 ISS C)	260°C
Wave Solder	Wave Solder profile not to exceed the profile recommended in IEC 61760-1 Section 6.1.3. Please refer to <u>application notes</u> for further information.
Input voltage, NCM6X05	10V
Input voltage, NCM6X12	40V
Input voltage, NCM6X48	80V
Control pin input voltage	±20V



TECHNICAL NOTES

ISOLATION VOLTAGE

'Hi Pot Test', 'Flash Tested', 'Withstand Voltage', 'Proof Voltage', 'Dielectric Withstand Voltage' & 'Isolation Test Voltage' are all terms that relate to the same thing, a test voltage, applied for a specified time, across a component designed to provide electrical isolation, to verify the integrity of that isolation.

Murata Power Solutions NCM6 series of DC-DC converters are all 100% production tested at their stated isolation voltage. This is 5.2kVDC for 1 second.

A question commonly asked is, "What is the continuous voltage that can be applied across the part in normal operation?"

The NCM6 series has been recognised by Underwriters Laboratory to 250Vrms for Reinforced Insulation.

REPEATED HIGH-VOLTAGE ISOLATION TESTING

It is well known that repeated high-voltage isolation testing of a barrier component can actually degrade isolation capability, to a lesser or greater degree depending on materials, construction and environment. We therefore strongly advise against repeated high voltage isolation testing, but if it is absolutely required, that the voltage be reduced by 20% from specified test voltage.

SAFETY APPROVAL

ANSI/AAMI ES60601-1

The NCM6 series has been recognised by Underwriters Laboratory (UL) to ANSI/AAMI ES60601-1 and provides 1 MOPP (Means Of Patient Protection) and 2 MOOP (Means Of Operator Protection) based upon a working voltage of 250 Vrms max., between Primary and Secondary. File number E202895 applies.

III 60950

The NCM6 series has been recognised by Underwriters Laboratory (UL) to UL 60950 for reinforced insulation to a working voltage of 250Vrms. File number E151252 applies.

FUSING

The NCM6 Series of converters are not internally fused so to meet the requirements of UL an anti-surge input line fuse should always be used with ratings as defined below.


Input Voltage, 5V 3A Input Voltage, 12V 2A Input Voltage, 48V 1A

All fuses should be UL recognised and rated to at least the maximum allowable DC input voltage.

ROHS COMPLIANCE INFORMATION



This series is compatible with RoHS soldering systems with a peak wave solder temperature of 260°C for 10 seconds. Please refer to application notes for further information. The pin termination finish on this product series is a Gold flash (0.05-0.10 micron) over Nickel Preplate. The series is backward compatible with Sn/Pb soldering systems. For further information, please visit www.murata.com/en-global/products/power/rohs





CHARACTERISATION TEST METHODS Ripple & Noise Characterisation Method Ripple and noise measurements are performed with the following test configuration. 1µF X7R multilayer ceramic capacitor, voltage rating to be a minimum of 3 times the output voltage of the DC-DC converter 10µF tantalum capacitor, voltage rating to be a minimum of 1.5 times the output voltage of the DC-DC converter with an ESR of less C2 than 100mΩ at 100 kHz C3 100nF multilayer ceramic capacitor, general purpose R1 450 $\!\Omega$ resistor, carbon film, ±1% tolerance R2 50Ω BNC termination T1 3T of the coax cable through a ferrite toroid **RLOAD** Resistive load to the maximum power rating of the DC-DC converter. Connections should be made via twisted wires Measured values are multiplied by 10 to obtain the specified values. Differential Mode Noise Test Schematic OSCILLOSCOPI



APPLICATION NOTES

Output Capacitance and start-up times

The NCM6 series does not require output capacitors to meet datasheet specification. To meet datasheet specification, output capacitance should not exceed:

Part No.	Maximum Load Capacitance (per output)	Start-up times		
rail No.	μF	ms		
NCM6D0505C	220	6		
NCM6D0512C	100	12		
NCM6D0515C	100	18		
NCM6S0503C	470	4		
NCM6S0505C	220	7		
NCM6S0512C	100	12		
NCM6S0515C	100	17		
NCM6D1205C	220	5		
NCM6D1212C	100	12		
NCM6D1215C	100	17		
NCM6S1203C	470	2		
NCM6S1205C	220	6		
NCM6S1212C	100	14		
NCM6S1215C	100	17		
NCM6D4805C	220	10		
NCM6D4812C	100	40		
NCM6D4815C	100	60		
NCM6S4803C	470	2		
NCM6S4805C	220	5		
NCM6S4812C	100	15		
NCM6S4815C	100	20		

Control Pin


This provides an OFF function which puts the converter into a low power mode when >3V is applied to the pin. When the control pin is left unconnected or less than 1V the converter is ON


Minimum Load

The minimum load to meet full datasheet specification is 10% of the full rated load across the specified input voltage range.


Between 0% and 10% output loading, the output voltage will remain within data sheet specification however, output ripple and noise may increase but will still be below 150mV p-p.





















EMC FILTERING AND SPECTRA

FILTERING

The module includes a basic level of filtering, sufficient for many applications. Where lower noise levels are desired, filters can easily be added to achieve any required noise performance.


A DC-DC converter generates noise in two principle forms: that which is radiated from its body and that conducted on its external connections. There are three separate modes of conducted noise: input differential, output differential and input-output.

This last appears as common mode at the input and the output, and cannot therefore be removed by filtering at the input or output alone. The first level of filtering is to connect capacitors between input and output returns, to reduce this form of noise. It typically contains high harmonics of the switching frequency, which tend to appear as spikes on surrounding circuits. The voltage rating of this capacitor must match the required isolation voltage. (Due to the great variety in isolation voltage and required noise performance, this capacitor has not been included within the converter.)

Input ripple is a voltage developed across the internal Input decoupling capacitor. It is therefore measured with a defined supply source impedance. Although simple series inductance will provide filtering, on its own it can degrade the stability. A shunt capacitor is therefore recommended across the converter input terminals, so that it is fed from a low impedance.

If no filtering is required, the inductance of long supply wiring could also cause a problem, requiring an input decoupling capacitor for stability. An electrolytic will perform well in these situations. The input-output filtering is performed by the common-mode choke on the primary. This could be placed on the output, but would then degrade the regulation and produce less benefit for a given size, cost, and power loss.

Radiated noise is present in magnetic and electrostatic forms. Thanks to the small size of these units, neither form of noise will be radiated "efficiently", so will not normally cause a problem. Any question of this kind usually better repays attention to conducted signals.





TO MEET CURV	ΕB							
Part Number	C1	C2	C3	C4	C5	L1	L2	L3
NCM6S0503C	1µF	1µF	1000μF	10nF	10nF	51105C	20μΗ	Not required
NCM6S0505C	1μF	1µF	1000μF	10nF	10nF	51105C	60µH	Not required
NCM6S0512C	1μF	1μF	1000μF	15nF	15nF	51305C	60μH	60μΗ
NCM6S0515C	1μF	1μF	1000μF	15nF	15nF	51305C	60μΗ	60μH
NCM6D0505C	1μF	1μF	1000μF	10nF	10nF	51105C	20μΗ	Not required
NCM6D0512C	1μF	1μF	1000μF	10nF	10nF	51105C	20μΗ	Not required
NCM6D0515C	1μF	1μF	1000μF	10nF	10nF	51105C	20μΗ	Not required
NCM6S1203C	1μF	1μF	47µF	10nF	10nF	51105C	Not required	Not required
NCM6S1205C	1μF	1μF	47µF	10nF	10nF	51105C	60μH	Not required
NCM6S1212C	1μF	1μF	47µF	10nF	10nF	51105C	20μΗ	Not required
NCM6S1215C	1μF	1μF	47µF	10nF	10nF	51105C	20μΗ	Not required
NCM6D1205C	1μF	1µF	47µF	10nF	10nF	51105C	Not required	Not required
NCM6D1212C	1μF	1μF	47µF	10nF	10nF	51105C	Not required	Not required
NCM6D1215C	1μF	1μF	47μF	10nF	10nF	51105C	20μΗ	Not required
NCM6S4803C	1μF	1µF	47µF	10nF	10nF	51105C	Not required	Not required
NCM6S4805C	1μF	1μF	47µF	10nF	10nF	51505C	Not required	Not required
NCM6S4812C	1μF	1μF	47µF	10nF	10nF	51505C	Not required	Not required
NCM6S4815C	1μF	1μF	47µF	10nF	10nF	51505C	Not required	Not required
NCM6D4805C	1μF	1µF	47µF	10nF	10nF	51505C	Not required	Not required
NCM6D4812C	1µF	1µF	47µF	10nF	10nF	51505C	60µH	Not required
NCM6D4815C	1μF	1μF	47μF	10nF	10nF	51505C	Not required	Not required





EMC FILTERING AND SPECTRA (Continued)


TO MEET CURVE	TO MEET CURVE A										
Part Number	C1	C2	C3	C4	C5	L1	L2	L3			
NCM6S0503C	1μF	1μF	1000μF	Not required	Not required	51105C	60µH	60µH			
NCM6S0505C	1μF	1μF	1000μF	Not required	Not required	51105C	60µH	60µH			
NCM6S0512C	1μF	1μF	1000µF	Not required	Not required	51305C	60µH	60µH			
NCM6S0515C	1μF	1µF	1000μF	Not required	Not required	51305C	60µH	60µH			
NCM6D0505C	1μF	1μF	1000μF	Not required	Not required	51105C	60µH	60µH			
NCM6D0512C	1μF	1µF	1000μF	Not required	Not required	51105C	60µH	60µH			
NCM6D0515C	1µF	1µF	1000μF	Not required	Not required	51105C	60µH	60µH			
NCM6S1203C	1μF	1μF	47μF	Not required	Not required	51105C	60µH	60µH			
NCM6S1205C	1µF	1µF	47μF	Not required	Not required	51105C	60µH	60µH			
NCM6S1212C	1μF	1μF	47μF	Not required	Not required	51105C	60µH	60µH			
NCM6S1215C	1μF	1μF	47μF	Not required	Not required	51105C	60µH	60µH			
NCM6D1205C	1μF	1µF	47μF	Not required	Not required	51105C	60µH	60µH			
NCM6D1212C	1μF	1µF	47μF	Not required	Not required	51105C	60µH	60µH			
NCM6D1215C	1μF	1μF	47μF	Not required	Not required	51105C	60µH	60µH			
NCM6S4803C	1μF	1μF	47μF	Not required	Not required	51105C	60µH	60µH			
NCM6S4805C	1μF	1µF	47μF	Not required	Not required	51505C	60µH	60µH			
NCM6S4812C	1µF	1µF	47µF	Not required	Not required	51505C	60µH	60µH			
NCM6S4815C	1µF	1µF	47µF	Not required	Not required	51505C	60µH	60µH			
NCM6D4805C	1μF	1μF	47µF	Not required	Not required	51505C	60µH	60µH			
NCM6D4812C	1μF	1μF	47µF	Not required	Not required	51505C	60µH	60µH			
NCM6D4815C	1μF	1µF	47µF	Not required	Not required	51505C	60µH	60µH			























NCM6 Series

Isolated 6W Wide Input Single & Dual Output DC-DC Converters

DISCLAIMER

Unless otherwise stated in the datasheet, all products are designed for standard commercial and industrial applications and NOT for safety-critical and/or life-critical applications.

Particularly for safety-critical and/or life-critical applications, i.e. applications that may directly endanger or cause the loss of life, inflict bodily harm and/or loss or severe damage to equipment/property, and severely harm the environment, a prior explicit written approval from Murata is strictly required. Any use of Murata standard products for any safety-critical, life-critical or any related applications without any prior explicit written approval from Murata shall be deemed unauthorised use.

These applications include but are not limited to:

- Aircraft equipment
- Aerospace equipment
- Undersea equipment
- Power plant control equipment
- Medical equipment
- Transportation equipment (automobiles, trains, ships, etc.)
- Traffic signal equipment
- Disaster prevention / crime prevention equipment
- Data Processing equipment

Murata makes no express or implied warranty, representation, or guarantee of suitability, fitness for any particular use/purpose and/or compatibility with any application or device of the buyer, nor does Murata assume any liability whatsoever arising out of unauthorised use of any Murata product for the application of the buyer. The suitability, fitness for any particular use/purpose and/or compatibility of Murata product with any application or device of the buyer remain to be the responsibility and liability of the buyer.

Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm, and take appropriate remedial actions. Buyer will fully indemnify and hold Murata, its affiliated companies, and its representatives harmless against any damages arising out of unauthorised use of any Murata products in any safety-critical and/or life-critical applications.

Remark: Murata in this section refers to Murata Manufacturing Company and its affiliated companies worldwide including, but not limited to, Murata Power Solutions.



This product is subject to the following <u>operating requirements</u> and the <u>Life and Safety Critical Application Sales Policy</u>:

Refer to: https://www.murata.com/en-eu/products/power/requirements

Murata Power Solutions (Milton Keynes) Ltd. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not imply the granting of licenses to make, use, or sell equipment constructed in accordance therewith. Specifications are subject to change without notice.