ULE Series

Isolated, High Density, Eighth-Brick 1.25–20 Amp, DC-DC Converters



Typical unit

The ULE Series "Eighth-Brick" DC-DC Converters are high-current isolated power converters designed for use in high-density system boards.

FEATURES

- RoHS compliant
- New 1/8-brick package, 1/4-brick pinout in through-hole or SMT version
- 0.89 x 2.22 x 0.36 in. (22.6 x 56.4 x 9.1mm)
- Output current: 1.25-20 Amps
- Output voltages: 1.5V to 48V
- Input voltage: 12V, 24V and 48V nominal
- Interleaved, synchronous-rectifier
 - topology delivers:
 - Outstanding efficiency (to 94%)
 - Low noise
 - Stable no-load operation
 - No output reverse conduction
- Excellent thermal performance
- On/off control, trim and sense pins
- Fully isolated (2250Vdc BASIC)
- Fully I/O protected; Thermal shutdown
- Certified to UL/IEC 60950-1 and CAN/CSA C22.2 No.60950-1, 2nd edition
- Lead-free construction/attach

PRODUCT OVERVIEW

Measuring just $0.89 \times 2.22 \times 0.36$ inches (22.6 \times 56.4 \times 9.1mm), these open-frame, low-profile E-bricks fit the industry-standard quarter-brick footprint. Now you can "cut-and-paste" the layout from your last Q-brick design to save time and save 44% board space (1.86 square inches versus 3.3) in the process.

From a 9-18V, 18-36V or 36-75V input, ULEs deliver 1.5 to 48 Volt outputs with current up to 20 Amps. They employ an interleaved, synchronous-rectifier topology that exploits 100% of their duty cycle. They simultaneously achieve high efficiency, low noise, tight line/load regulation, and quick step response.

An open-frame design, high efficiency, low-on-resistance FETs, and planar magnetics embedded in heavy-copper pc boards all contribute to impressive thermal derating. The ULEs feature set includes high isolation (2250Vdc, 48V models), input pi filters, input undervoltage shutdown, output overvoltage protection, current limiting, short-circuit protection, and thermal shutdown. The standard footprint carries Vour trim, on/off control, and sense pins (sense pins are not available on 12V or higher models).

All ULE E-Bricks are certified to the BASIC-insulation requirements of UL/IEC60950-1, 2nd edition, and all "D48" models (36-75V input ranges) carry the CE mark. Safety certifications, EMC compliance testing and qualification testing are available.



www.murata-ps.com/support

ULE Series

Isolated, High Density, Eighth-Brick 1.25–20 Amp, DC-DC Converters


				Outpu	t				Inp	out		Efficiency	
	Vout	Іоит	Power	· ·	Vp-p) ©	Regulatio	on (Max.)	VIN Nom.	Range	lın no load	lın full load		
Model Family ①	(V)	(A)	(W)	Тур.	Max.	Line	Load	(V)	(V)	(mA)	(A)	Min.	Тур.
ULE-1.5/20-D24xx-C	1.5	20	30	25	60	±0.15%	±0.15%	24	18-36	40	1.42	86%	88%
ULE-1.5/20-D48xx-C	1.5	20	30	25	60	±0.15%	±0.15%	48	36-75	40	0.74	84%	84.5
ULE-1.8/20-D24xx-C	1.8	20	36	40	80	±0.1%	±0.1%	24	18-36	40	1.72	85%	87%
ULE-1.8/20-D48xx-C	1.8	20	36	40	80	±0.25%	±0.25%	48	36-75	40	0.87	84.5%	86.5
ULE-2.5/20-D24xx-C	2.5	20	50	30	50	±0.05%	±0.05%	24	18-36	95	2.35	87%	88.5
ULE-2.5/20-D48xx-C	2.5	20	50	50	75	±0.05%	±0.1%	48	36-75	55	1.17	88%	89%
ULE-3.3/20-D12x-C	3.3	20 \$	66	60	100	±0.05%	±0.05%	12	9-18 S	100	6.15	88.9%	89.4
ULE-3.3/20-D12xM-C	3.3	20 \$	66	60	100	±0.05%	±0.05%	12	9-18 S	100	6.15	88.9%	89.4
ULE-3.3/20-D24x-C	3.3	20	66	50	80	±0.05%	±0.05%	24	18-36	60	3.09	88%	89%
ULE-3.3/20-D24xM-C	3.3	20	66	50	80	±0.05%	±0.05%	24	18-36	60	3.09	88%	89%
ULE-3.3/20-D48x-C	3.3	20	66	50	100	±0.1%	±0.25%	48	36-75	60	1.54	87%	89%
ULE-3.3/20-D48xM-C	3.3	20	66	50	100	±0.1%	±0.25%	48	36-75	60	1.54	87%	89%
ULE-5/10-D12x-C	5	10	50	60	125	±0.05%	±0.05%	12	9-18	160	4.63	87%	90%
ULE-5/12-D24x-C	5	12 3	60	50	100	±0.1%	±0.25%	24	19-36 3	160	2.78	88%	909
ULE-5/12-D24xM-C	5	12 3	60	50	100	±0.1%	±0.25%	24	19-36 3	160	2.78	88%	90%
ULE-5/12-D48x-C	5	12	60	50	100	±0.1%	±0.25%	48	36-75	90	1.38	88.5%	90.5
ULE-5/12-D48xM-C	5	12	60	50	100	±0.1%	±0.25%	48	36-75	90	1.38	88.5%	90.5
ULE-12/4.2-D24x-C	12	4.2 ④	50.4	50	150	±0.05%	±0.075%	24	18-36	55	2.31	89.5%	91%
ULE-12/4.2-D24xM-C	12	4.2 ④	50.4	50	150	±0.05%	±0.075%	24	18-36	55	2.31	89.5%	91%
ULE-12/4.2-D48x-C	12	4.2	50.4	50	150	±0.05%	±0.075%	48	36-75	55	1.14	91%	92%
ULE-12/4.2-D48xM-C	12	4.2	50.4	50	150	±0.05%	±0.075%	48	36-75	55	1.14	91%	92%
ULE-24/3-D48x-C	24	3	72	400	700	±0.3%	±1.25%	48	36-75	45	1.63	90.8%	92%
ULE-48/1.25-D48x-C	48	1.25	60	640	750	±0.175%	±3.2%	48	36-75	75	1.35	91%	92.5
ULE-48/1.25-D48xM-C	48	1.25	60	640	750	±0.175%	±3.2%	48	36-75	75	1.35	91%	92.5

④ Min. load = 10%. (5) If $V_{IN} = 9-10V$, lout = 18A Max.

 Please refer to the full model number structure for additional ordering part numbers and options.
All specifications are at nominal line voltage and full load, +25°C unless otherwise noted. See detailed specifications.
If V_{IN} = 19−20V, lout = 8A Max.

ULE Series

Isolated, High Density, Eighth-Brick 1.25–20 Amp, DC-DC Converters



Special quantity order is required; samples available with standard pin length only. SMT (M) versions not available in sample quantities. Some model number combinations may not be available. See website or contact your local Murata sales representative.

*See www.murata.com for model-specific availability.

ULE Series

Isolated, High Density, Eighth-Brick 1.25–20 Amp, DC-DC Converters

FUNCTIONAL SPECIFICATIONS

INPUT CHARACTI	ERISTICS							•								
		Under	Reflected			Load Cu	rrent			Inter-			Remote On/Off	Control	Start-	up Time
	Start-up threshold Min. (V)	Shut-	(back) Ripple Current② (mA)	Full Load Condi- tions	Inrush Transient Conditions (A²sec)		No Load	-	Standby Mode (mA)	nal Input Filter Type	Reverse Polarity Protec- tion		Positive Logic "P" model suffix	Negative Logic "N" model suffix	VIN to VOUT regulated (Max.) mSec	Remote On/Off to Vout regu- lated (Max.) mSec
ULE-1.5/20-D24 ②	17.0	16.0						1.96								
ULE-1.5/20-D48	34.0	33.0						0.98								
ULE-1.8/20-D24 ②	17.0	16.0						2.3								
ULE-1.8/20-D48	33.0	31.0]					1.16								
ULE-2.5/20-D24	17.0	16.0	1					3.23								
ULE-2.5/20-D48	33.0	32.0	1					1.55								
ULE-3.3/20-D12	8.5	8.0	1			40–250		7.42			None.		OFF=Ground pin	OFF=open or	6-90, model	6-90, model
ULE-3.3/20-D24	17.0	16.0	15–45,	See	05.1	model	40-160	4.10	1–8	-C	install	1.0		+3.5V to +13.5V	dependent	dependent
ULE-3.3/20-D48	34.5	33.5	model dependent	Ordering Guide	0.5–1	depen-	model dependent	2.05	model dependen	L-U	external	1.0	ON=open or 3.5V to +13.5V	max. ON=Ground pin		
ULE-5/10-D12	8.5	8.0	1			dent		6.14			fuse		max.	to +0.8V max.		
ULE-5/12-D24	19.0	17.5	1					3.30								
ULE-5/12-D48	34.5	33.5	1					1.82								
ULE-12/4.2-D24	17.0	16.0	1					3.04								
ULE-12/4.2-D48	35.0	34.0	1					1.51								
ULE-24/3-D48	35.0	33.0	1					2.17							150	150
ULE-48/1.25-D48	35.0	33.5	1					1.46							6-90	6-90

Model Family		Vout Accuracy 50% Load % of Vnom	Capacitive Loading Max. Low ESR <0.02Ω Max. resistive load (μF)	Adjustment Range	Temperature Coefficient	Minimum Loading	Remote Sense Compensation	Ripple/Noise (20 MHz bandwidth)®	Line/Load Regulation	Efficiency	Current Limit Inception 98% of Vout after warmup (A)
ULE-1.5/20-D24	1.5										24
ULE-1.5/20-D48	1.5					No Minimum Load					24
ULE-1.8/20-D24	1.8		10,000								24
ULE-1.8/20-D48	1.8										25
ULE-2.5/20-D24	2.5	_		of VNON model							24
ULE-2.5/20-D48	2.5				±0.02% of Vout range/°C		+10%				24
ULE-3.3/20-D12	3.3	±1 to ±2							24		
ULE-3.3/20-D24	3.3	of VNOM,						0	24		
ULE-3.3/20-D48	3.3	model						See Ordering Guide			26
ULE-5/10-D12	5	dependent							13		
ULE-5/12-D24	5										15
ULE-5/12-D48	5										16
ULE-12/4.2-D24	12	1	2000			100 mA					6
ULE-12/4.2-D48	12	1	2000			420 mA					6.25
ULE-24/3-D48	24	1	680			300 mA	none		4.25		
ULE-48/1.25-D48	48	1	470			No Minimum	1				2.5

See notes on page 5.

ULE Series

Isolated, High Density, Eighth-Brick 1.25–20 Amp, DC-DC Converters

Switching Frequency

KHz

 280 ± 15

280±15

 340 ± 15

340±15

 385 ± 15

385±45

310±15

385±15

365±15

 325 ± 15

450±15 450±15

400±15

380±15

240±30

 250 ± 15

ISOLATION CHARACTE	RISTICS				DYNAMIC CHARACTER	ISTICS
Model Family	Input to Output Min. (V)	Isolation Resistance (ΜΩ)	Isolation Capacitance (pF)	Isolation Safety Rating	Model Family	Dynamic Load Response (50-75-50% load step)
ULE-1.5/20-D24			1750		ULE-1.5/20-D24	100µSec to $\pm 1.5\%$ of final value
ULE-1.5/20-D48		100			ULE-1.5/20-D48	100µSec to $\pm 1.5\%$ of final value
ULE-1.8/20-D24					ULE-1.8/20-D24	100µSec to $\pm 1.5\%$ of final value
ULE-1.8/20-D48					ULE-1.8/20-D48	100µSec to $\pm 1.5\%$ of final value
ULE-2.5/20-D24					ULE-2.5/20-D24	150µSec to $\pm 1\%$ of final value
ULE-2.5/20-D48]				ULE-2.5/20-D48	80µSec to $\pm 1.5\%$ of final value
ULE-3.3/20-D12				Basic	ULE-3.3/20-D12	150µSec to $\pm 1.25\%$ of final value
ULE-3.3/20-D24	2000-2250				ULE-3.3/20-D24	150µSec to $\pm 1.5\%$ of final value
ULE-3.3/20-D48	min., model dependent	100		Insulation	ULE-3.3/20-D48	150µSec to $\pm 1\%$ of final value
ULE-5/10-D12			470		ULE-5/10-D12	75µSec to $\pm 2\%$ of final value
ULE-5/12-D24			470		ULE-5/12-D24	75µSec to $\pm 2\%$ of final value
ULE-5/12-D48					ULE-5/12-D48	100µSec to $\pm 1\%$ of final value
ULE-12/4.2-D24]		1750		ULE-12/4.2-D24	150µSec to $\pm 1.25\%$ of final value
ULE-12/4.2-D48					ULE-12/4.2-D48	150µSec to $\pm 1.25\%$ of final value
ULE-24/3-D48]		2000		ULE-24/3-D48	200µSec to $\pm 2\%$ of final value
ULE-48/1.25-D48			1500		ULE-48/1.25-D48	200µSec to $\pm 1\%$ of final value

MISCELLANEOUS CH	ARACTERIST	rics								
Model Family	Calculated MTBF ④	Operating Temperature Range See derating curves	Operating PCB Temperature (no derating)	Storage Temperature Range	Thermal Protection/ Shutdown	Short Circuit Current	Overvoltage Protection [®] via magnetic feedback (V)	Short Circuit Protection Method © ⑦	Short Circuit Duration ®	Relative Humidity
ULE-1.5/20-D24						ЗA	2.3			
ULE-1.5/20-D48						ЗA	2.0			
ULE-1.8/20-D24						ЗA	2.3			
ULE-1.8/20-D48						ЗA	2.3			
ULE-2.5/20-D24						ЗA	3.5			
ULE-2.5/20-D48						ЗA	3.0	Current		
ULE-3.3/20-D12					+105 to	300mA	3.96	limiting,	Continuouo	То
ULE-3.3/20-D24	TBC	40.1 0500 11.1	-40 to +105℃	—55 to	+105 to +125°C,	ЗA	3.96	hiccup	Continuous, output shorted to ground.	+85°C/85% non- condensing
ULE-3.3/20-D48	IBC	-40 to +85°C with derating		+125℃	model	ЗA	3.96	autorestart. Remove		
ULE-5/10-D12					dependent	5A	6.0	overload for	No damage.	
ULE-5/12-D24						5A	6.0	recovery		
ULE-5/12-D48						2A	6.4			
ULE-12/4.2-D24						ЗA	15.0			
ULE-12/4.2-D48						ЗA	14.0			
ULE-24/3-D48*						0.65A	28.0	1		
ULE-48/1.25-D48						500mA	55.0	1		

*No derating is required up to 85°C. See notes on page 5.

www.murata-ps.com/support



ULE Series

Isolated, High Density, Eighth-Brick 1.25–20 Amp, DC-DC Converters

FUNCTIONAL SPECIFICATION NOTES

- 1. All models are tested and specified with external 1110 µF ceramic/tantalum output capacitors and a 22 µF external input capacitor. All capacitors are low ESR types. These capacitors are necessary to accommodate our test equipment and may not be required to achieve specified performance in your applications. The ULE-12/4.2 and ULE-24/3 modules require minimum load; all other models regulate within spec and are stable under no-load to full load conditions. General conditions for Specifications are +25 deg.C, VIN=nominal, Vour=nominal, full load. Adequate airflow must be supplied for extended testing under power.
- 2. Input Ripple Current is tested and specified over a 5 Hz to 20 MHz bandwidth. Input filtering is C_{IN=33} μ F tantalum, C_{BUS=220} μ F electrolytic, L_{BUS=12} μ H.
- 3. Note that Maximum Power Derating curves indicate an average current at nominal input voltage. At higher temperatures and/or lower airflow, the DC-DC converter will tolerate brief full current outputs if the total RMS current over time does not exceed the Derating curve. All Derating curves are presented at sea level altitude. Be aware of reduced power dissipation with increasing density altitude.
- Mean Time Before Failure is calculated using the Telcordia (Belcore) SR-332 Method 1, Case 3, ground fixed conditions, Tpcboard=+25°C, full output load, natural air convection.
- 5. The On/Off Control is normally controlled by a switch. But it may also be driven with external logic or by applying appropriate external voltages which are referenced to Input Common. The On/Off Control Input should use either an open collector or open drain transistor.
- Short circuit shutdown begins when the output voltage degrades approximately 2% from the selected setting.
- 7. The outputs are not intended to sink appreciable reverse current..
- 8. Output noise may be further reduced by adding an external filter. See I/O Filtering and Noise Reduction.

- 9. All models are fully operational and meet published specifications, including "cold start" at -40°C
- 10. Regulation specifications describe the deviation as the line input voltage or output load current is varied from a nominal midpoint value to either extreme.
- 11. Alternate pin length and/or other output voltages are available under special quantity order.
- 12. Electronic overvoltage shutdown is not included on 48V input models to comply with certain telecom reliability requirements. These requirements attempt continued operation despite input overvoltage. The converter is rated only to the maximum input voltage.
- 13. Do not exceed maximum power specifications when adjusting the output trim.
- 14. At zero output current, the output may contain low frequency components which exceed the ripple specification. The output may be operated indefinitely with no load.
- 15. If reverse polarity is accidentally applied to the input, a body diode will become forward biased and will conduct considerable current. To ensure reverse input protection with full output load, always connect an external input fuse in series with the +VIN input. Use approximately twice the full input current rating with nominal input voltage.
- Output current limit is non-latching. When the overcurrent fault is removed, the converter will immediately recover.
- 17. The Sense inputs are not included on lower current output models.
- 18. ULE-5/12-D24 lout=8A max. if VIN=19-20V.

DUVCICAL	CHARACTERISTICS AND SAFETY	
PHYSICAL		

PHISICAL CHARACTERISTICS AND SAFELT	
Outline dimensions	See mechanical specs (below)
Pin material	Copper alloy
Pin diameter	0.04/0.062" (1.016/1.524mm)
Pin finish	Nickel underplate with gold overplate
Weight	1 ounce (28 grams)
Electromagnetic interference (external filter required)	Designed to meet EN55022/CISPR22 with external filter
Safety	Certified to UL/cUL 60950-1, CSA-C22.2 No. 60950-1, IEC 60950-1, 2nd edition

Absolute Maximum Ratings


Input Voltage: Continuous:

Continuous:	
12 Volt input models	18 Volts
24 Volt input models	36 Volts
48 Volt input models	75 Volts
Transient (100 mSec. Max.)	
12 Volt input models	25 Volts
24 Volt input models	50 Volts
48 Volt input models	100 Volts
On/Off Control (pin 2)	See specifications
Input Reverse Polarity Protection	5 Amps, 10 sec. max.
Output Overvoltage Protection	Magnetic feedback. See note (7).
Output Current *	Current-limited. Devices can with stand sustained short circuit without damage.
Storage Temperature	-55 to +125°C.
Lead Temperature	Refer to solder profile.


These are stress ratings. Exposure of devices to greater than any of these conditions may adversely affect long-term reliability. Proper operation under conditions other than those listed in the Performance/Functional Specifications Table is not implied.

* The outputs are not intended to sink reverse current.


ULE Series



ULE Series




ULE Series




ULE Series

Isolated, High Density, Eighth-Brick 1.25–20 Amp, DC-DC Converters




www.murata-ps.com/support


ULE Series




ULE Series



ULE Series



ULE Series






ULE Series

Isolated, High Density, Eighth-Brick 1.25–20 Amp, DC-DC Converters

MECHANICAL SPECIFICATIONS


The ULE series consist of a number of unique high performance designs sharing similar mechanical outlines and pinouts. The internal architecture uses several different topologies including push-pull, flyback and others.

The block diagrams below are typical examples and are not intended to be exact representations. Some models do not include Sense and Trim pins. Please be aware that Murata Power Solutions may change these designs as needed.





ULE Series



ULE Series


Isolated, High Density, Eighth-Brick 1.25–20 Amp, DC-DC Converters

MECHANICAL SPECIFICATIONS

Through-hole Pin Changes for 2008

In 2008, for through-hole models only, Murata Power Solutions will gradually phase over to a different extruded 0.040" (1.02 mm) diameter pin design and elimination of the spacer standoffs on most models. *This will have no effect on installation, interchange-ability, electrical or mechanical specifications.* Any machined 0.062" (1.57 mm) diameter pin will transition to a straight wire 0.062" pin. The new 0.040" pins will insert properly to existing host PC boards and include an integral pin shoulder to form the mounting plane (Figure 1). There is no model number change, only a slightly changed appearance. Use the drawings and table below to identify the new pin design. And, surface mount ULEs are not affected.

All new production models are RoHS-6 compliant and always use the –C model number suffix. Older non-RoHS models are also being changed over to the new extruded pins; however non-RoHS models are not listed in this table.



The "integral" pin shoulder is formed as part of the extruded pin fabrication and replaces the plastic standoff spacer. The shoulder diameter is 0.072 + -0.002" and forms the mounting plane of the converter. The user should provide sufficient clearance for a 0.040" pin hole but well below the 0.072" shoulder diameter. This mounting plane avoids mechanical stress placed on the converter components. Do not place the components below the converter.

RoHS Models (-C)	0.040" Pin depth*
ULE-1.5/20-D24P-C	0.25 (6.4)
ULE-1.5/20-D48-C	0.25 (6.4)
ULE-1.8/20-D24-C	0.25 (6.4)
ULE-1.8/20-D48-C	0.25 (6.4)
ULE-2.5/20-D24-C	0.19 (4.8)
ULE-2.5/20-D48-C	0.19 (4.8)
ULE-3.3/20-D12-C	0.19 (4.8)
ULE-3.3/20-D24-C	0.25 (6.4)
ULE-3.3/20-D48N-C	0.25 (6.4)
ULE-3.3/20-D48P-C	0.19 (4.8)
ULE-5/10-D12-C	0.19 (4.8)
ULE-5/12-D24-C	0.19 (4.8)
ULE-5/12-D48-C	0.25 (6.4)
ULE-12/4.2-D24-C	0.25 (6.4)
ULE-12/4.2-D48-C	0.25 (6.4)
ULE-24/3-D48N-C	0.25 (6.4)
ULE-48/1.25-D48-C	0.25 (6.4)

Dimensions in inches (mm)

*The "0.040-inch pin depth" is the distance between the mounting plane of the ULE converter (at the pin shoulder) and the inserted tip of the pin. Therefore it is the length of pin which the host receiving PC board must accept. The ULE mounting plane interfaces to the top mounting surface (seating plane) of the user's PC board. The ULE mounting plane is established either by an integral pin shoulder (new) or a plastic standoff (older) but not both. Users should avoid placing components immediately below the converter.

The pin finish for all models remains as gold plate over nickel underplate. The pin material is a copper alloy. The pin finish is suitable for both leaded and lead-free solders.

Extruded 0.040-inch Pin Configurations


ULE Connections

The ULE series consists of several different PC board layouts sharing a common outline specification and overall size. This simplifies interchangeability in case the user needs different input or output specifications.


Certain models do not include Sense or Trim connections. All models include Remote On/Off control pins. Please refer to the following table:

Model Number	Vout (Volts)	lout (Amps, max.)	Number of Pins	On/Off pin?	Trim pin?	Sense pins?
ULE-1.5/20-D24P-C	1.5	20	8	yes	yes	yes
ULE-1.5/20-D48N-C	1.5	20	8	yes	yes	yes
ULE-1.8/20-D24P-C	1.8	20	8	yes	yes	yes
ULE-1.8/20-D48N-C	1.8	20	8	yes	yes	yes
ULE-2.5/20-D24P-C	2.5	20	8	yes	yes	yes
ULE-2.5/20-D48N-C	2.5	20	8	yes	yes	yes
ULE-3.3/20-D12P-C	3.3	20	8	yes	yes	yes
ULE-3.3/20-D24P-C	3.3	20	8	yes	yes	yes
ULE-3.3/20-D48N-C	3.3	20	8	yes	yes	yes
ULE-5/10-D12P-C	5	10	8	yes	yes	yes
ULE-5/12-D24P-C	5	12	8	yes	yes	yes
ULE-5/12-D48N-C	5	12	8	yes	yes	yes
ULE-12/4.2-D24P-C	12	4.2	6	yes	yes	no
ULE-12/4.2-D48N-C	12	4.2	6	yes	yes	no
ULE-24/3-D48N-C	24	3	5	yes	no	no
ULE-48/1.25-D48N-C	48	1.25	5	yes	no	no

ULE Series




ULE Series




ULE Series


Isolated, High Density, Eighth-Brick 1.25–20 Amp, DC-DC Converters

MECHANICAL SPECIFICATIONS, Continued



ULE THRU-HOLE SERIES M	AXIMUM HEIGHTS		
Model Family	Height (Max)	Model Family	Height (Max)
ULE-1.5/20-D24	0.404 [10.26]	*ULE-5/12-D24	0.405 [10.29]
ULE-1.5/20-D48	0.381 [9.68]	ULE-5/12-D48	0.377 [9.58]
ULE-1.8/20-D24	0.404 [10.26]	ULE-12/4.2-D24	0.377 [9.58]
ULE-1.8/20-D48	0.381 [9.68]	ULE-12/4.2-D48	0.377 [9.58]
ULE-2.5/20-D24*	0.409 [10.39]	ULE-24/3-D48	0.425 [10.80]
ULE-2.5/20-D48*	0.409 [10.39]	ULE-48/1.25-D48	0.448 [11.38]
ULE-3.3/20-D12*	0.409 [10.39]	ULE-68/1.5-D48	0.377 [9.58]
ULE-3.3/20-D24	0.381 [9.68]		
ULE-3.3/20-D48*	0.409 [10.39]		





ULE 'M' TYPE SMT (GULL WING) SERIES MAXIMUM HEIGHTS										
Model Family	Height (Max)	Model Family	Height (Max)							
ULE-1.5/20-D24 M	0.404 [10.26]	ULE-5/10-D12 M	0.400 [10.16]							
ULE-1.5/20-D48 M	0.404 [10.26]	ULE-5/12-D24 M	0.400 [10.16]							
ULE-1.8/20-D24 M	0.404 [10.26]	ULE-5/12-D48 M	0.400 [10.16]							
ULE-1.8/20-D48 M	0.404 [10.26]	ULE-12/4.2-D24 M	0.400 [10.16]							
ULE-2.5/20-D24 M	0.404 [10.26]	ULE-48/1.25-D48 M	0.446 [11.33]							
ULE-3.3/20-D12 M	0.404 [10.26]									
ULE-3.3/20-D24 M	0.404 [10.26]									
ULE-3.3/20-D48 M	0.404 [10.26]									

DIMENSIONS ARE IN INCHES [mm]

TOLERANCES: 2 PLACE ±0.02 3 PLACE ±0.010

ANGLES: ±1°

COMPONENTS SHOWN ARE FOR REFERENCE ONLY

ULE Series

Isolated, High Density, Eighth-Brick 1.25–20 Amp, DC-DC Converters

TECHNICAL NOTES

Input Fusing

Certain applications and/or safety agencies may require the installation of fuses at the inputs of power conversion components. Fuses should also be used if the possibility of sustained, non-current-limited, input-voltage polarity reversals exist. For Murata Power Solutions ULE 24-60 Watt DC-DC Converters, you should use fast-blow type fuses, installed in the ungrounded input supply line, with values no greater than the following.

Model	Fuse Values
12 Volt Input	10 Amps
24 Volt input	5 Amps
48 Volt Input	4 Amps

All relevant national and international safety standards and regulations must be observed by the installer. For system safety agency approvals, the converters must be installed in compliance with the requirements of the end-use safety standard.

Input Undervoltage Shutdown and Start-Up Threshold

Under normal start-up conditions, devices will not begin to regulate until the ramping-up input voltage exceeds the Start-Up Threshold Voltage. Once operating, devices will not turn off until the input voltage drops below the Undervoltage Shutdown limit. Subsequent re-start will not occur until the input is brought back up to the Start-Up Threshold. This built in hysteresis prevents any unstable on/off situations from occurring at a single input voltage.

Start-Up Time

The V_{IN} to V_{OUT} Start-Up Time is the interval of time between the point at which the ramping input voltage crosses the Start-Up Threshold and the fully loaded output voltage enters and remains within its specified accuracy band. Actual measured times will vary with input source impedance, external input/output capacitance, and load. The ULE Series implements a soft start circuit that limits the duty cycle of its PWM controller at power up, thereby limiting the input inrush current.

The On/Off Control to Vour start-up time assumes the converter has its nominal input voltage applied but is turned off via the On/Off Control pin. The specification defines the interval between the point at which the converter is turned on and the fully loaded output voltage enters and remains within its specified accuracy band. Similar to the V_{IN} to Vour start-up, the On/Off Control to Vour start-up time is also governed by the internal soft start circuitry and external load capacitance.

The difference in start up time from V_{IN} to V_{OUT} and from On/Off Control to V_{OUT} is therefore insignificant.

Input Source Impedance

ULE converters must be driven from a low ac-impedance input source. The DC-DC's performance and stability can be compromised by the use of highly inductive source impedances. The input circuit shown in Figure 2 is a practical solution that can be used to

minimize the effects of inductance in the input traces. For optimum performance, components should be mounted close to the DC-DC converter. If the application has a high source impedance, low VIN models can benefit of increased external input capacitance.

I/O Filtering, Input Ripple Current, and Output Noise

All models in the ULE 24-60 Watt DC-DC Converters are tested/specified for input reflected ripple current and output noise using the specified external input/output components/circuits and layout as shown in the following two figures.

External input capacitors (C_{IN} in Figure 2) serve primarily as energy-storage elements, minimizing line voltage variations caused by transient IR drops in conductors from backplane to the DC-DC. Input caps should be selected for bulk capacitance (at appropriate frequencies), low ESR, and high rms-ripple-current ratings. The switching nature of DC-DC converters requires that dc voltage sources have low ac impedance as highly inductive source impedance can affect system stability. In Figure 2, C_{BUS} and L_{BUS} simulate a typical dc voltage bus. Your specific system configuration may necessitate additional considerations.




Figure 2. Measuring Input Ripple Current


ULE Series

Isolated, High Density, Eighth-Brick 1.25–20 Amp, DC-DC Converters

In critical applications, output ripple/noise (also referred to as periodic and random deviations or PARD) may be reduced below specified limits using filtering techniques, the simplest of which is the installation of additional external output capacitors. These output caps function as true filter elements and should be selected for bulk capacitance, low ESR and appropriate frequency response. All external capacitors should have appropriate voltage ratings and be located as close to the converter as possible. Temperature variations for all relevant parameters should also be taken carefully into consideration. The most effective combination of external I/O capacitors will be a function of line voltage and source impedance, as well as particular load and layout conditions.

In Figure 3, the two copper strips simulate real-world pcb impedances between the power supply and its load. In order to minimize measurement errors, scope measurements should be made using BNC connectors, or the probe ground should be less than ½ inch and soldered directly to the fixture.

Figure 3. Measuring Output Ripple/Noise (PARD)



Floating Outputs

Since these are isolated DC-DC converters, their outputs are "floating" with respect to their input. Designers will normally use the –Output (pin 4) as the ground/return of the load circuit. You can, however, use the +Output (pin 8) as ground/return to effectively reverse the output polarity.

Minimum Output Loading Requirements

ULE converters employ a synchronous-rectifier design topology. The ULE-12/4.2 and ULE-24/3 modules require minimum load; all other models regulate within spec and are stable under no-load to full load conditions. Operation under no-load conditions however might slightly increase the output ripple and noise.

Thermal Shutdown

These ULE converters are equipped with thermal-shutdown circuitry. If environmental conditions cause the internal temperature of the DC-DC converter to rise above the designed operating temperature, a precision temperature sensor will power down the unit. When the internal temperature decreases below the threshold of the temperature sensor, the unit will self start. See Performance/Functional Specifications.

Output Overvoltage Protection

ULE output voltages are monitored for an overvoltage condition via magnetic feedback. The signal is coupled to the primary side and if the output voltage rises to a level which could be damaging to the load, the sensing circuitry will power down the PWM controller causing the output voltages to decrease. Following a time-out period the PWM will restart, causing the output voltages to ramp to their appropriate values. If the fault condition persists, and the output voltages again climb to excessive levels, the overvoltage circuitry will initiate another shutdown cycle. This on/off cycling is referred to as "hiccup" mode.

Contact Murata Power Solutions for an optional output overvoltage monitor circuit using a comparator which is optically coupled to the primary side thus allowing tighter and more precise control.

Current Limiting

As soon as the output current increases to 10% to 50% above its rated value, the DC-DC converter will go into a current-limiting mode. In this condition, the output voltage will decrease proportionately with increases in output current, thereby maintaining somewhat constant power dissipation. This is commonly referred to as power limiting. Current limit inception is defined as the point at which the full-power output voltage falls below the specified tolerance. See Performance/Functional Specifications. If the load current, being drawn from the converter, is significant enough, the unit will go into a short circuit condition as specified under "Performance."

Short Circuit Condition

When a converter is in current-limit mode, the output voltage will drop as the output current demand increases. If the output voltage drops too low, the magnetically coupled voltage used to develop primary side voltages will also drop, thereby shutting down the PWM controller. Following a time-out period, the PWM will restart causing the output voltages to begin ramping to their appropriate values. If the short-circuit condition persists, another shutdown cycle will be initiated. This on/off cycling is referred to as "hiccup" mode. The hiccup cycling reduces the average output current, thereby preventing internal temperatures from rising to excessive levels. The ULE is capable of enduring an indefinite short circuit output condition.

Features and Options

On/Off Control

The input-side, remote On/Off Control function can be ordered to operate with either polarity:

Standard models are equipped with Positive-polarity ("P" part-number suffix) and these devices are enabled when the On/Off Control is left open or is pulled high, as per Figure 4. Positive-polarity devices are disabled when the On/Off Control is pulled low. **Figure 4. Driving the Positive Polarity On/Off Control Pin**

Optional Negative-polarity devices ("N" suffix) are off when the On/Off Control is open (or pulled high), and on when the On/Off Control is pulled low with respect to $-V_{IN}$ as shown in Figure 5.


Figure 5. Driving the Negative Polarity On/Off Control Pin

Dynamic control of the remote on/off function is facilitated with a mechanical relay or an open-collector/open-drain drive circuit (optically isolated if appropriate). The drive circuit

ON/OFF CONTROL ON/OFF CONTROL CONTROL -VIN

should be able to sink appropriate current (see Performance Specs) when activated and withstand appropriate voltage when deactivated. Applying an external voltage to the On/ Off Control when no input power is

applied to the converter can cause permanent damage to the converter.



Trimming Output Voltage


ULE converters have a trim capability that allows users to adjust the output voltages as listed in the specifications. Adjustments to the output voltages can be accomplished via a trim pot (Figure 6) or a single fixed resistor as shown in Figures 7 and 8. A single fixed resistor can increase or decrease the output voltage depending on its connection. The resistor should be located close to the converter and have a TCR less than 100ppm/°C to minimize sensitivity to changes in temperature. If the trim function is not used, leave the trim pin floating.

Figure 6. Trim Connections Using A Trimpot

Figure 7. Trim Connections To Increase Output Voltages Using a Fixed Resistor Figure 8. Trim Connections To Decrease Output Voltages

A single resistor connected from the Trim to the +Output, or +Sense where applicable, will increase the output voltage in this configuration. A resistor connected from the Trim to the -Output, or -Sense where applicable, will decrease the output voltage in this configuration.

Trim adjustments greater than the specified range can have an adverse affect on




the converter's performance and are not recommended. Excessive voltage differences


-VOUT

-VIN

C



between Vour and Sense, in conjunction with trim adjustment of the output voltage, can



cause the overvoltage protection circuitry to activate (see Performance Specifications for overvoltage limits). Power derating is based on maximum output current and voltage at the converter's output pins. Use of trim and sense functions can cause output voltages to increase, thereby increasing output power beyond the converter's specified rating or cause output voltages to climb into the output overvoltage region. Therefore:

(Vout at pins) x (lout) <= rated output power

Note: Resistor values are in $k\Omega$. Adjustment accuracy is subject to resistor tolerances and factory-adjusted output accuracy. Vo = desired output voltage.

Remote Sense Note: The Sense and Vout lines are internally connected through low value resistors. Nevertheless, if the sense function is not used for remote regulation the user should connect the +Sense to +Vout and -Sense to -Vout at the DC-DC converter pins.

ULE series converters have a sense feature to provide point of use regulation, thereby overcoming moderate IR drops in pcb conductors or cabling. The remote sense lines carry very little current and therefore require minimal cross-sectional-area conductors.

ULE Series

Isolated, High Density, Eighth-Brick

		Trim Eq	uations
	Trim Up		Trim Down
		1.5 Volt	Output
$R_{T_{UP}}(k\Omega) =$	6.23(Vo - 1.226) Vo - 1.5	-10.2	$R_{T_{DOWN}}(k\Omega) = \frac{7.64}{1.5 - V_0} - 10.2$
		1.8 Volt	Output
$R_{T_{UP}}(k\Omega) =$	7.44(Vo - 1.226) Vo - 1.8	-10.2	$R_{T_{DOWN}}(k\Omega) = \frac{9.12}{1.8 - V_0} -10.2$
		2.5 Volt	Output
$R_{T_{UP}}(k\Omega) =$	10(Vo - 1.226) Vo - 2.5	-10.2	$R_{T_{\text{DOWN}}}(k\Omega) = \frac{12.26}{2.5 - \text{Vo}} - 10.2$
		3.3 Volt	Output
$R_{T_{UP}}(k\Omega) =$	<u>13.3(Vo - 1.226)</u> Vo - 3.3	-10.2	$R_{T_{DOWN}}(k\Omega) = \frac{16.31}{3.3 - V_0} - 10.2$
		5 Volt (Output
$R_{T_{UP}}(k\Omega) =$	20.4(Vo - 1.226) Vo - 5	-10.2	$R_{T_{\text{DOWN}}}(k\Omega) = \frac{25.01}{5 - V_0} - 10.2$
		12 Volt	Output
$R_{T_{UP}}(k\Omega) =$	49.6(Vo - 1.226) Vo - 12	-10.2	$R_{T_{\text{DOWN}}}(k\Omega) = \frac{60.45}{12 - V_0} -10.2$
		15 Volt	Output
$R_{T_{UP}}(k\Omega) =$	62.9(Vo - 1.226) Vo - 15	-10.2	$R_{T_{\text{DOWN}}}(k\Omega) = \frac{76.56}{15 - V_0} - 10.2$

The sense lines are used by the feedback control-loop to regulate the output. As such, they are not low impedance points and must be treated with care in layouts and cabling.

Soldering Guidelines

Murata Power Solutions recommends the specifications below when installing these converters. These specifications vary depending on the solder type. Exceeding these specifications may cause damage to the product. Be cautious when there is high atmospheric humidity. We strongly recommend a mild pre-bake (100 °C. for 30 minutes). Your production environment may differ therefore please thoroughly review these guidelines with your process engineers.

Wave Solder Operations for through-hole mounted products (THMT)

ULE Series

Isolated, High Density, Eighth-Brick 1.25–20 Amp, DC-DC Converters

Sense lines on a pcb should be run adjacent to dc signals, preferably ground. In cables and discrete wiring applications, twisted pair or other techniques should be implemented.

ULE series converters will compensate for drops between the output voltage at the DC-DC and the sense voltage at the DC-DC provided that:


 $[Vout(+) - Vout(-)] - [Sense(+) - Sense(-)] \le 5\%$ Vout

Output overvoltage protection is monitored at the output voltage pin, not the Sense pin. Therefore, excessive voltage differences between Vour and Sense in conjunction with trim adjustment of the output voltage can cause the overvoltage protection circuitry to activate (see Performance Specifications for overvoltage limits). Power derating is based on maximum output current and voltage at the converter's output pins. Use of trim and sense functions can cause output voltages to increase thereby increasing output power beyond the ULE's specified rating or cause output voltages to climb into the output overvoltage region. Also, the use of Trim Up and Sense combined may not exceed +10% of Vour. Therefore, the designer must ensure:

Surface-Mount Package ("M" suffix)

Murata Power Solutions' ULE series SMT DC-DC converters are the only higher-power DC-DCs that can be automatically "pick-and-placed" using standard vacuum-pickup equipment and subsequently reflowed using high-temperature, lead-free solder.

Virtually all SMT DC-DCs today are unprotected "open-frame" devices assembled by their vendors with high-temperature solder (usually Sn96.5/Ag3.5 with a melting point +221°C) so that you may attach them to your board using low-temperature solder (usually Sn63/Pb37 with a melting point of +183°C). Conceptually straightforward, this "stepped" solder approach has its limitations . . . and is clearly out of step with an industry trending toward the broad use of lead-free solders. Users need to experiment



and develop reflow profiles that ensure the components on their DC-DC never exceed

			······,	
	For Sn/Pb l	based solders:		
115° C.	Maximum Pre	eheat Temperature	105° C.	
270° C.	Maximum Po	it Temperature	250° C.	
7 seconds	Maximum Sc	lder Dwell Time	6 seconds	
is for surfac	e-mount pr	oducts (SMT)		
		For Sn/Pb base	d solders:	
Less than 1 °C.	per second	Preheat Temperati	ure	Less than 1 °C. per second
45 to 75 secon	ds	Time over Liquidu	S	60 to 75 seconds
260 °C.		Maximum Peak Te	emperature	235 ℃.
Less than 3 °C.	per second	Cooling Rate		Less than 3 °C. per second
	115° C. 270° C. 7 seconds s for surfac Less than 1 °C. 45 to 75 secon 260 °C.	For Sn/Pb 1 115° C. Maximum Pr 270° C. Maximum Pc 7 seconds Maximum Sc 15 for surface-mount pr Less than 1 °C. per second 45 to 75 seconds	For Sn/Pb based solders: 115° C. Maximum Preheat Temperature 270° C. Maximum Pot Temperature 7 seconds Maximum Solder Dwell Time Is for surface-mount products (SMT) For Sn/Pb base Less than 1 °C. per second Preheat Temperature 45 to 75 seconds Time over Liquidu 260 °C. Maximum Pathet Temperature	115° C. Maximum Preheat Temperature 105° C. 270° C. Maximum Pot Temperature 250° C. 7 seconds Maximum Solder Dwell Time 6 seconds For Surface-mount products (SMT) For Sn/Pb based solders: Less than 1 °C. per second Preheat Temperature 45 to 75 seconds Time over Liquidus 260 °C. Maximum Peat Temperature

www.murata-ps.com/support

ULE Series

Isolated, High Density, Eighth-Brick 1.25–20 Amp, DC-DC Converters

215-216°C. If those components get too hot, "double-reflow" could compromise the reliability of their solder joints. Virtually all these devices demand you "cool down" the Sn63 profile you are likely using today.

Murata Power Solutions is not exempted from the Laws of Physics. And we do not have magic solders no one else has. We do have a simple and practical, straightforward approach that works. We assemble our SMT DC-DCs on a thermally-stable plastic lead-frame (nylon 46, UL94V-0 flammability rated) using a high temperature lead-free solder. The lead-frame ensures coplanarity (to within 0.004 in.) of the unit's tin-plated (150 microinches) copper leads and also supports a removable heat shield.

The disposable heat shield, with a cutaway exposing the package leads, provides thermal insulation to internal components during reflow and doubles as the vacuum pick-up location. The insulation properties of the heat shield are so effective that temperature differentials as high as 50°C develop inside-to-outside the shield. Oven temperature profiles with peaks of 250-260°C and dwell times exceeding 2 minutes above 221°C are easily achieved. Murata Power Solutions' new-generation SMT units are shipped in stackable, JEDEC-style plastic trays (Figure 13).

Automated Assembly Production Notes

Murata Power Solutions' new high-efficiency DC-DC converters are designed for modern surface-mount technology (SMT) automated assembly using screened solder paste, "pick and place" component positioning and forced hot air reflow oven soldering. If you are new to SMT techniques and have a volume application, these features save time, cost and improve manufacturing efficiency. Murata Power Solutions' DC-DC assembly operations themselves make extensive use of such techniques.

Even if you have previous SMT experience, you should read the sections below on solder reflow profiles and heat shields. This information is not intended to replace the documentation for your SMT system. We assume that you are already experienced with all the components of your SMT system.

This section will discuss several SMT issues, including:

- I/O Mechanical Configuration
- Part Handling and Supply
- Printed Circuit Board (pcb) Mounting
- Soldering using Reflow Technology
- Temperature Profiling
- Heat Shields and Removal

Mechanical Configuration of Input/Output Connections

These new converters are supplied either using traditional through-hole pins or SMT leads. (Note that some models are offered only with lead mounting). The pin options insert into plated-through holes in the host pcb. Be aware that some heat dissipation is carried off by either the pins or leads. The Derating Curves assume that some additional pad area is available on your host pcb to absorb the heat.

The lead option uses either short tabs in "gullwing" style or standoff leads under the converter. The gullwing leads typically are copper alloy with 150 microinches of tin plating. Solder paste (typically 0.008" to 0.009" thick) is applied to the host pcb using a solder mask pressure screening technique and the board is heated and cooled long enough for the solder to reflow and adhere to both the host pads and the converter's mounting leads.

After such mounting, the entire mechanical mounting load is carried by the solder. Obviously the converters must be accurately positioned all during the solder reflow period. Where solder surface tension is sufficient to force tiny components into position, these larger converters may not move and must be accurately positioned by your SMT system.

Part Handling and Supply

SMT eighth- and quarter-brick DC-DC converters (plus installed heat shields if used) are supplied in JEDEC-standard 5.35" by 12.4" waffle trays which are compatible with the feeders on industry-standard pick-and-place machines.

Since the converters are larger and heavier than many other components, make sure your system can reliably remove the units from their trays, move them to the host pcb and accurately position them. The plastic heat shield (Figure 10) doubles as a vacuum pickup area.

Figure 10. ULE SMT DC-DC with Disposable Heat Shield

Solder Balls

ULE converters are thoroughly inspected according to military standard J-STD-001B for the presence of solder balls. The specification allows small solder balls as long as they are rigidly attached and do not compromise the spacing and clearance requirements needed to maintain electrical isolation.

Figure 11. Recommended Solder Profile (When the Heat-shield temperature exceeds +250°C, the air within is 50°C cooler)

Post Reflow Procedures


After successful solder reflow, be sure to completely clean and dry your assembled boards using a recommended wash solution and dryer. Failure to remove all flux may cause long term deterioration of on-board conductors and components. And, traces of contaminants which are not removed may reduce isolation voltages or risk a safety hazard. Be aware that low remaining concentrations of flux or other assembly compounds can be very difficult to detect by eye.



Pick and Place pcb Mounting

The main issues here are pad area, orientation, positioning accuracy, vacuum pickup and coplanarity. Murata Power Solutions recommends that pcb pads to interface with the DC-DC converter should be sized as shown in the diagram below. The pads footprint accommodates the positioning accuracy of your SMT equipment and manufactured tolerances of the DC-DC mounting leads.

Figure 12. Recommended SMT Mounting Pad Dimensions




Orientation: When loaded into JEDEC trays, the converters are oriented in the same direction. See the diagram below. For the ULE series, a notch is placed on the top of the case (on the removal tabs) to indicate the pin 1 position. You should visually inspect the tray to be sure of this orientation.

Most pick-and-place automatic assembly systems use a camera which must be trained to recognize the orientation of the converter before it is assembled onto the host PC board. This "training" locates and identifies prominent, dimensionally stable landmarks such as the board corners or fiducial marks.

On the bottom of the converter, the ULE series include optical fiducial marks viewable by your SMT imaging system. Observing from the bottom, your SMT imaging camera should find these marks to identify the converter and verify pin 1. On most pick-and-place systems, during head transit, the imaging system will automatically fine tune the end mounting position of the converter using image comparisons from these fiducials or other reference marks you have chosen.

The fiducial marks are placed fairly close together because many imaging systems have a one inch or less observing area since most SMT parts are considerably smaller



than these converters. You may prefer to train your imaging system to use a corner of

Isolated, High Density, Eighth-Brick 1.25–20 Amp, DC-DC Converters

ULE Series

the converter or an I/O lead.

The fiducial marks will remain identical within any date code lot of converters. In the remote possibility that the fiducials may have changed position with a PC board revision, you should not mix different date lots on any one production assembly session. In addition, to avoid non-recognition or misplacement of the converter, retrain your imaging system at the beginning of each series of assembly sessions. There may be tiny variations in the absolute position from unit to unit.

If you use a camera above the pcb after placement on the solder paste, do not rely on the inkjet marking on the heat shield to verify proper orientation. Use the pin 1 notch instead.

Coplanarity: Murata Power Solutions manufactures these converters with very flat mounting leads (see coplanarity specs) however your host pcb must also be flat for a successful mounting. Be aware of possible warping of the pcb under heat gradients and/ or humidity conditions. The solder paste will tolerate a small amount of mismatch and will tend to "wet" the entire pad area by capillary action if the temperatures are correct.

Vacuum Pickup: Select the vacuum collet on your SMT placement system for the weight and size of the DC-DC converter. Note that units with heatsinks are slightly heavier. Tests at Murata Power Solutions have shown that excellent acceleration and transit head speed are available for these converters if the collet size is proper and the vacuum is sufficient. When positioning the vacuum collet, use the geometric center of the heat shield as the pickup area since the center of gravity is very close.

Soldering

Reflow technology works well for small parts. However, larger components such as these DC-DC's with higher thermal mass may require additional reflow time (but not enough to disturb smaller parts also being reflowed concurrently with the DC-DC). When this is combined with higher temperature lead-free solders (or solders with reduced heavy metals), there is increased risk of reheating components inside the DC-DC enough so that they either change positions (and possibly stop functioning) or the components are damaged by the heat.

For these reasons, Murata Power Solutions developed disposable heat shields using high temperature plastic. The DC-DC is installed and reflowed with the shield in place. After successful reflow and cooling, and before washing, the heat shield should be removed.

Temperature Profiling

We wish to ramp the temperature up and down to successfully reflow the solder without heat damage. Each reflow oven, humidity conditions, solder paste type, oven feed rate, and the number of heat zones all require a different profile. Therefore you may have to experiment.

Since these converters are constructed using high temperature solders, there will be no heat problems on your host pcb using traditional solder with 63% lead and 37% tin with a melting point of +183°C. Device lead temperature must remain below 230°C for less than 75 seconds, assuming that the heat shield is in place. Murata Power Solutions uses a 216°C melt lead-free tin/silver/copper alloy to assemble these converters.

There are several lead-free solders suitable for your host pcb depending on your SMT system and whatever local certification and environmental regulations you must observe. Contact Murata Power Solutions if you need specific advice.

ULE Series


Isolated, High Density, Eighth-Brick 1.25–20 Amp, DC-DC Converters

Heat Shield

Careful thermocouple testing has shown that the interior of the DC-DC under the heat shield is tens of degrees cooler than the outside ambient temperature for typical reflow profiles. This protects internal components and limits the amount of reflow where it is not desired. The heat shield also includes marking for product identification and a date/ lot code.

On ULE models, the heat shield is attached to the converter using molded plastic pins on the heat shield interior which insert into recessed dimples in the pinframe. An extra molded pin on the heat shield at the pin 1 location (and corresponding notch on the pcb) can only be installed one way properly on the pinframe. If the shield accidentally comes loose, it may be reinstalled by aligning the pins and dimples.

To remove the shield from the converter, after successful mounting and cooling, squeeze the heat shield ears inward toward the converter body and pull the shield upwards. Discard or recycle the shield. If you are using a flux wash cycle, remove the heat shield before washing to avoid coming loose inside the washer.



ULE Series

Isolated, High Density, Eighth-Brick 1.25–20 Amp, DC-DC Converters




Figure 14. Vertical Wind Tunnel

Vertical Wind Tunnel

Murata Power Solutions employs a computer controlled custom-designed closed loop vertical wind tunnel, infrared video camera system, and test instrumentation for accurate airflow and heat dissipation analysis of power products. The system includes a precision low flow-rate anemometer, variable speed fan, power supply input and load controls, temperature gauges, and adjustable heating element.

The IR camera monitors the thermal performance of the Unit Under Test (UUT) under static steady-state conditions. A special optical port is used which is transparent to infrared wavelengths.

Both through-hole and surface mount converters are soldered down to a 10" x 10" host carrier board for realistic heat absorption and spreading. Both longitudinal and transverse airflow studies are possible by rotation of this carrier board since there are often significant differences in the heat dissipation in the two airflow directions. The combination of adjustable airflow, adjustable ambient heat, and adjustable Input/Output currents and voltages mean that a very wide range of measurement conditions can be studied.

The collimator reduces the amount of turbulence adjacent to the UUT by minimizing airflow turbulence. Such turbulence influences the effective heat transfer characteristics and gives false readings. Excess turbulence removes more heat from some surfaces and less heat from others, possibly causing uneven overheating.

Both sides of the UUT are studied since there are different thermal gradients on each side. The adjustable heating element and fan, built-in temperature gauges, and no-contact IR camera mean that power supplies are tested in real-world conditions.

Murata Power Solutions, Inc. 129 Flanders Rd. Westborough, Ma 01581, USA. ISO 9001 and 14001 REGISTERED



This product is subject to the following <u>operating requirements</u> and the <u>Life and Safety Critical Application Sales Policy</u>: Refer to: <u>https://www.murata-ps.com/requirements/</u>

Murata Power Solutions, Inc. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infinge upon existing or future patent rights. The descriptions contained herein do not imply the granting of licenses to make, use, or sell equipment constructed in accordance therewith. Specifications are subject to change without notice.

ULE Series

Isolated, High Density, Eighth-Brick 1.25–20 Amp, DC-DC Converters

MODEL NUMBER	PRODUCT STATUS	LTB DATE
ULE-1.2/30-D48N-C	Discontinued	10/9/2014
ULE-1.2/30-D48P-C	Discontinued	10/9/2014
ULE-1.5/20-D24N-C	Discontinued	12/9/2014
ULE-1.5/20-D24NM-C	Discontinued	12/9/2014
ULE-1.5/20-D24P-C	Discontinued	10/9/2014
ULE-1.5/20-D24PM-C	Discontinued	12/9/2014
ULE-1.5/20-D48N-C	Discontinued	12/9/2014
ULE-1.5/20-D48NM-C	Discontinued	12/9/2014
ULE-1.5/20-D48P-C	Discontinued	12/9/2014
ULE-1.5/20-D48PM-C	Discontinued	12/9/2014
ULE-1.8/20-D24N-C	Discontinued	12/9/2014
ULE-1.8/20-D24NM-C	Discontinued	12/9/2014
ULE-1.8/20-D24P-C	Discontinued	12/9/2014
ULE-1.8/20-D24PM-C	Discontinued	12/9/2014
ULE-1.8/20-D48N-C	Discontinued	12/9/2014
ULE-1.8/20-D48NL2-C	Discontinued	12/9/2014
ULE-1.8/20-D48NM-C	Discontinued	12/9/2014
ULE-1.8/20-D48P-C	Discontinued	12/9/2014
ULE-1.8/20-D48PM-C	Discontinued	12/9/2014
ULE-12/4.2-D24N-C	Discontinued	3/31/2022
ULE-12/4.2-D24NL1-C	Discontinued	3/31/2022
ULE-12/4.2-D24NL2-C	Discontinued	3/31/2022
ULE-12/4.2-D24NL5-C	Discontinued	3/31/2022
ULE-12/4.2-D24NM-C	Discontinued	12/9/2014
ULE-12/4.2-D24P-C	Discontinued	3/31/2022
ULE-12/4.2-D24PL1-C	Discontinued	3/31/2022
ULE-12/4.2-D24PM-C	Discontinued	12/9/2014
ULE-12/4.2-D48N-C	Discontinued	2/21/2018
ULE-12/4.2-D48NL2-C	Discontinued	9/18/2017
ULE-12/4.2-D48NM-C	Discontinued	12/9/2014
ULE-12/4.2-D48P-C	Discontinued	2/21/2018
ULE-12/4.2-D48PL1-C	Discontinued	9/18/2017
ULE-12/4.2-D48PL2-C	Discontinued	9/18/2017
ULE-12/4.2-D48PM-C	Discontinued	12/9/2014
ULE-2.5/20-D24N-C	Discontinued	12/9/2014
ULE-2.5/20-D24NM-C	Discontinued	3/31/2022
ULE-2.5/20-D24P-C	In Production	N/A
ULE-2.5/20-D24PM-C	Discontinued	12/9/2014
ULE-2.5/20-D48N-C	Discontinued	12/9/2014
ULE-2.5/20-D48NM-C	Discontinued	2/5/2015
ULE-2.5/20-D48P-C	Discontinued	2/5/2015
ULE-2.5/20-D48PM-C	Discontinued	2/5/2015

Under Development	Products under development. Listed product specifications are subject to change without prior notice. Please contact us for sample availability and mass production schedule.
In Production	Product is in mass production.
NRND	Not recommended for new design.
To be discontinued	We are planning to discontinue production of this item. 'Last Time Buy' date or Discontinuation date may be shown on our web site. Before these dates, please contact us with your requirements
Discontinued	Production of this product has stopped.
Recommended	Murata particularly recommends this product for reasons of size and performance. Please contact Murata regarding pricing and delivery.
New	This is a new product. Please contact Murata regarding pricing and delivery.



This product is subject to the following <u>operating requirements</u> and the <u>Life and Safety Critical Application Sales Policy</u>: Refer to: <u>https://www.murata-ps.com/requirements/</u>

Murata Power Solutions, Inc. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not imply the granting of licenses to make, use, or sell equipment constructed in accordance therewith. Specifications are subject to change without notice. © 2022 Murata Power Solutions, Incc.

129 Flanders Rd. Westborough, Ma 01581, USA.

Murata Power Solutions, Inc.

ISO 9001 and 14001 REGISTERED

ULE Series

Isolated, High Density, Eighth-Brick 1.25–20 Amp, DC-DC Converters

ULE-24/3-D48N-C	Discontinued	2/21/2018
ULE-24/3-D48NL2-C	Discontinued	9/18/2017
ULE-24/3-D48NM-C	Discontinued	2/21/2018
ULE-24/3-D48P-C	Discontinued	2/21/2018
ULE-24/3-D48PM-C	Discontinued	2/21/2018
ULE-3.3/20-D12N-C	Discontinued	3/31/2022
ULE-3.3/20-D12NM-C	Discontinued	2/5/2015
ULE-3.3/20-D12P-C	Discontinued	3/31/2022
ULE-3.3/20-D12PM-C	Discontinued	2/5/2015
ULE-3.3/20-D24N-C	Discontinued	3/31/2022
ULE-3.3/20-D24NM-C	Discontinued	3/31/2022
ULE-3.3/20-D24P-C	Discontinued	3/31/2022
ULE-3.3/20-D24PM-C	Discontinued	2/5/2015
ULE-3.3/20-D48N-C	Discontinued	2/27/2018
ULE-3.3/20-D48NL1-C	Discontinued	9/18/2017
ULE-3.3/20-D48NL2-C	Discontinued	9/18/2017
ULE-3.3/20-D48NM-C	Discontinued	2/5/2015
ULE-3.3/20-D48P-C	Discontinued	2/27/2018
ULE-3.3/20-D48PL1-C	Discontinued	9/18/2017
ULE-3.3/20-D48PL2-C	Discontinued	9/18/2017
ULE-3.3/20-D48PM-C	Discontinued	2/5/2015
ULE-48/1.25-D48N-C	To Be Discontinued	3/31/2023
ULE-48/1.25-D48NM-C	Discontinued	2/5/2015
ULE-48/1.25-D48P-C	Discontinued	3/31/2022
ULE-48/1.25-D48PM-C	Discontinued	2/5/2015
ULE-5/10-D12N-C	Discontinued	2/5/2015
ULE-5/10-D12NM-C	Discontinued	2/5/2015
ULE-5/10-D12P-C	Discontinued	2/5/2015
ULE-5/10-D12PM-C	Discontinued	2/5/2015
ULE-5/12-D24N-C	Discontinued	3/31/2022
ULE-5/12-D24NL1-C	Discontinued	3/31/2022
ULE-5/12-D24NM-C	Discontinued	3/31/2022
ULE-5/12-D24P-C	Discontinued	3/31/2022
ULE-5/12-D24PL1-C	Discontinued	3/31/2022
ULE-5/12-D24PM-C	Discontinued	4/5/2016
ULE-5/12-D48N-C	Discontinued	2/20/2018
ULE-5/12-D48NL1-C	Discontinued	2/20/2018
ULE-5/12-D48NL2-C	Discontinued	2/20/2018
OLL OF IL DHONILLO	Discontinued	
ULE-5/12-D48NM-C	Discontinued	2/5/2015

Under Development	Products under development. Listed product specifications are subject to change without prior notice. Please contact us for sample availability and mass production schedule.
In Production	Product is in mass production.
NRND	Not recommended for new design.
To be discontinued	We are planning to discontinue production of this item. 'Last Time Buy' date or Discontinuation date may be shown on our web site. Before these dates, please contact us with your requirements
Discontinued	Production of this product has stopped.
Recommended	Murata particularly recommends this product for reasons of size and performance. Please contact Murata regarding pricing and delivery.
New	This is a new product. Please contact Murata regarding pricing and delivery.

Murata Power Solutions, Inc. 129 Flanders Rd. Westborough, Ma 01581, USA. ISO 9001 and 14001 REGISTERED



This product is subject to the following <u>operating requirements</u> and the <u>Life and Safety Critical Application Sales Policy</u>: Refer to: <u>https://www.murata-ps.com/requirements/</u>

Murata Power Solutions, Inc. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not imply the granting of locenses to make, use, or sell equipment constructed in accordance therewith. Specifications are subject to change without notice. © 2022 Murata Power Solutions, Inc.