



### **FEATURES**

- Patent protected
- Optimised bipolar output voltages for IGBT/ SiC & MOSFET gate drives
- Reinforced insulation to UL62368 recognition pending
- ANSI/AAMI ES60601-1 recognition pending
- 5.7kVDC isolation test voltage 'Hi Pot Test'
- Ultra low isolation capacitance
- Surface mount package style
- 12V & 15V inputs
- +15V/-9V, +15V/-5V & +20V/-5V outputs
- Operation up to 105°C (with derating)
- Short circuit protection
- Characterised CMTI >200kV/µS
- Continuous barrier withstand voltage 2.5kV
- Characterised partial discharge performance

### **PRODUCT OVERVIEW**

The MGJ2 series of DC-DC converters is ideal for powering 'high side' and 'low side' gate drive circuits for IGBTs/SiC and MOSFETs in bridge circuits. A choice of asymmetric output voltages allows optimum drive levels for best system efficiency. The MGJ2 series is characterised for high isolation requirements commonly seen in bridge circuits used in motor drives and inverters, while the MGJ2 industrial grade temperature rating and construction gives long service life and reliability.



www.murata.com

# **MGJ2 Surface Mount Series**

5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters

SELECTION GUIDE											
Order Code <sup>1</sup>	Nominal Input Voltage	Output Voltage 1	Output Voltage 2	Output Current 1	Output Current 2	Input Current at Rated Load	Load Regulation (Typ)	Load Regulation L Tro (Max)	Load Regulation (Typ)	Load Regulation 5 (Max)	
	V	V	V		mA			9	%		
MGJ2D121505MPC	12	15	-5	100	100	210	9	14	7	12	
MGJ2D121509MPC	12	15	-9	80	80	210	8	13	7	12	
MGJ2D122005MPC	12	20	-5	80	80	215	7.5	12	6.5	11	
MGJ2D151505MPC	15	15	-5	100	100	170	7	11	5.5	9	
MGJ2D151509MPC	15	15	-9	80	80	170	6	10	5	9	
MGJ2D152005MPC	15	20	-5	80	80	170	6	9	5	8	

SELECTION GUIDE	(Continued)						
Order Code <sup>1</sup>	Ripple & Noise (Typ) <sup>3</sup>	Ripple & Noise (Max) <sup>3</sup>	Efficiency (Min)	Efficiency (Typ)	Isolation Capacitance	MTT E2	
	mV	р-р	0	%	pF	MIL.	
	IIIV	h-h	70		рі	kHrs	
MGJ2D121505MPC	35	55	73	77	3	1411	5
MGJ2D121509MPC	20	45	72	77	3	1548	4
MGJ2D122005MPC	20	45	71	75	3	1217	4
MGJ2D151505MPC	30	65	72	77	3	1224	5
MGJ2D151509MPC	20	45	73	77	3	1332	5

45

MGJ2D152005MPC

20

INPUT CHARACTERISTICS							
Parameter	Conditions	Min.	Тур.	Max.	Units		
Voltage range	Continuous operation, 12V input types	10.8	12	13.2	v		
	Continuous operation, 15V input types	13.5	15	16.5	V		
Input short circuit current I <sub>sc</sub>	12V input types		90				
	15V input types		55		mA		
Input reflected ripple			10		mA		
			10		р-р		

71

76

3

OUTPUT CHARACTERISTICS						
Parameter	Conditions	Min.	Тур.	Max.	Units	
Rated power	T <sub>A</sub> =-40°C to 85°C			2.0	W	
Voltage set point accuracy	See tolerance envelopes					
Line regulation	MGJ2D121505MPC		1.1	1.25		
	MGJ2D121509MPC		1.1	1.3	%/%	
	All others		1.1	1.2		

1. Components are supplied in tape and reel packaging, please refer to package specification section. Orderable part numbers are MGJ2DXXXXXMPC-R7 (80 pieces per reel), or MGJ2DXXXXXMPC-R13 (400 pieces per reel).

2. Calculated using MIL-HDBK-217 FN2 and Telcordia SR-332 calculation model with nominal input voltage at full load. 3. See ripple & noise test method.

All specifications typical at T<sub>A</sub>=25°C, nominal input voltage and rated output current unless otherwise specified

Tel.

52799 47759

42399

56429

56879

43521

1108

# **MGJ2 Surface Mount Series**

### 5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters

Parameter		Conditions		Min.	Тур.	Max.	Units
Isolation test voltage		Production tested for 1 second	t	5700			VDO
		Qualification tested for 1 minute		5700			VDC
Resistance		Viso= 1000VDC	1			GΩ	
Continuous barrier v	ontinuous barrier withstand voltage Non-safety barrier application					2500	V
Cofoty standard	UL62368-1	Reinforced	Crosses and closresses 0mm			250	VAC
Safety standard <sup>1</sup>	ANSI/AAMI ES60601-1	2 MOPP	Creepage and clearance 9mm			250	VAC

GENERAL CHARACTERISTICS					
Parameter	Conditions	Min.	Тур.	Max.	Units
Switching frequency	12V input type		110		kHz
	15V input type		100		КПZ

TEMPERATURE CHARACTER	ISTICS				
Parameter	Conditions	Min.	Тур.	Max.	Units
Specification	All output types (see derating curves)	-40		105	
Storage		-40		125	
	12V input types		27		°C
Product temperature above ambient	MGJ2D122005MPC & MGJ2D152005MPC		32		
	15V input types		25		
Cooling	Free air convection				

ABSOLUTE MAXIMUM RATINGS	
Short-circuit protection	Continuous
Input voltage VIN, MGJ2D12	15V
Input voltage VIN, MGJ2D15	18V

1. UL62368-1 and ANSI/AAMI ES60601-1 recognition is currently pending.

# **MGJ2 Surface Mount Series**

### 5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters

#### **TECHNICAL NOTES**

#### **ISOLATION VOLTAGE**

'Hi Pot Test', 'Flash Tested', 'Withstand Voltage', 'Proof Voltage', 'Dielectric Withstand Voltage' & 'Isolation Test Voltage' are all terms that relate to the same thing, a test voltage, applied for a specified time, across a component designed to provide electrical isolation, to verify the integrity of that isolation.

Murata Power Solutions MGJ2 series of DC-DC converters are all 100% production tested at 5.7kVDC for 1 second and have been qualification tested at 5.7kVDC for 1 minute.

A question commonly asked is, "What is the continuous voltage that can be applied across the part in normal operation?"

When the insulation in the MGJ2 series is not used as a safety barrier , i.e. provides functional isolation only, continuous or switched voltages across the barrier up to 2.5kV are sustainable. Long term reliability testing at these voltages continues. Peak Inception voltages measured were in excess of 2.5kV when testing for partial discharge in accordance with IEC 60270. Please contact Murata for further information.

The MGJ2 series is pending recognition by Underwriters Laboratory to 250VAC Reinforced Insulation, please see safety approval section below.

#### **REPEATED HIGH-VOLTAGE ISOLATION TESTING**

It is well known that repeated high-voltage isolation testing of a barrier component can actually degrade isolation capability, to a lesser or greater degree depending on materials, construction and environment. We therefore strongly advise against repeated high voltage isolation testing, but if it is absolutely required, that the voltage be reduced by 20% from specified test voltage.

#### SAFETY APPROVAL

#### ANSI/AAMI ES60601-1

The MGJ2 series is pending recognition by Underwriters Laboratory (UL) to ANSI/AAMI ES60601-1 and provides 2 MOPP (Means Of Patient Protection) based upon a working voltage of 250VAC max, between Primary and Secondary.

#### UL62368-1

The MGJ2 series is pending recognition by Underwriters Laboratory (UL) to UL62368-1 for reinforced insulation to a working voltage of 250VAC.

Creepage and clearance 9mm. Working altitude 5000m

#### **RoHS COMPLIANCE AND MSL INFORMATION**



This series is compatible with Pb-Free soldering systems and is also backward compatible with Sn/Pb soldering systems. The series can be soldered in accordance with J-STD-020. Please refer to <u>application notes</u> for further information. This series have a classification temperature of 260°C and moisture sensitivity level 2. The termination finish on this product is Gold with plating thickness 0.12 microns.


# **MGJ2 Surface Mount Series**

### 5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters

### ENVIRONMENTAL VALIDATION TESTING

0	e been conducted on this product series, as p Aurata if further information about the tests is	part of our design verification process. The datasheet characteristics specify user operating conditions for this s required.
Test	Standard	Condition
Temperature cycling	JEDEC JESD22-A104	500 cycles in a dual zone chamber from -40 (+5/-10)°C to 105 (+10/-5)°C. 15mins dwell at each (inclusive of ramps). 2 cycles per hour.
Humidity (unbiased)	JEDEC JESD22-A118	130±2°C, 85±5% R.H. for 96 (-0/+2) hours
Storage life	JEDEC JESD22-A103, Condition A	125°C +10/-0°C for ≥1000 hours
Vibration	BS EN 61373 with respect to BS EN 60068-2-64, Test Fh Category 1 Class B	5 – 150Hz. Level at each axis – Vertical, Traverse and Longitudinal: 5.72m/s2 rms. 5 hours in each axis. Crest factor: 3 Sigma. Device is secured via the pads.
Shock	BS EN 61373: Category 1, Class B	Test is 30ms duration, 3 shocks in each sense of 3 mutually perpendicular axes (18 shocks total). Level at each axis: Vertical, Traverse and Longitudinal: 50m/s2. Device is secured via the pads.
Solvent cleaning	Resistance to cleaning agents	Solvent – Novec 71IPA & Topklean EL-20A. Pulsed ultrasonic immersion 45°C - 65°C
Solvent resistance	MIL-STD-883 Method 2015	The parts and the bristle portion of the brush are immersed in Isopropanol for a minimum of 1 minute. The parts are brushed 3 times, after the third time the parts are blown dry and inspected.

#### PART NUMBER STRUCTURE



### MGJ2 Surface Mount Series

5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters


### CHARACTERISATION TEST METHODS

#### **Ripple & Noise Characterisation Method**

Ripple and noise measurements are performed with the following test configuration.

C1	1µF X7R multilayer ceramic capacitor, voltage rating to be a minimum of 3 times the output voltage of the DC-DC converter
C2	$10\mu$ F tantalum capacitor, voltage rating to be a minimum of 1.5 times the output voltage of the DC-DC converter with an ESR of less than $100m\Omega$ at $100$ kHz
C3	100nF multilayer ceramic capacitor, general purpose
R1	450Ω resistor, carbon film, $\pm$ 1% tolerance
R2	50Ω BNC termination
T1	3T of the coax cable through a ferrite toroid
RLOAD	Resistive load to the maximum power rating of the DC-DC converter. Connections should be made via twisted wires

Differential Mode Noise Test Schematic



### APPLICATION NOTES

#### Minimum load

The minimum load to meet datasheet specification is 10% of the full rated load across the specified input voltage range. Lower than 10% minimum loading will result in an increase in output voltage, which may rise to typically 1.25 times the specified output voltage if the output load falls to less than 5%.

#### Gate Drive Applications Advisory Note

For general guidance for product usage in gate drive applications please refer to "gate drive application notes".

#### Capacitive loading and start up Typical Start-Up Wave Form Start-up time ms 10µF MGJ2D121505MPC 3 MGJ2D121509MPC 4 MGJ2D122005MPC 5 MGJ2D151505MPC 3 MGJ2D151509MPC 4 MGJ2D152005MPC 4


# **MGJ2 Surface Mount Series**

5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters

### **APPLICATION NOTES (Continued)**


The MGJ2 series is a dual output DC-DC specifically designed for gate drive applications and its output configuration is not suitable for application usage as a general dual output DC-DC converter. However the MGJ2 series can be used as a general purpose single output converter, by loading from +Vout to -Vout.

The MGJ2 series provides a dual output by using a patented pnp emitter follower current shunt divider network circuit with short circuit protection.



**Optional Configuration:** 


For optional configuration where alternative negative output voltages are required, an external zener diode network can be connected across the main 20V or 25V output. However this zener diode will no longer be protected from short circuits as the internal short circuit protection is bypassed.



www.murata.com

# **MGJ2 Surface Mount Series**

muRata Ps Murata Power Solutions 5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters




# **MGJ2 Surface Mount Series**

5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters

#### POSITIVE OUTPUT VOLTAGE TOLERANCE ENVELOPES

The voltage tolerance envelopes show typical load regulation characteristics for this product series. The tolerance envelope is the maximum output voltage variation due to changes in output loading and set point accuracy.



### **MGJ2 Surface Mount Series** muRata Ps Murata Power Solutions

### 5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters


#### The voltage tolerance envelopes show typical load regulation characteristics for this product series. The tolerance envelope is the maximum output voltage variation due to changes in output loading and set point accuracy. MGJ2D121505MPC MGJ2D121509MPC 10% 6% 5% 4% **Dutput Voltage Dutput Voltage** 1% 0% -5% -8% 25 75 25 75 10 50 100 10 50 100 Output Load Current (%) Output Load Current (%) MGJ2D122005MPC MGJ2D151505MPC 10% 4% 4% **Dutput Voltage Output Voltage** 1% -4% -5% -4% -11% 25 50 75 25 75 50 10 100 10 100 Output Load Current (%) Output Load Current (%) MGJ2D151509MPC MGJ2D152005MPC 4% **Output Voltage Output Voltage** 1% -1% -2% -3% -5% -7% -10% 10 25 50 75 75 100 25 50 100 10 Output Load Current (%) Output Load Current (%)

**NEGATIVE OUTPUT VOLTAGE TOLERANCE ENVELOPES** 

www.murata.com

# **MGJ2 Surface Mount Series**

5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters



# **MGJ2 Surface Mount Series**

5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters




www.murata.com

# MGJ2 Surface Mount Series

5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters


### EMC FILTERING AND SPECTRA FILTERING The following filter circuit and filter table shows the input filters typically required to meet EN55022 Quasi-PeakCurve A or B. L1 +





Cdamp Electrolytic capacitor

muRata Ps Murata Power Solutions

	Inductor			Capacitor			
	L1, μΗ	SMD	Through Hole	C1&2, µF	Part number	Cdamp, µF	
MGJ2D121505MPC	22	84223C	11R223C	10	GRM188C81C106MA73	100	
MGJ2D121509MPC	22	84223C	11R223C	10	GRM188C81C106MA73	100	
MGJ2D122005MPC	22	84223C	11R223C	10	GRM188C81C106MA73	100	
MGJ2D151505MPC	33	84333C	11R333C	10	GRM188C81C106MA73	100	
MGJ2D151509MPC	33	84333C	11R333C	10	GRM188C81C106MA73	100	
MGJ2D152005MPC	47	84473C	11R473C	10	GRM188C81C106MA73	100	








1.00E+07

1.00E+08

# **MGJ2 Surface Mount Series**

5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters




www.murata.com

KDC\_MGJ2SM\_D01 Page 13 of 16


# **MGJ2 Surface Mount Series**

5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters



# **MGJ2 Surface Mount Series**

5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters



# **MGJ2 Surface Mount Series**

### 5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters

#### DISCLAIMER

Unless otherwise stated in the datasheet, all products are designed for standard commercial and industrial applications and NOT for safety-critical and/or life-critical applications.

Particularly for safety-critical and/or life-critical applications, i.e. applications that may directly endanger or cause the loss of life, inflict bodily harm and/or loss or severe damage to equipment/property, and severely harm the environment, a prior explicit written approval from Murata is strictly required. Any use of Murata standard products for any safety-critical, life-critical or any related applications without any prior explicit written approval from Murata shall be deemed unauthorised use.

These applications include but are not limited to:

- Aircraft equipment
- Aerospace equipment
- Undersea equipment
- Power plant control equipment
- Medical equipment
- Transportation equipment (automobiles, trains, ships, etc.)
- Traffic signal equipment
- Disaster prevention / crime prevention equipment
- Data Processing equipment

Murata makes no express or implied warranty, representation, or guarantee of suitability, fitness for any particular use/purpose and/or compatibility with any application or device of the buyer, nor does Murata assume any liability whatsoever arising out of unauthorised use of any Murata product for the application of the buyer. The suitability, fitness for any particular use/purpose and/or compatibility of Murata product with any application or device of the buyer remain to be the responsibility and liability of the buyer.

Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm, and take appropriate remedial actions. Buyer will fully indemnify and hold Murata, its affiliated companies, and its representatives harmless against any damages arising out of unauthorised use of any Murata products in any safety-critical and/ or life-critical applications.

Remark: Murata in this section refers to Murata Manufacturing Company and its affiliated companies worldwide including, but not limited to, Murata Power Solutions.



This product is subject to the following <u>operating requirements</u> and the <u>Life and Safety Critical Application Sales Policy</u>: Refer to: https://www.murata.com/en-eu/products/power/requirements

Murata Power Solution(Milton keynes) Ltd. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not imply the granting of licenses to make, use, or sell equipment constructed in actionace therewith. Specifications are subject to change without notice. *@ 2023 Murata Power Solution(Milton keynes) Ltd.*