

#### Inductor Built-in Step-Down "mini DC/DC" Converters

☆Green Operation Compatible

### ■GENERAL DESCRIPTION

The MYRGP-W/B series is a synchronous step-down mini DC/DC converter which integrates an inductor and a control IC in one tiny package (2.5mm×2.0mm, H=1.0mm). A stable power supply with an output current of 600mA is configured using only two capacitors connected externally. Operating voltage range is from 2.0V to 6.0V.

Output voltage is internally set in a range from 0.8V to 4.0V in increments of 0.05V.

The device is operated by 3.0MHz, and includes 0.42Ω P-channel driver transistor

and  $0.52\Omega$  N-channel switching transistor. As for operation mode, the MYRGP-W series is PWM control, the MYRGP-B series is automatic PWM/PFM switching control.

During stand-by, the device is shutdown to reduce current consumption to as low as 1.0µA or less. With the built-in UVLO (Under Voltage Lock Out) function, the internal driver transistor is forced OFF when input voltage becomes 1.4V or lower. MYRGP-x-RC integrate C∟ auto discharge function which enables the electric charge stored at the output capacitor C∟ to be discharged via the internal auto-discharge switch located between the Lx and Vss pins.

When the devices enter stand-by mode, output voltage quickly returns to the V<sub>SS</sub> level as a result of this function.

#### APPLICATIONS

- Mobile phones, Smart phones
- Bluetooth Headsets
- WiMAX PDAs, MIDs, UMPCs
- Portable game consoles
- Digital cameras, Camcorders
- Electronic dictionaries

#### **■**FEATURES

Ultra-Small : 2.5mm × 2.0mm, H=1.0mm

Input Voltage : 2.0V ~ 6.0V

**Output Voltage**  $: 0.8V \sim 4.0V (+2.0\%)$ High Efficiency : 90% (V<sub>IN</sub>=4.2V, V<sub>OUT</sub>=3.3V)

**Output Current** : 600mA

: 3.0MHz (<u>+</u>15%) Oscillation Frequency

Maximum Duty Cycle : 100%

Capacitor : Low ESR Ceramic

**CE** Function : Active High

Soft-Start Circuit Built-In C<sub>L</sub> High Speed Auto Discharge

**Protection Circuits** :Current Limiter Circuit Built-In

(Constant Current & Latching)

: PWM (MYRGP-W) Control Methods

PWM/PFM Auto (MYRGP-B)


**Operating Ambient Temperature** : -40°C ~ 85°C

**Environmentally Friendly** : EU RoHS Compliant, Pb Free

Halogen Free


### ■TYPICAL APPLICATION CIRCUIT

## **■TYPICAL PERFORMANCE** CHARACTERISTICS



\* "L1 and Lx", and "L2 and Vout" is connected by wiring

## MYRGP330060W/B21RC 100 MYRGP-B(PWM/PFM) 80








Inductor Built-in Step-Down "mini DC/DC" Converters

### ■BLOCK DIAGRAM

MYRGP-x-RC series




NOTE: The MYRGP-W offers a fixed PWM control, a signal from CE/MODE Control Logic to PWM/PFM Selector is fixed to "L" level inside. The MYRGP-B control scheme is PWM/PFM automatic switching, a signal from CE/MODE Control Logic to PWM/PFM Selector is fixed to "H" level inside. The diodes placed inside are ESD protection diodes and parasitic diodes.



Inductor Built-in Step-Down "mini DC/DC" Converters

### **■PIN CONFIGURATION**



- $^{\star}$  It should be connected the Vss pin (No. 2 and 5) to the GND pin.
- \* If the dissipation pad needs to be connected to other pins, it should be connected to the GND pin.
- \* Please refer to pattern layout page for the connecting to PCB.



## Inductor Built-in Step-Down "mini DC/DC" Converters

### **■ PIN ASSIGNMENT**

PIN NUMBER	PIN NAME	FUNCTIONS
1	L <sub>x</sub>	Switching Output
2,5	Vss	Ground
3	Vout	Fixed Output Voltage Pin
4	CE / MODE	Chip Enable & Mode Switch
6	V <sub>IN</sub>	Power Input
7	L1	Inductor Electrodes
8	L2	inductor Electrodes

### **■**FUNCTION

CE/MODE	OPERATIONAL STATES		
CE/MODE	MYRGP-W	MYRGP-B	
H Level (*1)	Synchronous PWM Fixed Control	Synchronous PWM/PFM Automatic Switching	
L Level (*2)	Stand-by	Stand-by	

<sup>\*\*</sup>series CE/MODE pin voltage level range

 $^{(*1)}$ H Level :0.65V  $\leq$  H Level  $\leq$  6V (MYRGP-W/B)

### ■ABSOLUTE MAXIMUM RATINGS

PARAMETER	SYMBOL	RATINGS	UNITS
V <sub>IN</sub> Pin Voltage	V <sub>IN</sub>	-0.3 ~ 6.5	V
L <sub>x</sub> Pin Voltage	VLx	-0.3 ~ V <sub>IN</sub> + 0.3	V
V <sub>OUT</sub> Pin Voltage	V <sub>оит</sub>	-0.3 ~ 6.5	V
CE/MODE Pin Voltage	V <sub>CE</sub>	-0.3 ~ 6.5	V
L <sub>X</sub> Pin Current	IL <sub>X</sub>	±1500	mA
Power Dissipation(Ta=25°C)	Pd	1000 (40mm x 40mm Standard board) (*1)	mW
Operating Ambient Temperature	Topr	-40 ~ 85	°C
Storage Temperature	Tstg	-40 ~ 125	$^{\circ}$ C

<sup>(\*1)</sup> The power dissipation figure shown is PCB mounted and is for reference only. The mounting condition is please refer to PACKAGING INFORMATION.

 $<sup>^{(*2)}</sup>$ L Level :0V  $\leq$  L Level  $\leq$  0.25V



Inductor Built-in Step-Down "mini DC/DC" Converters

## ■ELECTRICAL CHARACTERISTICS (Continued)

●MYRGP-x-RC Ta=25°C

PARAMETER	SYMBOL	CONDITIONS	MIN.	TYP.	MAX.	UNITS	CIRCUIT
Output Voltage	V <sub>OUT</sub>	When connected to external components, $V_{IN} = V_{CE} = 5.0V$ , $I_{OUT} = 30$ mA	<e-1></e-1>	<e-2></e-2>	<e-3></e-3>	V	1
Operating Voltage Range	$V_{IN}$		2.0	-	6.0	V	1
Maximum Output Current	I <sub>OUTMAX</sub>	V <sub>IN</sub> =V <sub>OUT(T)</sub> +2.0V, V <sub>CE</sub> =1.0V When connected to external components (*8)	600	-	-	mA	1
UVLO Voltage	$V_{\text{UVLO}}$	V <sub>CE</sub> =V <sub>IN</sub> ,V <sub>OUT</sub> =0V, Voltage which Lx pin holding "L" level (*1,*10)	1.00	1.40	1.78	V	3
Supply Current (MYRGP-W)		\\ -\\ -E 0\\ \\ -\\ \\ ×4.4\\	-	46	65	^	2
Supply Current (MYRGP-B)	$I_{DD}$	$V_{IN} = V_{CE} = 5.0V$ , $V_{OUT} = V_{OUT(T)} \times 1.1V$		21	35	μΑ	(2)
Stand-by Current	I <sub>STB</sub>	$V_{IN}$ =5.0V, $V_{CE}$ =0V, $V_{OUT}$ = $V_{OUT(T)} \times 1.1V$	-	0	1.0	μΑ	2
Oscillation Frequency	f <sub>osc</sub>	When connected to external components, $V_{IN} = V_{OUT(T)} + 2.0V, V_{CE} = 1.0V, I_{OUT} = 100 \text{mA}$	2550	3000	3450	kHz	1
PFM Switching Current (*11)	I <sub>PFM</sub>	When connected to external components, $V_{IN}$ = $V_{OUT(T)}$ +2.0V, $V_{CE}$ = $V_{IN}$ , $I_{OUT}$ =1mA	<e-4></e-4>	<e-5></e-5>	<e-6></e-6>	mA	10
PFM Duty Limit (*11)	DTY <sub>LIMIT_PFM</sub>	$V_{CE} = V_{IN} = V_{OUT(T)} + 1.0V$ , $I_{OUT} = 1$ mA	-	200	300	%	1
Maximum Duty Cycle	MAXDTY	$V_{IN} = V_{CE} = 5.0V, V_{OUT} = V_{OUT(T)} \times 0.9V$	100	-	-	%	3
Minimum Duty Cycle	MINDTY	$V_{IN} = V_{CE} = 5.0V, V_{OUT} = V_{OUT(T)} \times 1.1V$	-	-	0	%	3
Efficiency(*2)	EFFI	When connected to external components, $V_{CE} = V_{IN} = V_{OUT,(T)} + 1.2V$ , $I_{OUT} = 100$ mA	-	<e-7></e-7>	-	%	1
Lx SW "H" ON Resistance 1	$R_{L \times H}$	$V_{IN} = V_{CE} = 5.0V, V_{OUT} = 0V, IL_X = 100 \text{mA}^{(*3)}$	-	0.35	0.55	Ω	4
Lx SW "H" ON Resistance 2	$R_{L_{\times}H}$	$V_{IN} = V_{CE} = 3.6V, V_{OUT} = 0V, IL_X = 100 \text{mA}^{(*3)}$	-	0.42	0.67	Ω	4
Lx SW "L" ON Resistance 1	$R_{L \times L}$	$V_{IN} = V_{CE} = 5.0V^{(*4)}$	-	0.45	0.65	Ω	-
Lx SW "L" ON Resistance 2	$R_{L \times L}$	$V_{IN} = V_{CE} = 3.6V^{(*4)}$	-	0.52	0.77	Ω	-
Lx SW "H" Leakage Current (*5)	I <sub>LEAKH</sub>	$V_{IN} = V_{OUT} = 5.0V, V_{CE} = 0V, L_X = 0V$	-	0.01	1.0	μΑ	9
Current Limit (*9)	I <sub>LIM</sub>	$V_{IN} = V_{CE} = 5.0V, V_{OUT} = V_{OUT}(T) \times 0.9V^{(*7)}$	900	1050	1350	mA	6
Output Voltage Temperature Characteristics	$\Delta V_{OUT}/$ ( $V_{OUT} \cdot \Delta Topr$ )	I <sub>OUT</sub> =30mA -40°C≦Topr≦85°C	-	±100	-	ppm/ °C	1
CE "H" Voltage	$V_{CEH}$	V <sub>O∪T</sub> =0V, Applied voltage to V <sub>CE</sub> , Voltage changes Lx to "H" level <sup>(*10)</sup>	0.65	-	6.0	V	3
CE "L" Voltage	$V_{CEL}$	V <sub>OUT</sub> =0V, Applied voltage to V <sub>CE</sub> , Voltage changes Lx to "L" level <sup>(*10)</sup>	$V_{\text{SS}}$	-	0.25	V	3
CE "H" Current	I <sub>CEH</sub>	$V_{IN} = V_{CE} = 5.0V$ , $V_{OUT} = 0V$	- 0.1	0.0	0.1	μΑ	5
CE "L" Current	I <sub>CEL</sub>	$V_{IN}$ =5.0V, $V_{CE}$ = 0V, $V_{OUT}$ = 0V	- 0.1	0.0	0.1	μΑ	(5)
Soft Start Time	t <sub>ss</sub>	When connected to external components, $V_{CE}$ =0 $V$ $\rightarrow V_{IN}$ , $I_{OUT}$ =1mA	0.5	0.9	2.5	ms	1
Latch Time	t <sub>LAT</sub>	$V_{IN}=V_{CE}=5.0V$ , $V_{OUT}=0.8 \times V_{OUT(T)}$ Short Lx at 1 $\Omega$ resistance (*6)	1.0	-	20	ms	7
Short Protection Threshold Voltage	V <sub>SHORT</sub>	Sweeping $V_{OUT}$ , $V_{IN}$ = $V_{CE}$ =5.0V, Short Lx at 1 $\Omega$ resistance, $V_{OUT}$ voltage which Lx becomes "L" level within 1ms	<e-8></e-8>	<e-9></e-9>	<e-10></e-10>	V	Ī
C <sub>L</sub> Discharge	R <sub>DCHG</sub>	$V_{IN} = 5.0V$ $L_X = 5.0V$ $V_{CE} = 0V$ $V_{OUT} = open$	200	300	450	Ω	8
Inductance Value	L	Test frequency=1MHz	-	1.5	-	μΗ	-
Allowed Inductor Current	$I_{DC}$	∆T=40°C	-	1000	-	mA	-

Test conditions: Unless otherwise stated, V<sub>IN</sub>=5.0V, V<sub>OUT (T)</sub> = Nominal Voltage

#### NOTE:

- (\*1) Including hysteresis operating voltage range.
- (\*2) EFFI = { (output voltage × output current ) / (input voltage × input current) } × 100
- $^{(^{\circ}3)}$  ON resistance (  $\Omega$  )= (V<sub>IN</sub> Lx pin measurement voltage) / 100mA
- (\*4) Design value
- When temperature is high, a current of approximately 10  $\mu$  A (maximum) may leak.
- (6) Time until it short-circuits  $V_{OUT}$  with GND via  $1\Omega$  of resistor from an operational state and is set to Lx=0V from current limit pulse generating.
- (\*7) When V<sub>IN</sub> is less than 2.4V, limit current may not be reached because voltage falls caused by ON resistance.
- (\*8) When the difference between the input and the output is small, some cycles may be skipped completely before current maximizes. If current is further pulled from this state, output voltage will decrease because of P-ch driver ON resistance.
- (\*9) Current limit denotes the level of detection at peak of coil current.
- (\*10) "H"= $V_{IN}$ ~ $V_{IN}$ -1.2V, "L"=+0.1V~-0.1V
- (\*11) I<sub>PFM</sub> and DTY<sub>LIMIT\_PFM</sub> are defined only for the MYRGP-B series which have PFM control function. (Not for the MYRGP-W series)



Inductor Built-in Step-Down "mini DC/DC" Converters

## ■ ELECTRICAL CHARACTERISTICS (Continued)

## Output Voltage

	NOMINAL	V <sub>OUT</sub> (V)			
PART NUMBER	OUTPUT VOLTAGE	<e-1></e-1>	<e-2></e-2>	<e-3></e-3>	
	$V_{OUT(T)}$	MIN	TYP	MAX	
MYRGP100060W/B21RC	1.00	0.980	1.000	1.020	
MYRGP120060W/B21RC	1.20	1.176	1.200	1.224	
MYRGP140060W/B21RC	1.40	1.372	1.400	1.428	
MYRGP150060W/B21RC	1.50	1.470	1.500	1.530	
MYRGP180060W/B21RC	1.80	1.764	1.800	1.836	
MYRGP190060W/B21RC	1.90	1.862	1.900	1.938	
MYRGP250060W/B21RC	2.50	2.450	2.500	2.550	
MYRGP300060W/B21RC	3.00	2.940	3.000	3.060	
MYRGP330060W/B21RC	3.30	3.234	3.300	3.366	

#### ●PFM Switching Current

NOMINAL OUTPUT	I <sub>PFM</sub> (mA)			
NOMINAL OUTPUT VOLTAGE	<e-4></e-4>	<e-5></e-5>	<e-6></e-6>	
VOLTAGE	MIN	TYP	MAX	
V <sub>OUT(T)</sub> ≦1.2V	190	260	350	
1.2V < V <sub>OUT(T)</sub> ≤ 1.75V	180	240	300	
1.8V≦V <sub>OUT(T)</sub>	170	220	270	

#### Efficiency

NOMINAL	Efficiency (%)	
OUTPUT	MYRGP-W/B	
VOLTAGE	<e-7></e-7>	
$V_{\text{OUT(T)}}$	3.0MHz	
1.00	79	
1.20	82	
1.40	83	
1.50	84	
1.80	05	
1.90	85	
2.50		
3.00	86	
3.30		


#### Short Protection Threshold Voltage


NOMINAL	V <sub>SHORT</sub> (V)		
OUTPUT		MYRGP-x-RC	
VOLTAGE	<e-8></e-8>	<e-9></e-9>	<e-10></e-10>
$V_{\text{OUT(T)}}$	MIN	TYP	MAX
1.00	0.375	0.500	0.625
1.20	0.450	0.600	0.750
1.40	0.525	0.700	0.875
1.50	0.563	0.750	0.938
1.80	0.675	0.900	1.125
1.90	0.713	0.950	1.188
2.50	0.938	1.250	1.563
3.00	1.125	1.500	1.875
3.30	1.238	1.650	2.063




# Inductor Built-in Step-Down "mini DC/DC" Converters


### TEST CIRCUITS








< Circuit No.2 >





























Inductor Built-in Step-Down "mini DC/DC" Converters

## **■**TYPICAL APPLICATION CIRCUIT

#### ●MYRGP-x-RC Series



#### External Components

CIN:  $10V/4.7 \mu$  F (Ceramic)  $C_L$ : 6.3V/10  $\mu$  F (Ceramic)

NOTE

The Inductor can be used only for this DC/DC converter.

Please do not use this inductor for the other reasons.

Please use B, X5R, and X7R grades in temperature characteristics for  $C_{\text{\tiny IN}}$  and  $C_{\text{\tiny L}}$  capacitors.

These grade ceramic capacitors minimize capacitance-loss as a function of voltage stress.



### Inductor Built-in Step-Down "mini DC/DC" Converters

#### ■OPERATIONAL DESCRIPTION

The MYRGP-W/B series consists of a reference voltage source, ramp wave circuit, error amplifier, PWM comparator, phase compensation circuit, output voltage adjustment resistors, P-channel MOSFET driver transistor, N-channel MOSFET switching transistor for the synchronous switch, current limiter circuit, UVLO circuit with control IC, and an inductor. (See the block diagram above.)

Using the error amplifier, the voltage of the internal voltage reference source is compared with the feedback voltage from the Vout pin through split resistors, R1 and R2. Phase compensation is performed on the resulting error amplifier output, to input a signal to the PWM comparator to determine the turn-on time during PWM operation. The PWM comparator compares, in terms of voltage level, the signal from the error amplifier with the ramp wave from the ramp wave circuit, and delivers the resulting output to the buffer driver circuit to cause the Lx pin to output a switching duty cycle. This process is continuously performed to ensure stable output voltage.

The current feedback circuit monitors the P-channel MOS driver transistor current for each switching operation, and modulates the error amplifier output signal to provide multiple feedback signals. This enables a stable feedback loop even when a low ESR capacitor such as a ceramic capacitor is used ensuring stable output voltage.

#### <Reference Voltage Source>

The reference voltage source provides the reference voltage to ensure stable output voltage of the DC/DC converter.

#### <Ramp Wave Circuit>

The ramp wave circuit determines switching frequency. The frequency is fixed internally 3.0MHz. Clock pulses generated in this circuit are used to produce ramp waveforms needed for PWM operation, and to synchronize all the internal circuits.

#### <Error Amplifier>

The error amplifier is designed to monitor output voltage. The amplifier compares the reference voltage with the feedback voltage divided by the internal split resistors, R1 and R2. When a feedback voltage is lower than the reference voltage, the output voltage of the error amplifier is increased. The gain and frequency characteristics of the error amplifier output are fixed internally to deliver an optimized signal to the mixer.


#### <Current Limit>

The current limiter circuit of the MYRGP-W/B series monitors the current flowing through the P-channel MOS driver transistor connected to the Lx pin, and features a combination of the current limit mode and the operation suspension mode.

- ① When the driver current is greater than a specific level, the current limit function operates to turn off the pulses from the Lx pin at any given timing.
- When the driver transistor is turned off, the limiter circuit is then released from the current limit detection state.
- 3 At the next pulse, the driver transistor is turned on. However, the transistor is immediately turned off in the case of an over current state.
- ④ When the over current state is eliminated, the IC resumes its normal operation.

The IC waits for the over current state to end by repeating the steps 1 through 3. If an over current state continues for a few milliseconds and the above three steps are repeatedly performed, the IC performs the function of latching the OFF state of the driver transistor, and goes into operation suspension state. Once the IC is in suspension state, operations can be resumed by either turning the IC off via the CE/MODE pin, or by restoring power to the  $V_{IN}$  pin. The suspension state does not mean a complete shutdown, but a state in which pulse output is suspended; therefore, the internal circuitry remains in operation. The current limit of the MYRGP-W/B series can be set at 1050mA at typical.

Depending on the state of the PC Board, latch time may become longer and latch operation may not work. In order to avoid the effect of noise, an input capacitor is placed as close to the IC as possible.





Inductor Built-in Step-Down "mini DC/DC" Converters

## ■ OPERATIONAL DESCRIPTION (Continued)

#### <Short-Circuit Protection>

The short-circuit protection circuit monitors the internal R1 and R2 divider voltage from the V<sub>OUT</sub> pin (refer to FB point in the block diagram shown in the previous page). In case where output is accidentally shorted to the Ground and when the FB point voltage decreases less than half of the reference voltage (Vref) and a current more than the I<sub>LIM</sub> flows to the driver transistor, the short-circuit protection quickly operates to turn off and to latch the driver transistor.

In the latch state, the operation can be resumed by either turning the IC off and on via the CE/MODE pin, or by restoring power supply to the  $V_{IN}$  pin.

When sharp load transient happens, a voltage drop at the  $V_{OUT}$  is propagated to the FB point through  $C_{FB}$ , as a result, short circuit protection may operate in the voltage higher than 1/2  $V_{OUT}$  voltage.

#### <UVLO Circuit>

When the  $V_{IN}$  pin voltage becomes 1.4V or lower, the P-channel output driver transistor is forced OFF to prevent false pulse output caused by unstable operation of the internal circuitry. When the  $V_{IN}$  pin voltage becomes 1.8V or higher, switching operation takes place. By releasing the UVLO function, the IC performs the soft start function to initiate output startup operation. The soft start function operates even when the  $V_{IN}$  pin voltage falls momentarily below the UVLO operating voltage. The UVLO circuit does not cause a complete shutdown of the IC, but causes pulse output to be suspended; therefore, the internal circuitry remains in operation.


#### <PFM Switch Current>


In PFM control operation, until coil current reaches to a specified level (IPFM), the IC keeps the P-ch MOSFET on. In this case, on-time (ton) that the P-ch MOSFET is kept on can be given by the following formula.

$$t_{ON} = L \times IPFM / (V_{IN} - V_{OUT}) \rightarrow I_{PFM}$$

#### <PFM Duty Limit>

In the PFM control operation, the PFM Duty Limit (DTY<sub>LIMIT\_PFM</sub>) is set to 200% (TYP.). Therefore, under the condition that the duty increases (e.g. the condition that the step-down ratio is small), it's possible for P-ch MOSFET to be turned off even when coil current doesn't reach to IPFM. →IPFM②








Inductor Built-in Step-Down "mini DC/DC" Converters

## ■ OPERATIONAL DESCRIPTION (Continued)

<CE/MODE Pin Function>

The operation of the MYRGP-W/B series will enter into the shutdown mode when a low level signal is input to the CE/MODE pin. During the shutdown mode, the current consumption of the IC becomes  $0\,\mu$  A (TYP.), with a state of high impedance at the Lx pin and Vout pin. The IC starts its operation by inputting a high level signal to the CE/MODE pin. The input to the CE/MODE pin is a CMOS input and the sink current is  $0\,\mu$  A (TYP.).

#### ●MYRGP-W/B series - Examples of how to use CE/MODE pin



(A)		
CW CE	SELECTED	
SW_CE	STATUS	
ON	Stand-by	
OFF	Operation	

(B)	
CM CE	SELECTED
SW_CE	STATUS
ON	Operation
OFF	Stand-by




Inductor Built-in Step-Down "mini DC/DC" Converters

## ■OPERATIONAL DESCRIPTION (Continued)

<Soft Start>

The MYRGP-x-RC series provide 0.9ms (TYP).

Soft start time is defined as the time to reach 90% of the output nominal voltage when the CE pin is turned on.



## ■FUNCTION CHART

CE/MODE	OPERATIONAL STATES		
VOLTAGE LEVEL	MYRGP-W	MYRGP-B	
H Level (*1)	Synchronous PWM Fixed Control	Synchronous PWM/PFM Automatic Switching	
L Level (*2)	Stand-by	Stand-by	

Note on CE/MODE pin voltage level range

(\*1) H level:  $0.65V \le H$  level  $\le 6V$  (for MYRGP-W/B)

(\*2) L level:  $0V \le L$  level  $\le 0.25V$ 



### Inductor Built-in Step-Down "mini DC/DC" Converters

#### ■NOTE ON USE


- 1. The MYRGP-W/B series is designed for use with ceramic output capacitors. If, however, the potential difference is too large between the input voltage and the output voltage, a ceramic capacitor may fail to absorb the resulting high switching energy and oscillation could occur on the output. If the input-output potential difference is large, connect an electrolytic capacitor in parallel to compensate for insufficient capacitance.
- 2. Spike noise and ripple voltage arise in a switching regulator as with a DC/DC converter. These are greatly influenced by external component selection, such as the coil inductance, capacitance values, and board layout of external components. Once the design has been completed, verification with actual components should be done.
- Depending on the input-output voltage differential, or load current, some pulses may be skipped, and the ripple voltage may increase.
- 4. When the difference between VIN and VOUT is large in PWM control, very narrow pulses will be outputted, and there is the possibility that some cycles may be skipped completely.
- 5. When the difference between VIN and VOUT is small, and the load current is heavy, very wide pulses will be outputted and there is the possibility that some cycles may be skipped completely.
- 6. With the IC, the peak current of the coil is controlled by the current limit circuit. Since the peak current increases when dropout voltage or load current is high, current limit starts operation, and this can lead to instability. When peak current becomes high, please adjust the coil inductance value and fully check the circuit operation. In addition, please calculate the peak current according to the following formula:

 $lpk = (V_{IN} - V_{OUT}) \times OnDuty / (2 \times L \times f_{OSC}) + IOUT$ 

L: Coil Inductance Value

fosc: Oscillation Frequency

- 7. When the peak current which exceeds limit current flows within the specified time, the built-in P-ch driver transistor turns off. During the time until it detects limit current and before the built-in transistor can be turned off, the current for limit current flows; therefore, care must be taken when selecting the rating for the external components such as a coil.
- 8. When VIN is less than 2.4V, limit current may not be reached because voltage falls caused by ON resistance.
- Depending on the state of the PC Board, latch time may become longer and latch operation may not work. In order to avoid the effect of noise, the board should be laid out so that input capacitors are placed as close to the IC as possible.
- 10. Use of the IC at voltages below the recommended voltage range may lead to instability.
- 11. This IC should be used within the stated absolute maximum ratings in order to prevent damage to the device.
- 12. When the IC is used in high temperature, output voltage may increase up to input voltage level at no load because of the leak current of the driver transistor.
- 13. The current limit is set to 1350mA (MAX.) at typical. However, the current of 1350mA or more may flow. In case that the current limit functions while the Vout pin is shorted to the GND pin, when P-ch MOSFET is ON, the potential difference for input voltage will occur at both ends of a coil. For this, the time rate of coil current becomes large. By contrast, when N-ch MOSFET is ON, there is almost no potential difference at both ends of the coil since the Vout pin is shorted to the GND pin. Consequently, the time rate of coil current becomes quite small. According to the repetition of this operation, and the delay time of the circuit, coil current will be converged on a certain current value, exceeding the amount of current, which is supposed to be limited originally. Even in this case, however, after the over current state continues for several ms, the circuit will be latched. A coil should be used within the stated absolute maximum rating in order to prevent damage to the device.
  - ①Current flows into P-ch MOSFET to reach the current limit (ILIM).
  - ②The current of ILIM or more flows since the delay time of the circuit occurs during from the detection of the current limit to OFF of P-ch MOSFET.
  - 3 Because of no potential difference at both ends of the coil, the time rate of coil current becomes quite small.
  - (4) Lx oscillates very narrow pulses by the current limit for several ms.
  - ⑤The circuit is latched, stopping its operation.







## Inductor Built-in Step-Down "mini DC/DC" Converters

## ■NOTE ON USE (Continued)

- 14. In order to stabilize  $V_{IN}$  voltage level and oscillation frequency, we recommend that a by-pass capacitor (CIN) be connected as close as possible to the  $V_{IN}$  &  $V_{SS}$  pins.
- 15. High step-down ratio and very light load may lead an intermittent oscillation when PWM mode.
- 16. Please use within the power dissipation range below. Please also note that the power dissipation may change by test conditions. The power dissipation figure shown is PCB mounted.
- 17. The proper position of mounting is based on the coil terminal





The power loss of mini DC/DC according to the following formula:

power loss =  $V_{OUT} \times I_{OUT} \times ((100/EFFI) - 1)$  (W)

 $V_{\text{OUT}}: \text{Output Voltage (V)} \\ I_{\text{OUT}}: \text{Output Current (A)}$ 

EFFI: Conversion Efficiency (%)




## Inductor Built-in Step-Down "mini DC/DC" Converters


## ■NOTE ON USE (Continued)

#### 18. Instructions of pattern layouts

- (1) In order to stabilize  $V_{IN}$  voltage level, we recommend that a by-pass capacitor ( $C_{IN}$ ) be connected as close as possible to the  $V_{IN}$  (No.6) &  $V_{SS}$  (No.5) pins.
- (2) Please mount each external component as close to the IC as possible.
- (3) Wire external components as close to the IC as possible and use thick, short connecting traces to reduce the circuit impedance.
- (4) Make sure that the PCB GND traces are as thick as possible, as variations in ground potential caused by high ground currents at the time of switching may result in instability of the IC.
- (5) This series' internal driver transistors bring on heat because of the output current and ON resistance of driver transistors.
- (6) Please connect Lx (No.1) pin and L1 (No.7) pin by wiring on the PCB.
- (7) Please connect V<sub>OUT</sub> (No.3) pin and L2 (No.8) pin by wiring on the PCB.

#### MYRGP-x-RC





<FRONT>


<BACK (Flip Horizontal)>




Inductor Built-in Step-Down "mini DC/DC" Converters

## **■TYPICAL PERFORMANCE CHARACTERISTICS**


(1) Efficiency vs. Output Current




(2) Output Voltage vs. Output Current




(3) Ripple Voltage vs. Output Current




(4) Oscillation Frequency vs. Ambient Temperature



(5) Supply Current vs. Ambient Temperature



(6) Output Voltage vs. Ambient Temperature







Inductor Built-in Step-Down "mini DC/DC" Converters

## ■TYPICAL PERFORMANCE CHARACTERISTICS (Continued)


(7) UVLO Voltage vs. Ambient Temperature




(8) CE "H" Voltage vs. Ambient Temperature




(9) CE "L" Voltage vs. Ambient Temperature



(10) Soft Start Time vs. Ambient Temperature



(11) "Pch / Nch" Driver on Resistance vs. Input Voltage






Inductor Built-in Step-Down "mini DC/DC" Converters

## ■TYPICAL PERFORMANCE CHARACTERISTICS (Continued)

(12) Soft-Start Time vs. Ambient Temperature

MYRGP330060W/B21RC 500 400 Soft Start Time: tss (µs) VIN=5.0V IOUT=1.0mA 300 200 100 0 -50 -25 25 50 75 100 (13) CL Discharge Resistance vs. Ambient Temperature




Ambient Temperature: Ta (°C)


(14) Load Transient Response 1

 ${\sf MODE}: {\sf PWM/PFM} \ {\sf Automatic} \ {\sf Switching} \ {\sf Control}$ 


Ambient Temperature: Ta (°C)




Time:  $100 \,\mu$  s /div



Time:  $100 \mu \text{ s/div}$ 



Time:  $100 \,\mu$  s /div



Time:  $100 \mu \text{ s/div}$ 




Inductor Built-in Step-Down "mini DC/DC" Converters

## ■TYPICAL PERFORMANCE CHARACTERISTICS (Continued)


(15) Load Transient Response 2 MODE: PWM Control





Time:  $100 \mu \text{ s/div}$ 

#### MYRGP180060W21RC




Time:  $100 \,\mu$  s /div

#### MYRGP180060W21RC



Time:  $100 \mu \text{ s/div}$ 

#### MYRGP180060W21RC




Time:  $100 \mu \text{ s /div}$ 




Inductor Built-in Step-Down "mini DC/DC" Converters


### **■PACKAGING INFORMATION**

#### ●Packaging (2.0mm×2.5mm, h=1.0mm)










■External Lead


X Au

Sn

●Reference Pattern Layout (unit: mm)

●Reference Metal Mask Design (unit: mm)







## Inductor Built-in Step-Down "mini DC/DC" Converters

#### **■PACKAGING INFORMATION**

#### Power Dissipation

Power dissipation data for the package is shown in this page.

The value of power dissipation varies with the mount board conditions.

Please use this data as one of reference data taken in the described condition.

1. Measurement Condition (Reference data)

Condition: Mount on a board
Ambient: Natural convection
Soldering: Lead (Pb) free

Board Dimensions: 40 x 40 mm (1600mm2 in one side)

Copper (Cu) traces occupy 50% of the board area


in top and back faces Package heat-sink

is tied to the copper traces.

Material: Glass Epoxy (FR-4)

Thickness : 1.6 mm


Through-hole: 4 x 0.8 Diameter



Evaluation Board (Unit:mm)


# 2. Power Dissipation vs. Ambient Temperature(85 $^{\circ}$ C) Board Mount ( Tjmax=125 $^{\circ}$ C)

Ambient	Power	Thermal
Temperature	Dissipation	Resistance
(°C)	Pd (mW)	(°C/W)
25	1000	100.00
85	400	100.00



#### 3. Power Dissipation vs. Ambient Temperature(105°C)


Ambient	Power	Thermal	
Temperature	Dissipation	Resistance	
(°C)	Pd (mW)	(°C/W)	
25	1000	100.00	
105	200		





## Inductor Built-in Step-Down "mini DC/DC" Converters

### **■**MARKING RULE



1) represents products series

MARK	PRODUCT SERIES	
K	MYRGP-W-RC	
L	MYRGP-B-RC	

#### 2 represents type of DC/DC converters

OUTPUT VOLTAGE	MARK
(V)	MYRGP-x-RC
0.x	F
1.x	Н
2.x	K
3.x	L
4.x	M

3 represents the decimal part of output voltage

OUTPUT VOLTAGE (V)	MARK	PRODUCT SERIES
X.0	0	MYRGPx00060x21RC
X.05	Α	MYRGPx05060x21RC
X.1	1	MYRGPx10060x21RC
X.15	В	MYRGPx15060x21RC
X.2	2	MYRGPx20060x21RC
X.25	С	MYRGPx25060x21RC
X.3	3	MYRGPx30060x21RC
X.35	D	MYRGPx35060x21RC
X.4	4	MYRGPx40060x21RC
X.45	Е	MYRGPx45060x21RC
X.5	5	MYRGPx50060x21RC
X.55	F	MYRGPx55060x21RC
X.6	6	MYRGPx60060x21RC
X.65	Н	MYRGPx65060x21RC
X.7	7	MYRGPx70060x21RC
X.75	K	MYRGPx75060x21RC
X.8	8	MYRGPx80060x21RC
X.85	L	MYRGPx85060x21RC
X.9	9	MYRGPx90060x21RC
X.95	М	MYRGPx95060x21RC

4,5 represents production lot number

01~09、0A~0Z、11~9Z、A1~A9、AA~AZ、B1~ZZ in order.

(G, I, J, O, Q, W excluded) Note: No character inversion used.



## Inductor Built-in Step-Down "mini DC/DC" Converters

- The product and product specifications contained herein are subject to change without notice to improve performance characteristics. Consult us, or our representatives before use, to confirm that the information in this datasheet is up to date.
- 2. The information in this datasheet is intended to illustrate the operation and characteristics of our products. We neither make warranties or representations with respect to the accuracy or completeness of the information contained in this datasheet nor grant any license to any intellectual property rights of ours or any third party concerning with the information in this datasheet.
- Applicable export control laws and regulations should be complied and the procedures required by such laws and regulations should also be followed, when the product or any information contained in this datasheet is exported.
- 4. The product is neither intended nor warranted for use in equipment of systems which require extremely high levels of quality and/or reliability and/or a malfunction or failure which may cause loss of human life, bodily injury, serious property damage including but not limited to devices or equipment used in 1) nuclear facilities, 2) aerospace industry, 3) medical facilities, 4) automobile industry and other transportation industry and 5) safety devices and safety equipment to control combustions and explosions. Do not use the product for the above use unless agreed by us in writing in advance.
- 5. Although we make continuous efforts to improve the quality and reliability of our products; nevertheless Semiconductors are likely to fail with a certain probability. So in order to prevent personal injury and/or property damage resulting from such failure, customers are required to incorporate adequate safety measures in their designs, such as system fail safes, redundancy and fire prevention features.
- 6. Our products are not designed to be Radiation-resistant.
- 7. Please use the product listed in this datasheet within the specified ranges.
- 8. We assume no responsibility for damage or loss due to abnormal use.
- 9. All rights reserved. No part of this datasheet may be copied or reproduced unless agreed by Murata manufacturing Co., Ltd in writing in advance.

Murata Manufacturing Co.,Ltd