

5.2kVDC Isolated 1W Gate Drive DC-DC Converters



muRata

FEATURES

- Optimised bipolar output voltages for IGBT/ Mosfet, SiC & GaN gate drives
- Reinforced insulation to UL62368-1 recognised
- ANSI/AAMI ES60601-1, 1 MOPP/2 MOOPs pending
- 5.2kVDC isolation test voltage 'Hi Pot Test'
- Ultra low isolation capacitance
- 5V, 12V, 15V & 24V inputs
- +6V/-3V, +15V/-3V, +15V/-5V, +15V/-9V, +18V/-2.5V & +20V/-5V outputs
- Operation to 105°C
- Characterised CMTI >200kV/µS
- Continuous barrier withstand voltage 2.4kVDC
- Characterised partial discharge performance

PRODUCT OVERVIEW

The MGJ1 SIP series of DC-DC converters is ideal for powering 'high side' and 'low side' gate drive circuits for IGBT/Mosfet, SiC & GaN gate drives in bridge circuits. A choice of asymmetric output voltages allows optimum drive levels for best system efficiency and EMI. The MGJ1 SIP series is characterised for high isolation and dv/dt requirements commonly seen in bridge circuits used in motor drives and inverters, while the MGJ1 SIP high operating temperature rating and construction gives long service life and reliability.

SELECTION GUID)E									
		-	2	-	2		Outp	out 1	Outp	out 2
Order Code	Nominal Input Voltage	Output Voltage 1	Output Voltage 2	Output Current 1	Output Current 2	Input Current at Rated Load	Load Regulation (Typ)	Load Regulation (Max)	Load Regulation (Typ)	Load Regulation (Max)
	V	V	V		mA			9	6	
MGJ1D050603SC	5	6	-3	111	111	260	0.7	1.5	25	30
MGJ1D052005SC	5	20	-5	40	40	280	5.0	8.0	0.5	1.0
MGJ1D120603SC	12	6	-3	111	111	110	0.4	1.5	16	25
MGJ1D121503SC	12	15	-3	55.6	55.6	100	4.0	8.0	0.5	1.0
MGJ1D121505SC	12	15	-5	50	50	100	5.0	8.0	0.5	1.0
MGJ1D121802SC	12	18	-2.5	48.8	48.8	100	4.0	7.0	0.5	1.0
MGJ1D122005SC	12	20	-5	40	40	110	4.0	9.0	0.5	1.0
MGJ1D151509SC	15	15	-9	41.7	41.7	85	5.0	9.0	0.5	1.0
MGJ1D152005SC	15	20	-5	40	40	85	4.0	9.0	0.5	1.0
MGJ1D241503SC	24	15	-3	55.6	55.6	55	4.0	7.0	0.5	1.0
MGJ1D241505SC	24	15	-5	50	50	55	4.0	8.0	0.5	1.0
MGJ1D241509SC	24	15	-9	41.7	41.7	55	5.0	9.0	0.5	1.0
MGJ1D241802SC	24	18	-2.5	48.8	48.8	55	3.0	7.0	0.5	1.0
MGJ1D242005SC	24	20	-5	40	40	55	4.0	8.0	0.5	1.0

SELECTION GUIDE (Continued)

Order Code	Ripple & Noise (Typ) ²	Ripple & Noise (Max) ²	Efficiency (Min)	Efficiency (Typ)	Isolation Capacitance	M	ſTF ¹
	mV	р-р	a	6	pF	MIL.	Tel.
	111V	h-h		/0	pi	k	Hrs
MGJ1D050603SC	20	50	73	77	3	3620	108788
MGJ1D052005SC	20	50	67	71.5	3	2626	62618
MGJ1D120603SC	20	50	74	79	3	3200	103610
MGJ1D121503SC	20	50	76	79.5	3	3893	144172
MGJ1D121505SC	20	50	77	80	3	3707	136596
MGJ1D121802SC	20	50	75	78	3	3477	133403
MGJ1D122005SC	20	50	75	78	3	3331	128852
MGJ1D151509SC	20	50	74	78	3	3693	131693
MGJ1D152005SC	20	50	74	78	3	3226	137002
MGJ1D241503SC	20	50	71	76	3	3012	85564
MGJ1D241505SC	20	50	72	76	3	2546	72774
MGJ1D241509SC	20	50	69	74	3	2532	63241
MGJ1D241802SC	20	50	69	74	3	2465	64642
MGJ1D242005SC	20	50	69	74	3	2453	63535



1. Calculated using MIL-HDBK-217 and Telecordia SR-332 calculation model with nominal input voltage at full load. 2. See ripple & noise test method.

All specifications typical at T_A=25°C, nominal input voltage and rated output current unless otherwise specified.

www.murata.com

MGJ1 SIP Series

5.2kVDC Isolated 1W Gate Drive DC-DC Converters

Parameter	Conditions	Min.	Тур.	Max.	Units	
	Continuous operation, 5V input types	4.5	5	5.5		
Voltago rongo	Continuous operation, 12V input types	10.8	12	13.2	v	
Voltage range	Continuous operation, 15V input types	13.5	15	16.5	v	
	Continuous operation, 24V input types	21.6	24	26.4		
nout rofloated ringle	MGJ1D050603SC & MGJ1D052005SC		20		mApk-p	
Input reflected ripple	All other types		10		шарк-рі	
	MGJ1D050603SC		65			
	MGJ1D120603SC		25			
Chart aircuit input ourrant	MGJ1D052005SC		80		mA	
Short circuit input current	MGJ1D1215XXSC, MGJ1D121802SC & MGJ1D122005SC		25		IIIA	
	MGJ1D15XXXXSC		20			
	MGJ1D24XXXXSC		15			

GENERAL CHARACTERIST	rics				
Parameter	Conditions	Min.	Тур.	Max.	Units
	MGJ1D050603SC		40		
	MGJ1D052005SC		60		
Switching frequency	MGJ1D120603SC, MGJ1D121503SC, MGJ1D121505SC & MGJ1D121802SC		55		kHz
	MGJ1D122005SC & MGJ1D15XXXXSC		65		
	MGJ1D24XXXXSC		70		

OUTPUT CHARACTERISTICS						
Parameter	Conditions	Conditions			Max.	Units
Rated Power	T _A =-40°C to 105°C			1.00		W
Voltage Set Point Accuracy	See tolerance envelopes					
	MGJ1D050603SC & MGJ1D120603SC	0P1		0.10	0.30	
	Miga 1 D03000336 & Miga 1 D 1 2000336	0P2		3.20	4.00	
	MGJ1DXX2005SC	0P1		1.30	1.40	
	MGJTDAA20035C	0P2		0.25	0.50	
Line regulation	MGJ1DXX1503SC & MGJ1DXX1802SC	0P1		1.20	1.30	%/%
Line regulation	MG1DAX13035C & MG1DAX18023C	0P2		0.25	0.50	70/70
	MGJ1DXX1505SC	0P1		1.40	1.50	
	WIGJTDAAT30336	0P2		0.25	0.50	
	MGJ1DXX1509SC	0P1		1.60	1.70	
	MIG11DVV120820	0P2		0.25	0.50	

ISOLATION CHA	RACTERISTICS					
Parameter			Min.	Тур.	Max.	Units
loolation toot volta	20	Production tested for 1 second		5200		VDC
Isolation test voltage		Qualification tested for 1 minute		5200		VDC
Resistance		Viso = 1000VDC	1			GΩ
Continuous barrier	withstand voltage	Non-safety barrier application		2400		VDC
	UL62368-1	Reinforced		300		
Safety standard	Basic/supplementary	Basic/supplementary		600		Vrms
Salety Stallualu	ANSI/AAMI	1 MOOP		300		VIIIIS
	ES60601-11	2 MOOP/1 MOPP		200		

1. ANSI/AAMI ES60601-1 recognition is currently pending for the MGJ1DxxxxxSC variants.

MGJ1 SIP Series

5.2kVDC Isolated 1W Gate Drive DC-DC Converters

Wave Solder profile not to exceed the profile recommended in IEC 61760-1

Section 6.1.3. Please refer to <u>application notes</u> for further information.

TEMPERATURE CHARACTERISTI	CS						
Parameter	Conditions			Тур.	Max.	Units	
Specification	All output types		-40		105		
Storage			-50		125	°C	
Case Temperature chave embient	All other types			15		6	
Case Temperature above ambient	MGJ1D052005SC, MGJ1D241509SC, MGJ1D241802SC & MGJ1D2420	005SC		20			
Cooling	Free air convection						
ABSOLUTE MAXIMUM RATINGS							
Input voltage V _{IN} , MGJ1D05xxxxSC	7V						
Input voltage VIN, MGJ1D12xxxxSC	15V	15V					
Input voltage VM, MGJ1D15xxxxSC 18V							
Input voltage V _M , MGJ1D24xxxxSC 28V							
Short-circuit protection	Continu	Continuous, automatic recovery					
Lead temperature 1mm from case for	10 seconds 260°C						

www.murata.com

Wave Solder

KDC_MGJ1_SIP_A01 Page 3 of 22

MGJ1 SIP Series

5.2kVDC Isolated 1W Gate Drive DC-DC Converters

TECHNICAL NOTES

ISOLATION VOLTAGE

'Hi Pot Test', 'Flash Tested', 'Withstand Voltage', 'Proof Voltage', 'Dielectric Withstand Voltage' & 'Isolation Test Voltage' are all terms that relate to the same thing, a test voltage, applied for a specified time, across a component designed to provide electrical isolation, to verify the integrity of that isolation.

Murata Power Solutions MGJ1 SIP series of DC-DC converters are all 100% production tested at 5.2kVDC for 1 second and have been qualification tested at 5.2kVDC for 1 minute.

The MGJ1 SIP series is recognised by Underwriters Laboratory, please see safety approval section for more information. When the insulation in the MGJ1 SIP series is not used as a safety barrier, i.e. provides functional isolation only, continuous or switched voltages across the barrier up to 2.4kV are sustainable. This is established by measuring the partial discharge Inception voltage in accordance with IEC 60270. Please contact Murata for further information.

REPEATED HIGH-VOLTAGE ISOLATION TESTING

It is well known that repeated high-voltage isolation testing of a barrier component can actually degrade isolation capability, to a lesser or greater degree depending on materials, construction and environment. We therefore strongly advise against repeated high voltage isolation testing, but if it is absolutely required, that the voltage be reduced by 20% from specified test voltage.

SAFETY APPROVAL

ANSI/AAMI ES60601-1

The MGJ1 SIP series is pending recognition by Underwriters Laboratory (UL) to ANSI/AAMI ES60601-1 and provides 1 MOOP (Mean Of Operator Protection) based on a working voltage of 300Vrms or 2 MOOP and 1 MOPP (Mean Of Patient Protection) based on a working voltage of 200Vrms, between Primary and Secondary.

File number E202895 applies.

UL62368-1

The MGJ1 SIP series is recognised by Underwriters Laboratory (UL) to UL62368-1 for reinforced insulation to a working voltage of 300Vrms or basic insulation to a working voltage of 600Vrms.

File number E151252 applies.

Creepage and clearance 6mm Working altitude 5000m

Fusing

The MGJ1 SIP series of converters are not internally fused so to meet the requirements of UL an anti-surge input line fuse should always be used with ratings as defined below. MGJ1D05xxxxSC: 430mA

MGJ1D12xxxxSC: 170mA MGJ1D15xxxxSC: 140mA MGJ1D24xxxxSC: 90mA

All fuses should be UL recognised and rated to 125VDC.

RoHS COMPLIANCE INFORMATION



This series is compatible with RoHS soldering systems with a peak wave solder temperature of 260°C for 10 seconds. Please refer to <u>application</u> <u>notes</u> for further information. The pin termination finish on this product series is Tin Plate, Hot Dipped over Matte Tin with Nickel Preplate. The series is backward compatible with Sn/Pb soldering systems. For further information, please visit www.murata.com/en-global/products/power/ rohs

MGJ1 SIP Series


5.2kVDC Isolated 1W Gate Drive DC-DC Converters

ENVIRONMENTAL VALIDATION TESTING

The following tests have been conducted on this product series, as part of our design verification process. The datasheet characteristics specify user operating conditions for this series, please contact Murata if further information about the tests is required.
Test
Standard
Condition

Temperature cycling	JEDEC JESD22-A104	200 cycles in a dual zone chamber from -40 (+5/-10)°C to 105 (+10/-5)°C. 15mins dwell at each (inclusive of ramps). 2 cycles per hour.
Humidity bias	JEDEC JESD22-A101	$85^{\circ}C \pm 2^{\circ}C$, $85\% \pm 5\%$ R.H. for >1000 hours.
High temperature storage life	JEDEC JESD22-A103, Condition A	125°C (+10/-0°C) for ≥1000 hours.
Vibration	MIL-STD-883 Method 2007, Condition A	$1.5 mm\ pk-pk$ / 20g pk min, 20-2000-20Hz, 4 sweeps in each of 3 mutually perpendicular axes at 3 oct/min.
Shock	MIL-STD-883 Method 2002, Condition A	500g 1.0ms half sine, 5 shocks in each direction of 3 mutually perpendicular axis.
ESD	JEDEC JESD22-A114	HBM 8.0kV.
Bump	IEC Class 4M5 of ETS 300 019-2-4	Shock Spectrum Type II, 6mS duration, 250m/s ² 500 bumps in 6 directions.
Solderability	EIA/IPC/JEDEC J-STD-002, Test A and A1	SnPb (Test A) For leaded solderability the parts are conditioned in a steam ager for 8 hours ± 15 min. at a temperature of 93°C ± 3 °C. Dipped in solder at 245°C ± 5 °C for 5 (+0/-0.5) seconds. Pb-free (Test A1) For lead free solderability the parts are conditioned in a steam ager for 8 hours ± 15 min. at a temperature of 93°C ± 3 °C. Dipped in solder at 255°C ± 5 °C for 5 (+0/-0.5) seconds.
Solder heat	JEDEC JESD22-B106	The test sample is subjected to a molten solder bath at $270^{\circ}C \pm 5^{\circ}C$ for 7 (+2/-0) seconds.
Solder heat (hand)	MIL-STD-202 Method 210, Condition A	The soldering iron is heated to $350^{\circ}C \pm 10^{\circ}C$ and applied to the terminations for a duration of 4 to 5 seconds.
Solvent cleaning	Resistance to cleaning agents	Solvent – Novec 71IPA & Topklean EL-20A. Pulsed ultrasonic immersion 45°C - 60°C.
Solvent Resistance	MIL-STD-883 Method 2015	Separate samples subjected to IPA cleaning.
Lead Integrity (Adhesion)	MIL-STD-883 Method 2025	Leads are bent through 90° until a fracture occurs.
Lead Integrity (Fatigue)	MIL-STD-883 Method 2004, Condition B_2	The leads are bent to an angle of 15°. Each lead is subjected to 3 cycles.
Lead Integrity (Tension/Pull)	MIL-STD-883 Method 2004, Condition A	Pull of 0.227kg applied for 30 seconds. The force is then increased until the pins snap.
Aqueous wash	Resistance to wash process	Parts washed in an aqueous/ultrasonic process, in a suitable chemical for 30 mins at a con- trolled temperature. Followedby a towns water wash at low pressure and a demineralised water wash at low pressure. Dried in a vacuum oven.

PART NUMBER STRUCTURE



MGJ1 SIP Series

ple & Noise (Characterisation Method					
ple and noise	measurements are performed with the following test configuration.					
C1	1µF X7R multilayer ceramic capacitor, voltage rating to be a minimum of 3 times the output voltage of the DC-DC converter					
C2	10μ F tantalum capacitor, voltage rating to be a minimum of 1.5 times the output voltage of the DC-DC converter with an ESR of less than $100m\Omega$ at 100 kHz					
C3	100nF multilayer ceramic capacitor, general purpose					
R1	450Ω resistor, carbon film, \pm 1% tolerance					
R2	50Ω BNC termination					
T1	3T of the coax cable through a ferrite toroid					
RLOAD	Resistive load to the maximum power rating of the DC-DC converter. Connections should be made via twisted wires					
Measured va	lues are multiplied by 10 to obtain the specified values.					
ferential Mo	de Noise Test Schematic					

MGJ1 SIP Series

5.2kVDC Isolated 1W Gate Drive DC-DC Converters

APPLICATION NOTES

Minimum load

The minimum load to meet datasheet specification is 10% of the full rated load across the specified input voltage range. Lower than 10% minimum loading will result in an increase in output voltage, which may rise to typically 1.5 times the specified output voltage if the output load falls to 0%.

Gate Drive Applications Advisory Note

For general guidance for product usage in gate drive applications please refer to "gate drive application notes".


MGJ1DXX0603MC Capacitive loading and start up

The typical start up for single output variants, using a 56 μ F capacitor is 5mS. The start up behaviour of the +Vout and -Vout rails of a dual output DC-DC using a divider network depends significantly on the additional capacitance added to the outputs. This is because the two capacitors behave as a capacitive divider. If the two capacitors are equal and 9V is applied across them the outputs will initially start as +/-4.5V.


There will be a settling time while the divider circuit adjusts to the correct voltages, to calulcate the approixmate value please refer to the following formula.

Settling time \approx 3000 x C (s)

So, for instance if a maximum capacitance of 100uF is applied to each output the settling time will be about 300ms.



To avoid spurious gate pulses it is recommended that the PWM gate signal is not applied until after the settling time has ended. An alternative method to reduce the settling time is to adjust the values of the additional capacitance so that the CV products are equal. i.e. $C3 \times 6V = C4 \times 3V$. So, for instance if a maximum capacitance of 75uF is applied to the +6V output and 150uF is applied to the -3V output the settling time is greatly reduced.



MGJ1 SIP Series


5.2kVDC Isolated 1W Gate Drive DC-DC Converters

APPLICATION NOTES (Continued)


Capacitive loading and start up

Typical start up times for this series, with a typical input voltage rise time of 2.2μ s and output capacitance of 10μ F, are shown in the table below. The product series will start into capacitance up to 47μ F with increased start times.


	Start-up time
	ms
MGJ1D052005SC	7
MGJ1D121503SC	4
MGJ1D121505SC	5
MGJ1D121802SC	6
MGJ1D122005SC	7
MGJ1D151509SC	5
MGJ1D152005SC	6
MGJ1D241503SC	2
MGJ1D241505SC	5
MGJ1D241509SC	5
MGJ1D241802SC	5
MGJ1D242005SC	5




MGJ1 SIP Series




MGJ1 SIP Series



MGJ1 SIP Series




MGJ1 SIP Series




MGJ1 SIP Series

5.2kVDC Isolated 1W Gate Drive DC-DC Converters



TEMPERATURE DERATING GRAPHS




MGJ1 SIP Series

5.2kVDC Isolated 1W Gate Drive DC-DC Converters


POSITIVE OUTPUT VOLTAGE TOLERANCE ENVELOPES

The voltage tolerance envelopes show typical load regulation characteristics for this product series. The tolerance envelope is the maximum output voltage variation due to changes in output loading and set point accuracy. 052005 XX0603 7% 5% 4% **Dutput Voltage** Output Voltage 3% 2% -3% -4% -5% . 50 25 50 75 25 75 10 100 10 100 Output Load Current (%) Output Load Current (%) 121503 121505 6% 5% **Output Voltage Output Voltage** 2% 2% 1% 1% -5% -5% 10 25 50 75 100 10 25 50 75 100 Output Load Current (%) Output Load Current (%) 121802 122005 11% 5% Output Voltage Output Voltage 5% 2% 2% 0% 0% -5% 10 25 50 75 100 10 25 50 75 100 Output Load Current (%) Output Load Current (%)

MGJ1 SIP Series



MGJ1 SIP Series



MGJ1 SIP Series

5.2kVDC Isolated 1W Gate Drive DC-DC Converters


		+ C1 			DC DC	
		Inductor			Capacitor	
	L, µH	SMD	Through Hole	C, µF	SMD	Through Hole
MGJ1D050603SC	10	84103C	13R103C	4.7	GRM21BC71E475KE11L	RCER71H475K3K1H03B
MGJ1D052005SC	10	84103C	13R103C	4.7	GRM21BC71E475KE11L	RCER71H475K3K1H03B
MGJ1D120603SC	10	84103C	13R103C	4.7	GRM21BC71E475KE11L	RCER71H475K3K1H03B
MGJ1D121503SC	10	84103C	13R103C	4.7	GRM21BC71E475KE11L	RCER71H475K3K1H03B
MGJ1D121505SC	10	84103C	13R103C	4.7	GRM21BC71E475KE11L	RCER71H475K3K1H03B
MGJ1D121802SC	10	84103C	13R103C	4.7	GRM21BC71E475KE11L	RCER71H475K3K1H03B
MGJ1D122005SC	10	84103C	13R103C	4.7	GRM21BC71E475KE11L	RCER71H475K3K1H03B
MGJ1D151509SC	10	84103C	13R103C	4.7	GRM21BC71E475KE11L	RCER71H475K3K1H03B
MGJ1D152005SC	10	84103C	13R103C	4.7	GRM21BC71E475KE11L	RCER71H475K3K1H03B
MGJ1D241503SC	10	84103C	13R103C	4.7	GRM21BC71H475KE11L	RCER71H475K3K1H03B
MGJ1D241505SC	10	84103C	13R103C	4.7	GRM21BC71H475KE11L	RCER71H475K3K1H03B
MGJ1D241509SC	10	84103C	13R103C	4.7	GRM21BC71H475KE11L	RCER71H475K3K1H03B
MGJ1D241802SC	10	84103C	13R103C	4.7	GRM21BC71H475KE11L	RCER71H475K3K1H03B
MGJ1D242005SC	10	84103C	13R103C	4.7	GRM21BC71H475KE11L	RCER71H475K3K1H03B
M	IGJ1D050603S	C (Quasi-Peak)			MGJ1D050603SC	(Average)
80				80 -		
70				70 -		
60				60 -		


20 ALA LINE UNA 10 0 1.00E+05 1.00E+06 1.00E+07 1.00E+08 Frequency (Hz) MGJ1D052005SC (Quasi-Peak)

1.00E+06

Frequency (Hz)

1.00E+07





www.murata.com

80

70

60

50

40

30


20

10 0

1.00E+05

dBuV

MGJ1 SIP Series




www.murata.com

KDC_MGJ1_SIP_A01 Page 18 of 22

MGJ1 SIP Series

5.2kVDC Isolated 1W Gate Drive DC-DC Converters




www.murata.com

KDC_MGJ1_SIP_A01 Page 19 of 22

MGJ1 SIP Series


5.2kVDC Isolated 1W Gate Drive DC-DC Converters



www.murata.com

KDC_MGJ1_SIP_A01 Page 20 of 22

MGJ1 SIP Series



MGJ1 SIP Series

5.2kVDC Isolated 1W Gate Drive DC-DC Converters

DISCLAIMER

Unless otherwise stated in the datasheet, all products are designed for standard commercial and industrial applications and NOT for safety-critical and/or life-critical applications.

Particularly for safety-critical and/or life-critical applications, i.e. applications that may directly endanger or cause the loss of life, inflict bodily harm and/or loss or severe damage to equipment/property, and severely harm the environment, a prior explicit written approval from Murata is strictly required. Any use of Murata standard products for any safety-critical, life-critical or any related applications without any prior explicit written approval from Murata shall be deemed unauthorised use.

These applications include but are not limited to:

- Aircraft equipment
- Aerospace equipment
- Undersea equipment
- Power plant control equipment
- Medical equipment
- Transportation equipment (automobiles, trains, ships, etc.)
- Traffic signal equipment
- Disaster prevention / crime prevention equipment
- Data Processing equipment

Murata makes no express or implied warranty, representation, or guarantee of suitability, fitness for any particular use/purpose and/or compatibility with any application or device of the buyer, nor does Murata assume any liability whatsoever arising out of unauthorised use of any Murata product for the application of the buyer. The suitability, fitness for any particular use/purpose and/or compatibility of Murata product with any application or device of the buyer remain to be the responsibility and liability of the buyer.

Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm, and take appropriate remedial actions. Buyer will fully indemnify and hold Murata, its affiliated companies, and its representatives harmless against any damages arising out of unauthorised use of any Murata products in any safety-critical and/ or life-critical applications.

Remark: Murata in this section refers to Murata Manufacturing Company and its affiliated companies worldwide including, but not limited to, Murata Power Solutions.



This product is subject to the following <u>operating requirements</u> and the <u>Life and Safety Critical Application Sales Policy</u>: Refer to: https://www.murata.com/en-eu/products/power/requirements

Murata Power Solutions (Milton Keynes) Ltd. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The described herein do not imply the granting of licenses to make, use, or sell equipment constructed in accordance therewith. Specifications are subject to change without notice.