

Product Search Data Sheet

LFL183G55TC2B908

In Production Recommended RoHS REACH

Applications

Unsuitable	Please be sure to read and comply with	
Applications	these "Precautions for use."	
Specific Applications	Consumer equipment,Industrial Equipment,Medical equipment [GHTF A/B],Mobile Electronics Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual	
Recommended	Product. Consumer equipment,Industrial Equipment,Medical equipment [GHTF	
Applications	A/B],Mobile Electronics	


Note: This datasheet may be out of date. Please download the latest datasheet of LFL183G55TC2B908 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-gb/products/productdetail?partno=LFL183G55TC2B908

Packaging Information

Packaging	Specifications	Standard Packing Quantity
-	180mm Paper Tape	4000

Appearance & Shape



1 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





Product Search Data Sheet

LFL183G55TC2B908

Note: This datasheet may be out of date. Please download the latest datasheet of LFL183G55TC2B908 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-gb/products/productdetail?partno=LFL183G55TC2B908

Features

small, low-profiled, lightweight chip filters based on ceramic multilayer technology.

Offering stable high selectivity up to very high frequency.

- 1. Low loss
- 2. Ultra-small, low-profiled, lightweight low-pass filters.

3. Ideal for removing high-frequency harmonics at power amplifier and IF stage.

- 4. Available in tape and reel packings for automatic mounting.
- 5. Absolutely no adjustment required.
- 6. Reflow solderable.

7. Center frequencies and responses are ready for customization. Samples are available in a short lead time.

2 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering





Product Search Data Sheet

LFL183G55TC2B908

Note: This datasheet may be out of date. Please download the latest datasheet of LFL183G55TC2B908 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-gb/products/productdetail?partno=LFL183G55TC2B908

Specifications

Applications	WIMAX
Nominal Center Frequency (fo)	3550.00MHz
Bandwidth(BW)	fo±250.00MHz
Insertion Loss in BW I)	0.45dB max. (at 25°C)
Insertion Loss in BW II)	0.55dB max. (-40 to +85°C)
Attenuation(Absolute Value)	17.0dB min. at 6600.00 to 7600.00MHz
Attenuation(Absolute Value)	20.0dB min. at 9900.00 to
)	11400.00MHz
VSWR(max.)	1.9
Characteristic Impedance (Nom.)	50Ω
Power Capacity	3W
Operating Temperature Range	-40°C to 85°C
L x W (size)	1.60x0.80mm
Thickness(max.)	0.7mm

3 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

