

FDA1254-H-1R2M#

Note: This datasheet may be out of date.

Please download the latest datasheet of FDA1254-H-1R2M# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-gb/products/productdetail?partno=FDA1254-H-1R2M%23

"#"at the end indicates the package specification code.
















Applications

Unsuitable	Please be sure to read and comply with	
Applications	these "Precautions for use."	
	Consumer equipment,Medical	
	equipment [GHTF A/B/C] except for	
	implant & surgery & auto injector,	
	Industrial equipment except for	
	transportation & facility & energy	
	equipment	
Specific	Please refer to Our Website and	
Applications	specifications, etc. for information about	
	the performance, functions, quality,	
	management, and safety required for	
	the above applications, and use	
	Products after confirming the	
	performance and reliability of the actual	
	Product.	
Recommended	Consumer equipment	
Applications		



Appearance & Shape







Notices

Rated current (Isat) is specified when the decrease of the initial inductance value at 20%. Rated current (Itemp) is specified when temperature of the inductor is raised 40°C by DC current.



References

Packaging	Specifications	Standard Packing Quantity
=P3	330Embossed Tape	500

Mass (typ.)	
1 piece	4.361g

1 of 3

Attentior

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





FDA1254-H-1R2M#

Note: This datasheet may be out of date.

Please download the latest datasheet of FDA1254-H-1R2M# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-gb/products/productdetail?partno=FDA1254-H-1R2M%2

"#"at the end indicates the package specification code.



Specifications

L size	12.6±0.3mm
W size	12.5±0.3mm
T size	5.4mm
Size code inch (mm)	5049 (126125)
Inductance	1.2µH±20%
Inductance Test Frequency	0.1MHz
Rated current (Isat) (Based on Inductance change)	20200mA
Rated current (Itemp) (Based on Temperature rise)	18400mA
Max. of DC resistance	0.0026Ω
Operating Temperature Range (Self-temperature rise is included)	-40°C to 125°C
Class of magnetic shield	Shielded (Metal Alloy)
Absolute maximum voltage	30Vdc
Brand	Murata
Dimensions	A:13.5mmB:1.8mmC:7.7mm
Series	FDA1254

2 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

 $2. This \ data{sheet has only typical specifications because there is no space for \ detailed \ specifications.}$

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





FDA1254-H-1R2M#

Note: This datasheet may be out of date.


Please download the latest datasheet of FDA1254-H-1R2M# from the official website of Murata Manufacturing Co., Ltd.


http://www.murata.com/en-gb/products/productdetail?partno=FDA1254-H-1R2M%23

"#"at the end indicates the package specification code.



Characteristic Data





Impedance - Current Characteristics

Temperature Increase Characteristic

3 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

